

INNOVATIONS

CREATIVITY MEETS EVOLUTIONARY DESIGN



THE FRANKLIN RESTORATION COLLECTION

CATALOG 2017A



INNOVATIONS

CREATIVITY MEETS EVOLUTIONARY DESIGN

INNOVATIONS LIGHTING was founded in 2014 in Westchester County, New York. This new venture is a landmark of my 40th year in the lighting industry. My career began with the iconic Geringer & Sons, founded in 1913, which later led to my partnership with Leonard Geringer, my mentor. From this experience I have learned a simple strategy for success: create a quality product at a fair price, make a commitment to service and the customer will repeatedly purchase with confidence.

This new company showcases the highest quality in design and material while promoting versatility for your exact needs. In this catalog, you will find over 4,000 combinations of lighting styles, finishes, glass shapes, colors and sizes.

I welcome you to enjoy this second edition of the Innovations product line. You can look forward to many more product designs in the future, but always keep in mind that our customer service is the key not only to our success but yours as well. We look forward to serving you.

Robert B. Marash

INNOVATIONS LIGHTING
3199 ALBANY POST ROAD SUITE 307/310
BUCHANAN, NY 10511

PH: 914-734-8076
FX: 413-740-0394

SALES@INNOVATIONSLIGHTING.COM
WWW.INNOVATIONSLIGHTING.COM

INNOVATIONS LIGHTING QUALITY FEATURES LIFETIME WIRING AND TWO YEAR FINISH WARRANTY

ALL FINISHES ARE EITHER
ELECTROPLATED OR HAND
PAINTED DEPENDING ON
WHICH FINISH YOU SELECT

2MM HEAVY CAST BACKPLATE
WITH ENGRAVED LINE
AND SOLID NECK

SOLID BRASS 180 DEGREE ADJUSTABLE SWIVEL
INTERNAL TEETH LOCK IN AT 5 DEGREE INTERVALS FOR THE
PERFECT POSITION YOU DESIRE

ONE PIECE CAST
SOCKET COVER
WITH ENGRAVING

1.5 MM HEAVY METAL HOLDER
WITH HEAVY KNURLED SCREWS

PORCELAIN SOCKET
WITH 392 DEGREE WIRING
100 WATT UL/CUL RATED





OVER 4,000 POSSIBILITIES

INNOVATIONS

CREATIVITY MEETS EVOLUTIONARY DESIGN

“HOW IT WORKS”
SIMPLY PICK:

MODEL

+

FINISH

+

GLASS



BB
BRUSHED BRASS



BAB
BLACK/ ANTIQUE BRASS



AC
ANTIQUÉ COPPER



OB
OIL RUBBED BRONZE



PC
POLISHED CHROME



PN
POLISHED NICKEL



SN
SATIN NICKEL



M1-7* M9* M10-SN M11-OB



G61 G62 G63 G64



G51 G52 G53 G54



G41 G42 G43 G44



G71 G72 G73 G74



G142 G146 G165



G171 G172 G173



G182 G184 G192 G194



G2

*SEE CATALOG FOR
AVAILABLE FINISHES



ALL CORD FIXTURES HAVE 10' OF BLACK TEXTURED FABRIC WIRE



200C-OB(OONLY)-R RED WIRE



200C-OB(OONLY)-OR ORANGE WIRE



211NH/3-AC*

10" DIA x 3 LIGHTS (+1 OPTIONAL)
CORD MOUNT

211-* 10" PAN ONLY WITH HARDWARE
ADAPTABLE TO CORD HUNG FIXTURES

200C-OB* WITH 4 1/2" CANOPY
CORD MOUNT

212NH/6-PN* 14" DIA x 6 LIGHT(+1 OPTIONAL)
CORD MOUNT

212-* 17" PAN ONLY WITH HARDWARE ADAPTABLE
TO CORD HUNG FIXTURES

199-* NO CANOPY (for 211
and 212 models)



207NH-SN*
15" DIA x 6" HT
SWIVEL STEM MOUNT

ALL STEM MOUNT FIXTURES ARE
SUPPLIED WITH 6"+12"+12" STEM
SET ALONG WITH 10' OF WIRE

ADDITIONAL STEMS ARE
AVAILABLE

90 DEGREE HANG STRAIGHT
SWIVEL WITH 4 1/2" DIA. CAST
CANOPY

CAN BE USED ON VAULTED
CEILINGS

214NH-BAB*

48" LONG x 2" W x 5" HT
SWIVEL STEM MOUNT



200S-BB*

2" DIA x 4" HT
SWIVEL STEM MOUNT

206NH-PN*

2" DIA x 7" HT
SWIVEL STEM MOUNT



213NH-OB*

36" LONG x 2" W x 5" HT
SWIVEL STEM MOUNT





200NH-F-SN* 4 1/2" DIA x 9" HT



517NH-C-PN* 4 1/2" DIA x 5" HT



203NH-BAB* 4 1/2" W x 6" HT x 5" EXT
(SHOWN WITH EXTRA BACKPLATE BP-5-AB*
SEE PAGE 39 FOR MORE INFORMATION)

BP-5-AB*



562NH-3C-PC* 10" DIA x 5" HT

ALL PRODUCTS ARE MADE
WITH CAST COMPONENTS


SOLID BRASS SWIVELS
4 1/2" DIA. CAST CANOPY



203NH-BB*



208NH-AC*
12" W x 5" HT x 5" EXT



CAN BE USED AS
CEILING MOUNT



205NH-OB* 30" W x 5" HT x 4" EXT



215NH-SN* 42" W x 5" HT x 4" EXT

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED

*- AVAILABLE IN **7** FINISHES

GENESEO SERIES



ALL CORD FIXTURES HAVE 10'
OF BLACK
TEXTURED FABRIC WIRE

211/3-SN*-G165
14" DIA x 3 LIGHTS (+1 OPTIONAL)
(10" PAN) CORD MOUNT



201C-SN*-G165
6 1/2" DIA x 12" HT
(4 1/2" CANOPY) CORD MOUNT



212/6-OB*-G165
18" DIA x 6 LIGHT (+1 OPTIONAL)
(14" PAN) CORD MOUNT

ALL STEM MOUNT FIXTURES ARE
SUPPLIED WITH 6"+12"+12" STEM
SET ALONG WITH 10' OF WIRE

ADDITIONAL STEMS ARE
AVAILABLE

90 DEGREE HANG STRAIGHT
SWIVEL WITH 4 1/2" DIA. CAST
CANOPY

CAN BE USED ON VAULTED
CEILINGS

CLEAR CRACKLE
HAND-BLOWN
HEAVY GLASS



207-SN*-G165
19" DIA x 14" HT
SWIVEL STEM MOUNT

2015-AC*-G165
6 1/2" DIA x 11" HT
SWIVEL STEM MOUNT



206-OB*-G165
6 1/2" DIA x 15" HT
SWIVEL STEM MOUNT

213-SN*-G165
36" LONG x 6 1/2" W x 14" HT
SWIVEL STEM MOUNT



214-BAB*-G165
48" LONG x 6 1/2" W x 14" HT
SWIVEL STEM MOUNT





201F-AC*-G165
6 1/2" DIA x 17" HT



517-1CH-SN*-G165
6 1/2" DIA x 14" HT



203-BB*-G165
6 1/2" W x 14" HT x 9" EXT

ALL PRODUCTS ARE MADE WITH CAST COMPONENTS

SOLID BRASS SWIVELS

4 1/2" DIA. CAST CANOPY

CLEAR CRACKLE
HAND-BLOWN
HEAVY GLASS

203-BAB*-G165



208-SN*-G165
17" W x 12" HT x 8" EXT



205-PN*-G165 30"W x 14" HT x 8" EXT



CAN BE USED AS
CEILING MOUNT



215-OB*-G165 42" W x 14" HT x 8" EXT

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED

*- AVAILABLE IN **7** FINISHES

CHATHAM SERIES



ALL CORD FIXTURES HAVE 10' OF BLACK TEXTURED FABRIC WIRE

211/3-SN*-G146 MERCURY PLATED
12" DIA x 3 LIGHTS (+1 OPTIONAL)
(10" PAN) CORD MOUNT



201C-AC*-G146 MERCURY PLATED
6" DIA x 9" HT
(4 1/2" CANOPY) CORD MOUNT



212/6-SN*-G142 CLEAR
16" DIA x 6 LIGHTS (+1 OPTIONAL)
(14" PAN) CORD MOUNT

ALL STEM MOUNT FIXTURES ARE SUPPLIED WITH 6"+12"+12" STEM SET ALONG WITH 10' OF WIRE

ADDITIONAL STEMS ARE AVAILABLE

90 DEGREE HANG STRAIGHT SWIVEL WITH 4 1/2" DIA. CAST CANOPY

CAN BE USED ON VAULTED CEILINGS

GLASS AVAILABLE IN:
G142-CLEAR
G146-MERCURY PLATED



2015-SN*-G142 CLEAR
6" DIA x 10" HT
SWIVEL STEM MOUNT



207-PN*-G146 MERCURY PLATED
18" DIA x 14" HT
SWIVEL STEM MOUNT



213-BB*-G146 MERCURY PLATED
36" LONG x 6" W x 12" HT
SWIVEL STEM MOUNT



214-SN*-G142 CLEAR
48" LONG x 6" W x 12" HT
SWIVEL STEM MOUNT

206-OB*-G142 CLEAR
6" DIA x 14" HT
SWIVEL STEM MOUNT

*- AVAILABLE IN **6** FINISHES

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED



201F-SN*-G142 CLEAR
6" DIA x 15" HT



517-1CH-AC*-G146 MERCURY PLATED
6" DIA x 11" HT



203-OB*-G146 MERCURY PLATED
6" W x 12" HT x 8" EXT



203-PN*-G142 CLEAR

GLASS AVAILABLE IN:
G142-CLEAR
G146-MERCURY PLATED

ALL PRODUCTS ARE MADE
WITH CAST COMPONENTS
SOLID BRASS SWIVELS
4 1/2" DIA. CAST CANOPY



208-PC*-G142 CLEAR
16" W x 12" HT x 8" EXT



205-BAB*-G146 MERCURY PLATED
30" W x 12" HT x 7" EXT



CAN BE USED AS
CEILING MOUNT



215-PN*-G142 CLEAR
42" W x 12" HT x 7" EXT

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED

*- AVAILABLE IN **7** FINISHES



211/3-SN*-G184 SEEDY
12" DIA x 3 LIGHTS (+1 OPTIONAL)
(10" PAN) CORD MOUNT



201C-AC*-G182 CLEAR
6" DIA x 10" HT
(4 1/2" CANOPY) CORD MOUNT



212/6-OB*-G184 SEEDY
16" DIA x 6 LIGHTS (+1 OPTIONAL)
(14" PAN) CORD MOUNT

ALL CORD FIXTURES HAVE 10'
OF BLACK
TEXTURED FABRIC WIRE




207-SN*-G182 CLEAR
18" DIA x 13" HT
SWIVEL STEM MOUNT

213-SN*-G184 SEEDY
36" LONG x 6" W x 11" HT
SWIVEL STEM MOUNT

2015-BAB*-G184 SEEDY
6" DIA x 10" HT
SWIVEL STEM MOUNT

206-SN*-G182 CLEAR
6" DIA x 14" HT
SWIVEL STEM MOUNT



214-OB*-G182 CLEAR
48" LONG x 6" W x 11" HT
SWIVEL STEM MOUNT

ALL STEM MOUNT FIXTURES ARE
SUPPLIED WITH 6"+12"+12" STEM
SET ALONG WITH 10' OF WIRE

ADDITIONAL STEMS ARE
AVAILABLE

90 DEGREE HANG STRAIGHT
SWIVEL WITH 4 1/2" DIA. CAST
CANOPY

CAN BE USED ON VAULTED
CEILINGS

GLASS AVAILABLE IN:

G182-CLEAR
G184-SEEDY

*- AVAILABLE IN **6** FINISHES

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED



201F-AC*-G182 CLEAR
6" DIA x 16" HT

GLASS AVAILABLE IN:

G182-CLEAR
G184-SEEDY



517-1CH-BAB*-G184 SEEDY
6" DIA x 13" HT



203-BAB*-G184 SEEDY
6" W x 13" HT x 8" EXT

ALL PRODUCTS ARE MADE
WITH CAST COMPONENTS

SOLID BRASS SWIVELS

4 1/2" DIA. CAST CANOPY

203-SN*-G184 SEEDY



208-SN*-G182 CLEAR
16" W x 13" HT x 8" EXT



CAN BE USED AS
CEILING MOUNT



205-PC*-G184 SEEDY
30" W x 12" HT x 7" EXT



215-OB*-G182 CLEAR
42" W x 12" HT x 7" EXT

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED

*- AVAILABLE IN **7** FINISHES



211/3-SN*-G194 SEEDY
12" DIA x 3 LIGHTS (+1 OPTIONAL)
(10" PAN) CORD MOUNT



201C-SN*-G192 CLEAR
6" DIA x 10" HT
(4 1/2" CANOPY) CORD MOUNT

ALL CORD FIXTURES HAVE 10'
OF BLACK
TEXTURED FABRIC WIRE



212/6-OB*-G194 SEEDY
16" DIA x 6 LIGHTS (+1 OPTIONAL)
(14" PAN) CORD MOUNT

ALL STEM MOUNT FIXTURES ARE
SUPPLIED WITH 6"+12"+12" STEM
SET ALONG WITH 10' OF WIRE


ADDITIONAL STEMS ARE
AVAILABLE

90 DEGREE HANG STRAIGHT
SWIVEL WITH 4 1/2" DIA. CAST
CANOPY

CAN BE USED ON VAULTED
CEILINGS


GLASS AVAILABLE IN:

G192-CLEAR
G194-SEEDY



207-SN*-G192 CLEAR
18" DIA x 13" HT
SWIVEL STEM MOUNT

201C-BAB*-G194 SEEDY
6" DIA x 10" HT
SWIVEL STEM MOUNT



213-SN*-G194 SEEDY
36" LONG x 6" W x 12" HT
SWIVEL STEM MOUNT



214-OB*-G192 CLEAR
48" LONG x 6" HT x 12" HT
SWIVEL STEM MOUNT

206-SN*-G192 CLEAR
6" DIA x 13" HT
SWIVEL STEM MOUNT





201F-AC*-G194 SEEDY
6" DIA x 15" HT



517-1CH-SN*-G194 SEEDY
6" DIA x 11" HT



203-BAB*-G194 SEEDY
6" W x 12" HT x 8" EXT



203-PN*-G192 CLEAR

GLASS AVAILABLE IN:

G192-CLEAR
G194-SEEDY

ALL PRODUCTS ARE MADE
WITH CAST COMPONENTS


SOLID BRASS SWIVELS
4 1/2" DIA. CAST CANOPY



208-PC*-G192 CLEAR
16" W x 12" HT x 7" EXT



205-OB*-G194 SEEDY
30" W x 12" HT x 7" EXT



CAN BE USED AS
CEILING MOUNT



215-PN*-G192 CLEAR
42" W x 12" HT x 7" EXT

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED

*- AVAILABLE IN **7** FINISHES



211/3-SN*-G172 CLEAR
14" DIA x 3 LIGHTS (+1 OPTIONAL)
(10" PAN) CORD MOUNT



201C-BAB*-G171
CASED MATTE WHITE
7" DIA x 8" HT
(4 1/2" CANOPY) CORD MOUNT



212/6-OB*-G172 CLEAR
20" DIA x 6 LIGHTS (+1 OPTIONAL)
(14" PAN) CORD MOUNT

ALL CORD FIXTURES HAVE 10'
OF BLACK
TEXTURED FABRIC WIRE



2015-SN*-G172 CLEAR
7" DIA x 9" HT
SWIVEL STEM MOUNT

ALL STEM MOUNT FIXTURES ARE
SUPPLIED WITH 6"+12"+12" STEM
SET ALONG WITH 10' OF WIRE

ADDITIONAL STEMS ARE
AVAILABLE

90 DEGREE HANG STRAIGHT
SWIVEL WITH 4 1/2" DIA. CAST
CANOPY

CAN BE USED ON VAULTED
CEILINGS



GLASS AVAILABLE IN:
G171-CASED MATTE WHITE
G172-CLEAR
G173-PLATED SMOKE



206-OB*-G173
PLATED SMOKE
7" DIA x 12" HT
SWIVEL STEM MOUNT

213-AC*-G173 PLATED SMOKE
36" W x 7" HT x 10" HT
SWIVEL STEM MOUNT



207-SN*-G171
CASED MATTE WHITE
20" DIA x 11" HT
SWIVEL STEM MOUNT

214-SN*-G171 CASED MATTE WHITE
48" W x 7" HT x 10" HT
SWIVEL STEM MOUNT



*- AVAILABLE IN **6** FINISHES

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED



201F-SN*-G172 CLEAR
7" DIA x 13" HT

GLASS AVAILABLE IN:
G171-CASED MATTE WHITE
G172-CLEAR
G173-PLATED SMOKE



517-1CH-AC*-G173 PLATED SMOKE
7" DIA x 9" HT



203-OB*-G171 CASED MATTE WHITE
7" W x 9" HT x 10" EXT



203-BAB*-G172 CLEAR

ALL PRODUCTS ARE MADE
WITH CAST COMPONENTS

SOLID BRASS SWIVELS

4 1/2" DIA. CAST CANOPY



208-PC*-G172 CLEAR
18" W x 10" HT x 8" EXT



205-PN*-G173 PLATED SMOKE
30" W x 10" HT x 9" EXT



CAN BE USED AS
CEILING MOUNT



215-SN*-G171 CASED MATTE WHITE
42" x 10" HT x 9" EXT

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED

*- AVAILABLE IN **7** FINISHES





SMALL CONE SERIES



211/3-BB*-G61 CASED MATTE WHITE
12" DIA x 3 LIGHTS (+1 OPTIONAL)
(10" PAN) CORD MOUNT



201C-OB*-G64 SEEDY
6" DIA x 9" HT
(4 1/2" CANOPY) CORD MOUNT

ALL CORD FIXTURES HAVE 10'
OF BLACK
TEXTURED FABRIC WIRE



212/6-BAB*-G63 PLATED SMOKE
16" DIA x 6 LIGHTS (+1 OPTIONAL)
(14" PAN) CORD MOUNT



2015-SN*-G62 CLEAR
6" DIA x 9" HT
SWIVEL STEM MOUNT

ALL STEM MOUNT FIXTURES ARE
SUPPLIED WITH 6"+12"+12" STEM
SET ALONG WITH 10' OF WIRE

ADDITIONAL STEMS ARE
AVAILABLE

90 DEGREE HANG STRAIGHT
SWIVEL WITH 4 1/2" DIA. CAST
CANOPY

CAN BE USED ON VAULTED
CEILING



213-PN*-G63 PLATED SMOKE
36" LONG x 6" W x 11" HT
SWIVEL STEM MOUNT

GLASS AVAILABLE IN:
G61-CASED MATTE WHITE
G62-CLEAR
G63-PLATED SMOKE
G64-SEEDY

206-PN*-G61
CASED MATTE WHITE
6" DIA x 12" HT
SWIVEL STEM MOUNT

214-AC*-G62 CLEAR
48" LONG x 6" W x 11" HT
SWIVEL STEM MOUNT

207-SN*-G64 CLEAR
18" DIA x 14" HT
SWIVEL STEM MOUNT



*- AVAILABLE IN **6** FINISHES

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED

SMALL CONE SERIES



201F-SN*-G63 PLATED SMOKE
6" DIA x 15" HT



517-1CH-PC*-G61 CASED MATTE WHITE
6" DIA x 9" HT



203-BB*-G64 SEEDY
6" W x 12" HT x 8" EXT



203-BAB*-G63 PLATED SMOKE

ALL PRODUCTS ARE MADE WITH CAST COMPONENTS

SOLID BRASS SWIVELS

4 1/2" DIA. CAST CANOPY

GLASS AVAILABLE IN:

G61-CASED MATTE WHITE

G62-CLEAR

G63-PLATED SMOKE

G64-SEEDY



208-SN*-G61 CASED MATTE WHITE
16" W x 12" HT x 7" EXT



205-AC*-G63 CASED SMOKE
30" W x 12" HT x 7" EXT



CAN BE USED AS CEILING MOUNT



215-PC*-G62 CLEAR
42" W x 12" HT x 7" EXT

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED

*- AVAILABLE IN **7** FINISHES



211/5-AC*-G43 PLATED SMOKE
14" DIA x 3 LIGHTS (+1 OPTIONAL)
(10" PAN) CORD MOUNT



2 SIZES
8" AND 12"

201C-OB*-G42 CLEAR
8" DIA x 11" HT
(4 1/2" CANOPY) CORD MOUNT
201C-OB*-G42L CLEAR
12" DIA x 15" HT



212/6-BB*-G41 CASED MATTE WHITE
18" DIA x 6 LIGHTS (+1 OPTIONAL)
(14" PAN) CORD MOUNT

ALL CORD FIXTURES HAVE 10'
OF BLACK
TEXTURED FABRIC WIRE

GLASS AVAILABLE IN:
G41-CASED MATTE WHITE
G42-CLEAR
G43-PLATED SMOKE
G44-SEEDY



2 SIZES
8" AND 12"

206-SN*-G44L SEEDY
12" DIA x 18" HT
SWIVEL STEM MOUNT
206-SN*-G44 SEEDY
8" DIA x 14" HT



207-PN*-G42 CLEAR
22" DIA x 14" HT
SWIVEL STEM MOUNT

ALL STEM MOUNT FIXTURES ARE
SUPPLIED WITH 6"+12"+12" STEM
SET ALONG WITH 10' OF WIRE

ADDITIONAL STEMS ARE
AVAILABLE

90 DEGREE HANG STRAIGHT
SWIVEL WITH 4 1/2" DIA. CAST
CANOPY

CAN BE USED ON VAULTED
CEILINGS



213-BAB*-G44 SEEDY
36" LONG x 8" W x 12" HT
SWIVEL STEM MOUNT



214-SN*-G43 PLATED SMOKE
48" LONG x 8" W x 12" HT
SWIVEL STEM MOUNT

201S-BAB*-G41 CASED MATTE WHITE
8" DIA x 10" HT
SWIVEL STEM MOUNT
201S-BAB*-G41L CASED MATTE WHITE
12" DIA x 15" HT

*- AVAILABLE IN **6** FINISHES

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED



2 SIZES
8" AND 12"

201F-SN*-G41 CASED MATTE WHITE
8" DIA x 16" HT
201F-SN*-G41L CASED MATTE WHITE
12" DIA x 18" HT



517-1CH-PC*-G43 PLATED SMOKE
8" DIA x 10" HT
517-1CH-PC*-G43L PLATED SMOKE
12" DIA x 14" HT



203-OB*-G44 SEEDY
8" W x 13" HT x 9" EXT



203-AC*-G41 CASED MATTE WHITE

ALL PRODUCTS ARE MADE WITH CAST COMPONENTS

SOLID BRASS SWIVELS

4 1/2" DIA. CAST CANOPY

GLASS AVAILABLE IN:

G41-CASED MATTE WHITE

G42-CLEAR

G43-PLATED SMOKE

G44-SEEDY



208-BAB*-G43 PLATED SMOKE
18" W x 12" HT x 10" EXT



205-BB*-G42 CLEAR
34" W x 12" HT x 9" EXT



CAN BE USED AS CEILING MOUNT



215-PC*-G43 PLATED SMOKE
44" W x 12" HT x 9" EXT

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED

*- AVAILABLE IN **7** FINISHES



211/3-BB*-G51 CASED MATTE WHITE
12" DIA x 3 LIGHTS (+1 OPTIONAL)
(10" PAN) CORD MOUNT



201C-OB*-G53 PLATED SMOKE
5" DIA x 9" HT
(4 1/2" CANOPY) CORD MOUNT

ALL CORD FIXTURES HAVE 10'
OF BLACK
TEXTURED FABRIC WIRE



212/6-BAB*-G52 CLEAR
16" DIA x 6 LIGHTS (+1 OPTIONAL)
(14" PAN) CORD MOUNT



2015-SN*-G54 SEEDY
5" DIA x 9" HT
SWIVEL STEM MOUNT

ALL STEM MOUNT FIXTURES ARE
SUPPLIED WITH 6"+12"+12" STEM
SET ALONG WITH 10' OF WIRE

ADDITIONAL STEMS ARE
AVAILABLE

90 DEGREE HANG STRAIGHT
SWIVEL WITH 4 1/2" DIA. CAST
CANOPY

CAN BE USED ON VAULTED
CEILINGS

207-PN*-G51
CASED MATTE WHITE
18" DIA x 12" HT
SWIVEL STEM MOUNT

GLASS AVAILABLE IN:
G51-CASED MATTE WHITE
G52-CLEAR
G53-PLATED SMOKE
G54-SEEDY

213-PN*-G52 CLEAR
36" LONG x 5" W x 10" HT
SWIVEL STEM MOUNT



214-BAB*-G53 PLATED SMOKE
48" LONG x 5" W x 10" HT
SWIVEL STEM MOUNT



206-AC*-G52 CLEAR
5" DIA x 12" HT
SWIVEL STEM MOUNT

*- AVAILABLE IN **6** FINISHES

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED



201F-SN*-G52 CLEAR
5" DIA x 15" HT



517-1CH-AC*-G51 CASED MATTE WHITE
5" DIA x 9" HT

GLASS AVAILABLE IN:
G51-CASED MATTE WHITE
G52-CLEAR
G53-PLATED SMOKE
G54-SEEDY

ALL PRODUCTS ARE MADE
WITH CAST COMPONENTS
SOLID BRASS SWIVELS
4 1/2" DIA. CAST CANOPY



203-PC*-G54 SEEDY
5" W x 12" HT x 7" EXT



203-PN*-G52 CLEAR



208-BB*-G51 CASED MATTE WHITE
15" W x 12" HT x 8" EXT



205-BAB*-G52 CLEAR
30" W x 11" HT x 8" EXT



CAN BE USED AS
CEILING MOUNT



215-PC*-G54 SEEDY
42" W x 11" HT x ** EXT

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED

*- AVAILABLE IN **7** FINISHES

LARGE BELL SERIES



211/3-AC*-G73 PLATED SMOKE
14" DIA x 3 LIGHTS (+1 OPTIONAL)
(10" PAN) CORD MOUNT



201C-BAB*-G74 SEEDY
8" DIA x 10" HT
(4 1/2" CANOPY) CORD MOUNT
201C-BAB*-G71L SEEDY
12" DIA x 12" HT



212/6-OB*-G72 CLEAR
18" DIA x 6 LIGHTS (+1 OPTIONAL)
(14" PAN) CORD MOUNT

ALL CORD FIXTURES HAVE 10'
OF BLACK
TEXTURED FABRIC WIRE

GLASS AVAILABLE IN:
G71-CASED MATTE WHITE
G72-CLEAR
G73-PLATED SMOKE
G74-SEEDY

2 SIZES
8" AND 12"

ALL STEM MOUNT FIXTURES ARE
SUPPLIED WITH 6"+12"+12" STEM
SET ALONG WITH 10' OF WIRE

ADDITIONAL STEMS ARE
AVAILABLE

90 DEGREE HANG STRAIGHT
SWIVEL WITH 4 1/2" DIA. CAST
CANOPY

CAN BE USED ON VAULTED
CEILING



2 SIZES
8" AND 12"

206-BB*-G74L SEEDY
12" DIA x 17" HT
SWIVEL STEM MOUNT
206-BB*-G74 SEEDY
8" DIA x 13" HT




2015-AC*-G71 CASED MATTE WHITE
8" DIA x 9" HT
SWIVEL STEM MOUNT
2015-AC*-G71L CASED MATTE WHITE
12" DIA x 12" HT



207-PN*-G74 SEEDY
22" DIA x 13" HT
SWIVEL STEM MOUNT

213-PN*-G73 PLATED SMOKE
36" LONG x 8" W x 10" HT
SWIVEL STEM MOUNT



214-OB*-G72 CLEAR
48" LONG x 8" W x 10" HT
SWIVEL STEM MOUNT



LARGE BELL SERIES

2 SIZES
8" AND 12"



201F-SN*-G73 PLATED SMOKE
8" DIA x 16" HT
201F-SN*-G73L PLATED SMOKE
12" DIA x 18" HT



517-1CH-AC*-G72 CLEAR
8" DIA x 10" HT
517-1CH-AC*-G72L CLEAR
8" x 12" HT



203-PC*-G74 SEEDY
8" W x 12" HT x 9" EXT



203-BB*-G71 CASED MATTE WHITE

ALL PRODUCTS ARE MADE
WITH CAST COMPONENTS

SOLID BRASS SWIVELS

4 1/2" DIA. CAST CANOPY

GLASS AVAILABLE IN:

- G71-CASED MATTE WHITE
- G72-CLEAR
- G73-PLATED SMOKE
- G74-SEEDY



208-OB*-G72 CLEAR
19" W x 12" HT x 9" EXT



205-BAB*-G71 CASED MATTE WHITE
34" W x 12" HT x 9" EXT



CAN BE USED AS
CEILING MOUNT



215-PC*-G74 SEEDY
44" W x 12" HT x 9" EXT

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED

*- AVAILABLE IN **7** FINISHES

HALOPHANE SERIES



211/3-SN*-G2
15" DIA x 3 LIGHTS (+1 OPTIONAL)
(10" PAN) CORD MOUNT

ALL CORD FIXTURES HAVE 10'
OF BLACK
TEXTURED FABRIC WIRE



201C-AC*-G2
9" DIA x 6" HT
(4 1/2" CANOPY) CORD MOUNT



212/6-BAB*-G2
19" DIA x 6" LIGHTS (+1 OPTIONAL)
(14" PAN) CORD MOUNT



2015-OB*-G2
9" DIA x 5" HT
SWIVEL STEM MOUNT

207-PN*-G2
23" DIA x 10" HT
SWIVEL STEM MOUNT



206-PN*-G2
9" DIA x 9" HT
SWIVEL STEM MOUNT

ALL STEM MOUNT FIXTURES ARE
SUPPLIED WITH 6"+12"+12" STEM
SET ALONG WITH 10' OF WIRE

ADDITIONAL STEMS ARE
AVAILABLE

90 DEGREE HANG STRAIGHT
SWIVEL WITH 4 1/2" DIA. CAST
CANOPY

CAN BE USED ON VAULTED
CEILINGS



213-AC*-G2
36" LONG x 9" W x 8" HT
SWIVEL STEM MOUNT



214-SN*-G2
48" LONG x 9" W x 8" HT
SWIVEL STEM MOUNT



201F-AC*-G2
9" DIA x 12" HT



517-1CH-PC*-G2
9" DIA x 7" HT



203-SN*-G2
9" DIA x 8" HT x 11" EXT

ALL PRODUCTS ARE MADE
WITH CAST COMPONENTS

SOLID BRASS SWIVELS

4 1/2" DIA. CAST CANOPY



203-BAB*-G2



208-PN*-G2
21" W x 7" HT x 11" EXT



205-AC*-G2
34" W x 11" HT x 11" EXT



CAN BE USED AS
CEILING MOUNT



215-PC*-G2
44" W x 10" HT x 11" EXT

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED

*- AVAILABLE IN **7** FINISHES

ADDISON SERIES



211/3-SN*-M9SN
12" DIA x 3 LIGHTS (+1 OPTIONAL)
(10" PAN) CORD MOUNT



201C-AC*-M9AC
5" DIA x 8" HT
(4 1/2" CANOPY) CORD MOUNT

ALL CORD FIXTURES HAVE 10'
OF BLACK
TEXTURED FABRIC WIRE



212/6-OB*-M9OB
16" DIA x 6 LIGHTS (+1 OPTIONAL)
(14" PAN) CORD MOUNT



206-OB*-M9OB
5" DIA x 13" HT
SWIVEL STEM MOUNT



207-PN*-M9PN
18" DIA x 12" HT
SWIVEL STEM MOUNT

201S-BB*-M9BB
5" DIA x 10" HT
SWIVEL STEM MOUNT



ALL STEM MOUNT FIXTURES ARE
SUPPLIED WITH 6"+12"+12" STEM
SET ALONG WITH 10' OF WIRE

ADDITIONAL STEMS ARE
AVAILABLE

90 DEGREE HANG STRAIGHT
SWIVEL WITH 4 1/2" DIA. CAST
CANOPY

CAN BE USED ON VAULTED
CEILING

MIX OR MATCH ANY
METAL/SHADE OPTIONS:

- M9PN-POLISHED NICKEL
- M9SN-SATIN NICKEL
- M9AC-ANTIQUÉ COPPER
- M9BB-BRUSHED BRASS
- M9OB-OIL RUBBED BRONZE
- M9BK-MATTE BLACK
- M9PC-POLISHED CHROME



213-SN*-M9SN
36" LONG x 5" W x 10" HT
SWIVEL STEM MOUNT



214-SN*-M9BK
48" LONG x 5" W x 10" HT
SWIVEL STEM MOUNT

*- AVAILABLE IN **6** FINISHES

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED



201F-AC*-M9BK
5" DIA x 13" HT



517-1CH-BB*-M9BB
5" DIA x 9" HT



203-PN*-M9BK
5" W x 12" HT x 7" EXT
(SHOWN WITH EXTRA BACKPLATE
BP-5-BK SEE PAGE 39)

BP-5-BK

MIX OR MATCH ANY
METAL/SHADE OPTIONS:

- M9PN-POLISHED NICKEL
- M9SN-SATIN NICKEL
- M9AC-ANTIQUÉ COPPER
- M9BB-BRUSHED BRASS
- M9OB-OIL RUBBED BRONZE
- M9BK-MATTE BLACK
- M9PC-POLISHED CHROME



203-BAB*-M9BK



208-PC*-M9PC
14" W x 10" HT x 7" EXT

ALL PRODUCTS ARE MADE
WITH CAST COMPONENTS

SOLID BRASS SWIVELS

4 1/2" DIA. CAST CANOPY



205-OB*-M9AC
30" W x 10" HT x 7" EXT



CAN BE USED AS
CEILING MOUNT



215-SN*-M9SN
42" W x 11" HT x 7" EXT

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED

*- AVAILABLE IN **7** FINISHES



211/3-BB*-M4BB
14" DIA x 3 LIGHTS (+1 OPTIONAL)
(10" PAN) CORD MOUNT



201C-BAB*-M6BK
8" DIA x 6" HT
(4 1/2" CANOPY) CORD MOUNT

ALL CORD FIXTURES HAVE 10'
OF BLACK
TEXTURED FABRIC WIRE



212/6-OB*-M5OB
18" DIA x 6 LIGHTS (+1 OPTIONAL)
(14" PAN) CORD MOUNT



207-PN*-M6BK
20" DIA x 11" HT
SWIVEL STEM MOUNT

ALL STEM MOUNT FIXTURES ARE
SUPPLIED WITH 6"+12"+12" STEM
SET ALONG WITH 10' OF WIRE

ADDITIONAL STEMS ARE
AVAILABLE

90 DEGREE HANG STRAIGHT
SWIVEL WITH 4 1/2" DIA. CAST
CANOPY

CAN BE USED ON VAULTED
CEILINGS



213-AC*-M6BK
36" LONG x 8" W x 10" HT
SWIVEL STEM MOUNT

MIX OR MATCH ANY
METAL/SHADE OPTIONS:

- M1PN-POLISHED NICKEL
- M2SN-SATIN NICKEL
- M3AC-ANTIQUÉ COPPER
- M4BB-BRUSHED BRASS
- M5OB-OIL RUBBED BRONZE
- M6BK-MATTE BLACK
- M7PC-POLISHED CHROME



2015-SN*-M2SN
8" DIA x 6" HT
SWIVEL STEM MOUNT



206-OB*-M5OB
8" DIA x 11" HT
SWIVEL STEM MOUNT



214-PN*-M1PN
48" LONG x 8" W x 10" HT
SWIVEL STEM MOUNT



201F-AC*-M6BK
8" DIA x 13" HT



517-1CH-PC*-M7PC
8" DIA x 9" HT



203-BAB*-M6BK
8" DIA x 10" HT x 9" EXT

MIX OR MATCH ANY
METAL/SHADE OPTIONS:

- M1PN-POLISHED NICKEL
- M2SN-SATIN NICKEL
- M3AC-ANTIQUE COPPER
- M4BB-BRUSHED BRASS
- M5OB-OIL RUBBED BRONZE
- M6BK-MATTE BLACK
- M7PC-POLISHED CHROME



203-SN*-M2SN

ALL PRODUCTS ARE MADE
WITH CAST COMPONENTS

SOLID BRASS SWIVELS
4 1/2" DIA. CAST CANOPY



208-PN*-M6BK
18" W x 11" HT x 9" EXT



205-OB*-M5OB
32" W x 11" HT x 9" EXT



CAN BE USED AS
CEILING MOUNT



215-PC*-M6BK
44" W x 11" HT x 9" EXT

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED

*- AVAILABLE IN **7** FINISHES

BRIARCLIFF SERIES



211/3-SN*-M10
16" DIA x 3 LIGHTS (+1 OPTIONAL)
(10" PAN) CORD MOUNT

ALL CORD FIXTURES HAVE 10'
OF BLACK
TEXTURED FABRIC WIRE



201C-OB*-M11
10" DIA x 11" HT
(4 1/2" CANOPY) CORD MOUNT



212/6-SN*-M10
20" DIA x 6 LIGHTS (+1 OPTIONAL)
(14" PAN) CORD MOUNT



206-OB*-M11
10" DIA x 15" HT
SWIVEL STEM MOUNT



2015-SN*-M10
10" DIA x 11" HT
SWIVEL STEM MOUNT

207-SN*-M10
24" DIA x 13" HT
SWIVEL STEM MOUNT



ALL STEM MOUNT FIXTURES ARE
SUPPLIED WITH 6"+12"+12" STEM
SET ALONG WITH 10' OF WIRE

ADDITIONAL STEMS ARE
AVAILABLE

90 DEGREE HANG STRAIGHT
SWIVEL WITH 4 1/2" DIA. CAST
CANOPY

CAN BE USED ON VAULTED
CEILINGS



213-SN*-M10
36" LONG x 10" W x 10" HT
SWIVEL STEM MOUNT



214-OB*-M11
48" LONG x 10" W x 10" HT
SWIVEL STEM MOUNT



201F-OB*-M11
10" DIA x 13" HT



517-1CH-SN*-M10
10" DIA x 10" HT



203-OB*-M11
10" W x 10" HT x 11" EXT

ALL PRODUCTS ARE MADE WITH CAST COMPONENTS
SOLID BRASS SWIVELS
4 1/2" DIA. CAST CANOPY



203-SN*-M10



208-SN*-M10
21" W x 10" HT x 11" EXT



205-OB*-M11
32" W x 10" HT x 11" EXT



CAN BE USED AS CEILING MOUNT



215-SN*-M10
44" W x 10" HT x 11" EXT

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED

*- AVAILABLE IN **2** FINISHES

OB-OILED RUBBED BRONZE SN-SATIN BRUSHED NICKEL



SHOWN AS A CEILING MOUNT

237-OB*-M11

ALSO AVAILABLE 237-SN-M10 (SATIN NICKEL)
10" W x 10" HT x 18" EXT



237-SN*-G182
6" W x 10" HT x 15" EXT



G41 8" DIA x 6 1/2" HT



G42 8" DIA x 6 1/2" HT



G71 8" DIA x 5 3/4" HT



G72 8" DIA x 5 3/4" HT

SINGLE ARM

ADJUSTABLE SWING ARM WITH
SOLID BRASS SWIVELS
(BOTH UP TO DOWN AND SIDE TO SIDE)
4 1/2" CAST BACKPLATE

17" MAX. BODY HEIGHT (6" MIN.)
6" - 18" BODY EXTENTION

TWO 12" SOLID TUBE CORD COVERS
INCLUDED
3 WAY TURN KEY CAST SOCKET WITH
MOLDED PLUG AND 7' OF WIRE
COMES WITH DUMMY PLUG FOR HARD
WIRE CONVERSION OR CEILING MOUNT



G182 6" DIA x 7" HT



G184 6" DIA x 7" HT

*- AVAILABLE IN **2** FINISHES

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED

OB-OILED RUBBED BRONZE SN-SATIN BRUSHED NICKEL



SHOWN AS CEILING MOUNT



238-SN*-M10
ALSO AVAILABLE AS 238-OB-M11 (OIL RUBBED BRONZE)
10" W x 16" HT x 28" EXT**



238-OB*-G192
6" W x 16" HT x 24" EXT**



G43 8" DIA x 6 1/2" HT



G44 8" DIA x 6 1/2" HT



G73 8" DIA x 5 3/4" HT



G74 8" DIA x 5 3/4" HT



G192 6" DIA x 6 1/2" HT



G194 6" DIA x 6 1/2" HT

DOUBLE ARM

ADJUSTABLE SWING ARM WITH SOLID BRASS SWIVELS (BOTH UP TO DOWN AND SIDE TO SIDE)
4 1/2" CAST BACKPLATE

17" MAX. BODY HEIGHT (9" MIN.)
**- 15" - 38" BODY EXTENSION

TWO 12" SOLID TUBE CORD COVERS INCLUDED
3 WAY TURN KEY CAST SOCKET WITH MOLDED PLUG AND 7" OF WIRE
COMES WITH DUMMY PLUG FOR HARD WIRE CONVERSION OR CEILING MOUNT

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED

*- AVAILABLE IN **2** FINISHES

OB-OILED RUBBED BRONZE SN-SATIN BRUSHED NICKEL



515-1W-SN*-CL

5 1/4" W x 10 3/4" HT x 9" EXT



515-2W-SN*-CL

15" W x 12" HT x 9" EXT



515-3W-SN*-CL

25" W x 12" HT x 9" EXT

ALL PRODUCTS ARE MADE WITH CAST COMPONENTS

SOLID BRASS SWIVELS

4 1/2" DIA. CAST CANOPY

2 1/4" FITTER

GLASS AVAILABLE IN:
CL-CLEAR ANGLE CUT GLASS
AM-AMBER ANGLE CUT GLASS




515-2W-OB*-AM

15" W x 12" HT x 9" EXT



515-3W-OB*-AM

25" W x 12" HT x 9" EXT



515-1W-OB*-AM

5 1/4" W x 10 3/4" HT x 9" EXT

*- AVAILABLE IN **2** FINISHES

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED

OB-OILED RUBBED BRONZE SN-SATIN BRUSHED NICKEL



515-2W-OB*-M12
15" W x 12" HT x 9" EXT



515-1W-OB*-M12
5 1/4" W x 13 3/4" HT x 9" EXT



515-3W-OB*-M12
25" W x 12" HT x 9" EXT

ALL PRODUCTS ARE MADE WITH CAST COMPONENTS
SOLID BRASS SWIVELS
4 1/2" DIA. CAST CANOPY
2 1/4" FITTER



515-1W-SN*-M12
5 1/4" W x 10 3/4" HT x 9" EXT



515-2W-SN*-M12
15" W x 12" HT x 9" EXT



515-3W-SN*-M12
25" W x 12" HT x 9" EXT

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED

*- AVAILABLE IN 2 FINISHES

OB-OILED RUBBED BRONZE SN-SATIN BRUSHED NICKEL



515-1W-OB*-G72
8" DIA x 12" HT x 10" - 16" EXT



515-3W-SN*-G72



515-3W-OB*-G72
28" W x 12" HT x 10" - 16" EXT

ALL FIXTURES ON THIS PAGE ARE AVAILABLE WITH ANY GLASS FROM THIS CATALOG SHOWN ON PAGE 40



515-2W-SN*-G42



515-1W-SN*-G42
8" DIA x 12" HT x 10" - 16" EXT



515-2W-OB*-G42
18" W x 12" HT x 10" - 16" EXT

*- AVAILABLE IN **2** FINISHES

BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED

OB-OILED RUBBED BRONZE SN-SATIN BRUSHED NICKEL



202-BAB*
SHOWN WITH
BP-5-BK*



5" UNIVERSAL DUMMY
BACKPLATE TO COVER
OVERSIZED HOLES



BP-5-OB



BP-5-BK



BP-5-PC



BP-5-SN



BP-5-PN



BP-5-AB



BP-5-AC



BP-5-BB

HR-214-* AVAILABLE IN ALL FINISHES

2 1/4" STANDARD HOLDER
ADAPTABLE TO ALL FRANKLIN
RESTORATION COLLECTION ITEMS

CONVERT ANY ONE OF OUR FIXTURES
TO USE ANY STANDARD FAN GLASS
THAT HAS A 2 1/4" NECK



BULBS NOT INCLUDED- 100 WATT DAMP LOCATION RATED UL/CUL LISTED

*- AVAILABLE IN **8** FINISHES

ALL 3 1/4" FITTER GLASS NECK
*-EXCEPTION

M1-7
8" D
2" H
PG 30-31



M9*
5 1/4" D
5 1/2" H
PG 28-29



M10-SN
10" D
5 1/2" H
PG 32-33



M11-OB
10" D
5 1/2" H
PG 32-33



G61
6 1/4" D
5 3/4" H
PG 18-19



G62
6 1/4" D
5 3/4" H
PG 18-19



G63
6 1/4" D
5 3/4" H
PG 18-19



G64
6 1/4" D
5 3/4" H
PG 18-19



G51
5" D
5 3/4" H
PG 22-23



G52
5" D
5 3/4" H
PG 22-23



G53
5" D
5 3/4" H
PG 22-23



G54
5" D
5 3/4" H
PG 22-23



G41
7 3/4" D
6" H
PG 20-21



G42
7 3/4" D
6" H
PG 20-21



G43
7 3/4" D
6" H
PG 20-21



G44
7 3/4" D
6" H
PG 20-21



G71
8" D
5 3/4" H
PG 24-25



G72
8" D
5 3/4" H
PG 24-25



G73
8" D
5 3/4" H
PG 24-25



G74
8" D
5 3/4" H
PG 24-25



G142
6 1/4" D
6 3/4" H
PG 8-9



G146
6 1/4" D
6 3/4" H
PG 8-9



G165
7" D
9 1/4" H
PG 6-7



G2
9" D
2 1/2" H
PG 26-27



G171
6 3/4" D
5 1/4" H
PG 14-15



G172
6 3/4" D
5 1/4" H
PG 14-15



G173
6 3/4" D
5 1/4" H
PG 14-15



G182
6" D
7 1/4" H
PG 10-11



G184
6" D
7 1/4" H
PG 10-11



G192
6 1/4" D
6 1/2" H
PG 12-13



G194
6 1/4" D
6 1/2" H
PG 12-13





BB BRUSHED BRASS



PC POLISHED CHROME



BAB BLACK ANTIQUE BRASS



OB OIL RUBBED BRONZE



PN POLISHED NICKEL



SN SATIN NICKEL



AC ANTIQUE COPPER

INNOVATIONS LIGHTING QUALITY FEATURES LIFETIME WIRING AND TWO YEAR FINISH WARRANTY



**INNOVATIONS LIGHTING, LLC.
ALL DESIGNS COPYRIGHTED®**

**INNOVATIONS LIGHTING
3199 ALBANY POST ROAD SUITE 307/310
BUCHANAN, NY 10511**

**PH: 914-734-8076
FX: 413-740-0394**

**SALES@INNOVATIONSLIGHTING.COM
WWW.INNOVATIONSLIGHTING.COM**

CATALOG 2017A

\$5