



*life*AGLOW®



HINKLEY

L I G H T I N G

HINKLEY

L I G H T I N G

CLASSIC, CHIC COLLECTIONS | HINKLEYLIGHTING.COM



FREDRICK RAMOND

ESTABLISHED 1965

HINKLEY'S LUXURY LINE | FREDRICKRAMOND.COM

THIS SUPPLEMENT INCLUDES NEW PRODUCTS AND LINE EXTENSIONS FOR INTERIOR
AND EXTERIOR LIGHTING FROM HINKLEY AND FREDRICK RAMOND.
FOR LANDSCAPE LIGHTING, SEE OUR FULL LINE HINKLEY LANDSCAPE LIGHTING CATALOG.

HINKLEY LIGHTING, INC. | 2017



***“CREATIVITY IS
WHAT DRIVES US.
IT MOTIVATES
US TO CONNECT
AND CONTEMPLATE,
INSPIRE AND
INNOVATE.”***

RICK WIEDEMER, CEO | HINKLEY LIGHTING

We like to consider a home as the ultimate design lab for a creative life: an ever-evolving source of self-expression and creative energy. Whether you crave tranquility with a minimalist aesthetic or a sense of play with bright colors and patterned flair, we design our products to provide you with comprehensive styles and solutions.



▶ [WATCH THE VIDEO ON HINKLEYLIGHTING.COM](https://www.hinkleylighting.com)

**THE WIEDEMER FAMILY SHARES A PASSION FOR DESIGN
THAT HAS CONTINUED FOR 4 GENERATIONS.**

FROM LEFT: **ERIC WIEDEMER**, VICE PRESIDENT, GENERAL COUNSEL
RICK WIEDEMER, CEO | **JESS WIEDEMER**, PRESIDENT, COO

THE AWARD-WINNING ATLANTIS LED DESIGN (AS SEEN ON THE COVER) IS TRANSLATED INTO A DRAMATIC SCULPTURE IN COLLABORATION WITH RENOWNED SCULPTOR DAVID DEMING. ON THE GROUNDS OF HINKLEY'S GLOBAL HEADQUARTERS, IT SETS THE TONE FOR A DAILY APPRECIATION OF DESIGN AND CREATIVITY.

go ahead, **APPLAUD!**



Find lighting you will love

with Hinkley's signature mix of products, design inspiration and lighting tips. Illuminate indoor and outdoor spaces with ease by browsing our source book, curated style guides and how-to videos, and even locate your preferred lighting showroom in a snap!



TO DOWNLOAD ON YOUR IPAD, SEARCH "HINKLEY LIGHTING" IN THE APP STORE.

PRODUCT ICONS



ADA COMPLIANT

Indicates fixtures that adhere to the standards and guidelines listed by the Americans with Disabilities Act.



COMBINATION MOUNT

Indicates fixtures that are supplied with the means to be chain hung or mounted flush to the ceiling.



DARK SKY

Indicates fixtures that are engineered to minimize light glare upward into the night sky.



FIXTURE EXCEEDS 50LBS.

Indicates fixtures weighing over 50lbs. Fixtures must be supported independently of the outlet box unless the outlet box is UL listed for the appropriate weight. Required hardware included.



INVISI-MOUNT

Indicates fixtures where the mounting hardware is hidden on the back plate.



LED

Fixtures come equipped with a fully integrated LED panel and built-in driver.



OPEN AIR

Indicates fixtures that are appropriate and rated for both interior and exterior applications.



QUICKFIT

Fixtures recommended for use with QuickFit recessed can light converter kit.



TITLE 24

Title 24 is a state of California Residential Energy Code updated every three years. It applies to any project under review through a building permit. Designated LED products meeting Title 24 also qualify for Title 21 Commercial use.

HINKLEY FINISHES

AN	ANTIQUÉ NICKEL
BC	BRUSHED CARAMEL
BK	BLACK
BN	BRUSHED NICKEL
BR	BRUSHED BRONZE
BZ	BRONZE
CG	CEMENT GRAY
CM	CHROME
CW	CLASSIC WHITE
DG	DELUXE GOLD
DZ	AGED ZINC
EN	ENGLISH NICKEL
GV	GALVANIZED
GZ	GRAPHITE BRONZE
HB	HERITAGE BRASS
HE	HEMATITE
IN	INDUSTRIAL IRON
IR	IRON RUST
KZ	BUCKEYE BRONZE
LZ	LIGHT OILED BRONZE
MM	METALLIC MATTE BRONZE
OP	OLDE PENNY
OZ	OIL RUBBED BRONZE
PL	POLISHED ANTIQUE NICKEL
PN	POLISHED NICKEL
PT	POLISHED WHITE
SK	SATIN BLACK
SQ	SEQUOIA
VI	VINTAGE IRON
WZ	WEATHERED ZINC

FREDRICK RAMOND FINISHES

ANI	ANTIQUÉ NICKEL
CPG	CHAMPAGNE GOLD
CPN	CHAMPAGNE
CWW	COTTAGE WHITEWASH
DXG	DELUXE GOLD
GMT	GUNMETAL
HBZ	HAMMERED BRONZE
HRR	HEIRLOOM BRASS
HBR	HERITAGE BRASS
IRR	IRON RUST
MMB	METALLIC MATTE BRONZE
PNK	POLISHED NICKEL
SBK	SATIN BLACK
SLF	SILVER LEAF
SSG	SUNSET GOLD
VBZ	VINTAGE BRONZE
VIR	VINTAGE IRON
WTA	WEATHERED ASH
WWT	WARM WHITE

CONTENTS

JANUARY 2017



FENMORE 4946TZ AND TRELIS 1436RB

CHANDELIER COLLECTIONS

ALISTER	S228
AMELIA	S257
ASTRID	S244
BARSTOW	S256
BECKETT	S252
CHARLOTTE	S263
CLANCY	S269
COLBIN	S268
DENTON	S250
EUCLID	S240
FLETCHER	S259
FULHAM	S236
HARPER	S266
HOWELL	S261
LANZA	S271
LARCHMERE	S220
LATITUDE	S234
MERCER	S270
MIDDLETON	S224
ODEON	S260
REFINERY	S232
SOMERSET	S258
SURREY	S218
THEORY	S248
WEXLEY	S222
WYATT	S254



COLLECTIONS

ABINGDON	S316
ANYA	S308
ARTEMIS	S300
CARSON	S320
DELFINA	S302
EMILIE	S318
EMPIRE	S298
ENSEMBLE	S294
EVE	S312
GEMMA	S303
GIGI	S278
ISLA	S304
KARMA	S290
MIDDLEFIELD	S319
MOXIE	S286
ODETTE	S282
SIRENA	S306
SOLSTICE	S288
TRYST	S292
TULAH	S310
ZUMA	S274

BATH COLLECTIONS

AVON	S333
BALDWIN	S344
BENNETT	S334
BLYTHE	S342
CLANCY	S335
DAPHNE	S328
FAYE	S341
JACKSON	S330
KYRA	S338
LATITUDE	S329
MILA	S327
SADIE	S337
SIMI	S325
TESSA	S340
THISTLEDOWN	S346
VERVE	S336

OUTDOOR COLLECTIONS

ALFORD PLACE	S402
ANCHORAGE	S400
ARIA	S376
ATWELL	S354
BRIGGS	S388
BROMLEY	S404
BURKE	S382
CARSON	S356
ENZO	S406
FREEPORT	S390
GLACIER	S360
KUBE	S374
LUNA	S370
MARINA	S394
MIST	S366
PERRY	S392
PLAZA	S364
PORTER	S386
SAWYER	S352
SURF	S368
TATUM	S398
THEO	S380
TRELLIS	S408
VAPOR	S362

natural JUXTAPOSITION

Our innate desire to build the habitat of a home stems from a natural need to connect with our surroundings. Interior spaces that are reminiscent of outdoor elements provide an indescribable comfort; a retreat we yearn for to balance the hustle of a busy day. The pairing of geometric pattern and organic materials is prevalent in nature yet unexpectedly invigorating in the home. Allow angular lighting forms to add luminosity to your space as both an element of function and a contemplative feature of design.

Styling tip: Add color with deep tranquil blues and earthy greens to complement the warmth of sleek natural wood and woven textiles.

FIXTURES SHOWN: THEORY 3576DZ AND LEX 2715BZ



CHANDELIER COLLECTIONS



ALISTER	S228
AMELIA	S257
ASTRID	S244
BARSTOW	S256
BECKETT	S252
CHARLOTTE	S263
CLANCY	S269
COLBIN	S268
DENTON	S250
EUCLID	S240
FLETCHER	S259
FULHAM	S236
HARPER	S266
HOWELL	S261
LANZA	S271
LARCHMERE	S220
LATITUDE	S234
MERCER	S270
MIDDLETON	S224
ODEON	S260
REFINERY	S232
SOMERSET	S258
SURREY	S218
THEORY	S248
WEXLEY	S222
WYATT	S254

SURREY™

FINISH POLISHED NICKEL
SHADE WHITE LINEN (OPTIONAL)

Surrey combines traditional elegance and dazzling crystal details into a fresh, streamlined silhouette. Slim, tapered arms in Polished Nickel with faceted crystal bobeches surround a striking oblong center. Optional white fabric shades add a discreet layer of glamour.



4006 PN
26½" DIA., 32" H



4006 PN
26½" DIA., 32" H
(shown with optional shades,
28" diameter)



4000 SH
5¾" DIA., 6" H
(optional shade)



4002 PN
11¾" W, 15¼" H



4005 PN
24" DIA., 31¾" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
4002 PN	2-60w Cand.	6"	13¼"	4½" Square Back Plate	
4005 PN	5-60w Cand.			6" Dia. Canopy	12', 10'
4006 PN	6-60w Cand.			6" Dia. Canopy	12', 10'
4000 SH	Do not exceed 40w				

LARCHMERE™

FINISH ENGLISH NICKEL
GLASS WHITE LINEN HARDBACK

Combining the clean lines of an angular, architectural frame with a white linen hardback drum shade, Larchmere elevates the minimalist geometric form to a new level of transitional elegance. Subtly integrating chic design elements, from a heavy crystal center column, metal trim shade detailing an etched glass diffuser, underscore an attention to detail that yields Larchmere's discerning silhouette.



4485 EN
28" DIA., 21" H
59½" MAX. H*



4483 EN
18" DIA., 13¾" H



4484 EN
24" DIA., 20¾" H
59¼" MAX. H*

ITEM	BULBS	CANOPY	WIRE	STEMS INCLUDED
4483 EN	3-100w Med.	6¾" Dia.		
4484 EN	4-100w Med.	6¾" Dia.	10'	2-6", 2-12"
4485 EN	4-100w Med.	6¾" Dia.	10'	2-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6038 EN.

WEXLEY™

FINISH HERITAGE BRASS, OIL RUBBED BRONZE, POLISHED NICKEL
GLASS CLEAR

Wexley is a distinctive transitional pendant with bold, oval shaped clear glass as the centerpiece of the design. Decorative cast details and crystal accents, combined with rich finish options, make a modern statement with vintage flair.



4325 HB
18" DIA., 27½" H



4325 OZ
18" DIA., 27½" H



4325 PN
18" DIA., 27½" H



4323 HB
12" DIA., 19½" H



4323 OZ
12" DIA., 19½" H



4323 PN
12" DIA., 19½" H

ITEM	BULBS	CANOPY	WIRE/CHAIN
4323 HB, OZ, PN	3-60w Cand.	6" Dia.	6', 5'
4325 HB, OZ, PN	5-60w Cand.	6" Dia.	12', 10'

Ideal for vintage filament bulbs (not included).

MIDDLETON™

FINISH POLISHED NICKEL

This confident transitional design exemplifies that less is more. Possessing strong lines and seamless finishing, Middleton's solid metal construction is sleek and precise, available in either a commanding Polished Nickel finish or a rich Graphite Bronze finish with warm undertones.

OBJECT OF OUR
AFFECTION

Middleton's refined forms strike the ultimate note of sophistication



3774 PN
26" DIA., 30" H
62¾" MAX. H*



3773 PN
20" DIA., 23½" H
56¼" MAX. H*



3777 PN
8" DIA., 12¾" H
45½" MAX. H*



3776 PN
52" W, 14" H
46¾" MAX. H*

ITEM	BULBS	DEPTH	CANOPY	WIRE	STEMS INCLUDED	ADDITIONAL FINISHES
3773 PN	4-60w Cand.		5¼" Dia.	10'	1-6", 2-12"	GZ
3774 PN	4-60w Cand.		5¼" Dia.	10'	1-6", 2-12"	GZ
3776 PN	6-100w Med.	10"	4¾" W, 12" L	10'	2-6", 4-12"	GZ
3777 PN	1-100w Med.		5¼" Dia.	10'	1-6", 2-12"	GZ

*Maximum achievable height with stems included. Additional 12" stems available. For 3773 PN, 3776 PN and 3777 PN use 6031 PN. For 3774 PN use 6061 PN. Ideal for vintage filament bulbs (not included).

MIDDLETON™

FINISH GRAPHITE BRONZE

This confident transitional design exemplifies that less is more. Possessing strong lines and seamless finishing, Middleton's solid metal construction is sleek and precise, available in either a commanding Polished Nickel finish or a rich Graphite Bronze finish with warm undertones.



3774 GZ
26" DIA., 30" H
62¾" MAX. H*



3773 GZ
20" DIA., 23½" H
56¼" MAX. H*



3777 GZ
8" DIA., 12¾" H
45½" MAX. H*



3776 GZ
52" W, 14" H
46¾" MAX. H*

ITEM	BULBS	DEPTH	CANOPY	WIRE	STEMS INCLUDED	ADDITIONAL FINISHES
3773 GZ	4-60w Cand.		5¼" Dia.	10'	1-6", 2-12"	PN
3774 GZ	4-60w Cand.		5¼" Dia.	10'	1-6", 2-12"	PN
3776 GZ	6-100w Med.	10"	4¾" W, 12" L	10'	2-6", 4-12"	PN
3777 GZ	1-100w Med.		5¼" Dia.	10'	1-6", 2-12"	PN

*Maximum achievable height with stems included. Additional 12" stems available. For 3773 GZ, 3776 GZ and 3777 GZ use 6031 GZ. For 3774 GZ use 6061 GZ. Ideal for vintage filament bulbs (not included).


ALISTER™

FINISH ANTIQUE NICKEL

Chic minimalism is captured with Alister's airy, open appearance. The streamlined, stem-hung design exudes sophistication, capturing both clean and classic lines in its timeless silhouette.



3078 AN
32" DIA., 29" H
79" MAX. H*



3076 AN
28" DIA., 26" H
76" MAX. H*



3072 AN
9¾" W, 14¼" H



3075 AN
24" DIA., 24" H
74" MAX. H*

ITEM	BULBS	EXT.	TOP TO OUTLET	CANOPY/ BACKPLATE	WIRE	STEMS INCLUDED	ADDITIONAL FINISHES
3072 AN	2-60w Cand.	4"	8½"	4½" Dia. Back Plate			KZ
3075 AN	6-60w Cand.			6" Dia. Canopy	10'	1-4", 1-6", 1-12", 1-24"	KZ
3076 AN	8-60w Cand.			6" Dia. Canopy	10'	1-4", 1-6", 1-12", 1-24"	KZ
3078 AN	12-60w Cand.			6" Dia. Canopy	10'	1-4", 1-6", 1-12", 1-24"	KZ

*Maximum achievable height with stems included. Additional 12" stems available, 4312 AN. Ideal for vintage filament bulbs (not included).

ALISTER™

FINISH BUCKEYE BRONZE

Chic minimalism is captured with Alister's airy, open appearance. The streamlined, stem-hung design exudes sophistication, capturing both clean and classic lines in its timeless silhouette.



3078 KZ
32" DIA., 29" H
79" MAX. H*



3076 KZ
28" DIA., 26" H
76" MAX. H*



3072 KZ
9¾" W, 14¼" H



3075 KZ
24" DIA., 24" H
74" MAX. H*

ITEM	BULBS	EXT.	TOP TO OUTLET	CANOPY/ BACKPLATE	WIRE	STEMS INCLUDED	ADDITIONAL FINISHES
3072 KZ	2-60w Cand.	4"	8½"	4½" Dia. Back Plate			AN
3075 KZ	6-60w Cand.			6" Dia. Canopy	10'	1-4", 1-6", 1-12", 1-24"	AN
3076 KZ	8-60w Cand.			6" Dia. Canopy	10'	1-4", 1-6", 1-12", 1-24"	AN
3078 KZ	12-60w Cand.			6" Dia. Canopy	10'	1-4", 1-6", 1-12", 1-24"	AN

*Maximum achievable height with stems included. Additional 12" stems available, 6036 KZ. Ideal for vintage filament bulbs (not included).

REFINERY™


FINISH BRUSHED NICKEL, CHROME, SATIN BLACK

GLASS CLEAR, MIRRORRED, SMOKED


Refinery is a chic interpretation of modern-industrial design. A variety of stylish glass and finish options ensure this pared down style can seamlessly add a dash of retro-modern charm to any space.



63306 SK-CL
43¾" W, 11¼" H
56" MAX. H*



63307 BN-CL
7¾" DIA., 12" H
56¾" MAX. H*



63307 BN-SM
7¾" DIA., 12" H
56¾" MAX. H*



63307 CM-MR
7¾" DIA., 12" H
56¾" MAX. H*



63307 CM-SM
7¾" DIA., 12" H
56¾" MAX. H*



63306 SK-SM
43¾" W, 11¼" H
56" MAX. H*



63307 SK-CL
7¾" DIA., 12" H
56¾" MAX. H*



63307 SK-SM
7¾" DIA., 12" H
56¾" MAX. H*

ITEM	BULBS	DEPTH	CANOPY	WIRE	STEMS INCLUDED
63306 SK-CL	1-100w Med.		5" Dia.	10'	2-6", 6-12"
63306 SK-SM	1-100w Med.		5" Dia.	10'	2-6", 6-12"
63307 BN-CL	1-100w Med.		5" Dia.	10'	1-6", 3-12"
63307 BN-SM	1-100w Med.		5" Dia.	10'	1-6", 3-12"
63307 CM-MR	1-100w Med.		5" Dia.	10'	1-6", 3-12"
63307 CM-SM	1-100w Med.		5" Dia.	10'	1-6", 3-12"
63307 SK-CL	6-100w Med.	8¼"	4¾" W, 18½" L	10'	1-6", 3-12"
63307 SK-SM	6-100w Med.	8¼"	4¾" W, 18½" L	10'	1-6", 3-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6034 BN, CM, SK. Ideal for vintage filament bulbs (not included).

LATITUDE™

FINISH BRUSHED NICKEL
GLASS CLEAR BEVELED INSIDE-ETCHED

Latitude is contemporary and sleek, finding its true beauty in the minimalist design. The slim glass panel features rectangular etching while the Brushed Nickel frame adds understated architectural style.




3992 BN
8" W, 16" H



5651 BN
5½" W, 21½" H



3996 BN
42" W, 8½" H, 8" D
49½" MAX. H*



3997 BN
8" W, 16½" H
55" MAX. H*

ITEM	BULBS	DEPTH	EXT.	TTO	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED	ADDITIONAL FINISHES
3992 BN	2-60w Cand.		4"	7¾"	8" W, 15½" H Back Plate			OZ
3996 BN	4-100w Med.	8"			4¼" W, 9¼" L Canopy	10'	4-6", 4-12"	OZ
3997 BN	2-100w Med.				4¾" Dia. Canopy	10'	2-6", 2-12"	OZ
5651 BN	2-100w Med.		5½"	10¾"	5½" W, 21½" H			CM, OZ

*Maximum achievable height with stems included. Additional 12" stems available. For 3996 BN use 6068 BN, and for 3997 BN use FR84312BNI.

Latitude is contemporary and sleek, finding its true beauty in the minimalist design. The slim glass panel features rectangular etching while the Oil Rubbed Bronze frame adds understated architectural style.

LATITUDE™

OIL RUBBED BRONZE FINISH
CLEAR BEVELED INSIDE-ETCHED GLASS



3997 OZ
8" W, 16½" H
55" MAX. H*



5651 OZ
5½" W, 21½" H



3992 OZ
8" W, 16" H



3996 OZ
42" W, 8½" H, 8" D
49½" MAX. H*

ITEM	BULBS	DEPTH	EXT.	TTO	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED	ADDITIONAL FINISHES
3992 OZ	2-60w Cand.		4"	7¾"	8" W, 15½" H Back Plate			BN
3996 OZ	4-100w Med.	8"			4¼" W, 9¼" L Canopy	10'	4-6", 4-12"	BN
3997 OZ	2-100w Med.				4¾" Dia. Canopy	10'	2-6", 2-12"	BN
5651 OZ	2-100w Med.		5½"	10¾"	5½" W, 21½" H			BN, CM

*Maximum achievable height with stems included. Additional 12" stems available. For 3996 OZ use 6068 OZ, and for 3997 OZ use 4312 OZ.


FULHAM™

FINISH POLISHED ANTIQUE NICKEL
GLASS CLEAR BEVELED LENS

Fulham's bold orb design showcases clear beveled glass lenses that punctuate the minimalist elegance with an industrial edge. Its sleek lines combine with cast sockets and mid-century elements for a dynamic transitional style.



3925 PL
32" DIA., 32½" H
69¼" MAX. H*



3927 PL
7¾" W, 9" H
41¾" MAX. H*



3920 PL
7¾" W, 21½" H



3924 PL
26" DIA., 26½" H
62½" MAX. H*

ITEM	BULBS	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED	ADDITIONAL FINISHES
3920 PL	1-100w Med.		5"	10¾"	7½" Dia. Back Plate			KZ
3924 PL	4-100w Med.				5" Dia. Canopy	10'	1-6", 2-12"	KZ
3925 PL	5-100w Med.				5" Dia. Canopy	10'	1-6", 2-12"	KZ
3927 PL	1-100w Med.	4½"			5" Dia. Canopy	10'	1-6", 2-12"	KZ

*Maximum achievable height with stems included. Additional 12" stems available. For 3924 PL and 3927 PL, use 4312 PL. For 3925 PL, use 4512 PL. Ideal for vintage filament bulbs (not included).

FULHAM™

FINISH BUCKEYE BRONZE WITH HERITAGE BRASS

GLASS CLEAR BEVELED LENS

Fulham's bold orb design showcases clear beveled glass lenses that punctuate the minimalist elegance with an industrial edge. Its sleek lines combine with cast sockets and mid-century elements for a dynamic transitional style.



3925 KZ
32" DIA., 32½" H
69¼" MAX. H*



3927 KZ
7¾" W, 9" H
41¾" MAX. H*



3920 KZ
7¾" W, 21½" H



3924 KZ
26" DIA., 26½" H
62½" MAX. H*

ITEM	BULBS	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED	ADDITIONAL FINISHES
3920 KZ	1-100w Med.		5"	10¾"	7½" Dia. Back Plate			PL
3924 KZ	4-100w Med.				5" Dia. Canopy	10'	1-6", 2-12"	PL
3925 KZ	5-100w Med.				5" Dia. Canopy	10'	1-6", 2-12"	PL
3927 KZ	1-100w Med.	4½"			5" Dia. Canopy	10'	1-6", 2-12"	PL

*Maximum achievable height with stems included. Additional 12" stems available. For 3924 KZ and 3927 KZ, use 6037 HB. For 3925 KZ, use 6067 HB. Ideal for vintage filament bulbs (not included).

EUCLID™

FINISH CEMENT GRAY WITH BRUSHED GOLD

Euclid is a unique style that defies trends. Blending traditional warmth and contemporary flair, its bold proportions and rich two tone finish create a stunning silhouette.



3464 CG
44" DIA., 49" H





3468 CG
28¼" DIA., 33" H



3469 CG
36" DIA., 41" H



3460 CG
9½" W, 20" H



3463 CG
20" DIA., 24½" H



3466 CG
21¼" DIA., 25¾" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	ADDITIONAL FINISHES
3460 CG	2-60w Cand.	5½"	10"	4½" W, 9" H Back Plate		SB
3463 CG	3-60w Cand.			7" Dia. Canopy	12', 10'	SB
3464 CG	16-60w Cand.			7" Dia. Canopy	12', 10'	SB
3466 CG	6-60w Cand.			7" Dia. Canopy	12', 10'	SB
3468 CG	8-60w Cand.			7" Dia. Canopy	12', 10'	SB
3469 CG	12-60w Cand.			7" Dia. Canopy	12', 10'	SB

Ideal for vintage filament bulbs (not included).

EUCLID™

FINISH SPANISH BRONZE WITH HERITAGE BRASS

Euclid is a unique style that defies trends. Blending traditional warmth and contemporary flair, its bold proportions and rich two tone finish create a stunning silhouette.



3464 SB
44" DIA., 49" H





3468 SB
28¼" DIA., 33" H



3469 SB
36" DIA., 41" H



3460 SB
9½" W, 20" H



3463 SB
20" DIA., 24½" H



3466 SB
21¼" DIA., 25¾" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	ADDITIONAL FINISHES
3460 SB	2-60w Cand.	5½"	10"	4½" W, 9" H Back Plate		CG
3463 SB	3-60w Cand.			7" Dia. Canopy	12', 10'	CG
3464 SB	16-60w Cand.			7" Dia. Canopy	12', 10'	CG
3466 SB	6-60w Cand.			7" Dia. Canopy	12', 10'	CG
3468 SB	8-60w Cand.			7" Dia. Canopy	12', 10'	CG
3469 SB	12-60w Cand.			7" Dia. Canopy	12', 10'	CG

Ideal for vintage filament bulbs (not included).

ASTRID™

FINISH DELUXE GOLD WITH METALLIC MATTE BRONZE

Sleek and chic, Astrid is designed as an airy geometric beauty balanced with robust welded construction. The inner light cluster, uniquely wired from the bottom, appears to float inside the outer cage. The two-tone finish further enhances the layering effect for added depth and dimension.



3025 DG
28" W, 34¼" H



3027 DG
12" W, 10½" H
43¼" MAX. H*



3023 DG
20" W, 26¾" H

ITEM	BULBS	CANOPY	WIRE/CHAIN	STEMS INCLUDED	ADDITIONAL FINISHES
3023 DG	3-60w Cand.	5" Dia.	12', 10'		MM
3025 DG	6-60w Cand.	5" Dia.	12', 10'		MM
3027 DG	1-100w Med.	5" Dia.	10' Wire	1-6", 2-12"	MM

*Maximum achievable height with stems included. Additional 12" stems available, 6030 DG. Ideal for vintage filament bulbs (not included).

ASTRID™

FINISH METALLIC MATTE BRONZE WITH DELUXE GOLD

Sleek and chic, Astrid is designed as an airy geometric beauty balanced with robust welded construction. The inner light cluster, uniquely wired from the bottom, appears to float inside the outer cage. The two-tone finish further enhances the layering effect for added depth and dimension.



3025 MM
28" W, 34¼" H



3027 MM
12" W, 10½" H
43¼" MAX. H*



3023 MM
20" W, 26¾" H

ITEM	BULBS	CANOPY	WIRE/CHAIN	STEMS INCLUDED	ADDITIONAL FINISHES
3023 MM	3-60w Cand.	5" Dia.	12', 10'		DG
3025 MM	6-60w Cand.	5" Dia.	12', 10'		DG
3027 MM	1-100w Med.	5" Dia.	10' Wire	1-6", 2-12"	DG

*Maximum achievable height with stems included. Additional 12" stems available, 6030 MM. Ideal for vintage filament bulbs (not included).

THEORY™

FINISH AGED ZINC WITH HERITAGE BRASS

Theory's multi-faceted cage design proves the ultimate style solution to the elegance equation. This vintage, mid-century design is updated with a sophisticated two-tone finish, enhancing its modern geometric shape with a bold layering effect.



3576 DZ
24¼" W, 17¾" H
52¼" MAX. H*



3574 DZ
10¾" W, 14¾" H
49¼" MAX. H*

ITEM	BULBS	CANOPY	WIRE	STEMS INCLUDED
3574 DZ	4-60w Cand.	5" Dia.	10'	1-6", 2-12"
3576 DZ	6-60w Cand.	5" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available. For 3574 DZ use 6037 HB, and for 3576 DZ use 6067 HB. Ideal for vintage filament bulbs (not included).



DENTON™

FINISH INDUSTRIAL IRON WITH VINTAGE WALNUT
GLASS CLEAR

Vintage warmth meets modern minimalism in the Denton collection. Offering a range of refined designs to choose from, Denton integrates an Industrial Iron finish with rustic Vintage Walnut accents. An over-scaled classic glass form pairs with T-style lamping to deliver a fresh take on modern-farmhouse style.



3266 IN
36" W, 15 $\frac{3}{4}$ " H
47 $\frac{3}{4}$ " MAX. H**



3265 IN
15¾" DIA., 42¾" H (SHOWN)
42¾" MAX. H**



3267 IN
5¼" DIA., 10" H
42" MAX. H**



3263 IN
10½" DIA., 36¾" H (SHOWN)
42¾" MAX. H**



3260 IN
5¼" W, 15¾" H.

ITEM	BULBS	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
3260 IN	1-60w Med.*		6¼"	3¾"	4¾" W, 7½" H Back Plate		
3263 IN	3-60w Med.*				10" Dia. Canopy	10'	3-6", 9-12"
3265 IN	5-60w Med.*				15" Dia. Canopy	10'	5-6", 10-12"
3266 IN	5-60w Med.*	5¼"			4¾" W, 11¾" L Canopy	10'	2-6", 4-12"
3267 IN	1-60w Med.*				5¼" Dia. Canopy	10'	1-6", 2-12"

*Bulbs included. **Maximum achievable height with stems included. Additional 12" stems available, 6033 IN.

BECKETT™

FINISH IRON RUST
GLASS STEEL MESH

Beckett's combination of vintage industrial and rustic elements imparts a design that resonates with texture and depth. A sturdy steel mesh shade interspersed with solid wood uprights is captured in an oval, open-air linear shade. A subtly designed center down light is surrounded by minimalist arms with visible sockets to customize with the bulbs of your choice.

DESIGN NOTE

CENTER DOWNLIGHT PROVIDES
ADDED ILLUMINATION, PERFECT
FOR DINING AND WORK SPACES



4826 IR
30" DIA., 27" H
59¼" MAX. H*



4825 IR
42" W, 24" H

4824 IR
22¼" DIA., 23" H
55½" MAX. H*

ITEM	BULBS	DEPTH	CANOPY	WIRE/CHAIN	STEMS INCLUDED
4824 IR	3-100w Med., 1-35w GU-10**		5¼" Dia.	10'	1-6", 2-12"
4825 IR	4-100w Med., 1-35w GU-10**	12"	4½" W, 6½" L	12', 10'	
4826 IR	5-100w Med., 1-35w GU-10**		5¼" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6033 IN. **GU-10 bulb for downlight included. Ideal for vintage filament bulbs (not included).

WYATT™

FINISH IRON RUST WITH WEATHERD ASH (WTA)
SHADE OATMEAL CHAMBRAY (OPTIONAL)
OATMEAL CHAMBRAY HARDBACK (3910 IR, 3913 IR INCLUDED)

Reinventing a classic, Wyatt's bold design tames the Wild West. Its refined rustic silhouette reinterprets the wagon wheel in a solid wood polygonal ring tailored with modern sensibility. Deluxe details, such as textured metal brackets and candle sleeves, a wood-trimmed canopy and forged hooks enrich its luxe lodge appeal.



3918 IR
30" DIA., 27" H



3916 IR
24" DIA., 16" H



3913 IR
19" DIA., 17" H



3910 IR
8½" W, 12½" H



3910 SH
5¼" W, 4½" H
(optional shade)




3916 IR
25" DIA., 16" H
(show with optional shades)

ITEM	BULBS	EXT.	TTO	BACK PLATE/CANOPY	WIRE	CHAIN
3910 IR	1-60w Med.	5½"	5¼"	4½" W, 10¼" H Back Plate		
3913 IR	3-60w Cand.			6" Dia. Canopy	6'	5'
3916 IR	6-60w Cand.			8¼" Dia. Canopy	6'	3-5'
3918 IR	8-60w Cand.			8¼" Dia. Canopy	12'	4-5'
3910 SH	Do not exceed 40w					

BARSTOW™

FINISH BUCKEYE BRONZE, GALVANIZED

A marriage of form and function, Barstow unites a vintage shape and industrial elements for a farmhouse chic statement. With its robust profile, bold finish options, prominent mesh screens and sturdy die-cast facets, Barstow is a perfect addition to a variety of interiors.



3604 GV
16¼" DIA., 12" H
45" MAX. H*



3604 KZ
16¼" DIA., 12" H
45" MAX. H*


ITEM	BULBS	CANOPY	WIRE	STEMS INCLUDED
3604 GV	1-100w Med.	5½" Dia.	10'	1-6", 2-12"
3604 KZ	1-100w Med.	5½" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6037 GV, KZ.


Amelia's classic pendant design reinvents vintage details with a cast glass fitter, cast metal trim ring and ornamental clasps. The Polished White finish will infuse any space with dash of fresh American style.

AMELIA™

POLISHED WHITE WITH POLISHED NICKEL FINISH



3126 PT
13" DIA., 13" H
46" MAX. H*



3122 PT
11½" DIA., 9" H
42" MAX. H*

ITEM	BULBS	CANOPY	WIRE	STEMS INCLUDED
3122 PT	1-100w Med.	5¼" Dia.	10'	1-6", 2-12"
3126 PT	1-100w Med.	5¼" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6067 PN.

SOMERSET™

FINISH BRUSHED NICKEL, BUCKEYE BRONZE, HERITAGE BRASS

GLASS ETCHED OPAL

Chic and elegant, the Somerset collection exudes a quiet and precise sophistication. Subtly fusing modernity with vintage appeal, its etched opal glass deftly floats inside a streamlined metal yoke and ring while understated turned metal knobs add an authentic edge.



3407 HB
11½" W, 17" H
49¾" MAX. H*



3407 BN
11½" W, 17" H
49¾" MAX. H*



3407 KZ
11½" W, 17" H
49¾" MAX. H*


ITEM	BULBS	CANOPY	WIRE	STEMS INCLUDED
3407 BN	1-100w Med.	6" Dia.	10'	1-6", 2-12"
3407 HB	1-100w Med.	6" Dia.	10'	1-6", 2-12"
3407 KZ	1-100w Med.	6" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4512 BN, KZ and 6067 HB.


Fletcher's chic vibe transcends style boundaries. A seamless dome shade features a cast-fitter and an elegant capture ring that secures the etched opal glass with decorative cast knobs. Spanning vintage to industrial, classic to transitional, Fletcher seamlessly unifies any décor declaration.

FLETCHER™

AGED ZINC WITH HERITAGE BRASS, POLISHED NICKEL FINISH
ETCHED OPAL GLASS



4834 DZ
13½" DIA., 14½" H
49¼" MAX. H*



4834 PN
13½" DIA., 14½" H
49¼" MAX. H*

ITEM	BULBS	CANOPY	WIRE	STEMS INCLUDED
4834 DZ	2-100w Med.	5½" Dia.	10'	1-6", 2-12"
4834 PN	2-100w Med.	5½" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6037 HB, PN.

ODEON™

FINISH BRUSHED NICKEL, OIL RUBBED BRONZE
 GLASS INSIDE ETCHED HOLOPHANE

Inspired by the stylish Tribeca brasserie, Odeon elicits a fashionable, urban feel that is both modern and timeless. The metal frame follows the contour of the holophane sphere, inspiring perfection in any setting.



4744 BN
 15" DIA., 18" H
 54¼" MAX. H*



4744 OZ
 15" DIA., 18" H
 54¼" MAX. H*

ITEM	BULBS	CANOPY	WIRE	STEMS INCLUDED
4744 BN	3-100w Med.	6" Dia.	10'	1-6", 2-12"
4744 OZ	3-100w Med.	6" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4312 BN and 6037 OZ.

Howell features a dramatic etched holophane glass orb suspended from bold Oil Rubbed Bronze decorative chain. With its vintage appeal, Howell achieves superior style from every angle.

HOWELL™

OIL RUBBED BRONZE FINISH
HOLOPHANE GLASS



3843 OZ
21" DIA., 31½" H



3844 OZ
24½" DIA., 38½" H

ITEM	BULBS	CANOPY	WIRE/CHAIN
3843 OZ	3-100w Med.	5¼" Dia.	10', 5'
3844 OZ	4-100w Med.	5¼" Dia.	10', 5'



Charlotte is an updated traditional design featuring a richly textured off-white fabric shade captured by wide solid metal uprights and trim rings. The domed bottom diffuser is captured inside a heavy trim ring and held by cast decorative knobs for a refined vintage touch.

CHARLOTTE™

WOVEN OFF-WHITE FABRIC SHADE ANTIQUE NICKEL FINISH
 ETCHED OPAL GLASS



3523 AN
 16" DIA., 19½" H
 68¼" MAX. H*



3522 AN
 20" DIA., 13½" H



3521 AN
 16" DIA., 13" H

ITEM	BULBS	CANOPY	WIRE	STEMS INCLUDED	ADDITIONAL FINISHES
3521 AN	3-75w Med.	5½" Dia.			BC, CM
3522 AN	3-100w Med.	7" Dia.			BC, CM
3523 AN	3-75w Med.	5" Dia.	10'	1-4", 1-6", 1-12", 1-24"	BC, CM

*Maximum achievable height with stems included. Additional 12" stems available, 6068 AN.

CHARLOTTE™

FINISH BRUSHED CARAMEL

GLASS ETCHED OPAL

SHADE WOVEN OFF-WHITE FABRIC

Charlotte is an updated traditional design featuring a richly textured off-white fabric shade captured by wide solid metal uprights and trim rings. The domed bottom diffuser is captured inside a heavy trim ring and held by cast decorative knobs for a refined vintage touch.



3522 BC
20" DIA., 13½" H



3523 BC
16" DIA., 19½" H
68¼" MAX. H*



3521 BC
16" DIA., 13" H

ITEM	BULBS	CANOPY	WIRE	STEMS INCLUDED	ADDITIONAL FINISHES
3521 BC	3-75w Med.	5½" Dia.			AN, CM
3522 BC	3-100w Med.	7" Dia.			AN, CM
3523 BC	3-75w Med.	5" Dia.	10'	1-4", 1-6", 1-12", 1-24"	AN, CM

*Maximum achievable height with stems included. Additional 12" stems available, 4312 BC.

Charlotte is an updated traditional design featuring a richly textured off-white fabric shade captured by wide solid metal uprights and trim rings. The domed bottom diffuser is captured inside a heavy trim ring and held by cast decorative knobs for a refined vintage touch.

CHARLOTTE™

WOVEN OFF-WHITE FABRIC SHADE CHROME FINISH
ETCHED OPAL GLASS



3523 CM
16" DIA., 19½" H
68¼" MAX. H*



3522 CM
20" DIA., 13½" H



3521 CM
16" DIA., 13" H

ITEM	BULBS	CANOPY	WIRE	STEMS INCLUDED	ADDITIONAL FINISHES
3521 CM	3-75w Med.	5½" Dia.			AN, BC
3522 CM	3-100w Med.	7" Dia.			AN, BC
3523 CM	3-75w Med.	5" Dia.	10'	1-4", 1-6", 1-12", 1-24"	AN, BC

*Maximum achievable height with stems included. Additional 12" stems available, 4312 CM.

HARPER™

FINISH BRUSHED NICKEL, CHROME, HERITAGE BRASS, OIL RUBBED BRONZE
GLASS ETCHED OPAL

Harper's sleek, retro design elevates the traditional flush mount with a unique opal glass bound by a prominent metal ring and decorative knobs available in four finishes.



3643 BN
3643 BN-LED
18" DIA., 10" H



3643 HB
3643 HB-LED
18" DIA., 10" H



3643 OZ
3643 OZ-LED
18" DIA., 10" H



3643 CM
3643 CM-LED
18" DIA., 10" H





3641 BN
3641 BN-LED
14½" DIA., 10" H



3641 HB
3641 HB-LED
14½" DIA., 10" H



3641 OZ
3641 OZ-LED
14½" DIA., 10" H



3641 CM
3641 CM-LED
14½" DIA., 10" H

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	CANOPY
3641 BN	3-100w Med.	3641 BN-LED	32w LED	1900	2700K	96	2-100w	7" Dia.
3641 CM	3-100w Med.	3641 CM-LED	32w LED	1900	2700K	96	2-100w	7" Dia.
3641 HB	3-100w Med.	3641 HB-LED	32w LED	1900	2700K	96	2-100w	7" Dia.
3641 OZ	3-100w Med.	3641 OZ-LED	32w LED	1900	2700K	96	2-100w	7" Dia.
3643 BN	3-100w Med.	3643 BN-LED	48w LED	2850	2700K	96	3-100w	7" Dia.
3643 CM	3-100w Med.	3643 CM-LED	48w LED	2850	2700K	96	3-100w	7" Dia.
3643 HB	3-100w Med.	3643 HB-LED	48w LED	2850	2700K	96	3-100w	7" Dia.
3643 OZ	3-100w Med.	3643 OZ-LED	48w LED	2850	2700K	96	3-100w	7" Dia.

COLBIN™

FINISH AGED ZINC WITH POLISHED NICKEL, BRUSHED NICKEL,
OIL RUBBED BRONZE WITH BRUSHED BRONZE
GLASS ETCHED OPAL

Colbin is sleek, chic and poised. Its sleek etched opal glass and decorative knurled knobs enhance a design that easily crosses style boundaries, from traditional to modern.



3233 BN
16½" DIA., 5¾" H



3233 OZ
16½" DIA., 5¾" H



3233 DZ
16½" DIA., 5¾" H



3231 BN
12½" DIA., 4¾" H



3231 OZ
12½" DIA., 4¾" H



3231 DZ
12½" DIA., 4¾" H

ITEM	BULBS	CANOPY
3231 BN, 3231 DZ, 3231 OZ	2-60w Med.	11" Dia.
3233 BN, 3233 DZ, 3233 OZ	3-60w Med.	14¾" Dia.

Clancy's transitional design features a clear glass urn, retro decorative construction elements and soft curves for an elegant style with vintage overtones.

CLANCY™

AGED ZINC, BRUSHED NICKEL, BUCKEYE BRONZE, POLISHED NICKEL FINISH
CLEAR GLASS



3030 BN
6" W, 11¼" H



3030 DZ
6" W, 11¼" H



3030 KZ
6" W, 11¼" H



3030 PN
6" W, 11¼" H


ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE
3030 BN	1-100w Med.	6½"	5"	5" Dia.
3030 DZ	1-100w Med.	6½"	5"	5" Dia.
3030 KZ	1-100w Med.	6½"	5"	5" Dia.
3030 PN	1-100w Med.	6½"	5"	5" Dia.

MERCER™


FINISH ANTIQUE NICKEL, HERITAGE BRASS, OIL RUBBED BRONZE,
POLISHED NICKEL
GLASS ETCHED OPAL

Synonymous with vintage glamour, Mercer's mid-century modern design has a cool simplicity that blends robust metal construction and circular glass shades that emit a soft glow, creating a perfect accent for any decor.



3650 AN
6¾" W, 6¾" H





3650 HB
6¾" W, 6¾" H




3650 OZ
6¾" W, 6¾" H




3650 PN
6¾" W, 6¾" H



ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE
3650 AN	1-60w Cand.	4"	3½"	6" Dia.
3650 HB	1-60w Cand.	4"	3½"	6" Dia.
3650 OZ	1-60w Cand.	4"	3½"	6" Dia.
3650 PN	1-60w Cand.	4"	3½"	6" Dia.

Lanza makes a chic statement with its strong, rectangular metal work. The geometric detailing is softened with linen shades for a warm sophisticated look.


LANZA™


ANTIQUÉ NICKEL, BRUSHED BRONZE, OIL RUBBED BRONZE FINISH
OFF-WHITE LINEN HARDBACK AND OATMEAL LINEN SHADE




3162 AN
10" W, 11½" H





3162 BR
10" W, 11½" H




3162 OZ
10" W, 11½" H


ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE
3162 AN	2-60w Cand.	4"	3½"	5½" W, 5¾" H
3162 BR	2-60w Cand.	4"	3½"	5½" W, 5¾" H
3162 OZ	2-60w Cand.	4"	3½"	5½" W, 5¾" H





ABINGDON	\$316
ANYA	\$308
ARTEMIS	\$300
CARSON	\$320
DELFINA	\$302
EMILIE	\$318
EMPIRE	\$298
ENSEMBLE	\$294
EVE	\$312
GEMMA	\$303
GIGI	\$278
ISLA	\$304
KARMA	\$290
MIDDLEFIELD	\$319
MOXIE	\$286
ODETTE	\$282
SIRENA	\$306
SOLSTICE	\$288
TRYST	\$292
TULAH	\$310
ZUMA	\$274

ZUMA™

SCULPTURAL AND EXOTIC, ZUMA TANTALIZES WITH A PURELY CONTEMPORARY FORM. THE OVER-SCALED GEOMETRIC PENDANT IN WARM WHITE OR SATIN BLACK IS SOFTENED WITH LAYERS OF FINE GOLD JEWELERS' CHAIN FLOWING FROM ITS EPICENTER.

Zuma cable hung fixtures are provided with 12' of wire and 10' of cable.

Bulb specifications indicate maximum wattage.

OBJECT OF OUR
AFFECTION


Jewelers' chain adds a layer of glamorous texture to this chic statement piece.



FR32806WWT [43.25" W, 13.25" H, 8.75" D]



FR32805WWT [25.75" DIA., 18.25" H]



FR32804WWT [17.75" DIA., 14.25" H]

FR32804WWT
17.75" DIA., 14.25" H
4.75" DIA. CANOPY
6-60W CANDELABRA

FR32806WWT
43.25" W, 13.25" H, 8.75" D
4.75" W, 19.75" L CANOPY
5-60W CANDELABRA

FR32805WWT
25.75" DIA., 18.25" H
6" DIA. CANOPY
8-60W CANDELABRA

ZUMA™

SCULPTURAL AND EXOTIC, ZUMA TANTALIZES WITH A PURELY CONTEMPORARY FORM. THE OVER-SCALED GEOMETRIC PENDANT IN WARM WHITE OR SATIN BLACK IS SOFTENED WITH LAYERS OF FINE GOLD JEWELERS' CHAIN FLOWING FROM ITS EPICENTER.

Zuma cable hung fixtures are provided with 12' of wire and 10' of cable.


Bulb specifications indicate maximum wattage.



FR32806SBK [43.25" W, 13.25" H, 8.75" D]



FR32805SBK [25.75" DIA., 18.25" H]



FR32804SBK [17.75" DIA., 14.25" H]

FR32804SBK
17.75" DIA., 14.25" H
4.75" DIA. CANOPY
6-60W CANDELABRA

FR32806SBK
43.25" W, 13.25" H, 8.75" D
4.75" W, 19.75" L CANOPY
5-60W CANDELABRA

FR32805SBK
25.75" DIA., 18.25" H
6" DIA. CANOPY
8-60W CANDELABRA

GIGI™

GIGI'S ASYMMETRICAL SILHOUETTE CREATES A DRAMATIC STATEMENT. THE COLLECTION'S SLEEK LINES IMPART BOTH GLAMOUR AND SOPHISTICATION. AVAILABLE IN A CRYSTAL VERSION WITH A SEMI-TRANSLUCENT SHADE AND POLISHED NICKEL FINISH, OR A STYLISH TWO-TONE HERITAGE BRASS AND SATIN BLACK COMBINATION, GIGI IS THE ESSENCE OF CHIC.



Gigi stem hung fixtures are provided with 10' of wire and the following stems: (1) 6" and (2) 12"

*Maximum achievable height with stems included. Additional 12" stems are available: **6068HB**

FR34315HBR [26" DIA., 15.25" H]



SCONCE
FR34310HBR [5" W, 11.5" H]



FR34314HBR [21" DIA., 15.5" H]



FR34317HBR [10" DIA., 18.25" H]

FR34310HBR
5" W, 11.5" H, 3.25" EXT.
5" W, 11.5" H BACK PLATE
5.75" TTO
1-60W CANDELABRA
ADA compliant

FR34315HBR
26" DIA., 15.25" H
48.25" MAX. HEIGHT*
6.25" DIA. CANOPY
5-60W CANDELABRA

FR34314HBR
21" DIA., 15.5" H
48.75" MAX. HEIGHT*
6.25" DIA. CANOPY
3-60W CANDELABRA

FR34317HBR
10" DIA., 18.25" H
51.25" MAX. HEIGHT*
6.25" DIA. CANOPY
1-100W MEDIUM

GIGI™

GIGI'S ASYMMETRICAL SILHOUETTE CREATES A DRAMATIC STATEMENT. THE COLLECTION'S SLEEK LINES IMPART BOTH GLAMOUR AND SOPHISTICATION. AVAILABLE IN A CRYSTAL VERSION WITH A SEMI-TRANSLUCENT SHADE AND POLISHED NICKEL FINISH, OR A STYLISH TWO-TONE HERITAGE BRASS AND SATIN BLACK COMBINATION, GIGI IS THE ESSENCE OF CHIC.



Gigi stem hung fixtures are provided with 10' of wire and the following stems: (1) 6" and (2) 12"

*Maximum achievable height with stems included. Additional 12" stems are available: **FR86212PNI**

FR34415PNI [26" DIA., 15.25" H]



SCONCE
FR34410PNI [7.25" W, 12" H]



FR34417PNI [10" DIA., 18" H]



FR34414PNI [21" DIA., 15.25" H]

FR34410PNI
7.25" W, 12" H, 4" EXT.
5" W, 11.5" H BACK PLATE
6" TTO
1-60W CANDELABRA
ADA compliant


FR34415PNI
26" DIA., 15.25" H
48.25" MAX. HEIGHT*
6.25" DIA. CANOPY
5-60W CANDELABRA

FR34414PNI
21" DIA., 15.25" H
48.5" MAX. HEIGHT*
6.25" DIA. CANOPY
3-60W CANDELABRA

FR34417PNI
10" DIA., 18" H
51" MAX. HEIGHT*
6.25" DIA. CANOPY
1-100W MEDIUM

ODETTE™


THE LUXURIOUS COMPOSITION OF ODETTE'S MODERN DESIGN FORMS A STATEMENT-MAKING JEWELRY PIECE, CERTAIN TO BE THE CENTER OF ATTENTION. EMERALD CUT, SOLID GLASS CRYSTAL PANELS ADD BREATHTAKING SPARKLE. ODETTE IS OFFERED IN A GLEAMING POLISHED NICKEL OR LUSTROUS GUNMETAL FINISH.



Odette stem hung fixtures are provided with 10' of wire and the following stems: (1) 6" and (2) 12" For FR39216GMT: (2) 6", (4) 12"

*Maximum achievable height with stems included. Additional 12' stems are available:
For FR39214GMT and FR39215GMT: **FR86067GMT**
For FR39213GMT and FR39216GMT: **FR86037GMT**


FR39215GMT [30" DIA., 19.25" H]



SCONCE
FR39212GMT [13" W, 7.25" H]




FR39213GMT
CAN BE MOUNTED IN A
CLOSE TO CEILING POSITION.



FR39213GMT [17" DIA., 14" H]



FR39216GMT [42" W, 10" H, 8.25" D]



FR39214GMT [24" DIA., 16" H]

FR39212GMT
13" W, 7.25" H, 5.75" EXT.
7.5" W, 4.75" H BACK PLATE
3.75" TTO
2-60W CANDELABRA

FR39213GMT
17" DIA., 14" H
46.5" MAX. HEIGHT*
6" DIA. CANOPY
4-60W CANDELABRA


FR39214GMT
24" DIA., 16" H
48.5" MAX. HEIGHT*
6" DIA. CANOPY
6-60W CANDELABRA

FR39215GMT
30" DIA., 19.25" H
51.75" MAX. HEIGHT*
6" DIA. CANOPY
9-60W CANDELABRA

FR39216GMT
42" W, 10" H, 8.25" D
42.5" MAX. HEIGHT*
4.75" W, 26.75" L CANOPY
6-60W CANDELABRA

ODETTE™


THE LUXURIOUS COMPOSITION OF ODETTE'S MODERN DESIGN FORMS A STATEMENT-MAKING JEWELRY PIECE, CERTAIN TO BE THE CENTER OF ATTENTION. EMERALD CUT, SOLID GLASS CRYSTAL PANELS ADD BREATHTAKING SPARKLE. ODETTE IS OFFERED IN A GLEAMING POLISHED NICKEL OR LUSTROUS GUNMETAL FINISH.



Odette stem hung fixtures are provided with 10' of wire and the following stems: (1) 6" and (2) 12" For FR39216PNI: (2) 6", (4) 12"

*Maximum achievable height with stems included. Additional 12' stems are available:
For FR39214GMT and FR39215GMT: **6067PN**
For FR39213GMT and FR39216GMT: **6037PN**


FR39215PNI [30" DIA., 19.25" H]




SCONCE
FR39212PNI [13" W, 7.25" H]




FR39213PNI
CAN BE MOUNTED IN A
CLOSE TO CEILING POSITION.



FR39213PNI [17" DIA., 14" H]



FR39216PNI [42" W, 10" H, 8.25" D]



FR39214PNI [24" DIA., 16" H]

FR39212PNI
13" W, 7.25" H, 5.75" EXT.
7.5" W, 4.75" H BACK PLATE
3.75" TTO
2-60W CANDELABRA

FR39213PNI
17" DIA., 14" H
46.5" MAX. HEIGHT*
6" DIA. CANOPY
4-60W CANDELABRA

FR39214PNI
24" DIA., 16" H
48.5" MAX. HEIGHT*
6" DIA. CANOPY
6-60W CANDELABRA

FR39215PNI
30" DIA., 19.25" H
51.75" MAX. HEIGHT*
6" DIA. CANOPY
9-60W CANDELABRA

FR39216PNI
42" W, 10" H, 8.25" D
42.5" MAX. HEIGHT*
4.75" W, 26.75" L CANOPY
6-60W CANDELABRA

MOXIE™

A STAR IS BORN. MOXIE TAKES CENTER STAGE WITH A SHOW-STOPPING DESIGN OF INTERLOCKING HEXAGONS SUSPENDED FROM SLEEK CABLES. ITS CONTEMPORARY FORM AND ROBUST CONSTRUCTION IS CONFIDENTLY UNDERSCORED BY A DRAMATIC SUNSET GOLD AND BRONZE TWO-TONE FINISH COMBINATION THAT COMMANDS THE ROOM'S ATTENTION.

Moxie chandeliers are provided with 12' of wire and 10' of cable.


Bulb specifications indicate maximum wattage.



FR38016SSG [30.25" W, 4" H]



FR38018SSG [45.5" W, 4" H, 30.25" D]



FR38015SSG [22" DIA., 8" H]



SCONCE
FR38012SSG [12" W, 19.75" H]

FR38012SSG
12" W, 19.75" H, 5" EXT.
10" W, 5" H BACK PLATE
3.5" TTO
2-60W CANDELABRA

FR38016SSG
30.25" W, 4" H
7" DIA. CANOPY
6-60W CANDELABRA

FR38015SSG
22" DIA., 8" H
7" DIA. CANOPY
6-60W CANDELABRA

FR38018SSG
45.5" W, 4" H, 30.25" D
7" DIA. CANOPY
8-60W CANDELABRA

SOLSTICE™

THE CONTEMPORARY, STEM HUNG DESIGN OF SOLSTICE CREATES AN INTERSECTING TRANSPARENT SPHERE WITH SEMI-CIRCULAR GLASS PANELS BROUGHT TOGETHER BY BOLD METAL HINGES. AVAILABLE IN SMOKED GLASS AND HEIRLOOM BRASS OR IN CLEAR GLASS WITH POLISHED CHROME.



Solstice stem hung fixtures are provided with 10' of wire and the following stems: (1) 6', (1) 12', and (1) 18'

*Maximum achievable height with stems included. Additional 12" stems are available: **6035HR**

Bulb specifications indicate maximum wattage.

FR47506HRR [24" DIA., 24.75" H]



FR47505HRR [18" DIA., 18.75" H]



FR47507HRR [13" DIA., 13" H]

FR47505HRR
 18" DIA., 18.75" H
 58" MAX. HEIGHT*
 5.5" DIA. CANOPY
 4-60W CANDELABRA

FR47507HRR
 13" DIA., 13" H
 52.25" MAX. HEIGHT*
 5.5" DIA. CANOPY
 1-100W MEDIUM

FR47506HRR
 24" DIA., 24.75" H
 64" MAX. HEIGHT*
 5.5" DIA. CANOPY
 4-100W MEDIUM

KARMA™

KARMA'S MODERN EUROPEAN DESIGN IS CONSTRUCTED FROM LIGHT WEIGHT DIE CAST ALUMINUM. THE UNIQUE ARM DESIGN FEATURES UP AND DOWN LAMPING, COMPLEMENTED BY A CHIC CHAMPAGNE OR POLISHED NICKEL FINISH.




Karma stem hung fixtures are provided with 10' of wire and the following stems: (1) 4", (1) 6", (1) 12", and (1) 18"


*Maximum achievable height with stems included. Additional 12" stems are available: **FR86069CPN**

Bulb specifications indicate maximum wattage.

FR41949CPN [30.25" W, 18.75" H]



FR41948CPN [30.75" W, 11.75" H]



FR41946CPN [30.25" W, 5" H]



SCONCE
FR41941CPN [5" W, 5" H]

FR41941CPN
5" W, 5" H, 4" EXT.
5" DIA. BACK PLATE
2.5" TTO
2-60W CANDELABRA
Shown with G16½ bulbs
Invisible mounting hardware
ADA Compliant

FR41946CPN
30.25" W, 5" H
36.25" MAX. HEIGHT*
4.75" DIA. CANOPY
12-60W CANDELABRA
Shown with G16½ bulbs

FR41948CPN
30.75" W, 11.75" H
43" MAX. HEIGHT*
4.75" DIA. CANOPY
18-60W CANDELABRA
Shown with G16½ bulbs

FR41949CPN
30.25" W, 18.75" H
50" MAX. HEIGHT*
4.75" DIA. CANOPY
24-60W CANDELABRA
Shown with G16½ bulbs

TRYST™

A SEAMLESS BLEND OF VINTAGE SOPHISTICATION AND CONTEMPORARY CLOUT, TRYST OFFERS A STRIKING MIX OF DESIGN ELEMENTS. HAMMERED BRONZE STEMS RADIATING FROM A SPHERICAL BODY SHIMMER AS THE LIGHT DANCES ACROSS THE FACETS, CREATING A ROBUST YET AIRY EFFECT.




Tryst stem hung fixtures are provided with 10' of wire and the following stems: (1) 6" and (2) 12"

*Maximum achievable height with stems included. Additional 12" stems are available: **FR86060HBZ**

Bulb specifications indicate maximum wattage.

FR43016HBZ [42" DIA., 42" H]



FR43015HBZ [30" DIA., 30" H]



FR43014HBZ [22" DIA., 22" H]

FR43014HBZ
 22" DIA., 22" H
 57" MAX. HEIGHT*
 6.5" DIA. CANOPY
 8-60W CANDELABRA

FR43016HBZ
 42" DIA., 42" H
 77" MAX. HEIGHT*
 6.5" DIA. CANOPY
 16-40W CANDELABRA

FR43015HBZ
 30" DIA., 30" H
 65" MAX. HEIGHT*
 6.5" DIA. CANOPY
 12-60W CANDELABRA

ENSEMBLE™

ENSEMBLE'S DARING SILHOUETTE COMBINES LAYERS OF SLEEK EDGES WITH A GLEAMING POLISHED NICKEL FINISH TO CREATE A CAPTIVATING FORM FROM ANY ANGLE.




Ensemble stem hung fixtures are provided with 10' of wire and the following stems: For FR42449PNI: (1) 4", (1) 6", (2) 12", (1) 30"
For FR42446PNI: (2) 4", (2) 6", (4) 12"

*Maximum achievable height with stems included. Additional 12" stems are available: **FR86212PNI**

Bulb specifications indicate maximum wattage.

FR42449PNI [32.5" W, 52.5" H]



FR42446PNI [62" W, 13.25" H, 8.25" D]



FR42448PNI [28" W, 46.5" H]



FR42442PNI [17.5" W, 25.5" H]

FR42442PNI
 17.5" W, 25.5" H, 7" EXT.
 7" DIA. BACK PLATE
 3.5" TTO
 2-100W MEDIUM


FR42448PNI
 28" W, 46.5" H
 71.5" MAX. HEIGHT*
 5" SQUARE CANOPY
 7-100W MEDIUM

FR42446PNI
 62" W, 13.25" H, 8.25" D
 45.5" MAX. HEIGHT*
 6" W, 10" L CANOPY
 6-100W MEDIUM

FR42449PNI
 32.5" W, 52.5" H
 89.5" MAX. HEIGHT*
 5" SQUARE CANOPY
 13-75W MEDIUM
 Fixture exceeds 50lbs.



FR42447PNI
Shown mounted as a sconce



FR42447PNI [7" W, 11.75" H]

FR42444PNI
30.75" W, 31.25" H
68.25" MAX. HEIGHT*
5" SQUARE CANOPY
5-100W MEDIUM

FR42447PNI
7" W, 11.75" H
125" MAX. HEIGHT*
5" SQUARE CANOPY
1-100W MEDIUM

FR42445PNI
33" W, 32.75" H
69.75" MAX. HEIGHT*
5" SQUARE CANOPY
9-100W MEDIUM



FR42444PNI [30.75" W, 31.25" H]



FR42445PNI [33" W, 32.75" H]



ENSEMBLE FR42449PNI

EMPIRE™

EMPIRE'S STATELY PRESENCE FEATURES SQUARE-FACETED GLASS PILLARS COMPLEMENTED BY A GLEAMING POLISHED NICKEL FOR DRAMATIC EFFECT.



Empire chandeliers are provided with 12' of wire and 10' of chain.

Empire stem hung fixtures are provided with 10' of wire and the following stems:

For FR36013PNI: (2) 6", (2) 12"

For FR36018PNI: (4) 6", (4) 12"

*Maximum achievable height with stems included. Additional 12" stems are available:

4312PN

Bulb specifications indicate maximum wattage.

FR36015PNI [17" W, 33.25" H]




FR36014PNI [13" W, 26" H]



FR36013PNI [15.25" W, 15.25" H]



SCNCE
FR36012PNI [8" W, 16" H]



FR36018PNI [48" W, 12.5" H, 10" D]

FR36012PNI
8" W, 16" H, 4" EXT.
6" W, 15.75" H BACK PLATE
8" TTO
2-60W CANDELABRA
ADA Compliant

FR36013PNI
15.25" W, 15.25" H
53.75" MAX. HEIGHT*
6" SQUARE CANOPY
4-60W CANDELABRA

FR36014PNI
13" W, 26" H
6" SQUARE CANOPY
4-60W CANDELABRA

FR36015PNI
17" W, 33.25" H
6" SQUARE CANOPY
4-60W CANDELABRA

FR36018PNI
48" W, 12.5" H, 10" D
51" MAX. HEIGHT*
4.5" W, 18" L CANOPY
6-60W CANDELABRA

ARTEMIS™

THE EYE-CATCHING DESIGN OF THE ARTEMIS PENDANT IS A BOLD MERGER OF ATMOSPHERE AND ARCHITECTURE. AN OPEN STEEL FRAME SLEEKLY COMBINES ANTIQUE NICKEL AND BLACK CHROME FINISHES, ENCLOSING AN ELEGANT INTERIOR GLOBE THAT IS ORGANICALLY FORMED FROM SUSPENDED SMOKED CRYSTALS.

FR48204ANI

18" W, 16.5" H
55.25" MAX. HEIGHT*
6" DIA. CANOPY
4-60W CANDELABRA


FR48205ANI

22" W, 24" H
62.5" MAX. HEIGHT*
6" DIA. CANOPY
5-60W CANDELABRA

Artemis stem hung fixtures are provided with 10' of wire and the following stems: (1) 6", (3) 12"

*Maximum achievable height with stems included. Additional 12" stems are available:
For FR48204ANI: **FR86035BCM**
For FR48205ANI: **FR86065BCM**

Bulb specifications indicate maximum wattage.



FR48205ANI [22" W, 24" H]



FR48204ANI [18" W, 16.5" H]

DELFINA™

THE DELFINA COLLECTION FEATURES A BOLDLY ELEGANT STEEL RIBBON AVAILABLE IN DELUXE GOLD OR METALLIC MATTE BRONZE. THIS ORGANIC SHAPE IS BOTH VISUALLY INTRIGUING AND PLEASING AS THE LIGHT FLOWS GENTLY ACROSS THE OVERLAPPING RIBBONS.

FR48602DXG

9" W, 12" H, 6" EXT.
4.5" SQ. BACK PLATE
6" TTO
2-60W CANDELABRA

FR48602MMB

9" W, 12" H, 6" EXT.
4.5" SQ. BACK PLATE
6" TTO
2-60W CANDELABRA

Bulb specifications indicate maximum wattage.



FR48602DXG [9" W, 12" H]



FR48602MMB [9" W, 12" H]

GEMMA™

Gemma stem hung fixtures are provided with 10' of wire and the following stems: (2) 6", (2) 12" and (2) 18"

*Maximum achievable height with stems included. Additional 12" stems are available: **FR84512SLF5**, **FR84512VBZ5**

Bulb specifications indicate maximum wattage.

GEMMA IS A CONTEMPORARY CHANDELIER COLLECTION WITH STUNNING RECTANGULAR PRISMS OF AMBER PEARL AND CLEAR CRYSTAL SET WITHIN A FRAME OF SILVER LEAF OR VINTAGE BRONZE TO CREATE A SEAMLESS SPARKLING, JEWELRY-LIKE EFFECT.



FR33738VBZ [45" W, 10.25" H, 14" D]

FR33738SLF
45" W, 10.25" H, 14" D
49" MAX. HEIGHT*
4.75" W, 12" L CANOPY
6-100W MEDIUM

FR33738VBZ
45" W, 10.25" H, 14" D
49" MAX. HEIGHT*
4.75" W, 12" L CANOPY
6-100W MEDIUM



FR33738SLF [45" W, 10.25" H, 14" D]

ISLA™

ISLA DRAWS INSPIRATION FROM THE SEA, SEAMLESSLY MESHING SOPHISTICATED COASTAL ACCENTS INTO A SOOTHING TRANSITIONAL DESIGN. THE RECURRING GEOMETRIC PATTERN OF WHITE CAPIZ SHELL DIAMONDS, CIRCLES AND SQUARES RESTS AGAINST THE BACKDROP OF AN ELEGANT SILVER ORGANZA SHADE SET INSIDE A SILVER LEAF FRAME.



FR37123SLF
CAN BE MOUNTED IN A
CLOSE TO CEILING POSITION.




FR37123SLF [23.75" DIA., 10.5" H]

Isla stem hung fixtures are provided with 10' of wire and the following stems: (1) 6" and (2) 12"

*Maximum achievable height with stems included. Additional 12" stems are available: **FR84312SLF3**

Bulb specifications indicate maximum wattage.



FR37127SLF [9.75" DIA., 10" H]



SCONCE
FR37122SLF [7.75" W, 9.5" H]

FR37122SLF
7.75" W, 9.5" H, 4" EXT.
7.75" W, 9.5" H BACK PLATE
4.75" TTO
2-60W CANDELABRA
ADA compliant

FR37127SLF
9.75" DIA., 10" H
42.25" MAX. HEIGHT*
5" DIA. CANOPY
1-100W MEDIUM

FR37123SLF
23.75" DIA., 10.5" H
43" MAX. HEIGHT*
6" DIA. CANOPY
3-100W MEDIUM

SIRENA™

SIRENA EXUDES EUROPEAN SOPHISTICATION IN THIS TRANSITIONAL COLLECTION, DETAILED WITH CLASSICALLY INSPIRED NATURAL ELEMENTS. AN OUTER FRAME OF INLAID KABIBE SHELL CAPTURES A FLUID WAVELIKE PATTERN IN HAND-APPLIED SILVER LEAF. A GRACEFULLY TAPERED CENTER COLUMN SEAMLESSLY TRANSITIONS TO CURVED CANDELABRA ARMS WITH KABIBE BOBESHES BENEATH AN OYSTER ORGANZA DRUM SHADE.

OBJECT OF OUR

AFFECTION

Integrating exotic natural kabibe shell adds a layer of luminous organic beauty.



Sirena chandeliers are provided with 12' of wire and 10' of chain.

Bulb specifications indicate maximum wattage.

FR48055CPG [22.25" DIA., 29.25" H]



FR48053CPG [16" DIA., 13.75" H]



SCONCE
FR48052CPG [8" W, 12" H]



FR48056CPG [36" W, 30" H]

FR48052CPG
8" W, 12" H, 4.75" EXT.
8" W, 12" H BACK PLATE
6" TTO
2-60W CANDELABRA

FR48053CPG
16" DIA., 13.75" H
4.75" DIA. CANOPY
4-60W CANDELABRA

FR48055CPG
22.25" DIA., 29.25" H
5" DIA. CANOPY
5-60W CANDELABRA

FR48056CPG
36" W, 30" H
4.5" W, 8" L CANOPY
6-60W CANDELABRA

ANYA™

HIGH IMPACT GLAMOUR PAIRS WITH ARTISAN CRAFTSMANSHIP TO CREATE ANYA'S CHIC SILHOUETTE. A FREE-FORM PATTERN OF CONNECTED CIRCLES IN VARYING SIZES EXUDE AN EFFERVESCENT, ORGANIC ELEGANCE. SPARKLING FACETED CRYSTALS ARE INDIVIDUALLY PLACED WITHIN SILVER LEAF RINGS, RADIATING LUXURY AND DRAMA FROM EVERY ANGLE.



FR44819SLF [20" DIA., 42.75" H]

Anya chandeliers are provided with 12' of wire and 10' of chain.

FR44817SLF is provided with 10' of wire and the following stems: (1) 6' and (2) 12'

*Maximum achievable height with stems included. Additional 12" stems are available: **FR86060SLF**

Bulb specifications indicate maximum wattage.



FR44814SLF [24" DIA., 16" H]



FR44817SLF [8" DIA., 12.25" H]



FR44816SLF [16" DIA., 31.5" H]



FR44818SLF [40" W, 13.25" H, 24" D]



FR44812SLF [8" W, 14" H]



FR44813SLF [16" DIA., 11" H]

FR44812SLF
8" W, 14" H, 4.75" EXT.
6.5" DIA. BACK PLATE
7" TTO
2-60W CANDELABRA

FR44813SLF
16" DIA., 11" H
6.5" DIA. CANOPY
4-60W CANDELABRA

FR44814SLF
24" DIA., 16" H
5" DIA. CANOPY
6-60W CANDELABRA

FR44816SLF
16" W, 31.5" H
5" DIA. CANOPY
6-60W CANDELABRA

FR44817SLF
8" DIA., 12.25" H
44.5" MAX. HEIGHT*
5" DIA. CANOPY
1-100W MEDIUM

FR44818SLF
40" W, 13.25" H, 24" D
4.5" W, 8" L CANOPY
10-60W CANDELABRA

FR44819SLF
20" DIA., 42.75" H
5" DIA. CANOPY
9-60W CANDELABRA
Fixture exceeds 50lbs.

TULAH™

TULAH'S MULTIFACETED ASYMMETRICAL DESIGN IS HAND CRAFTED WITH ARTISAN DETAILS. ITS BEAUTY UNFOLDS IN LAYERS, REVEALING DELICATELY SCALLOPED CANOPIES, A LUSTROUS SILVER LEAF FINISH, AND DAZZLING FACETED CLEAR CRYSTAL EMBELLISHMENTS ADDING THE PERFECT AMOUNT OF SPARKLE.

Tulah chandeliers are provided with 12' of wire and 10' of chain.

Bulb specifications indicate maximum wattage.



FR31028SLF [26.5" DIA., 34.25" H]



FR31025SLF [28" DIA., 19.25" H]



FR31027SLF [12" DIA., 15.25" H]



FR31023SLF [15" DIA., 7.75" H]



FR31022SLF [9" W, 11.75" H]



FR31024SLF [20" DIA., 25.5" H]

FR31022SLF
 9" W, 11.75" H, 5.25" EXT.
 4.75" W, 8.75" H BACK PLATE
 6.75" TTO
 2-60W CANDELABRA

FR31023SLF
 15" DIA., 7.75" H
 10" DIA. CANOPY
 3-60W CANDELABRA

FR31024SLF
 20" DIA., 25.5" H
 6.5" DIA. CANOPY
 4-60W CANDELABRA

FR31025SLF
 28" DIA., 19.25" H
 6.5" DIA. CANOPY
 5-60W CANDELABRA

FR31027SLF
 12" DIA., 15.25" H
 6.5" DIA. CANOPY
 2-60W CANDELABRA

FR31028SLF
 26.5" DIA., 34.25" H
 6.5" DIA. CANOPY
 8-60W CANDELABRA

EVE™

EVE CREATES AN INTOXICATING AND WHIMSICAL FUSION OF FINISH, TEXTURE AND DESIGN. GRACEFUL, HAND-FORGED TUBING CREATES A NATURAL, VINE-LIKE PATTERN IN A LUSH CHAMPAGNE GOLD FINISH, CONTRASTING AGAINST THE CLEAN, SLEEK CANDLE SLEEVES AND CENTER COLUMN. FACETED CLEAR CRYSTAL "BUDS" EMANATE FROM THE TIPS CREATING AN ORGANIC, VISUAL FEAST.

Eve chandeliers are provided with 12' of wire and 10' of chain.

Bulb specifications indicate maximum wattage.



FR46810CPG [48.5" DIA., 44" H]



FR46806CPG [26" DIA., 30" H]



FR46803CPG [18.5" DIA., 34.75" H]



FR46809CPG [33.5" DIA., 36" H]

FR46803CPG
18.5" DIA., 34.75" H
5" DIA. CANOPY
3-60W CANDELABRA

FR46809CPG
33.5" DIA., 36" H
5" DIA. CANOPY
9-60W CANDELABRA

FR46806CPG
26" DIA., 30" H
5" DIA. CANOPY
6-60W CANDELABRA

FR46810CPG
48.5" DIA., 44" H
6.5" DIA. CANOPY
12-60W CANDELABRA



FR46802CPG [14.25" W, 15.5" H]



FR46800CPG [5.5" W, 16" H]

FR46800CPG
 5.5" W, 16" H, 8" EXT.
 5.5" DIA. BACK PLATE
 10" TTO
 1-60W CANDELABRA

FR46801CPG
 16" DIA., 10.75" H
 6.5" DIA. CANOPY
 4-60W CANDELABRA

FR46802CPG
 14.25" W, 15.5" H, 6.75" EXT.
 5.5" DIA. BACK PLATE
 8.25" TTO
 2-60W CANDELABRA

FR46804CPG
 18" DIA., 26.25" H
 6.5" DIA. CANOPY
 3-60W CANDELABRA



FR46804CPG [18" DIA., 26.25" H]



FR46801CPG [16" DIA., 10.75" H]



FR46808CPG [20" DIA., 39" H]



FR46805CPG [14.5" DIA., 29" H]

FR46805CPG
14.5" DIA., 29" H
6.5" DIA. CANOPY
6-60W CANDELABRA

FR46808CPG
20" DIA., 39" H
6.5" DIA. CANOPY
9-60W CANDELABRA

ABINGDON™

RUSTIC YET SOPHISTICATED, ABINGDON FINDS INSPIRATION IN THE CHARM OF A EUROPEAN COUNTRY CHATEAU. INTEGRATING RAW AND REFINED MATERIALS, A MODEST OPEN GLOBE OF WEATHERED ASH WOOD IS ACCENTED BY THE CHIC PATINA OF SILVER LEAF BANDING. AN INTRICATE INTERIOR CHANDELIER IS COMPOSED OF SCROLLED ARMS AND SOLID GLASS CHAMPAGNE DROPS FOR A LUXE, TIMELESS APPEAL.

Abingdon wood finish:
Weathered Ash (WTA)

Abingdon chandeliers are
provided with 12' of wire and
10' of chain.

Bulb specifications indicate
maximum wattage.



FR37235SLF [30.25" DIA., 32.5" H]



FR37233SLF [24.25" DIA., 26" H]



FR37231SLF [24.25" DIA., 12.25" H]

FR37231SLF
24.25" DIA., 12.25" H
14.75" DIA. CANOPY
4-60W CANDELABRA

FR37233SLF
24.25" DIA., 26" H
5.25" DIA. CANOPY
4-60W CANDELABRA

FR37235SLF
30.25" DIA., 32.5" H
5.25" DIA. CANOPY
4-60W CANDELABRA

EMILIE™

EMILIE EXUDES COTTAGE-CHIC STYLE WHILE RETAINING A CONTEMPORARY SENSIBILITY. THE BOLD OPENWORK WOODEN DESIGN IN COTTAGE WHITEWASH OFFERS RUSTIC MINIMALISM. THE COLLECTION'S SIMPLE SILHOUETTES INSPIRE A MODERN FARMHOUSE VIBE OR OFFER THE OPTION OF A TRADITIONAL CHANDELIER, RICHLY LAYERED WITH ELEGANT DETAILS LIKE FACETED CRYSTAL DROPS, FLORETS AND BOBECHES.

FR41213IRR

14" W, 34" H
5.25" DIA. CANOPY
3-60W CANDELABRA

FR41214IRR

16" W, 38" H
5.25" DIA. CANOPY
4-60W CANDELABRA



FR41214IRR [16" W, 38" H]



FR41213IRR [14" W, 34" H]

Emilie wood finish: Cottage Whitewash (CWW)

Emilie chandeliers are provided with 12' of wire and 10' of chain.

Bulb specifications indicate maximum wattage.

MIDDLEFIELD™

Middlefield wood finish:
Weathered Ash (WTA)

Bulb specifications indicate
maximum wattage.

MIDDLEFIELD'S RUSTIC-CHIC DESIGN CAPTURES A HISTORICAL FEEL WITH ITS SOLID DISTRESSED WOOD REMINISCENT OF WEATHERED ASH, STEEL CONSTRUCTION AND IRON RUST FINISH. A PEAR-SHAPED WOOD FINIAL ADDS AN ADDITIONAL ELEGANT DETAIL AND MAY BE HUNG INSIDE OR OUTSIDE THE FRAME.

FR40571IRR
23.75" W, 13.25" H
14.75" DIA. CANOPY
4-100W MEDIUM



FR40571IRR [23.75" DIA., 13.25" H]



OTHER *POPULAR STYLES* FROM
THE MIDDLEFIELD COLLECTION



FROM LEFT: FR40566IRR, FR40575IRR, FR40572IRR, FR40564IRR, FR40579IRR

CARSON™

CARSON PAIRS A HINT OF INDUSTRIAL SOPHISTICATION AND REPURPOSED CRAFTSMANSHIP WITH ITS BOLD OVERLAPPING METAL RIBBONS. THE HAND-CRAFTED PENDANTS IN AN IRON RUST FINISH ARE SUSPENDED FROM AN AGED ROPE COLUMN FOR A SUBTLE TOUCH OF RECLAIMED CHARM.

Carson chandeliers are provided with 12' of wire and 10' of chain.

Bulb specifications indicate maximum wattage.



FR40708VIR [34" DIA., 43" H]



FR40703VIR [19" DIA., 26" H]



FR40707VIR [12.5" DIA., 14.25" H]



FR40705VIR [26.5" DIA., 33.25" H]

FR40703VIR
19" DIA., 26" H
4.75" DIA. CANOPY
3-60W CANDELABRA

FR40705VIR
26.5" DIA., 33.25" H
4.75" DIA. CANOPY
5-60W CANDELABRA

FR40707VIR
12.5" DIA., 14.25" H
4.75" DIA. CANOPY
1-100W MEDIUM

FR40708VIR
34" DIA., 43" H
5.25" DIA. CANOPY
8-60W CANDELABRA



A BLUEPRINT FOR DESIGN

Set your mind at ease with this calm and cleansing hue. Bathrooms with a spa-like essence provide needful serenity to the space where we rise in the morning and unwind at day's end. Whether you gravitate toward deep teal tones or are drawn to the cool freshness of marine and mist, we're all shining light on the many shades of blue.

ABOVE: BENNETT 5350PN

BATH COLLECTIONS



AVON	S333
BALDWIN	S344
BENNETT	S334
BLYTHE	S342
CLANCY	S335
DAPHNE	S328
FAYE	S341
JACKSON	S330
KYRA	S338
LATITUDE	S329
MILA	S327
SADIE	S337
SIMI	S325
TESSA	S340
THISTLEDOWN	S346
VERVE	S336



SCANDINAVIAN SIMPLICITY

Nordic style is the sweet spot of interiors; creating timeless modernism with exceptional ease. Streamlined forms, a curation of thoughtful sustainable materials and a fixture with a crisp chrome finish elevate a functional space to the height of style.

ABOVE: SIMI 59923CM

Minimal in form, Simi makes a strong case for simplicity.
 Sleek end caps and a center bracelet in Chrome or
 Brushed Nickel finish options add a seamless finishing
 touch to the slim profile.

SIMI™

CHROME FINISH
 ETCHED OPAL GLASS



59923 CM
 5¼" W, 22¾" H
 (mounted vertically)



59922 CM
 5¼" W, 12½" H



59923 CM
 22¾" W, 5¼" H



59924 CM
 32¼" W, 5¼" H

LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
59922 CM	17w LED	1250	3000K	92	1-100w	3¾"	10½"	5¼" W, 6¾" H	BN	•
59923 CM	33w LED	2450	3000K	92	4-60w	3¾"	2¾"	6¾" W, 5¼" H	BN	•
59924 CM	52w LED	3800	3000K	92	6-60w	3¾"	2¾"	6¾" W, 5¼" H	BN	•

Simi fixtures are fully dimmable. LED components have a lifespan of 30,000 hours and carry a 5-year limited warranty.

SIMI™

FINISH BRUSHED NICKEL
GLASS ETCHED OPAL

Minimal in form, Simi makes a strong case for simplicity. Sleek end caps and a center bracelet in Chrome or Brushed Nickel finish options add a seamless finishing touch to the slim profile.



59923 BN
5 1/4" W, 22 3/4" H
(mounted vertically)



59922 BN
5 1/4" W, 12 1/2" H



59923 BN
22 3/4" W, 5 1/4" H



59924 BN
32 1/4" W, 5 1/4" H



LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
59922 BN	17w LED	1250	3000K	92	1-100w	3 3/4"	10 1/2"	5 1/4" W, 6 3/4" H	CM	•
59923 BN	33w LED	2450	3000K	92	4-60w	3 3/4"	2 3/4"	6 3/4" W, 5 1/4" H	CM	•
59924 BN	52w LED	3800	3000K	92	6-60w	3 3/4"	2 3/4"	6 3/4" W, 5 1/4" H	CM	•

Simi fixtures are fully dimmable. LED components have a lifespan of 30,000 hours and carry a 5-year limited warranty.

Mila's modern design captivates with sleek symmetry as the elongated shades appear to float next to angled panel transitions to create a seamless form.



Top view of Mila glass showing oval shape.

MILA™

CHROME FINISH
ETCHED OPAL GLASS



53552 CM
53552 CM-LED
16" W, 5" H



53553 CM
53553 CM-LED
24" W, 5" H



53550 CM
53550 CM-LED
7¾" W, 10" H



53554 CM
53554 CM-LED
32¼" W, 5" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
53550 CM	1-60w G9 halogen*	53550 CM-LED	1-4.5w G9 LED**	4"	5"	7¾" W, 10" H	BN	•
53552 CM	2-60w G9 halogen*	53552 CM-LED	2-4.5w G9 LED**	4"	2½"	16" W, 5" H	BN	•
53553 CM	3-60w G9 halogen*	53553 CM-LED	3-4.5w G9 LED**	4"	2½"	24" W, 5" H	BN	•
53554 CM	4-60w G9 halogen*	53554 CM-LED	4-4.5w G9 LED**	4"	2½"	32¼" W, 5" H	BN	•

*G9 halogen bulbs included. **G9 LED bulbs included.

DAPHNE™

FINISH BRUSHED NICKEL, CHROME

GLASS ETCHED BUBBLE ART

Daphne features contemporary pocket style bubble art glass set against a sleek raceway back plate in chic Chrome or Brushed Nickel finishes. The etched bottom lens conceals the light source.



5922 BN-LED2,
5922 CM-LED2 (shown)
16" W, 5" H



5923 BN-LED2,
5923 CM-LED2 (shown)
24" W, 5" H



5920 BN-LED2 (shown),
5920 CM-LED2
8½" W, 9" H



5924 BN-LED2 (shown),
5924 CM-LED2
32" W, 5" H



5925 BN-LED2,
5925 CM-LED2 (shown)
40" W, 5" H




LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE
5920 BN-LED2, 5920 CM-LED2	7w LED	600	2700K	90	1-60w	4¼"	4½"	8½" W, 9" H
5922 BN-LED2, 5922 CM-LED2	14w LED	1200	2700K	90	2-60w	4¼"	2½"	16" W, 5" H
5923 BN-LED2, 5923 CM-LED2	21w LED	1800	2700K	90	3-60w	4¼"	2¾"	16" W, 5" H
5924 BN-LED2, 5924 CM-LED2	28w LED	2400	2700K	90	4-60w	4¼"	2¾"	16" W, 5" H
5925 BN-LED2, 5925 CM-LED2	35w LED	3000	2700K	90	5-60w	4¼"	2¾"	16" W, 5" H

Daphne fixtures are fully dimmable. LED components have a lifespan of 40,000 hours and carry a 5-year limited warranty.

Latitude is contemporary and sleek, finding its true beauty in the minimalist design. The slim glass panel features rectangular etching while the subtle, split fork frames add understated architectural style.

LATITUDE™

BRUSHED NICKEL, CHROME, OIL RUBBED BRONZE FINISH
CLEAR BEVELED INSIDE ETCHED GLASS



5652 BN-LED2,
5652 CM-LED2,
5652 OZ-LED2 (shown)
18" W, 5½" H



NEW

SLEEK & STREAMLINED
ADA COMPLIANT PROFILE
WITH IMPROVED LED
PERFORMANCE



5654 BN-LED2 (shown),
5654 CM-LED2,
5654 OZ-LED2
26" W, 5½" H



5650 BN-LED2,
5650 CM-LED2 (shown),
5650 OZ-LED2
5" W, 8" H



5656 BN-LED2,
5656 CM-LED2 (shown),
5656 OZ-LED2
37½" W, 5½" H



LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE
5650 BN-LED2, 5650 CM-LED2, 5650 OZ-LED2	7w LED	600	2700K	90	1-60w	3½"	4"	5" W, 8" H
5652 BN-LED2, 5652 CM-LED2, 5652 OZ-LED2	14w LED	1200	2700K	90	2-60w	3½"	3¼"	17" W, 4¾" H
5654 BN-LED2, 5654 CM-LED2, 5654 OZ-LED2	28w LED	1800	2700K	90	3-60w	3½"	3¼"	25" W, 4¾" H
5656 BN-LED2, 5656 CM-LED2, 5656 OZ-LED2	42w LED	2400	2700K	90	4-60w	3½"	3¼"	36¼" W, 4¾" H

Latitude fixtures are fully dimmable. LED components have a lifespan of 40,000 hours and carry a 5-year limited warranty.

JACKSON™


FINISH POLISHED NICKEL

GLASS CLEAR SEEDY

Jackson merges traditional details such as clear seedy glass, finished glass collars and distinctive hammered accent plates to create a seamless, polished look that is at home in a rustic lodge or an urban loft.



51823 PN
24" W, 7¼" H



51822 PN
16¼" W, 7¼" H



51820 PN
5" W, 7¼" H



51824 PN
32¾" W, 7¼" H



51825 PN
38¼" W, 7¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
51820 PN	1-100w Med.	7"	4"	5" W, 6¾" H	BN, KZ	•
51822 PN	2-100w Med.	7"	4¾"	16¼" W, 5" H	BN, KZ	•
51823 PN	3-100w Med.	7"	4¾"	24" W, 5" H	BN, KZ	•
51824 PN	4-100w Med.	7"	4¾"	32¾" W, 5" H	BN, KZ	•
51825 PN	5-100w Med.	7"	4¾"	38¼" W, 5" H	BN, KZ	•

Jackson merges traditional details such as clear seedy glass, finished glass collars and distinctive hammered accent plates to create a seamless, polished look that is at home in a rustic lodge or an urban loft.

JACKSON™

BUCKEYE BRONZE WITH ANTIQUE COPPER FINISH
CLEAR SEEDY GLASS



51822 KZ
16¼" W, 7¼" H



51823 KZ
24" W, 7¼" H



51824 KZ
32¾" W, 7¼" H



51820 KZ
5" W, 7¼" H



51825 KZ
38¼" W, 7¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
51820 KZ	1-100w Med.	7"	4"	5" W, 6¾" H	BN, PN	•
51822 KZ	2-100w Med.	7"	4¾"	16¼" W, 5" H	BN, PN	•
51823 KZ	3-100w Med.	7"	4¾"	24" W, 5" H	BN, PN	•
51824 KZ	4-100w Med.	7"	4¾"	32¾" W, 5" H	BN, PN	•
51825 KZ	5-100w Med.	7"	4¾"	38¼" W, 5" H	BN, PN	•

JACKSON™

FINISH BRUSHED NICKEL
GLASS CLEAR SEEDY

Jackson merges traditional details such as clear seedy glass, finished glass collars and distinctive hammered accent plates to create a seamless, polished look that is at home in a rustic lodge or an urban loft.



51823 BN
24" W, 7¼" H



51822 BN
16¼" W, 7¼" H



51820 BN
5" W, 7¼" H



51824 BN
32¾" W, 7¼" H



51825 BN
38¼" W, 7¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
51820 BN	1-100w Med.	7"	4"	5" W, 6¾" H	KZ, PN	•
51822 BN	2-100w Med.	7"	4¾"	16¼" W, 5" H	KZ, PN	•
51823 BN	3-100w Med.	7"	4¾"	24" W, 5" H	KZ, PN	•
51824 BN	4-100w Med.	7"	4¾"	32¾" W, 5" H	KZ, PN	•
51825 BN	5-100w Med.	7"	4¾"	38¼" W, 5" H	KZ, PN	•

Avon's updated traditional style features a clean minimalist design with cast detailing. Available in a range of finishes and glass combinations to easily complement any décor.

AVON™

CHROME FINISH
CLEAR SEEDY GLASS



5550 CM-CL
7¼" W, 7½" H



5553 CM-CL
23" W, 8" H



5554 CM-CL
31¾" W, 8" H



5552 CM-CL
14½" W, 8" H



5555 CM-CL
40¼" W, 8" H



5556 CM-CL
48" W, 8" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
5550 CM-CL	1-100w Med.	6¼"	5¼"	7¼" W, 4½" H	BN, CM, KZ
5552 CM-CL	2-100w Med.	6¼"	5¾"	7¼" W, 4½" H	BN, CM, KZ
5553 CM-CL	3-100w Med.	6¼"	5¾"	7¼" W, 4½" H	BN, CM, KZ
5554 CM-CL	4-100w Med.	6¼"	5¾"	7¼" W, 4½" H	BN, CM, KZ
5555 CM-CL	5-100w Med.	6¼"	5¾"	18¼" W, 4½" H	BN, CM, KZ
5556 CM-CL	6-100w Med.	6¼"	5¾"	18¼" W, 4½" H	BN, CM, KZ

BENNETT™

FINISH POLISHED NICKEL
GLASS CLEAR HOLOPHANE

Charming and graceful, Bennett's distinctive details set it apart. Petite arched arms and latches bring an artisan touch to its transitional design while the pressed holophane glass cups add a dash of vintage panache.

OBJECT OF OUR
AFFECTION

Clear holophane glass gives Bennett a cool, crisp look.



5352 PN
16" W, 8¾" H



5350 PN
5¼" W, 9" H



5353 PN
24¼" W, 8¾" H



5354 PN
31¾" W, 8¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5350 PN	1-100w Med.	6¾"	6½"	5" Dia.
5352 PN	2-100w Med.	6¾"	6¼"	7" W, 5" H
5353 PN	3-100w Med.	6¾"	6¼"	9" W, 5" H
5354 PN	4-100w Med.	6¾"	6¼"	9" W, 5" H

Clancy is an updated traditional silhouette. Petite etched opal glass and a Brushed Nickel finish convey an understated elegance. Soft curves are echoed throughout the design, adding a vintage touch.

CLANCY™

BRUSHED NICKEL FINISH
ETCHED OPAL GLASS



5442 BN
16" W, 8¼" H



5443 BN
25" W, 8¼" H



5440 BN
6" W, 11¼" H



5444 BN
32¾" W, 8¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5440 BN	1-100w Incan. or 1-17w LED Med.	6½"	5"	5" Dia.
5442 BN	2-100w Incan. or 2-17w LED Med.	6½"	3¼"	9" W, 5" H
5443 BN	3-100w Incan. or 3-17w LED Med.	6½"	3¼"	9" W, 5" H
5444 BN	4-100w Incan. or 4-17w LED Med.	6½"	3¼"	9" W, 5" H

VERVE™

FINISH CHROME
GLASS ETCHED OPAL

Catch a wave with Verve's contemporary silhouette. Individual curved cast fitters support the modern etched opal glass while mimicking the sleek contours of the bar. A crisp Chrome finish balances the unique, undulating design.



51102 CM
51102 CM-LED
15½" W, 4¾" H



51100 CM
51100 CM-LED
6¾" W, 7¼" H



51103 CM
51103 CM-LED
24" W, 4¾" H



51104 CM
51104 CM-LED
32¾" W, 4¾" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	INV
51100 CM	1-60w G9*	51100 CM-LED	1-4.5w G9 LED**	4¾"	3¾"	4¾" W, 7¼" H	•
51102 CM	2-60w G9*	51102 CM-LED	2-4.5w G9 LED**	4¾"	2½"	11" W, 4¾" H	•
51103 CM	3-60w G9*	51103 CM-LED	3-4.5w G9 LED**	4¾"	2½"	11" W, 4¾" H	•
51104 CM	4-60w G9*	51104 CM-LED	4-4.5w G9 LED**	4¾"	2½"	11" W, 4¾" H	•

*G9 halogen bulbs included. **G9 LED bulb included. Verve fixtures must be mounted up.

Sadie's transitional design showcases an elegantly arched cross bar. Slim and graceful, the etched opal glass can be mounted either up or down for maximum flexibility and the Brushed Nickel finish ensures Sadie is the perfect complement to any spa setting.

SADIE™

BRUSHED NICKEL FINISH
ETCHED OPAL GLASS



52232 BN
15¾" W, 8¾" H



52233 BN
23¼" W, 8¾" H



52230 BN
5¾" W, 7¾" H



52234 BN
32¾" W, 8¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
52230 BN	1-100w Incan. or 1-17w LED Med.	6¾"	3½"	5¾" Dia.
52232 BN	2-100w Incan. or 2-17w LED Med.	7¾"	6"	5¾" Dia.
52233 BN	3-100w Incan. or 3-17w LED Med.	8"	6"	5¾" Dia.
52234 BN	4-100w Incan. or 4-17w LED Med.	8¼"	6"	5¾" Dia.

KYRA™

FINISH POLISHED NICKEL

GLASS ETCHED OPAL

Clean and crisp, Kyra's minimalist design is anchored with a bold yet simple aesthetic. The sleek cross bar ends with a subtle curve for an element of softness. Rich finish options of Brushed Nickel or Polished Nickel complement the elegant etched opal glass.



55022 PN
14" W, 7¾" H



55020 PN
4¾" W, 7¾" H



55023 PN
24" W, 7¾" H



55024 PN
30" W, 7¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
55020 PN	1-100w Incan. or 1-17w LED Med.	5¼"	4¼"	4¾" W, 7" H	BN	•
55022 PN	2-100w Incan. or 2-17w LED Med.	5¼"	5¼"	7" W, 4¾" H	BN	•
55023 PN	3-100w Incan. or 3-17w LED Med.	5¼"	5¼"	7" W, 4¾" H	BN	•
55024 PN	4-100w Incan. or 4-17w LED Med.	5¼"	5¼"	7" W, 4¾" H	BN	•

Clean and crisp, Kyra's minimalist design is anchored with a bold yet simple aesthetic. The sleek cross bar ends with a subtle curve for an element of softness. Rich finish options of Brushed Nickel or Polished Nickel complement the elegant etched opal glass.

KYRA™

BRUSHED NICKEL FINISH
ETCHED OPAL GLASS



55022 BN
14" W, 7¾" H



55023 BN
24" W, 7¾" H



55020 BN
4¾" W, 7¾" H



55024 BN
30" W, 7¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
55020 BN	1-100w Incan. or 1-17w LED Med.	5¼"	4¼"	4¾" W, 7" H	PN	•
55022 BN	2-100w Incan. or 2-17w LED Med.	5¼"	5¼"	7" W, 4¾" H	PN	•
55023 BN	3-100w Incan. or 3-17w LED Med.	5¼"	5¼"	7" W, 4¾" H	PN	•
55024 BN	4-100w Incan. or 4-17w LED Med.	5¼"	5¼"	7" W, 4¾" H	PN	•

TESSA™

FINISH CHROME
GLASS ETCHED OPAL

Tessa's dynamic details exude quality. The precision die-cast back plate, arm and cup combine with a sturdy cross bar to balance its square etched opal glass shades. The ultimate touch: a luxurious Chrome finish that radiates with transitional sophistication.



57132 CM
13" W, 7½" H



57130 CM
5¾" W, 7¾" H



57133 CM
22" W, 7½" H



57134 CM
31" W, 7½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
57130 CM	1-100w Incan. or 1-17w LED Med.	5¾"	6¼"	5¾" Square	•
57132 CM	2-100w Incan. or 2-17w LED Med.	6½"	6¼"	5¾" Square	•
57133 CM	3-100w Incan. or 3-17w LED Med.	6½"	6¼"	5¾" Square	•
57134 CM	4-100w Incan. or 4-17w LED Med.	6½"	6¼"	5¾" Square	•

Faye is a fresh take on traditional design with clean lines reinforcing a timeless sophistication. Softly curved cased opal glass cups, accented with step details, pair with a crisp Chrome finish for sparkling allure.

FAYE™

CHROME FINISH
CASED OPAL GLASS



5602 CM
15" W, 8¾" H



5603 CM
24" W, 8¾" H



5600 CM
5¾" W, 8¾" H



5604 CM
33¼" W, 8¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5600 CM	1-100w Incan. or 1-17w LED Med.	6¾"	5¼"	4¾" W, 7¼" H
5602 CM	2-100w Incan. or 2-17w LED Med.	6¾"	5¼"	7¼" W, 4¾" H
5603 CM	3-100w Incan. or 3-17w LED Med.	6¾"	5¼"	7¼" W, 4¾" H
5604 CM	4-100w Incan. or 4-17w LED Med.	6¾"	5¼"	7¼" W, 4¾" H

BLYTE™

FINISH POLISHED NICKEL

GLASS ETCHED OPAL

Blythe sparkles with an air of refinement and elegance, with a precision die-cast back plate emphasizing quality. Faceted crystal knobs are precisely placed, subtly accenting each angle to enhance its chic, transitional style.



5282 PN
16" W, 8¾" H



5820 PN
5" W, 8¾" H



5283 PN
24¾" W, 8¾" H



5284 PN
33¾" W, 8¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
5280 PN	1-100w Incan. or 1-17w LED Med.	6½"	5"	5" Dia.	AN	•
5282 PN	2-100w Incan. or 2-17w LED Med.	5½"	5"	8" W, 5" H	AN	•
5283 PN	3-100w Incan. or 3-17w LED Med.	5½"	5"	8" W, 5" H	AN	•
5284 PN	4-100w Incan. or 4-17w LED Med.	5½"	5"	8" W, 5" H	AN	•

Blythe sparkles with an air of refinement and elegance, with a precision die-cast back plate emphasizing quality. Faceted crystal knobs are precisely placed, subtly accenting each angle to enhance its chic, transitional style.

BLYTHE™

ANTIQUE NICKEL FINISH
ETCHED OPAL GLASS



5282 AN
16" W, 8¾" H



5283 AN
24¾" W, 8¾" H



5820 AN
5" W, 8¾" H



5284 AN
33¾" W, 8¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
5280 AN	1-100w Incan. or 1-17w LED Med.	6½"	5"	5" Dia.	PN	•
5282 AN	2-100w Incan. or 2-17w LED Med.	5½"	5"	8" W, 5" H	PN	•
5283 AN	3-100w Incan. or 3-17w LED Med.	5½"	5"	8" W, 5" H	PN	•
5284 AN	4-100w Incan. or 4-17w LED Med.	5½"	5"	8" W, 5" H	PN	•

BALDWIN™

FINISH POLISHED NICKEL

GLASS ETCHED OPAL

Inspired by classic drawer pulls, Baldwin perfectly fuses transitional and traditional style elements. A precision die-cast back plate, knob and glass fitter complement the tapered square etched opal glass shades for a silhouette that adds beauty to any décor.



56672 PN
13¾" W, 7" H



56670 PN
4½" W, 8¼" H



56673 PN
23½" W, 7" H



56674 PN
33½" W, 7" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
56670 PN	1-100w Incan. or 1-17w LED Med.	5½"	3¾"	4½" W, 7½" H	AN	•
56672 PN	2-100w Incan. or 2-17w LED Med.	6"	3¾"	7½" W, 4½" H	AN	•
56673 PN	3-100w Incan. or 3-17w LED Med.	6"	3¾"	7½" W, 4½" H	AN	•
56674 PN	4-100w Incan. or 4-17w LED Med.	6"	3¾"	7½" W, 4½" H	AN	•

Inspired by classic drawer pulls, Baldwin perfectly fuses transitional and traditional style elements. A precision die-cast back plate, knob and glass fitter complement the tapered square etched opal glass shades for a silhouette that adds beauty to any décor.

BALDWIN™

ANTIQUE NICKEL FINISH
ETCHED OPAL GLASS



56672 AN
13¾" W, 7" H



56673 AN
23½" W, 7" H



56670 AN
4½" W, 8¼" H



56674 AN
33½" W, 7" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
56670 AN	1-100w Incan. or 1-17w LED Med.	5½"	3¾"	4½" W, 7½" H	PN	•
56672 AN	2-100w Incan. or 2-17w LED Med.	6"	3¾"	7½" W, 4½" H	PN	•
56673 AN	3-100w Incan. or 3-17w LED Med.	6"	3¾"	7½" W, 4½" H	PN	•
56674 AN	4-100w Incan. or 4-17w LED Med.	6"	3¾"	7½" W, 4½" H	PN	•

THISTLEDOWN™

FINISH POLISHED NICKEL

GLASS CLEAR SEEDY

Thistledown is an updated traditional design with smooth, flowing lines and a practical elegance that adds sophistication to any space.



51802 PN
16" W, 10½" H



51800 PN
5¼" W, 10½" H



51803 PN
24" W, 10½" H



51804 PN
30" W, 10½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
51800 PN	1-100w Med.	6¼"	7"	5" W, 7" H	BN
51802 PN	2-100w Med.	6¼"	8"	7" W, 5" H	BN
51803 PN	3-100w Med.	6¼"	8"	7" W, 5" H	BN
51804 PN	4-100w Med.	6¼"	8"	7" W, 5" H	BN

Thistledown is an updated traditional design with smooth, flowing lines and a practical elegance that adds sophistication to any space.

THISTLEDOWN™

BRUSHED NICKEL FINISH
CLEAR SEEDY GLASS



51802 BN-CL
16" W, 10½" H



51803 BN-CL
24" W, 10½" H



51800 BN-CL
5¼" W, 10½" H



51804 BN-CL
30" W, 10½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
51800 BN-CL	1-100w Med.	6¼"	7"	5" W, 7" H	PN
51802 BN-CL	2-100w Med.	6¼"	8"	7" W, 5" H	PN
51803 BN-CL	3-100w Med.	6¼"	8"	7" W, 5" H	PN
51804 BN-CL	4-100w Med.	6¼"	8"	7" W, 5" H	PN

serene
SURROUNDINGS

Well-designed dwellings that bring the outside in and the inside out embrace the tranquility and vitality of a seamless living experience. Everyday activities are made more enjoyable in the presence of the sights and sounds of nature—from morning yoga and coffee to evening entertaining. Whether the moments are social or those of solitude, expanding a home's environment and extending its usability with outdoor lighting adds a breath of fresh air from sunrise to sundown.

A SEASONAL APPROACH >

MAKE THE MOST OF YOUR PROPERTY BY ILLUMINATING A FULL YEAR OF OUTDOOR LIVING: FROM THE FRESHNESS OF SPRING AND RADIANT RISE OF SUMMER TO THE WARM HUES OF FALL AND CRISP PRESENCE OF WINTER.

FIXTURES SHOWN: WALKER 2105KZ



OUTDOOR COLLECTIONS



ALFORD PLACE	S402
ANCHORAGE	S400
ARIA	S376
ATWELL	S354
BRIGGS	S388
BROMLEY	S404
BURKE	S382
CARSON	S356
ENZO	S406
FREEPORT	S390
GLACIER	S360
KUBE	S374
LUNA	S370
MARINA	S394
MIST	S366
PERRY	S392
PLAZA	S364
PORTER	S386
SAWYER	S352
SURF	S368
TATUM	S398
THEO	S380
TRELLIS	S408
VAPOR	S362



OPEN AIR

As the design movement to create a seamless transition between a home's interior and exterior continues, Hinkley's collection of outdoor-rated chandeliers has grown. These stunning new fixtures are appropriate for any exterior space—a dining terrace, backyard pergola or front porch.

**LOOK FOR THE ABOVE OPEN AIR ICON TO
FIND THE PERFECT INTERIOR-INSPIRED PIECE
TO ILLUMINATE YOUR ALFRESCO AREA.**

CARSON 29705VI AND 29700VI

...AND THE OUTDOORS IN



SHELTER 1328BK

Think outside the house! Exterior fixtures may offer the statement you've been searching for. A few of our favorite pendants look equally at home over a bar or kitchen island as they do outdoors.

AS AN ADDED BONUS, EXTERIOR FIXTURES OFTEN BOAST MORE ECO-FRIENDLY CONFIGURATIONS!



ARIA 2302SK



CARSON 29707V1



BELDEN PLACE 2862OZ



COLFAX 2922PS



PERRY 2382OZ



ATWELL 1112OZ



WALKER 2102KZ

SAWYER™

FINISH SEQUOIA
GLASS CLEAR SEEDY

The fresh, rustic design of the Sawyer collection will inject any outdoor living experience with the warm, cozy ambiance of an indoor setting. Constructed with Hinkley's own anti-corrosion coating, the faux wood finish over coated steel ensures maximum resiliency and performance in the elements.



an **OPEN AIR** collection

CHIC DESIGNS RATED FOR USE IN BOTH
INTERIOR AND EXTERIOR SPACES



29208 SQ
30" DIA., 27³/₄" H



29206 SQ
24" DIA., 21¾" H



29203 SQ
15" DIA., 4¾" H



29201 SQ
9" DIA., 4½" H



29202 SQ
9" W, 12" H



29205 SQ
42" W, 7¾" H

ITEM	BULBS	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
29201 SQ	2-60w Cand.					
29202 SQ	2-60w Cand.		2¾"	2¼"	4½" W, 4½" H Back Plate	
29203 SQ	3-60w Cand.					
29205 SQ	5-60w Cand.	3"			4¾" W, 12¾" L Canopy	10', 5'
29206 SQ	6-60w Cand.				5¼" Dia. Canopy	10', 5'
29208 SQ	9-60w Cand.				5¼" Dia. Canopy	10', 5'

Ideal for vintage filament bulbs (not included).

ATWELL™

FINISH AGED ZINC, OIL RUBBED BRONZE
GLASS CLEAR SEEDY

Industrial-inspired Atwell recalls turn-of-the-century American factory lighting. Aged Zinc and Oil Rubbed Bronze finish options reinforce its vintage silhouette. Clear seedy glass, cast glass holder and authentic details like gooseneck arms and bespoke back plate and canopy enhance Atwell's nostalgic appeal.



an **OPEN AIR** collection

CHIC DESIGNS RATED FOR USE IN BOTH
INTERIOR AND EXTERIOR SPACES



1113 OZ
24¼" DIA., 10¼" H
45½" MAX. H*

1113 DZ
24¼" DIA., 10¼" H
45½" MAX. H*



1110 DZ
11½" W, 11¾" H



1114 DZ
14½" W, 15¼" H



1114 OZ
14½" W, 15¼" H



1110 OZ
11½" W, 11¾" H



1112 DZ
14½" DIA., 11" H
44" MAX. H*

1112 OZ
14½" DIA., 11" H
44" MAX. H*

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
1110 DZ**, 1110 OZ**	1-100w Med.	13"	4¾"	5" Dia. Back Plate		
1112 DZ**, 1112 OZ**	1-100w Med.			5" Dia. Canopy	10'	1-6", 2"12"
1113 DZ**, 1113 OZ**	3-100w Med.			6" Dia. Canopy	10'	1-6", 2-12"
1114 DZ**, 1114 OZ**	1-100w Med.	16"	5¼"	6" Dia. Back Plate		

*Maximum achievable height with stems included. Additional 12" stems available, 6067 DZOD, OZOD. **When fitted with DSL-40 this item is Dark Sky compliant, see hinkleylighting.com. Ideal for vintage filament bulbs (not included).

CARSON™

FINISH WEATHERED ZINC
GLASS CLEAR SEEDY

Carson features bold overlapping metal ribbons of Iron Rust or Weathered Zinc, enhancing an outdoor living area with style and substance. The hand-crafted pendants combine a hint of industrial sophistication with the allure of artisan craftsmanship.



an **OPEN AIR** collection

CHIC DESIGNS RATED FOR USE IN BOTH
INTERIOR AND EXTERIOR SPACES



29705 WZ
26½" DIA., 26¼" H
61¾" MAX. H*



29703 WZ
18½" DIA., 19" H
54" MAX. H*



29700 WZ
10" W, 10½" H



29707 WZ
10" DIA., 10" H
46" MAX. H*

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED	ADDITIONAL FINISHES
29700 WZ*	1-100w Med.	12½"	6"	5" Dia. Back Plate			VI
29703 WZ	3-60w Cand.			4¾" Dia. Canopy	10'	1-6", 2-12"	VI
29705 WZ	5-60w Cand.			4¾" Dia. Canopy	10'	1-6", 2-12"	VI
29707 WZ*	1-100w Med.			4¾" Dia. Canopy	10'	1-6", 2-12"	VI

*Maximum achievable height with stems included. Additional 12" stems available. For 29703 WZ and 29705 WZ use 6063 WZ. For 29707 WZ use 6033 WZ.
**When fitted with DSL-40 this item is Dark Sky compliant, see hinkleylighting.com.

CARSON™

FINISH VINTAGE IRON
GLASS CLEAR SEEDY

Carson features bold overlapping metal ribbons of Iron Rust or Weathered Zinc, enhancing an outdoor living area with style and substance. The hand-crafted pendants combine a hint of industrial sophistication with the allure of artisan craftsmanship.



an **OPEN AIR** collection

CHIC DESIGNS RATED FOR USE IN BOTH
INTERIOR AND EXTERIOR SPACES



29705 VI
26½" DIA., 26¼" H
61¾" MAX. H*



29703 VI
18½" DIA., 19" H
54" MAX. H*



29700 VI
10" W, 10½" H



29707 VI
10" DIA., 10" H
46" MAX. H*

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED	ADDITIONAL FINISHES
29700 VI*	1-100w Med.	12½"	6"	5" Dia. Back Plate			WZ
29703 VI	3-60w Cand.			4¾" Dia. Canopy	10'	1-6", 2-12"	WZ
29705 VI	5-60w Cand.			4¾" Dia. Canopy	10'	1-6", 2-12"	WZ
29707 VI*	1-100w Med.			4¾" Dia. Canopy	10'	1-6", 2-12"	WZ

*Maximum achievable height with stems included. Additional 12" stems available. For 29703 VI and 29705 VI use 6063 VI. For 29707 VI use 6033 VI.

**When fitted with DSL-40 this item is Dark Sky compliant, see hinkleylighting.com.

GLACIER™

FINISH BRONZE, TITANIUM
GLASS CLEAR SEEDY

Glacier's impressive form merges industrial and contemporary design elements into a breath-taking silhouette. A substantial block of clear seedy glass with etched grooves brilliantly channels light from the high-performance LED, which is held in suspension by the powder-coated aluminum frame.

DESIGN
NOTE TOP LID IS
REMOVABLE FOR
MORE UP LIGHT



2835 TT
4¾" W, 28" H



2835 BZ
4¾" W, 28" H






2830 TT
4¾" W, 15½" H









2830 BZ
4¾" W, 15½" H



2834 TT
(side view)






2834 TT
4¾" W, 22" H






2834 BZ
4¾" W, 22" H




ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE
2830 BZ	15w LED	800	2700K	91	1-60w	4"	7¾"	4¾" Square
2830 TT	15w LED	800	2700K	91	1-60w	4"	7¾"	4¾" Square
2834 BZ	15w LED	800	2700K	91	1-60w	4"	11"	4¾" Square
2834 TT	15w LED	800	2700K	91	1-60w	4"	11"	4¾" Square
2835 BZ	15w LED	800	2700K	91	1-60w	4"	14"	4¾" Square
2835 TT	15w LED	800	2700K	91	1-60w	4"	14"	4¾" Square

Glacier fixtures are fully dimmable. LED components have a lifespan of 40,000 hours and carry a 5-year limited warranty.

VAPOR™

FINISH BRONZE, TITANIUM
GLASS CRACKLE

Vapor's streamlined profile allows the spectacular crackled glass to star in this captivating design. The low profile back plate and stamped metal construction project a sleek, contemporary style statement.



2855 BZ
4¾" W, 28" H



2855 TT
4¾" W, 28" H





2850 BZ
4¾" W, 14" H



2850 TT
4¾" W, 14" H





**DESIGN
NOTE**

.....

VAPOR'S CRACKLED
GLASS PATTERN
IS EVEN MORE
DECORATIVE IN THE
DARK, CREATING
ADDED INTEREST
AT NIGHT.



2854 BZ
4¾" W, 21" H



2854 TT
4¾" W, 21" H




ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE
2850 BZ	1-35w GU10*	3¾"	7"	4¾" Square
2850 TT	1-35w GU10*	3¾"	7"	4¾" Square
2854 BZ	1-35w GU10*	3¾"	10½"	4¾" Square
2854 TT	1-35w GU10*	3¾"	10½"	4¾" Square
2855 BZ	1-35w GU10*	3¾"	14"	4¾" Square
2855 TT	1-35w GU10*	3¾"	14"	4¾" Square

*GU10 bulb included.

PLAZA™

FINISH BRONZE, TITANIUM
GLASS ETCHED ACRYLIC LENS

Plaza features a contemporary form constructed from durable aluminum. This sleek shape creates a unique wall-wash effect with a down light producing a subtle interior grazing for a layered sense of illumination.




20300 BZ
10" W, 10" H



20300 TT
10" W, 10" H



20305 TT
7" W, 20" H



20305 BZ
7" W, 20" H



ITEM	INTEGRATED LED LIGHT SOURCE	ENGINE LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE
20300 BZ	24w LED	1900	2700K	90	2-75w	4"	5"	6¼" Square
20300 TT	24w LED	1900	2700K	90	2-75w	4"	5"	6¼" Square
20305 BZ	22w LED	1950	2700K	90	2-75w	4"	10"	5" W, 15¼" H
20305 TT	22w LED	1950	2700K	90	2-75w	4"	10"	5" W, 15¼" H

Plaza fixtures are fully dimmable. LED components have a lifespan of 40,000 hours and carry a 5-year limited warranty.

The sleek design of the Mist collection discreetly emphasizes its contemporary heritage. Featuring a prominent interior panel of clear seeded glass captured on both ends and encased in a protective clear acrylic cylinder. Its solid aluminum construction is underscored by bold Satin Black, Bronze or Titanium finish options. Mist is both Dark Sky and ADA compliant.

MIST™

BRONZE FINISH
CLEAR ACRYLIC OUTSIDE CYLINDER, GLASS
SEEDY GLASS INSIDE PANEL



1225 BZ
4¾" W, 28½" H



1220 BZ
4¾" W, 15½" H



1224 BZ
4¾" W, 22" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
1220 BZ	1-35w GU-10	3¾"	7½"	4¾" Square	TT, SK
1224 BZ	1-35w GU-10	3¾"	11"	4¾" Square	TT, SK
1225 BZ	1-35w GU-10	3¾"	14¼"	4¾" Square	TT, SK

MIST™

FINISH TITANIUM

GLASS CLEAR ACRYLIC OUTSIDE CYLINDER,
SEEDY GLASS INSIDE PANEL

The sleek design of the Mist collection discreetly emphasizes its contemporary heritage. Featuring a prominent interior panel of clear seedy glass captured on both ends and encased in a protective clear acrylic cylinder. Its solid aluminum construction is underscored by bold Satin Black, Bronze or Titanium finish options. Mist is both Dark Sky and ADA compliant.



1225 TT
4¾" W, 28½" H




1220 TT
4¾" W, 15½" H




1224 TT
4¾" W, 22" H



ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
1220 TT	1-35w GU-10	3¾"	7½"	4¾" Square	BZ, SK
1224 TT	1-35w GU-10	3¾"	11"	4¾" Square	BZ, SK
1225 TT	1-35w GU-10	3¾"	14"	4¾" Square	BZ, SK


The sleek design of the Mist collection discreetly emphasizes its contemporary heritage. Featuring a prominent interior panel of clear seeded glass captured on both ends and encased in a protective clear acrylic cylinder. Its solid aluminum construction is underscored by bold Satin Black, Bronze or Titanium finish options. Mist is both Dark Sky and ADA compliant.

MIST™

SATIN BLACK FINISH
CLEAR ACRYLIC OUTSIDE CYLINDER, GLASS
SEEDY GLASS INSIDE PANEL



1224 SK
4¾" W, 22" H




1220 SK
4¾" W, 15½" H




1225 SK
4¾" W, 28½" H



ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
1220 SK	1-35w GU-10	3¾"	7½"	4¾" Square	BZ, TT
1224 SK	1-35w GU-10	3¾"	11"	4¾" Square	BZ, TT
1225 SK	1-35w GU-10	3¾"	14¼"	4¾" Square	BZ, TT

SURF™

FINISH SATIN BLACK, TITANIUM

Surf's chic design reflects the natural curl of a breaking wave. Constructed of solid aluminum, this LED lantern emits light both up and down. Surf is finished with marine grade powder coat for maximum durability.



2355 SK
9½" W, 24" H



2355 TT
9½" W, 24" H





ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
2350 SK	20w LED	950	2700K	91	2-60w	4¾"	8¾"	4½" W, 7½" H	BZ, SS
2350 TT	20w LED	950	2700K	91	2-60w	4¾"	8¾"	4½" W, 7½" H	BZ, SS
2354 SK	26w LED	1300	2700K	91	2-75w	5¾"	11"	4½" W, 7½" H	BZ, SS
2354 TT	26w LED	1300	2700K	91	2-75w	5¾"	11"	4½" W, 7½" H	BZ, SS
2355 SK	30w LED	1600	2700K	91	2-100w	7"	13¾"	4½" W, 7½" H	BZ, SS
2355 TT	30w LED	1600	2700K	91	2-100w	7"	13¾"	4½" W, 7½" H	BZ, SS

Surf fixtures are fully dimmable. LED components have a lifespan of 40,000 hours and carry a 5-year limited warranty.

LUNA™

FINISH BRONZE, SATIN BLACK, SATIN WHITE, TITANIUM
GLASS ETCHED GLASS LENSES

Luna is a modern collection of solid aluminum fixtures offered in a unique combination of contemporary styles, including sleek wall lanterns. Luna also offers chic pocket wall sconces and compact ceiling mounts that are ideal for indoor or out.



1664 SK
1664 SK-LED
9" W, 24" H





1664 TT
1664 TT-LED
9" W, 24" H



1664 BZ
1664 BZ-LED
9" W, 24" H



1660 SK
1660 SK-LED
6" W, 16" H



1660 TT
1660 TT-LED
6" W, 16" H



1660 BZ
1660 BZ-LED
6" W, 16" H



ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE
1660 BZ	2-20w GU-10*	1660 BZ-LED	15w LED	1200	2700K	90	2-50w	3½"	10" to 13½"***	6" W, 16" H
1660 SK	2-20w GU-10*	1660 SK-LED	15w LED	1200	2700K	90	2-50w	3½"	10" to 13½"***	6" W, 16" H
1660 TT	2-20w GU-10*	1660 TT-LED	15w LED	1200	2700K	90	2-50w	3½"	10" to 13½"***	6" W, 16" H
1664 BZ	2-20w GU-10*	1664 BZ-LED	15w LED	1200	2700K	90	2-50w	4"	11½" to 20½"***	9" W, 24" H
1664 SK	2-20w GU-10*	1664 SK-LED	15w LED	1200	2700K	90	2-50w	4"	11½" to 20½"***	9" W, 24" H
1664 TT	2-20w GU-10*	1664 TT-LED	15w LED	1200	2700K	90	2-50w	4"	11½" to 20½"***	9" W, 24" H

*GU-10 bulbs included. **Adjustable mounting hardware. LED components have a lifespan of 40,000 hours and carry a 5-year limited warranty.



CEILING MOUNT
1665 BZ
8" DIA., 3¼" H



CEILING MOUNT
1665 TT
8" DIA., 3¼" H



CEILING MOUNT
1665 SK
8" DIA., 3¼" H



1647 BZ-LED
9" W, 9" H



1647 SW-LED
9" W, 9" H



1647 SK-LED
9" W, 9" H



1647 TT-LED
9" W, 9" H

ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE
1647 BZ-LED	15w LED	1200	2700K	90	2-50w	4"	4½"	4½" W, 6¾" H
1647 SK-LED	15w LED	1200	2700K	90	2-50w	4"	4½"	4½" W, 6¾" H
1647 SW-LED	15w LED	1200	2700K	90	2-50w	4"	4½"	4½" W, 6¾" H
1647 TT-LED	15w LED	1200	2700K	90	2-50w	4"	4½"	4½" W, 6¾" H
1665 BZ	8w LED	600	2700K	90	1-50w			
1665 SK	8w LED	600	2700K	90	1-50w			
1665 TT	8w LED	600	2700K	90	1-50w			

LED components have a lifespan of 40,000 hours and carry a 5-year limited warranty.



1661 will cast light down



1662 will cast light up and down



POCKET DOWN LIGHT
1661 BZ
9" W, 5" H



POCKET DOWN LIGHT
1661 TT
9" W, 5" H



POCKET DOWN LIGHT
1661 SK
9" W, 5" H



POCKET UP/DOWN LIGHT
1662 BZ
9" W, 5" H



POCKET UP/DOWN LIGHT
1662 TT
9" W, 5" H



POCKET UP/DOWN LIGHT
1662 SK
9" W, 5" H



ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE
1661 BZ	8w LED	600	3000K	90	1-60w	4"	2½"	9" W, 5" H
1661 SK	8w LED	600	3000K	90	1-60w	4"	2½"	9" W, 5" H
1661 TT	8w LED	600	3000K	90	1-60w	4"	2½"	9" W, 5" H
1662 BZ	15w LED	1200	2700K	90	2-50w	4"	2½"	9" W, 5" H
1662 SK	15w LED	1200	2700K	90	2-50w	4"	2½"	9" W, 5" H
1662 TT	15w LED	1200	2700K	90	2-50w	4"	2½"	9" W, 5" H

LED components have a lifespan of 40,000 hours and carry a 5-year limited warranty.

KUBE™

FINISH BRONZE, SATIN BLACK, SATIN WHITE, TITANIUM
GLASS ETCHED LENSES

A collection of sleek designs, Kube's contemporary style featuring solid aluminum construction provides a chic, minimalist statement to complement a variety of exteriors.



1768 will cast light down

1769 will cast light up and down



CEILING MOUNT
1765 BZ
6" W, 6" H
Icons: Three dots, Moon, T24



CEILING MOUNT
1765 TT
6" W, 6" H
Icons: Three dots, Moon, T24



CEILING MOUNT
1765 SK
6" W, 6" H
Icons: Three dots, Moon, T24



CEILING MOUNT
1765 SW
6" W, 6" H
Icons: Three dots, Moon, T24



POCKET DOWN LIGHT
1768 BZ
6" W, 6" H
Icons: Three dots, Moon, T24



POCKET DOWN LIGHT
1768 TT
6" W, 6" H
Icons: Three dots, Moon, T24



POCKET DOWN LIGHT
1768 SK
6" W, 6" H
Icons: Three dots, Moon, T24



POCKET DOWN LIGHT
1768 SW
6" W, 6" H
Icons: Three dots, Moon, T24



POCKET UP/DOWN LIGHT
1769 BZ
6" W, 6" H
Icons: Three dots, T24



POCKET UP/DOWN LIGHT
1769 TT
6" W, 6" H
Icons: Three dots, T24



POCKET UP/DOWN LIGHT
1769 SK
6" W, 6" H
Icons: Three dots, T24



POCKET UP/DOWN LIGHT
1769 SW
6" W, 6" H
Icons: Three dots, T24

ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE
1765 BZ, SK, SW, TT	8w LED	600	2700K	90	1-50w			
1768 BZ, SK, SW, TT	8w LED	600	2700K	90	1-50w	6¾"	3"	4½" Square
1769 BZ, SK, SW, TT	15w LED	1200	2700K	90	2-50w	6¾"	3"	4½" Square



ARIA™

FINISH BLACK

Aria is a contemporary style that effortlessly complements the facade of any exterior. Its modern shape in durable aluminum is enhanced by a stainless-steel mesh shade. Aria's high style and low maintenance comes standard Dark Sky compliant.



2305 BK
2305 BK-LED
7" W, 21¾" H





2302 BK
2302 BK-LED
5" W, 19¼" H
51½" MAX. H*
  






2300 BK
2300 BK-LED
5" W, 15½" H
  





2306 BK
2306 BK-LED
4½" W, 14½" H
  



2304 BK
2304 BK-LED
5" W, 18½" H
  



2307 BK
8½" W, 18" H
 



2307 BK
(side view)
8½" W, 18" H
 

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	STEMS INCLUDED	ADD. FINISHES
2300 BK	1-75w Med.	2300 BK-LED	15w LED	900	2700K	92	1-100w	6¾"	5"	4½" W, 8¼" H Back Plate		KZ
2302 BK	1-100w Med.	2302 BK-LED	15w LED	900	2700K	92	1-100w			6" Dia. Canopy	10'	1-6", 2-12" KZ
2304 BK	1-100w Med.	2304 BK-LED	15w LED	900	2700K	92	1-100w	6¾"	5"	4½" W, 8¼" H Back Plate		KZ
2305 BK	1-100w Med.	2305 BK-LED	15w LED	900	2700K	92	1-100w	8¾"	5"	4½" W, 8¼" H Back Plate		KZ
2306 BK	1-60w Med.	2306 BK-LED	15w LED	900	2700K	92	1-100w	4¾"	5"	4½" W, 8¼" H Back Plate		KZ
2307 BK	1-50w GU10**							4"	2¾"	7¾" W, 5¼" H Back Plate		KZ

*Maximum achievable height with stems included. Additional 12" stems available, 6034 BKOD. Reflector type or Par type lamp recommended.
**GU10 bulb included. LED components have a lifespan of 40,000 hours and carry a 5-year limited warranty.

ARIA™

FINISH BUCKEYE BRONZE

Aria is a contemporary style that effortlessly complements the facade of any exterior. Its modern shape in durable aluminum is enhanced by a stainless-steel mesh shade. Aria's high style and low maintenance comes standard Dark Sky compliant.



2305 KZ
2305 KZ-LED
7" W, 21³/₄" H





2302 KZ
2302 KZ-LED
5" W, 19¼" H
51½" MAX. H*






2300 KZ
2300 KZ-LED
5" W, 15½" H






2306 KZ
2306 KZ-LED
4½" W, 14½" H






2304 KZ
2304 KZ-LED
5" W, 18½" H






2307 KZ
8½" W, 18" H





2307 KZ
(side view)
8½" W, 18" H



ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	STEMS INCLUDED	ADD. FINISHES
2300 KZ	1-75w Med.	2300 KZ-LED	15w LED	900	2700K	92	1-100w	6¾"	5"	4½" W, 8¼" H Back Plate		BK
2302 KZ	1-100w Med.	2302 KZ-LED	15w LED	900	2700K	92	1-100w			6" Dia. Canopy	10'	1-6", 2-12" BK
2304 KZ	1-100w Med.	2304 KZ-LED	15w LED	900	2700K	92	1-100w	6¾"	5"	4½" W, 8¼" H Back Plate		BK
2305 KZ	1-100w Med.	2305 KZ-LED	15w LED	900	2700K	92	1-100w	8¾"	5"	4½" W, 8¼" H Back Plate		BK
2306 KZ	1-60w Med.	2306 KZ-LED	15w LED	900	2700K	92	1-100w	4¾"	5"	4½" W, 8¼" H Back Plate		BK
2307 KZ	1-50w GU10**							4"	2¾"	7¾" W, 5¼" H Back Plate		BK

*Maximum achievable height with stems included. Additional 12" stems available, 4312 KZ. Reflector type or Par type lamp recommended.
 **GU10 bulb included. LED components have a lifespan of 40,000 hours and carry a 5-year limited warranty.

THEO™

FINISH OIL RUBBED BRONZE
SHADE WIRE MESH

Theo's robust frame features precision die-cast components and a sturdy mesh cage that creates a welcoming glow from its high-performance LED technology. The transitional style adds a layer of industrial chic that is at home on a variety of exteriors.



2745 OZ
8" W, 14" H





2740 OZ
6" W, 8¾" H



2744 OZ
8" W, 11¾" H



2742 OZ
8" W, 11¼" H



ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2740 OZ	13w LED	700	2700K	80	1-60w	7½"	2¼"	4¼" W, 5¼" H Back Plate	
2742 OZ	13w LED	700	2700K	80	1-60w			5" Dia. Canopy	6', 5'
2744 OZ	13w LED	700	2700K	80	1-60w	9½"	2¼"	4¼" W, 6¾" H Back Plate	
2745 OZ	13w LED	700	2700K	80	1-60w	8½"	2¼"	4¼" W, 6¾" H Back Plate	

LED components have a lifespan of 40,000 hours and carry a 5-year limited warranty.

BURKE™

FINISH OIL RUBBED BRONZE

GLASS CLEAR SEEDY

Burke's design has its roots in American Arts and Crafts architecture. A focus on solid construction, craftsmanship and clean lines make this impeccable design a fitting addition to almost any façade or outdoor living area.



2795 OZ-CL
10¼" W, 16¾" H



2792 OZ-CL
9" W, 13" H
47½" MAX. H*



2794 OZ-CL
9" W, 14" H



2790 OZ-CL
7" W, 10¾" H



2791 OZ-CL
9" W, 16" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
2790 OZ-CL**	1-100w Med.	7¼"	2¾"	4½" W, 5½" H Back Plate		
2791 OZ-CL	1-100w Med.			3" Dia. Post Fitter		
2792 OZ-CL**	1-100w Med.			5" Dia. Canopy	10'	1-6", 2-12"
2794 OZ-CL**	1-100w Med.	9¼"	3¼"	4½" W, 6¾" H Back Plate		
2795 OZ-CL**	1-100w Med.	9½"	3¼"	4½" W, 6¾" H Back Plate		

*Maximum achievable height with stems included. Additional 12" stems available, 6032 OZOD. **When fitted with DSL-40 this item is Dark Sky compliant, see hinkleylighting.com. Ideal for vintage filament bulbs (not included). For posts and pier mounts, see hinkleylighting.com

BURKE™

FINISH OIL RUBBED BRONZE

GLASS ETCHED OPAL

Burke's design has its roots in American Arts and Crafts architecture. A focus on solid construction, craftsmanship and clean lines make this impeccable design a fitting addition to almost any façade or outdoor living area.



2795 OZ
10¼" W, 16¾" H



2792 OZ
9" W, 13" H
47½" MAX. H*



2794 OZ
9" W, 14" H



2790 OZ
7" W, 10¾" H



2791 OZ
9" W, 16" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
2790 OZ	1-100w Med.	7¼"	2¾"	4¼" W, 5½" H Back Plate		
2791 OZ	1-100w Med.			3" Dia. Post Fitter		
2792 OZ	1-100w Med.			5" Dia. Canopy	10'	1-6", 2-12"
2794 OZ	1-100w Med.	9¼"	3¼"	4½" W, 6¾" H Back Plate		
2795 OZ	1-100w Med.	9½"	3¼"	4½" W, 6¾" H Back Plate		

*Maximum achievable height with stems included. Additional 12" stems available, 6032 OZOD. For posts and pier mounts, see hinkleylighting.com

PORTER™

FINISH AGED ZINC
GLASS CLEAR

A fusion of chic styles makes Porter a design standout. Merging Modern Farmhouse, Industrial and Arts and Crafts elements, the fine rivet details and a sturdy hanger loop create a stunning and distinctive statement.

OBJECT OF OUR
AFFECTION

Porter's craft and versatility complement a wide span of styles.



2805 DZ
7½" W, 25" H



2804 DZ
6½" W, 22" H



2800 DZ
6" W, 18½" H



2802 DZ
7½" W, 19" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2800 DZ*	1-100w Med.**	7¼"	4½"	6" W, 9" H Back Plate	
2802 DZ*	1-100w Med.**			5" Square Canopy	6', 5'
2804 DZ*	1-100w Med.**	8¼"	4½"	6" W, 9" H Back Plate	
2805 DZ*	1-100w Med.**	9¼"	4½"	6" W, 9" H Back Plate	

*When fitted with DSL-40 this item is Dark Sky compliant, see hinkleylighting.com. **Vintage filament T bulb included.

BRIGGS™

FINISH BUCKEYE BRONZE
GLASS ETCHED SEEDY

Briggs is a beacon of style in this sea-worthy design. Discreet nautical elements complement the classic lines of a signal lantern to create a bold, clean silhouette.



2495 KZ
10¼" W, 21" H



2492 KZ
8¾" DIA., 17¾" H
50¾" MAX. H*



2490 KZ
6½" W, 13½" H



2494 KZ
8¾" W, 17¼" H



PIER MOUNT
2497 KZ
8¾" W, 15" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
2490 KZ	1-100w Med.	7¼"	4¾"	4¼" W, 7¾" H Back Plate		
2492 KZ	1-100w Med.			6" Dia. Canopy	10'	1-6", 2-12"
2494 KZ	1-100w Med.	9½"	6"	4¼" W, 10" H Back Plate		
2495 KZ	1-100w Med.	11¼"	7"	5¼" W, 11½" H Back Plate		
2497 KZ	1-100w Med.			8" Dia. Base		

*Maximum achievable height with stems included. Additional 12" stems available, 6034 KZOD.

FREEPORT™

FINISH CLASSIC WHITE

GLASS CLEAR SEEDY

Freeport features a classic New England design in cast aluminum construction for timeless, traditional style.



1805 CW
1805 CW-LED
10" W, 15¼" H





1802 CW
1802 CW-LED
10" DIA., 14" H



1804 CW
1804 CW-LED
8" W, 12¼" H



1800 CW
1800 CW-LED
6" W, 9¼" H



1807 CW
8" DIA., 17¾" H



1801 CW
1801 CW-LED
10" DIA., 20¼" H
(shown as pier mount
with 1304 CW)**



ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	ADDITIONAL FINISHES
1800 CW*	1-75w Med.	1800 CW-LED	10w LED	550	2700K	96	2-50w	7"	2½"	4½" W, 6" H Back Plate		BK, OP, OZ
1801 CW	1-100w Med.	1801 CW-LED	15w LED	900	2700K	92	1-100w			3" Dia. Post Fitter		BK, OP, OZ
1802 CW*	1-100w Med.	1802 CW-LED	15w LED	800	2700K	96	1-100w			4¼" Dia. Canopy	6', 5'	BK, OP, OZ
1804 CW*	1-100w Med.	1804 CW-LED	15w LED	800	2700K	96	1-100w	9"	3"	5" W, 8" H Back Plate		BK, OP, OZ
1805 CW*	1-100w Med.	1805 CW-LED	15w LED	800	2700K	96	1-100w	11¼"	3¼"	5¾" W, 9½" H Back Plate		BK, OP, OZ
1807 CW	1-100w Med.									3" Dia. Post Fitter		BK, OP, OZ

*When fitted with DSL-40 this item is Dark Sky compliant, see hinkleylighting.com. **Not for use within 4ft. of ground. For additional posts and pier mounts, see hinkleylighting.com. LED components have a lifespan of 40,000 hours and carry a 5-year limited warranty.

PERRY™

FINISH OIL RUBBED BRONZE
GLASS CLEAR SEEDY

Named for Commodore Oliver Hazard Perry, who led a fleet to victory in one of the most significant naval battles in the War of 1812, this nautical-inspired aluminum lantern offers distinctive longitudinal and latitudinal cage construction. Clear seedy glass and a durable Oil Rubbed Bronze finish reinforce Perry's transitional style, which effortlessly complements a variety of façades.



2384 OZ
8" W, 24" H





2380 OZ
5½" W, 19¾" H



2382 OZ
5¼" W, 16" H
48½" MAX. H*



ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
2380 OZ	1-50w GU-10**	6¾"	10"	5" W, 6½" H Back Plate		
2382 OZ	1-50w GU-10**			5" Dia. Canopy	10'	1-6", 2-12"
2384 OZ	1-50w GU-10**	10"	12"	5" W, 6½" H Back Plate		

*Maximum achievable height with stems included. Additional 12" stems available, 6061 OZOD. **GU-10 bulb included.

MARINA™

FINISH HEMATITE

GLASS CLEAR OR ETCHED HOLOPHANE

Set sail with Marina. Inspired by authentic ship passageway lighting, its die-casted aluminum construction uniquely emphasizes the captured etched holophane or clear holophane glass. Robust finish options include Bronze or Hematite and showcase the fresh, modern-nautical cast cage design.

DESIGN NOTE

AVAILABLE TO ORDER WITH
EITHER CLEAR OR ETCHED
HOLOPHANE GLASS TO BEST
COMPLEMENT YOUR DECOR



2484 HE
10¼" W, 14½" H



2413 HE
10¼" W, 5" H



2480 HE
8¼" W, 11¾" H



2414 HE
10¼" W, 14½" H



2410 HE
8¼" W, 11¾" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
2410 HE	1-100w Med.	8½"	2½"	5" Dia.	BZ
2413 HE	2-60w Med.				BZ
2414 HE	1-100w Med.	10½"	2½"	5" Dia.	BZ
2480 HE*	1-100w Med.	8½"	2½"	5" Dia.	BZ
2484 HE*	1-100w Med.	10½"	2½"	5" Dia.	BZ

*When fitted with DSL-40 this item is Dark Sky compliant, see hinkleylighting.com.

MARINA™

FINISH BRONZE

GLASS CLEAR OR ETCHED HOLOPHANE

Set sail with Marina. Inspired by authentic ship passageway lighting, its die-casted aluminum construction uniquely emphasizes the captured etched holophane or clear holophane glass. Robust finish options include Bronze or Hematite and showcase the fresh, modern-nautical cast cage design.



2414 BZ
10¼" W, 14½" H



2413 BZ
10¼" W, 5" H



2410 BZ
8¼" W, 11¾" H



2484 BZ
10¼" W, 14½" H



2480 BZ
8¼" W, 11¾" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
2410 BZ	1-100w Med.	8½"	2½"	5" Dia.	HE
2413 BZ	2-60w Med.				HE
2414 BZ	1-100w Med.	10½"	2½"	5" Dia.	HE
2480 BZ*	1-100w Med.	8½"	2½"	5" Dia.	HE
2484 BZ*	1-100w Med.	10½"	2½"	5" Dia.	HE

*When fitted with DSL-40 this item is Dark Sky compliant, see hinkleylighting.com.

TATUM™

FINISH OIL RUBBED BRONZE
GLASS CLEAR SEEDY

Perfectly proportioned, Tatum's clean lines feature a hint of nautical nuance. A sturdy die cast housing with a bold decorative rim at the bottom edge in Oil Rubbed Bronze showcases the elegant clear seedy glass in an appealing vintage shape.



1884 OZ
8¼" W, 14¼" H



1880 OZ
5½" W, 9¾" H



1882 OZ
8¼" DIA., 16" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1880 OZ*	1-100w Med.	6¼"	3½"	5" Dia. Back Plate	
1882 OZ*	1-100w Med.			5½" Dia. Canopy	6', 5'
1884 OZ*	1-100w Med.	8½"	4½"	5" W, 7" H Back Plate	

*When fitted with DSL-40 this item is Dark Sky compliant, see hinkleylighting.com. Ideal for vintage filament bulbs (not included).

ANCHORAGE™

FINISH LIGHT OILED BRONZE

GLASS CLEAR

Anchorage is an early American lantern design crafted of solid aluminum to reflect a bold yet refined silhouette. The Light Oiled Bronze finish and clear glass complement the long clean lines, elegant arched carriage handle and sturdy knobs, resulting in a vintage style with classic charisma.



1858 LZ
13" W, 25" H

DOWNSCALED LANTERN IN THE ANCHORAGE COLLECTION'S POPULAR AGED ZINC FINISH

NEW



1854 LZ
9 1/4" W, 17 3/4" H



1850 LZ
7" W, 13" H



1850 DZ
7" W, 13" H



1852 LZ
11" W, 23 3/4" H



1855 LZ
11" W, 21 1/4" H



1851 LZ
11" W, 24 1/4" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	ADDITIONAL FINISHES
1850 DZ, LZ*	1-100w Med.	6"	7 3/4"	4 1/2" W, 6" H Back Plate		
1851 LZ	3-60w Cand.			3" Dia. Post Fitter		DZ
1852 LZ	3-60w Cand.			5 3/4" Canopy	6', 5'	DZ
1854 LZ	2-60w Cand.	7 3/4"	12 1/4"	4 1/2" W, 7" H Back Plate		DZ
1855 LZ	3-60w Cand.	9"	15 1/2"	4 1/2" W, 7" H Back Plate		DZ
1858 LZ	4-60w Cand.	10 3/4"	17 1/2"	4 1/2" W, 9" H Back Plate		DZ

*When fitted with DSL-40 this item is Dark Sky compliant, see hinkleylighting.com. For posts and pier mounts, see hinkleylighting.com

ALFORD PLACE™

FINISH OIL RUBBED BRONZE
GLASS CLEAR

The clean and classic design of Alford Place features a precision die-cast frame, hanging arm and top loop, paired with a sealed glass roof, providing excellent illumination from all sides.



2565 OZ
12" W, 20½" H



2562 OZ
12" W, 19½" H



2564 OZ
10" W, 17½" H



2560 OZ
8" W, 14" H



2561 OZ
10" W, 20¼" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2560 OZ	2-60w Cand.	9"	7"	4¾" W, 5½" H Back Plate	
2561 OZ	2-60w Cand.			3" Dia. Post Fitter	
2562 OZ	3-60w Cand.			5" Dia. Canopy	6', 5'
2564 OZ	2-60w Cand.	11¼"	8"	4¾" W, 6¾" H Back Plate	
2565 OZ	3-60w Cand.	13½"	9¼"	4¾" W, 8¼" H Back Plate	

For posts and pier mounts, see hinkleylighting.com

BROMLEY™

FINISH OIL RUBBED BRONZE

GLASS CLEAR

Bromley's handsome silhouette features an updated traditional design that combines elegant and stately details. These dignified die-casted aluminum fixtures convey sophistication in an Oil Rubbed Bronze finish that complements any façade. Specialty touches such as a "Shepard's Hook" decorative scrolled arm and multiple mounting points highlight Bromley's homage to tradition and quality.



2366 OZ
10" W, 24³/₄" H



2362 OZ
10" W, 19" H



2364 OZ
8" W, 19¾" H



2360 OZ
8" W, 15¼" H



2368 OZ
8" W, 11¾" H



2365 OZ
10" W, 19" H



2361 OZ
10" W, 22½" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2360 OZ	2-60w Cand.	9¼"	7½"	4½" W, 8¼" H Back Plate	
2361 OZ	3-60w Cand.			3" Dia. Post Fitter	
2362 OZ	3-60w Cand.			5" Dia. Canopy	6', 5'
2364 OZ	2-60w Cand.	9½"	12½"	4½" W, 8¼" H Back Plate	
2365 OZ	3-60w Cand.	11¼"	8½"	4½" W, 8¼" H Back Plate	
2366 OZ	3-60w Cand.	11¾"	16¾"	4½" W, 8¼" H Back Plate	
2368 OZ*	1-100w Med.	9¼"	7¾"	4½" W, 8¼" H Back Plate	

*When fitted with DSL-40 this item is Dark Sky compliant, see hinkleylighting.com. For posts and pier mounts, see hinkleylighting.com

ENZO™


FINISH OIL RUBBED BRONZE
GLASS CLEAR SEEDY

Enzo blends delicate beauty and lasting durability. The intricate die cast aluminum construction features graceful scrolls with Old World allure. An Oil Rubbed Bronze finish combines with clear seedy glass for timeless elegance.



2275 OZ
2275 OZ-LED
10" W, 18¾" H





2272 OZ
2272 OZ-LED
10" W, 19" H

2278 OZ
2278 OZ-LED
10" W, 28½" H

2274 OZ
2274 OZ-LED
8" W, 14" H

2271 OZ
2271 OZ-LED
10" W, 21" H

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
2271 OZ	1-100w Med.	2271 OZ-LED	15w LED	800	2700K	96	1-100w			3" Dia. Post Fitter	
2272 OZ*	1-100w Med.	2272 OZ-LED	15w LED	900	2700K	92	1-100w			5" Square Canopy	6', 5'
2274 OZ*	1-100w Med.	2274 OZ-LED	15w LED	800	2700K	96	1-100w	9¼"	6"	4½" W, 8¼" H Back Plate	
2275 OZ*	1-100w Med.	2275 OZ-LED	15w LED	800	2700K	96	1-100w	11¼"	7"	4½" W, 8¼" H Back Plate	
2278 OZ*	1-100w Med.	2278 OZ-LED	15w LED	800	2700K	96	1-100w	11¾"	14½"	5¼" W, 18½" H Back Plate	

*When fitted with DSL-40, this item is Dark Sky compliant, see hinkleylighting.com. LED components have a lifespan of 40,000 hours and carry a 5-year limited warranty. For posts and pier mounts, see hinkleylighting.com

TRELLIS™

FINISH AGED ZINC
GLASS CLEAR

Trellis is a traditional European hanging wall lantern design in an Aged Zinc finish with clear glass or Regency Bronze with clear seeded glass. The large scroll arm detail, cast loop finial and true rivet detail create a refined elegance.



1435 DZ
11" W, 22¼" H



1429 DZ
9" W, 14¾" H
(can be used with 1433DZ-SCR)



1433 DZ
(1433DZ-SCR included)
29¾" W, 14¾" H



1433 DZ-SCR
29¾" W, 9" H



THE SUGGESTION BOX

Optional scrolls allow for a variety of decorative arrangements.



1438 DZ
13" W, 26¼" H



PIER MOUNT
1437 DZ
11" W, 19¾" H



1431 DZ
11" W, 21" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	ADDITIONAL FINISHES
1429 DZ	3-60w Cand.	11½"	8½"	4½" W, 10" H Back Plate	RB
1431 DZ	3-60w Cand.			3" Dia. Post Fitter	RB
1433 DZ	3-60w Cand.	11½"	8½"	4½" W, 10" H Back Plate	RB
1433 DZ-SCR					RB
1435 DZ	4-60w Cand.	16½"	8"	4½" W, 10" H Back Plate	RB
1437 DZ	4-60w Cand.			10¼" Square Base	RB
1438 DZ	4-60w Cand.	19"	9½"	5" W, 13" H Back Plate	RB

For posts and pier mounts, see hinkleylighting.com

NEW

LARGE SCALE HANGER IN THE
TRELLIS COLLECTION'S POPULAR
REGENCY BRONZE FINISH



1428 RB
16" W, 31¼" H



1432 DZ
11" W, 23¼" H



1428 DZ
16" W, 31¼" H



1430 DZ
7" W, 15¼" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	ADDITIONAL FINISHES
1428 DZ	4-60w Cand.			6" Square Canopy	12', 10'	RB
1428 RB	4-60w Cand.			6" Square Canopy	12', 10'	DZ
1430 DZ*	1-100w Med.	11¼"	6"	4½" W, 7" H Back Plate		RB
1432 DZ	3-60w Cand.			4½" Square Canopy	6', 5'	RB

*When fitted with DSL-40 this item is Dark Sky compliant, see hinkleylighting.com



1434 DZ
9" W, 19¾" H



1439 DZ
16" W, 52" H



1436 DZ
11" W, 35¾" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	ADDITIONAL FINISHES
1434 DZ	3-60w Cand.	14½"	8"	4½" W, 10" H Back Plate	RB
1436 DZ	4-60w Cand.	16½"	18¾"	4½" W, 13" H Back Plate	RB
1439 DZ	4-60w Cand.	24"	27½"	4¾" W, 20" H Back Plate	RB

INDEX

1110DZ	S355	1765SK	S374	2355SK	S368	2834BZ	S361	3233OZ	S268
1110OZ	S355	1765SW	S374	2355TT	S368	2834TT	S361	3260IN	S251
1112DZ	S355	1765TT	S374	2360OZ	S405	2835BZ	S360	3263IN	S251
1112OZ	S355	1768BZ	S374	2361OZ	S405	2835TT	S360	3265IN	S251
1113DZ	S354	1768SK	S374	2362OZ	S405	2850BZ	S363	3266IN	S250
1113OZ	S354	1768SW	S374	2364OZ	S405	2850TT	S363	3267IN	S251
1114DZ	S355	1768TT	S374	2365OZ	S405	2854BZ	S363	3407BN	S258
1114OZ	S355	1769BZ	S374	2366OZ	S404	2854TT	S363	3407HB	S258
1220BZ	S365	1769SK	S374	2368OZ	S405	2855BZ	S362	3407KZ	S258
1220SK	S367	1769SW	S374	2380OZ	S393	2855TT	S362	3460CG	S241
1220TT	S366	1769TT	S374	2382OZ	S393	2920ISQ	S353	3460SB	S243
1224BZ	S365	1800CW	S391	2384OZ	S392	29202SQ	S353	3463CG	S241
1224SK	S367	1801CW	S391	2410BZ	S397	29203SQ	S353	3463SB	S243
1224TT	S366	1802CW	S391	2410HE	S395	29205SQ	S353	3464CG	S240
1225BZ	S365	1804CW	S391	2413BZ	S397	29206SQ	S353	3464SB	S242
1225SK	S367	1805CW	S390	2413HE	S395	29208SQ	S352	3466CG	S241
1225TT	S366	1807CW	S391	2414BZ	S396	29700VI	S359	3466SB	S243
1304CW	S391	1850DZ	S401	2414HE	S395	29700WZ	S357	3468CG	S241
1428DZ	S410	1850LZ	S401	2480BZ	S397	29703VI	S359	3468SB	S243
1428RB	S410	1851LZ	S401	2480HE	S395	29703WZ	S357	3469CG	S241
1429DZ	S409	1852LZ	S401	2484BZ	S397	29705VI	S358	3469SB	S243
1430DZ	S410	1854LZ	S401	2484HE	S394	29705WZ	S356	3521AN	S263
1431DZ	S409	1855LZ	S401	2490KZ	S389	29707VI	S359	3521BC	S264
1432DZ	S410	1858LZ	S400	2492KZ	S389	29707WZ	S357	3521CM	S265
1433DZ	S409	1880OZ	S399	2494KZ	S389	3023DG	S245	3522AN	S263
1433DZ-SCR	S409	1882OZ	S399	2495KZ	S388	3023MM	S247	3522BC	S264
1434DZ	S411	1884OZ	S398	2497KZ	S389	3025DG	S244	3522CM	S265
1435DZ	S408	20300BZ	S364	2560OZ	S403	3025MM	S246	3523AN	S263
1436DZ	S411	20300TT	S364	2561OZ	S403	3027DG	S245	3523BC	S264
1437DZ	S409	20305BZ	S364	2562OZ	S403	3027MM	S247	3523CM	S265
1438DZ	S409	20305TT	S364	2564OZ	S403	3030BN	S269	3574DZ	S248
1439DZ	S411	2271OZ	S407	2565OZ	S402	3030DZ	S269	3576DZ	S248
1647BZ	S372	2272OZ	S407	2740OZ	S381	3030KZ	S269	3604GV	S256
1647SK	S372	2274OZ	S407	2742OZ	S381	3030PN	S269	3604KZ	S256
1647SW	S372	2275OZ	S406	2744OZ	S381	3072AN	S229	3641BN	S267
1647TT	S372	2278OZ	S407	2745OZ	S380	3072KZ	S231	3641CM	S267
1660BZ	S371	2300BK	S377	2790OZ	S385	3075AN	S229	3641HB	S267
1660SK	S371	2300KZ	S379	2790OZ-CL	S383	3075KZ	S231	3641OZ	S267
1660TT	S371	2302BK	S377	2791OZ	S385	3076AN	S229	3643BN	S266
1661BZ	S373	2302KZ	S379	2791OZ-CL	S383	3076KZ	S231	3643CM	S266
1661SK	S373	2304BK	S377	2792OZ	S385	3078AN	S228	3643HB	S266
1661TT	S373	2304KZ	S379	2792OZ-CL	S383	3078KZ	S230	3643OZ	S266
1662BZ	S373	2305BK	S376	2794OZ	S385	3122PT	S257	3650AN	S270
1662SK	S373	2305KZ	S378	2794OZ-CL	S383	3126PT	S257	3650HB	S270
1662TT	S373	2306BK	S377	2795OZ	S384	3162AN	S271	3650OZ	S270
1664BZ	S371	2306KZ	S379	2795OZ-CL	S382	3162BR	S271	3650PN	S270
1664TT	S371	2307BK	S377	2800DZ	S387	3162OZ	S271	3773GZ	S227
1664SK	S370	2307KZ	S379	2802DZ	S387	3231BN	S268	3773PN	S225
1665BZ	S372	2350SK	S369	2804DZ	S387	3231DZ	S268	3774GZ	S226
1665SK	S372	2350TT	S369	2805DZ	S386	3231OZ	S268	3774PN	S224
1665TT	S372	2354SK	S369	2830BZ	S361	3233BN	S268	3776GZ	S227
1765BZ	S374	2354TT	S369	2830TT	S361	3233DZ	S268	3776PN	S225

3777GZ	S227	51803PN	S348	5553CM-CL	S333	63307BN-CL	S233	FR39216PNI	S285
3777PN	S225	51804BN-CL	S349	5554CM-CL	S333	63307BN-SM	S233	FR40571IRR	S319
3843OZ	S261	51804PN	S348	5555CM-CL	S333	63307CM-MR	S233	FR40703VIR	S321
3844OZ	S261	51820BN	S332	5556CM-CL	S333	63307CM-SM	S233	FR40705VIR	S321
3910IR	S255	51820KZ	S331	5600CM	S341	63307SK-CL	S233	FR40707VIR	S321
3910SH	S255	51820PN	S330	5602CM	S341	63307SK-SM	S233	FR40708VIR	S320
3913IR	S255	51822BN	S332	5603CM	S341	FR31022SLF	S311	FR41213IRR	S318
3916IR	S255	51822KZ	S331	5604CM	S341	FR31023SLF	S311	FR41214IRR	S318
3918IR	S254	51822PN	S330	5650BN	S329	FR31024SLF	S311	FR41941CPN	S291
3920KZ	S239	51823BN	S332	5650CM	S329	FR31025SLF	S311	FR41946CPN	S291
3920PL	S237	51823KZ	S331	5650OZ	S329	FR31027SLF	S311	FR41948CPN	S291
3924KZ	S239	51823PN	S330	5651BN	S234	FR31028SLF	S310	FR41949CPN	S290
3924PL	S237	51824BN	S332	5651OZ	S235	FR32804SBK	S277	FR42442PNI	S295
3925KZ	S238	51824KZ	S331	5652BN	S329	FR32804WWT	S275	FR42444PNI	S296
3925PL	S236	51824PN	S330	5652CM	S329	FR32805SBK	S277	FR42445PNI	S296
3927KZ	S239	51825BN	S332	5652OZ	S329	FR32805WWT	S275	FR42446PNI	S295
3927PL	S237	51825KZ	S331	5654BN	S329	FR32806SBK	S276	FR42447PNI	S296
3992BN	S234	51825PN	S330	5654CM	S329	FR32806WWT	S274	FR42448PNI	S295
3992OZ	S235	52230BN	S337	5654OZ	S329	FR33738SLF	S303	FR42449PNI	S294
3996BN	S234	52232BN	S337	5656BN	S329	FR33738VBZ	S303	FR43014HBZ	S293
3996OZ	S235	52233BN	S337	5656CM	S329	FR34310HBR	S279	FR43015HBZ	S293
3997BN	S234	52234BN	S337	5656OZ	S329	FR34314HBR	S279	FR43016HBZ	S292
3997OZ	S235	5280AN	S343	56670AN	S345	FR34315HBR	S278	FR44812SLF	S309
4000SH	S219	5280PN	S342	56670PN	S344	FR34317HBR	S279	FR44813SLF	S309
4002PN	S219	5282AN	S343	56672AN	S345	FR34410PNI	S281	FR44814SLF	S309
4005PN	S219	5282PN	S342	56672PN	S344	FR34414PNI	S281	FR44816SLF	S309
4006PN	S218	5283AN	S343	56673AN	S345	FR34415PNI	S280	FR44817SLF	S309
4323HB	S223	5283PN	S342	56673PN	S344	FR34417PNI	S281	FR44818SLF	S309
4323OZ	S223	5284AN	S343	56674AN	S345	FR36012PNI	S299	FR44819SLF	S308
4323PN	S223	5284PN	S342	56674PN	S344	FR36013PNI	S299	FR46800CPG	S314
4325HB	S222	5350PN	S334	57130CM	S340	FR36014PNI	S299	FR46801CPG	S314
4325OZ	S223	5352PN	S334	57132CM	S340	FR36015PNI	S298	FR46802CPG	S314
4325PN	S223	5353PN	S334	57133CM	S340	FR36018PNI	S299	FR46803CPG	S313
4483EN	S221	5354PN	S334	57134CM	S340	FR37122SLF	S305	FR46804CPG	S314
4484EN	S221	53550CM	S327	5920BN	S328	FR37123SLF	S304	FR46805CPG	S315
4485EN	S220	53552CM	S327	5920CM	S328	FR37127SLF	S305	FR46806CPG	S313
4744BN	S260	53553CM	S327	5922BN	S328	FR37231SLF	S317	FR46808CPG	S315
4744OZ	S260	53554CM	S327	5922CM	S328	FR37233SLF	S317	FR46809CPG	S313
4824IR	S253	5440BN	S335	5923BN	S328	FR37235SLF	S316	FR46810CPG	S312
4825IR	S253	5442BN	S335	5923CM	S328	FR38012SSG	S287	FR47505HRR	S289
4826IR	S252	5443BN	S335	5924BN	S328	FR38015SSG	S287	FR47506HRR	S288
4834DZ	S259	5444BN	S335	5924CM	S328	FR38016SSG	S286	FR47507HRR	S289
4834PN	S259	55020BN	S339	5925BN	S328	FR38018SSG	S287	FR48052CPG	S307
51100CM	S336	55020PN	S338	5925CM	S328	FR39212GMT	S283	FR48053CPG	S307
51102CM	S336	55022BN	S339	59922BN	S326	FR39212PNI	S285	FR48055CPG	S306
51103CM	S336	55022PN	S338	59922CM	S325	FR39213GMT	S283	FR48056CPG	S307
51104CM	S336	55023BN	S339	59923BN	S326	FR39213PNI	S285	FR48204ANI	S301
51800BN-CL	S349	55023PN	S338	59923CM	S325	FR39214GMT	S283	FR48205ANI	S300
51800PN	S348	55024BN	S339	59924BN	S326	FR39214PNI	S285	FR48602DXG	S302
51802BN-CL	S349	55024PN	S338	59924CM	S325	FR39215GMT	S282	FR48602MMB	S302
51802PN	S348	5550CM-CL	S333	63306SK-CL	S232	FR39215PNI	S284		
51803BN-CL	S349	5552CM-CL	S333	63306SK-SM	S233	FR39216GMT	S283		



THIS IS HINKLEY

At your fingertips | AWARD-WINNING CATALOGS

Check out our full range of products in easy-to-use, full color catalogs complete with sizing guidelines, design ideas and eco-tips.

Information 24/7/365 | DYNAMIC WEBSITE

hinkleylighting.com

Surf all of the details on our lighting collections, including the newest products from Hinkley and Fredrick Ramond, tips from professional designers and locate a Hinkley showroom in your area.

Make the world a better place | COMMUNITY INVOLVEMENT

The Hinkley Lighting family proudly supports breast cancer initiatives. By increasing awareness and supporting education and community events, together we can work towards finding a cure. Hinkley also supports a variety of other charitable organizations that strive to make a positive difference in the lives of others. Visit hinkleylighting.com for more information.

Be inspired | ENGAGING VIDEOS

youtube.com/hinkleylightinginc

Visit Hinkley on YouTube to watch our product, educational and brand videos.

Talk is chic | SOCIAL MEDIA

See what captivates us:

facebook.com/hinkleylighting

pinterest.com/hinkleylighting

houzz.com/hinkleylighting

instagram.com/hinkleylighting

twitter.com/hinkleylighting



Hinkley Lighting stands behind the quality of our lighting fixtures with product warranties that are among the strongest in the industry. For details of warranty coverage on specific products, please refer to hinkleylighting.com or consult a qualified Hinkley retail distributor.

Several Hinkley Lighting products are protected under U.S. Patent and foreign patent, or patent pending. For current information regarding Hinkley Lighting's patent portfolio, please visit hinkleylighting.com.

Consistent with our corporate strategy, we have printed this catalog using vegetable-based inks, paper made with wind power and FSC® certified paper which consists of 10% post-consumer recovered fiber.

According to the Mohawk Environmental Calculator, our paper selection preserves 44 trees for the future, saves 20,730 gallons of wastewater flow and prevents 3,822 lbs of greenhouse gases from being emitted into the atmosphere. Please consider joining our environmental efforts and recycling this catalog.

©2017 Hinkley Lighting, Inc.
All rights reserved in all copyrightable works.



Hinkley Lighting is a proud partner of the American Lighting Association.

HINKLEY

L I G H T I N G

CLASSIC, CHIC COLLECTIONS | HINKLEYLIGHTING.COM



FREDRICK RAMOND

ESTABLISHED 1965

HINKLEY'S LUXURY LINE | FREDRICKRAMOND.COM

33000 PIN OAK PARKWAY | AVON LAKE, OHIO 44012
PHONE (440) 653 5500 | FAX (440) 653 5555
SHOWROOM 3210 | DALLAS TRADE MART | DALLAS, TEXAS 75207

JANUARY 2017 CATALOG SUP117

