

## MORKSMARTER NOTIBARDER




#### **Table of Contents:**


WIRE MANAGEMENT TOOLS	
Rack-A-Tiers – Wire Dispenser	3
Hooker – Pipe Wrench Adapter	3
EZ Roll – Wheeled Wire Dispenser	4
Tug Wise – Reel Dispenser	4
Cable Caddy, Carts, Dolly, Truck, & Data Carts	5
Plate Vise & Wire Pull Pro	5
Reel Mac 60, 70, 80 & Spindles	6
Ratchet Reel Mac	6
Mac Line Racks & Reels	7
Easy Stripper	8
Copper Wire Stripper	8
Pocket Kart – Reel Carrying Tool	9
Gorilla Nuts – Cushion Grip Connectors	9
Dryconn – Waterproof Connectors	9
WIRE PULLING AND FISHING	
All-American Pull Buddy	10
LB Wire Guide	10
Wire Vortex	10
Ropematic – Rope and Fish Tape Pulller	11
Snatch Strap – Wire Puller	11
Power Pull-It	11
Magnepull & Magnespot	12
Flex Puller	13
Coneheads	13
Laserline – Line Dart Shooter	13
Plastic Coated Fiberfish, Glowfish & Attachments	14
Fibersnakes & Contractor Packs	15
Bag Pipers	15
TOOL BAGS AND OTHER STUFF	
Combination Tool Belt & Pouch	16
Butt Pouches	17
Lift-n-Lok Tool Box	17
Staple Shark	18
Bigg Lugg	18
Carpenter's Pencil	18
Felt marker	18
Hammer	18
Croc's – Needle Nose Wire Stripper	19
V-Cutter – Electrician`s Wire Stripper Attachment	19
Bend-All – Cable Bender	19
Racksy Knee Pads	20
Booty Pack – Disposable Boot Covers, Gloves, Respirators	20
Gopher LED Flashlight	20
Bolt Template	20
Panel Buddy – Knockout Kit	21
P. S. Knight Electical Code Books	21
DeWALT Professional Reference Series	21
Owik Lok – Locking Plug	22
Sluggo-Ox	22
Piper - Conduit Tracking System	23
Nut Blaster – Wire Connector Tools	23

Breaker Lok	23
HOLE CUTTING	
Mega TCT Hole Saws	24
Heavy Duty TCT Masonry Hole Saws	24
Carbide Tipped Steel Cutters	25
Multi Bits (Step Drills)	25
The Javelin - Drilling Extension Kit	25
Bumper Balls & Flexible Auger Bits	26
Auger Bit File	27
Nail Chipper, Ship Auger, Tri-Cut, Standard & Overdrive	27
Multi-Function Hole Cutters & Accessories	28
Driller's Dust Bowl	29
Exploding Garbage Can	29
COLORED RACKY BITS	
#0 Yellow Square	30
#1 Green Square	30
#2 Red Square	30
#3 Black Square	30
#4 Orange Square	30
#1 Light Blue Phillips	30
#2 Blue Phillips	30
4" & 6" Double Ended Bits – #2 Phillips & 1/4 slot	30
4" & 6" Double Ended Bits – #2 Trillings & 174 Sidt	30
Robertson® Impact Driver Bits	30
Magnetic Hex Bits	30
Lockhard #1 Square with Wings 4" & 6"	31
Dicquic Scrowdrivors	21
Picquic Screwdrivers  ProGraphit Kit - Damaged Screw Remover	31 31
ProGrabit Kit – Damaged Screw Remover	31 31
ProGrabit Kit – Damaged Screw Remover	31
ProGrabit Kit – Damaged Screw Remover  PIPE AND CONDUIT BENDING  Hoppy Bender – Conduit Pipe Bender	31
ProGrabit Kit – Damaged Screw Remover  PIPE AND CONDUIT BENDING  Hoppy Bender – Conduit Pipe Bender  Pipe Viper – Cold PVC Pipe Bender	31 32 33
ProGrabit Kit – Damaged Screw Remover  PIPE AND CONDUIT BENDING  Hoppy Bender – Conduit Pipe Bender  Pipe Viper – Cold PVC Pipe Bender  PVC Bend-It	31
ProGrabit Kit – Damaged Screw Remover  PIPE AND CONDUIT BENDING  Hoppy Bender – Conduit Pipe Bender  Pipe Viper – Cold PVC Pipe Bender  PVC Bend-It	31 32 33 33
ProGrabit Kit – Damaged Screw Remover  PIPE AND CONDUIT BENDING  Hoppy Bender – Conduit Pipe Bender  Pipe Viper – Cold PVC Pipe Bender  PVC Bend-It.  LEVELS AND TESTERS  Laser Plumb Bob	31 32 33 33 34
ProGrabit Kit – Damaged Screw Remover  PIPE AND CONDUIT BENDING  Hoppy Bender – Conduit Pipe Bender  Pipe Viper – Cold PVC Pipe Bender  PVC Bend-It  LEVELS AND TESTERS  Laser Plumb Bob  Straight Shot Level	31 32 33 33 34 34
ProGrabit Kit – Damaged Screw Remover  PIPE AND CONDUIT BENDING  Hoppy Bender – Conduit Pipe Bender  Pipe Viper – Cold PVC Pipe Bender  PVC Bend-It.  LEVELS AND TESTERS  Laser Plumb Bob  Straight Shot Level  Jet level	31 32 33 33 34 34 34
ProGrabit Kit – Damaged Screw Remover  PIPE AND CONDUIT BENDING  Hoppy Bender – Conduit Pipe Bender  Pipe Viper – Cold PVC Pipe Bender  PVC Bend-It  LEVELS AND TESTERS  Laser Plumb Bob  Straight Shot Level  Jet level  Plug Master Circuit Tester	31 32 33 33 34 34 34 35
ProGrabit Kit – Damaged Screw Remover  PIPE AND CONDUIT BENDING  Hoppy Bender – Conduit Pipe Bender  Pipe Viper – Cold PVC Pipe Bender  PVC Bend-It  LEVELS AND TESTERS  Laser Plumb Bob  Straight Shot Level  Jet level  Plug Master Circuit Tester  Circuit Siren	31 32 33 33 34 34 34 35 35
ProGrabit Kit – Damaged Screw Remover  PIPE AND CONDUIT BENDING  Hoppy Bender – Conduit Pipe Bender  Pipe Viper – Cold PVC Pipe Bender  PVC Bend-It  LEVELS AND TESTERS  Laser Plumb Bob  Straight Shot Level  Jet level  Plug Master Circuit Tester  Circuit Siren  AC Sensors	31 32 33 33 34 34 34 35
ProGrabit Kit – Damaged Screw Remover  PIPE AND CONDUIT BENDING  Hoppy Bender – Conduit Pipe Bender  Pipe Viper – Cold PVC Pipe Bender  PVC Bend-It  LEVELS AND TESTERS  Laser Plumb Bob  Straight Shot Level  Jet level  Plug Master Circuit Tester  Circuit Siren  AC Sensors  CONNECTORS, ETC	31 32 33 34 34 34 35 35 35
ProGrabit Kit – Damaged Screw Remover  PIPE AND CONDUIT BENDING  Hoppy Bender – Conduit Pipe Bender  Pipe Viper – Cold PVC Pipe Bender  PVC Bend-It  LEVELS AND TESTERS  Laser Plumb Bob  Straight Shot Level  Jet level  Plug Master Circuit Tester  Circuit Siren  AC Sensors  CONNECTORS, ETC  Cable Protection Systems	31 32 33 33 34 34 35 35 35 36
ProGrabit Kit – Damaged Screw Remover  PIPE AND CONDUIT BENDING  Hoppy Bender – Conduit Pipe Bender  Pipe Viper – Cold PVC Pipe Bender  PVC Bend-It  LEVELS AND TESTERS  Laser Plumb Bob  Straight Shot Level  Jet level  Plug Master Circuit Tester  Circuit Siren  AC Sensors  CONNECTORS, ETC  Cable Protection Systems  Racky Strap – Utility Strap	31 32 33 33 34 34 35 35 35 36 36
ProGrabit Kit – Damaged Screw Remover  PIPE AND CONDUIT BENDING  Hoppy Bender – Conduit Pipe Bender  Pipe Viper – Cold PVC Pipe Bender  PVC Bend-It  LEVELS AND TESTERS  Laser Plumb Bob  Straight Shot Level  Jet level  Plug Master Circuit Tester  Circuit Siren  AC Sensors  CONNECTORS, ETC  Cable Protection Systems  Racky Strap – Utility Strap  Handi Hoop	31 32 33 33 34 34 35 35 35 36 36 36
ProGrabit Kit – Damaged Screw Remover  PIPE AND CONDUIT BENDING  Hoppy Bender – Conduit Pipe Bender  Pipe Viper – Cold PVC Pipe Bender  PVC Bend-It  LEVELS AND TESTERS  Laser Plumb Bob  Straight Shot Level  Jet level  Plug Master Circuit Tester  Circuit Siren  AC Sensors  CONNECTORS, ETC  Cable Protection Systems  Racky Strap – Utility Strap  Handi Hoop  Stud Buddies – Steel Stud Bushings	31 32 33 34 34 35 35 35 36 36 36 36 36
ProGrabit Kit – Damaged Screw Remover  PIPE AND CONDUIT BENDING  Hoppy Bender – Conduit Pipe Bender  Pipe Viper – Cold PVC Pipe Bender  PVC Bend-It  LEVELS AND TESTERS  Laser Plumb Bob  Straight Shot Level  Jet level  Plug Master Circuit Tester  Circuit Siren  AC Sensors  CONNECTORS, ETC  Cable Protection Systems  Racky Strap – Utility Strap  Handi Hoop  Stud Buddies – Steel Stud Bushings  KOK Series – 1/2" to 2" Plastic Knock Out Fillers	31 32 33 33 34 34 35 35 35 36 36 36 36 36 37
ProGrabit Kit – Damaged Screw Remover  PIPE AND CONDUIT BENDING  Hoppy Bender – Conduit Pipe Bender  Pipe Viper – Cold PVC Pipe Bender  PVC Bend-It.  LEVELS AND TESTERS  Laser Plumb Bob  Straight Shot Level  Jet level  Plug Master Circuit Tester  Circuit Siren  AC Sensors  CONNECTORS, ETC  Cable Protection Systems  Racky Strap – Utility Strap  Handi Hoop  Stud Buddies – Steel Stud Bushings  KOK Series – 1/2" to 2" Plastic Knock Out Fillers  Level Jack – Low Voltage Datacom Mud Ring	31 32 33 33 34 34 35 35 35 36 36 36 37 37
ProGrabit Kit – Damaged Screw Remover  PIPE AND CONDUIT BENDING  Hoppy Bender – Conduit Pipe Bender  Pipe Viper – Cold PVC Pipe Bender  PVC Bend-It  LEVELS AND TESTERS  Laser Plumb Bob  Straight Shot Level  Jet level  Plug Master Circuit Tester  Circuit Siren  AC Sensors  CONNECTORS, ETC  Cable Protection Systems  Racky Strap – Utility Strap  Handi Hoop  Stud Buddies – Steel Stud Bushings  KOK Series – 1/2" to 2" Plastic Knock Out Fillers  Level Jack – Low Voltage Datacom Mud Ring  Rapid Fire Connectors – 1/2" & 3/4"	31 32 33 33 34 34 35 35 35 36 36 36 36 37 37
ProGrabit Kit – Damaged Screw Remover  PIPE AND CONDUIT BENDING  Hoppy Bender – Conduit Pipe Bender  Pipe Viper – Cold PVC Pipe Bender  PVC Bend-It  LEVELS AND TESTERS  Laser Plumb Bob  Straight Shot Level  Jet level  Plug Master Circuit Tester  Circuit Siren  AC Sensors  CONNECTORS, ETC  Cable Protection Systems  Racky Strap – Utility Strap  Handi Hoop  Stud Buddies – Steel Stud Bushings  KOK Series – 1/2" to 2" Plastic Knock Out Fillers  Level Jack – Low Voltage Datacom Mud Ring  Rapid Fire Connectors – 1/2" & 3/4"  Tom Two Way 1/2" Connectors	31 32 33 33 34 34 35 35 35 36 36 36 37 37
ProGrabit Kit – Damaged Screw Remover  PIPE AND CONDUIT BENDING  Hoppy Bender – Conduit Pipe Bender  Pipe Viper – Cold PVC Pipe Bender  PVC Bend-It  LEVELS AND TESTERS  Laser Plumb Bob  Straight Shot Level  Jet level  Plug Master Circuit Tester  Circuit Siren  AC Sensors  CONNECTORS, ETC  Cable Protection Systems  Racky Strap – Utility Strap  Handi Hoop  Stud Buddies – Steel Stud Bushings  KOK Series – 1/2" to 2" Plastic Knock Out Fillers  Level Jack – Low Voltage Datacom Mud Ring  Rapid Fire Connectors – 1/2" & 3/4"  Tom Two Way 1/2" Connectors  SCREWS AND OTHER FASTENERS	31 32 33 33 34 34 35 35 35 36 36 36 36 37 37 37
ProGrabit Kit – Damaged Screw Remover  PIPE AND CONDUIT BENDING  Hoppy Bender – Conduit Pipe Bender  Pipe Viper – Cold PVC Pipe Bender  PVC Bend-It  LEVELS AND TESTERS  Laser Plumb Bob  Straight Shot Level  Jet level  Plug Master Circuit Tester  Circuit Siren  AC Sensors  CONNECTORS, ETC  Cable Protection Systems  Racky Strap – Utility Strap  Handi Hoop  Stud Buddies – Steel Stud Bushings  KOK Series – 1/2" to 2" Plastic Knock Out Fillers  Level Jack – Low Voltage Datacom Mud Ring  Rapid Fire Connectors – 1/2" & 3/4"  Tom Two Way 1/2" Connectors	31 32 33 33 34 34 35 35 35 36 36 36 36 37 37

THE RACK-A-TIERS WIRE DISPENSER IS THE ONE TOOL THAT DOES IT ALL. IT'S NO SURPRISE THAT WE'VE SOLD HUNDREDS OF THOUSANDS OF THEM TO ELECTRICIANS EVERYWHERE. THIS TOOL IS VERSATILE, WATERPROOF, RUSTPROOF, RUGGED, AND VERY RELIABLE. IT EVEN **LOCKS TOGETHER TO MAKE A COMFORTABLE SEAT!** 

- WIRE PULLING
- CADDY
- PIPE VISE
- SEAT
- SAW HORSE - WORKBENCH
- PORTABLE
- VERSATILE
- RELIABLE
- RUGGED
- INTERLOCKING PAIRS
- EASY TO USE







"Turn your Rack-A-Tiers into a Pipe Vise"

Light **Fast** Simple Inexpensive





Part# 10455

NOTE: REQUIRES PIPE WRENCH 18" RIDGID® or equivalent fit. (not supplied)

## F-Z ROLL Wire Reck

The ultra compact/collapsible wheeled wire dispenser!

When you're ready to pull wire, wheel the e-z roll into position and dispense wire directly from your pipe bender or 1" EMT.



#### Features:

- Rigid Steel Construction
- · Light-weight Design
- Durable 'Caution Yellow' Finish
- · Compact (fits in any job box)
- 150 lb. Load Tested
- Holds Reels up to 18"



Collapsible for easy storage & handling






#### Ever had a jack-stand kick out on you?

An accident like that can cost you a lot of time, and towing a clunky reel trailer behind your vehicle is no faster! Why risk it? Simply attach the Tug-Wise to the base of your reel and be ready to pull cable instantly.

Part# **11931** - Standard Part# **11932** - Deluxe



#### Standard Model

#### Features:

- Size: 15" x 15"
- · Handles up to 1000 lbs reels
- · Works with wooden and plastic reels






#### Features:

- Size: 21.5" x 21.5"
- · Handles up to 2000 lbs reels
- · Made of 3/8" thick aluminum alloy
- · Built to handle anything



#### 3 Easy Steps:

- · Screw to base of reel.
- · Flip reel over.
- Pull Wire!



- Constructed of rugged 1" steel tubing.
- Both are 43" tall with 7" rubber wheels.
- · Both can accommodate spools up to 16" wide on solid steel 1/2" axles.
- · Cable Caddy features 6 axle positions for unlimited versatility.
- · Cable Truck has 4 axle positions and a solid steel plate for transporting material.

Part# CT1100 Cable Truck



Part# CC1200 Cable Caddy

#### **Cable Dolly**

· Cable Dolly features 8-12" wide spindles to accommodate a wide assortment of reel sizes. Durable locking casters are rated up to 1200 lb.

#### Part# CD3000

Made to order

 Cable Dolly Jr. features 4–12" wide spindles. Extensions also available.

Part# CD3100 (Not Shown)

· 8 piece spindle extension set with tube connectors. (17" extensions)

Part# CD3000-EXT





#### **Cable Carts**

- · Comes with interchangeable 1" and 3/4" axles.
- Holds up to 30 spools of THHN.
- Vertical racks swing forward for easy loading.
- Space for plywood work table on top.

Dimensions: 43"H x 41 1/2"L x 28"W

Shipping weight: 150 lbs.

Part# CC2000 Cable Cart Made to order





Part# CC2000D Cable Cart - Data Made to order



Part# 13355

#### Made of solid steel! Features:

- · Weight: 3.9 lbs.
- · Holds several lumber sizes including but not limited to: 1"x2", 2"x4", 2"x6" and 4"x4"
- Includes 12" Ruler



#### Common features:

#### Lifts material for easy:

- Cutting
- Drilling
- Measuring
- And Tightening




- Plastic & Metal Pipe
- · Conduit, Unistrut, Rebar
- Lumber & Dowels
- · And Much More!



#### Features:

- · Weight: 14.5 lbs. each
- As a set can hold 1" to 6" conduit, up to 36" wire spools and up to 1,000 lbs.







#### Standard features:

- · Self-lubricating Roller Bearings no grease required
- Quick-action lock washer for fast positioning
- · Fall Guard feature to reduce pinching
- One-bolt disassembly no welding required for service



#### REEL MAC 60

Screw type telescoping reel jack for 26-56" diameter reels.



#### REEL MAC 80

Heavy duty ratchet drive reel jack for reels up to 90" in diameter. Convenient, detachable ratchet handle stores in base when not in use.



REEL MAC SPINDLES Used with Reel Mac reel jacks. (Sold separately)

REEL MAC & JACK-A-TIER							
Description	Part No.	Reel Diameter	Capacity	Weight			
Reel Mac #60	11860	26-56"	2500lb.	27 b.			
Reel Mac #70	11870	46-96"	2500lb.	46 b.			
Reel Mac #80	11880	up to 90"	3750lb.	99 b.			
Jack-A-Tiers #75	11875	46-92"	2500lb.	34 b.			

Corresponding SPINDLES						
Description	Part No.	Dimensions	Capacity	Weight		
#61	11861	2 3/8" x 62"	5000lb.	39lb.		
#71	11871	2 3/8" x 76"	5000lb.	47lb.		
#81	11881	3 1/2" x 100"	7500lb.	119 b.		
#71	11871	2 3/8" x 76"	5000lb.	47lb.		

KEEPS SPINDLES
SECURELY IN PLACE

Use these charts to select the right Reel Mac, Jack-A-Tiers or spindle for your needs.

# RATCHET REEL MAC Ratchet design allows for easy lifting 2,500 lbs. capacity each 17.5" to 28" lifting range up to 55" diameter reels Designed for use with #350 & #500 wire reels Patent-pending safety head Use with Reel Mac Spindles Part# 11885

Weight: 28 lb/12.7 Kg

## 

#### Caddy Mac features:

- · Accommodate wide range of spool sizes.
- Wire guides for smooth feeding from the spool.
- · Patented spindle locking system spindles stay put during transportation.
- 1/4" solid spindles are attached to Caddy Mac cart... no loose pieces.
- Spindles swing out to set position for convenient loading of wire spools.
- Spindles can be easily removed for the occasional use of larger spools.
- · Spindles store in special loops... will not fall out even during transportation.
- · Large 10" wheels

#### MAC RACK 1



- 1,000 lb load capacity
- · Eight bins of storage
- · Arms fold easily with plunger release

Part# 11917



#### CADDY MAC #1 Part# 11901

Number of Spools	Max Spool Dia.	Load Capacity	Weight	Width	Additional Features
8-#10 awg. or 12-#12 awg.	7.5 in 19 cm	200 b. 90 kg.	50 lb. 23 kg.	26 in 66 cm	Transports spools on spindles and works as a dolly. Wire is dispensed while laying flat.



#### CADDY MAC #2

Part# 11902

Number of Spools	Max Spool Dia	<b>Load Capacity</b>	Weight	Width	Additional Features
16-#10 awg. or	7.5 in	400 lb.	64 b.	26 in	Folds up for compact storage
24-#12 awg.	19 cm	180 Kg.	29 kg.	66 cm	

#### **CADDY MAC #4** Part# 11904

Capacity	Weight	Width	Additional Features
6-500' spools - 8" diameter	67 lb.	27 in	A large capacity cart, dispenses wire while laying flat.
6-2,500' spools - 16" diameter	30.5 kg.	69 cm	



#### Spool Mac A REEL TRANSPORTER

Part# 11900

						MOI MOI
	Max Reel Width	Max Spool Dia.	Reel Capacity	Weight	Width	Additional Features
	25 in 63.5 cm	40 in 101 cm	350 lb. 160 kg.	80 lb. 36.4 kg.	31.5 in 80 cm	All steel frame, easy set-up for cable dispensing. Compact storage.

## **COPPER WIRE STRIPPER**

#### **RECOVER COPPER WIRE & ALUMINUM QUICKLY** AND EASILY WITH THESE MONEY MAKING MACHINES



#### Model CWS-2

#### Part# 47200

- All aluminum frame
- Strips 14 500 AWG
- Strip solid core or stranded wire
- Hardened one piece blade
- Blade made from tool steel
- 1/2 HP motor with 56c frame
- Blade easily re-sharpened
- Fully adjustable wire guide
- Strips 120 feet per minute
- Bench model Anti-slip base

#### Model CWS-1

#### Part# 47100

- All aluminum frame
- Strips wire from 14AWG 3"
- Strips NMSC cable 10 14 AWG
- Strip solid core or stranded wire
- Hardened one piece blade
- Blade made from tool steel
- 3/4 HP motor with 56c frame
- Blade easily re-sharpened
- Fully adjustable wire guide
- Strips 120 feet per minute
- Bench model Anti-slip base

Made in Canada

## EasyStripper

Strip the cover off your scrap wire in minutes with the Easy Stripper! Increase your earnings on every single job you complete.

Don't return your copper wire with the cover still on. Remove the cover in minutes with the Easy Stripper and get 300% more money for your scrap wire. It's that simple!

- Less than 10% the price of a standard motorized wire stripper
- Powered by any normal power drill
- Get 300% more money for returning your wire uncovered
- Way EASIER and FASTER than using your knife!
- Environmentally friendly no burning required

Tired of burning the rubber off your copper wire just for a few extra bucks? It makes a mess, but more importantly, it hurts the environment. Don't be that guy - use the Easy Stripper to strip your wire in seconds and get MORE MONEY for returning scrap wire!



HE MAKE ALL THE MONEYS



Part# 47020 Blade Part# 47020B



## WIRE MANAGEMENT TOOLS

Save your fingertips!





#### Features:

- Light weight
- · Fits in pouches
- Swivelling handle Fits in pockets
- Folds up easy
   Holds up to 200 lbs

Part# **56000** 





Part #-Blue/Gray

Part #-Red/Yellow

Part #-Orange/Blue

Box of 50 #KI68310

Box of 100 #KI68210 Canister of 300 #KI68230 Canister of 500 #KI68250

Box of 100 #KI68110







#### Filled Connectors for Outdoor Use

Selling Unit Wire Range

2110	Card of 6	22 — 12	Filled Connectors for Direct Bury Use			
2125	Bag of 25	22 — 12	Part #		Wire Range	
2210	Card of 5	22 — 8	10600	Card of 2	22 — 8	
25	Bag of 20	22 — 8	10666		22 — 8	
0	Card of 3	14 — 6	10999	Bag of 8	14 — 6	
335	Bag of 50	14 — 6	10444	J	18 — 12	
			10555	Bag of 10	14 —10	

#### TRY THESE TOOLS WHEN YOU NEED AN EXTRA PAIR OF HANDS PULLING WIRE!



'Shoehorns for your wire!'

- · Reduces Time and Labour
- · Reduces the chance of damaging wires
- · Turns wire pulling into a one person job
- · Why not protect the conductors on all your pulls?

Three Sizes Available: 1/2" 3/4" 1"


Part# 42050-1/2"

Part# 42075-3/4"

Part# 42100-1"

Part# 42000-Multi-Pack





11








- · Can pull most ropes and fish tapes
- · Pull more efficiently, faster & safer
- Saves an average of 30 minutes based on a 75' pull
- Use both hands ergonomically for maximum pulling strength without the pain


Part# 42400



Time is money and when you thin it, a lot of time is spent stripping, taping and untaping wire for fishtape pulls. The SNATCH STRAP gives you back this time. By staggering the wire, you can pull more conductors with less effort. Plus SNATCH STRAPS can be daisy chained; you can easily drop wire groups at boxes along the pull. Color coded for easy circuit and phase identification.

Part# **69455** 





No stripping or taping required









#### The powerful new way to pull wire without breaking a sweat!

Power Pull-it is a compact and portable wire pulling device that utilizes your cordless drill to efficiently pull wire, and dramatically reduce hand-pulling fatigue and injuries. Just attach the pull line to your drill, and let it do all the work for you. Made in the USA, Power Pull-it's sturdy construction includes a precision bearing assembly, and requires no anchors. Includes a spare line sleeve and tool pouch.

- Saves on labor costs
- Precision bearing assembly
- Sturdy construction
- No anchors required
- Reduces pulling fatigue and hand injuries







EXTREMELY POWERFUL, YET DELICATE, MAGNETIC WIRE SNAKE FOR FISHING WIRE THROUGH WALLS. IT EVEN WORKS THROUGH INSULATION! THIS NEW VERSION HAS A MUCH STRONGER MAGNET AND A SMOOTHER ROLLING SURFACE.



#### **FEATURES**

- Hand roller with powerful magnet and smooth finish to avoid damaging walls
- 10' ball chain included
- Flexible leader with magnet head
- Also makes a great stud finder

#### Mfg Note

Any fiber fish can easily be threaded onto the magnet head. This will help push through dense insulation and guide through fire-block drill holes.

Part# 42800

#### THE NEW MAGNESPOT HAS ARRIVED!



The Magnespot is a reference point locator that gives users complete self-assurance before drilling, cutting, or any other task you may previously had to do blindly.

Place the Magnespot Transmitter on the wall, ceiling, or floor that you need to drill. On the other side hold the Receiver in the general direction of the Transmitter, the red LED arrows on the Receiver will indicate to you which direction to move. When all 4 Arrows illuminate, the Transmitter and Receiver are lined up within a ½ inch.

#### Specifications:

- Maximum Distance: 48" / 4'
- Receiver Accuracy: 1/2" @ 18"
- Transmitter Battery Type: 9V Alkaline (included)
- Receiver Battery Type: 9V Alkaline (included)

Part# 42900

#### Stop getting caught up in insulation or other obstacles!



## FLEX PULLER

FLEXIBLE METAL
CONDUIT PULLING TOOL
EASILY SCREWS ONTO
EXTERIOR OF MC CABLE
AND PROVIDES A HOOK
TO PULL CABLE.

Can be used on #14, #12, & #10 MC Cable!

Part# 42620

## CONEHEADS

Easy way to pull flexible conduit. Simply thread into interior of flexible conduit, hook onto your string or fish tape and pull!







Part# **42600** Kit includes 1 each for 1/2" & 3/4" Flex



This CO2 powered gun broots a roam dart with a line attached to it up to 200 it.

Stop climbing your ladder and moving it every ten feet to pull your wire across a

T-Bar ceiling. Pull your wire the entire distance in one shot with the Laserline!

Tired of wiggling through a crawl space just to drag your wire to the other end? F


he Laserline, attach your wire, then walk around and pull it across while standing

It's that easy!

You don't even have to recoil the line. Each spool has 1200 ft of line, so you just cut it after each shot and re-attach the dart. Then just load in a new spool when you need it. CO2 cartridges are also replaceable and inexpensive!


Get the job done faster and have some fun – get the Laserline!

Laserline Kit - Part# **83000**Replacement Line 2 (1200ft) - Part# **83001**Dart 3 Pack - Part# **83003** 



#### CALNUCCADON UNA CINAPINANI IN

We've re-engineered the attachments to fit both the 3/16" rods and the 5/32" rods. They will still be compatible with all existing parts in the field, and the cost remains the same.



FishHook - Use to retrieve or snag wire & cable.

Directional Tool - Offset bend helps guide the Fiberfish around obstructions in walls. Magnet Head - Used with Fish Finder or to catch the ball chain inside wall cavities. Pull Ring - Used to attach multiple wires for larger pulls.

Ball Chain -Attach to Fiberfish for interior wall pulls — can be retrieved through small access hole in wall with magnet or Flex-Fish.

Wisp Head - Use over suspended ceilings — won't catch on T-bars.

Screw Tip - Screw into the end of small communication wires for faster and easier pulls.

Contains: FishHook, Directional Tool, Magnet Head, Pull Ring, Ball Chain, and 2 replacement tips. Stored in convenient vinyl pouch.



FIB120 Fiberfish Attachment Kit (1/4" rods) FIB520 Universal Attachment Kit for ALL (3/16" rods) & (5/32" rods)

#### **Master Attachment Kit**

Contains same as above plus: Wisp Head, Screw Tip, Flex-Fish



FIB140 Fiberfish Master Attachment Kit (1/4" rods) FIB540 Universal Master Attachment Kit for ALL (3/16" rods) & (5/32" rods)



JO ALE LICO HAIHIADIL

- 20' Fiberglass Telepole
- Attachment Kit
- Carry Case



#### **Contractor Pack**

#### Contains:

- F berfish II Kit
- 1/2"x72" Auger Piranhabit
- 3/8"x72" HSS Piranhabit
- 20' Fiberglass Telepole
- Attachment Kit
- Wisp Head
- Flex Fish
- Steering Guide
- 1" Auger Bit
- Carry Case







#### THE *MOST INNOVATIVE* TOOL BELTS & BAGS ON THE MARKET



#### PART#

SMALL COMBO - 43421 MEDIUM COMBO - 43242

LARGE COMBO - 43243 X-LARGE COMBO - 43244

XX-LARGE COMBO - 43245 XXX-LARGE COMBO - 43246

SMALL BELT - 43401

MEDIUM BELT - 43402 LARGE BELT - 43403 X-LARGE BELT - 43404

XX-LARGE BELT - 43409 XXX-LARGE BELT - 43410

ELECTRICIAN'S TOOL POUCH - 43201 LARGE 9 POCKET TOOL POUCH - 43202

#### INCLUDES:

Molded Support Belt, Electrician's Tool Pouch, Large 9 Pocket Tool **Pouch, Hammer Holster and Tape Holder** 

#### FEATURES:

- Reinforced with bar-tack stitching and heavy duty metal rivets
- 1250 denier DuraTek fabric with high density nylon webbing around pocket openings.



#### FEATURES:

- The first ever 'Molded Air-Channel Tool Belt' that offers incredible comfort, support, and ventilation for your back.
- The high density nylon 'Web Core' inside the padded belt provides strength to stitching and stress points.
- Metal rings are stitched to the belt's web core with high-density nylon webbing that provides the strongest way possible to attach suspenders.
- All stress points are reinforced with 'bar-tack' stitching along with heavy duty rivets.
- Double metal buckles that add strength and dependability.
- All of our belts and bags are made from double layered 1250 denier DuraTek fabric.
- Available in sizes from 26" to 54"





Our popular padded suspenders easily clip onto the - Adjustable Thick Molded Foam Shoulder Pads sturdy metal rings that are built into our tool belts. The padded shoulder straps make these the ideal set of suspenders for your tool belt rig.

- 2" Wide Adjustable Nylon Straps
- Leather Crossover Divider
- Heavy Duty Spring Hooks that attach to the rings on the **Molded Air-Channel Belts**

#### **Pocket Tool Holder**

#### Features:

- Quick to put on AND COMFORTABLE!
- · These tool pouches fit in your pocket
- · Made of ballistic nylon
- · Lightweight & durable

Mini - Part# **43015** Grande - Part# **43095** Driller - Part# **43110** 

Mini





No belt required!

Driller

#### Small 25 Pocket Tray Tool Carrier

#### Features:

- 14 exterior pockets (5 with velcro closures)
- 14 interior compartments & pockets
- 1 7" x 5 1/2" twelve-compartment plastic tray
- 1 large exterior zip-top pocket
- 1 measuring tape clip
- · Includes shoulder strap

Part# 43707



#### Large 44 Pocket Tray Tool Carrier

#### Features:

- 29 exterior pockets (3 with velcro closures. 1 large clear pocket with velcro closure)
- 16 interior compartments and pockets
- 2 7" x 5 1/2" twelve-compartment plastic trays
- · Includes shoulder strap

Part# 43706

## PROFESSIONAL QUALITY ORGANIZATION

A new revolutionary tool box




- No mixing between drawer compartments
- Extremely strong
- Easy to operate
- Made in USA

Part# 66536 - Yellow/Black



TOOL BAGS AND OTHER STUFF 2



**FEATURES** 

OF CABLE STAPLE.

- MADE OF HARDENED STEEL.
- DOUBLES AS AN 8 INCH RULER
- INCLUDES A HANDY NAIL PULLER AND PRY BAR FOR MULTIPURPOSE USE.

EASY STAPLE PULLING FOR ANY SIZE

PART# 52455

Pencil

Bigg Lugg I

The original cordless drill holder.

Part# 43001

#### Bigg Lugg II

The next generation for personal tool carriers designed for cordless drills, air-nailers, paint cans, etc. (limit 10 lbs)

Part# 43002

#### **MEASURING TAPE**

- Easy one-person pipe measuring
- Non-slip end hook
- Three stop buttons
- Sturdy casing







1" Wide 25' Long



Show up your buddies on the job site with your Rack-A-Tiers branded carpenter's pencil. They do the job and look great.

Part# 52466

#### Hammer

You asked us and we delivered. Finally, a solid hammer available at a decent price. Don't break the bank on your hammer, buy it from us! Part# 52477

#### Felt Marker

Complete your tool kit with a black felt marker from Rack-A-Tiers. These things come in handy and ours won't run dry on you! Part# 52488

## TOOL BAGS AND OTHER STUFF





- · Needle nose tips
- NMSC stripper at the "nose" where it is easier to use inside boxes
- Strips conductor sizes from #10 down to #22 AWG (for telephone wire)
- Large cutting blades for easy general purpose cuts
- Barrel sleeve crimper near the pivot
- Ergonomic "hourglass" shaped handles for comfort & speed
- Glow-in-the-dark handles

Part# 47000



ATTACHABLE PRECISION WIRE STRIPPE



- · A new way to strip NMSC cable
- Easily attaches to most wire strippers
- Strips cable in or out of electric boxes with push action
- Virtually eliminates nicking or cutting the wire insulator

Part# 47010



#### BEND ALL Cable Bender



Finally! The amazing knuckle saver from Rack-A-Tiers®

- Captures wire
- · Bend inside enclosures to the right or left
- · Bend to the front or back
- · Your feeders will lie in the lugs

#### Part# 77455

Machined from 6061 aircraft aluminum Fits a standard 1/2" ratchet. Fits #3 to 500 MCM conductors

Ever give a meter base a knuckle sandwich? Too bad it was your own. Next time, defend yourself with the Bend All. Perfectly sized for 4/0, it takes the pain out of 200 amp services or sub feeders and conductors like it too. The Bend All makes micro adjustable bends without brutalizing the wire.







#### RACKSY PAD KNEE PADS

WITH GEL IMPLANTS



Save your knees, you'll need them later!

Sturdy and so comfortable, you'll actually wear them. Velcro/elastic straps make these knee pads easy to pu on and take off.

Part# 66455


So comfortable, you is never want to get up.






Kit Includes: 6 pairs of booties, 4 pairs of nitrile gloves 4 pairs of vinyl gloves and a 3-N95 Respirator

Booty Kit: Part# 47099 Booties only sold separately: Part# 47099B Bag of Booties (6 Pairs): Part# 47099BB



## Bolt Template

41 Templates in One! Quick and Easy! Reusable! Set-Up in Minutes! Weather Resistant ABS Plastic.



Select a hole saw that measures about 1/8" larger than the bolt to be used and drill the template at the selected easy centering divot mark.

Part# 67441

For setting poles 8" - 24





#### **Panel Buddy Knockout Kit**

#### Tired of trying to remove knockouts?

- · Kit removes knockouts on Electrical, Security, Alarm and Datacom Panels
- Works with lipped and unlipped panels.

Part# **7WBK100** 







#### P.S. Knight Electrical Code Books

#### \*over 750,000 copies sold

The industry's most comprehensive publication Based on the 22nd Edition of the Canadian Electrical Code on Canadian electrical code clarifies the New Code Rules.

- Now over 1000 pages
- Over 1000 code rules & revisions. clearly explained & indexed
- 1000 Detailed illustrations & calculations
- Code tables & practice exam
- 400 questions & answers added

#### Commercial & Industrial Book 2

For the Professional Electrician By P. S. Knight




Clarity - These books are clear and to the point. Easy to understand explanations replace official jargon. Part #73129 - Electrical Code Simplified

#73110 - B.C. #73111- Alta., Sask., Man., NB. NS. Nfld.

#73115 - Ontario

Canadian product produced by a Canadian for use by Canadians.



#### **DEWALT Reference Books**

#### Electrical **Trade Series**



On the job pocket reference books offer easy to read charts & detailed illustrations. The 4" x 6" size fits easily in a toolbox or pocket. Each book features over 350 pages of complete reference material.

Professional Reference Books Part #'s

73200-Electrical

73205-Wiring Diagrams

73203-Lighting & Maintenance

73208-Electrical Estimating

73201-Datacom

73204-Electric Motor

73210-Security, Sound & Video

#### Electrical Licensing Part# 73206


Based on the 2011 International Code®

Subjects include methods to improve test scores, strategies to prepare, study aids and tips, examination regulations, formulas and references, realistic sample exams, and answer keys with corresponding NEC® references.

#### Electrical Code Reference Part# 73207

Based on the 2011 International Code®

Illustrates hundreds of the most common code requirements, violations and installation concerns including: materials, notching and cutting, commercial hoods, combustion air openings, access and clearances, duct construction, mechanical ventilation.





## Owik Lok

▶ The CLICK you can Trust

ARANTEES EXTENSION CORDS AND TOOLS ARE CKED TOGETHER. IT IS THE TOUGHEST, STRONGEST, ST RELIABLE. 120V - 15A CONNECTOR.







Tired of this?

- Qwik-Lok is the 'Must-Have' locking retro-fit /replacement connector for extension cords
- An outstanding end that eliminates tied, frayed, burned out or ruined cords and connectors
- · Works with common 2 or 3 pronged plugs
- · Eliminates need for 'twist-lock' devices
- Delivers consistent, reliable power at all times for demanding industries & trades

Part# 97008



## The Ultimate Ground Rod Driving Tool

SLUGGO- $OX^{TM}$  is the revolutionary new tool that's taking the industry by storm.

#### Features:

- Incredibly strong, made of 3" hot-rolled, heat-treated, hardened steel
- 3 1/2" bore to accept 3/4" and 5/8" ground rods
- 80% more striking surface
- One piece, light-weight (7lbs.)
- Yellow zinc chromate surface to deter rust



"YOUR TURN TO HOLD THE GROUND ROD. ROD, I THINK IT'S TIME WE GOT A 'SLUGGO-OX'!"





Conduit Tracking System

- Tracks conduits in minutes.
- Works in unobstructed 1/2" to 6" EMT, Rigid, or Plastic pipes to well over 300 feet.
- Finds pipe ends that would be impossible to locate by the old "stuff the fish down the pipe" method.



## **Nut Blaster**

The Nut Blaster Universal Wire Connector Tools

#### **FEATURES**

- Fast, Easy Installation
- Prevents sore fingers and cramping hands
- Fits all brands, red, grey & blue



## BREAKER + LOK



LOCK YOUR BREAKER IN THE ON OR OFF POSITION WITH THE **BREAKER LOK** 

#### **Features**

- The only breaker lock you need
- Fits most manufacturer's breakers
- Also works on standard toggle switches

Part# 75000



#### We've Got the Hole Thing Covered!

Brick, Fiberglass, Plywood, Plastic, Roofing, Tile, Mdf Fibre Cement Board, Laminates, Osb, Concrete Block, Aluminum, Steel, Stainless Steel, Hardie Board, Stucco, Sheetrock, Hard Woods, Soft Woods, Slate, Nonferrous Metals, Sheet Metal and...

Well, you get the picture!

#### **Mega TCT Hole Saws**

- · Cut wood, sheetrock, fiber cement board, plaster, fiberglass, OSB, chipboard, MDF, and other tough materials.
- Tough Tungsten Carbide teeth extend past inside and outside walls for reduced friction and much faster cutting.
- · Large side gullet slots for fast chip removal and fast plug removal
- · Ultra Deep 2" cutting depth
- · Use with standard hole saw arbors
- · Cuts through nails.


Part#	Size
91613	1-1/8"
91615	1-3/8"
91617	1-5/8"
91619	1-7/8"
91621	2-1/16"
91622	2-1/8"
91625	2-9/16"
91627	2-3/4"
91629	3-1/8"
91630	3-3/8"
91632	3-5/8"
91633	4"



#### **Heavy Duty TCT Masonry Hole Saws**

- Engineered for fast cutting through stucco or FRP / fiberglass as well as metal lath and plywood.
- · Cuts through heavy duty brick and cinderblock.
- All hole cutters have a 2-3/8" cutting depth.
- · Perfect for use with 18 volt hand drills to cut holes up to 4-1/4" diameter.

Part#	Size
91412	1-1/4"
91414	1-1/2"
91416	1-3/4"
91417	2"
91419	2-1/4"
91420	2-1/2"
91421	2-5/8"
91422	3"
91434	3-1/2"
91424	4"
91426	4-1/4"



#### **Carbide Tipped Steel Cutters**

#### WE HAVE HIGH END AND LOW END CUTTERS

- · Ejector spring
- · Tapered center drill
- 5/8" up to 5 1/2"





Part# 93000 Series

Part# 92000 Series

#### IF YOU ARE TIRED OF HOLE CUTTERS THAT DON'T CUT IT, CALL US FOR INFORMATION ON OUR GERMAN QUALITY HOLE CUTTERS.

#### Multi Bit (Step Drills)

Hardened stepped Bits for clean cuts in sheet metal, electrical boxes, arborite, etc. Handy for creating knockouts.

MLT1 1/8" - 1/2" 13 step
MLT3 1/4" - 3/4" 9 step
MLT4 3/16" - 7/8" 12 step
MLT5 7/16" - 1 1/8" 12 step
MLT 7 1/4" - 1 1/2" 11 step



Available in 1/8" to 1 1/2" sizes

Never get caught in a drilling extension jam again!

## The Javelin™


ALL-IN-ONE DRILLING EXTENSION

HOLDS HOLE SAWS, SPADE BITS, SCREW TIP HOLDERS, NUT DRIVERS AND ANY OTHER TOOL WITH A 1/4" HEX SHANK.

- Cut 3/8"-16 threaded rod to desired length
- Fits any tool with 1/4" hex shaft
- · Fits in all standard drill chucks
- · Can be extended by using 3/8" rod couplings
- · Hole saw arbor also included

Part# **95000**Pat# 7,802,948







**ACKAGE INCLUDES:** 





3/8"-16 Threaded Rod (6" Length & 1-1/4" Length)



NOT ALL HOLE CUTTERS ARE EQUAL! LET US FIND THE RIGHT ONE FOR YOU.











## BUMPER BALLS

These balls will keep your bits centered!





**AFTER** 

#### NO MORE...

- Bit walking
- Nail hitting
- Wall patching
- Carpet

Fits all 3/16" shaft auger bits

Kit includes 1 each of 1 3/4" & 2 1/4" Balls

Part# **BB3412** 

#### **PIRANHABITS**

Piranhabits have 3/16" flexible shafts so they can bend while rotating. This allows drilling inside wall cavities, through box cut-outs or through other small openings.

#### **Quattro Flex Auger Bits**

Fast and aggressive self feed auger bits, welded to a flexible shaft. Cuts clean holes. Crossbored at both ends for easy wire pulling. Use for wood only.

QTT3824	3/8"x24"	Auger flexbit
QTT3836	3/8"x36"	Auger flexbit
QTT3848	3/8"x48"	Auger flexbit
QTT3854	3/8"x54"	Auger flexbit
QTT3872	3/8"x72"	Auger flexbit
QTT1224	1/2"x24"	Auger flexbit
QTT1236	1/2"x36"	Auger flexbit
QTT1248	1/2"x48"	Auger flexbit
QTT1254	1/2"x54"	Auger flexbit
QTT1272	1/2"x72"	Auger flexbit
QTT91624	9/16"x24"	Auger flexbit
QTT91636	9/16"x36"	Auger flexbit
QTT91648	9/16"x48"	Auger flexbit
QTT91654	9/16"x54"	Auger flexbit
QTT91672	9/16"x72"	Auger flexbit
QTT3424	3/4"x24"	Auger flexbit
QTT3436	3/4"x36"	Auger flexbit
QTT3448	3/4"x48"	Auger flexbit
QTT3454	3/4"x54"	Auger flexbit
QTT3472	3/4"x72"	Auger flexbit

More sizes available

#### **High Speed Steel**

Superior quality M-2 High Speed Steel drill bit, welded to a flexible shaft. Cuts both metal and wood. No need to worry about hidden nails or metal studs when drilling.

FLX1424	1/4"x24"	HSS Flexbit
FLX1436	1/4"x36"	HSS Flexbit
FLX1448	1/4"x48"	HSS Flexbit
FLX1454	1/4"x54"	HSS Flexbit
FLX1472	1/4"x72"	HSS Flexbit
FLX3824	3/8"x24"	HSS Flexbit
FLX3836	3/8"x36"	HSS Flexbit
FLX3848	3/8"x48"	HSS Flexbit
FLX3854	3/8"x54"	HSS Flexbit
FLX3872	3/8"x72"	HSS Flexbit
FLX1224	1/2"x24"	HSS Flexbit
FLX1236	1/2"x36"	HSS Flexbit
FLX1248	1/2"x48"	HSS Flexbit
FLX1254	1/2"x54"	HSS Flexbit
FLX1272	1/2"x72"	HSS Flexbit



Allows the Piranhabits to bend for drilling from outside the wall cavity.



#### **NEW SWITCH BIT LINE!**

Rack-A-Tiers is proud to announce our newest line of flexible installer bits, The Switch Bit Line. Now you can quickly customize your set with these flexible installer bits with interchangeable heads and various shank lengths for any job.

#### CROSSBORED THROUGH SHAFT TO ALLOW WIRE PULLING!

ET31621	Single Shank	3/16"	21"
ET31633	Single Shank	3/16"	33"
ET31651	Single Shank	3/16"	51"
ET31669	Single Shank	3/16"	69"
ET1415	Single Shank	1/4"	15"
ET1421	Single Shank	1/4"	21"
ET1433	Single Shank	1/4"	33"
ET1451	Single Shank	1/4"	51"
ET1469	Single Shank	1/4"	69"



#### Auger Bit File

THE BEST FILE FOR AUGERS IS BACK!

This file is specially designed to prevent damage to surfaces next to those being filed. One end has safe (uncut) edges and the other end has safe sides. Perfect for sharpening auger bits.



#### Flex Bit Extensions

Flexible Extensions provide more reach and feature dual set screws for extra strong hold. Use the 1/4" Extensions for the 3/4" Auger Piranhabits

FIBEX48 3/16" x 48" Extension
FIBEX54 3/16" x 54" Extension
FIBEX72 3/16" x 72" Extension
FIBEX1448 1/4" x 48" Extension for 3/4" bits
FIBEX1454 1/4" x 54" Extension for 3/4" bits
FIBEX1472 1/4" x 72" Extension for 3/4" bits



DESIGNED FOR BATTERY DRILLS

Part #AW34OD-3/4" x 7" #AW78OD-7/8" x 7"

**Cuts like a knife through butter!** 



## Tired of junk auger bits? Rack-a-Tiers found the star-m brand that has produced quality products for over 80 years for professional trades people.

#### **Nail Chipper Ship Auger**



TRI-CUT design with 3 precision ground edges for fast, smooth cutting without resistance

REDUCES NAILS TO CHIPS without grabbing and leaves a clean hole with minimal "blowout."

#### Standard Ship Auger



- Precision ground cutting edge for fast cutting of clean holes in wood.

Burr-free lead screw for easy starts and pull-through without material build-up.

**NOTHING BUT THE BEST!** 

- Burr-Free Lead Screw
- Light Weight
- Carbon Steel Construction

With precise heat-treat and hardening processes for strength and durability.


#### 18" Auger Bits

AW3818	3/8"
AW1218	1/2"
AW11618	11/16"
AW3418	3/4"
AW7818	7/8"
AW118	1"
AW1418	1 1/4"

#### 7 1/2" Auger Bits

AW3807	3/8"
AW1207	1/2"
AW11607	11/16"
AW3407	3/4"
AW7807	7/8"
AW107	1"

To order Tri-Cut Bits add a 'T' to the Part #'s



"By the way – the electricians are in the crawl space drilling holes for the wiring to the new hot-water tank."



#### **Multi-Function Hole Cutter**

#### Cuts through:

- Plywood
- · Fiber cement board
- Sheetrock
- · Up to 20 GA. sheet metal
- Fiberglass
- Aluminum

Part# **90200**Part# **90300**Part# **90400** 

Compare Features -	→ Other Hole Saw Kits -	HOLE PRO
Adjusts to exact hole size needed	NO Van full of dull hole saws	YES 1 7/8" - 9" 1 7/8" - 12" 1 7/8" - 17
Dust collector shield	NO Lady finds new contractor	YES Clean job
Designed to reduce kickback	<b>NO</b> Jaw breaker	YES Non-Jaw breaker
Economical replaceable blades	NO Sharpen a bunch of little teeth	YES Sharpen only two blades
Price	\$300.00	Less than half No-brainer!!!





Part# 90-VH HSS
Part# 90-VT Carbide

SAVE YOUR LUNGS! CUTTING HOLES WITHOUT PROTECTION CAN BE HAZARDOUS TO YOUR HEALTH. PROTECT YOU & YOUR CREW WITH THE HOLE PRO.

#### **Hole Saw Accessories**

#### **Arbor Extension**



Part# 90105

#### **HOLE SAW DUST SHIELD**

- Has a ABS shield that collects all the dust and shavings when using a hole saw.
- Has a 7 3/4" OD and 6 3/8" ID supporting a hole saw up to 6 1/4" in diameter and up to 2 1/2" cutting depth.
- · Saw and vacuum adapter sold separately
- Requires arbor extension for use.



#### ARBOR HOLE SAW ADAPTER FOR ALL HOLE CUTTER MODELS


- Converts any hole cutters for use with any hole saw
- Unique dual head design allows mounting 1/2"-20" or 5/8"-18" threaded hole saws



#### VACUUM ADAPTER FOR ALL HOLE PRO DUST SHIELDS

- Reusable plug to re-seal shield hole
- Perfect addition to hole-pro shields, power series X & XL models
- Attaches to standard 1" power tool vacuum hose

Part# 90101



#### DRILLER'S Dust Bowl


**HOLE SAW DUST COLLECTOR** 

← Old way

Best way! -

Fits hole saws up to 8"

**NEW IMPROVED WITH NYLON BUSHING** 





#### SAVE THE BALLS FOR THE COURT!

You may enjoy a face full of drywall dust, but your customers might not. The flexible DRILLER'S DUST BOWL compresses against the work surface and traps all dust and debris as you drill. It fits your drill and hole saw without any adjustments. Put an end to 'unprotected hole sawing'.

Part# 48000



Heavy duty, tear resistant, polytuf fabric

#### **COLLAPSIBLE TRASH CONTAINER**

· Featuring an internal support spring that "Springs into Action"

Part# 51000



19" x 24" (open) 1 1/2" x 24" (collapsed)







Who says you're a slob? Clean up your reputation with your own trash can. The Exploding Garbage Can will dazzle your customers, especially if you use it! Pops up and folds flat — ready when needed. You can also take one home for the garden.

## RACKY BITS

**COLOR CODED DRIVE BITS** 

Faster, easier and more efficient bit selection!



#### **ROBERTSON®** IMPACT DRIVER BITS



7011PI Phillips #1 x 1" Short, skinny grey 7012PI Phillips #1 x 2" Long, skinny grey 7021PI Phillips #2 x 1" Short, thick grey 7022PI Phillips #2 x 2" Long, thick grey 7011RI Robertson #1 x 1" Short green

7012RI Robertson #1 x 2" Long green 7021RI Robertson #2 x 1" Short red 7022RI Robertson #2 x 2" Long red 7031RI Robertson #3 x 1" Short black Long black 7032RI Robertson #3 x 2"



**YELLOW** 5/16" Hex Drive **BLUE** 3/8" Hex Drive **BROWN** 7/16" Hex Drive 1/2" Hex Drive **BLACK** Available in: 21/2" & 6" Hex Bits

#### Genuine **ROBERTSON®** Bits

**YELLOW** #0 Square Drive **GREEN** #1 Square Drive #2 Square Drive **RED BLACK** #3 Square Drive #4 Square Drive **ORANGE** 

#### Phillips Bits


#2 Phillips LIGHT BLUE #1 Phillips



1/4" slot #1 square drive #2 square drive




- Ordering Options:
  1. Convenient blister cards
- 2. Bulk qty(s) for display case



#### THE PEG THAT FITS THE HOLE





Part# **72134P 4"** Part# **72136P 6"**  Available in both bulk quantities or packaged blister cards.



- Slim, comfortable and solid
- Corrosion proof magnetic alloy shank
- Legendary instant-bit-change

#### Stubby

- · Solid, comfortable, high torque handle
- · 6 High quality 1.3" length insert bits
- · Ideal for work in close quarters



Part# **P91000** 

#### Dash 7

- 7 2" length, 1/4" Hex Powerbits
- · Comes in 4 bright new colors





Part# **P05001** 

#### **SIXPAC Plus**

- 7 3" length, 1/4" Hex Powerbits
- 11.5" total length

Part# **P88001** 



#### **Industrial Series**



## Damaged Screw Remover

· Works on jagged, uneven and rough breaks

- Self centering tip, no walking
- · Compatible with quick connect chuck systems
- Easy to use with 3/8" variable speed reversible drill
- Extracts screws up to 4 inches

	Screws	Bolts
Grabit #1	No. 4 - No. 6	No. 10 (5mm)
Grabit #2	No. 8 - No. 10	1/4" (6mm)



Rounded out screw heads, what a nightmare! Not anymore. Just drill out the damaged screw / bolt with one end of the Grabit, then flip it over and the "grab end" winds out the screw. MADE IN USA



## HOPPY BENDER

THE HOPPY BENDER IS HANDS DOWN THE MOST INNOVATIVE AND SMARTEST BENDER ON THE MARKET.

WE HAVE REVOLUTIONIZED THE WAY ELECTRICIANS BEND PIPE -- IT HAS NEVER BEEN EASIER OR FASTER THAN IT IS NOW WITH THE HOPPY BENDER


#### **FEATURES**

- A "STOP" ATTACHED TO THE BENDER HEAD USED TO CREATE EXACT AND REPEATABLE BENDS EVERY TIME.
- SIMPLIFIED "MULTIPLIERS" ENGRAVED INTO THE BENDER FOR PLACING THE "STOP" PRIOR TO MAKING OFFSETS AND FOUR-POINT SADDLES.
- SPECIAL 22.5 AND 45 DEGREE MARKS ENGRAVED INTO THE BENDER FOR PLACEMENT OF CONDUIT BEND MARKS AS WELL AS STAN-DARD DEGREE MARKS FOR STOP PLACEMENT, USED TOGETHER FOR BENDING THREE-POINT SADDLES WITHOUT REVERSING THE CONDUIT IN THE SHOE.
- HANDY REFERENCE CHARTS ATTACHED TO THE HANDLE FOR LOCATING BEND MARKS.

EVEN THE MOST COMPLICATED BENDS ARE MADE AS EASY AS 1,2,3.

OFFSETS, 3 & 4 POINT SADDLES, 90° BENDS ALWAYS PERFECT AND DONE IN A FRACTION OF THE TIME!

1/2" Hoppy Bender - 57050 3/4" Hoppy Bender - 57075 Replacement Handle - 57002 Replacement Thumb Screw - 57005 1/2" Replacement Label - 57050Lab 1/2" Replacement Swing-Stop - 57057 3/4" Replacement Label - 57075Lab 3/4" Replacement Swing-Stop - 57077







**FASTER AND EASIER THAN CUTTING AND GLUING FACTORY FITTINGS** 

HOW?

INSERT THE SPRING INTO THE PIPE AND BEND ACROSS YOUR KNEE!

- No Heat Guns
- No Heat Blankets
- Fewer PVC Fittings

Cold **PVC Pipe** Bender

**YOU CAN COLD BEND** 

RIGID PVC PIPE WITHOUT COLLAPSE OR FRACTURE



#### **Definition of Cold**

NOTE: Pipe should be 50° F or warmer. PVC pipe requires slight over bending which will "pop back" a few degrees upon the release of bending pressure.





Part# **58050** - 1/2" Part# 58075 - 3/4" Part# 58100 - 1" Part# 58125 - 1 1/4" Part# 58150 - 1 1/2" Part# 58200 - 2" Part# 58250 - 2 1/2" Part# 58300 - 3"

Part# 58350 - 3 1/2"

Part# 58400 - 4"



#### PVC BENDIT OFFERS:

- THE MOST CAPABLE, AFFORDABLE AND FLEXIBLE SYSTEM FOR HEATING AND BENDING PVC PIPE.
- CREATE COMPLEX COMPOUND BENDS WITHOUT MISSHAPING THE PIPE FOR LENGTHS UP TO 18 FT.
- CONSERVES ENERGY BY HEATING FROM THE INSIDE WITH A TOOL CALIBRATED FOR THE PRECISE BENDING TEMPERATURE FOR PVC.
- YOU WOULDN'T HEAT YOUR HOUSE FROM THE OUTSIDE. WHY DO THE SAME WITH PVC PIPE?

CONDUIT ABOVEGROUND AND UNDERGROUND (SCHEDULE 40) NEMA





LOOKING FOR A BETTER WAY TO LAY OUT COMPLEX CEILING AND HIGH BAYS? THE LASER PLUMB BOB, THE SELF LEVELING VERTICAL LASER FROM RACK-A-TIERS, IS THE ANSWER!



Part# 88455

- SOLID BRASS CONSTRUCTION
- CONVENIENT ON/OFF SWITCH FACTORY ALIGNED LASER MODULE CALIBRATED TO PRECISE 0.15 ACCURACY
- MAGNETIC DAMPING FOR QUICK STABILIZATION
- SELF LEVELING AND ALIGNING (VERTICALLY)
- DURABLE PLASTIC CARRY CASE BATTERY INCLLIDED

MFG NOTE: FOR ALL COMMERCIAL, INDUSTRIAL, OR RESIDENTIAL INSTALLATIONS. GREAT FOR LAYING OUT CEILING LIGHTS.

Laser Plumb Bob - 88455 Laser Plumb Bob Arm With Magnet Attached - 88-ARM
Laser Plumb Bob Base - 88-BASE Laser Plumb Bob Battery CR 123 - 88-BAT

#### THE STRAIGHT SHOT LEVEL

- PART# 45303
- THREE PRECISION VIALS: 0°, 45°, AND 90°,
- THREE RARE EARTH MAGNETS.
- EXTRA LARGE "V" GROOVED EDGE REMAINS PARALLEL ON SURFACES UP TO 10" DIAMETER.
- LASER DESIGNED TO LOCATE REFERENCE POINTS WHEN INSTALLING RACEWAYS.
- MAKES A GREAT LASER POINTER FOR BOSSING AROUND APPRENTICES!



#### WIE JEW HAVEL

PART# 45404

- CNC MILLED FROM 5061 ALUMINUM EXTRA LARGE "VD" GROOVE, STRADDLES UP TO 10" DIAMETER.
- RARE EARTH MAGNETS FOR EXTRA HOLDING.
  - WATER & SHOCK RESISTANT,
  - THIS CONVENIENT AND STRONG POCKET LEVEL COMES WITH 4 PRECISION VIALS OF 0, 30, 45, AND 90 DEGREES.



#### Make Your Job Safer, Faster, Easier

#### Features:

- Combines full function dual-outlet circuit tester with 220V detection and multiple direction bubble level.
- Eliminates the need for multiple tools to test and straighten any wall outlets
- Levels Diagnostics Terminal Covers

Part# 99102







Includes FREE adapter Set





THE POWER IS TURNED OFF BEFORE PROCEEDING...

#### Prevent Electrical Shock!

- Non-contact detection of 50-1000 VAC
- · Troubleshoot electrical circuits
- · A simple way to locate dangerous defective grounds
- Hand held device for determining presence or absence of 50-1000 Volts AC in insulated wires, wall receptacles, fuses, junction boxes and voltage carrying electrical systems
- Outstanding safety instruments that locate defective grounds, energized circuits, induced voltage
- · Senses voltage without metallic contact
- 2 replaceable "AAA" alkaline batteries included



AC Sensor 50-1000 Volts AC Bright red glow indicates AC voltage.


Part# **99000** 



Ultimate AC Sensor 50-1000 Volts AC Bright red glow indicates AC voltage AND audio alert.

Part# 99001

Note: Before using the AC Sensor or Ultimate AC Sensor, always test it on a known live voltage source to insure proper operation.



The Temporary Cable Guard helps you restore services quickly, reduces truck rolls, and eliminates downtime due to traffic or roadway activities. Perfect for new construction pre-wiring or new installations too. Available in easy-to-use 5' sections. Accommodates cable up to .750 hardline. Withstands heavy vehicle traffic without damaging cable. Can be produced in any length through special order. Easily anchored with concrete screws if needed.

#### Racky Strap

#### Versatile Utility Strap with a Firm Hold & Quick Release!

Features:

- · Holds anything up to 33lb per sq. inch
- · Quality hook and loop fastener with superior shear strength rating
- Double sided hook and loop may be used with soft side up or down
- Made with heavy duty Velcro
- · Great for data cable
- Available in 1/2" x 12" and 1" x 12" strips



1" straps



1/2" straps




Part# RS1005 1/2" RS1010 1"

## HOOP IT UP WITH "BUY 'EM USE 'EM, LOVE 'EM!"



- 1. Use for cable management in Telecommunication
- 2. Used as guides and supports to organize existing runs or assisting with new installs.
- 3. Install to conform to NEC and local codes.
- 4. A smart Hand-Hoop pathway creates the condition whereby "one man pulls" can be accomplished.



Part# HH1010

## BUDDIES

Fits all Standard Steel Studs & Punches



- One hand installation
- Fire rated V.O.

Part# **SB240** 

#### STEEL STUD BUSHINGS



- More cables, easier pulls
- Why Square Bushing? 70% more cross sectional area!

Part# SB220



## **Killers**

#### PLASTIC KNOCKOUT FILLERS



#### Features:

- No tools required
- Snap in with ease
- Snap out with ease
- Non-conductive, safer
   Part# KOK Series

Fits thin (1/32") and thick (1/8") wall thickness.

Available in 1/2" through 2" trade designations.

All thumbs? Good, because that's all you need to install our plastic KO Killers. Just pop'em in. No more tools, hammers, flying metal fillers, exploding buss bars, etc. Needing no tools is a big plus, especially when working space is tight.

#### **RAPID FIRE CONNECTORS**

**RAT 500** 

1/2"

Part# RAT500

( Per

**RAT 750** 

Part# **RAT750** 

4" 7750


FAST – NO LOCKNUTS

EASY – NO TOOLS REQUIRED

RAT 750 3/4"	Single Cables:	8/3, 6/3
RAT 500 & TT 500 1/2"	Single Cables: Two Cables:	14/2, 14/3, 12/2, 12/3, 10/2, 10/3 14/2, 14/3, 12/2

#### TT 500

#### TOM TWO WAY



OLD WORK, NEW WORK
INSTALLS FROM INSIDE
OR OUTSIDE THE BOX



1/2"

Part# TT500

Doing some renovation work? The TT500 also installs from the inside of the box after the wire is fished in. Ingenious. The RAT500 and RAT750 feature the same quality and large wire capacity but install from the outside for use in new construction. If you like the best, try these.

#### LEVEL JACK D

#### LOW VOLTAGE DATA/COM MUD RING



No tape measure  $\cdot$  No level required

Available in 1/2", 5/8" and 1" rise


#### HOW DOES IT WORK?

Alignment tabs reach across wood/metal studs to level low voltage outlets with A.C. boxes.

LEVEL

#### **EXTRA OFFSET:**

- Allows use of all standard fittings
- · Reduces A.C. interference to low voltage devices
- · Improves drywall finish



Part# LJ50R LJ58R LJ100R

If you're fussy about your rough-in layout, the Level Jack makes life easy. If you're not, no one will notice because you can't screw up with the Level Jack. Just clip it on to the AC box and screw it down. No level, no tape measure, no special boxes, no special fittings required. Level Jacks fit most AC boxes. See the cartoon for details.

### ROBERTSON<sup>®</sup> SCREWS!



USE THEM WITH OUR ROBERTSON DRIVER BITS.



The Original Robertson screw is the only one that guarantees a perfect "Cling Fit"











#### ROBERTSON "CLING FIT"



**ROBERTSON bits &** screws provide maximum penetration and "Cling Fit"

#### RECESS TOO NARROW



When the recess is too narrow, the driver does not penetrate deep enough into the recess.

#### RECESS TOO LARGE



When the recess is too large, the driver will wobble and come out.

#### INCORRECT RECESS ANGLE



When the recess or bit is at an incorrent angle, the driver will wiggle excessively.



## 



#### FLAT HEAD WOOD SCREWS








A deep thread screw with wide spacing for superior holding in softwoods, hardwoods, and particle boards.

Single lead thread (Lo-Root®) only available up to size 8. For size 10 and up, double lead thread (Kwixin®) wil be available.

#### PAN HEAD SHEET METAL SCREWS





Fully threaded single lead type "A" thread, our sheet metal screws are the ideal choice for use in metal and plastics (can also be used in wood).

#### **ROUND HEAD MACHINE SCREWS**





Commercial Zinc plated for increased corrosion resistance, Robertson® machine screws are perfect for any fastening application you may need them for.

#### CAMTAP® SELF DRILLING SCREWS





No more pre-drilling into metals! Camtap® Screws combine the advantages of a thread forming screw and a drill point, saving valuable time on the job site.



#### STEEL ZINC FLAT WASHERS

- Sizes from #6 1/2"
- other sizes and quantities available by request



#### STEEL ZINC HEXAGON NUTS & BOLTS

- Sizes from #6 1/2"
- Other sizes and quantities available by request



Part# REJAR

#### **ANCHORS**

- We have an assortment of anchors tailored to Electricians.
- Call for special request







FOR ALL THE DETAILS!

#### VISIT US AT WWW.RACK-A-TIERS.COM

FACEBOOK.COM/RACKATIERS

TWITTER.COM/RACKATIERS

YOUTUBE.COM/RACKATIERS












#### JOIN OUR MAILING LIST AND RECIEVE:

- LATEST PRODUCT NEWS
- SPECIAL OFFERS
- TIPS & TRICKS
- CONTESTS
- CARTOONS
- NEWS ABOUT OUR NEW REWARDS PROGRAM!





Tools Invented by Electricians Just Like You. Have an Idea? ... Yours could be Next.