

# RACK-A-TIERS®

SPECIALTY ELECTRICAL TOOLS

# WORK SMARTER NOT HARDER



MANY  
NEW PRODUCTS  
INSIDE!

# 2012/2013 PRODUCT CATALOG

# Table of Contents:

## WIRE MANAGEMENT TOOLS

Rack-A-Tiers – Wire Dispenser .....	3
Hooker – Pipe Wrench Adapter .....	3
EZ Roll – Wheeled Wire Dispenser .....	4
Tug Wise – Reel Dispenser .....	4
Wire Tub – Coil Spinner for MC Cable, Flex & NMSC .....	5
Thomas Wheeler – Coil Spinner for MC Cable, Flex & NMSC .....	5
Pocket Kart – Reel Carrying Tool .....	6
Reel-End – Spool Repair .....	6
Spool Aid – Spool Repair Discs .....	6
Rack' N Roller – Reel Dispenser .....	6
Cable Caddy, Carts, Dolly, Truck, & Data Carts .....	7
Plate Vise & Wire Pull Pro .....	7
Reel Mac 60, 70, 80 & Spindles .....	8
Ratchet Reel Mac .....	8
Mac Line Racks & Reels .....	9
Easy Stripper .....	10
Copper Wire Stripper .....	10
Speedway Cable Support System .....	11

## WIRE PULLING AND FISHING

All-American Pull Buddy .....	12
PulLee Wire Roller .....	12
Wire Vortex .....	12
Ropematic – Rope and Fish Tape Puller .....	13
Snatch Strap – Wire Puller .....	13
LB Wire Guide .....	13
Magnepull & Magnespot .....	14
Flex Puller .....	15
Coneheads .....	15
Laserline – Line Dart Shooter .....	15
Plastic Coated Fiberfish, Glowfish & Attachments .....	16
Fibersnakes & Contractor Packs .....	17
Bag Pipers .....	17

## TOOL BAGS AND OTHER STUFF

Combination Tool Belt & Pouch.....	18
Butt Pouches .....	19
Lift-n-Lok Tool Box .....	19
Staple Shark .....	20
Bigg Lugg .....	20
Carpenter's Pencil.....	20
Felt marker.....	20
Hammer.....	20
Croc's – Needle Nose Wire Stripper .....	21
V-Cutter – Electrician's Wire Stripper Attachment .....	21
Bend-All – Cable Bender .....	21
Racksy Knee Pads .....	22
Booty Pack – Disposable Boot Covers, Gloves, Respirators .....	22
Gopher LED Flashlight .....	22
Bolt Template .....	22
Panel Buddy – Knockout Kit .....	23
DeWALT & Ugly's Professional Reference Series .....	23

Owik Lok – Locking Plug .....	24
Sluggo-Ox .....	24
Piper - Conduit Tracking System .....	25
Nut Blaster – Wire Connector Tools .....	25
Breaker Lok .....	25

## HOLE CUTTING

Mega TCT Hole Saws .....	26
Heavy Duty TCT Masonry Hole Saws .....	26
Carbide Tipped Steel Cutters .....	27
Multi Bits (Step Drills) .....	27
The Javelin - Drilling Extension Kit .....	27
Bumper Balls & Flexible Auger Bits .....	28
Auger Bit File .....	29
Nail Chipper, Ship Auger, Tri-Cut, Standard & Overdrive .....	29
Multi-Function Hole Cutters & Accessories .....	30
Driller's Dust Bowl .....	31
Exploding Garbage Can .....	31

## COLORED RACKY BITS

#0 Yellow Square .....	32
#1 Green Square .....	32
#2 Red Square .....	32
#3 Black Square .....	32
#4 Orange Square .....	32
#1 Light Blue Phillips .....	32
#2 Blue Phillips .....	32
4" & 6" Double Ended Bits – #2 Phillips & 1/4 slot .....	32
4" & 6" Double Ended Bits – #1 & #2 Square Drive .....	32
Robertson® Impact Driver Bits .....	32
Magnetic Hex Bits .....	32
Lockhard #1 Square with Wings 4" & 6" .....	33
Picquic Screwdrivers .....	33
ProGrabit Kit – Damaged Screw Remover .....	33

## PIPE AND CONDUIT BENDING

Hoppy Bender – Conduit Pipe Bender .....	34
Pipe Viper – Cold PVC Pipe Bender .....	35
PVC Bend-It.....	35

## LEVELS AND TESTERS

Laser Plumb Bob .....	36
Straight Shot Level .....	36
Jet level .....	36
Plug Master Circuit Tester .....	37
Circuit Siren .....	37
AC Sensors .....	37

## CONNECTORS, ETC

Cable Protection Systems .....	38
Racky Strap – Utility Strap .....	38
Handi Hoop .....	38
Stud Buddies – Steel Stud Bushings .....	38
KOK Series – 1/2" to 2" Plastic Knock Out Fillers .....	39
Level Jack – Low Voltage Datacom Mud Ring .....	39
Rapid Fire Connectors – 1/2" & 3/4" .....	39
Tom Two Way 1/2" Connectors .....	39



# RACK-A-TIERS

## THE ONE TOOL THAT DOES IT ALL

THE RACK-A-TIERS WIRE DISPENSER IS THE ONE TOOL THAT DOES IT ALL. IT'S NO SURPRISE THAT WE'VE SOLD HUNDREDS OF THOUSANDS OF THEM TO ELECTRICIANS EVERYWHERE. THIS TOOL IS VERSATILE, WATERPROOF, RUSTPROOF, RUGGED, AND VERY RELIABLE. IT EVEN LOCKS TOGETHER TO MAKE A COMFORTABLE SEAT!

- WIRE PULLING
- PIPE VISE
- SAW HORSE
- WORKBENCH
- CADDY
- SEAT
- PORTABLE
- VERSATILE
- RELIABLE
- RUGGED
- INTERLOCKING PAIRS
- EASY TO USE



PART# 11455


<p><b>PULL WIRE</b></p>	<p><b>HOOKING</b></p>	<p><b>PIPE VISE</b></p>	<p><b>SAW HORSE</b></p>
<p><b>PORTABLE</b></p>	<p><b>WORK BENCH</b></p>	<p><b>CADDY</b></p>	<p><b>SEAT</b></p>
		<p><b>EASY SET-UP</b></p>	

Every RACK-A-TIER needs a Hooker!

### The Hooker Pipe Wrench Adaptor

"Turn your Rack-A-Tiers into a Pipe Vise"

Light  
Fast  
Simple  
Inexpensive



Part# 10455


NOTE: REQUIRES PIPE WRENCH 18" RIDGID® or equivalent fit. (not supplied)



# E-Z ROLL Wire Rack

The ultra compact/collapsible wheeled wire dispenser!

When you're ready to pull wire, wheel the e-z roll into position and dispense wire directly from your pipe bender or 1" EMT.



## Features:

- Rigid Steel Construction
- Light-weight Design
- Durable 'Caution Yellow' Finish
- Compact (fits in any job box)
- 150 lb. Load Tested
- Holds Reels up to 18"

Part# 55455

Collapsible for easy storage & handling




# TUG WISE

Ever had a jack-stand kick out on you?

An accident like that can cost you a lot of time, and towing a clunky reel trailer behind your vehicle is no faster! Why risk it? Simply attach the Tug-Wise to the base of your reel and be ready to pull cable instantly.



Part# 11931 - Standard  
Part# 11932 - Deluxe



## Standard Model

### Features:

- Size: 15" x 15"
- Handles up to 1000 lbs reels
- Works with wooden and plastic reels



## Deluxe Model

### Features:

- Size: 21.5" x 21.5"
- Handles up to 2000 lbs reels
- Made of 3/8" thick aluminum alloy
- Built to handle anything



## 3 Easy Steps:

- Screw to base of reel.
- Flip reel over.
- Pull Wire!





# Wire Tub

Wire Rewinder and Dispenser

## Features:

- 360° feed adjusts automatically
- 3-way adjustable center hub
- Removable top plate has a handle for **rewinding wire**
- Large 24" diameter capacity


Part# 18455



Top plate on for rewinding



Salvaged wire ready for reinstallation



# THOMAS WHEELER

## Wire Spool®

No wire spool?  
No problem!


Most coil dispensers are too big, cumbersome and expensive. Not this one. The Thomas Wheeler knocks down and sets up in seconds, hangs on a 2x4, in the trusses, above tee bar or on a ladder. Light, simple, rugged and it really works. A great value.

This easy-to-hang wire dispenser allows fast, twist-free NMSC, MC cable or Flex pulling.


- Affordable
- Dependable
- Saves Time
- Eliminates Waste
- No Maintenance
- Collapsible

Part# 19455

Hangs from  
a Ladder



Space Saver





# POCKET KART



Save your fingertips!

Use the Pocket Kart to carry wire reels of all sizes.



## Features:

- Light weight
- Swivelling handle
- Folds up easy
- Fits in pouches
- Fits in pockets
- Holds up to 200 lbs

Part# 56000



## “Wire Spool Repair”

How many broken spools in your shop? A few? A bunch? There's gold in them thar rolls but how do you get at it? **Fix them with the reel-end.**

Pays for itself with the first roll saved and it's reusable.

Part# 17455

The Reel-End fits plastic spools #10 through #18 gauge.

**A REAL MONEY MAKER.**


## Features:

- Salvages “unusable” wire
- Reusable over and over
- Money maker

**Application** - 6 1/2" diameter plastic spools



Broken



Fixed

# RACK 'N ROLLER

STORE AND PROTECT YOUR INDUSTRIAL, CONSTRUCTION AND WAREHOUSE WIRES WITH THE SPOOLMATE WIRE CART!



RACK-A-TIER'S RACK 'N ROLLER INCORPORATES AN EASY LATCH SYSTEM AND SPRING LOADED BAR FOR QUICK AND EASY SPOOL ACCESS. HOLDS UP TO 5 SPOOLS OF 500' OF 10, 12 AND 14 GAUGE WIRES (UP TO 200LB CAPACITY). SPOOLMATE'S BLUE WIRE CART FEATURES INTEGRATED HANDLES, HEAVY-DUTY STEEL ROLLERS AND 6" WHEELS FOR SIMPLIFIED MOBILITY UP RAMPS AND OVER DIRT.

DIMENSIONS OF THE SPOOLMATE WIRE CART ARE 13-1/2"W X 10"D X 36"H AND WEIGHS 21 POUNDS. WIRE CARTS ARE MANUFACTURED WITH A DURABLE STEEL FRAME TO WITHSTAND HARSH ENVIRONMENTS WITH DIRT AND CHEMICALS. ONE YEAR MANUFACTURER WARRANTY IS INCLUDED.

Part# 12888

## SPOOL-AID

Part# 128SA

SPOOL-AID REPAIR DISCS ARE NOW AVAILABLE AS AN INEXPENSIVE ALTERNATIVE TO REPLACING BROKEN WIRE SPOOLS. JUST SCREW THE REPAIR DISC ON TOP OF THE EXISTING SPOOL DISC AND VOILA, GOOD AS NEW!





## Cable Truck & Cable Caddy

- Constructed of rugged 1" steel tubing.
- Both are 43" tall with 7" rubber wheels.
- Both can accommodate spools up to 16" wide on solid steel 1/2" axles.
- Cable Caddy features 6 axle positions for unlimited versatility.
- Cable Truck has 4 axle positions and a solid steel plate for transporting material.



Part# **CT1100**  
Cable Truck

Part# **CC1200**  
Cable Caddy

## Cable Dolly

- Cable Dolly features 8–12" wide spindles to accommodate a wide assortment of reel sizes. Durable locking casters are rated up to 1200 lb.
- Cable Dolly Jr. features 4–12" wide spindles. Extensions also available.
- 8 piece spindle extension set with tube connectors. (17" extensions)



Part# **CD3000**  
Made to order

Part# **CD3100** (Not Shown)

Part# **CD3000-EXT**

## Cable Carts

- Comes with interchangeable 1" and 3/4" axles.
- Holds up to 30 spools of THHN.
- Vertical racks swing forward for easy loading.
- Space for plywood work table on top.

Dimensions: 43"H x 41 1/2"L x 28"W  
Shipping weight: 150 lbs.

Part# **CC2000**  
Cable Cart  
Made to order



Part# **CC2000D**  
Cable Cart - Data  
Made to order



Part# **13355**

Made of solid steel!

Features:

- Weight: 3.9 lbs.
- Holds several lumber sizes including but not limited to: 1"x2", 2"x4", 2"x6" and 4"x4"
- Includes 12" Ruler



Common features:

Lifts material for easy:

- Cutting
- Drilling
- Measuring
- And Tightening

Tightly holds:

- Plastic & Metal Pipe
- Conduit, Unistrut, Rebar
- Lumber & Dowels
- And Much More!



Part# **13555**

Features:

- Weight: 14.5 lbs. each
- As a set can hold 1" to 6" conduit, up to 36" wire spools and up to 1,000 lbs.
- Sold separately



Makes your job faster, more accurate and MUCH SAFER!



# REELMAG THE REAL JACK

## Standard features:

- Self-lubricating Roller Bearings – no grease required
- Quick-action lock washer for fast positioning
- Fall Guard feature to reduce pinching
- One-bolt disassembly – no welding required for service

### REEL Mac 60

Screw type telescoping reel jack for 26-56" diameter reels.



### REEL Mac 70

Screw-type telescoping reel jack for 46 to 96" diameter reels.



### REEL Mac 80

Heavy duty ratchet drive reel jack for reels up to 90" in diameter. Convenient, detachable ratchet handle stores in base when not in use.



## REEL Mac SPINDLES

Used with Reel Mac reel jacks. (Sold separately)



REEL MAC & JACK-A-TIER				
Description	Part No.	Reel Diameter	Capacity	Weight
Reel Mac #60	11860	26-56"	2500lb.	27lb.
Reel Mac #70	11870	46-96"	2500lb.	46lb.
Reel Mac #80	11880	up to 90"	3750lb.	99lb.
Jack-A-Tiers #75	11875	46-92"	2500lb.	34lb.

Corresponding SPINDLES				
Description	Part No.	Dimensions	Capacity	Weight
#61	11861	2 3/8" x 62"	5000lb.	39lb.
#71	11871	2 3/8" x 76"	5000lb.	47lb.
#81	11881	3 1/2" x 100"	7500lb.	119lb.
#71	11871	2 3/8" x 76"	5000lb.	47lb.

Use these charts to select the right Reel Mac, Jack-A-Tiers or spindle for your needs.

## RATCHET REEL MAC

### Standard features:

- Self-lubricating bearings
- Built-in handle storage
- Patent-pending safety head
- Use with Reel Mac Spindles

Part# 11885



Weight: 28 lb/12.7 Kg

### MID-RANGE RATCHET REEL STAND

- Ratchet design allows for easy lifting
- 2,500 lbs. capacity each
- 17.5" to 28" lifting range
- up to 55" diameter reels
- Designed for use with #350 & #500 wire reels



**KEEPS SPINDLES  
SECURELY IN PLACE**



# THE MAC LINE

## Caddy Mac features:

- Accommodate wide range of spool sizes.
- Wire guides for smooth feeding from the spool.
- Patented spindle locking system - spindles stay put during transportation.
- 1/4" solid spindles are attached to Caddy Mac cart... no loose pieces.
- Spindles swing out to set position for convenient loading of wire spools.
- Spindles can be easily removed for the occasional use of larger spools.
- Spindles store in special loops... will not fall out even during transportation.
- Large 10" wheels

## AC RACK



- 1,000 lb load capacity
- Eight bins of storage
- Arms fold easily with plunger release

Part# 11917

## CADDY AC

Part# 11901



Number of Spools	Max Spool Dia.	Load Capacity	Weight	Width	Additional Features
8-#10 awg. or 12-#12 awg.	7.5 in 19 cm	200 lb. 90 kg.	50 lb. 23 kg.	26 in 66 cm	Transports spools on spindles and works as a dolly. Wire is dispensed while laying flat.



## CADDY AC

Part# 11902

Number of Spools	Max Spool Dia.	Load Capacity	Weight	Width	Additional Features
16-#10 awg. or 24-#12 awg.	7.5 in 19 cm	400 lb. 180 Kg.	64 lb. 29 kg.	26 in 66 cm	Folds up for compact storage



## CADDY AC

Part# 11904

Capacity	Weight	Width	Additional Features
6-500' spools - 8" diameter 6-2,500' spools - 16" diameter	67 lb. 30.5 kg.	27 in 69 cm	A large capacity cart, dispenses wire while laying flat.



## AC

### A REEL TRANSPORTER

Part# 11900



Max Reel Width	Max Spool Dia.	Reel Capacity	Weight	Width	Additional Features
25 in 63.5 cm	40 in 101 cm	350 lb. 160 kg.	80 lb. 36.4 kg.	31.5 in 80 cm	All steel frame, easy set-up for cable dispensing. Compact storage.

Made in USA

# COPPER WIRE STRIPPER

RECOVER COPPER WIRE & ALUMINUM QUICKLY AND EASILY WITH THESE MONEY MAKING MACHINES



Model CWS-2

## Model CWS-2

Part# 47200

- All aluminum frame
- Strips 14 - 500 AWG
- Strip solid core or stranded wire
- Hardened one piece blade
- Blade made from tool steel
- 1/2 HP motor with 56c frame
- Blade easily re-sharpened
- Fully adjustable wire guide
- Strips 120 feet per minute
- Bench model - Anti-slip base

## Model CWS-1

Part# 47100

- All aluminum frame
- Strips wire from 14AWG - 3"
- Strips NMSC cable 10 - 14 AWG
- Strip solid core or stranded wire
- Hardened one piece blade
- Blade made from tool steel
- 3/4 HP motor with 56c frame
- Blade easily re-sharpened
- Fully adjustable wire guide
- Strips 120 feet per minute
- Bench model - Anti-slip base

Made in Canada

# EasyStripper


Strip the cover off your scrap wire in minutes with the Easy Stripper! Increase your earnings on every single job you complete.

Don't return your copper wire with the cover still on. Remove the cover in minutes with the Easy Stripper and get 300% more money for your scrap wire. It's that simple!

- Less than 10% the price of a standard motorized wire stripper
- Powered by any normal power drill
- Get 300% more money for returning your wire uncovered
- Way EASIER and FASTER than using your knife!
- Environmentally friendly – no burning required

Tired of burning the rubber off your copper wire just for a few extra bucks? It makes a mess, but more importantly, it hurts the environment. Don't be that guy – use the Easy Stripper to strip your wire in seconds and get MORE MONEY for returning scrap wire!

Part# 47020  
Blade Part# 47020B



WHY DOES HE MAKE ALL THE MONEY?



Strips wire from 14 - 4/0 AWG



# NON-METALLIC CABLE SUPPORT SYSTEM

BY: **SPEEDWAY**  
ELECTRICAL PRODUCTS

- Quick & easy installation
- No structural damage from drilling
- No gluing
- Easily add cables
- Great for new construction
- Add circuits when needed
- Perfect for remodelling
- No more expensive drill bits
- Reduce home run length up to 30%



**8 AND 10 FOOT  
LENGTHS AVAILABLE!**




## Maximum number of installed cables allowed.

CABLE TYPES NMB-UF-SEU	
CABLE WIRE SIZES	MAX NUMBER OF INSTALLED CABLES
14-2	38
12-2	30
10-2	22
8-2	14
6-2	10
4-2	5
2-2	4
2/0-2	2
4/0-2	2

CABLE TYPES NMB-UF-SEU	
CABLE WIRE SIZES	MAX NUMBER OF INSTALLED CABLES
14-3	29
12-3	23
10-3	16
8-3	10
6-3	6
4-3	3
2-3	2
2/0-3	1
4/0-3	1

Note: All cables listed contain an equipment grounding conductor that is bare and covered with the cable sheath. Passed UL temperature test with 80% load of the over-current device. Combinations of cables can be used not exceeding 40% maximum fill. UL Listed for one and two family dwellings.

TRY THESE TOOLS WHEN YOU NEED AN EXTRA PAIR OF HANDS PULLING WIRE!



## Wire Vortex

### TIME SAVING WIRE PULLING GUIDE

- Protects wire from damage when pulling
- Can pull wire in all 4 directions
- Use for 4" standard shallow or deep boxes
- Built with durable, impact-resistant plastic
- Easy to slip on and off



Part# 40001

## PulLee

### ROLLING WIRE GUIDE FOR SMOOTH AND CONTROLLED PULLING

- Guides wire and cable into the feeding end at the correct angle
- Spring loaded tips keep it locked in place
- Stainless steel design for maximum strength

Part# 41100



## The All American Pull Buddy

'Shoehorns for your wire!'

- Reduces Time and Labour
- Reduces the chance of damaging wires
- Turns wire pulling into a one person job
- Why not protect the conductors on all your pulls?



Three Sizes Available:  
1/2" 3/4" 1"

Part# 42050-1/2"  
Part# 42075-3/4"  
Part# 42100-1"  
Part# 42000-Multi-Pack







**ROPEMATIC PRO**  
THE SMART WAY TO PULL




**STOP** hurting hands and wrists.  
**STOP** breaking expensive fishtape.



- Can pull most ropes and fish tapes
- Pull more efficiently, faster & safer
- Saves an average of 30 minutes based on a 75' pull
- Use both hands ergonomically for maximum pulling strength without the pain

Part# 42400




1/2" PIPE?  
90° BENDS?  
FITS EASILY!

Time is money and when you think about it, a lot of time is spent stripping, taping and untaping wire for fishtape pulls. The SNATCH STRAP gives you back this time. By staggering the wire, you can pull more conductors with less effort. Plus SNATCH STRAPS can be daisy chained; you can easily drop wire groups at boxes along the pull. Color coded for easy circuit and phase identification.


Part# 69455

FAST ATTACHMENT  
FOR CONDUIT PULLS

**SNATCH STRAP**  
WIRE PULLER



3 STRAPS PER KIT



No stripping or taping required


**LB WIRE GUIDE**



THE LB WIRE GUIDE IS A  
"SHOE HORN" FOR 2" LB'S.

**FEATURES**

- FOR PVC LB FITTINGS AND IS ADAPTABLE TO MOST METAL LB'S
- FAST FOR ONE PERSON CONDUCTOR INSTALLATIONS
- INSTALLS IN TWO POSITIONS TO FIT BOTH "ENDS" OF THE LB



Part# 42200






EXTREMELY POWERFUL, YET DELICATE, MAGNETIC WIRE SNAKE FOR FISHING WIRE THROUGH WALLS. IT EVEN WORKS THROUGH INSULATION! THIS NEW VERSION HAS A MUCH STRONGER MAGNET AND A SMOOTHER ROLLING SURFACE.



**FEATURES**

- Hand roller with powerful magnet and smooth finish to avoid damaging walls
- 10' ball chain included
- Flexible leader with magnet head
- Also makes a great stud finder



**Mfg Note**

Any fiber fish can easily be threaded onto the magnet head. This will help push through dense insulation and guide through fire-block drill holes.

Part# 42800

**THE NEW MAGNESPOT HAS ARRIVED!**



The Magnespot is a reference point locator that gives users complete self-assurance before drilling, cutting, or any other task you may previously had to do blindly.

Place the Magnespot Transmitter on the wall, ceiling, or floor that you need to drill. On the other side hold the Receiver in the general direction of the Transmitter, the red LED arrows on the Receiver will indicate to you which direction to move. When all 4 Arrows illuminate, the Transmitter and Receiver are lined up within a 1/2 inch.

**Specifications:**

- Maximum Distance: 48" / 4'
- Receiver Accuracy: 1/2" @ 18"
- Transmitter Battery Type: 9V Alkaline (included)
- Receiver Battery Type: 9V Alkaline (included)

Part# 42900





Stop getting caught up in insulation or other obstacles!



# FLEX PULLER

**FLEXIBLE METAL  
CONDUIT PULLING TOOL  
EASILY SCREWS ONTO  
EXTERIOR OF MC CABLE  
AND PROVIDES A HOOK  
TO PULL CABLE.**

- Can be used on #14, #12, & #10 MC Cable!

Part# 42620

# CONEHEADS

Easy way to pull flexible conduit. Simply thread into interior of flexible conduit, hook onto your string or fish tape and pull!



Part# 42600  
Kit includes 1 each  
for 1/2" & 3/4" Flex

# LASERLINE®

WEST INDUSTRIES INC.



This CO2 powered gun shoots a foam dart with a line attached to it up to 200 ft. Stop climbing your ladder and moving it every ten feet to pull your wire across a T-Bar ceiling. Pull your wire the entire distance in one shot with the Laserline! Tired of wiggling through a crawl space just to drag your wire to the other end? Fire the Laserline, attach your wire, then walk around and pull it across while standing. It's that easy!

You don't even have to recoil the line. Each spool has 1200 ft of line, so you just cut it after each shot and re-attach the dart. Then just load in a new spool when you need it. CO2 cartridges are also replaceable and inexpensive!

Get the job done faster and have some fun – get the Laserline!



Laserline Kit - Part# 83000  
Replacement Line 2 (1200ft) - Part# 83001  
Dart 3 Pack - Part# 83003

# PLASTIC COATED FIBERFISH AND GLOWFISH

Our Fiberfish and Glowfish rods with a durable plastic coating offer the same great performance with no risk of splintering or slivering of the fiberglass.

## Plastic Coated Fiberfish II 3/16" DIAMETER ORANGE RODS

The most versatile of the Fiberfish with our new plastic coating process. Perfect for a wide range of installation situations and challenges.

### KITS

- PCF207 Fiberfish Kit contains: 1 - 6' B/F, 4 - 6' M/F w/ tips
- PCF208 3' Fiberfish Kit contains: 1 - 3' B/F, 7- 3' M/F rods w/ tips
- PCF230 "FourPack" contains: 1 - 3' B/F, 3 - 3' M/F, tip, and FishHook in vinyl pouch

### REPLACEMENT RODS

- PCF206 6' Bullnose/Female (B/F) rod
- PCF210 6' Male/Female (M/F) rod
- PCF214 3' Bullnose/Female (B/F) rod
- PCF215 3' Male/Female (M/F) rod



## Plastic Coated Glowfish II 5/32" DIAMETER LUMINOUS RODS

Super flexible glow-in-the-dark rods with our new plastic coating process. Great for tight jobs. The handy clear carry case keeps them constantly "charged" and ready.

### KITS

- GLF407 Glowfish Kit contains: 1 - 6' B/F, 4 - 6' M/F w/ tips
- GLF408 3' Glowfish Kit contains: 1 - 3' B/F, 7- 3' M/F rods w/ tips

### REPLACEMENT RODS

- GLF403 6' Bullnose/Bullnose (B/B) rod
- GLF406 6' Bullnose/Female (B/F) rod
- GLF410 6' Male/Female (M/F) rod
- GLF414 3' Bullnose/Female (B/F) rod
- GLF415 3' Male/Female (M/F) rod



## Fiberfish

### 1/4" DIAMETER YELLOW RODS


The original Fiberfish rods. Stiff enough for drop ceilings and flexible enough for insulated walls. Heavy duty rods for tough pulls.

### KITS

- FIB107 Fiberfish Kit contains: 1 - 6' B/F, 2 - 6' M/F, and 2 - 3' M/F rods w/ tips
- FIB108 3' Fiberfish Kit contains: 1 - 3' B/F, 5 - 3' M/F rods w/ tips
- FIB130 "FourPack" contains: 1 - 3' B/F, 3 - 3' M/F, tip, and FishHook in vinyl pouch

### REPLACEMENT RODS

- FIB103 6' Bullnose/Female (B/F) rod
- FIB113 6' Male/Female (M/F) rod
- FIB110 3' Bullnose/Female (B/F) rod
- FIB114 3' Male/Female (M/F) rod



# ATTACHMENTS AND ACCESSORIES

We've re-engineered the attachments to fit both the 3/16" rods and the 5/32" rods. They will still be compatible with all existing parts in the field, and the cost remains the same.



Fish Hook



Directional Tool



Magnet Head



Pull Ring



Ball Chain



Wisp Head



Screw Tip



Replacement Tip

**FishHook** - Use to retrieve or snag wire & cable.

**Directional Tool** - Offset bend helps guide the Fiberfish around obstructions in walls.

**Magnet Head** - Used with Fish Finder or to catch the ball chain inside wall cavities.

**Pull Ring** - Used to attach multiple wires for larger pulls.

**Ball Chain** - Attach to Fiberfish for interior wall pulls — can be retrieved through small access hole in wall with magnet or Flex-Fish.

**Wisp Head** - Use over suspended ceilings — won't catch on T-bars.

**Screw Tip** - Screw into the end of small communication wires for faster and easier pulls.

## Attachment Kit

Contains: FishHook, Directional Tool, Magnet Head, Pull Ring, Ball Chain, and 2 replacement tips. Stored in convenient vinyl pouch.



FIB120 Fiberfish Attachment Kit (1/4" rods)

FIB520 Universal Attachment Kit for ALL (3/16" rods) & (5/32" rods)

## Master Attachment Kit

Contains same as above plus: Wisp Head, Screw Tip, Flex-Fish



FIB140 Fiberfish Master Attachment Kit (1/4" rods)

FIB540 Universal Master Attachment Kit for ALL (3/16" rods) & (5/32" rods)



# FIBERSNAKES

Fibersnake Fishtapes and Rodders are designed for use in conduit. The reinforced fiberglass core is jacketed with a plastic coating for superior flexibility and durability. Non-conductive, so it's great for conduit with existing wiring. Rust-proof brass tips and fittings.

## 3/16" FIBERSNAKE

FIBT50 50' Fibersnake  
 FIBT100 100' Fibersnake  
 FIBT150 150' Fibersnake  
 FIBT200 200' Fibersnake  
 FIBT250 250' Fibersnake  
 FIBT300 300' Fibersnake

RT50 50' Replacement Rodder only  
 RT100 100' Replacement Rodder only  
 RT150 150' Replacement Rodder only  
 RT200 200' Replacement Rodder only  
 RT250 250' Replacement Rodder only  
 RT300 300' Replacement Rodder only

## 1/4" FIBERSNAKE

FIBR200 200' Fibersnake  
 FIBR250 250' Fibersnake  
 FIBR300 300' Fibersnake  
 FIBR350 350' Fibersnake  
 FIBR400 400' Fibersnake  
 FIBR450 450' Fibersnake  
 FIBR500 500' Fibersnake  
 FIBR550 550' Fibersnake  
 FIBR600 600' Fibersnake

RR200 200' Replacement Rodder only  
 RR250 250' Replacement Rodder only  
 RR300 300' Replacement Rodder only  
 RR350 350' Replacement Rodder only  
 RR400 400' Replacement Rodder only  
 RR450 450' Replacement Rodder only  
 RR500 500' Replacement Rodder only  
 RR550 550' Replacement Rodder only  
 RR600 600' Replacement Rodder only

## 5/16" FIBERSNAKE


Fibersnakes and Replacement Rodders are available in 400'-1000'

Fibersnakes Part # FIBL400-FIBL1000

Replacement Rodder Part # RL400-RL1000

Our 5/16" Fibersnakes are made to order. Returns due to the wrong size being ordered will **NOT** be accepted. Please order carefully.

Rodder Diameter	Recommended conduit sizes (in inches)	Maximum Length
(FIBT) 3/16"	½, ¾, 1, 1¼	300'
(FIBR) ¼"	1, 1¼, 1½, 2, 2½	600'
(FIBL) 5/16"	1½, 2, 2½, 3, 3½, 4	1000'



Fibersnakes are designed to pull fish line or rope. They are not recommended for pulling wire and cable.

**Note:** We do not replace fibersnakes broken due to improper use. However, we will send a repair kit at no extra charge.




# CONTRACTOR PACKS

## Installer Pack

Contains:

- Fiberfish II Kit
- 1/2"x72" Auger Piranhabit
- 3/8"x72" HSS Piranhabit
- 20' Fiberglass Telepole
- Attachment Kit
- Carry Case

Part# **CON100**



## Contractor Pack

Contains:

- Fiberfish II Kit
- 1/2"x72" Auger Piranhabit
- 3/8"x72" HSS Piranhabit
- 20' Fiberglass Telepole
- Attachment Kit
- Wisp Head
- Flex Fish
- Steering Guide
- 1" Auger Bit
- Carry Case

Part# **CON200**



It's simple...

Foam line carriers are expensive

Bag-Pipers are cheaper and work much better



3 sizes available to fit conduit 1/2" up to 6"



- Part #BP05-125 (sm) 1/2" x 1 1/4"
- #BP150-40 (med) 1 1/2" x 4"
- #BP20-60 (lrg) 2" x 6"
- #BP05-600 (multi-pack) 1/2" - 6"





## COMBINATION TOOL BELT

### PART#

SMALL COMBO - 43421  
MEDIUM COMBO - 43242  
LARGE COMBO - 43243  
X-LARGE COMBO - 43244  
XX-LARGE COMBO - 43245  
XXX-LARGE COMBO - 43246

SMALL BELT - 43401  
MEDIUM BELT - 43402  
LARGE BELT - 43403  
X-LARGE BELT - 43404  
XX-LARGE BELT - 43409  
XXX-LARGE BELT - 43410

ELECTRICIAN'S TOOL POUCH - 43201  
LARGE 9 POCKET TOOL POUCH - 43202

### INCLUDES:

Molded Support Belt, Electrician's Tool Pouch, Large 9 Pocket Tool Pouch, Hammer Holster and Tape Holder

### FEATURES:

- Reinforced with bar-tack stitching and heavy duty metal rivets
- 1250 denier DuraTek fabric with high density nylon webbing around pocket openings.



## MOLDED AIR CHANNEL SUPPORT BELT

### FEATURES:

- The first ever 'Molded Air-Channel Tool Belt' that offers incredible comfort, support, and ventilation for your back.
- The high density nylon 'Web Core' inside the padded belt provides strength to stitching and stress points.
- Metal rings are stitched to the belt's web core with high-density nylon webbing that provides the strongest way possible to attach suspenders.
- All stress points are reinforced with 'bar-tack' stitching along with heavy duty rivets.
- Double metal buckles that add strength and dependability.
- All of our belts and bags are made from double layered 1250 denier DuraTek fabric.
- Available in sizes from 26" to 54"



## MOLDED AIR CHANNEL SUSPENDERS

### FEATURES:

Our popular padded suspenders easily clip onto the sturdy metal rings that are built into our tool belts. The padded shoulder straps make these the ideal set of suspenders for your tool belt rig.

### INCLUDES:

- Adjustable Thick Molded Foam Shoulder Pads
- 2" Wide Adjustable Nylon Straps
- Leather Crossover Divider
- Heavy Duty Spring Hooks that attach to the rings on the Molded Air-Channel Belts



PART# 43606



# Butt Pouch Pocket Pro

## Pocket Tool Holder

### Features:

- Quick to put on AND COMFORTABLE!
- These tool pouches fit in your pocket
- Made of ballistic nylon
- Lightweight & durable

Mini - Part# 43015  
 Grande - Part# 43095  
 Driller - Part# 43110

Mini



Grande



Driller



No belt required!



## Small 25 Pocket Tray Tool Carrier

### Features:

- 14 exterior pockets (5 with velcro closures)
- 14 interior compartments & pockets
- 1 7" x 5 1/2" twelve-compartment plastic tray
- 1 large exterior zip-top pocket
- 1 measuring tape clip
- Includes shoulder strap

Part# 43707



## Large 44 Pocket Tray Tool Carrier

### Features:

- 29 exterior pockets (3 with velcro closures. 1 large clear pocket with velcro closure)
- 16 interior compartments and pockets
- 2 7" x 5 1/2" twelve-compartment plastic trays
- Includes shoulder strap

Part# 43706



A new revolutionary tool box



- No mixing between drawer compartments
- Extremely strong
- Easy to operate
- Made in USA

Part# 66536 – Yellow/Black



Part# 66536





# STAPLESHARK

THE STAPLE SHARK IS A DUAL-ENDED TOOL! ONE END IS USED FOR PULLING STUBBORN STAPLES AND THE OTHER ACTS AS A MULTI-PURPOSE PRY BAR. THIS UNIQUE TOOL PROVIDES EASY STAPLE PULLING FOR ANY SIZE OF CABLE STAPLE.

### FEATURES

- MADE OF HARDENED STEEL.
- DOUBLES AS AN 8 INCH RULER.
- INCLUDES A HANDY NAIL PULLER AND PRY BAR FOR MULTIPURPOSE USE.



PART# 52455

# BIGG LUGG

## Bigg Lugg I

The original cordless drill holder.

Part# 43001

## Bigg Lugg II

The next generation for personal carriers designed for cordless drills, air-nailers, paint cans, etc. (limit 10 lbs)

Part# 43002



### MEASURING TAPE

- Easy one-person pipe measuring
- Non-slip end hook
- Three stop buttons
- Sturdy casing

1" Wide 25' Long



Part# 52499



### Pencil

Show up your buddies on the job site with your Rack-A-Tiers branded carpenter's pencil. They do the job and look great.

Part# 52466

### Hammer

You asked us and we delivered. Finally, a solid hammer available at a decent price. Don't break the bank on your hammer, buy it from us!

Part# 52477



### Felt Marker

Complete your tool kit with a black felt marker from Rack-A-Tiers. These things come in handy and ours won't run dry on you!

Part# 52488



# CROC'S

## NEEDLE NOSE WIRE STRIPPERS



- Needle nose tips
- NMSC stripper at the "nose" where it is easier to use inside boxes
- Strips conductor sizes from #10 down to #22 AWG (for telephone wire)
- Large cutting blades for easy general purpose cuts
- Barrel sleeve crimper near the pivot
- Ergonomic "hourglass" shaped handles for comfort & speed
- Glow-in-the-dark handles

Part# 47000



## V-CUTTER

ATTACHABLE PRECISION WIRE STRIPPER



- A new way to strip NMSC cable
- Easily attaches to most wire strippers
- Strips cable in or out of electric boxes with push action
- Virtually eliminates nicking or cutting the wire insulator

Part# 47010

## BEND ALL Cable Bender



Finally! The amazing knuckle saver from Rack-A-Tiers®

- Captures wire
- Bend inside enclosures to the right or left
- Bend to the front or back
- Your feeders will lie in the lugs

Part# 77455

Machined from 6061 aircraft aluminum  
Fits a standard 1/2" ratchet.  
Fits #3 to 500 MCM conductors

*Ever give a meter base a knuckle sandwich? Too bad it was your own. Next time, defend yourself with the Bend All. Perfectly sized for 4/0, it takes the pain out of 200 amp services or sub feeders and conductors like it too. The Bend All makes micro adjustable bends without brutalizing the wire.*



### KNUCKLE BUSTER!



### PIECE OF CAKE!





# RACKSY PAD KNEE PADS WITH GEL IMPLANTS

Save your knees, you'll need them later!



Sturdy and so comfortable, you'll actually wear them. Velcro/elastic straps make these knee pads easy to put on and take off.

Part# 66455



So comfortable, you'll never want to get up!

# BOOTY PACK

Keepin' It Clean!

Leave a clean impression, not your dirty tracks with these slip resistant plastic booties, comfy gloves & respirator.



Kit Includes: 6 pairs of booties, 4 pairs of nitrile gloves  
4 pairs of vinyl gloves and a 3-N95 Respirator

Booty Kit: Part# 47099

Booties only sold separately: Part# 47099B

Bag of Booties (6 Pairs): Part# 47099BB

# THE GOPHER LED RECHARGEABLE FLASHLIGHT


- FEATURES A 0.5 WATT BRIGHT WHITE LED EMITTER
- CRYSTAL PLASTIC REFLECTOR OPTIC
- ANODIZED ALUMINUM STURDY CONSTRUCTION
- BUILT-IN RECHARGEABLE BATTERIES
- CHARGES DIRECTLY FROM CIGARETTE LIGHTER SOCKET
- 120 MINUTES USAGE, FULL RECHARGE IN 6-8 HOURS



Part# 53010

# Bolt Template

41 Templates in One! Quick and Easy! Reusable!  
Set-Up in Minutes! Weather Resistant ABS Plastic.



Select a hole saw that measures about 1/8" larger than the bolt to be used and drill the template at the selected easy centering divot mark.

Part# 67441

For setting  
poles 8" - 24"






# Panel Buddy Knockout Kit

Tired of trying to remove knockouts?

- Kit removes knockouts on Electrical, Security, Alarm and Datacom Panels
- Works with lipped and unlipped panels.


Part# 7WBK100



## The Original Electrical Reference Books

Everyone Needs an Ugly's


Revised 2011 Edition



On the Job Reference:

- Mathematical formulas
- National electrical code
- Wiring configurations
- Conduit bending
- Voltage drops
- Life saving first aid procedures
- Much, much more

All in an easy-to-read and easy-to-access format



Part#'s

Electrical References	73215
Electrical Safety & NFPA 70E®	73214
Referencias Eléctricas	73217
Electric Motors & Controls	73216
Electrical Desk Reference	73213
Conduit Bending	73218

# DEWALT Reference Books

## Electrical Trade Series



In the job pocket reference books offer easy to read charts & detailed illustrations. The 4 1/2" x 6 1/2" size fits easily in a toolbox or pocket. Each book features over 350 pages of complete reference material.

### Professional Reference Books


- Part # s
- 73200 Electrical
  - 73205 Wiring Diagrams
  - 73203 Lighting & Maintenance
  - 73208 Electrical Estimating
  - 73201 Datacom
  - 73204 Electric Motor
  - 73210 Security Sound & Video

### Electrical Licensing Part# 73206

Based on the 2011 International Code®  
Subjects include methods to improve test scores, strategies to prepare, study aids and tips, examination regulations, formulas and references, realistic sample exams, and answer keys with corresponding NEC® references.

### Electrical Code Reference Part# 73207

Based on the 2011 International Code®  
Illustrates hundreds of the most common code requirements, violations and installation concerns including: materials, notching and cutting, commercial hoods, combustion air openings, access and clearances, duct construction, mechanical ventilation.






# Qwik Lok

▶ The CLICK you can Trust

**GUARANTEES EXTENSION CORDS AND TOOLS ARE LOCKED TOGETHER. IT IS THE TOUGHEST, STRONGEST, MOST RELIABLE, 120V - 15A CONNECTOR.**



#### Features:

- Qwik-Lok is the 'Must-Have' locking retro-fit /replacement connector for extension cords
- An outstanding end that eliminates tied, frayed, burned out or ruined cords and connectors
- Works with common 2 or 3 pronged plugs
- Eliminates need for 'twist-lock' devices
- Delivers consistent, reliable power at all times for demanding industries & trades

Part# 97008




## SLUGGO-OX™ The Ultimate Ground Rod Driving Tool

SLUGGO-OX™ is the revolutionary new tool that's taking the industry by storm.

#### Features:


- Incredibly strong, made of 3" hot-rolled, heat-treated, hardened steel
- 3 1/2" bore to accept 3/4" and 5/8" ground rods
- 80% more striking surface
- One piece, light-weight (7lbs.)
- Yellow zinc chromate surface to deter rust

Part# 67119



**"YOUR TURN TO HOLD THE GROUND ROD. ROD, I THINK IT'S TIME WE GOT A 'SLUGGO-OX'!"**





# PIPER

Conduit Tracking System

- Tracks conduits in minutes.
- Works in unobstructed 1/2" to 6" EMT, Rigid, or Plastic pipes to well over 300 feet.
- Finds pipe ends that would be impossible to locate by the old "stuff the fish down the pipe" method.



Part# 99005 1/2" - 1"  
Part# 99006 1/2" - 2"

# Nut Blaster

The Nut Blaster Universal Wire Connector Tools

## FEATURES

- Fast, Easy Installation
- Prevents sore fingers and cramping hands
- Fits all brands, red, grey & blue



XL - Part# 72101  
XXL - Part# 72102

# BREAKER LOK

LOCK YOUR BREAKER IN THE ON OR OFF POSITION WITH THE BREAKER LOK



## Features

- The only breaker lock you need
- Fits most manufacturer's breakers
- Also works on standard toggle switches

Part# 75000



# We've Got the Hole Thing Covered!

Brick, Fiberglass, Plywood, Plastic, Roofing, Tile, Mdf Fibre Cement Board, Laminates, Osb, Concrete Block, Aluminum, Steel, Stainless Steel, Hardie Board, Stucco, Sheetrock, Hard Woods, Soft Woods, Slate, Nonferrous Metals, Sheet Metal and...

*Well, you get the picture!*

## Mega TCT Hole Saws

- Cut wood, sheetrock, fiber cement board, plaster, fiberglass, OSB, chipboard, MDF, and other tough materials.
- Tough Tungsten Carbide teeth extend past inside and outside walls for reduced friction and much faster cutting.
- Large side gullet slots for fast chip removal and fast plug removal
- Ultra Deep 2" cutting depth
- Use with standard hole saw arbors
- **Cuts through nails.**



Part#	Size
91613	1-1/8"
91615	1-3/8"
91617	1-5/8"
91619	1-7/8"
91621	2-1/16"
91622	2-1/8"
91625	2-9/16"
91627	2-3/4"
91629	3-1/8"
91630	3-3/8"
91632	3-5/8"
91633	4"



## Heavy Duty TCT Masonry Hole Saws

- Engineered for fast cutting through stucco or FRP / fiberglass as well as metal lath and plywood.
- Cuts through heavy duty brick and cinderblock.
- All hole cutters have a 2-3/8" cutting depth.
- Perfect for use with 18 volt hand drills to cut holes up to 4-1/4" diameter.



Part#	Size
91412	1-1/4"
91414	1-1/2"
91416	1-3/4"
91417	2"
91419	2-1/4"
91420	2-1/2"
91421	2-5/8"
91422	3"
91434	3-1/2"
91424	4"
91426	4-1/4"





## Carbide Tipped Steel Cutters

WE HAVE HIGH END AND LOW END CUTTERS

- Ejector spring
- Tapered center drill
- 5/8" up to 5 1/2"



Part# 93000 Series

Part# 92000 Series

**IF YOU ARE TIRED OF HOLE CUTTERS THAT DON'T CUT IT, CALL US FOR INFORMATION ON OUR GERMAN QUALITY HOLE CUTTERS.**

## Multi Bit (Step Drills)

Hardened stepped Bits for clean cuts in sheet metal, electrical boxes, arborite, etc. Handy for creating knockouts.

MLT1	1/8" - 1/2"	13 step
MLT3	1/4" - 3/4"	9 step
MLT4	3/16" - 7/8"	12 step
MLT5	7/16" - 1 1/8"	12 step
MLT 7	1/4" - 1 1/2"	11 step



Available in 1/8" to 1 1/2" sizes

Never get caught in a drilling extension jam again!

# The Javelin™

## ALL-IN-ONE DRILLING EXTENSION

HOLDS HOLE SAWS, SPADE BITS, SCREW TIP HOLDERS, NUT DRIVERS AND ANY OTHER TOOL WITH A 1/4" HEX SHANK.

- Cut 3/8"-16 threaded rod to desired length
- Fits any tool with 1/4" hex shaft
- Fits in all standard drill chucks
- Can be extended by using 3/8" rod couplings
- Hole saw arbor also included


Part# 95000  
Pat# 7,802,948

PACKAGE INCLUDES:



DON'T GET RIPPED OFF!

NOT ALL HOLE CUTTERS ARE EQUAL! LET US FIND THE RIGHT ONE FOR YOU.



# BUMPER BALLS

These balls will keep your bits centered!



**BEFORE**



**AFTER**

## NO MORE...

- Bit walking
- Nail hitting
- Wall patching
- Carpet

Fits all 3/16" shaft auger bits

Kit includes 1 each of 1 3/4" & 2 1/4" Balls

Part# **BB3412**

## PIRANHABITS

Piranhabits have 3/16" flexible shafts so they can bend while rotating. This allows drilling inside wall cavities, through box cut-outs or through other small openings.

### Quattro Flex Auger Bits

Fast and aggressive self feed auger bits, welded to a flexible shaft. Cuts clean holes. Crossbored at both ends for easy wire pulling. Use for wood only.

QTT3824	3/8"x24"	Auger flexbit
QTT3836	3/8"x36"	Auger flexbit
QTT3848	3/8"x48"	Auger flexbit
QTT3854	3/8"x54"	Auger flexbit
QTT3872	3/8"x72"	Auger flexbit
QTT1224	1/2"x24"	Auger flexbit
QTT1236	1/2"x36"	Auger flexbit
QTT1248	1/2"x48"	Auger flexbit
QTT1254	1/2"x54"	Auger flexbit
QTT1272	1/2"x72"	Auger flexbit
QTT91624	9/16"x24"	Auger flexbit
QTT91636	9/16"x36"	Auger flexbit
QTT91648	9/16"x48"	Auger flexbit
QTT91654	9/16"x54"	Auger flexbit
QTT91672	9/16"x72"	Auger flexbit
QTT3424	3/4"x24"	Auger flexbit
QTT3436	3/4"x36"	Auger flexbit
QTT3448	3/4"x48"	Auger flexbit
QTT3454	3/4"x54"	Auger flexbit
QTT3472	3/4"x72"	Auger flexbit

More sizes available

### High Speed Steel

Superior quality M-2 High Speed Steel drill bit, welded to a flexible shaft. Cuts both metal and wood. No need to worry about hidden nails or metal studs when drilling.

FLX1424	1/4"x24"	HSS Flexbit
FLX1436	1/4"x36"	HSS Flexbit
FLX1448	1/4"x48"	HSS Flexbit
FLX1454	1/4"x54"	HSS Flexbit
FLX1472	1/4"x72"	HSS Flexbit
FLX3824	3/8"x24"	HSS Flexbit
FLX3836	3/8"x36"	HSS Flexbit
FLX3848	3/8"x48"	HSS Flexbit
FLX3854	3/8"x54"	HSS Flexbit
FLX3872	3/8"x72"	HSS Flexbit
FLX1224	1/2"x24"	HSS Flexbit
FLX1236	1/2"x36"	HSS Flexbit
FLX1248	1/2"x48"	HSS Flexbit
FLX1254	1/2"x54"	HSS Flexbit
FLX1272	1/2"x72"	HSS Flexbit



**Guide Tool**  
Part# **FIB-GUD**

Allows the Piranhabs to bend for drilling from outside the wall cavity.

## HEAD & SHANK COMBOS SWITCHBIT HEAD & SHANK PACKAGES

### NEW SWITCH BIT LINE!

Rack-A-Tiers is proud to announce our newest line of flexible installer bits, The Switch Bit Line.

Now you can quickly customize your set with these flexible installer bits with interchangeable heads and various shank lengths for any job.

### CROSSBORED THROUGH SHAFT TO ALLOW WIRE PULLING!

ET31621	Single Shank	3/16"	21"
ET31633	Single Shank	3/16"	33"
ET31651	Single Shank	3/16"	51"
ET31669	Single Shank	3/16"	69"
ET1415	Single Shank	1/4"	15"
ET1421	Single Shank	1/4"	21"
ET1433	Single Shank	1/4"	33"
ET1451	Single Shank	1/4"	51"
ET1469	Single Shank	1/4"	69"





# Auger Bit File

**THE BEST FILE FOR AUGERS IS BACK!**

This file is specially designed to prevent damage to surfaces next to those being filed. One end has safe (uncut) edges and the other end has safe sides. Perfect for sharpening auger bits.

**COMING  
THIS FALL**



Part# AUFILE

# Flex Bit Extensions

Flexible Extensions provide more reach and feature dual set screws for extra strong hold. Use the 1/4" Extensions for the 3/4" Auger Piranhbits



FIBEX48	3/16" x 48" Extension
FIBEX54	3/16" x 54" Extension
FIBEX72	3/16" x 72" Extension
FIBEX1448	1/4" x 48" Extension for 3/4" bits
FIBEX1454	1/4" x 54" Extension for 3/4" bits
FIBEX1472	1/4" x 72" Extension for 3/4" bits

# OverDRIVE™

**FAST BORING AUGER BITS**

**DESIGNED FOR BATTERY DRILLS**



Part #AW34OD-3/4" x 7"  
#AW78OD-7/8" x 7"

**Cuts like a knife through butter!**



**Tired of junk auger bits? Rack-a-Tiers found the star-m brand that has produced quality products for over 80 years for professional trades people.**

## Nail Chipper Ship Auger



TRI-CUT design with 3 precision ground edges for fast, smooth cutting without resistance.

REDUCES NAILS TO CHIPS without grabbing and leaves a clean hole with minimal "blowout."

## Standard Ship Auger



Precision ground cutting edge for fast cutting of clean holes in wood.

Burr-free lead screw for easy starts and pull-through without material build-up.

**NOTHING BUT THE BEST!**

- Burr-Free Lead Screw
- Light Weight
- Carbon Steel Construction

With precise heat-treat and hardening processes for strength and durability.

## 18" Auger Bits

AW3818	3/8"
AW1218	1/2"
AW11618	11/16"
AW3418	3/4"
AW7818	7/8"
AW118	1"
AW1418	1 1/4"

## 7 1/2" Auger Bits

AW3807	3/8"
AW1207	1/2"
AW11607	11/16"
AW3407	3/4"
AW7807	7/8"
AW107	1"

To order Tri-Cut Bits add a 'T' to the Part #'s



"By the way – the electricians are in the crawl space drilling holes for the wiring to the new hot-water tank."



# Multi-Function Hole Cutter



## Cuts through:

- Plywood
- Fiber cement board
- Sheetrock
- Up to 20 GA. sheet metal
- Fiberglass
- Aluminum

Part# 90200  
Part# 90300  
Part# 90400



Compare Features →	Other Hole Saw Kits →	<b>HOLE PRO</b>
Adjusts to exact hole size needed	<b>NO</b> Van full of dull hole saws	<b>YES</b> <b>1 7/8" - 9"</b> <b>1 7/8" - 12"</b> <b>1 7/8" - 17"</b>
Dust collector shield	<b>NO</b> Lady finds new contractor	<b>YES</b> <b>Clean job</b>
Designed to reduce kickback	<b>NO</b> Jaw breaker	<b>YES</b> <b>Non-Jaw breaker</b>
Economical replaceable blades	<b>NO</b> Sharpen a bunch of little teeth	<b>YES</b> <b>Sharpen only two blades</b>
Price	<b>\$300.00</b>	<b>Less than half No-brainer!!!</b>

Replacement Blades



Part# 90-VH HSS  
Part# 90-VT Carbide

**SAVE YOUR LUNGS! CUTTING HOLES WITHOUT PROTECTION CAN BE HAZARDOUS TO YOUR HEALTH. PROTECT YOU & YOUR CREW WITH THE HOLE PRO.**

## Hole Saw Accessories

### Arbor Extension



Part# 90105

### HOLE SAW DUST SHIELD

- Has a ABS shield that collects all the dust and shavings when using a hole saw.
- Has a 7 3/4" OD and 6 3/8" ID supporting a hole saw up to 6 1/4" in diameter and up to 2 1/2" cutting depth.
- Saw and vacuum adapter sold separately
- Requires arbor extension for use.



Part# 90103

### ARBOR HOLE SAW ADAPTER FOR ALL HOLE CUTTER MODELS

- Converts any hole cutters for use with any hole saw
- Unique dual head design allows mounting 1/2"-20" or 5/8"-18" threaded hole saws




### VACUUM ADAPTER FOR ALL HOLE PRO DUST SHIELDS

- Reusable plug to re-seal shield hole
- Perfect addition to hole-pro shields, power series X & XL models
- Attaches to standard 1" power tool vacuum hose

Part# 90101





# DRILLER'S Dust Bowl

HOLE SAW DUST COLLECTOR


← Old way      Best way! →

Fits hole saws up to 8"

**NEW IMPROVED WITH NYLON BUSHING**



Drill & saw are not included



## SAVE THE BALLS FOR THE COURT!

You may enjoy a face full of drywall dust, but your customers might not. The flexible DRILLER'S DUST BOWL compresses against the work surface and traps all dust and debris as you drill. It fits your drill and hole saw without any adjustments. Put an end to 'unprotected hole sawing'.

Part# 48000

# EXPLODING GARBAGE CAN

Heavy duty, tear resistant, polytuf fabric



## COLLAPSIBLE TRASH CONTAINER

- Featuring an internal support spring that "Springs into Action"

Part# 51000

Size:  
19" x 24" (open)  
1 1/2" x 24" (collapsed)



Who says you're a slob? Clean up your reputation with your own trash can. The Exploding Garbage Can will dazzle your customers, especially if you use it! Pops up and folds flat — ready when needed. You can also take one home for the garden.

# RACKY BITS

**COLOR CODED DRIVE BITS**

Faster, easier and more efficient bit selection!



## Magnetic Hex Bits

- RED** 1/4" Hex Drive
  - YELLOW** 5/16" Hex Drive
  - BLUE** 3/8" Hex Drive
  - BROWN** 7/16" Hex Drive
  - BLACK** 1/2" Hex Drive
- Available in: 2 1/2" & 6" Hex Bits

## 4" & 6" Double Ended Bits

- #2 Phillips 1/4" slot
- #1 square drive
- #2 square drive

## ROBERTSON® IMPACT DRIVER BITS



- |        |                   |                    |
|--------|-------------------|--------------------|
| 7011PI | Phillips #1 x 1"  | Short, skinny grey |
| 7012PI | Phillips #1 x 2"  | Long, skinny grey  |
| 7021PI | Phillips #2 x 1"  | Short, thick grey  |
| 7022PI | Phillips #2 x 2"  | Long, thick grey   |
| 7011RI | Robertson #1 x 1" | Short green        |
| 7012RI | Robertson #1 x 2" | Long green         |
| 7021RI | Robertson #2 x 1" | Short red          |
| 7022RI | Robertson #2 x 2" | Long red           |
| 7031RI | Robertson #3 x 1" | Short black        |
| 7032RI | Robertson #3 x 2" | Long black         |

## Genuine ROBERTSON® Bits

- YELLOW** #0 Square Drive
- GREEN** #1 Square Drive
- RED** #2 Square Drive
- BLACK** #3 Square Drive
- ORANGE** #4 Square Drive

## Phillips Bits


- BLUE** #2 Phillips
- LIGHT BLUE** #1 Phillips



## Ordering Options:

1. Convenient blister cards
2. Bulk qty(s) for display case





## THE PEG THAT FITS THE HOLE

# lock HARD™



The lockHARD locks in place  
and never strips.

Part# 72134P 4"  
Part# 72136P 6"

Available in both bulk quantities  
or packaged blister cards.

## PICQUIC®

### Stubby

- Solid, comfortable, high torque handle
- 6 High quality 1.3" length insert bits
- Ideal for work in close quarters



Part# P91000

- Slim, comfortable and solid
- Corrosion proof magnetic alloy shank
- Legendary instant-bit-change

### Dash 7

- 7 – 2" length, 1/4" Hex Powerbits
- Comes in 4 bright new colors



Part# P05001

### SIXPAC Plus

- 7 – 3" length, 1/4" Hex Powerbits
- 11.5" total length

Part# P88001



## proGrabIt

### Damaged Screw Remover

- Works on jagged, uneven and rough breaks
- Self centering tip, no walking
- Compatible with quick connect chuck systems
- Easy to use with 3/8" variable speed reversible drill
- Extracts screws up to 4 inches

	Screws	Bolts
Grabit #1	No. 4 - No. 6	No. 10 (5mm)
Grabit #2	No. 8 - No. 10	1/4" (6mm)



Rounded out screw heads, what a nightmare! Not anymore. Just drill out the damaged screw / bolt with one end of the Grabit, then flip it over and the "grab end" winds out the screw. MADE IN USA

Kit Part# 72120



# HOPPY BENDER

THE HOPPY BENDER IS HANDS DOWN THE MOST INNOVATIVE AND SMARTEST BENDER ON THE MARKET.

WE HAVE REVOLUTIONIZED THE WAY ELECTRICIANS BEND PIPE -- IT HAS NEVER BEEN EASIER OR FASTER THAN IT IS NOW WITH THE HOPPY BENDER

## FEATURES

- A "STOP" ATTACHED TO THE BENDER HEAD USED TO CREATE EXACT AND REPEATABLE BENDS EVERY TIME.
- SIMPLIFIED "MULTIPLIERS" ENGRAVED INTO THE BENDER FOR PLACING THE "STOP" PRIOR TO MAKING OFFSETS AND FOUR-POINT SADDLES.
- SPECIAL 22.5 AND 45 DEGREE MARKS ENGRAVED INTO THE BENDER FOR PLACEMENT OF CONDUIT BEND MARKS AS WELL AS STANDARD DEGREE MARKS FOR STOP PLACEMENT, USED TOGETHER FOR BENDING THREE-POINT SADDLES WITHOUT REVERSING THE CONDUIT IN THE SHOE.
- HANDY REFERENCE CHARTS ATTACHED TO THE HANDLE FOR LOCATING BEND MARKS.

## MFG NOTE

EVEN THE MOST COMPLICATED BENDS ARE MADE AS EASY AS 1,2,3. OFFSETS, 3 & 4 POINT SADDLES, 90° BENDS ALWAYS PERFECT AND DONE IN A FRACTION OF THE TIME!

Hoppy Bender Part#'s  
 1/2" Hoppy Bender - 57050  
 3/4" Hoppy Bender - 57075  
 Replacement Handle - 57002  
 Replacement Thumb Screw - 57005  
 1/2" Replacement Label - 57050Lab  
 1/2" Replacement Swing-Stop - 57057  
 3/4" Replacement Label - 57075Lab  
 3/4" Replacement Swing-Stop - 57077

### STEP ONE

READ TABLE & MARK CONDUIT



### STEP TWO:

SET STOP



### STEP THREE:

INSERT CONDUIT



### STEP FOUR:

BEND!





# The Pipe Viper™

**FASTER AND EASIER THAN CUTTING AND GLUING FACTORY FITTINGS**

## HOW?

**INSERT THE SPRING INTO THE PIPE AND BEND ACROSS YOUR KNEE!**

- No Heat Guns
- No Heat Blankets
- Fewer PVC Fittings



## Definition of Cold

NOTE: *Pipe should be 50° F or warmer.*  
PVC pipe requires slight over bending which will "pop back" a few degrees upon the release of bending pressure.

## Cold PVC Pipe Bender

**YOU CAN COLD BEND RIGID PVC PIPE WITHOUT COLLAPSE OR FRACTURE**

**COMING THIS FALL**

# PVC BENDIT INC.

## PVC BENDIT OFFERS:

- THE MOST CAPABLE, AFFORDABLE AND FLEXIBLE SYSTEM FOR HEATING AND BENDING PVC PIPE.
- CREATE COMPLEX COMPOUND BENDS WITHOUT MISSHAPING THE PIPE FOR LENGTHS UP TO 18 FT.
- CONSERVES ENERGY BY HEATING FROM THE INSIDE WITH A TOOL CALIBRATED FOR THE PRECISE BENDING TEMPERATURE FOR PVC.
- YOU WOULDN'T HEAT YOUR HOUSE FROM THE OUTSIDE. WHY DO THE SAME WITH PVC PIPE?

Part# 59100 - PVC Bendit Series A  
Can bend 1/2", 3/4", 1", and 1 1/4" PVC Pipe

Part# 59200 - PVC Bendit Series B  
Can bend 1 1/2", 2" 2 1/2", and 3" PVC Pipe

A sleeve is required for any PVC Pipe 2" - 3"



# LASER PLUMB BOB

## BEFORE



## AFTER



Part# 88455

LOOKING FOR A BETTER WAY TO LAY OUT COMPLEX CEILING AND HIGH BAYS? THE LASER PLUMB BOB, THE SELF LEVELING VERTICAL LASER FROM RACK-A-TIERS, IS THE ANSWER!

### FEATURES

- SOLID BRASS CONSTRUCTION
- CONVENIENT ON/OFF SWITCH
- FACTORY ALIGNED LASER MODULE CALIBRATED TO PRECISE 0.15 ACCURACY
- MAGNETIC DAMPING FOR QUICK STABILIZATION
- SELF LEVELING AND ALIGNING (VERTICALLY)
- DURABLE PLASTIC CARRY CASE
- BATTERY INCLUDED

MFG NOTE: FOR ALL COMMERCIAL, INDUSTRIAL, OR RESIDENTIAL INSTALLATIONS. GREAT FOR LAYING OUT CEILING LIGHTS.

Laser Plumb Bob - 88455  
 Laser Plumb Bob Arm With Magnet Attached - 88-ARM  
 Laser Plumb Bob Base - 88-BASE  
 Laser Plumb Bob Battery CR 123 - 88-BAT

## THE STRAIGHT SHOT LEVEL

PART# 45303

- THREE PRECISION VIALS: 0°, 45°, AND 90°.
- THREE RARE EARTH MAGNETS.
- EXTRA LARGE "V" GROOVED EDGE REMAINS PARALLEL ON SURFACES UP TO 10" DIAMETER.
- LASER DESIGNED TO LOCATE REFERENCE POINTS WHEN INSTALLING RACEWAYS.
- MAKES A GREAT LASER POINTER FOR BOSSING AROUND APPRENTICES!



## THE JET LEVEL

PART# 45404

- CNC MILLED FROM 6061 ALUMINUM EXTRA LARGE "VD" GROOVE, STRADDLES UP TO 10" DIAMETER.
- RARE EARTH MAGNETS FOR EXTRA HOLDING.
- WATER & SHOCK RESISTANT.
- THIS CONVENIENT AND STRONG POCKET LEVEL COMES WITH 4 PRECISION VIALS OF 0, 30, 45, AND 90 DEGREES.



# P lugMaster™

Make Your Job Safer, Faster, Easier

Features:

- Combines full function dual-outlet circuit tester with 220V detection and multiple direction bubble level.
- Eliminates the need for multiple tools to test and straighten any wall outlets
- **Levels • Diagnostics • Terminal Covers**

Part# 99102



## AUDIBLE CIRCUIT IDENTIFIER



**SOUND - It's Simple & Reliable**

Features:

- 3 to 130 volt AC & DC
- Built in polarity lights
- Handy adapter fittings
- Adjustable volume control

Part# 99101



Includes **FREE** adapter Set



TO BE ON THE SAFE SIDE, I BETTER CHECK TO MAKE SURE THE POWER IS TURNED OFF BEFORE PROCEEDING...



**Prevent Electrical Shock!**

- Non-contact detection of 50-1000 VAC
- Troubleshoot electrical circuits
- A simple way to locate dangerous defective grounds
- Hand held device for determining presence or absence of 50-1000 Volts AC in insulated wires, wall receptacles, fuses, junction boxes and voltage carrying electrical systems
- Outstanding safety instruments that locate defective grounds, energized circuits, induced voltage
- Senses voltage without metallic contact
- 2 replaceable "AAA" alkaline batteries included



AC Sensor  
50-1000 Volts AC  
Bright red glow indicates AC voltage.

Part# 99000




Ultimate AC Sensor  
50-1000 Volts AC  
Bright red glow indicates AC voltage AND audio alert.

Part# 99001

*Note: Before using the AC Sensor or Ultimate AC Sensor, always test it on a known live voltage source to insure proper operation.*

**ULTRA-**  
**SIDEWINDER**  
CABLE PROTECTION SYSTEMS

- Articulating pieces offer flexible design - curves, corners and s-curves are easily made while maintaining a completely flat profile.
- Simple installation. No tools required.
- Available in black, yellow, brown, and gray.
- Fully customizable length - From 4.5" to an unlimited length.



*Please call for pricing information and part #*



**TEMPORARY  
CABLE  
GUARD**



The Temporary Cable Guard helps you restore services quickly, reduces truck rolls, and eliminates downtime due to traffic or roadway activities. Perfect for new construction pre-wiring or new installations too. Available in easy-to-use 5' sections. Accommodates cable up to .750 hard-line. Withstands heavy vehicle traffic without damaging cable. Can be produced in any length through special order. Easily anchored with concrete screws if needed.

**Racky Strap**

Versatile Utility Strap with a Firm Hold & Quick Release!

Features:

- Holds anything up to 33lb per sq. inch
- Quality hook and loop fastener with superior shear strength rating
- Double sided hook and loop may be used with soft side up or down
- Made with heavy duty Velcro
- Great for data cable
- Available in 1/2" x 12" and 1" x 12" strips



1" straps



1/2" straps



Part# RS1005 1/2"  
RS1010 1"

HOOP IT UP WITH  
**HANDI - HOOP**  
"BUY 'EM USE 'EM, LOVE 'EM!"



1. Use for cable management in Telecommunication
2. Used as guides and supports to organize existing runs or assisting with new installs.
3. Install to conform to NEC and local codes.
4. A smart Hand-Hoop pathway creates the condition whereby "one man pulls" can be accomplished.



Part# HH1010

**STUD  
BUDDIES**

Fits all Standard Steel Studs & Punches



- One piece
  - One hand installation
  - Fire rated V.O.
- Part# SB240

**STEEL STUD BUSHINGS**



- More cables, easier pulls
- Why Square Bushing?  
70% more cross sectional area!

Part# SB220



TAKE THE FIGHT  
OUT OF THOSE KO'S  
WITH KO KILLERS!



# KO Killers

## PLASTIC KNOCKOUT FILLERS



### Features:

- No tools required
  - Snap in with ease
  - Snap out with ease
  - Non-conductive, safer
- Part# **KOK Series**

Fits **thin** (1/32")  
and **thick** (1/8")  
wall thickness.

Available in 1/2"  
through 2" trade  
designations.

All thumbs? Good, because that's all you need to install our plastic KO Killers. Just pop'em in. No more tools, hammers, flying metal fillers, exploding buss bars, etc. Needing no tools is a big plus, especially when working space is tight.

## RAPID FIRE CONNECTORS

### RAT 500

1/2"

Part# RAT500



### RAT 750

3/4"

Part# RAT750




**FAST** – NO LOCKNUTS  
**EASY** – NO TOOLS REQUIRED

<b>RAT 750</b> 3/4"	Single Cables:	8/3, 6/3
<b>RAT 500</b> & <b>TT 500</b> 1/2"	Single Cables:	14/2, 14/3, 12/2, 12/3, 10/2, 10/3
	Two Cables:	14/2, 14/3, 12/2

## TT 500

## TOM TWO WAY



OLD WORK, NEW WORK  
INSTALLS FROM **INSIDE**  
OR **OUTSIDE** THE BOX



1/2"

Part# TT500

Doing some renovation work? The TT500 also installs from the inside of the box after the wire is fished in. Ingenious. The RAT500 and RAT750 feature the same quality and large wire capacity but install from the outside for use in new construction. If you like the best, try these.

## LEVEL JACK

## LOW VOLTAGE DATA/COM MUD RING




No tape measure • No level required

Available in 1/2", 5/8" and 1" rise

### HOW DOES IT WORK?

Alignment tabs reach across wood/metal studs to level low voltage outlets with A.C. boxes.



### EXTRA OFFSET:

- Allows use of all standard fittings
- Reduces A.C. interference to low voltage devices
- Improves drywall finish

Part# **LJ50R**  
**LJ58R**  
**LJ100R**

If you're fussy about your rough-in layout, the Level Jack makes life easy. If you're not, no one will notice because you can't screw up with the Level Jack. Just clip it on to the AC box and screw it down. No level, no tape measure, no special boxes, no special fittings required. Level Jacks fit most AC boxes. See the cartoon for details.



# VISIT US AT [WWW.RACK-A-TIERS.COM](http://WWW.RACK-A-TIERS.COM)

[FACEBOOK.COM/RACKATIERS](http://FACEBOOK.COM/RACKATIERS)

[TWITTER.COM/RACKATIERS](http://TWITTER.COM/RACKATIERS)

[YOUTUBE.COM/RACKATIERS](http://YOUTUBE.COM/RACKATIERS)



## JOIN OUR MAILING LIST AND RECIEVE:

- LATEST PRODUCT NEWS
- SPECIAL OFFERS
- TIPS & TRICKS
- CONTESTS
- CARTOONS
- NEWS ABOUT OUR **NEW** REWARDS PROGRAM!

# RackRewards

CONTRACTOR REWARDS PROGRAM

COMING SOON



[www.rack-a-tiers.com/rewards](http://www.rack-a-tiers.com/rewards)

 **Tools Invented by Electricians Just Like You.**  
**Have an Idea? ...Yours could be Next.**