



**PRODUCT
SUPPLEMENT**
JANUARY 2018

FD



Table of Contents

2 PICTORIAL INDEX
7 WHAT'S YOUR STYLE?
16 FIXTURE COLLECTIONS

56 PENDANTS

57 CLOSE-TO-CEILING



62 BATH COLLECTIONS

80 OUTDOOR



93 UTILITY
96 INDEX

FIXTURE COLLECTIONS

ANJOUX
Silver Ridge p.17



ANJOUX
Antique Bronze p.19



ANJOUX
Silver Ridge p.17



ANJOUX
Antique Bronze p.19



CARISA
Brushed Nickel p.42



CARISA
Vintage Gold p.44



CONESTEE
Galvanized p.26



CONESTEE
Graphite p.28



DOMAIN
Black p.46



GULLIVER
Galvanized Finish p.31



GULLIVER
Graphite p.31



JUDSON
Antique Bronze p.38



JUDSON
Polished Nickel p.40



LAIRD
Brushed Nickel p.48



LAIRD
Antique Bronze p.50



LITCHFIELD
Polished Chrome p.24



TILLEY
Brushed Nickel p.32



TILLEY
Antique Bronze p.34



TINSLEY
Brushed Bronze p.20



TINSLEY
Polished Chrome p.22



PENDANTS

ANJOUX
Silver Ridge p.17



ANJOUX
Antique Bronze p.19



APOGEE
Brushed Nickel p.52



APOGEE
Architectural Bronze p.54



CENTRE
White p.36



CENTRE
Antique Bronze p.37



CONESTEE
Galvanized Finish p.27



CONESTEE
Graphite p.29



GATHER
Brushed Nickel p.57



GATHER
Antique Bronze p.57



GATHER
Polished Chrome p.57



GULLIVER
Galvanized Finish p.31



GULLIVER
Galvanized Finish p.30



GULLIVER
Graphite p.31



JUDSON
Antique Bronze p.39



JUDSON
Polished Nickel p.41



LAIRD
Brushed Nickel p.49



LAIRD
Antique Bronze p.51



LITCHFIELD
Polished Chrome p.25



NEAT
Brushed Nickel p.56



NEAT
Antique Bronze p.56



TILLEY
Antique Bronze p.33



TILLEY
Antique Bronze p.35



TINSLEY
Brushed Bronze p.21



TINSLEY
Polished Chrome p.23



SCONCES / WALL BRACKETS

ANJOUX
Antique Bronze p.62



ANJOUX
Silver Ridge p.63



APOGEE
Brushed Nickel p.53



APOGEE
Architectural Bronze p.55



CARISA
Brushed Nickel p.70



CARISA
Vintage Gold p.71



CIRCUIT
Brushed Nickel p.73



CIRCUIT
Polished Chrome p.73



DART
Graphite p.64



DOMAIN
Black p.69



GULLIVER
Galvanized p.66



GULLIVER
Graphite p.67



INDEX
Brushed Nickel p.76



INDEX
Black p.76



JUDSON
Antique Bronze p.68



JUDSON
Polished Nickel p.68



LEAP
Antique Bronze p.77



LEAP
Brushed Nickel p.77



LITCHFIELD
Polished Chrome p.25



LITCHFIELD
Polished Chrome p.65



LAIRD
Antique Bronze p.78



LAIRD
Brushed Nickel p.79



TINSLEY
Brushed Bronze p.21



TINSLEY
Brushed Bronze p.23



BATH COLLECTIONS

ANJOUX
Antique Bronze p.62



ANJOUX
Silver Ridge p.63



BALANCE LED
Brushed Nickel p.72



CARISA
Brushed Nickel p.70



CARISA
Vintage Gold p.71



CIRCUIT
Brushed Nickel p.73



CIRCUIT
Polished Chrome p.73



CONCOURSE
Brushed Nickel p.74



DART
Galvanized Finishl p.64



DOMAIN
Black p.69



GULLIVER
Galvanized Finish p.66



GULLIVER
Graphite p.67



INDEX
Brushed Nickel p.76



INDEX
Textured Black p.76



JUDSON
Antique Bronze p.68



JUDSON
Brushed Nickel p.68



LAIRD
Antique Bronze p.78



LAIRD
Brushed Nickel p.79



LEAP
Brushed Nickel p.77



LEAP
Antique Bronze p.77



LITCHFIELD
Polished Chrome p.65



PONDER
Antique Bronze p.75



PONDER
Graphite p.75



OUTDOOR

3" CYLINDERS

Antique Bronze p.89



3" CYLINDERS

White p.89



3" CYLINDERS

Graphite p.89



3" CYLINDERS

Satin Nickel p.89



BARNETT

Antique Bronze p.80



CONOVER

Antique Bronze p.84



CONOVER

Antique Pewter p.85



GABLES

Textured Black p.88



GLOBE LANTERN

Textured Black p.88



GUNTHER

Antique Bronze p.87



HOLCOMBE

Black p.82



HOLLINGSWORTH

Black p.83



LAINÉ

Architectural Bronze p.81



MCPHERSON

Black p.86



PIER 33

Black p.88



STRATA

White p.91



STRATA

Black p.91



STRATA

Metallic Gray p.91



STRATA

Antique Bronze p.91



Z-1050

Black p.90



Z-1060

Black p.90




What's Your Style?



DISCOVER AFFORDABLE LUXURY LIGHTING FOR EVERY BUDGET & STYLE.

One of today's most popular design trends encourages individuals to create unique lighting designs by mixing and matching their favorite fixtures within the same space. There is no need to feel limited by fixtures or finishes in one particular collection!



ALLOW SPHERES TO SET THE SCENE

Conestee pendant groupings serve as an attractive alternative to the traditional bedside lamps, while also providing a timeless look to this modern master suite.

The cool metal tones in both Conestee and Circuit collections complement the handcrafted modern furniture and wood flooring, ultimately creating an inviting and relaxing room to retreat to at the end of a long day.





Featuring Tinsley chandelier and Design Series Carlyn wall brackets.



GET COZY WITH A HINT OF GLAM

Celebrate a new addition's grand entrance with a nursery to match! Designers today are incorporating sophisticated and simple elements to create magical settings for children.

The furniture selection carries a monochromatic color scheme, while floral accents and textured accessories add character to the space shown. Crystal finials in our Anjoux collection pair perfectly with Carlyn's luxurious pattern and glass accents to create a gorgeous nursery with a touch of glam.

DELIVER TIMELESS APPEAL

Warm and inviting, this open living space creates an environment that balances relaxation with elegance. Leather accessories and rich color tones complement Tinsley's frame finished in Brushed Bronze. Finally, our Barnett wall lanterns paired on either side of a vintage art piece deliver a timeless appeal.







Featuring Gulliver wall bracket and pendant and Tilley chandeliers and pendant.



ENJOY THE SEASIDE IN STYLE

Coastal-inspired décor features clean sophistication and a relaxed attitude, ideal for areas where friends and family tend to gather the most.

Gulliver's weathered accents and wood grained frame complement the organic furnishings and textured materials in this room setting. The look is completed with Tilley's two-toned frame, which enhances the beach-inspired artwork and neutral color palette.

ANJOUX



P400087-134



A distinctive collection with casual crystal details. Each fixture in the Anjoux family features variations of complementary designs. Sconces are highlighted by clear waterglass shades, while chandeliers are adorned by elegant crystal finials. A flushmount version features cascading crystal teardrop accents.

FINISHES

- Antique Bronze - 020
- Silver Ridge - 134

ALSO AVAILABLE IN

Bath & Vanity, page 62



P500100-134

P400087-134
shown with
P860007-000
shade**WALL BRACKET**

P300116-134 Silver Ridge
5" W., 8-5/8" ht.
Extends 6-7/8". H/CTR 4-1/2".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE

P350094-134 Silver Ridge
Hanging and ceiling mount
hardware included.
14-1/2" dia., 17-1/2" ht.
Overall ht. w/chain 53", wire 10'.
Three candelabra lamps,
each 60w max.

FIVE-LIGHT FLUSH MOUNT

P350096-134 Silver Ridge
16" dia., 14" ht.
Five candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400087-134 Silver Ridge
24-5/8" dia., 26-1/2" ht.
Overall ht. w/chain 100-1/2", wire 15'.
Five candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400088-134 Silver Ridge
34" dia., 34" ht.
Overall ht. w/chain 156", wire 15'.
Nine candelabra lamps,
each 60w max.

FOUR-LIGHT FOYER PENDANT

P500099-134 Silver Ridge
16" dia., 24" ht.
Overall ht. w/chain 98", wire 15'.
Extends 15-3/4".
Four candelabra lamps,
each 60w max.

SIX-LIGHT FOYER

P500100-134 Silver Ridge
22" dia., 30" ht.
Overall ht. w/chain 104-1/2", wire 15'.
Six candelabra lamps,
each 60w max.

ACCESSORY SHADE

P860007-000 Ivory Silk
1" uno-style candle fitter
5-3/4" dia., 4-1/2" ht.



P350094-134

P350096-134



P300116-134



P860007-000



P500099-134

P400088-134
shown with
P860007-000
shade



P400087-020



P500100-020



P400087-020
shown with
P860008-000
shade

WALL BRACKET

P300116-020 Antique Bronze
5" W., 8-5/8" ht.
Extends 6-7/8". H/CTR 4-1/2".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE

P350094-020 Antique Bronze
Hanging and ceiling mount
hardware included.
14-1/2" dia., 17-1/2" ht.
Overall ht. w/chain 53", wire 10'.
Three candelabra lamps,
each 60w max.

FIVE-LIGHT FLUSH MOUNT

P350096-020 Antique Bronze
16" dia., 14" ht.
Five candelabra lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400087-020 Antique Bronze
24-5/8" dia., 26-1/2" ht.
Overall ht. w/chain 100-1/2", wire 15'.
Five candelabra lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400088-020 Antique Bronze
34" dia., 34" ht.
Overall ht. w/chain 156", wire 15'.
Nine candelabra lamps,
each 60w max.

FOUR-LIGHT FOYER PENDANT

P500099-020 Antique Bronze
16" dia., 24" ht.
Overall ht. w/chain 98", wire 15'.
Extends 15-3/4".
Four candelabra lamps,
each 60w max.

SIX-LIGHT FOYER

P500100-020 Antique Bronze
22" dia., 30" ht.
Overall ht. w/chain 104-1/2", wire 15'.
Six candelabra lamps,
each 60w max.

ACCESSORY SHADE

P860008-000 Vintage Linen
1" uno-style fitter
5-3/4" dia., 4-1/2" ht.



P350094-020



P350096-020



P300116-020



P860008-000



P500099-020



P400088-020

TINSLEY



P400066-109



Featuring soft angles and impressive sculptural curves, Tinsley is a refreshingly updated design for Luxe, Transitional and Traditional interiors. The frame is complemented by classic etched glass shades or open candle designs. Overscale details found in Tinsley are ideal for welcoming guests and visitors in a foyer or entryway, as well as in luxe dining room or classic living room settings.

FINISH

- Polished Chrome - 015
- Brushed Bronze - 109



P500062-109



P400067-109

SEMI-FLUSH CONVERTIBLE P350079-109 Brushed Bronze Hanging and ceiling mount hardware included. 16-1/2" dia., 11-1/2" ht. Overall ht. w/chain 51", wire 10'. Two medium base lamps, each 100w max.

TWO-LIGHT FLUSH MOUNT P350103-109 Brushed Bronze 16-1/2" dia., 5-7/8" ht. Two medium base lamps, each 60w max.

THREE-LIGHT CHANDELIER P400065-109 Brushed Bronze 23-1/2" dia., 19" ht. Overall ht. w/chain 94", wire 15'. Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER P400066-109 Brushed Bronze 23" dia., 24" ht. Overall ht. w/chain 99", wire 15'. Five candelabra base lamps, each 60w max.

NINE-LIGHT CHANDELIER P400067-109 Brushed Bronze 29-1/4" dia., 31" ht. Overall ht. w/chain 154", wire 15'. Nine candelabra base lamps, each 60w max.

FIFTEEN-LIGHT CHANDELIER P400110-109 Brushed Bronze 42" dia., 41-3/4" ht. Overall ht. w/chain 154", wire 15'. Fifteen candelabra base lamps, each 60w max.

THREE-LIGHT PENDANT P500062-109 Brushed Bronze 22-1/2" dia., 22-1/2" ht. Overall ht. w/chain 97-1/2", wire 15'. Three medium base lamps, each 100w max.

MINI-PENDANT P500072-109 Brushed Bronze 7-1/2" dia., 12-1/2" ht. Overall ht. w/stem 80-1/2", wire 10'. One medium base lamp, 100w max.

WALL SCONCE P710028-109 Brushed Bronze 4-7/8" W., 15-1/2" ht. Extends 5-1/2". H/CTR 8". One candelabra base lamp, 100w max.



P400065-109



P350103-109



P350079-109



P400110-109



P500062-109



P710028-109



P400066-015

TINSLEY



P400065-015



P400067-015

SEMI-FLUSH CONVERTIBLE

P350079-015 Polished Chrome
Hanging and ceiling mount hardware included.
16-1/2" dia., 11-1/2" ht.
Overall ht. w/chain 51", wire 10'.
Two medium base lamps, each 100w max.

TWO-LIGHT FLUSH MOUNT

P350103-015 Polished Chrome
16-1/2" dia., 5-7/8" ht.
Two medium base lamps, each 60w max.

THREE-LIGHT CHANDELIER

P400065-015 Polished Chrome
23-1/2" dia., 19" ht.
Overall ht. w/chain 94", wire 15'.
Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER

P400066-015 Polished Chrome
23" dia., 24" ht.
Overall ht. w/chain 99", wire 15'.
Five candelabra base lamps, each 60w max.

NINE-LIGHT CHANDELIER

P400067-015 Polished Chrome
29-1/4" dia., 31" ht.
Overall ht. w/chain 154", wire 15'.
Nine candelabra base lamps, each 60w max.

FIFTEEN-LIGHT CHANDELIER

P400110-015 Polished Chrome
42" dia., 41-3/4" ht.
Overall ht. w/chain 154", wire 15'.
Fifteen candelabra lamps, each 60w max.

THREE-LIGHT PENDANT

P500062-015 Polished Chrome
22-1/2" dia., 22-1/2" ht.
Overall ht. w/chain 97-1/2", wire 15'.
Three medium base lamps, each 100w max.

MINI-PENDANT

P500072-015 Polished Chrome
7-1/2" dia., 12-1/2" ht.
Overall ht. w/stem 80-1/2", wire 10'.
One medium base lamp, 100w max.

WALL SCONCE

P710028-015 Polished Chrome
4-7/8" W., 15-1/2" ht.
Extends 5-1/2". H/CTR 8".
One candelabra lamp, 100w max.



P500062-015



P350103-015



P350079-015



P400110-015



P500072-015



P710028-015

LITCHFIELD



P400103-015



A casual, coastal-inspired collection. Litchfield features an hourglass-inspired column complemented by a crisp Chrome finish.

FINISH

● Polished Chrome - 015

ALSO AVAILABLE IN

Bath & Vanity, page 65

P500113-015



P350093-015



**SEMI-FLUSH CONVERTIBLE
P350093-015** Polished Chrome
Hanging and ceiling mount
hardware included.
18" dia., 14-3/4" ht.
Overall ht. w/chain 52", wire 10'.
Extends 14-3/4".
Three medium base lamps,
each 60w max.

P500114-015



P400102-015
shown with
P860027-000
shade



**THREE-LIGHT CHANDELIER
P400102-015** Polished Chrome
19-3/8" dia., 22-1/8" ht.
Overall ht. w/chain 96-1/2", wire 15'.
Three candelabra lamps,
each 60w max.

**FIVE-LIGHT CHANDELIER
P400103-015** Polished Chrome
25-7/8" dia., 21-7/8" ht.
Overall ht. w/chain 97", wire 15'.
Five candelabra lamps,
each 60w max.

**NINE-LIGHT CHANDELIER
P400104-015** Polished Chrome
34" dia., 32-1/2" ht.
Overall ht. w/chain 155-1/2", wire 15'.
Nine candelabra lamps,
each 60w max.

**MINI-PENDANT
P500113-015** Polished Chrome
4-3/4" dia., 9-3/8" ht.
Overall ht. w/stem 75-1/2", wire 10'.
One medium base lamp,
60w max.

**THREE-LIGHT PENDANT
P500114-015** Satin Aluminum
13-5/8" dia., 18" ht.
Overall ht. w/stem 84", wire 15'.
Three candelabra lamps,
each 60w max.

**WALL BRACKET
P710044-015** Polished Chrome
5" W., 13" ht. Extends 14-1/2".
Adjustable arm
One medium base lamp,
60w max.

**ACCESSORY SHADE
P860027-000** White Sailcloth
1" uno-style candle fitter
6-3/4" dia., 5" ht.



P860027-000



P710044-015
shown above
and below with
adjustable arm

P400104-015



CONESTEE



P500094-141



The Conestee collection features a stunning armillary-style frame. Dual tone finish combinations are hand painted Galvanized with antique white accents or Graphite with weathered gray accents. While Conestee is ideal for Rustic Farmhouse or Urban Industrial home environments, it can also be paired with a number of Coastal-inspired fixtures to complement natural wood materials.

FINISHES

- Galvanized - 141
- Graphite - 143

MINI-PENDANT

P500092-141 Galvanized
12" dia., 14" ht.
Overall ht. w/chain 89", wire 10'.
One medium base lamp,
60w max.

THREE-LIGHT PENDANT

P500093-141 Galvanized
21-1/4" dia., 24" ht.
Overall ht. w/chain 99", wire 15'.
Three medium base lamps,
each 60w max.

SIX-LIGHT PENDANT

P500094-141 Galvanized
28" dia., 30-3/4" ht.
Overall ht. w/chain 106", wire 15'.
Six medium base lamps,
each 60w max.

*Fixtures shown with P7825-01
vintage lamps*





P500094-143



P500094-143

MINI-PENDANT

P500092-143 Graphite
12" dia., 14" ht.
Overall ht. w/chain 89", wire 10'.
One medium base lamp,
60w max.

THREE-LIGHT PENDANT

P500093-143 Graphite
21-1/4" dia., 24" ht.
Overall ht. w/chain 99", wire 15'.
Three medium base lamps,
each 60w max.

SIX-LIGHT PENDANT

P500094-143 Graphite
28" dia., 30-3/4" ht.
Overall ht. w/chain 106", wire 15'.
Six medium base lamps,
each 60w max.

*Fixtures shown with P7825-01
vintage lamps*



P500092-143



P500093-143

GULLIVER



P500023-141



Three circular bands wrap together to create an open design for Gulliver. Dual toned frame color combinations are hand painted Galvanized with antique white accents or Graphite with weathered gray accents. A hand painted wood grained texture complements Rustic and Modern Farmhouse home décor, as well as Urban Industrial and Coastal interior settings.

FINISHES

- Galvanized - 141
- Graphite - 143

ALSO AVAILABLE IN

Bath & Vanity, page 66
See complete collection:
ProgressLighting.com



P350049-141



P500022-141

SEMI-FLUSH CONVERTIBLE

P350049-141 Galvanized
Hanging and ceiling mount
hardware included.
17" dia., 13-1/2" ht.
Overall ht. w/chain 52-1/2", wire 10'.
Three medium base lamps,
each 75w max.

FOUR-LIGHT LINEAR CHANDELIER

P400097-141 Galvanized
P400097-143 Graphite
38-1/2" W., 10-1/2" L., 17" ht.
Overall ht. w/chain 91-1/2", wire 15'.
Extends 10-1/2".
Four medium base lamps,
each 75w max.



P400097-141

MINI-PENDANT

P500022-141 Galvanized
8-1/2" dia., 10" ht.
Overall ht. w/chain 85", wire 10'.
One medium base lamp,
75w max.



P710031-141

FOUR-LIGHT PENDANT

P500023-141 Galvanized
21-5/8" dia., 18-1/4" ht.
Overall ht. w/chain 93-1/2", wire 10'.
Four medium base lamps,
each 75w max.



P400097-143

FIVE-LIGHT PENDANT

P500090-141 Galvanized
P500090-143 Graphite
27-3/4" dia., 22-3/4" ht.
Overall ht. w/chain 93-1/2", wire 10'.
Five medium base lamps,
each 75w max.



P710031-143

WALL BRACKET

P710031-141 Galvanized
P710031-143 Graphite
6" dia., 12" ht.
Extends 7". H/CTR 9-3/8".
One medium base lamp, 75w max.



P500090-143



P500090-141

*Fixtures shown with P7825-01
vintage lamps*

TILLEY



P400074-009



Rustic and vintage décor is a popular trend that can transform a home into a nostalgic retreat. Tilley features warehouse style shades formed from metal mesh that merge with a faux-painted, wooden rim for an artful yet Industrial style.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ALSO AVAILABLE IN

Bath & Vanity, visit:
ProgressLighting.com

**THREE-LIGHT CHANDELIER**

P400073-009 Brushed Nickel
20" dia., 15-1/4" ht.
Overall ht. w/chain 90-1/2", wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P400074-009 Brushed Nickel
24" dia., 16-7/8" ht.
Overall ht. w/stem 92", wire 15'.
Five medium base lamps,
each 100w max.

MINI-PENDANT

P500078-009 Brushed Nickel
8" dia., 7-1/2" ht.
Overall ht. w/stem 73-1/2", wire 10'.
One medium base lamp,
100w max.

THREE-LIGHT PENDANT

P500079-009 Brushed Nickel
16" dia., 10-7/8" ht.
Overall ht. w/stem 77", wire 120'.
Three medium base lamps,
each 60w max.

THREE-LIGHT FLUSH MOUNT

P350091-009 Brushed Nickel
16" dia., 9-7/8" ht.
Three medium base lamps,
each 60w max.

*Fixtures shown with P7825-01
vintage lamps*



P500078-009



P500079-009



P350091-009





P400074-020



P400074-020

THREE-LIGHT CHANDELIER
P400073-020 Antique Bronze
 20" dia., 15-1/4" ht.
 Overall ht. w/chain 90-1/2", wire 15'.
 Three medium base lamps,
 each 100w max.

FIVE-LIGHT CHANDELIER
P400074-020 Antique Bronze
 24" dia., 16-7/8" ht.
 Overall ht. w/chain 92", wire 15'.
 Five medium base lamps,
 each 100w max.

MINI-PENDANT
P500078-020 Antique Bronze
 8" dia., 7-1/2" ht.
 Overall ht. w/stem 73-1/2", wire 10'.
 One medium base lamp,
 100w max.

THREE-LIGHT PENDANT
P500079-020 Antique Bronze
 16" dia., 10-7/8" ht.
 Overall ht. w/stem 77", wire 120'.
 Three medium base lamps,
 each 60w max.

THREE-LIGHT FLUSH MOUNT
P350091-020 Antique Bronze
 16" dia., 9-7/8" ht.
 Three medium base lamps,
 each 60w max.

*Fixtures shown with P7825-01
 vintage lamps*



P400073-020



P500078-020



P500079-020




P350091-020

CENTRE



P500112-030



A beautiful and elegant geometric frame is the highlight of the Centre collection. A striking dual-tone finish heightens the elegance of these modern pendants. Hang individually or pair in groupings over dining room tables or kitchen islands to create a dramatic focal point in the home.

FINISHES

- Antique Bronze - 020
- White - 030



P350108-020
Shown as semi-flush



P350108-030
Shown as semi-flush

SEMI-FLUSH CONVERTIBLE
P350108-020 Antique Bronze
P350108-030 White

Hanging and ceiling mount hardware included.
16" sq., 11-7/8" ht.
Overall ht. w/stem 78", wire 10'.
Four medium base lamps, each 100w max.



P350108-020
Shown as pendant



P350108-030
Shown as pendant

FOUR-LIGHT PENDANT

P500111-020 Antique Bronze
P500111-030 White
20" Sq., 13-3/4" ht.
Overall ht. w/stem 80", wire 15'.
Four medium base lamps, each 100w max.



P500111-020



P500111-030

SIX-LIGHT PENDANT

P500112-020 Antique Bronze
P500112-030 White
30" Sq., 18-3/4" ht.
Overall ht. w/stem 85", wire 15'.
Six medium base lamps, each 100w max.

Fixtures shown with P7825-01 vintage lamps



P500112-020



P500112-020

JUDSON



P400058-020



The Judson collection features a timeless clear schoolhouse-style globe. Metal fittings add distinction to complete the vintage look. Available in hanging, wall and ceiling styles, Judson provides the perfect compliment to farmhouse or coastal-inspired homes.

FINISHES

- Antique Bronze - 020
- Polished Nickel - 104

ALSO AVAILABLE IN

Bath & Vanity, page 68



ONE-LIGHT FLUSH MOUNT
P350074-020 Antique Bronze
 11" dia., 12" ht.
 One medium base lamp,
 75w max.

THREE-LIGHT CHANDELIER
P400057-020 Antique Bronze
 22" dia., 18-1/4" ht.
 Overall ht. w/chain 91-1/2", wire 15'.
 Three medium base lamps,
 each 75w max.

FIVE-LIGHT CHANDELIER
P400058-020 Antique Bronze
 26" dia., 19" ht.
 Overall ht. w/chain 92-1/2", wire 15'.
 Five medium base lamps,
 each 75w max.

ONE-LIGHT PENDANT
P500061-020 Antique Bronze
 11" dia., 11-1/4" ht.
 Overall ht. w/stem 78", wire 10'.
 One medium base lamp,
 75w max.

*Fixtures shown with P7825-01
 vintage lamps, except P350074*





P400058-104



ONE-LIGHT FLUSH MOUNT
P350074-104 Polished Nickel
11" dia., 12" ht.
One medium base lamp,
75w max.

THREE-LIGHT CHANDELIER
P400057-104 Polished Nickel
22" dia., 18-1/4" ht.
Overall ht. w/chain 91-1/2", wire 15'.
Three medium base lamps,
each 75w max.

FIVE-LIGHT CHANDELIER
P400058-104 Polished Nickel
26" dia., 19" ht.
Overall ht. w/chain 92-1/2", wire 15'.
Five medium base lamps,
each 75w max.

ONE-LIGHT PENDANT
P500061-104 Polished Nickel
11" dia., 11-1/4" ht.
Overall ht. w/stem 78", wire 10'.
One medium base lamp,
75w max.


*Fixtures shown with P7825-01
vintage lamps, except P350074*



CARISA



P400060-009



Inspired by the revival of Mid-Century fashions, the Carisa collection brings home this classic style. A metallic finish supports glossy white opal glass globes to create a timeless modern design.

FINISHES

- Brushed Nickel - 009
- Vintage Gold - 078

ALSO AVAILABLE IN

Bath & Vanity, page 70



P400061-009

WALL BRACKET

P300084-009 Brushed Nickel
6-1/2" W., 10" ht.
Extends 8-1/2". H/CTR 4-5/8".
One medium base lamp,
75w max.

ONE-LIGHT FLUSH MOUNT

P350075-009 Brushed Nickel
7-3/8" dia., 8-3/4" ht.
One medium base lamp,
each 75w max.

THREE-LIGHT CHANDELIER

P400059-009 Brushed Nickel
21-1/2" dia., 17-1/2" ht.
Overall ht. w/stem 83-1/2", wire 15'.
Three medium base lamps,
each 75w max.

FIVE-LIGHT CHANDELIER

P400060-009 Brushed Nickel
25-1/2" dia., 20-3/4" ht.
Overall ht. w/stem 86-1/2", wire 15'.
Five medium base lamps,
each 75w max.

NINE-LIGHT CHANDELIER

P400061-009 Brushed Nickel
31-1/2" dia., 36-1/2" ht.
Overall ht. w/stem 102-1/2", wire 15'.
Nine medium base lamps,
each 75w max.



P400060-009



P350075-009



P300084-009



P400059-009



P400060-078



P400061-078

WALL BRACKET

P300084-078 Vintage Gold
6-1/2" W., 10" ht.
Extends 8-1/2". H/CTR 4-5/8".
One medium base lamp,
75w max.

ONE-LIGHT FLUSH MOUNT

P350075-078 Vintage Gold
7-3/8" dia., 8-3/4" ht.
One medium base lamp,
each 75w max.

THREE-LIGHT CHANDELIER

P400059-078 Vintage Gold
21-1/2" dia., 17-1/2" ht.
Overall ht. w/stem 83-1/2", wire 15'.
Three medium base lamps,
each 75w max.

FIVE-LIGHT CHANDELIER

P400060-078 Vintage Gold
25-1/2" dia., 20-3/4" ht.
Overall ht. w/stem 86-1/2", wire 15'.
Five medium base lamps,
each 75w max.

NINE-LIGHT CHANDELIER

P400061-078 Vintage Gold
31-1/2" dia., 36-1/2" ht.
Overall ht. w/stem 102-1/2", wire 15'.
Nine medium base lamps,
each 75w max.



P400060-078



P350075-078



P300084-078



P400059-078

DOMAIN



P400035-031



A sensible, yet sophisticated, lighting collection rooted in updated classical modern styling. Suitable for Urban Industrial, Modern and Mid-Century Modern interiors, Domain features a Matte Black finish. A double ring accent and squared off socket holder complement over scale etched glass shades.

FINISH

● Black - 031

ALSO AVAILABLE IN

Bath & Vanity, page 74

THREE-LIGHT CHANDELIER

P400034-031 Black
22-3/8" dia., 15-3/8" ht.
Overall ht. w/stem 81-1/2", wire 15'.
Three medium base lamps,
each 100w max.

FOUR-LIGHT CHANDELIER

P400035-031 Black
29" dia., 19" ht.
Overall ht. w/stem 85", wire 15'.
Four medium base lamps,
each 100w max.

SIX-LIGHT CHANDELIER

P400036-031 Black
Two-tier.
32" dia., 24" ht.
Overall ht. w/stem 90", wire 15'.
Six medium base lamps,
each 100w max.



LAIRD



P400063-009

The Laird collection provides a contemporary complement to casual interiors popular in today's homes. Glass shades add distinction and provide pleasing illumination to any room, while scrolling arms create an airy effect.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ALSO AVAILABLE IN

Bath & Vanity, page 78

FIVE-LIGHT CHANDELIER

P400063-009 Brushed Nickel
23-3/4" dia., 17-1/2" ht.
Overall ht. w/chain 61-1/2", wire 9.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P400064-009 Brushed Nickel
27-3/4" dia., 25-1/2" ht.
Overall ht. w/chain 65", wire 12".
Nine medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER

P400062-009 Brushed Nickel
19-3/4" dia., 16" ht.
Overall ht. w/chain 60", wire 9.
Three medium base lamps,
each 100w max.

SEMI-FLUSH CONVERTIBLE

P350057-009 Brushed Nickel
Hanging and ceiling mount
hardware included.
13" dia., 9-7/8" ht.
Overall ht. w/chain 55", wire 10".
Extends 9-7/8".
Two medium base lamps,
each 100w max.

THREE-LIGHT PENDANT

P500071-009 Brushed Nickel
17" dia., 20-3/4" ht.
Overall ht. w/chain 87-1/2", wire 9.
Three medium base lamps,
each 100w max.





P400063-020



P400064-020

FIVE-LIGHT CHANDELIER

P400063-020 Antique Bronze
23-3/4" dia., 17-1/2" ht.
Overall ht. w/chain 61-1/2", wire 9.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P400064-020 Antique Bronze
27-3/4" dia., 25-1/2" ht.
Overall ht. w/chain 65", wire 12'.
Nine medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER

P400062-020 Antique Bronze
19-3/4" dia., 16" ht.
Overall ht. w/chain 60", wire 9.
Three medium base lamps,
each 100w max.

SEMI-FLUSH CONVERTIBLE

P350057-020 Antique Bronze
Hanging and ceiling mount
hardware included.
13" dia., 9-7/8" ht.
Overall ht. w/chain 55", wire 10'.
Extends 9-7/8".
Two medium base lamps,
each 100w max.



P500071-020



P400063-020

THREE-LIGHT PENDANT

P500071-020 Antique Bronze
17" dia., 20-3/4" ht.
Overall ht. w/chain 87-1/2", wire 9.
Three medium base lamps,
each 100w max.



P350057-020

P350057-009



P400062-020

APOGEE



P350066-009-30

Designed for both commercial and residential interiors, Apogee fixtures deliver both style and bright illumination. The collection includes flush mount and pendant options that can also be installed as a semi-flush mount fixture. All fixtures feature 120-277V input with standard 0-10V dimming. Etched glass shade provides an even and pleasing light effect.

FINISHES

- Brushed Nickel - 009
- Architectural Bronze - 129



P350065-009-30



P710036-009-30

SEMI-FLUSH CONVERTIBLE

P350064-009-30 Brushed Nickel
Hanging and ceiling mount hardware included.
15" dia., 10-3/4" ht.
Overall ht. w/chain 85-1/4, wire 15'.
30w integrated LED, 3000K, 90CRI, 1855 lumens.

P350064-009-30
*shown as semi-flush***SEMI-FLUSH CONVERTIBLE**

P350065-009-30 Brushed Nickel
Hanging and ceiling mount hardware included.
21" dia., 14-1/2" ht.
Overall ht. w/chain 92", wire 15'.
45w integrated LED, 3000K, 90CRI, 2765 lumens.



P350066-009-30

P350064-009-30
*shown as pendant***SEMI-FLUSH CONVERTIBLE**

P350066-009-30 Brushed Nickel
Hanging and ceiling mount hardware included.
27" dia., 20-5/8" ht.
Overall ht. w/chain 98, wire 15'.
71w integrated LED, 3000K, 90CRI, 4215 lumens.



P350071-009-30



P350070-009-30

FLUSH MOUNT

P350070-009-30 Brushed Nickel
15" dia., 3-11/16" ht. , wire 8".
30w integrated LED, 3000K, 90CRI, 1660 lumens.

**FLUSH MOUNT**

P350071-009-30 Brushed Nickel
21" dia., 4-1/2" ht.
45w integrated LED, 3000K, 90CRI, 2550 lumens.

**FLUSH MOUNT**

P350072-009-30 Brushed Nickel
27" dia., 5-3/8" ht.
71w integrated LED, 3000K, 90CRI, 3850 lumens.



P350072-009-30

WALL SCNCE

P710036-009-30 Brushed Nickel
15" W., 7-1/2" ht., 3-11/16" extends or depth.
20w integrated LED, 3000K, 90CRI, 940 lumens.





P350066-129-30



SEMI-FLUSH CONVERTIBLE
P350064-129-30 Architectural Bronze
 Hanging and ceiling mount hardware included.
 15" dia., 10-3/4" ht.
 Overall ht. w/chain 85-1/4, wire 15'.
 30w integrated LED, 3000K, 90CRI, 1855 lumens.



SEMI-FLUSH CONVERTIBLE
P350065-129-30 Architectural Bronze
 Hanging and ceiling mount hardware included.
 21" dia., 14-1/2" ht.
 Overall ht. w/chain 92", wire 15'.
 45w integrated LED, 3000K, 90CRI, 2765 lumens.



SEMI-FLUSH CONVERTIBLE
P350066-129-30 Architectural Bronze
 Hanging and ceiling mount hardware included.
 27" dia., 20-5/8" ht.
 Overall ht. w/chain 98, wire 15'.
 71w integrated LED, 3000K, 90CRI, 4215 lumens.



FLUSH MOUNT
P350070-129-30 Architectural Bronze
 15" dia., 3-11/16" ht. , wire 8".
 30w integrated LED, 3000K, 90CRI, 1660 lumens.



FLUSH MOUNT
P350071-129-30 Architectural Bronze
 21" dia., 4-1/2" ht.
 45w integrated LED, 3000K, 90CRI, 2550 lumens.



FLUSH MOUNT
P350072-129-30 Architectural Bronze
 27" dia., 5-3/8" ht.
 71w integrated LED, 3000K, 90CRI, 3850 lumens.



WALL SCONCE
P710036-129-30 Architectural Bronze
 15" W., 7-1/2" ht., Extends 3-11/16".
 20w integrated LED, 3000K, 90CRI, 940 lumens.



NEAT LED

These timeless and classic LED pendants feature designer oriented details and polished opal glass. Can be displayed singularly or in groupings of two or more in a variety of spaces, such as Modern Farmhouse, Coastal and Mid-Century Modern environments.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ONE-LIGHT PENDANT

P500065-009-30 Brushed Nickel

P500065-020-30 Antique Bronze

4-3/8" dia., 13-1/2" ht.

Overall ht. W/Cord 124-1/2", wire 10'.

One 9w LED module, 3000K, 90CRI, 624 lumens.



ONE-LIGHT PENDANT

P500066-009-30 Brushed Nickel

P500066-020-30 Antique Bronze

6-5/8" dia., 13-1/2" ht.

Overall ht. W/Cord 124-1/2", wire 10'.

One 9w LED module, 3000K, 90CRI, 624 lumens.



PROGRESS **LED**





P350080-015-30

GATHER LED

Simplified frame with updated styling and elegant etched glass shades. Energy efficient version is available with select fixtures in the Brushed Nickel finish.

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Antique Bronze - 020

ALSO AVAILABLE IN

See complete collection:
ProgressLighting.com

SEMI-FLUSH CONVERTIBLE

P350088-009-30 Brushed Nickel
P350088-015-30 Polished Chrome
P350088-020-30 Antique Bronze
 Hanging and ceiling mount hardware included.
 12-7/8" dia., 10-3/8" ht.
 Overall ht. w/chain 50", wire 10".
 One 17w LED module, 3000K, 90CRI, 1276 lumens.



PROGRESS **LED**

FORTUNE LED

Fortune LED flush mount fixtures feature beautiful opal glass in an elegant form. The frame and metal fittings are finished in Polished Chrome. Fortune LED offers simple, clean lines to coordinate with Luxe, Transitional and Coastal interiors.

FINISH

- Polished Chrome - 015

ALSO AVAILABLE IN

See complete collection:
ProgressLighting.com

ONE-LIGHT FLUSH MOUNT

P350080-015-30 Polished Chrome
 16" dia., 7-5/8" ht.
 One 17w LED module 3000K, 90CRI, 1452 lumens.



PROGRESS **LED**

BEZEL LED



Featuring a sleek and slim appearance, Bezel LED is an architectural series of flush mount options. Etched white glass is accented by a metal trim in a metallic finish. The glass shade is illuminated on both the bottom and sides to provide a pleasing lighted effect.

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Antique Bronze - 020

ONE-LIGHT FLUSH MOUNT

P350085-009-30 Brushed Nickel
P350085-015-30 Polished Chrome
P350085-020-30 Antique Bronze
 10-1/2" dia., 3-1/2" ht.
 One 17w LED module, 3000K,
 90CRI, 1276 lumens.



ONE-LIGHT FLUSH MOUNT

P350086-009-30 Brushed Nickel
P350086-015-30 Polished Chrome
P350086-020-30 Antique Bronze
 13" dia., 3-7/8" ht.
 One 25w LED module, 3000K,
 90CRI, 1770 lumens.



P350085-009-30



P350086-009-30



P350085-015-30



P350086-015-30



P350085-020-30



P350086-020-30

PROGRESS **LED**

OPAL-LINEN LED



Opal-Linen LED features architectural details for a variety of home styles. A combination of glass textures work together to create an interesting effect for today's interiors. Metallic finishes complement the opal/linen double glass.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ONE-LIGHT FLUSH MOUNT

P350081-009-30 Brushed Nickel

P350081-020-30 Antique Bronze

12" dia., 4-3/4" ht.

One 17w LED module, 3000K,
90CRI, 1452 lumens.



ONE-LIGHT FLUSH MOUNT

P350082-009-30 Brushed Nickel

P350082-020-30 Antique Bronze

15" dia., 5" ht.

One 25w LED module, 3000K,
90CRI, 2015 lumens.



PROGRESS **LED**



P350081-020-30



P350082-020-30



P350081-009-30



P350082-009-30

LED FLUSH MOUNT

LED Flushmount offers traditional form factor for ambient illumination. The etched glass dominates the design with its distinctive and sculptural bowl. The elegant glass is paired with a metallic frame.

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Antique Bronze - 020

ALSO AVAILABLE IN

See complete collection:
ProgressLighting.com

ONE-LIGHT FLUSH MOUNT

P350100-009-30 Brushed Nickel

P350100-015-30 Polished Chrome

P350100-020-30 Antique Bronze

11" dia., 4-1/4" ht.

One 17w LED module, 3000K,
 90CRI, 1276 lumens.



P350100-009-30



P350101-009-30

ONE-LIGHT FLUSH MOUNT

P350101-009-30 Brushed Nickel

P350101-015-30 Polished Chrome

P350101-020-30 Antique Bronze

13-1/2" dia., 4-1/2" ht.

One 25w LED module, 3000K,
 90CRI, 1770 lumens.



P350100-015-30



P350101-015-30

PROGRESS **LED**



P350100-020-30



P350101-020-30

The Maier DC LED flush mounts feature an acrylic diffuser which twists into the frame so there are no exposed fasteners for a clean modern look.



P350078-030-30



P350076-030-30



P350077-030-30



P350078-009-30



P350076-009-30



P350077-009-30



P350078-020-30



P350076-020-30



P350077-020-30

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020
- White - 030

LED SEMI-FLUSH

P350076-009-30 Brushed Nickel
P350076-020-30 Antique Bronze
P350076-030-30 White
9-1/16" dia., 4-5/16" ht.
One 20.5w integrated LED, 3000K, 90CRI, 1354 lumens.



LED SEMI-FLUSH

P350077-009-30 Brushed Nickel
P350077-020-30 Antique Bronze
P350077-030-30 White
14" dia., 4-3/4" ht.
One 26w integrated LED, 3000K, 90CRI, 2016 lumens.



LED SEMI-FLUSH

P350078-009-30 Brushed Nickel
P350078-020-30 Antique Bronze
P350078-030-30 White
18" dia., 5-1/4" ht.
One 28.5w integrated LED, 3000K, 90CRI, 2064 lumens.



PROGRESS **LED**

ANJOUX



P300117-020

A distinctive collection with casual crystal details. Each fixture in the Anjoux family features variations of complementary designs. Sconces are highlighted by clear waterglass shades, while chandeliers are adorned by elegant crystal finials.

FINISHES

- Antique Bronze - 020
- Silver Ridge - 134

ALSO AVAILABLE IN

Fixture Collections, page 16

ONE-LIGHT BATH

P300116-020 Antique Bronze
5" W., 8-5/8" ht.
Extends 6-7/8". H/CTR 4-1/2".
One medium base lamp,
100w max.



P300116-020

TWO-LIGHT BATH

P300117-020 Antique Bronze
14" W., 7-1/2" ht.
Extends 6-7/8". H/CTR 5".
Two medium base lamps,
each 100w max.

P300118-020
mounted down

THREE-LIGHT BATH

P300118-020 Antique Bronze
23" W., 7-1/2" ht.
Extends 7". H/CTR 5".
Three medium base lamps,
each 100w max.



P300119-020

FOUR-LIGHT BATH

P300119-020 Antique Bronze
32" W., 7-1/2" ht.
Extends 7". H/CTR 5".
Four medium base lamps,
each 100w max.



P300116-134

P300116-134
*mounted down***ONE-LIGHT BATH**

P300116-134 Silver Ridge
5" W., 8-5/8" ht.
Extends 6-7/8". H/CTR 4-1/2".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P300117-134 Silver Ridge
14" W., 7-1/2" ht.
Extends 6-7/8". H/CTR 5".
Two medium base lamps,
each 100w max.



P300117-134

P300117-134
*mounted down***THREE-LIGHT BATH**

P300118-134 Silver Ridge
23" W., 7-1/2" ht.
Extends 7". H/CTR 5".
Three medium base lamps,
each 100w max.



P300118-134

FOUR-LIGHT BATH

P300119-134 Silver Ridge
32" W., 7-1/2" ht.
Extends 7". H/CTR 5".
Four medium base lamps,
each 100w max.

Fixtures mount up or down.

P300119-134
mounted down

P300119-134

DART



P300145-143

Dart is a display of modern architectural design styling. Etched white glass shades balance on a striking arched frame. Subtle detailing is enhanced by a Graphite finish with Brushed Nickel accents.

FINISHES

- Graphite - 143

ONE-LIGHT BATH

P300144-143 Graphite
4-1/2" W., 16-7/8" ht.
Extends 6-7/8". H/CTR 8".
One medium base lamp,
100w max.



P300146-143

TWO-LIGHT BATH

P300145-143 Graphite
14-1/4" W., 7-7/8" ht.
Extends 6-7/8". H/CTR 5-5/8".
Two medium base lamps,
each 100w max.



P300144-143

THREE-LIGHT BATH

P300146-143 Graphite
23-5/8" W., 7-7/8" ht.
Extends 6-7/8". H/CTR 5-5/8".
Three medium base lamps,
each 100w max.



P300147-143

FOUR-LIGHT BATH

P300147-143 Graphite
33" W., 7-7/8" ht.
Extends 6-7/8". H/CTR 5-5/8".
Four medium base lamps,
each 100w max.

Fixtures mount up or down.

LITCHFIELD



P300138-015

A casual, coastal-inspired collection. Litchfield features an hourglass-inspired column complemented by a crisp Chrome finish.

FINISHES

- Polished Chrome - 015

ALSO AVAILABLE IN

Fixture Collections, page 24



P300137-015



P300139-015



P300140-015

ONE-LIGHT BATH

P300137-015 Polished Chrome
5" W., 9-1/4" ht.
Extends 7-3/8". H/CTR 5".
One medium base lamp,
60w max.

TWO-LIGHT BATH

P300138-015 Polished Chrome
15-3/8" W., 9-1/4" ht.
Extends 7-3/8". H/CTR 4-5/8".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH

P300139-015 Polished Chrome
24-3/8" W., 9-1/4" ht.
Extends 7-3/8". H/CTR 4-5/8".
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH

P300140-015 Polished Chrome
33-3/8" W., 9-1/4" ht.
Extends 7-3/8". H/CTR 4-5/8".
Four medium base lamps,
each 60w max.

Fixtures mount up or down.

GULLIVER



P300124-141

Three circular bands wrap together to create an open design for Gulliver. Dual toned frame color combinations are Galvanized with antique white accents or Graphite with weathered gray accents. A hand painted wood grained texture complements Rustic and Modern Farmhouse home décor, as well as Urban Industrial and Coastal interior settings.

ONE-LIGHT BATH

P710031-141 Galvanized
6" dia., 12" ht.
Extends 7". H/CTR 9-3/8".
One medium base lamp, 75w max.



P710031-141

TWO-LIGHT BATH

P300124-141 Galvanized
15-1/2" W., 8-1/2" ht.
Extends 5". H/CTR 6-1/8".
Two medium base lamps, 60w max.

P300125-141
mounted down

THREE-LIGHT BATH

P300125-141 Galvanized
24" W., 8-1/2" ht.
Extends 5". H/CTR 6-1/8".
Three medium base lamps, 60w max.



P300126-141

FOUR-LIGHT BATH

P300126-141 Galvanized
32-7/8" W., 8-1/2" ht.
Extends 5". H/CTR 6-1/8".
Four medium base lamps, 60w max.

FINISHES

- Galvanized - 141
- Graphite - 143

ALSO AVAILABLE IN

Fixture Collections, page 30
See complete collection:
ProgressLighting.com



P300124-143
mounted down



P300124-143



P300125-143
mounted down



P710031-143



P300125-143



P300126-143
mounted down



P300126-143

ONE-LIGHT BATH

P710031-143 Graphite
6" dia., 12" ht.
Extends 7". H/CTR 9-3/8".
One medium base lamp, 75w max.

TWO-LIGHT BATH

P300124-143 Graphite
15-1/2" W., 8-1/2" ht.
Extends 5". H/CTR 6-1/8".
Two medium base lamps, 60w max.

THREE-LIGHT BATH

P300125-143 Graphite
24" W., 8-1/2" ht.
Extends 5". H/CTR 6-1/8".
Three medium base lamps, 60w max.


FOUR-LIGHT BATH

P300126-143 Graphite
32-7/8" W., 8-1/2" ht.
Extends 5". H/CTR 6-1/8".
Four medium base lamps, 60w max.

*Fixtures shown with P7825-01
vintage lamps*

Fixtures mount up or down.

JUDSON



The Judson collection features a timeless clear schoolhouse-style globe. Metal fittings add distinction to complete the vintage look. Available in hanging, wall and ceiling styles, Judson provides the perfect compliment to farmhouse or coastal-inspired homes.

FINISHES

- Polished Nickel - 104
- Antique Bronze - 020

ALSO AVAILABLE IN

Fixture Collections, page 38-42

ONE-LIGHT BATH

P300080-020 Antique Bronze

P300080-104 Polished Nickel

6-1/2" W., 11-1/4" ht.

Extends 8-1/2". H/CTR 6-1/4".

One medium base lamp,
75w max.

TWO-LIGHT BATH

P300080-020 Antique Bronze

P300080-104 Polished Nickel

16-1/4" W., 11-1/4" ht.

Extends 8-1/2". H/CTR 7-1/2".

Two medium base lamps,
each 75w max.

THREE-LIGHT BATH

P300080-020 Antique Bronze

P300080-104 Polished Nickel

26" W., 11-1/4" ht.

Extends 8-1/2". H/CTR 7-1/2".

Three medium base lamps,
each 75w max.

FOUR-LIGHT BATH

P300083-020 Antique Bronze

P300083-104 Polished Nickel

35-3/4" W., 11-1/4" ht.

Extends 8-1/2". H/CTR 7-1/2".

Four medium base lamps,
each 75w max.



P300080-104



P300080-020



P300081-104



P300081-020



P300082-104



P300082-020



P300083-104



P300083-020



P300032-031
mounted down



P300032-031



P300033-031



P300033-031
mounted down



P300034-031



P300034-031
mounted down



A sensible, yet sophisticated, lighting collection rooted in updated classical modern styling. Suitable for Urban Industrial, Modern and Mid-Century Modern interiors, Domain features a Matte Black finish. A double ring accent and squared off socket holder complement over scale etched glass shades. Bath and vanity and chandelier options are available.

FINISH

- Black - 031

ALSO AVAILABLE IN

Fixture Collections, page 46

ONE-LIGHT BATH

P300032-031 Black
8-3/4" W., 6-5/8" ht.
Extends 9-1/2". H/CTR 4-1/2".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P300033-031 Black
20" W., 6-1/2" ht.
Extends 9-1/2". H/CTR 4-1/8".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P300034-031 Black
32" W., 6-1/2" ht.
Extends 9-1/2". H/CTR 4-1/8".
Three medium base lamps,
each 100w max.

Fixtures mount up or down.

CARISA



Inspired by the revival of mid-century fashions, the Carisa collection brings home this classic style. A metallic finish supports glossy white glass globes to create a timeless modern design.

FINISHES

- Brushed Nickel - 009
- Vintage Gold - 078

ALSO AVAILABLE IN

Fixture Collections, page 42

ONE-LIGHT BATH

P300084-009 Brushed Nickel
6-1/2" W., 10" ht.
Extends 8-1/2". H/CTR 4-5/8".
One medium base lamp,
75w max.

TWO-LIGHT BATH

P300085-009 Brushed Nickel
15-1/4" W., 10" ht. , wire 6.
Extends 8". H/CTR 6".
Two medium base lamp,
75w max.

THREE-LIGHT BATH

P300086-009 Brushed Nickel
25" W., 10" ht.
Extends 8". H/CTR 6".
Three medium base lamp,
75w max.

FOUR-LIGHT BATH

P300087-009 Brushed Nickel
32-3/4" W., 10" ht.
Extends 8". H/CTR 6".
Four medium base lamp,
75w max.



P300084-009
mounted up



P300084-009



P300085-009
mounted up



P300085-009



P300086-009



P300087-009



P300084-078

P300084-078
*mounted up***ONE-LIGHT BATH**

P300084-078 Vintage Gold
6-1/2" W., 10" ht.
Extends 8-1/2". H/CTR 4-5/8".
One medium base lamp,
75w max.

TWO-LIGHT BATH

P300085-078 Vintage Gold
15-1/4" W., 10" ht. , wire 6.
Extends 8". H/CTR 6".
Two medium base lamp,
75w max.



P300085-078

P300085-078
*mounted up***THREE-LIGHT BATH**

P300086-078 Vintage Gold
25" W., 10" ht.
Extends 8". H/CTR 6".
Three medium base lamp,
75w max.



P300086-078

P300086-078
*mounted up***FOUR-LIGHT BATH**

P300087-078 Vintage Gold
32-3/4" W., 10" ht.
Extends 8". H/CTR 6".
Four medium base lamp,
75w max.



P300087-078

BALANCE LED

Soft acrylic lens and a Brushed Nickel finish are highlights of these Energy Star fixtures. Fixtures can be wall or ceiling mounted. Can be installed vertically or horizontally.

FINISH

● Brushed Nickel - 009

ALSO AVAILABLE IN

See complete collection:
ProgressLighting.com

TWO-LIGHT BATH

P300171-009-30 Brushed Nickel
11-1/2" W., 5" ht.
Extends 3". H/CTR 2-1/2".
Two 9w LED module, 3000K,
90CRI, 670 lumens.



THREE-LIGHT BATH

P300172-009-30 Brushed Nickel
16-3/4" W., 5" ht.
Extends 3". H/CTR 2-1/2".
Three 9w LED module, 3000K,
90CRI, 670 lumens.



FOUR-LIGHT BATH

P300173-009-30 Brushed Nickel
22" W., 5" ht.
Extends 3". H/CTR 2-1/2".
Four 9w LED module, 3000K,
90CRI, 670 lumens.



PROGRESS **LED**



P300171-009-30



P300172-009-30



P300173-009-30



P300171-009-30



P300172-009-30




P300173-009-30

CIRCUIT



P300148-009-WB

P300148-009-WB
mounted vertical

P300149-009-WB

P300148-015-WB
mounted vertical

P300148-015-WB



P300149-015-WB



Connectivity and electric circuit diagrams inspired the design behind this new bath and vanity collection. Circuit fixtures appear to contain a lamp that is a continuous tube for an intriguing appearance. This collection is ideal for residential or light commercial applications, such as restaurants or other Urban Industrial and Vintage Electric design schemes. Can be installed vertically or horizontally.

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015

ONE-LIGHT BATH

P300148-009-WB Brushed Nickel

P300148-015-WB Polished Chrome

13-1/2" W., 5-1/8" ht.

Extends 3". H/CTR 2-1/2".

One medium base T10 lamp,
40w max included.

TWO-LIGHT BATH

P300149-009-WB Brushed Nickel

P300149-015-WB Polished Chrome

27-1/4" W., 5-1/8" ht.

Extends 3". H/CTR 2-1/2".

Two medium base T10 lamps,
Each 40w max included.

P860028-001 Vintage Amber Bulb

Overall L 8-3/4".

40w T10 medium base.



P860028-001

CONCOURSE LED



Architectural details and a full size canopy are key elements in Concourse LED vanity fixtures. A dual tone reflector frames the canopy to provide a mirror like effect. Etched opal glass is paired with Brushed Nickel and polished stainless accents in this versatile cylindrical fixture. Mounts horizontal and vertical.

FINISH

● Brushed Nickel - 009

ONE-LIGHT BATH

P300093-009-30 Brushed Nickel
24" W., 4-3/4" ht.
Extends 3-1/2". H/CTR 2-3/8".
One 37w LED module, 3000K,
90CRI, 2191 lumens

JAB

ONE-LIGHT BATH

P300094-009-30 Brushed Nickel
36" W., 4-3/4" ht.
Extends 3-1/2". H/CTR 2-3/8".
One 53w LED module, 3000K,
90CRI, 2969 lumens

JAB

PROGRESS **LED**



P300093-009-30
mounted vertical

P300094-009-30
mounted vertical



P300093-009-30



P300094-009-30

PONDER LED



P300092-020-30




P300091-020-30



P300092-143-30



P300091-143-30



Ponder vanity fixtures with prismatic glass shades offer a sleek, industrial-inspired appearance. Etched prismatic glass is framed within a die cast bezel to enhance visual interest in Urban Industrial or Farmhouse-style interiors.

FINISH

- Antique Bronze - 020
- Graphite - 143

TWO-LIGHT BATH

P300091-020-30 Antique Bronze

P300091-143-30 Graphite

16-1/8" W., 4-5/8" ht.

Extends 3-5/8". H/CTR 2-3/8".

Two 9w LED module, 3000K, 90CRI, 624 lumens.



THREE-LIGHT BATH

P300092-020-30 Antique Bronze

P300092-143-30 Graphite

25-3/8" W., 4-5/8" ht.

Extends 3-5/8". H/CTR 2-3/8".

Three 9w LED module, 3000K, 90CRI, 624 lumens.



PROGRESS **LED**

INDEX



Etched opal glass shades are nestled in sleek linear bands in the Index collection. Ideal for modern bath and vanity areas, Index enhances a spa-like environment.

FINISHES

- Brushed Nickel - 009
- Black - 031

ONE-LIGHT BATH

P300076-009 Brushed Nickel

P300076-031 Black

4-7/8" W., 8" ht.

Extends 6-1/8". H/CTR 4-1/2".

One G9 base lamp,
60w max.

TWO-LIGHT BATH

P300077-009 Brushed Nickel

P300077-031 Black

15" W., 5" ht.

Extends 6-1/8". H/CTR 3".

Two G9 base lamps,
each 60w max.

THREE-LIGHT BATH

P300078-009 Brushed Nickel

P300078-031 Black

23-3/8" W., 5" ht.

Extends 6-1/8". H/CTR 3".

Three G9 base lamps,
each 60w max.

FOUR-LIGHT BATH

P300079-009 Brushed Nickel

P300079-031 Black

33" W., 5" ht.

Extends 6-1/8". H/CTR 3".

Four G9 base lamps,
each 60w max.




P300076-009



P300077-009



P300078-009



P300079-009



P300076-031



P300077-031



P300078-031



P300079-031



G9 LED 3G9DLED27
See p.96 for details.



P300131-009



P300132-009



P300133-009



P300134-009



P300131-020



P300132-020



P300133-020



P300134-020

LEAP



Leap vanity fixtures feature tapered etched glass shades to complement contemporary design trends. Available in Brushed Nickel and Antique Bronze finishes options makes this collection on trend.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ALSO AVAILABLE IN

See complete collection:
ProgressLighting.com

ONE-LIGHT BATH

P300131-009 Brushed Nickel
P300131-020 Antique Bronze
 5" W., 8-1/8" ht.
 Extends 6-1/8". H/CTR 4-1/4".
 One medium base lamps,
 each 100w max.

TWO-LIGHT BATH

P300132-009 Brushed Nickel
P300132-020 Antique Bronze
 13-7/8" W., 8-3/8" ht.
 Extends 6-1/8". H/CTR 6".
 Two medium base lamps,
 each 100w max.

THREE-LIGHT BATH

P300133-009 Brushed Nickel
P300133-020 Antique Bronze
 22-7/8" W., 8-3/8" ht.
 Extends 6-1/8". H/CTR 6".
 Three medium base lamps,
 each 100w max.

FOUR-LIGHT BATH

P300134-009 Brushed Nickel
P300134-020 Antique Bronze
 31-3/4" W., 8-3/8" ht.
 Extends 6-1/8". H/CTR 6".
 Four medium base lamps,
 each 100w max.

Fixtures mount up or down.

LAIRD



The Laird collection provides a contemporary complement to casual interiors popular in today's homes. Glass shades add distinction and provide pleasing illumination to any room, while scrolling arms create an airy effect.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ALSO AVAILABLE IN

Fixture Collections, page 48

ONE-LIGHT BATH

P300095-020 Antique Bronze
5-3/4" W., 9" ht.
Extends 8". H/CTR 3-5/8".
One medium base lamp,
each 100w max.



TWO-LIGHT BATH

P300096-020 Antique Bronze
14-3/4" W., 8" ht.
Extends 7-1/4". H/CTR 5-3/4".
Two medium base lamps,
each 100w max.



THREE-LIGHT BATH

P300097-020 Antique Bronze
23-3/4" W., 8" ht.
Extends 7-1/4". H/CTR 5-3/4".
Three medium base lamps,
each 100w max.



FOUR-LIGHT BATH

P300098-020 Antique Bronze
33" W., 8-1/4" ht.
Extends 7-1/4". H/CTR 5-7/8".
Four medium base lamps,
each 100w max.



FIVE-LIGHT BATH

P300099-020 Antique Bronze
41-5/8" W., 8" ht.
Extends 7-1/4". H/CTR 5-3/4".
Five medium base lamps,
each 100w max.





P300095-009

P300095-009
mounted downP300096-009
mounted down

P300096-009



P300097-009

P300098-009
mounted down

P300099-009

ONE-LIGHT BATH

P300095-009 Brushed Nickel
5-3/4" W., 9" ht.
Extends 8". H/CTR 3-5/8".
One medium base lamp,
each 100w max.

TWO-LIGHT BATH

P300096-009 Brushed Nickel
14-3/4" W., 8" ht.
Extends 7-1/4". H/CTR 5-3/4".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P300097-009 Brushed Nickel
23-3/4" W., 8" ht.
Extends 7-1/4". H/CTR 5-3/4".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P300098-009 Brushed Nickel
33" W., 8-1/4" ht.
Extends 7-1/4". H/CTR 5-7/8".
Four medium base lamps,
each 100w max.

FIVE-LIGHT BATH

P300099-009 Brushed Nickel
41-5/8" W., 8" ht.
Extends 7-1/4". H/CTR 5-3/4".
Five medium base lamps,
each 100w max.

Fixtures mount up or down.

BARNETT



Barnett lanterns deliver timeless appeal with a decidedly modern flair. Large clear panes of glass frame your choice of traditional or vintage style bulbs. A graphic-inspired over-scale loop features a contrasting brass-tone finish.

FINISH

● Antique Bronze - 020

POST LANTERN

P540028-020 Antique Bronze
Fits 3" post (sold separately).
11-1/4" W., 9" L., 27" ht.
Two medium base lamps,
each 60w max.

HANGING LANTERN

P550028-020 Antique Bronze
11-1/4" W., 9" L., 26-7/8" ht.
Overall ht. w/chain 102", wire 10'.
Two medium base lamps,
each 60w max.

SMALL WALL LANTERN

P560077-020 Antique Bronze
6-1/2" W., 15-1/8" ht.
Extends 6-7/8". H/CTR 7-1/4".
One medium base lamp,
each 100w max.

MEDIUM WALL LANTERN

P560078-020 Antique Bronze
9" W., 18-7/8" ht.
Extends 8-1/8". H/CTR 9".
One 100w max. medium

LARGE WALL LANTERN

P560079-020 Antique Bronze
11-1/4" W., 23-5/8" ht.
Extends 10". H/CTR 10".
Two medium base lamps,
each 60w max.

*Fixtures shown with P7825-01
vintage lamps*





P550022-129

P540022-129



P560059-129



P560060-129



P560061-129



Laine features a cylindrical frame accented with clear glass and metallic elements. Traditional Architectural Bronze profile is paired with vintage gold accents. Wall lantern option features an arm that resembles a pipe fitting, offering an industrial-inspired appeal. Available in wall, hanging and post lantern options.

FINISHES

- Architectural Bronze - 129

POST LANTERN

P540022-129 Architectural Bronze
 Fits 3" post (sold separately).
 9-3/4" dia., 18-3/4" ht.
 One medium base lamp,
 100w max.

HANGING LANTERN

P550022-129 Architectural Bronze
 9-3/4" dia., 15-7/8" ht.
 Overall ht. w/chain 91", wire 10'.
 One medium base lamp,
 100w max.

SMALL WALL LANTERN

P560059-129 Architectural Bronze
 6-1/2" W., 12-1/2" ht.
 Extends 7-1/4". H/CTR 3".
 One medium base lamp,
 100w max.

MEDIUM WALL LANTERN

P560060-129 Architectural Bronze
 8" W., 15" ht.
 Extends 8-7/8". H/CTR 2-3/4".
 One medium base lamp,
 100w max.

LARGE WALL LANTERN

P560061-129 Architectural Bronze
 9-3/4" W., 16-1/2" ht.
 Extends 10-5/8". H/CTR 3-1/8".
 One medium base lamp,
 100w max.

*Fixtures shown with P7825-01
 vintage lamps*

HOLCOMBE



A nautical-inspired collection ideal for a variety of exteriors, including Coastal, Transitional and Urban Industrial settings. Black lanterns with clear seeded glass feature a hint of brushed nickel on the interior. Geometric details offer a finishing touch for wall, hanging and post lantern options.

FINISH

● Black - 031

POST LANTERN

P540025-031 Black
Fits 3" post (sold separately).
10-1/2" dia., 18-1/4" ht.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P560065-031 Black
6-3/8" W., 10-5/8" ht.
Extends 8". H/CTR 3-7/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560066-031 Black
8-1/4" W., 13-5/8" ht.
Extends 9-3/8". H/CTR 3-5/8".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P560067-031 Black
10-1/2" W., 16" ht.
Extends 12-1/4". H/CTR 3-5/8".
One medium base lamp,
100w max.

HANGING LANTERN

P550025-031 Black
10-1/2" dia., 16-5/8" ht.
Overall ht. w/chain 91-1/2", wire 10'.
One medium base lamp,
100w max.



P550025-031



P540025-031



P560065-031



P560066-031



P560067-031



P550029-031



P560080-031



P560081-031



P540029-031



P560082-031



Hollingsworth lanterns feature a crisscross design that surrounds clear seeded glass, emulating popular Farmhouse décor. Ideal for a variety of transitional exteriors when paired with either vintage or traditional bulbs. Includes wall, hanging and post options.

FINISH

- Black - 031

POST LANTERN

P540029-031 Black
Fits 3" post (sold separately).
10" dia., 23" ht.
One medium base lamp,
100w max.

HANGING LANTERN

P550029-031 Black
10" dia., 20-1/4" ht.
Overall ht. w/chain 94", wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P560080-031 Black
6" W., 14-1/2" ht.
Extends 8-1/8". H/CTR 7".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560081-031 Black
8" W., 19" ht.
Extends 10-5/8". H/CTR 8-5/8".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P560082-031 Black
10" W., 24" ht.
Extends 13-1/8". H/CTR 11-1/8".
One medium base lamp,
100w max.

Fixtures shown with P7825-01 vintage lamps

CONOVER



Conover is an outdoor lantern collection featuring nautical influences. A protective die cast ring surrounds beautiful clear seeded glass. Vintage metallic finishes are available for this collection that is sure to enhance curb appeal for a variety of exteriors.

FINISH

- Antique Bronze - 020
- Antique Pewter - 103

POST LANTERN

P540030-020 Antique Bronze
Fits 3" post (sold separately).
10-7/8" dia., 19" ht.
One medium base lamp,
100w max.

HANGING LANTERN

P550030-020 Antique Bronze
10-7/8" dia., 15-1/2" ht.
Overall ht. w/chain 90-1/2", wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P560083-020 Antique Bronze
7" W., 14-1/4" ht.
Extends 9". H/CTR 7-1/2".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560084-020 Antique Bronze
8-5/8" W., 16" ht.
Extends 10-1/4". H/CTR 7-5/8".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P560085-020 Antique Bronze
10-7/8" W., 21" ht.
Extends 13-1/8". H/CTR 9-3/8".
One medium base lamp,
100w max.



P550030-020



P560083-020



P540030-020



P560084-020



P560085-020



P560083-103

POST LANTERN

P540030-103 Antique Pewter
Fits 3" post (sold separately).
10-7/8" dia., 19" ht.
One medium base lamp,
100w max.

HANGING LANTERN

P550030-103 Antique Pewter
10-7/8" dia., 15-1/2" ht.
Overall ht. w/chain 90-1/2", wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P560083-103 Antique Pewter
7" W., 14-1/4" ht.
Extends 9". H/CTR 7-1/2".
One medium base lamp,
100w max.

**MEDIUM WALL LANTERN**

P560084-103 Antique Pewter
8-5/8" W., 16" ht.
Extends 10-1/4". H/CTR 7-5/8".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P560085-103 Antique Pewter
10-7/8" W., 21" ht.
Extends 13-1/8". H/CTR 9-3/8".
One medium base lamp,
100w max.



P560084-103



P560085-103

*Fixtures shown with P7825-01
vintage lamps*

MCPHERSON



McPherson outdoor lanterns are sure to make a statement. A clever clover-shaped handle accentuates elegantly fluted clear seeded glass. Wall, hanging and post lanterns are finished in Black and complement Rustic and Modern Farmhouse exteriors, as well as Traditional and Transitional homes.

FINISH

● Black - 031

POST LANTERN

P540023-031 Black

Fits 3" post (sold separately).
9-1/2" dia., 19" ht.
Three candelabra base lamps,
each 60w max.

HANGING LANTERN

P550023-031 Black

9-1/2" W., 19" ht.
Overall ht. w/chain 93", wire 10'.
Three candelabra base lamps,
each 60w max.

SMALL WALL LANTERN

P560062-031 Black

7-1/2" W., 13-1/2" ht.
Extends 7-1/8". H/CTR 9-1/2".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560063-031 Black

9-1/2" W., 17-1/2" ht.
Extends 9-1/4". H/CTR 12-1/4".
Two candelabra base lamps,
each 60w max.

LARGE WALL LANTERN

P560064-031 Black

10-5/8" W., 20" ht.
Extends 10-1/2". H/CTR 13-3/4".
Three candelabra base lamps,
each 60w max.



P550023-031



P560062-031



P560063-031



P540023-031



P560064-031



P550020-020



P560057-020



P540020-020



P560058-020



P550021-020



Gunther lanterns provide an affordable and stylish option to update a home's curb appeal. Inspired by the popular farmhouse design trend, these cylindrical lights provide the perfect showcase for vintage style light bulbs.

FINISH

● Antique Bronze - 020

TWO-LIGHT FLUSH MOUNT

P550021-020 Antique Bronze
12-5/8" dia., 5-3/4" ht.
Two medium base lamps,
each 75w max.

SMALL WALL LANTERN

P560057-020 Antique Bronze
6-1/2" dia., 9-1/2" ht.
Extends 7-3/4". H/CTR 2-3/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560058-020 Antique Bronze
8" dia., 11-1/2" ht.
Extends 9-1/4". H/CTR 3-3/8".
One medium base lamp,
100w max.

POST LANTERN

P540020-020 Antique Bronze
8" dia., 13-1/2" ht.
One medium base lamp,
100w max.

HANGING LANTERN

P550020-020 Antique Bronze
8" dia., 12" ht.
Overall ht. w/chain 87", wire 10'.
One medium base lamp,
100w max.

*Fixtures shown with P7825-01
vintage lamps*

GABLES

Engineered polymers are used to create the distinctive Gables lanterns. Developed to withstand a broad range of environmental conditions, the corrosion-resistant housing delivers beautiful lighting and reliability. A clear glass globe enhances the classic design.

FINISH

- Antique Bronze - 020

SMALL WALL LANTERN

P560087-020 Antique Bronze
5-7/8" W., 11-3/8" ht.
Extends 6-7/8". H/CTR 7-5/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560088-020 Antique Bronze
7-1/2" W., 14-1/8" ht.
Extends 8-1/2".
H/CTR 10-9/16".
One medium base lamp,
100w max.



P560087-020



P560088-020

PIER 33

Outdoor wall lanterns from the Pier 33 collection feature coastal undertones and a design reminiscent of industrial spaces. LED and incandescent options are comprised of a die-cast frame. Clear seeded glass complements a Black finish.

FINISH

- Black - 031

ALSO AVAILABLE IN

See complete collection:
ProgressLighting.com

MEDIUM LED WALL LANTERN

P560071-031-30 Black
8-1/8" W., 8" ht.
Extends 9". H/CTR 3-1/8".
One 9w LED module, 3000K,
90CRI, 624 lumens.

MEDIUM WALL LANTERN

P560089-031 Black
8-1/8" W., 8" ht.
Extends 9". H/CTR 3-1/8".
One medium base lamp,
100w max.



P560071-031-30



P560089-031
shown with P7825-01
vintage lamp

GLOBE LANTERN

Classic in both form and function, the Globe lanterns provide a stylish update for the home. A clear glass diffuser is the perfect way to showcase vintage or globe style light bulbs.

FINISH

- Black - 031

POST LANTERN

P540007-031 Black
9-7/8" dia., 13-1/4" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560092-031 Black
9-7/8" dia., 11-5/8" ht.
Extends 11". H/CTR 9".
One medium base lamp,
100w max.



P540007-031
shown with
P7825-01
vintage lamp



P560092-031
shown with P7825-01
vintage lamp



P563000-020-30K



P563001-020-30K



P563000-030-30K



P563001-030-30K



P563000-143-30K



P563001-143-30K



P563000-147-30K



P563001-147-30K



Sleek, cylindrical forms in elegant finish selections. Die-cast aluminum wall brackets and heavy-duty aluminum framing. Fade and chip-resistant. UL listed for wet locations.

FINISHES

- Antique Bronze - 020
- White - 030
- Graphite - 143
- Satin Nickel - 147

3" DOWNLIGHT CYLINDER

P563000-020-30K Antique Bronze

P563000-030-30K White

P563000-143-30K Graphite

P563000-147-30K Satin Nickel

5-1/2" W., 5-5/8" ht.

One 12w LED module, 3000K, 90CRI, 900 lumens.



3" UP/DOWNLIGHT CYLINDER

P563001-020-30K Antique Bronze

P563001-030-30K White

P563001-143-30K Graphite

P563001-147-30K Satin Nickel

5-1/2" W., 8-1/4" ht.

Two 12w LED module, 3000K, 90CRI, 1800 lumens.



PROGRESS LED

Z-1050

Featuring a modern design, the Z-1050 LED sconce is suitable for a variety of exterior or interior architecture settings. Wall sconce is wet location listed with a replaceable LED module protected within a glass enclosure.

FINISH

- Black - 031

MEDIUM WALL LANTERN

P560093-031-30 Black

12" dia., 12" ht.

Extends 3". H/CTR 6".

One 9w LED module, 3000K, 90CRI, 670 lumens.



PROGRESS **LED**



P560093-031-30

Z-1060

Z-1060 presents a functional design with a modern sensibility. Architectural style housing is die-cast for added durability. The glass diffuser is secured without visible fasteners for an overall clean appearance. LED source delivers both energy efficiency and maintenance-free operation.

FINISH

- Black - 031

SMALL WALL LANTERN

P560072-031-30 Black

4-1/2" W., 4-1/2" ht.

Extends 4-3/4". H/CTR 2-1/4".

One 9w LED module, 3000K, 90CRI, 624 lumens.



SMALL WALL LANTERN

P560073-031-30 Black

Shown with glass

4-1/2" W., 4-1/2" ht.

Extends 4-3/4". H/CTR 2-1/4".

One 9w LED module, 3000K, 90CRI, 624 lumens.



PROGRESS **LED**



P560072-031-30



P560073-031-30

STRATA



P560090-030-30K



P560090-082-30K



P560090-020-30K



P560090-031-30K

The Strata features a modern, low profile design ideal for residential and multifamily applications. Energy efficient and functional, wall mounted, can be installed indoor and outdoor.

FINISHES

- White - 030
- Metallic Gray - 82
- Antique Bronze - 020
- Black - 031

WALL LANTERN

P560090-020-30K Antique Bronze

P560090-030-30K White

P560090-031-30K Black

P560090-082-30K Metallic Gray

6-5/8" W., 5-1/2" ht.

One 12w LED module, 3000K, 90CRI, 624 lumens.



P860006-031

POLE BASE

FINISH

- Black - 031

P860006-031 Black

11" dia., 24" ht.

Cast aluminum.

Fits 3" smooth and fluted posts (sold separately).

LED UNDERCABINET

HIDE a LITE V

The **HIDE-A-LITE V** linear undercabinet series provides the ideal solution for residential and light commercial applications. Die-cast aluminum construction featuring a lens design to optimize light distribution to ensure proper illumination. The **HIDE-A-LITE V** series utilizes a simple mounting method, and direct wiring, for a hassle free installation. Energy efficient and functional lighting, which can be dimmed down to 10% with many Forward Phase (Triac) and Electronic Low Voltage (ELV) dimmers.

FINISHES

- Antique Bronze - 020
- White - 028

PROGRESS **LED**

LED UNDERCABINET

P700000-020-30 Antique Bronze

P700000-028-30 White

3-1/4" W., 1-1/8" ht.

Extends 9".

One 3000K, 90CRI,

4.5w max. LED, 300 lumens.



P700000-028-30



P700000-020-30

LED UNDERCABINET

P700001-020-30 Antique Bronze

P700001-028-30 White

3-1/4" W., 1-1/8" ht.

Extends 11-1/2".

One 3000K, 90CRI,

7.5w max. LED, 500 lumens.



P700001-028-30



P700001-020-30

LED UNDERCABINET

P700002-020-30 Antique Bronze

P700002-028-30 White

3-1/4" W., 1-1/8" ht.

Extends 17-1/2".

One 3000K, 90CRI,

12.5w max. LED, 815 lumens.



P700002-028-30



P700002-020-30

LED UNDERCABINET

P700003-020-30 Antique Bronze

P700003-028-30 White

3-1/4" W., 1-1/8" ht.

Extends 23-1/2".

One 3000K, 90CRI,

15.5w max. LED, 980 lumens.



P700003-028-30



P700003-020-30

LED UNDERCABINET

P700004-020-30 Antique Bronze

P700004-028-30 White

3-1/4" W., 1-1/8" ht.

Extends 35-1/2".

One 3000K, 90CRI,

20w max. LED, 1500 lumens.



P700004-028-30



P700004-020-30

CLOUD LED + DRUM

FINISH

○ White - 030

*Dimmable to 10% with
Triac and ELV dimmers*

LED DRUM

P730005-030-30 White

P730005-031-30 Black

11" W., 4" ht.

21w integrated LED, 3000K,
90CRI, 1680 lumens.



LED CLOUD

P730008-030-30 White

11" W., 4" ht.

21w integrated LED, 3000K,
90CRI, 1575 lumens.



LED DRUM

P730002-030-30 White

13-5/8" W., 4" ht.

22.5w integrated LED, 3000K,
90CRI, 2025 lumens.



LED CLOUD

P730006-030-30 White

13-5/8" W., 4" ht.

22.5w integrated LED, 3000K,
90CRI, 1845 lumens.



LED DRUM

P730003-030-30 White

17" W., 4" ht.

28w integrated LED, 3000K,
90CRI, 2520 lumens.



LED CLOUD

P730007-030-30 White

17" W., 4" ht.

28w integrated LED, 3000K,
90CRI, 2548 lumens.



P730005-031-30



P730008-030-30



P730005-030-30



P730006-030-30



P730002-030-30



P730007-030-30



P730003-030-30

LED WRAP & STRIP

FINISHES

○ White - 030

● Black - 031

*Dimmable to 10% with
Triac and ELV dimmers*

LED Wrap

LED WRAP

P7183-3030K8 White

9" W., 24" L., 3 1/16" ht.

25w LED, 3000K, 80CRI,
2500 lumens.



LED Strip

LED STRIP

P7265-3030K9 White

1-3/4" W., 22-7/8" L., 1-7/8 ht.

19w LED, 3000K, 90CRI,
1500 lumens.



LED WRAP

P7186-3030K8 White

9" W., 48" L., 3 1/16" ht.

39w LED, 3000K, 80CRI,
3800 lumens.



LED STRIP

P7267-3030K9 White

1-3/4" W., 46-1/2" L., 1-7/8 ht.

36w LED, 3000K, 90CRI,
3000 lumens.



P7186-3030K8



P7183-3030K8



P7265-3030K9



P7267-3030K9

LED STEPLIGHTS

The mini-steplights are ideal for indoor residential applications. Energy efficient steplights include both vertical and horizontal louvers and are available in four finishes.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020
- White - 028
- Black - 031

LED STEP LIGHT

P660003-009-30K Brushed Nickel

P660003-020-30K Antique Bronze

P660003-028-30K White

P660003-031-30K Black

2-3/4" W., 4-1/2" ht.

3/4w LED, 3000K, 90CRI, 12 lumens.



P660003-009-30K



P660003-020-30K



P660003-028-30K



P660003-031-30K



WAYSTAR™

The Waystar™ Series offers quality and value with a compact and attractive LED based emergency light. Each unit comes standard with round and rectangle trim options. Housing is a flame-rated UV stable thermoplastic in white and black finish options. The unit has 4 LED Source, each as individual, adjustable optic assemblies, consuming 1 watt each during operation. Self-diagnostics fixture monitors LED status, LED load transfer circuit, battery capacity and charger function and displays any fault detection by means of a flashing code. The self-test feature automatically runs a 1 minute test once a month and an alternating 30 or 60 minute test once every 6 months. Multi-color LED indicator provides visible fault detection and charging status. For installation in IC ceilings. Complies with UL 924, NFPA 101 and NFPA 70

FINISHES

- White - 028
- Black - 031

LED EMERGENCY LIGHT

PECEM-30 White

PECEM-31 Black

8-1/2" W., 5-1/2" L., 2-5/8" ht.

4w. LED, 4000K, 90CRI, 350 lumens.

SELF-DIAGNOSTICS

LED EMERGENCY LIGHT

PECEM-30-SD White

PECEM-31-SD Black

Self diagnostic

8-1/2" W., 5-1/2" L., 2-5/8" ht.

4w. LED, 4000K, 90CRI, 350 lumens.



PECEM-30
PECEM-30-SD
shown with rectangle trim



PECEM-30
PECEM-30-SD
shown with round trim



PECEM-31
PECEM-31-SD
shown with rectangle trim



PECEM-31
PECEM-31-SD
shown with round trim




LED EDGELIT RECESSED


Slim, low profile recessed downlight combines innovative technology, aesthetics, functionality and affordability. No more housing or J-Box required for installation and wet location listed provides the ultimate flexibility. The low profile downlight is ideal for many residential, multi-family, commercial and hospitality applications. Featuring a detachable driver box, which can be mounted remotely for shallow ceiling installations. Energy efficient design provides up to a 75% energy savings and up 50,000 hours of LED life. Flicker free dimming down to 10% with many Forward Phase (Triac) and Electronic Low Voltage (ELV) dimmers.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020
- White - 028
- Black - 031



DETACHED JUNCTION BOX




ATTACHED JUNCTION BOX

5" LED EDGELIT

- P800004-009-30** Brushed Nickel
 - P800004-020-30** Antique Bronze
 - P800004-028-30** White
 - P800004-031-30** Black
- 5" W., 3" ht.
9.5w LED, 3000K, 90CRI,
550 lumens.



P800004-028-30



P800004-028-30
back view

7" LED EDGELIT

- P800005-009-30** Brushed Nickel
 - P800005-020-30** Antique Bronze
 - P800005-028-30** White
 - P800005-031-30** Black
- 7" W., 3" ht.
13w LED, 3000K, 90CRI,
800 lumens.



P800005-028-30



P800005-028-30
back view



LAMPS



LED LAMP 3G9DLED27

3w LED G9 base lamp
2700K, 270 lumens,
25,000 hours, dimmable.



LED LAMP F4T10DLED927/JA8

4w T10 LED medium base
filament lamp
2700K, 300 lumens,
15,000 hours, dimmable.

JA8



LED LAMP V6.5ST19DLED922/JA8

6.5w ST19 LED medium base
amber filament lamp
2200K, 450 lumens,
15,000 hours, dimmable.



JA8

See complete
collection of LED
and vintage lamps:
ProgressLighting.com

CANOPY

Progress Lighting's canopy accessory offers a convenient way to mount groupings of pendants. The round accessory accommodates 3 fixtures, while the linear option can mount either 2, 3, 5 or 6 pendants. Now available in Brushed Nickel, Antique Bronze and Graphite finishes.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020
- Graphite - 143

THREE-LIGHT ROUND

P8403-143 Graphite
Round canopy can be used for three pendants. Maximum pendant width for three lights is 9-1/2" each. 15-1/2" dia., 1-3/8" ht.

Additional finish options available at progresslighting.com

THREE-LIGHT LINEAR

P8404-143 Graphite
Linear canopy can be used for two or three pendants. Maximum pendant width for two lights is 18" each. Maximum pendant width for five lights is 9" each. 4-1/4" W., 23-1/4" L., 11/16" ht.

Additional finish options available at progresslighting.com

FIVE-LIGHT LINEAR

P860004-009 Brushed Nickel
P860004-143 Graphite
P860004-020 Antique Bronze
Linear canopy can be used for three or five pendants. Maximum pendant width for three lights is 20" each. Maximum pendant width for five lights is 12" each. 4-1/4" W., 59-5/8" L., 1" ht.

SIX-LIGHT LINEAR


P860005-009 Brushed Nickel
P860005-143 Graphite
P860005-020 Antique Bronze
Linear canopy can be used for six pendants. Maximum pendant width for six lights is 8" each. 8-1/8" W., 39-5/8" L., 1" ht.



P860005-143
shown in use with
Staunton pendants



P8404-143



P860005-020



P860004-009



P860004-143



P8403-143

PRODUCT INDEX

P300000

P300032	69
P300033	69
P300034	69
P300076	76
P300077	76
P300078	76
P300079	76
P300080	68
P300081	68
P300082	68
P300083	68
P300084	43, 45, 70, 71
P300085	70, 71
P300086	70, 71
P300087	70, 71
P300091	75
P300092	75
P300093	74
P300094	74
P300095	78, 79
P300096	78, 79
P300097	78, 79
P300098	78, 79
P300099	78, 79
P300116	17, 19, 62, 63
P300117	62, 63
P300118	62, 63
P300119	62, 63
P300124	66, 67
P300125	66, 67
P300126	66, 67
P300131	77
P300132	77
P300133	77
P300134	77
P300137	65
P300138	65
P300139	65
P300140	65
P300144	64
P300145	64
P300146	64
P300147	64
P300148	73
P300149	73

P300171	72
P300172	72
P300173	72
P350049	31
P350057	49, 51
P350064	53, 55
P350065	53, 55
P350066	53, 55
P350070	53, 55
P350071	53, 55
P350072	53, 55
P350074	39, 41
P350075	43, 45
P350076	61
P350077	61
P350078	61
P350079	21, 23
P350080	57
P350081	59
P350082	59
P350085	58
P350086	58
P350088	57
P350091	33, 35
P350093	25
P350094	17, 19
P350096	17, 19
P350100	60
P350101	60
P350103	21, 23
P350108	37

P400000

P400034	47
P400035	47
P400036	47
P400057	39, 41
P400058	39, 41
P400059	43, 45
P400060	43, 45
P400061	43, 45
P400062	49, 51
P400063	49, 51
P400064	49, 51
P400065	21, 23

P400066	21, 23
P400067	21, 23
P400073	33, 35
P400074	33, 35
P400087	17, 19
P400088	17, 19
P400097	31
P400102	25
P400103	25
P400104	25
P400110	21, 23

P500000

P500022	31
P500023	31
P500061	39, 41
P500062	21, 23
P500065	56
P500066	56
P500071	49, 51
P500072	21, 23
P500078	33, 35
P500079	33, 35
P500090	31
P500092	27, 29
P500093	27, 29
P500094	27, 29
P500099	17, 19
P500100	17, 19
P500111	37
P500112	37
P500113	25
P500114	25
P540007	88
P540020	87
P540022	81
P540023	86
P540025	82
P540028	80
P540029	83
P540030	84, 85
P550020	87
P550021	87
P550022	81
P550023	86

P550025	82
P550028	80
P550029	83
P550030	84, 85
P560054	82
P560057	87
P560058	87
P560059	81
P560060	81
P560061	81
P560062	86
P560063	86
P560064	86
P560065	82
P560066	82
P560067	82
P560071	88
P560072	90
P560073	90
P560077	80
P560078	80
P560079	80
P560080	83
P560081	83
P560082	83
P560083	84, 85
P560084	84, 85
P560085	84, 85
P560087	88
P560088	88
P560089	88
P560090	91
P560092	88
P560093	90
P563000	89
P563001	89

P600000

P660003	94
---------	----

P700000

P700000	92
P700001	92
P700002	92

P700003	92
P700004	92
P710028	21, 23
P710031	31, 66, 67
P710044	25
P710136	53, 55
P7183	93
P7186	93
P7265	93
P7267	93
P730002	93
P730003	93
P730005	93
P730006	93
P730007	93
P730008	93

P800000

P800004	95
P800005	95
P8403	96
P8404	96
P860004	96
P860005	96
P860006	91
P860007	17
P860008	19
P860027	25

PECEM	94
-------	----

LAMPS

3G9DLED27	96
F4T10DLED927/ja8	96
V6.5ST19DLED922/JA8	96



Products identified as Energy Efficient have been designed to utilize light sources that consume less power than equivalent traditional incandescent sources.



Products referencing this logo meet the energy efficiency requirements for light fixtures set forth in ENERGY STAR® product specifications. Please refer to www.energystar.gov for specific product qualifications and list of certified products.



This marking indicates fixtures that have an integrated LED or replaceable LED module that has been tested and listed in the California Appliance Database. Check for certified lamps, fixtures or LED light engines by searching the MAEDBS database. Go to cacertappliances.energy.ca.gov



Table 150.0A defines products that do not have to meet JA8 and can be used to comply with 2016 Title 24. The most common types include:

- Pin-based linear or compact fluorescent light sources using electronic ballasts
- GU-24 sockets containing light sources other than LEDs
- Inseparable SSL luminaires that are installed outdoors

Every effort has been made to ensure the accuracy of information in this catalog. Progress Lighting reserves the right to make product changes from time to time, without prior notification, which may change the information provided in this catalog. Errors brought to our attention will be corrected in subsequent issues.

UL, CSA, or ETL Listed or Classified unless otherwise noted. Bulbs not included with fixtures unless specified. Specifications subject to change without notice.

Metal finishes not specified as "solid" have quality plated or painted finishes.

Finish representations are high resolution digital reproductions, and, while every effort has been made to render colors accurately, they may vary slightly from the actual product, especially hand-painted finishes, due to the nature of hand craftsmanship.

©Progress Lighting 2018
All rights reserved.
International copyright secured.





PROGRESS LIGHTING

701 Millennium Boulevard
Greenville, South Carolina
29607

progresslighting.com

