



**PRODUCT
SUPPLEMENT**
JUNE 2019

PROGRESS
LIGHTING™



Table of Contents

2 PICTORIAL INDEX
 5 WHAT'S YOUR STYLE?
 16 FIXTURE COLLECTIONS

29 CLOSE-TO-CEILING

30 SCONCES



31 BATH COLLECTIONS

44 OUTDOOR

46 CEILING FANS



52 UTILITY
 56 INDEX

FIXTURE COLLECTIONS

DRUM SHADE

Black p.28

**FOSTER**

Gilded Iron p.24

**KEMPSEY**

Antique Bronze p.22

**KEMPSEY**

Brushed Nickel p.20

**MAST**

Antique Bronze p.26

**MAST**

Brushed Nickel p.27

**REPLAY**

Black p.28

**REPLAY**

Brushed Nickel p.28

**REPLAY**

Polished Nickel p.28

**SENECA**

Black p.16

**SENECA**

Polished Nickel p.18



CLOSE-TO-CEILING

ARCHIE

Vintage Brass p.29

**ETCHED GLASS**

Black p.29

**ETCHED GLASS**

Brushed Nickel p.29

**FOSTER**

Gilded Iron p.25

**MAST**

Antique Bronze p.27

**MAST**

Brushed Nickel p.27

**SIGNAL**

Graphite p.29

**SIGNAL**

Polished Chrome p.29



SCONCES / WALL BRACKETS

ADLEY
Black p.33



ADLEY
Brushed Nickel p.32



ADLEY
Polished Nickel p.33



ADLEY
Satin Brass p.32



ARCHIE
Vintage Brass p.31



CLASSIC
Black p.42



CLASSIC
Brushed Nickel p.42



INSPIRE LED
Summer Linen p.30



INSPIRE LED
Off White Linen p.30



KEMPSEY
Antique Bronze p.23



KEMPSEY
Brushed Nickel p.21



LINEN GLASS SCONCE
Black p.30



LINEN GLASS SCONCE
Brushed Nickel p.30



RUSHTON
Brushed Nickel p.34



RUSHTON
Graphite p.34



SIGNAL
Graphite p.41



SIGNAL
Polished Chrome p.40



BATH COLLECTIONS

ADLEY
Black p.33



ADLEY
Brushed Nickel p.32



ADLEY
Polished Nickel p.33



ADLEY
Satin Brass p.32



ARCHIE
Vintage Brass p.31



BRIARWOOD
Antique Bronze p.38



BRIARWOOD
Graphite p.38



CLASSIC
Black p.42



CLASSIC
Brushed Nickel p.42



MAST
Antique Bronze p.36



MAST
Brushed Nickel p.36



RUSHTON
Brushed Nickel p.34



RUSHTON
Graphite p.34



SIGNAL
Graphite p.41



SIGNAL
Polished Chrome p.40



OUTDOOR

ENGLEWOOD
Antique Bronze p.45



ENGLEWOOD
Antique Pewter p.45



ENGLEWOOD
Black p.45



GREENE RIDGE
Architectural Bronze p.44



GREENE RIDGE
Black p.44



CEILING FANS

GAZE
Black p.46



GULLIVER
Galvanized p.50



GULLIVER
Graphite p.51



VAST
Black p.48



What's Your Style?



DISCOVER STATEMENT-MAKING LIGHTING FOR EVERY BUDGET & STYLE.

One of today's most popular design trends encourages individuals to create unique lighting designs by mixing and matching their favorite fixtures within the same space. There is no need to feel limited by fixtures or finishes in one particular collection!



Featuring Mast Mini-Pendants and Gulliver Ceiling Fan.



REACH YOUR BLISS

Express style, relaxation, and tranquility using a tonal, minimal color palette in the bedroom. Neutral shades establish a calm and serene sentiment while textures and fabrics add layers of luxury to the mix for a modern-meets-farmhouse approach to inviting comfort. The Mast pendant placed bedside and the Gulliver fan overhead complement the subtly alluring, Zen look and ambiance.



BOLD, BEAUTIFUL BATH

Whether dark or bright, a bold pop of color is trending in bath design. Pair a dark vanity and mirror with a white palette and bright natural light for a classic, sophisticated look. The industrial-styled Rushton bath sconces illuminate the face while adding a vintage charm that creates a polished balance with the clean décor.



Featuring Briarwood Bath.

ROOM WITH A VIEW

Placing a bath vanity between two windows lets an abundance of natural light stream into the bathroom, and the Briarwood bath bar adds light at face level, right where it's needed. Briarwood's richly painted finish and metal detailing coordinates with the plumbing fixtures, while contrasting nicely with the room's white color scheme.




SWING ARM SCONCE

The Kempsey sconce features a swivel arm that provides customization to the direction of light once the fixture is mounted. Swivel the arm to be straight, left, right or anything in-between. This feature makes the Kempsey Sconce the perfect bedside companion.



Featuring Kempsey Sconces and Fleurette Chandelier.



TRANSITIONAL WITH A TWIST


Masculine and feminine touches balance comfortably in this Transitional bedroom. A neutral color palette is punctuated by interestingly textured pillows and pops of dark brown to add depth. The unexpected addition of the whimsical Fleurette chandelier contrasts nicely with the streamlined Kempsey wall brackets and the clean lines of the furniture.

Editor's Note:

View details on the Fleurette Chandelier online at progresslighting.com.



Featuring Gaze Ceiling Fan, Tobin Chandelier and Gresham Sconces.



COOL, CLASSIC AND COMFORTABLE

Modern Farmhouse design embraces tradition but is firmly planted in the present. With a nod to vintage touches of a weathered fireplace mantel, exposed beams, and an airy palette grounded by dark-toned furniture and accessories in a variety of textures, this open concept space modernizes a traditional approach. Our clean-lined Tobin chandelier and Gresham wall sconces accent the inviting ambiance with a touch of classic iron detailing while the Gaze ceiling fan offers a modern look and functionality as a refreshing update to Farmhouse style.

Editor's Note:

View details on the Tobin Chandelier and Gresham Sconces online at progresslighting.com.

AN INDUSTRIAL EDGE

With a simple but edgy vibe that takes its cue from industrial origins, this bedroom offers a warm backdrop of texture and interest against the clean ironwork designs of the lighting. Two low-hanging Foster pendants over the nightstands and the Sanford ceiling fan overhead play with the notions of substance and form, while organic elements of wood, layered textiles and a soothing color scheme celebrate the signature look of the Industrial setting.

Editor's Note:

View details on the Sanford Ceiling Fan online at progresslighting.com.





Featuring Foster Mini-Pendants and Sanford Ceiling Fan.

SENECA



P400115-031



Sophisticated simplicity is personified in the Seneca collection. Within its open cage design candelabra lights seem to float in midair, brought down to earth only by its simple base, offering a clean and modern look to any space.

FINISHES

- Black - 031
- Polished Nickel - 104



P400115-031



P500121-031

FIVE-LIGHT CHANDELIER


P400115-031 Black
25-1/2" dia., 15-7/8" ht.,
Overall ht. w/stem 81-1/2"; wire 180".
Five candelabra base lamps,
each 60w max.

SIX-LIGHT ISLAND

P400175-031 Black
38-1/4" W., 14-1/8" ht.,
Overall ht. w/stem 80-1/2"; wire 180".
Six candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400187-031 Black
30" dia., 20-7/8" ht.,
Overall ht. w/stem 86-1/2"; wire 180".
Nine candelabra base lamps,
each 60w max.



P400175-031

FOUR-LIGHT FOYER

P500121-031 Black
15" dia., 17-1/4" ht.,
Overall ht. w/stem 83-1/2"; wire 180".
Four candelabra base lamps,
each 60w max.

EIGHT-LIGHT FOYER

P500122-031 Black
19-5/8" dia., 32" ht.,
Overall ht. w/stem 98"; wire 180".
Eight candelabra base lamps,
each 60w max.



P400187-031



P500122-031



P400115-104



P400115-104



P500121-104

FIVE-LIGHT CHANDELIER


P400115-104 Polished Nickel
25-1/2" dia., 15-7/8" ht.,
Overall ht. w/stem 81-1/2"; wire 180".
Five candelabra base lamps,
each 60w max.

SIX-LIGHT ISLAND

P400175-104 Polished Nickel
38-1/4" W., 14-1/8" ht.,
Overall ht. w/stem 80-1/2"; wire 180".
Six candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400187-104 Polished Nickel
30" dia., 20-7/8" ht.,
Overall ht. w/stem 86-1/2"; wire 180".
Nine candelabra base lamps,
each 60w max.



P400175-104

FOUR-LIGHT FOYER

P500121-104 Polished Nickel
15" dia., 17-1/4" ht.,
Overall ht. w/stem 83-1/2"; wire 180".
Four candelabra base lamps,
each 60w max.

EIGHT-LIGHT FOYER

P500122-104 Polished Nickel
19-5/8" dia., 32" ht.,
Overall ht. w/stem 98"; wire 180".
Eight candelabra base lamps,
each 60w max.



P400187-104



P500122-104

KEMPSEY



P350110-009



For Farmhouse styling with a twist, look no further than Kempsey, whose inside-out design showcases stylish charm. A sturdy metal frame on the outside captures the textured linen shade within its arms, so that the structure becomes part of the design. The shade has an inner transparent backing, so its beautiful texture is visible from inside out. A wall bracket featuring a multi-directional arm holding the shade completes the collection.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020



P350110-009



P350110-009
Shown as
semi-flush



P500138-009

**THREE-LIGHT SEMI-FLUSH
CONVERTIBLE**

P350110-009 Brushed Nickel
Hanging and ceiling mount
hardware included
21-3/4" dia., 11" ht.,
Overall ht. w/stem 76"; wire 120".
Three medium base lamps,
each 60w max.

ONE-LIGHT PENDANT

P500138-009 Brushed Nickel
11-3/4" dia., 9" ht.,
Overall ht. w/stem 76"; wire 120".
One medium base lamp,
75w max.

THREE-LIGHT PENDANT

P500139-009 Brushed Nickel
17-3/4" dia., 21-3/8" ht.,
Overall ht. w/stem 87-1/2"; wire 120".
Three medium base lamps,
each 60w max.

ONE-LIGHT WALL BRACKET

P710045-009 Brushed Nickel
12" dia., 19-3/4" ht.,
Extends 23-5/8".
One medium base lamp, 75w max.
On/off rotary switch on backplate.



P500139-009



P710045-009



P350110-020



P350110-020



P500138-020

THREE-LIGHT SEMI-FLUSH CONVERTIBLE

P350110-020 Antique Bronze Hanging and ceiling mount hardware included 21-3/4" dia., 11" ht., Overall ht. w/stem 76"; wire 120". Three medium base lamps, each 60w max.

ONE-LIGHT PENDANT

P500138-020 Antique Bronze 11-3/4" dia., 9" ht., Overall ht. w/stem 76"; wire 120". One medium base lamp, 75w max.

THREE-LIGHT PENDANT

P500139-020 Antique Bronze 17-3/4" dia., 21-3/8" ht., Overall ht. w/stem 87-1/2"; wire 120". Three medium base lamps, each 60w max.

ONE-LIGHT WALL BRACKET

P710045-020 Antique Bronze 12" dia., 19-3/4" ht., Extends 23-5/8". One medium base lamp, 75w max. On/off rotary switch on backplate.



P350110-020
Shown as semi-flush



P500139-020



P710045-020

FOSTER



P400153-071



Clean ironwork inspired by antique trains defines the look of Foster. Substance and form are the watchwords of this family, with a simple design of bent metal arms enclosing exposed bulbs held by an ornamental socket cover. Foster's squared lines and mixed metal elements are ideal for Industrial and Rustic settings.

FINISH

- Gilded Iron - 071



P350116-071



P400153-071

TWO-LIGHT FLUSH MOUNT

P350116-071 Gilded Iron
16" dia., 6" ht.,
Two medium base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400153-071 Gilded Iron
25" dia., 14" ht.,
Overall ht. w/stem 80-1/2"; wire 180".
Five medium base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400154-071 Gilded Iron
30" dia., 14" ht.,
Overall ht. w/stem 81"; wire 180".
Six medium base lamps,
each 60w max.

ONE-LIGHT MINI-PENDANT

P500155-071 Gilded Iron
11-1/4" dia., 10-3/4" ht.,
Overall ht. w/stem 77"; wire 120".
One medium base lamp,
60w max.

*Fixtures shown with
V6.5ST19DLED922/JA8 vintage lamps.*



P500155-071



P400154-071

MAST



P400190-020



Mast combines a clean, modern design expression with faux wood accents for a modern-meets-farmhouse approach to lighting. The contrast of warm wood paired with sleek metallic lines and double glass shades offers a subtly alluring, Zen look to the linear pendant and mini-pendant. An oversized cylindrical frame banded top and bottom in Brushed Nickel or Antique Bronze and trimmed with faux wood accents gives a warm organic feel to the flush mount fixture.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ALSO AVAILABLE IN

Bath and Vanity, page 36
and Wall Sconce at
progresslighting.com





P400190-009

TWO-LIGHT FLUSH MOUNT**P350144-009** Brushed Nickel**P350144-020** Antique Bronze

13" dia., 5-1/4" ht.,

Two medium base lamps,
each 60w max.**FOUR-LIGHT ISLAND****P400190-009** Brushed Nickel**P400190-020** Antique Bronze

38" W., 14-3/4" ht.,

Overall ht. w/stem 80-1/2"; wire 180".

Four medium base lamps,
each 100w max.**ONE-LIGHT MINI-PENDANT****P500192-009** Brushed Nickel**P500192-020** Antique Bronze

6-1/4" dia., 14" ht.,

Overall ht. w/stem 80"; wire 120".

One medium base lamp,
100w max.

P400190-020



P350144-009



P350144-020



P500192-009



P500192-020

REPLAY

Smooth forms, linear details and a pleasingly elegant frame enhance a simplified modern look in the Replay pendant. A rectangular silhouette extending below the etched glass shade makes a strong and simple vertical statement.

FINISHES

- Brushed Nickel - 009
- Black - 031
- Polished Nickel - 104

ALSO AVAILABLE

Complete collection at progresslighting.com

FOUR-LIGHT FOYER PENDANT

P500206-009 Brushed Nickel

P500206-031 Black

P500206-104 Polished Nickel

18" dia., 31-3/4" ht.,

Overall ht. w/chain 106"; wire 180".

Four medium base lamps,
each 100w max.



P500206-009



P500206-104



P500206-031

DRUM SHADE

A perennially popular look, the simple lines of the Drum Shade pendant are refreshed with a Harvest Linen shade, giving a rustic, country casual feel to this classic fixture. The shade has an inner transparent backing, so its beautiful texture is visible from inside out.

FINISH

- Black - 031

FIVE-LIGHT PENDANT CHANDELIER

P400193-031 Black

21-5/8" dia., 21-1/8" ht.,

Overall ht. w/chain 65-1/2"; wire 120".

Five candelabra base lamps,
each 60w max.



P400193-031



P2334-163



P3740-163

P2334-163
Shown as
semi-flush

ARCHIE

The Archie Collection brings a vintage, industrial flair to interior settings. The collection's distinctive double prismatic glass adds visual interest as its crisscross pattern comes to life when illuminated. The unusual, finely crafted strap and knob detail add authentic industrial style. Fixtures are offered in a Vintage Brass finish and provide an updated design to this quintessential collection.

FINISH

- Vintage Brass - 163

TWO-LIGHT SEMI FLUSH CONVERTIBLE

P2334-163 Vintage Brass Hanging and ceiling mount hardware included
12-3/8" dia., 11-3/8" ht.,
Overall ht. w/chain 48-1/2"; wire 120".
Two medium base lamps,
each 100w max.

ALSO AVAILABLE IN

Bath and Vanity, page 31
Complete collection at
progresslighting.com

TWO-LIGHT FLUSH MOUNT

P3740-163 Vintage Brass
12 3/8" dia., 6 1/4" ht.,
Two medium base lamps,
each 75w max.

SIGNAL

Signal has an industrial origin, yet its clean lines beckon a modern sensibility. Clear blown glass shades deliver a lighter touch, balancing the substantial look of the metal angular arm and round backplate. With its emphasis on simplicity and function, Signal is ideal for many residential settings.



P350145-015



P350145-143

FINISHES

- Polished Chrome - 015
- Graphite - 143

ONE-LIGHT FLUSH MOUNT

P350145-015 Polished Chrome
P350145-143 Graphite
5-1/8" dia., 7-5/8" ht.,
One medium base lamp,
60w max.

ALSO AVAILABLE IN

Bath and Vanity, page 40

ETCHED GLASS

Some spaces call for a clean and straightforward close-to-ceiling fixture, and the Etched Glass flush mount easily fills that need. Unhindered by unnecessary detail, the fixture glows through a simple etched glass bowl clasped by a crown molding-inspired, wide metal band in Matte Black or Brushed Nickel.



P350146-009



P350146-031

FINISHES

- Brushed Nickel - 009
- Black - 031



P350147-009

PROGRESSLIGHTING.COM



P350147-031

ONE-LIGHT FLUSH MOUNT

P350146-009 Brushed Nickel
P350146-031 Black
11-1/2" dia., 3-3/4" ht.,
One medium base lamp,
60w max.

TWO-LIGHT FLUSH MOUNT

P350147-009 Brushed Nickel
P350147-031 Black
14" dia., 4-5/8" ht.,
Two medium base lamps,
each 60w max.

INSPIRE LED

Harkening back to a simpler time, the Inspire Collection freshens traditional forms with its clean lines. Now debuting with an integrated LED light source, the wall sconce softly shines through a textured Summer Linen Shade or a creamy Off-White Linen Shade

FINISHES

- Summer Linen - 030
- Off White Linen - 159

ALSO AVAILABLE

Complete collection at
progresslighting.com

LED WALL SCONCE

P710071-030-30 Summer Linen

P710071-159-30 Off White Linen

6-1/4" W., 9" ht.,
 Extends 3-1/8".

One 9w LED module, 3000K,
 90CRI, 624 source lumens.

ADA



P710071-030-30



P710071-159-30

LINEN GLASS SCONCE

With a squared-off, architectural form complemented by etched linen glass, the Linen Glass Sconce is simple, modern and ideal for use in any Transitional setting.

FINISHES

- Brushed Nickel - 009
- Black - 031

ONE-LIGHT WALL SCONCE

P710072-009 Brushed Nickel

P710072-031 Black

6" W., 12" ht.,
 Extends 4".

One medium base lamp,
 75w max.

ADA



P710072-009



P710072-031

ARCHIE



P2992-163

The Archie Collection brings a vintage, industrial flair to interior settings. The collection's distinctive double prismatic glass adds visual interest as its crisscross pattern comes to life when illuminated. The unusual, finely crafted strap and knob detail add authentic industrial style. Vanity fixtures are offered in a Vintage Brass finish and provide an updated design to this quintessential collection.

ONE-LIGHT BATH

P2989-163 Vintage Brass
5 3/4" W., 8 1/4" ht.,
Extends 7". H/CTR 5-1/4".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P2991-163 Vintage Brass
17 W., 8 3/4" ht.,
Extends 7". H/CTR 5-1/4".
Two medium base lamps,
each 100w max.



P2991-163



P2992-163

THREE-LIGHT BATH

P2992-163 Vintage Brass
26 1/4" W., 8 3/4" ht.,
Extends 7". H/CTR 5-1/4".
Three medium base lamps,
each 100w max.



P2989-163



P2997-163

FINISH

● Vintage Brass - 163

ALSO AVAILABLE IN

Close-to-Ceiling, page 29
Complete collection at
progresslighting.com

Fixtures mount up or down.

ADLEY



Fundamentally modern but with a traditional twist, Adley combines a clear glass shade with a curved rectangular back plate. This sophisticated bath light is offered as a one, two, three or four-light fixture in a choice of four finishes. Adley is a universal choice for New Traditional and Transitional settings.

FINISHES

- Brushed Nickel - 009
- Satin Brass - 012
- Black - 031
- Polished Nickel - 104

ONE-LIGHT BATH

P300154-009 Brushed Nickel

P300154-012 Satin Brass
4-1/2" W., 7-3/4" ht.,
Extends 6". H/CTR 5-3/8".
One medium base lamp,
60w max.

TWO-LIGHT BATH

P300155-009 Brushed Nickel

P300155-012 Satin Brass
13-7/8" W., 7-5/8" ht.,
Extends 6". H/CTR 5-3/8".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH

P300156-009 Brushed Nickel

P300156-012 Satin Brass
23" W., 7-5/8" ht.,
Extends 6". H/CTR 5-3/8".
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH

P300157-009 Brushed Nickel

P300157-012 Satin Brass
32" W., 7-5/8" ht.,
Extends 6". H/CTR 5-3/8".
Four medium base lamps,
each 60w max.



P300154-009



P300155-009



P300156-009



P300157-009



P300154-012



P300155-012



P300156-012



P300157-012



P300154-031



P300155-031



P300156-031



P300157-031



P300154-104



P300155-104



P300156-104



P300157-104

ONE-LIGHT BATH**P300154-031** Black**P300154-104** Polished Nickel

4-1/2" W., 7-3/4" ht.,

Extends 6". H/CTR 5-3/8".

One medium base lamp,

60w max.

TWO-LIGHT BATH**P300155-031** Black**P300155-104** Polished Nickel

13-7/8" W., 7-5/8" ht.,

Extends 6". H/CTR 5-3/8".

Two medium base lamps,
each 60w max.**THREE-LIGHT BATH****P300156-031** Black**P300156-104** Polished Nickel

23" W., 7-5/8" ht.,

Extends 6". H/CTR 5-3/8".

Three medium base lamps,
each 60w max.**FOUR-LIGHT BATH****P300157-031** Black**P300157-104** Polished Nickel

32" W., 7-5/8" ht.,

Extends 6". H/CTR 5-3/8".

Four medium base lamps,
each 60w max.*Fixtures mount up or down.*

RUSHTON



P300229-143

Celebrate the past with the industrial-styled Rushton vanity. Mechanical details like a pulley wheel complete with a faux cord holding a clear glass shade, an antique style socket, and an exposed bulb (not included) add vintage charm. The mixed metal fixture is offered in either Brushed Nickel accented with a Black tube arm, or Graphite with an Antique Brass tube arm, for a look that preserves a sense of history.

FINISHES

- Brushed Nickel - 009
- Graphite - 143

ONE-LIGHT BATH

P300226-009 Brushed Nickel

P300226-143 Graphite

5" W., 9-1/2" ht.,

Extends 6". H/CTR 6-1/2".

One medium base lamp,
60w max.



P300226-009



P300226-143

TWO-LIGHT BATH

P300227-009 Brushed Nickel

P300227-143 Graphite

16" W., 9-1/2" ht.,

Extends 6". H/CTR 7".

Two medium base lamps,
each 60w max.



P300227-009



P300227-143



P300228-009

THREE-LIGHT BATH**P300228-009** Brushed Nickel**P300228-143** Graphite

24" W., 9-1/2" ht.,

Extends 6". H/CTR 7".

Three medium base lamps,
each 60w max.**FOUR-LIGHT BATH****P300229-009** Brushed Nickel**P300229-143** Graphite

32" W., 9-1/2" ht.,

Extends 6". H/CTR 7".

Four medium base lamps,
each 60w max.*Fixtures shown with**V6.5ST19DLED922/JA8 vintage lamps.*

P300228-143



P300229-009



P300229-143

MAST



P300217-009

Mast combines a clean, modern design expression with faux wood accents for a modern-meets-farmhouse approach to lighting. The contrast of warm wood paired with sleek metallic lines and double glass shades offers a subtly alluring, Zen look to these vanity fixtures. An oversized cylindrical frame banded top and bottom in Brushed Nickel or Antique Bronze and trimmed with faux wood accents gives a warm organic feel to the flush mount fixture.

TWO-LIGHT BATH

P300216-009 Brushed Nickel

P300216-020 Antique Bronze

13-7/8" W., 7-5/8" ht.,
Extends 6-1/4". H/CTR 5-1/4".

Two medium base lamps,
each 100w max.



P300216-009



P300216-020

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ALSO AVAILABLE IN

Fixture Collections, page 26
and Wall Sconce at
progresslighting.com



P300217-009

THREE-LIGHT BATH

P300217-009 Brushed Nickel
P300217-020 Antique Bronze
 24" W., 7-3/4" ht.,
 Extends 6-1/4". H/CTR 5-1/4".
 Three medium base lamps,
 each 100w max.

FOUR-LIGHT BATH

P300218-009 Brushed Nickel
P300218-020 Antique Bronze
 33-7/8" W., 7-3/4" ht.,
 Extends 6-1/4". H/CTR 5-1/4".
 Four medium base lamps,
 each 100w max.



P300217-020



P300218-009



P300218-020

Fixtures mount up or down.

BRIARWOOD



P300231-143

The classic, X-brace pattern inspired by farmhouse or barn doors is re-imagined in the Briarwood two, three, and four-light wall sconce offerings. The simple geometric shape, a hallmark of the Briarwood collection, is mounted on the faux-painted wood back plate, with a clear glass shade completing the look.

TWO-LIGHT BATH

P300230-020 Antique Bronze

P300230-143 Graphite

14-3/4" W., 8-1/4" ht.,
Extends 6-1/2". H/CTR 5-7/8".

Two medium base lamps,
each 60w max.



P300230-020



P300230-143

FINISHES

- Antique Bronze - 020
- Graphite - 143

ALSO AVAILABLE

Complete collection at
progresslighting.com



P300231-020

THREE-LIGHT BATH**P300231-020** Antique Bronze**P300231-143** Graphite24-3/4" W., 8-1/4" ht.,
Extends 6-1/2". H/CTR 5-7/8".Three medium base lamps,
each 60w max.**FOUR-LIGHT BATH****P300232-020** Antique Bronze**P300232-143** Graphite34-3/4" W., 8-1/4" ht.,
Extends 6-1/2". H/CTR 5-7/8".Four medium base lamps,
each 60w max.*Fixtures mount up or down.**Fixtures shown with
V6.5ST19DLED922/JA8 vintage lamps.*

P300231-143



P300232-020



P300232-143

SIGNAL



Signal has an industrial origin, yet its clean lines beckon a modern sensibility. Clear blown glass shades deliver a lighter touch, balancing the substantial look of the metal angular arm and round backplate. With its emphasis on simplicity and function, Signal is ideal for many residential settings.

FINISHES

- Polished Chrome - 015
- Graphite - 143

ALSO AVAILABLE IN

Close-to-Ceiling, page 29

ONE-LIGHT BATH

P300174-015 Polished Chrome
5-1/8" W., 9-1/8" ht.,
Extends 5-3/8". H/CTR 2-5/8".
One medium base lamp,
60w max.

TWO-LIGHT BATH

P300175-015 Polished Chrome
13-1/2" W., 9-1/8" ht.,
Extends 5-3/8". H/CTR 2-5/8".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH

P300176-015 Polished Chrome
23-1/8" W., 9-1/8" ht.,
Extends 5-3/8". H/CTR 2-5/8".
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH

P300177-015 Polished Chrome
33-1/2" W., 9-1/8" ht.,
Extends 5-3/8". H/CTR 2-5/8".
Four medium base lamps,
each 60w max.



P300174-015



P300175-015



P300176-015



P300177-015



P300174-143

ONE-LIGHT BATH

P300174-143 Graphite
5-1/8" W., 9-1/8" ht.,
Extends 5-3/8". H/CTR 2-5/8".
One medium base lamp,
60w max.

TWO-LIGHT BATH

P300175-143 Graphite
13-1/2" W., 9-1/8" ht.,
Extends 5-3/8". H/CTR 2-5/8".
Two medium base lamps,
each 60w max.



P300175-143

THREE-LIGHT BATH

P300176-143 Graphite
23-1/8" W., 9-1/8" ht.,
Extends 5-3/8". H/CTR 2-5/8".
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH

P300177-143 Graphite
33-1/2" W., 9-1/8" ht.,
Extends 5-3/8". H/CTR 2-5/8".
Four medium base lamps,
each 60w max.

Fixtures mount up or down.

*Fixtures shown with
F8.5A19D927/JA8 vintage lamps.*



P300176-143



P300177-143

CLASSIC



P300233-009



P300233-031

Traditional details and graceful lines add modern elegance to any interior. Classic vanities feature etched glass shades and is offered in Matte Black or Brushed Nickel finish.

FINISHES

- Brushed Nickel - 009
- Black - 031

ALSO AVAILABLE

Complete collection at progresslighting.com

ONE-LIGHT BATH

P300233-009 Brushed Nickel

P300233-031 Black

5" W., 8" ht.,

Extends 7". H/CTR 3".

One medium base lamp,
100w max.



P300234-009



P300234-031

TWO-LIGHT BATH

P300234-009 Brushed Nickel

P300234-031 Black

13" W., 7-7/8" ht.,

Extends 7". H/CTR 3".

Two medium base lamps,
each 100w max.



P300235-009



P300235-031

THREE-LIGHT BATH

P300235-009 Brushed Nickel

P300235-031 Black

24" W., 7-7/8" ht.,

Extends 7". H/CTR 3".

Three medium base lamps,
each 100w max.



P300236-009

FOUR-LIGHT BATH**P300236-009** Brushed Nickel**P300236-031** Black30" W., 7-7/8" ht.,
Extends 7". H/CTR 3".Four medium base lamps,
each 100w max.

P300236-031

FIVE-LIGHT BATH**P300237-009** Brushed Nickel**P300237-031** Black36" W., 7-7/8" ht.,
Extends 7". H/CTR 3".Five medium base lamps,
each 100w max.

P300237-009

SIX-LIGHT BATH**P300238-009** Brushed Nickel**P300238-031** Black48" W., 7-7/8" ht.,
Extends 7". H/CTR 3".Six medium base lamps,
each 100w max.*Fixtures mount up or down.*

P300237-031



P300238-009



P300238-031

GREENE RIDGE



With its uncomplicated lines and tailored look, Greene Ridge unites simplicity and artistry in a tribute to its Craftsman-style inspiration. A strong, boxy shape tops a clear glass shade in keeping with the utilitarian design and lack of curves that define the Arts and Crafts look.

FINISHES

- Black - 031
- Architectural Bronze - 129

ONE-LIGHT HANGING LANTERN

P550033-031 Black
P550033-129 Architectural Bronze
 6-3/4" sq., 14" ht.,
 Overall ht. w/chain 88-1/2"; wire 120".
 One medium base lamp,
 100w max.

ONE-LIGHT SMALL WALL LANTERN

P560099-031 Black
P560099-129 Architectural Bronze
 5-1/4" W., 11-5/8" ht.,
 Extends 6-3/4". H/CTR 8".
 One medium base lamp,
 100w max.

ONE-LIGHT MED WALL LANTERN

P560100-031 Black
P560100-129 Architectural Bronze
 6-3/4" W., 14-1/4" ht.,
 Extends 8-1/4". H/CTR 10-3/4".
 One medium base lamp,
 100w max.

*Fixtures shown with
 V6.5ST19DLED922/JA8 vintage lamps.*



P560099-031



P560099-129



P560100-031



P560100-129




P550033-031



P550033-129



P540032-020



Inspired by the warmth and beauty of hammered copper home accents, Englewood's design displays elements of rustic craftsmanship. Available in Antique Bronze, Black or Antique Pewter, the inside of the shade features a metallic finish, offering higher illumination reflection. Antique Bronze and Black finishes feature a copper inside shade, while the Antique Pewter finish is paired with a metallic silver inner shade. The post top fixture adds the finishing touch to outdoor settings, giving eye-catching appeal to Farmhouse and Rustic homes, and is Dark Sky compliant.



P540032-031

FINISHES

- Antique Bronze - 020
- Black - 031
- Antique Pewter - 103

ALSO AVAILABLE

Complete collection at progresslighting.com

ONE-LIGHT POST LANTERN

P540032-020 Antique Bronze

P540032-031 Black

P540032-103 Antique Pewter

16" W., 13-1/2" ht.

Extends 12".

One medium base lamp,

100w max.

Fits 3" post (sold separately).



P540032-103

GAZE



P2554-3130K shown with Distressed Ebony blades

Three-blade 60" Gaze ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. An opal white shade contains an 18W dimmable, 3000K LED module. Gaze features a dual mount system and includes a three-speed remote control with full range dimming.

FEATURES

- Limited lifetime warranty
- Dual Mount
(flat or sloped ceiling-20°)
- Reversible plywood blades
- White shatterproof lens
- Remote control with batteries is included
- Remote may be replaced with P2630-30 or P2630-95 wall control

SIZE

60" dia., 13-1/8" ht.
80" lead wires

FINISH

● Black - 31

P2554-3130K

Matte Black



Matte Black



Distressed Ebony



Shown with Matte Black blades.



Shown with Distressed Ebony blades.

ALSO AVAILABLE

Complete Fan Collection at
progresslighting.com



P2554-0930K



P2554-1530K



P2554-2030K

ENERGY INFORMATION AT HIGH SPEED

AIRFLOW:	5,902 cubic feet per minute
ELECTRICITY USE:	75 watts (excludes lights)
AIRFLOW EFFICIENCY:	79 cubic feet per minute per watt

T20
Fan

JA8
Light


Dry
Indoor only

LAMPING INFORMATION

18w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable.



Three-Speed Remote Included
Full-range dimming for light
Three-speed fan operation

VAST



P2550-3130K shown with Matte Black blades

Beautiful and expansive in design, the 72" Vast ceiling fan is ideal for use in large areas and outdoor covered areas for maximum cooling. A white opal shade complements a variety of finish options, including Brushed Nickel with Chrome accents, Antique Bronze, White with Chrome accents or Matte Black. Vast features a dual mount system and comes with a full function remote control.

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC motor
- Aluminum blades
- White opal glass
- Remote control with batteries is included

SIZE

72" dia., 16-3/4" ht.
80" lead wires

FINISH

- Black - 31

P2550-3130K

Matte Black shown
and Matte Black blades



Matte Black

**ALSO AVAILABLE**

Complete Fan Collection at
progresslighting.com



P2550-0930K



P2550-2030K



P2550-3030K

ENERGY INFORMATION AT HIGH SPEED

AIRFLOW:	7,982 cubic feet per minute
ELECTRICITY USE:	28 watts (excludes lights)
AIRFLOW EFFICIENCY:	285 cubic feet per minute per watt

LAMPING INFORMATION

18w LED Module, 3000K, 90 CRI,
1400 lumens, dimmable.



Full Function Remote Control Included

Full-range dimming for light

Six-speed fan operation

Reverse direction control



Fan



Light



Damp

Indoor/Outdoor

GULLIVER



P250012-141-22 shown with Antique White Wood

Three circular bands wrap together to create an open design for Gulliver. Fan blades enclosed within a stylish cage design gives the rustic charm of a pendant combined with the functionality of a ceiling fan. Dual toned frame color combinations of Galvanized with antique white accents or Graphite with weathered gray accents. A hand painted wood grained texture complements Rustic and Modern Farmhouse home decor, as well as Urban Industrial and Coastal interior settings.

FEATURES

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC motor
- Remote control with batteries is included

SIZE

23" dia., 18-1/8" ht.
80" lead wires

FINISHES

- Galvanized -141
- Graphite - 143

P250012-141-22

Galvanized



Antique White Wood



P250012-143-22

Graphite



Gray Wood



ENERGY INFORMATION AT HIGH SPEED

AIRFLOW:	1,297 cubic feet per minute
ELECTRICITY USE:	39 watts (excludes lights)
AIRFLOW EFFICIENCY:	33 cubic feet per minute per watt

LAMPING INFORMATION

Three LED medium base vintage lamps, 2200K, 80 CRI, 5.5w max each, included. (dimnable)



Three-Speed Remote Included
Full-range dimming for light
Three-speed fan operation



Canada



T20 Fan



Damp
Indoor/Outdoor

LED EDGELIT FLUSH MOUNT

Edgelit technology creates a large glare free and evenly illuminated surface for a variety of applications for both residential and commercial applications. Offering a low profile design, LED Edgelit Flush Mount is available in 7" in a White finish. Additional sizes available; 11", 14" and 18". The integrated driver does not recess into junction box, allowing for easy installation into 4" octagonal, 4" round PVC and 4-1/2" ceiling pan junction boxes. LED Edgelit Flush Mount is wet location listed and offers a 50,000-hour LED life.

FINISH

○ White - 030

ALSO AVAILABLE

Complete collection at
progresslighting.com

LED EDGELIT FLUSH MOUNT

P810015-030-30 White

7" dia., 1-1/8" ht.

One 15w LED, 3000K,
90CRI, 1000 lumens.



P810015-030-30

EDGELIT RECESSED ACCESSORIES

Progress lighting has released two new accessories for the Edgelit Recessed fixtures. P860040-028 - 18" extender cable allows for the junction box to be remote and mounted further away from the fixture. P860044 - rough in accessory allows for Edge Lit recessed fixtures to be used in new construction installations. This accessory ensures a mounting location after the dry wall is installed and can be used when building codes require that the luminaire is supported from the building structure

18" CABLE W/ TERMINALS

P860040-028 Satin White

18" L., 1/2" dia.

EDGELIT RECESSED ROUGH IN ACCESSORY

P860044-001 Unfinished



20" W., 9" ht.,



P860040-028



P860044-001



5" SHALLOW CEILING RECESSED HOUSINGS

5" MEDIUM BASE REMODEL HOUSING

For complete fixture, order housing with trim.

Remodel Air-Tight IC



P1841-ICAT

Ceiling opening: 5-1/2"
Recessed depth: 5-3/8"
Pryouts: 1/2"

P1841-ICAT REMODEL WITH E26 SOCKET, IC RATED, AIR-TIGHT HOUSING

- Rated for direct contact with insulated ceiling
- Adjustable housing to accommodate ceiling thickness 1/2" to 1-1/2"
- Meets ASTM-E283 air flow requirements
- Use with compatible items only



5" LED REMODEL HOUSING

For complete fixture, order housing with trim.

Remodel Air-Tight IC



P1841-LED

Ceiling opening: 5-1/2"
Recessed depth: 5-3/8"
Pryouts: 1/2"

P1841-LED REMODEL, IC RATED, AIR-TIGHT HOUSING

- Rated for direct contact with insulated ceiling
- Adjustable housing to accommodate ceiling thickness 1/2" to 1-1/2"
- Meets ASTM-E283 air flow requirements
- Use with compatible LED items only. Visit progresslighting.com.



TRIM FOR P1841-ICAT

6-1/2" outside diameter.. Can also be used with P851-ICAT



SHALLOW STEP BAFFLE

Damp location listed.

P8475-28 Satin White

Lamp: PAR30/R30, 50w max.

Compatible with **P851-ICAT** and **P1841-ICAT**.

5" RECESSED TRIMS

6-1/2" outside diameter. Compatible with P851-ICAT housing.



OPEN

With gasket.

Damp location listed.

P8268-21 Clear Alzak

Lamp: PAR30/R30, 50w max.

Compatible with **P851-ICAT**.



OPEN

With gasket

Damp Location Listed

P8268-28 Satin White

Lamp: PAR30/R30, 50w max.

Compatible with **P851-ICAT**.



STEP BAFFLE

Damp location listed.

P868-31 Black

Lamp: PAR30/R30, 50w max.

Compatible with **P851-ICAT**.



P851-ICAT

New Construction, IC rated,

Air-tight Housing. Complete collection at progresslighting.com.

LED TAPE UNDERCABINET SYSTEM

LED Tape provides lighting to enhance aesthetics, while also aiding in tasks around the home. Common applications for LED Tape include; undercabinet lighting in kitchens to add illumination to work surfaces, highlighting back splashes in kitchens or bathroom areas and adding toe kick lighting at the bases of cabinets for dramatic and functional lighting.

HIDE a LITE

PROGRESS **LED**

FOLLOW FOUR SIMPLE STEPS:

1. CHOOSE A TAPE LENGTH






12", 60" and 240" lengths to meet different sized projects and features an adhesive backing for easy application to desired surfaces.



Flexible tape can be cut every 4 inches (cut ends can be reconnected, allowing for full use of LED tape).



Tape is fully enclosed in silicone to allow for use in damp location. 24 VDC tape pairs with 24 VDC power supplies.

PRODUCT NO.	COLOR TEMP.	SIZE	
P700008-000-27 P700008-000-30	2700K 3000K	12" L., 3/8" W., 1/8" ht.	
P700009-000-27 P700009-000-30	2700K 3000K	60" L., 3/8" W., 1/8" ht.	
P700010-000-27 P700010-000-30	2700K 3000K	240" L., 3/8" W., 1/8" ht.	

LED FEATURES

- 90CRI, 50,000 hr. life
- 300 lumens per foot and consumes 4.2 watts per foot (71 lumens/w)
- Field cuttable at every 4" to end of run.
- cETLus listed damp location
- 5 year warranty



P700008-000-27



P700009-000-27
P700010-000-27

2. SELECT TRANSFORMER

Progress Lighting offers multiple power supplies to meet various project sizes. Power supplies can be dimmed, flicker-free, on Forward Phase (TRIAC) and Reverse Phase (ELV) dimmers down to 10% output.

PRODUCT NO.	FINISH	SIZE	WATT	MAX LENGTH OF TAPE
P700020-031	Black	8-3/16" L., . 2" W., 1-3/4" HT	25w	60" Tape
P700021-031	Black	8-3/16" L., 2" W., 1-3/4" HT.	40w	120" Tape
P700023-031	Black	9-3/16" L., 3-3/8" W., 1-15/16" HT.	80w	240" Tape

PRODUCT FEATURES

- Maximum operating temperature -20° C to +40° C
- Enclosure provided
- Wire nuts and additional hardware included



P700020-000
P700021-000
P700023-000

3. ADDITIONAL SYSTEM CONNECTORS

Various connectors allow for customized layouts. Use linking connectors to join runs of tape. Use the L Connector for 90° bends and use the Y Connector to split one run of tape into two.



Connectors feature piercing conductors for secure connection.



Y, L and multi-linking connectors allow for flexibility in design.



Connectors provided with snap-fit covers for intuitive installation.

2" CONNECTOR CORD

P700011-000 Black
Connect tape sections
(P700008, P700009, P700010)
2" L., 5/8" W., 1/4" ht.



72" CONNECTOR CORD

P700015-000 Black
Connect tape sections
(P700008, P700009, P700010)
72" L., 5/8" W., 1/4" ht.



12" CONNECTOR CORD

P700012-000 Black
Connect tape sections
(P700008, P700009, P700010)
12" L., 5/8" W., 1/4" ht.



L CONNECTOR

P700016-000 Black
90° connector for connecting sections of tape (P700008, P700009, P700010) on corners.
2-1/16" L., 2-1/16" W., 1/6" ht.



18" CONNECTOR CORD

P700013-000 Black
Connect tape sections
(P700008, P700009, P700010)
18" L., 5/8" W., 1/4" ht.



Y CONNECTOR

P700017-000 Black
Three-way Y connector for connecting sections of tape (P700008, P700009, P700010)
3-3/16" L., 3-3/16" W., 1/4" ht.



36" CONNECTOR CORD

P700014-000 Black
Connect tape sections
(P700008, P700009, P700010)
36" L., 5/8" W., 1/4" ht.



OUTPUT POWER CONNECTOR

P700022-000 Black
60" L., 5/8" W., 1/4" ht.



4. MOUNTING CLIPS/END CLIPS

Select end caps or add mounting clips to finish the installation.

P700018-000

Pack of 10 clips/screws for straight runs for added support
(2 clips per foot recommended)
1-1/8" L., 1/4" W., 1/8" ht.



P700019-000

End caps to terminate run of LED tape. For use when tape has been cut at end of run. Sold in sets of 10.
1/2" L., 1/2" W., 1/4" ht.



CEILING FAN ACCESSORY DOWNRODS

3/4" diameter; approximately 1" outside diameter.

CEILING HT. DOWNROD L.	9'-10'	10'-11'	11'-12'	12'-14'	13'-15'	14'-16'	15'-17'
	12"	18"	24"	36"	48"	60"	72"
○ Matte White	P2603-28	P2604-28	P2605-28	P2606-28	P2607-28	-	-
● Matte Black	P2603-31	P2604-31	P2605-31	P2606-31	P2607-31	-	-



PRODUCT INDEX

P1000

P1841-ICAT	53
P1841-LED	53

P200000

P2334-163	29
P2603-28	56
P2603-31	56
P2604-28	56
P2604-31	56
P2605-28	56
P2605-31	56
P2606-28	56
P2606-31	56
P2607-28	56
P2607-31	56
P250012-141-22	50
P250012-143-22	51
P2550-3130K	48
P2554-3130K	46
P2989-163	31
P2991-163	31
P2992-163	31
P2997-163	31

P300000

P300154-009	32
P300154-012	32
P300154-031	33
P300154-104	33
P300155-009	32
P300155-012	32
P300155-031	33
P300155-104	33
P300156-009	32
P300156-012	32
P300156-031	33
P300156-104	33
P300157-009	32
P300157-012	32
P300157-031	33
P300157-104	33
P300174-015	40
P300174-143	41
P300175-015	40
P300175-143	41

P300176-015	40
P300176-143	41
P300177-015	40
P300177-143	41
P300216-009	36
P300216-020	36
P300217-009	36
P300217-020	37
P300218-009	37
P300218-020	37
P300226-009	34
P300226-143	34
P300227-009	34
P300227-143	34
P300228-009	35
P300228-143	35
P300229-009	35
P300229-143	34
P300230-020	38
P300230-143	38
P300231-020	39
P300231-143	38
P300232-020	39
P300232-143	39
P300233-009	42
P300233-031	42
P300234-009	42
P300234-031	42
P300235-009	42
P300235-031	42
P300236-009	43
P300236-031	43
P300237-009	43
P300237-031	43
P300238-009	43
P300238-031	43
P350110-009	20
P350110-020	22
P350116-071	25
P350144-009	27
P350144-020	27
P350145-015	29
P350145-143	29
P350146-009	29
P350146-031	29
P350147-009	29
P350147-031	29
P3740-163	29

P400000

P400115-031	16
P400115-104	18
P400153-071	24
P400154-071	25
P400175-031	17
P400175-104	19
P400187-031	17
P400187-104	19
P400190-009	27
P400190-020	26
P400193-031	28

P500000

P500121-031	17
P500121-104	19
P500122-031	17
P500122-104	19
P500138-009	21
P500138-020	23
P500139-009	21
P500139-020	23
P500155-071	25
P500192-009	27
P500192-020	27
P500206-009	28
P500206-031	28
P500206-104	28
P540032-020	45
P540032-031	45
P540032-103	45
P550033-031	44
P550033-129	44
P560099-031	44
P560099-129	44
P560100-031	44
P560100-129	44

P700000

P700008-000-27	54
P700008-000-30	54
P700009-000-27	54
P700009-000-30	54
P700010-000-27	54
P700010-000-30	54
P700011-000	55
P700012-000	55
P700013-000	55
P700014-000	55
P700015-000	55
P700016-000	55
P700017-000	55
P700018-000	55
P700019-000	55
P700020-031	54
P700021-031	54
P700022-000	55
P700023-031	54
P710045-009	21
P710045-020	23
P710071-030-30	30
P710071-159-30	30
P710072-009	30
P710072-031	30

P800000

P810015-030-30	52
P8268-21	53
P8268-28	53
P8475-28	53
P860040-028	52
P860044-001	52
P868-31	53



Products referencing this logo meet the energy efficiency requirements for light fixtures set forth in ENERGY STAR® product specifications. Please refer to www.energystar.gov for specific product qualifications and list of certified products.



This marking indicates fixtures that have an **integrated LED** or replaceable LED module that has been tested and listed in the California Appliance Database. Check for certified lamps, fixtures or LED light engines by searching the MAEDBS database. Go to cacertappliances.energy.ca.gov



Products comply with the California Appliance Efficiency Regulations. Certified products are listed on the appliance efficiency database found at www.appliances.energy.ca.gov.



Dry location, indoor only fans should only be used indoors. Even if an outdoor area or screened-in porch is covered, the motor and the blades can be affected when exposed to humidity.



Damp location, indoor/outdoor fans may be used indoors or outdoors under covered porches and should not be subjected to water spray or rain.



The ceiling fan products with this logo have passed the cUL requirements and are available for sale in Canada. These products include the additional safety features needed to comply with the regulations in Canada. Items with the icon are listed with NRCan.

Every effort has been made to ensure the accuracy of information in this catalog. Progress Lighting reserves the right to make product changes from time to time, without prior notification, which may change the information provided in this catalog. Errors brought to our attention will be corrected in subsequent issues.

UL, CSA, or ETL Listed or Classified unless otherwise noted. Bulbs (lamps) not included with fixtures unless specified. Specifications subject to change without notice.

Metal finishes not specified as "solid" have quality plated or painted finishes.

Finish representations are high resolution digital reproductions, and, while every effort has been made to render colors accurately, they may vary slightly from the actual product, especially hand-painted finishes, due to the nature of hand craftsmanship.



PROGRESS LIGHTING

701 Millennium Boulevard
Greenville, South Carolina
29607

progresslighting.com

