



LED Lighting Solutions

LIGHT COMMERCIAL • RESIDENTIAL LIGHTING



“Wherever people live, work and play,
you’ll find Lithonia Lighting[®]
LED lighting.”



Choose from our comprehensive line of residential and light commercial LED fixtures to enhance your home, multi-family project, assisted living community, workplace, hospitality area or retail space.

Why Lithonia Lighting LED?



ENERGY SAVINGS



MAINTENANCE SAVINGS



PERFORMANCE & QUALITY OF LIGHT



STOCK AVAILABLE - SINGLES & JOB LOT QUANTITIES



24-HOUR PERFORMANCE IDEAL FOR COMMERCIAL APPLICATIONS

Lithonia Lighting is a recognized leader in both lighting and LED technology, offering innovative products for all applications. Our products have always been known for quality, reliability and performance and we stand behind what we deliver.

Let Lithonia Lighting LED products create a better space for you!



- LED Recessed Downlighting 4
- LED Mini Pendants & Sconces 6
- LED Flush Mounts 8
- LED Track Lighting 10
- LED Lamps 12
- LED Cabinet Lighting 14
- LED Utility 16
- LED Security Floods 18
- LED Building Perimeter 20
- LED Entry Lights 22
- LED Canopy & Flood Lights 24
- Ordering Information 26

LED Recessed Downlighting

Illuminate general areas with recessed lighting

Lithonia Lighting offers a wide assortment of recessed LED downlighting solutions via integrated LED fixtures and Acculamp® LED lamped fixtures.

Recessed downlights using LED lamps from Acculamp are available in traditional recessed downlight fixture styles to deliver on the promise of LED — long life and energy savings all with a consistent look. Recessed downlights with integrated LEDs offer a new level of performance with higher life and lumens along with a simple, clean and elegant look.

- Available in a variety of finishes, color temperatures and lumen packages
- Lower maintenance, energy savings and delivery of light where it is needed
- Quick installation and retrofit

Suggested applications:

Ideal for general and task illumination in commercial and residential spaces.



6" – 6BP / 5" – 5BP / 4" – 4BP
P Series LED Downlight Retrofits

Finish:



Matte White (MW)

Coming soon — Black Baffle, Brushed Nickel, Oil Rubbed Bronze, Clear Diffuse



6" – 6G1 / 5" – 5G1 / 4" – 4G1
LED Gimbal Downlight Retrofits

Finishes:



Oil Rubbed Bronze (ORB)




Matte White (MW)



Matte Black (MB)



Brushed Nickel (BN)



6" – BR30, L7X & 6" Trim / 5" – BR30, L5 & 5" Trim
4" – BR20, L3 & 4" Trim
LED BR30 w/New Construction Housing and Full Reflector

Finishes:



Matte White (MW)



Black Baffle



Oil Rubbed Bronze (ORB)



Clear Specular (AZ)



Brushed Nickel (BN)



Clear Diffuse (A)



“We are a company of engineers...
applying technology and science to
create better products.”



LED BR lamps from Acculamp

The Acculamp BR lamps replace up to 100W incandescent lamps, with savings of up to 84% over traditional sources. These lamps can provide a total solution when paired with Lithonia Downlighting or Track fixtures.

See Page 12 for more details.



See more at www.lithonia.com



6" – BR30, L7X & 6" Eyeball / 5" – BR30, L5 & 5" Eyeball
4" – BR20, L3 & 4" Eyeball
LED BR30 w/New Construction Housing and Eyeball Trim

Finishes:



Matte White (MW)

Brushed Nickel (BN)

Oil Rubbed Bronze (ORB)




6" – 6BP & L7XLED T24 / 5" – 5BP & L5LED T24
4" – 4BP & L3LED T24
P Series LED Downlight w/New Construction LED Housing

Finish:



Matte White (MW)

Coming soon — Black Baffle, Brushed Nickel, Oil Rubbed Bronze, Clear Diffuse



6" – 6G1 & L7XLED T24 / 5" – 5G1 & L5LED T24
4" – 4G1 & L3LED T24
LED Gimbal Downlight w/New Construction LED Housing

Finishes:



Oil Rubbed Bronze (ORB)

Matte White (MW)

Matte Black (MB)

Brushed Nickel (BN)

See ordering information starting on page 26 for a complete listing of color temperature, finish and lumen options.

LED Mini Pendants & Sconces

Pendants and sconces illuminate and accent

LED Mini Pendants and Mini Sconces from Lithonia Lighting offer a wide selection of interchangeable decorative shades and high-performance LED fitters for matching or complementing your lighting design and decor. Advanced LED technology enables the smaller overall design making the mini pendants and sconces an attractive, energy-saving (9.5W) solution for accent or task lighting.

- Designed with style in mind around integrated LED source
- High performance dimmable illumination
- Perfect solution for accent or task lighting

Suggested applications:

Ideal for accent or task lighting in kitchens, common areas and bars in multi-family, hospitality and retail spaces.



DGNG 1007*
Blue Glass in Glass
5" W x 3-3/4" H



DTCL 1005*
Apple Red Tall Cylinder
3-3/8" W x 9-1/4" H



DGWW 1003*
Frosted White Cylinder Wave
4" W x 7-3/4" H



DSCL 1009*
Amber Twist Cylinder
3-3/8" W x 6" H



DBEL 1001*
Opal White Bell
4-1/2" W x 10-1/2" H

*Hardware and shades sold separately
**Back plate and diffuser sold separately



“For 60 years, the building industry has put its faith in our abilities and products.”

LED pendants and wall mount

Provides maintenance-free, energy-efficient general purpose and/or accent lighting in residential and commercial indoor applications. Designed for use with a variety of Lithonia Lighting decorative sconce diffusers to create a look that perfectly complements any décor.

Fitter and back plate sold separately from decorative shades to allow for maximum customization.



See more at www.lithonia.com/LEDpendants-sconces




DBIL 1015*
Rain Drop Billet
4-3/8" W x 5-1/2" H



DLSD10 BZ**
Boxed Diffuser
8" W x 4" H



DLSD7 BZ F08**
1/2 Cylinder Diffuser
10-7/8" W x 3-3/4" H



DLSD15**
Acrylic Diffuser
16-7/8" W x 3-7/8" H

See ordering information starting on page 26 for a complete listing of color temperature, finish and lumen options.

LED Flush Mounts

Save space with flush mount lighting

LED Flush Mount fixtures from Lithonia Lighting offer an excellent selection of LED everyday lighting for ceilings and walls with tremendous energy and cost-savings and long-life.

Designed for versatility and hassle-free installation — in a variety of shapes and sizes for nearly every application. Great illumination in a compact size. Simple dimmable illumination at your fingertips.

- Quick, easy installation
- Commercial rated for 24-hour operation
- Versatile enough for dozens of applications

Suggested applications:

Ideal for 24-hour applications such as hospitality or light commercial spaces, as well as common utility areas such as closets, laundry areas and hallways.



FMML 7 840 WL
LED Versi Lite
(Also wet location)

Finishes: ● Textured Bronze (DBBT) ● White



FMLSL 11 14840
11" Low Profile Square



FMLRL 11 14840
11" Low Profile Round



“We are industry professionals talking to other industry professionals. We speak your language.”

Versatile LED ceiling mounts

LED Flush Mount lighting from Lithonia Lighting is ideal for any situation that calls for clean aesthetics and performance. With 50,000 hours of light and no bulb changeouts these fixtures are a smart solution.

See more at www.lithonia.com



FMLRL 14 20840
14" Low Profile Round



FMLS 14 20840
14" Low Profile Square

See ordering information starting on page 26 for a complete listing of color temperature, finish and lumen options.

LED Track Lighting

Track lighting accents features and highlights task areas

For a new level of contemporary style and flair, consider Lithonia Lighting track heads with integrated LEDs. For a more traditional appearance, track heads are also available with LED lamps by Acculamp. Both family of products deliver on the promise of LED — long life and energy savings, from a market leader in LED technology.

- Customizable LED track program to fit your needs
- Multiple finishes and styles to match your décor
- Two distributions available to fit your task and accent lighting needs

Suggested applications:

Ideal for accent or task lighting in kitchens, common areas and bars in multi-family, hospitality and retail spaces.



Spotlight GU10 LED Lamp Track

Head: LTHSPLT MR16GU10 LED
Kit: LTKSPLT MR16GU10 LED

Finishes:
Oil Rubbed Bronze (ORB) Brushed Nickel (BN)



Shade BR20 LED Track

Head: LTHBRSD BR20 LED
Kit: LTKBRSD BR20 LED

Finishes:
Oil Rubbed Bronze (ORB) Brushed Nickel (BN)



Step Baffle Shade BR30 LED Track

Head: LTHSTBF BR30 LED
Kit: LTKSTBF BR30 LED

Finishes:
Matte White (MW) Black (DBL)



Step Baffle Shade BR20 LED Track

Head: LTHSTBF BR20 LED
Kit: LTKSTBF BR20 LED

Finishes:
Matte White (MW) Black (DBL)



“A solid handshake...you don't find that everywhere. But you find it at Lithonia Lighting.”



Ordering track is easy with 5 piece track kits

Each track kit comes with 3 lamped heads to your specifications, a 4' section of track, and a floating power track canopy to deliver electricity. Add on track sticks and heads with numerous connectors and adapters to customize your installation.

See more at www.lithonia.com



Spotlight Integrated LED Track

Head: LTIHSPILT ORB
Kit: LTIKSPLT ORB

Finish:  Oil Rubbed Bronze (ORB)



Bell Integrated LED Track

Head: LTIHBELL ORB
Kit: LTIKBELL ORB

Finish:  Oil Rubbed Bronze (ORB)



Gavel Integrated LED Track

Head: LTIHGAVL BN
Kit: LTIKGAVL BN

Finish:  Brushed Nickel (BN)



Mesh Back Integrated LED Track

Head: LTIHMSBK BN
Kit: LTIKMSBK BN

Finish:  Brushed Nickel (BN)

See ordering information starting on page 26 for a complete listing of color temperature, finish and lumen options.

LED Lamps

General purpose bulbs for everyday use

Acculamp offers a simple, energy efficient replacement option for existing technology, reducing energy costs up to 84% over traditional sources. They seamlessly replace incandescent bulbs by mimicking even distribution of light desired in residential and light commercial applications.

- Easiest way to upgrade a fixture to LED
- Most common lamp styles for any application
- Lower maintenance and energy savings

Suggested applications:

Ideal upgrade to LED in any application that uses a screw-based incandescent, halogen or CFL lamp where energy-efficient light output is desired.



BR20

ALEBR20 500L DIM M12
50W Incandescent Replacement



BR30

ALEBR30 850L DIM M12
75W Incandescent Replacement



BR40

ALEBR40 1045L DIM M12
100W Incandescent Replacement



A15 LAMPS

ALGP 250L DIM M60
30W Incandescent Replacement



“Confidence, certainty and consistent satisfaction have been the building block of our company.”



Pair Acculamp LED lamps with track and recessed fixtures from Lithonia Lighting

Our track and recessed fixtures pair well with the LED BR and GU10 lamps from Acculamp. With light output equivalent up to 100W incandescent lamps and energy savings of up to 84% over traditional sources, Acculamp LED lamps work great in round recessed lights, and directional eyeballs, gimbals and track heads, with a variety of finishes to fit your décor.



See more at www.acculamp.com



A19 Lamps
ALGP 420L DIM M60
40W Incandescent Replacement



A21 Lamps
ALGP 620L DIM M60
50W Incandescent Replacement



Candle Lamps
ALCND 250L FSG DIM M60 (Frosted)
ALCND 250L CSG DIM M60 (Clear)
35W Incandescent Replacement



GU10 MR16 Lamp
ALEMR16 280L WFL GU10 DIM
35W Incandescent Replacement

See ordering information starting on page 26 for a complete listing of color temperature, finish and lumen options.

LED Cabinet Lighting

Simple illumination at your fingertips

Linkable Cabinet Lighting solutions by Lithonia Lighting offer an array of options for cabinet lighting, featuring innovative features such as our UCLED adjustable swivel head design.

Each fixture can link together to create a chain of fixtures that can be operated by a single switch. Our products are engineered to surpass lighting expectations for your residential or light commercial needs.

- Linkable for multiple fixture installations
- Array of options meet all project needs
- Several finish and color temperatures available

Suggested applications:

Ideal for under cabinet, over cabinet, shelf, cover and toe-kick illumination in light commercial, residential and hospitality spaces.



UCLD 12 BZ M4, UCLD 18 BN M4, UCLD 24 WH M4
UCLD LED

- Finishes:**
- **Brushed Nickel (BN)**
 - **Bronze (BZ)**
 - **White (WH)**



RAZ9 M6, RAZ18 M6
Rayzer LED Modular System



“We are committed to providing sustainable lighting solutions enhanced by LED.”

Linkable cabinet lighting performance

The Lithonia Lighting linkable cabinet lighting family is designed for versatility and hassle-free installation. Each member of the linkable cabinet lighting family can be easily interchanged to upgrade your existing Lithonia Lighting fixtures.

See more at www.lithonia.com



STK6 M12, STK12 M12, STK18 M12
LED Stick



LOC 35 120

Over Cabinet Downlight

Convert to LED with our LED Acculamp MR16

See ordering information starting on page 26 for a complete listing of color temperature, finish and lumen options.

LED Utility

Built for everyday use

LED utility lights from Lithonia Lighting provide a wide range of products for multiple applications. Whether lighting your work area or the laundry facility in an apartment complex, LED lighting products provide excellent lighting performance and longer life than traditional lamp sources.


- Durable and resilient
- Even illumination and long life
- Reduces energy and maintenance costs

Suggested applications:

Ideal for general purpose and task areas where consistent, even illumination is designed for maximum energy savings and long life.



LBL2 & LBL4
LED Wrap



ZL1N & ZL2N
LED Strip



2GTL
LED Troffer



“The benefits of LED lighting
get even better
with the choices to suit your needs.”


Rely on LED

LED technology ensures extended service life of at least 50,000 hours. Less input watts and no lamp maintenance minimizes your total cost of ownership.

See more at www.lithonia.com



1290L
LED Shoplight



1292L
High Lumen LED Shoplight

See ordering information starting on page 26 for a complete listing of color temperature, finish and lumen options.

LED Security Floods

Energy-saving security lighting solution

LED Floodlights from Lithonia Lighting integrate long-life LED technology in an affordable, energy-saving security lighting solution.

- High-performance motion sensors promote safe environments
- Integrated photocells provide dusk-to-dawn operation
- Multiple heads allow for easy aiming of light



Suggested applications:

Ideal for anywhere you would use a wall pack or PAR holder security light such as covers, loading docks, driveways and building perimeter lighting in light commercial and multi-family applications.



OFLR 6LC 120 MO


2-Head LED Floodlight with 180° motion sensor including "look-down" perimeter protection

Finishes:  
Bronze (BZ) White (WH)



OFLR 6LC 120 P



Dusk-to-Dawn 2-Head LED Floodlight

Finishes:  
Bronze (BZ) White (WH)



OFLR 9LN 120 MO

3-Head LED Floodlight with 180° motion sensor including "look-down" perimeter protection

Finishes:  
Bronze (BZ) White (WH)



“Successfully combining safety and security with a decorative design.”



Delivering the promise of LED

Industry-leading performance and value. Optimal cost-per-lumen solution for outdoor security lighting.

See more at www.lithonia.com





OFLR 9LN 120 P
Dusk-to-Dawn 3-Head LED Floodlight

Finishes:  **(BZ)**  **(WH)**



OLF 2RH 40K 120 MO
2-Head LED Floodlight with 180° motion sensor

Finishes:  **(BZ)**  **(WH)**



OLF 14 PE BZ
LED Security Floodlight with dusk to dawn photocell

See ordering information starting on page 26 for a complete listing of color temperature, finish and lumen options.

LED Building Perimeter

Value and versatility defined

LED Wall Packs from Lithonia Lighting come in a wide variety of designs making it easy to find the right LED Wall Pack for your project. Each is designed with long-life LED technology for energy savings of up to 85%.

- Traditional-style LED luminaires for seamless renovations
- Modern designs for new construction
- Integrated photocells for energy-saving dusk-to-dawn operation

Suggested applications:

Ideal for illuminating the perimeter area of light commercial and residential spaces with a variety of light distributions and forms to meet your needs.



OLAW23 53K 120 PE BZ
LED Area / Wall Light
Replaces up to 100W Metal Halide



OLW14
LED Wall Pack
Replaces up to 175W Metal Halide

Finishes: ● Bronze ● White (WH)



OLW 23/31
LED Wall Pack
Replaces up to 250W Metal Halide

Finishes: ● Dark Bronze ● White (WH)



TDD LED 1 40K 120 PE
LED Barn Light / Wall Pack
Replaces up to 100W Metal Halide



“Protecting your business
and your home
with LED lighting.”

Protected against the elements

Each cast aluminum housing has either a glass or polycarbonate lens to protect the LEDs. These fixtures are sealed against moisture and environmental contaminants and the exterior parts are protected by a powder-coat finish that provides superior resistance to corrosion and weathering. Rest assured that they are built to withstand extreme climate changes without cracking or peeling

See more at www.lithonia.com



TWH LED / TWP LED

LED Wall Pack

Replaces up to 400W Metal Halide



TWR1 LED / TWR2 LED

LED Wall Pack

Replaces up to 320W / 400W Metal Halide



DSXW LED

LED Wall Pack

Replaces up to 400W Metal Halide

See ordering information starting on page 26 for a complete listing of color temperature, finish and lumen options.

LED Entry Lights

Properly illuminate your entryway

LED entry lights from Lithonia Lighting provides energy-efficient accent lighting that adds warmth and illumination to welcome guests without unwanted glare. Many different styles to match building aesthetics.

- Designs to match any building's aesthetic
- Multiple lumen output options available to light all size spaces
- Long life for minimal maintenance

Suggested applications:

Ideal for outdoor walkways, stairways and as accent lighting around entrance doors in commercial, multifamily and single family residential settings.



OLWP 11 PE BZ
LED Wall Pack
Replaces up to 70W HPS



TWS LED 1 50K 120 PE
LED Wall Pack
Replaces up to 70W HPS



OLCS 8
LED Wall Pack
Replaces up to 60W Incandescent

Finishes: Bronze (DDB) White (WH)



OLLWD
One-light LED Wall Cylinder
Replaces up to 60W Incandescent

Finishes: Bronze (DDB) White (WH)



OLLWU
Two-light LED Wall Cylinder
Replaces up to 2 60W Incandescent

Finishes: Bronze (DDB) White (WH)



“Invite them with lighting that feels pleasant and comfortable.”

Inviting light

Welcome them before they reach the door. The outside of the structure is all about first impressions. Decisions will be made when the guest first drives up to the entrance. Lighting plays a key role in setting the standard for what guests will find beyond the front doors.

See more at www.lithonia.com



OLSR

LED Small Wall Pack
Replaces up to 40W Incandescent

Finishes:  Bronze (DDB)  White (WH)



OLSS

LED Small Wall Pack
Replaces up to 40W Incandescent

Finishes:  Bronze (DDB)  White (WH)



OLVLT

Vapor Tight LED
Replaces up to 100W Incandescent

See ordering information starting on page 26 for a complete listing of color temperature, finish and lumen options.

LED Canopy & Flood Lights

Seamless and beautiful integration

Selecting the best outdoor LED luminaires can be daunting, especially when designing for a variety of applications on a single site. Whether it is performance, long life, energy savings or aesthetics that drives your decision, these LED luminaires deliver better lighting from every angle.

- Next-generation LED technology
- Precision engineered optics provide enhanced optical control
- Long life for limited maintenance

Suggested applications:

Floodlights are ideal for wall or ground mount applications to accent or feature building aesthetics. Canopy lights are ideal for outdoor walkways, parking areas, garages and loading areas.



VRC LED 1 50K MVOLT
LED Canopy/Ceiling
Replaces up to 250W Metal Halide



OLCFM 15
LED Outdoor Ceiling-Mount/Wall Light
Replaces up to 100W Incandescent

Finishes:  
Bronze (DBB) White (WH)



OSTLLED 120 P BL
LED Landscape Stake Light
Replaces up to 50W Quartz Halogen



OLBS 8
LED Bullet Spot
Replaces up to 100W PAR38 Halogen



OLBF 8
LED Bullet Flood
Replaces up to 100W PAR38 Halogen



“Our promise of delivering lighting from every angle.”

Safe and secure

Canopy lighting and flood lighting combine to provide a welcoming, secure environment. Long life LEDs allow for limited maintenance, giving you worry-free lighting for your outdoor spaces.

See more at www.lithonia.com



DSXF1 LED 1
LED Flood Light
Replaces up to 100W Metal Halide



DSXF1 LED 2
LED Flood Light
Replaces up to 175W Metal Halide



DSXF2 LED 3
LED Flood Light
Replaces up to 250W Metal Halide



DSXF2 LED 4
LED Flood Light
Replaces up to 250W Metal Halide

See ordering information starting on page 26 for a complete listing of color temperature, finish and lumen options.



“When it comes to key elements
with those y



of your building project, do business
you can trust.”

Ordering Information

Integrated LED Recessed Downlighting

ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.

EXAMPLE: **4BPMW LED L3LED T24**

Series/Reflector	Finish	Lamps/Lumens	Color Temperature	Voltage	Options
4BP 4" Baffle LED Module	MW Matte White	LED 620 Lumens	(blank) 3000K	(blank) 120	L3LED T24¹ New construction rough-in LED base L3LED T24¹ Remodel rough-in LED base L3² New construction rough-in L3R² Remodel rough-in
4G1 4" Gimbal LED Module	MW Matte White	LED 435 Lumens			
	MB Matte Black				
	ORB Oil Rubbed Bronze BN Brushed Nickel				
5BP 5" Baffle LED Module	MW Matte White	LED 620 Lumens	(blank) 3000K	(blank) 120	L5LED T24¹ New construction rough-in LED base L5LED T24¹ Remodel rough-in LED base L5² New construction rough-in L5R² Remodel rough-in
5G1 5" Gimbal LED Module	MW Matte White	LED 600 Lumens			
	MB Matte Black				
	ORB Oil Rubbed Bronze BN Brushed Nickel				
6BP 6" Baffle LED Module	MW Matte White	LED 620 Lumens HL LED 950 Lumens	(blank) 3000K	(blank) 120	L7XLED T24¹ New construction rough-in LED base L7XRLED T24¹ Remodel rough-in LED base LC6LED T24¹ New construction rough-in LED base L7X² New construction rough-in L7XR² Remodel rough-in LC6² New construction rough-in LCP^{2,3} New construction shallow rough-in L7XP^{2,3} New construction shallow rough-in L7XPR^{2,3} Remodel shallow rough-in
6G1 6" Gimbal LED Module	MW Matte White	LED 620 Lumens			
	MB Matte Black				
	ORB Oil Rubbed Bronze BN Brushed Nickel				

Accessories

TSA6	Makes 6" non-bracket housing compatible with the LED module; ships as units, J6, or J25
TSA5	Makes 5" non-bracket housing compatible with the LED module; ships as units, J6, or J25
FL2LED	Make L7XF housings compatible with the LED module

Notes:

¹ LED module ships less E26 adaptor and hardwire kit.

² Must be ordered on a separate line.

³ Available with the 6BP only.



Acculamp LED Lamps

ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.

EXAMPLE: **ALEBR30 850L DIM**

Series	Lumen Output ¹	Color Temperature	Base	Dimming
ALEBR20 BR20 LED Lamp	500L 8W, 500 lumens	(blank) 2700K	(blank) E26 Base	DIM Dimmable
ALEBR30 BR30 LED Lamp	850L 12.5W, 850 lumens			
ALEBR40 BR40 LED Lamp	1045L 17W, 1045 lumens			
ALGP General Purpose LED A lamp	250L 5W, 250 lumens, A15 420L 8W, 420 lumens, A19 620L 11W, 620 lumens, A21	(blank) 3000K (blank) 2700K (blank) 3000K	(blank) E26 Base	DIM Dimmable
ALCND LED Candle Lamp	250L 5W, 250 lumens	(blank) 2700K	(blank) E12 Base	DIM Dimmable
ALEMR16 MR16 GU10 LED Lamp	280L 4W, 280 lumens	(blank) 2700K	(blank) GU10 Base	DIM Dimmable

Notes:

¹ Total system delivered lumens.



LED Recessed Downlighting

ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.

EXAMPLE: L7X 7B2MW TOR / ALEBR30 850L DIM

Housing		Trim		Finish		Retention		Voltage		Accessories	
L3 L3R	New construction rough-in	3B1	Baffle	(blank)	Black, White Flange	(blank)	Friction Clips	(blank)	120	ALEBR20 500L DIM	Acculamp BR20
	Remodel rough-in			TRMW	Black, Matte White Flange						
				W	White						
				MW	Matte White						
				ORB	Oil Rubbed Bronze						
				BN	Brushed Nickel						
		301	Open	(blank)	White						
				MW	Matte White						
				ORB	Oil Rubbed Bronze						
				BN	Brushed Nickel						
				A PFMW	Clear Diffuse, Matte White Plastic Flange						
		3E1	Eyeball	(blank)	White						
				MW	Matte White						
				ORB	Oil Rubbed Bronze						
				BN	Brushed Nickel						
L5 L5R	New construction rough-in	5B2	Baffle	(blank)	Black, White Flange	TOR	Torsion Springs	(blank)	120	ALEBR20 500L DIM	Acculamp BR20
	Remodel rough-in			TRMW	Black, Matte White Flange						
				W	White						
				MW	Matte White						
				ORB	Oil-Rubbed Bronze						
				BN	Brushed Nickel						
		502	Open	(blank)	White						
				MW	Matte White						
				ORB	Oil-Rubbed Bronze						
				BN	Brushed Nickel						
				A PFMW	Clear Diffuse, Matte White Plastic Flange						
		5E1	Eyeball	(blank)	White						
				MW	Matte White						
				ORB	Oil Rubbed Bronze						
				BN	Brushed Nickel						
L7X L7XR LC6	New construction rough-in	7B2	Baffle	(blank)	Black, White Flange	TOR	Torsion Springs	(blank)	120	ALEBR20 500L DIM	Acculamp BR20
	Remodel rough-in			TRMW	Black, Matte White Flange						
	New construction rough-in			W	White						
				MW	Matte White						
				ORB	Oil Rubbed Bronze					ALEBR30 850L DIM	Acculamp BR30
				BN	Brushed Nickel					ALEBR40 1045L DIM	Acculamp BR40
		702	Open	(blank)	White						
				MW	Matte White						
				ORB	Oil Rubbed Bronze						
				BN	Brushed Nickel						
				A PFMW	Clear Diffuse, Matte White Plastic Flange						
		7E1	Eyeball	(blank)	White						
				MW	Matte White						
				ORB	Oil Rubbed Bronze						
				BN	Brushed Nickel						



LED Track Lighting

ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.


EXAMPLE: **LTKBRSD BR20 LED ORB**

Series		Lumen Output		Beam Angles		Color Temperature		Finish	
LTIKSPLT	Integrated LED Spotlight Track Kit ¹	(blank)	8W, 440 lumens	(blank)	40 degrees	(blank)	2700K	ORB	Oil Rubbed Bronze
LTIHSPLT	Integrated LED Spotlight Trackhead								
LTIKBELL	Integrated LED Bell Spot Track Kit ¹	(blank)	8W, 440 lumens	(blank)	40 degrees	(blank)	2700K	ORB	Oil Rubbed Bronze
LTIHBELL	Integrated LED Bell Spot Trackhead								
LTIKMSBK	Integrated LED Mesh Back Track Kit ¹	(blank)	8W, 440 lumens	(blank)	40 degrees	(blank)	2700K	BN	Brushed Nickel
LTIHMSBK	Integrated LED Mesh Back Trackhead								
LTIKGAVL	Integrated LED Gaval Track Kit ¹	(blank)	8W, 440 lumens	(blank)	40 degrees	(blank)	2700K	BN	Brushed Nickel
LTIHGAVL	Integrated LED Gaval Trackhead								
LTKSPLT	Spotlight LED Lamp Track Kit ²	MR16GU10 LED	5W, 310 (per head)	(blank)	40 degrees	(blank)	2700K	ORB	Oil Rubbed Bronze
LTHSPLT	Spotlight LED Lamp Trackhead							BN	Brushed Nickel
								ORB	Oil Rubbed Bronze
								BN	Brushed Nickel
LTKBRSD	BR20 Shade LED Lamp Track Kit ³	BR20 LED	8W, 500 (per head)	(blank)	110 degrees	(blank)	2700K	ORB	Oil Rubbed Bronze
LTHBRSD	BR20 Shade LED Lamp Trackhead							BN	Brushed Nickel
								ORB	Oil Rubbed Bronze
								BN	Brushed Nickel
LTKSTBF	Step Baffle BR20 Shade LED Lamp Track Kit ³	BR20 LED	8W, 500 (per head)	(blank)	110 degrees	(blank)	2700K	DBL	Black
LTHSTBF	Step Baffle BR20 Shade LED Lamp Trackhead							MW	Matte White
								DBL	Black
								MW	Matte White
LTKSTBF	Step Baffle BR30 Shade LED Lamp Track Kit ⁴	BR30 LED	12W, 850 (per head)	(blank)	110 degrees	(blank)	2700K	DBL	Black
LTHSTBF	Step Baffle BR30 Shade LED Lamp Trackhead							MW	Matte White
								DBL	Black
								MW	Matte White

Accessories

Live End Conduit


Connects to the end of the linear track section supplying power from a conduit feed



Model #	Finish
LTLECF	(blank) Matte white connector with black cover

T Connector


Joins three sections at 90° angles



Model #	Finish
LTTC	(blank) Matte white connector with black cover

Live End Power Feed


Permits track to be connected to grounded outlet using a 15' cord with switch included



Model #	Finish
LTLECS	(blank) Matte white

L Connector


Joins two track sections to make a 90° angle



Model #	Finish
LTLDC	(blank) Matte white connector with black cover

Floating Feed


Permits track to be wired anywhere along track length



Model #	Finish
LTFC	(blank) Matte white connector with black and white cover

Monopoint


Allows for a single linear track head to be installed into an existing junction box



Model #	Finish
LTMPR	(blank) Matte white

Straight Connector


Joins two track sections in a straight run



Model #	Finish
LTCV	(blank) Matte white connector with black cover

Live End Junction Box Feed

Connects to the end of the linear track section supplying power from a junction box



Model #	Finish
LTLLEDC	(blank) Matte white connector with black cover

Track Stick

4-foot or 8-foot, 1-circuit track section with end caps



Model #	Finish
LTS4	MW Matte white
LTS8	DBL Black

Notes:

¹ Track Kit (LTIK) Includes: (1) 44" Track Stick, (1) Floating Feed, and (3) Track Heads.

² Track Kit (LTK) Includes: (1) 44" Track Stick, (1) Floating Feed, (3) Track Heads, and (3) MR16GU10 LED lamps.

³ Track Kit (LTK) Includes: (1) 44" Track Stick, (1) Floating Feed, (3) Track Heads, and (3) BR20 LED lamps.

⁴ Track Kit (LTK) Includes: (1) 44" Track Stick, (1) Floating Feed, (3) Track Heads, and (3) BR30 LED lamps.




LED Mini-Pendants and Vanities


ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.

Series ¹		Finish	Lumen Output	Color Temperature	Options
MDPB	Bullet Style Mini Pendant	BNP Polished Brushed Nickel	275	3000K	Decorative shade options below
MWSB	Bullet Style Mini Sconce	BZ Bronze	275	3000K	Decorative shade options below
MWVB2	Bullet Style 2-Light Vanity		550	3000K	Decorative shade options below
MWVB3	Bullet Style 3-Light Vanity		825	3000K	Decorative shade options below
MDPC	Cylinder Style Mini Pendant		275	3000K	Decorative shade options below
MWSC	Cylinder Style Mini Sconce		275	3000K	Decorative shade options below
MWVC2	Cylinder Style 2-Light Vanity		550	3000K	Decorative shade options below
MWVC3	Cylinder Style 3-Light Vanity		825	3000K	Decorative shade options below



MWV - Cylinder Style Vanity/Sconce



MWV - Bullet Style Vanity/Sconce



MDPC - Cylinder Style Mini Pendant



MDPB - Bullet Style Mini Pendant

Notes:

¹ All diffusers require bullet or cylinder-style fitter (pendant or sconce).



LED Mini-Pendants and Vanities

ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.

Shades/Diffusers shape and finish options:

 <p>Bullet 4-1/2" W x 10-1/2" H</p> <table border="1"> <thead> <tr> <th>Finish</th> <th>Model</th> </tr> </thead> <tbody> <tr> <td>Opal White</td> <td>DBLT 1001</td> </tr> <tr> <td>Caramel Swirl</td> <td>DBLT 1004</td> </tr> </tbody> </table>	Finish	Model	Opal White	DBLT 1001	Caramel Swirl	DBLT 1004	 <p>Ball 4" W x 16" H</p> <table border="1"> <thead> <tr> <th>Finish</th> <th>Model</th> </tr> </thead> <tbody> <tr> <td>Opal White</td> <td>DRBL 1001</td> </tr> <tr> <td>Green Melon</td> <td>DRBL 1008</td> </tr> </tbody> </table>	Finish	Model	Opal White	DRBL 1001	Green Melon	DRBL 1008	 <p>Zentro 3-5/8" W x 10-3/4" H</p> <table border="1"> <thead> <tr> <th>Finish</th> <th>Model</th> </tr> </thead> <tbody> <tr> <td>Frosted White</td> <td>DZNT 1003</td> </tr> <tr> <td>Blue</td> <td>DZNT 1007</td> </tr> </tbody> </table>	Finish	Model	Frosted White	DZNT 1003	Blue	DZNT 1007												
Finish	Model																															
Opal White	DBLT 1001																															
Caramel Swirl	DBLT 1004																															
Finish	Model																															
Opal White	DRBL 1001																															
Green Melon	DRBL 1008																															
Finish	Model																															
Frosted White	DZNT 1003																															
Blue	DZNT 1007																															
 <p>Cone 5-5/8" W x 3" H</p> <table border="1"> <thead> <tr> <th>Finish</th> <th>Model</th> </tr> </thead> <tbody> <tr> <td>Opal White</td> <td>DCNE 1001</td> </tr> <tr> <td>White Melon</td> <td>DCNE 1002</td> </tr> <tr> <td>Cobalt Blue</td> <td>DCNE 1006</td> </tr> <tr> <td>Green Melon</td> <td>DCNE 1008</td> </tr> </tbody> </table>	Finish	Model	Opal White	DCNE 1001	White Melon	DCNE 1002	Cobalt Blue	DCNE 1006	Green Melon	DCNE 1008	 <p>Tall Cylinder 3-3/8" W x 9-1/4" H</p> <table border="1"> <thead> <tr> <th>Finish</th> <th>Model</th> </tr> </thead> <tbody> <tr> <td>Opal White</td> <td>DTCL 1001</td> </tr> <tr> <td>Apple Red</td> <td>DTCL 1005</td> </tr> <tr> <td>Amber Twist</td> <td>DTCL 1009</td> </tr> <tr> <td>White Drizzle</td> <td>DTCL 1010</td> </tr> </tbody> </table>	Finish	Model	Opal White	DTCL 1001	Apple Red	DTCL 1005	Amber Twist	DTCL 1009	White Drizzle	DTCL 1010	 <p>Short Cylinder 3-3/8" W x 5" H</p> <table border="1"> <thead> <tr> <th>Finish</th> <th>Model</th> </tr> </thead> <tbody> <tr> <td>Opal White</td> <td>DSCL 1001</td> </tr> <tr> <td>Apple Red</td> <td>DSCL 1005</td> </tr> <tr> <td>Amber Twist</td> <td>DSCL 1009</td> </tr> <tr> <td>White Drizzle</td> <td>DSCL 1010</td> </tr> </tbody> </table>	Finish	Model	Opal White	DSCL 1001	Apple Red	DSCL 1005	Amber Twist	DSCL 1009	White Drizzle	DSCL 1010
Finish	Model																															
Opal White	DCNE 1001																															
White Melon	DCNE 1002																															
Cobalt Blue	DCNE 1006																															
Green Melon	DCNE 1008																															
Finish	Model																															
Opal White	DTCL 1001																															
Apple Red	DTCL 1005																															
Amber Twist	DTCL 1009																															
White Drizzle	DTCL 1010																															
Finish	Model																															
Opal White	DSCL 1001																															
Apple Red	DSCL 1005																															
Amber Twist	DSCL 1009																															
White Drizzle	DSCL 1010																															
 <p>Cylinder Wave 5-5/8" W x 3" H</p> <table border="1"> <thead> <tr> <th>Finish</th> <th>Model #</th> </tr> </thead> <tbody> <tr> <td>Frosted White</td> <td>DGWV 1003</td> </tr> </tbody> </table>	Finish	Model #	Frosted White	DGWV 1003	 <p>Cylinder Dot 4" W x 7-3/4" H</p> <table border="1"> <thead> <tr> <th>Finish</th> <th>Model #</th> </tr> </thead> <tbody> <tr> <td>Frosted White</td> <td>DGDT 1003</td> </tr> </tbody> </table>	Finish	Model #	Frosted White	DGDT 1003	 <p>Bell 4-1/2" W x 10-1/2" H</p> <table border="1"> <thead> <tr> <th>Finish</th> <th>Model #</th> </tr> </thead> <tbody> <tr> <td>Opal White</td> <td>DBEL 1001</td> </tr> </tbody> </table>	Finish	Model #	Opal White	DBEL 1001																		
Finish	Model #																															
Frosted White	DGWV 1003																															
Finish	Model #																															
Frosted White	DGDT 1003																															
Finish	Model #																															
Opal White	DBEL 1001																															
 <p>Concave Bell 4-1/2" W x 6" H</p> <table border="1"> <thead> <tr> <th>Finish</th> <th>Model #</th> </tr> </thead> <tbody> <tr> <td>Opal White</td> <td>DBEL 1001</td> </tr> </tbody> </table>	Finish	Model #	Opal White	DBEL 1001	 <p>Billet 4-3/8" W x 5-1/2" H</p> <table border="1"> <thead> <tr> <th>Finish</th> <th>Model #</th> </tr> </thead> <tbody> <tr> <td>Amber Twist</td> <td>DCBL 1009</td> </tr> </tbody> </table>	Finish	Model #	Amber Twist	DCBL 1009	 <p>Top Rib 4-1/2" W x 51/2" H</p> <table border="1"> <thead> <tr> <th>Finish</th> <th>Model #</th> </tr> </thead> <tbody> <tr> <td>Carmel Mocha Swirl</td> <td>DTRB 1014</td> </tr> </tbody> </table>	Finish	Model #	Carmel Mocha Swirl	DTRB 1014																		
Finish	Model #																															
Opal White	DBEL 1001																															
Finish	Model #																															
Amber Twist	DCBL 1009																															
Finish	Model #																															
Carmel Mocha Swirl	DTRB 1014																															
 <p>Glass In Glass 5" W x 3-3/4" H</p> <table border="1"> <thead> <tr> <th>Finish</th> <th>Model #</th> </tr> </thead> <tbody> <tr> <td>Blue</td> <td>DGNG 1007</td> </tr> </tbody> </table>	Finish	Model #	Blue	DGNG 1007	 <p>Small Bell 4" W x 3" H</p> <table border="1"> <thead> <tr> <th>Finish</th> <th>Model #</th> </tr> </thead> <tbody> <tr> <td>Blue</td> <td>DSBL 1001</td> </tr> </tbody> </table>	Finish	Model #	Blue	DSBL 1001	 <p>Prismatic 6-5/8" W x 3-5/8" H</p> <table border="1"> <thead> <tr> <th>Finish</th> <th>Model #</th> </tr> </thead> <tbody> <tr> <td>Clear Ribbed</td> <td>DPRG 1011</td> </tr> </tbody> </table>	Finish	Model #	Clear Ribbed	DPRG 1011																		
Finish	Model #																															
Blue	DGNG 1007																															
Finish	Model #																															
Blue	DSBL 1001																															
Finish	Model #																															
Clear Ribbed	DPRG 1011																															

Notes:

¹ All diffusers require bullet or cylinder-style fitter (pendant or sconce).



LED Cabinet Lighting

ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.

EXAMPLE: **UCLD 12 BN**

Series	Size/Dimensions (L x W x H)	CRI	Color Temperature	Lamps Included	Lumens/Watts	Finish
UCLD	12 12-1/4" x 3-5/8" x 1"	83	(blank) 3000K	(3) LED	226lm / 5W	BN Brushed Nickel
	18 18-1/4" x 3-5/8" x 1"		27 2700K	(5) LED	377lm / 9W	BZ Bronze
	24 24-1/4" x 3-5/8" x 1"			(7) LED	504lm / 12W	WH White
RAZ^{1,2}	9 9-1/4" x 1-1/4" x 1/2"	85	(blank) 3000K	(3) LED	175lm / 5W	(blank) Brushed Nickel
	12 12-1/4" x 1-1/4" x 1/2"			(4) LED	239lm / 7W	
	18 18-1/4" x 1-1/4" x 1/2"			(6) LED	353lm / 10W	
	24 24-1/4" x 1-1/4" x 1/2"			(8) LED	441lm / 13W	
STK^{1,2,3}	6 6-1/4" x 1/2" x 3/8"	80	(blank) 3000K	(6) LED	226lm / 0.45W	(blank) Clear
	12 12-1/4" x 1/2" x 3/8"			(12) LED	377lm / 0.90W	
	18 18-1/4" x 1/2" x 3/8"			(18) LED	504lm / 1.35W	
LOC 35 120	17-1/4" x 3" x 6"			(1) 35W MR16 Halogen	35W	BN Brushed Nickel BZ Bronze

Notes:











¹ Link up to 10' of modular system to one transformer.

² Transformer is required for operation.

³ INCLUDES - 0.45W 24 volt LED ballasts, 0.9W 24 volt LED ballasts or 1.35W 24 volt LED ballasts.



Accessories

 <p>Splice Box Required for direct wire installation</p> <p>Model #</p> <p>UCD JB Matte White</p> <p>UCD JB BL Black</p>	 <p>24" Connector Cord Required for direct wire installation</p> <p>Model #</p> <p>UC ERC24 BL 24" Black Connector Cord</p> <p>UC ERC24 24" White Connector Cord</p> <p>STKCC24 24" LED connector cord</p> <p>STKCC3 3" LED connector cord</p>	 <p>Cord Cover (Standard) Required for plug-in installation</p> <p>Model #</p> <p>UCH WWC R12 18" cord cover (conceals cord). Resale packs must be ordered in increments of 12.</p>
 <p>Row Connector</p> <p>Model #</p> <p>UC ERC 1-1/8" row connector</p> <p>RAZ ERC End row connector</p>	 <p>Linking Cord (Included)</p> <p>Model #</p> <p>RAZ CC121 121" linking cord</p> <p>RAZ CC24 24" linking cord</p>	 <p>3" Linking Cord</p> <p>Model #</p> <p>RAZ CC3 3" linking cord</p> <p>RAZLVCC Low voltage linking cord</p>
 <p>24V Transformer (Required)</p> <p>Model #</p> <p>RAZTRANS24 120 120v power source</p> <p>RAZTRANS24 MVOLT Multi-Volt power source</p> <p>STKTRANS 24 Links up to 10' of fixtures per transformer.</p>	 <p>In-line Power Switch</p> <p>Model #</p> <p>RAZ INLS26 Matte White</p> <p>INLS26 STK Power Switch</p>	 <p>Power Hub Distributor</p> <p>Model #</p> <p>RAZ PHD 121" linking cord</p>
 <p>Step Dimmer with Remote Touch Pad</p> <p>Model #</p> <p>RAZDIM Matte White</p>		

LED Wall Mounts

ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.

EXAMPLE: **DLSD3 BW BZ**

Series ¹		Finish	Lumen Output	Color Temperature	Finish ²
SWBLED M12	LED Backplate	N/A	720	3000K	N/A
DLSD1	Diffuser	MB			Matte Black
DLSD2	Diffuser	BN P10			Brushed Nickel with Silver Rice Paper
DLSD3	Diffuser	BN/BZ			Brushed Nickel with Bronze
DLSD4	Diffuser	CH			Cherry Wood
DLSD5	Diffuser	BZ			Bronze
DLSD6	Diffuser	ANS			Antique Silver
DLSD7	Diffuser	BZ F08			Bronze with Umbria Linen
DLSD8	Diffuser	CLR P01			Clear with White Swirl
DLSD9	Diffuser	BZ/S03			Bronze with Root Beer Float
DLSD10	Diffuser	BZ/WH			Bronze with White
DLSD11	Diffuser	S08			Stormy Sky
DLSD12	Diffuser	BN P01			Brushed Nickel with White Swirl
DLSD13	Diffuser	P12			Window Pane
DLSD14	Diffuser	F03			Russell Square
DLSD15	Diffuser	S06			Comet Trails
DLSD16	Diffuser	BZ F02			Bronze with Chocolate Linen
DLSD17	Diffuser	BN P10			Brushed Nickel with Silver Rice Paper

Notes:

¹ All diffusers require SWBLED backplate for use.

² Additional color/finish/fabric options available, consult our spec sheet at www.lithonia.com/LEDpendant-sconces or refer to swatch book.



LED Flush Mounts

ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.

EXAMPLE: **FMML 7 830**

Series		Size	CRI	Color Temperature	Fixture Finish	Options
FMML	Versi LED Flush Mount	7 7" diameter	8 >80	40 4000K (660 lumens) 30 3000K (642 lumens) 27 2700K (612 lumens)	(blank) White (DDBT) Bronze	WL Wet Location
FMLRL	Round LED Flush Mount	11 11" diameter 14 14" diameter	148 208	40 4000K (1100 lumens) 40 4000K (1600 lumens)	(blank) White (blank) White	
FMLS	Square LED Flush Mount	11 11" diameter 14 14" diameter	148 208	40 4000K (1100 lumens) 40 4000K (1600 lumens)	(blank) White (blank) White	



LED Utility

ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.

EXAMPLE: **LBL4 347 LP840**

Series		Lumens	Color Temperature	Lens Type	Voltage	Wattage
LBL2 LP835	2' LED Wraparound	2000	3500K	Patterned #12 acrylic	120-277V	26
LBL2 LP840	2' LED Wraparound	2000	4000K	Patterned #12 acrylic	120-277V	26
LBL4 LP835	4' LED Wraparound	4000	3500K	Patterned #12 acrylic	120-277V	50
LBL4 LP840	4' LED Wraparound	4000	4000K	Patterned #12 acrylic	120-277V	50
LBL4 347 LP835	4' LED Wraparound	4000	3500K	Patterned #12 acrylic	347	50
LBL4 347 LP840	4' LED Wraparound	4000	4000K	Patterned #12 acrylic	347	50
2GTL2 LP835	2' x 2' LED Recessed Troffer	3700	3500K	Patterned #12 acrylic	120-277V	43
2GTL2 LP840	2' x 2' LED Recessed Troffer	3700	4000K	Patterned #12 acrylic	120-277V	43
2GTL4 LP835	2' x 4' LED Recessed Troffer	4000	3500K	Patterned #12 acrylic	120-277V	43
2GTL4 LP840	2' x 4' LED Recessed Troffer	4000	4000K	Patterned #12 acrylic	120-277V	43
2GTL2 347 LP835	2' x 2' LED Recessed Troffer	3700	3500K	Patterned #12 acrylic	347	43
2GTL2 347 LP840	2' x 2' LED Recessed Troffer	3700	4000K	Patterned #12 acrylic	347	43
2GTL4 347 LP835	2' x 4' LED Recessed Troffer	4000	3500K	Patterned #12 acrylic	347	43
2GTL4 347 LP840	2' x 4' LED Recessed Troffer	4000	4000K	Patterned #12 acrylic	347	43

EXAMPLE: **ZL1N L48 3000LM FST MVOLT 40K 80CRI WH**

Series	Length	Lumens	Diffuser	Voltage	Color Temperature	CRI	Options	Finish	
ZL1N LED striplight	L24 24"	3000LM	FST Snap on frosted, diffuse	MVOLT 120-277V	40K 4000K	80CRI	PLR Plug-in wiring	WH White	
		5000LM	L/LENS No diffuser	HVOLT 347-480V	30K 3000K	90CRI		GALV Galvanized	
	7000LM	35K 3500K			MB Matte black				
	ZL2N Lensed LED striplight	L24 24"	2000LM	MDD Medium diffuse	MVOLT 120-277V	40K 4000K	80CRI	PLR Plug-in wiring	WH White
3000LM			30K 3000K			90CRI			BSL722 Emergency battery pack ^{1,2}
		7000LM							
5000LM		50K 5000K	SKGY Smoke gray						

Notes:

¹ Specific voltage; 120 or 277.

² Output is 1400 lumens.



EXAMPLE: **1290L**

Series		Dimensions	CRI	Wattage	Color Temperature	Lumens	Metallic Trim Finish
1290L	LED Low Profile 4' shop light	46-1/3" x 3-3/4" x 2-1/3"	87	26	4000K	1700	(blank) White
1292L	LED Low Profile 4' shop light	46-1/3" x 3-3/4" x 2-1/3"	87	40	4000K	2900	(blank) Black/Grey



LED Security Floods

ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.

EXAMPLE: **OFLR 6LC 120 MO BZ**

Series	# of Heads	Color Temperature	Voltage	Controls	Finish
OFLR	6LC 2 heads, 6 LEDs	(blank) 5000K	120 120V	MO Motion Sensor	BZ Bronze
	9LN 3 heads, 9 LEDs			P Photocell	WH White
OLF	2RH 2 round heads	40K 4000K	120 120V	MO Motion Sensor	BZ Bronze
		(blank) 4000K	(blank) 120V	PE Photocell	WH White
OLFL	14 1 head	(blank) 4000K	(blank) 120V	PE Photocell	BZ Bronze



LED Building Perimeter

ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.

EXAMPLE: TWR2 LED 1 50K MVOLT DDB

Series	Performance Package	Color Temperature	Voltage	Controls	Finish
OLAW23	(blank) 2300 lumens	53K 5000K	120 120V	PE Photocell	BZ Bronze
OLW14	(blank) 1490 lumens	(blank) 5000K	(blank) MVOLT	(blank) Photocell	(blank) Bronze WH White
OLW	23 2700 lumens 31 3970 lumens	(blank) 4000K	(blank) 120V	PE Photocell	BZ Bronze
TDD LED	1 1412 lumens	40K 4000K	(blank) 120V	PE Photocell	(blank) Gray
TWR1 LED	1 2100 lumens 2 3500 lumens 3 4900 lumens	40K 4000K 50K 5000K	MVOLT 120-277V	(blank) No controls PE ¹ MVOLT Photocell	(blank) Dark Bronze
TWR2 LED	1 6980 lumens	50K 5000K	MVOLT 120-277V	(blank) No controls	DDB Dark Bronze

Notes:

¹ Available on 5000K only.



LED Entry Lights

ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.

EXAMPLE: OLLWD DDB

Series	Performance Package	Color Temperature	Voltage	Controls	Finish
OLWP	11 1100 lumens	(blank) 4000K	(blank) 120V	PE Photocell	BZ Dark Bronze
TWS LED	1 1017 lumens	50K 5000K	120 120V	PE Photocell	(blank) Dark Bronze
OLCS	8 500 lumens	(blank) 4000K	(blank) MVOLT	(blank) No controls	DDB Dark Bronze WH White
OLLWD 1 Light	(blank) 270 lumens	(blank) 4000K	(blank) MVOLT	(blank) No controls	DDB Dark Bronze WH White
OLLWU 2 Light	(blank) 500 lumens	(blank) 4000K	(blank) MVOLT	(blank) No controls	DDB Dark Bronze WH White
OLSR Round	(blank) 350 lumens	(blank) 4000K	(blank) MVOLT	(blank) No controls	DDB Dark Bronze
OLSS Square	(blank) 350 lumens	(blank) 4000K	(blank) MVOLT	(blank) No controls	WH White
OLVTCM Ceiling Mount	(blank) 600 lumens	(blank) 4000K	(blank) MVOLT	(blank) No controls	(blank) Gray
OLVTWM Wall Mount	(blank) 600 lumens	(blank) 4000K	(blank) MVOLT	(blank) No controls	(blank) Gray



LED Canopy and Floodlights

ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.

EXAMPLE: OLBF 8 30K DDB

Series	Performance Package	Color Temperature	Voltage	Controls	Finish
VRC LED	1 3389 lumens	50K 5000K	MVOLT 120-277V	(blank) Photocell	(blank) Dark Bronze
OLCFM	15 1030 lumens	(blank) 4000K	(blank) 120V	(blank) No controls	DDB Dark Bronze WH White
OSTLLED	(blank) 674 lumens	(blank) 4000K	120 120V	P Photocell	BL Black
OLBF 5x4 Flood Optics	8 800 lumens	30K 3000K	(blank) MVOLT	(blank) No controls	DDB Dark Bronze
OLBS 2x2 Spot Optics	8 800 lumens	50K 5000K	(blank) MVOLT	(blank) No controls	DDB Dark Bronze
DSXF1 LED	1 2100 lumens 2 4000 lumens	40K 4000K 50K 5000K	(blank) MVOLT	(blank) No controls	(blank) Dark Bronze
DSXF2 LED	3 5700 lumens 2 7500 lumens	40K 4000K 50K 5000K	(blank) MVOLT	(blank) No controls	(blank) Dark Bronze



For specific product warranty information, visit www.acuitybrands.com

Sustainable Lighting Solutions

Acuity Brands is the North American market leader and one of the world's leading providers of innovative, sustainable lighting products. With our comprehensive portfolio and proven expertise in indoor and outdoor luminaires, controls and daylighting, we provide customers with integrated, intelligent solutions from one company.

For more information and resources, visit www.acuitybrands.com

LIGHTING



DAYLIGHTING



ACUITY CONTROLS & SYSTEMS



TECHNOLOGIES

