



*Designers Fountain*®  
**Distinctive Lighting**









Lighting is often the final touch in your decorating projects and we understand that both design and function are equally important. Our product development teams are second to none in talent and experience.

*Designers Fountain* has been a leading manufacturer and distributor of decorative and functional residential lighting in the United States since 1985.

Headquartered in a state-of-the-art 22,000 square foot facility in the Los Angeles area, our products are available through a network of authorized lighting showrooms, distributors and Internet experts throughout North America. The company maintains qualified staff, sourcing, and design capabilities globally from the Pacific Rim to Europe to the United States.




































Our philosophy is to continue to provide the highest quality products to meet all your lighting needs. Whether you are searching for **Transitional**, **Traditional**, or **Contemporary** styling, we have the right collection for you. For those on a budget, our **Designers Value** product line allows you to indulge your creative instincts at an affordable price.

Designs fitting the most current and future fashion trends in addition to continued research and development of the latest technologies are what *Designers Fountain* is all about.

*Designers Fountain*®  
**Distinctive Lighting**











# Chandelier Family Collections

<b>Transitional</b> 6 - 33	 <b>Modesto</b> 6 - 8	 <b>Fieldhouse</b> 9 - 10	 <b>Del Ray</b> 11 - 13	
	 <b>Bradley</b> 14 - 16	 <b>Castello</b> 17 - 19	 <b>Austin</b> 20 - 22	
	 <b>Cortona</b> 23 - 25	 <b>Mission Ridge</b> 26 - 29	 <b>Del Amo</b> 30 - 33	
<b>Traditional</b> 36 - 67	 <b>Amherst</b> 36 - 40	 <b>Palatial</b> 41 - 43	 <b>Mendocino</b> 44 - 47	
	 <b>Barcelona</b> 48 - 53	 <b>Lauderhill</b> 54 - 55	 <b>Montreaux</b> 56 - 58	
	 <b>Alhambra</b> 59 - 61	 <b>Timberline</b> 62 - 65	 <b>Bollo</b> 66 - 67	
<b>Contemporary</b> 70 - 87	 <b>Mirage</b> 70 - 72	 <b>Bellemeade</b> 73 - 75	 <b>Cordova</b> 76 - 78	
	 <b>Avanti</b> 79 - 81	 <b>Candence</b> 82 - 84	 <b>Majorca</b> 85 - 87	
<b>Designers Value</b> 90 - 115	 <b>Montego</b> pages 90 - 92	 <b>Tackwood</b> 93 - 96	 <b>Stratton</b> 97 - 99	 <b>Apollo</b> 100 - 102
	 <b>Seville</b> 103 - 105	 <b>Arcadia</b> 106 - 107	 <b>Piazza</b> 108	 <b>Marbella</b> 109 - 111
	 <b>Madison</b> 112 - 114	 <b>Bistro</b> 115	 <b>Palladium</b> 115	



# Interior Collections

Pendant & Ceiling 117 - 143	 <b>Pendants</b> 117 - 122	 <b>Mini-Pendants</b> 123 - 126	 <b>Semi-Flushmounts</b> 127 - 130
	 <b>Flushmounts</b> 131 - 134	 <b>Fluorescent</b> 135 - 139	 <b>LED Recessed</b> 140 - 143
Bath, Vanity & Wall Sconces 145 - 168	 <b>Bath, Vanity &amp; Wall Sconces</b> 145 - 166	 <b>Wall Sconces</b> 167 - 168	

# Exterior Collections

LED 171 - 176		Abbington 172	Hawthorne 176	Prado 174	
		Bedford 175	Hillcrest 173	Weston 176	
		Brighton 176	Lexington 175	Whitmore 173	
		Cortland 175	Monrach 174	Winston 171	
		Drake 173			
Fluorescent 177 - 184		Builder Cast	Parkview 178	Stonyridge 177	
		Aluminum 183	Sedona-ES 180	Westchester 182	
		Builder-ES 184	Stockholm-ES 179		
		Kensington-ES 184			
Incandescent 185 - 213		3 Head Post 213	Bullet 211	Oak Park 196	
		Address Light 212	Canyon Lake 189	Pier Mounts 212	
		Allegro 213	Capella 202	Porch Lights 212	
		Berkshire 187	Chelsea 199	Riviera 204	
		Beveled Glass 209	Dayton 197	Sedona 193	
		Braxton 198	Devonshire 207	Stockholm 191	
		Builder Cast	Gladiator 185	Tiverton 205	
		Aluminum 210	Kensington 203	Westchester 200	
		Bulkhead 211	Nantucket 203		
Dark Sky 214 - 217		Amherst-DS 215	Security 218 - 219		Motion Detectors 218
		Barrington-DS 217			Area & Security 219
		Bayport-DS 214			
		Ellington-DS 216			

<b>Backplate Dimensions for Outdoor Lanterns</b>	<b>220</b>
<b>Stems and Chains</b>	<b>221</b>
<b>Index</b>	<b>222 - 227</b>
<b>Notes</b>	<b>228</b>
<b>Symbol Guide</b>	<b>229</b>





**T**ransitional is the fusion of traditional and contemporary styles, finishes, materials and fabrics equating to a classic, timeless design. Furniture lines are simple yet sophisticated, featuring either straight lines or rounded profiles. Fabric is as diverse as graphic patterns on overstuffed sofas and textured chenille on sleek wood frames. A lack of ornamentation and decoration keeps the focus on the simplicity and sophistication of the design.

# Transitional Collections



## Symbol Guide



ENERGY STAR® Qualified



Can be Mounted **UP** or **DOWN**

**(M)** Incandescent Medium Base



Bulb Included



Suitable for **DAMP** Locations

**(C)** Incandescent Candelabra Base



Title 24 Compliant



Suitable for **WET** Locations

**(FL)** Fluorescent Lamp



ADA Compliant



10 ft. chain and 12 ft. wire

**(H)** Halogen Lamp



Air Tight

- All chain mounted fixtures include 3 feet of chain & 12 feet of wire, unless otherwise noted.
- All stem mounted fixtures include one each 6 in., 12 in. & 18 in. stems, unless otherwise noted.




# Modesto Collection

Artisan Finish with White Opal Glass or White Fabric Shades


The bold detail of the nature inspired elements and the strong lines blends effortlessly to create a soft, refined and dramatic silhouette.

**B** 83789-ART


**A** 83711-ART



Finish:  
Artisan (ART)



Glass:  
White Opal



Shade:  
White Fabric




Canopy Detail


# Modesto

Artisan Finish with White Opal Glass or White Fabric Shades

C 83786-ART



D 83731-ART



E 83738-ART



Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	83711-ART Semi-Flush	14.5	10.5		3	(M)	60	White Fabric Shade	
B	83789-ART 9 Light Chandelier	30	31.5		9	(M)	100	White Opal Glass	Ⓢ
C	83786-ART 6 Light Chandelier	26	25		6	(M)	100	White Opal Glass	
D	83731-ART Pendant	22	25.25		3	(M)	100	White Fabric Shade	
E	83738-ART 3 Light Island	40	48.75		3	(M)	100	White Opal Glass	



# Modesto

Artisan Finish with White Opal Glass or White Fabric Shades



F 83701-ART



G 83702-ART









H 83730-ART



I 83703-ART



J 83704-ART

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
F	83701-ART Wall Sconce	10	7	4.5	1	(M)	100	White Opal Glass	
G	83702-ART 2 Light Bath Bar	14.5	6.25	5.25	2	(M)	100	White Opal Glass	 
H	83730-ART Mini Pendant	5.5	45.5		1	(M)	100	White Opal Glass	
I	83703-ART 3 Light Bath Bar	22	6.25	5.25	3	(M)	100	White Opal Glass	 
J	83704-ART 4 Light Bath Bar	29.5	6.25	5.25	4	(M)	100	White Opal Glass	 

# Fieldhouse Collection


*Flemish Bronze Finish*

Clean strong interesting lines are the hallmark feature of this collection. Adjustable assembly enhances the overall clean structure design and adds flexibility.



**A** 84301-FBZ


**B** 84389-FBZ



Finish:  
**Flemish Bronze (FBZ)**



Canopy Detail

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	84301-FBZ Wall Sconce	5	12.5	5	1	(C)	60		
B	84389-FBZ 9 Light Chandelier	36	68		9	(C)	60		



# Fieldhouse


*Flemish Bronze Glass*



**C** 84330-FBZ



**D** 84384-FBZ



**E** 84386-FBZ

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
C	84330-FBZ Mini Pendant	6.25	50.25		1	(C)	60		
D	84384-FBZ 4 Light Chandelier	12.5	63.25		4	(C)	60		
E	84386-FBZ 6 Light Chandelier	33	64		6	(C)	60		

# Del Ray Collection

*Flemish Bronze Finish with White Opal Glass or White Fabric Shades*

Clean lines and curves of hand worked metal create the perfect blend of form and function embracing today's casual style.


A 83889-FBZ



Finish:  
**Flemish Bronze  
(FBZ)**




Glass:  
**White Opal**



Shade:  
**White Fabric**



Canopy Detail

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A 83889-FBZ	9 Light Chandelier	34	26.25		9	(M)	100	White Opal Glass	



# Del Ray

Flemish Bronze Finish with White Opal Glass or White Fabric Shades

**B** 83884-FBZ



**C** 83831-FBZ











**D** 83886-FBZ

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
B	83884-FBZ 4 Light Chandelier	22	21		4	(M)	100	White Opal Glass	
C	83831-FBZ Pendant	21.75	23		3	(M)	100	White Fabric Shade	
D	83886-FBZ 6 Light Chandelier	28	23.5		6	(M)	100	White Opal Glass	

# Del Ray

Flemish Bronze Finish with White Opal Glass or White Fabric Shades




Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
E	83801-FBZ Wall Sconce	5	16.5	6	1	(M)	100	White Opal Glass	 
F	83811-FBZ Semi-Flush	17.5	11.5		3	(M)	60	White Fabric Shade	
G	83830-FBZ Mini Pendant	6	52		1	(M)	100	White Opal Glass	 
H	83803-FBZ 3 Light Bath Bar	24	6.5	6	3	(M)	100	White Opal Glass	 
I	83804-FBZ 4 Light Bath Bar	31.5	6.5	6	4	(M)	100	White Opal Glass	 

# Bradley Collection

*Charcoal Finish with Art Glass*

The artisan detailed handwork in the glass shades creates a warm and inviting environment.

A 84186-CHA



B 84130-CHA



Finish:  
Charcoal (CHA)



Glass:  
Art



Canopy Detail



# Bradley

Charcoal Finish with Art Glass

C 84183-CHA



D 84111-CHA



E 84131-CHA



Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	84186-CHA 6 Light Chandelier	26.5	28.75		6	(M)	100		
B	84130-CHA Mini Pendant	6	54		1	(M)	100		
C	84183-CHA 3 Light Chandelier	18	16.5		3	(M)	100		
D	84111-CHA Semi-Flush	13.5	9		3	(M)	60		
E	84131-CHA Pendant	16.5	21.5		3	(M)	100		

# Bradley

Charcoal Finish with Art Glass




F 84101-CHA



G 84103-CHA



H 84104-CHA

	Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
F	84101-CHA	Wall Sconce	5	14.75	5.5	1	(M)	100		
G	84103-CHA	3 Light Bath Bar	29	5	4.5	3	(M)	100		
H	84104-CHA	4 Light Bath Bar	38.75	5	4.5	4	(M)	100		

# Castello Collection

*Tuscana Finish with Antique Linen Glass*

A style that feels familiar but with a fresh clean interpretation, addressing today's casual life-style.



**A** 83630-TU



**B** 83689-TU



**Finish:**  
Tuscana (TU)



**Glass:**  
Antique Linen



Canopy Detail

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	83630-TU Mini Pendant	5.5	48.5		1	(M)	100		
B	83689-TU 9 Light Chandelier	29.5	32.5		9	(M)	100		Ⓢ



# Castello

*Tuscan Finish with Antique Linen Glass*



C 83631-TU



D 83611-TU



E 83686-TU

# Castello

*Tuscan Finish with Antique Linen Glass*

**F** 83601-TU



**G** 83603-TU



**H** 83604-TU



Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
C	83631-TU Inverted Pendant	19	22.75		3	(M)	100		
D	83611-TU Semi-Flush	15.5	11		2	(M)	100		
E	83686-TU 6 Light Chandelier	24.5	24.25		6	(M)	100		
F	83601-TU Wall Sconce	4.5	12.25	6	1	(M)	100		
G	83603-TU 3 Light Bath	22.5	7.75	5.5	3	(M)	100		
H	83604-TU 4 Light Bath	30	7.75	5.5	4	(M)	100		

# Austin Collection

*Weathered Saddle Finish with Satin Crepe Glass*

Handsomely styled ironwork and hand-forged details display a casual rustic Spanish style.

A 973812-WSD



**Finish:**  
**Weathered Saddle (WSD)**



**Glass:**  
**Satin Crepe**



Canopy Detail



# Austin

*Weathered Saddle Finish with Satin Crepe Glass*



**B** 97311-WSD



**C** 97331-WSD



**D** 97386-WSD

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	973812-WSD 12 Light Chandelier	36	33		12	(M)	100		Ⓢ
B	97311-WSD Semi-Flush	16.25	11.5		3	(M)	60		
C	97331-WSD 3L Inverted Pendant	21.25	30.5		3	(M)	100		
D	97386-WSD 6 Light Chandelier	27.25	24.25		6	(M)	100		

# Austin

*Weathered Saddle Finish with Satin Crepe Glass*



**E** 97330-WSD









**F** 97301-WSD



**G** 97302-WSD



**H** 97303-WSD

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
E	97330-WSD Mini Pendant	5.75	49.75		1	(M)	100		
F	97301-WSD Wall Sconce	5.5	10	8.25	1	(M)	100		 
G	97302-WSD 2 Light Bath Bar	17.5	10	7.5	2	(M)	100		 
H	97303-WSD 3 Light Bath Bar	27.5	10	7.5	3	(M)	100		 

# Cortona Collection

Chrome Finish with Gloss White Opal Glass

Large sweeping rectangular shape arms with "double drapping arm" detail adds dimension and surface for the effect to the finish.

A 84689-CH



Finish:  
Chrome (CH)



Glass:  
Gloss White Opal Style



Canopy Detail

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A 84689-CH	9 Light Chandelier	34	76.75		9	(M)	100	Incl. 2-6" and 3-12" Stems	



# Cortona

Chrome Finish with Gloss White Opal Glass




**B** 84601-CH



**C** 84683-CH



Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
B	84601-CH Wall Sconce	6	11.5	8	1	(M)	100		
C	84683-CH 3 Light Chandelier	22.25	68.25		3	(M)	100		

# Cortona

Chrome Finish with Gloss White Opal Glass



**D** 84630-CH



**E** 84685-CH

	Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
<b>D</b>	<b>84630-CH</b>	Mini Pendant	6	49.5		1	(M)	100		
<b>E</b>	<b>84685-CH</b>	5 Light Chandelier	26	69		5	(M)	100		

# Mission Ridge Collection

*Warm Mahogany Finish with Goldenrod Glass*

Framework reflecting the elegance and beauty of the Arts and Craft period. Clean, straight lines outline the pillar glass shades, adding a distinctive flair to any environment.

C 82130-WM



A 82121-WM

B 82189-WM



Finish:  
Warm Mahogany (WM)



Glass:  
Goldenrod



Canopy Detail

# Mission Ridge

Warm Mahogany Finish with Goldenrod Glass



**D** 82111-WM



**E** 82131-WM




**F** 82186-WM

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	82121-WM Flushmount	13	5		2	(M)	60		
B	82189-WM 9 Light Chandelier	30	32		9	(M)	100		Ⓢ
C	82130-WM Mini Pendant	6	48.25		1	(M)	100		
D	82111-WM Semi-Flush	13	10		2	(M)	100		
E	82131-WM Inverted Pendant	18.5	22		3	(M)	100		
F	82186-WM 6 Light Chandelier	27	25.5		6	(M)	100		



## Mission Ridge

*Warm Mahogany Finish with Goldenrod Glass*



*Distinctive Mission Design*

G 82183-WM



H 82138-WM



# Mission Ridge

Warm Mahogany Finish with Goldenrod Glass



I 82101-WM



J 82102-WM



K 82103-WM



L 82104-WM

	Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
G	82183-WM	3L Down Chandelier	23	23		3	(M)	100		
H	82138-WM	4 Light Island	35.5	47.5	4.75	4	(M)	100	Incl. 2 ea: 6", 12", 18" stems	
I	82101-WM	Wall Sconce	5	10.5	7	1	(M)	100		
J	82102-WM	2 Light Bath Bar	14.5	9.25	7	2	(M)	100		
K	82103-WM	3 Light Bath Bar	23.5	9.25	7	3	(M)	100		
L	82104-WM	4 Light Bath Bar	29.5	9.25	7	4	(M)	100		

# Del Amo Collection

*Burnished Bronze Finish with Tea Stained Alabaster Glass*

The refined elliptical center column that drapes down to softly curved arms holding alabaster shades offers warm and inviting lighting to complement today's architectural trends.

A 828815-BNB

B 82830-BNB



Finish:  
Burnished Bronze (BNB)



Glass:  
Tea Stained Alabaster



Canopy Detail

# Del Amo

*Burnished Bronze Finish with Tea Stained Alabaster Glass*



C 82889-BNB

D 82885-BNB

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	828815-BNB 15 Light Chandelier	40	42.5		15	(M)	60		Ⓢ
B	82830-BNB Mini Pendant	6.5	45		1	(M)	100		
C	82889-BNB 9 Light Chandelier	32.5	33.5		9	(M)	100		Ⓢ
D	82885-BNB 5 Light Chandelier	26.25	26		5	(M)	100		



# Del Amo

*Burnished Bronze Finish with Tea Stained Alabaster Glass*



**E** 82811-BNB

**F** 82831-BNB



**G** 82883-BNB

	Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
<b>E</b>	<b>82811-BNB</b>	Semi-Flush	14.75	12.5		2	(M)	100		
<b>F</b>	<b>82831-BNB</b>	Inverted Pendant	21.25	24.25		3	(M)	100		
<b>G</b>	<b>82883-BNB</b>	3 Light Chandelier	23	20		3	(M)	100		

# Del Amo

Burnished Bronze Finish with Tea Stained Alabaster Glass



Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
H	82807-BNB Wall Sconce	6.5	13	10.25	1	(M)	100		
I	82802-BNB 2 Light Bath Bar	19.25	8.5	9	2	(M)	100		
J	82803-BNB 3 Light Bath Bar	25.25	8.5	9	3	(M)	100		
K	82804-BNB 4 Light Bath Bar	33.5	8.5	9	4	(M)	100		



**T**he Traditional style can hail from 18th century England, the French countryside or even the exotic lands of the East. A slightly floral palette, or Damask, can be enhanced with bronze accents and warm wood tones for an inviting, comforting interior. The tailored look takes over windows, where panels are gathered loosely with tasseled cords. Still-life oil paintings, gilt frames and an emphasis on pairs also lend a room a proper traditional feeling.



# Traditional Collections



## Symbol Guide



ENERGY STAR® Qualified



Bulb Included



Title 24 Compliant



ADA Compliant



Air Tight



Can be Mounted **UP** or **DOWN**



Suitable for **DAMP** Locations



Suitable for **WET** Locations



10 Ft. chain and 12 Ft. wire

**(M)** Incandescent Medium Base

**(C)** Incandescent Candelabra Base

**(FL)** Fluorescent Lamp

**(H)** Halogen Lamp

- All chain mounted fixtures include 3 feet of chain & 12 feet of wire, unless otherwise noted.
- All stem mounted fixtures include one each 6 in., 12 in. & 18 in. stems, unless otherwise noted.



# Amherst Collection

*Burnt Umber Finish with Antique Harvest Beige Glass*

Intricately carved filigree details and exquisitely scrolled arms with a European influence impart a worldly sophistication.



A 97511-BU



B 975815-BU



Finish:  
Burnt Umber (BU)



Glass:  
Antique Harvest Beige



Canopy Detail

# Amherst

Burnt Umber Finish with Antique Harvest Beige Glass



Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	97511-BU Semi-Flush	17.5	13.25		3	(M)	100		
B	975815-BU 15 Light Chandelier	42	42		15	(M)	60		Ⓢ
C	97585-BU 5 Light Chandelier	28	28		5	(M)	100		
D	97583-BU 3 Light Chandelier	19.25	22		3	(M)	100		
E	97589-BU 9 Light Chandelier	32	32.5		9	(M)	100		Ⓢ

# Amherst


Burnt Umber Finish with Antique Harvest Beige Glass



**F** 97531-BU



**G** 97586-BU



**H** 97538-BU



**I** 97551-BU

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
F	97531-BU 3L Inverted Pendant	25.25	30		3	(M)	100		Ⓢ
G	97586-BU 5L Down Chandelier	25.5	25.75		5	(M)	100		
H	97538-BU 2 Light Island	38	26.25		2	(M)	100		
I	97551-BU 3 Light Foyer	15	28.25		3	(C)	60		Ⓢ

# Amherst

Burnt Umber Finish with Antique Harvest Beige Glass

J 97530-BU



K 97501-BU



L 97502-BU











M 97503-BU



N 97504-BU



Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
J	97530-BU Mini Pendant	6.5	49.5		1	(M)	100		
K	97501-BU Wall Sconce	6	10.25	8	1	(M)	100		 
L	97502-BU 2 Light Bath Bar	14	10	8	2	(M)	100		 
M	97503-BU 3 Light Bath Bar	22	10	8	3	(M)	100		 
N	97504-BU 4 Light Bath Bar	30	10	8	4	(M)	100		 



# Amherst - ENERGY STAR®

Burnt Umber Finish with Warm Amber Glaze Acrylic Lens

The Decorative Fluorescent fixtures add decorative styling and compliment our Amherst collection flawlessly.









O ES97540-BU



P ES97522-BU



Q ES97523-BU

Item	Description	W	H	L	Bulbs	Type	Watts/K	Features/Notes	Symbol
O	ES97540-BU Fluorescent Wall Sconce	16	6.25	4.5	1	(FL)	26/2,700K	PLC G24q-3 Base Lamp	 
P	ES97522-BU Fluorescent Flushmount	15.75	15.75	3.5	2	(FL)	22 & 32 /2,700K	T9 Base Lamp	 
Q	ES97523-BU Fluorescent Linear Flushmount	18.25	4.25	55.5	4	(FL)	32/2,700K	T8 Bi-pin Base Lamp	 


# Palatial Collection

Chrome Finish with White Opal Glass or White Fabric Shades

Simple elegant lines with elongated polished chrome candles feature tapered K-9 bobeche and elegantly cut center column.




**A** 84211-CH




**B** 84289-CH



**Finish:**  
Chrome (CH)



**Glass:**  
White Opal



**Shade:**  
White Fabric



Canopy Detail

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	84211-CH Semi-Flush	15.75	12.25		3	(M)	100	White Fabric Shade, Glass Diffuser	
B	84289-CH 9 Light Chandelier	31.50	35		9	(C)	60		Ⓢ

# Palatial

Chrome Finish with White Opal Glass or White Fabric Shades



C 84231-CH



D 84283-CH









E 84286-CH

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
C	84231-CH	Pendant	21	23.5	3	(M)	100	White Fabric Shade, Glass Diffuser	
D	84283-CH	3 Light Chandelier	17.5	20.5	3	(C)	60		
E	84286-CH	6 Light Chandelier	27	27.5	6	(C)	60		

# Palatial

Chrome Finish with White Opal Glass or White Fabric Shades



Item	Description	W	H	Ext	Type	Watts	Features/Notes	Symbol
F	84230-CH Mini Pendant	6	49.25		1 (C)	60		
G	84201-CH Wall Sconce	4.75	10.75	5.75	1 (C)	60		 
H	84203-CH 3 Light Bath Bar	22.5	9.75	5.75	3 (C)	60		 
I	84204-CH 4 Light Bath Bar	29.5	9.75	5.75	4 (C)	60		 



# Mendocino Collection

*Forged Sienna Finish with Warm Amber Glaze Glass*

Unique stunning double scrolled arms finished in a striking finish provide this clean combination of styles and design with an elegant personality.

C 81830-FSN



B 81889-FSN



A 81821-FSN



Finish:  
**Forged Sienna  
(FSN)**



Glass:  
**Warm Amber Glaze**



Canopy Detail

# Mendocino

Forged Sienna Finish with Warm Amber Glaze Glass



**D** 81832-FSN



**E** 81811-FSN



**F** 81838-FSN

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	81821-FSN Flushmount	14.75	8		2	(M)	60		
B	81889-FSN 9 Light Chandelier	31	32.5		9	(M)	100		Ⓢ
C	81830-FSN Mini Pendant	7	53		1	(M)	100		
D	81832-FSN Down Pendant	16	16.5		1	(M)	150		
E	81811-FSN Semi-Flush	15.75	13		2	(M)	100		
F	81838-FSN 3 Light Island	45.25	24.25	13	3	(M)	100		

# Mendocino

Forged Sienna Finish with Warm Amber Glaze Glass

**G** 81831-FSN



**H** 81883-FSN



**I** 81885-FSN



	Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
<b>G</b>	<b>81831-FSN</b>	Inverted Pendant	26.25	28.75		3	(M)	100		
<b>H</b>	<b>81883-FSN</b>	3L Down Chandelier	23	22.75		3	(M)	100		
<b>I</b>	<b>81885-FSN</b>	5 Light Chandelier	25.25	24.75		5	(M)	100		

# Mendocino

Forged Sienna Finish with Warm Amber Glaze Glass



J 81801-FSN



K 81802-FSN



L 81803-FSN



M 81804-FSN

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
J	81801-FSN Wall Sconce	7	17.25	7.5	1	(M)	100		
K	81802-FSN 2 Light Bath Bar	19.5	10.25	7.75	2	(M)	100		
L	81803-FSN 3 Light Bath Bar	24.25	10.25	7.75	3	(M)	100		
M	81804-FSN 4 Light Bath Bar	31.75	10.25	7.75	4	(M)	100		




# Barcelona Collection

*Natural Iron Finish with Ochere Finished Glass*

Hand forged softly scrolled ironworks captures the essence of the Old World charm.



A 96111-NI



B 96131-NI



C 96186-NI



Finish:  
Natural Iron (NI)



Glass:  
Ochere Finished



Canopy Detail

# Barcelona

Natural Iron Finish with Ochere Finished Glass

D 96185-NI



E 96130-NI



F 9039-NI



	Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	96111-NI	Semi-Flush	18.5	14.75		2	(M)	100		
B	96131-NI	Inverted Pendant	21	25.25		3	(M)	100		
C	96186-NI	6 Light Chandelier	30.75	27.5		6	(M)	100		
D	96185-NI	5L Down Chandelier	25.75	24		5	(M)	100		
E	96130-NI	Mini-Pendant	7.25	55.25		1	(M)	100		
F	9039-NI	9 Light Chandelier	27.75	27.75		9	(C)	60		

# Barcelona

Natural Iron Finish with Ochere Finished Glass



G 96121-NI

H 96151-NI



I 961815-NI



# Barcelona

Natural Iron Finish with Ochere Finished Glass



J 9032-NI



K 96132-NI



L 96189-NI

	Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
G	96121-NI	Flushmount	13	6.75		2	(M)	60		
H	96151-NI	1 Light Foyer	14	29		1	(M)	100		
I	961815-NI	15 Light Chandelier	40.25	39.5		15	(M)	60		Ⓢ
J	9032-NI	2 Light Wall Sconce	11	12	7.5	2	(C)	60		💡
K	96132-NI	Down Pendant	18	14.5		1	(M)	150		
L	96189-NI	9 Light Chandelier	30.75	31.75		9	(M)	100		Ⓢ



## Barcelona

*Natural Iron Finish with Ochere Finished Glass*

M 9036-NI



N 9031-NI



# Barcelona

Natural Iron Finish with Ochere Finished Glass



O 96101-NI



P 96102-NI



Q 96103-NI



R 96104-NI

	Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
M	9036-NI	6 Light Chandelier	25.5	27.25		6	(C)	60		
N	9031-NI	12L Chandelier w/Pot Rack	41.5	27.5		12	(C)	60		
O	96101-NI	Wall Sconce	7.25	8.5	9.25	1	(M)	100		
P	96102-NI	2 Light Bath Bar	17.25	8.5	9.75	2	(M)	100		
Q	96103-NI	3 Light Bath Bar	26	8.5	9.75	3	(M)	100		
R	96104-NI	4 Light Bath Bar	34.25	8.5	9.75	4	(M)	100		

# Lauderhill Collection

*Natural Iron Finish with Warm Amber Glaze Glass*

Hand forged iron feel is the essence of this rustic but refined design with the captured "column style candle" glass shade.



**B** 84711-NI



**A** 84785-NI



**C** 84789-NI



**Finish:**  
Natural Iron (NI)



**Glass:**  
Warm Amber Glaze



Canopy Detail

# Lauderhill

Natural Iron Finish with Warm Amber Glaze Glass



Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	84785-NI 5 Light Chandelier	27	24.5		5	(M)	100		
B	84711-NI Semi-Flush	17.25	9.75		3	(M)	100		
C	84789-NI 9 Light Chandelier	32	29.5		9	(M)	100		Ⓢ
D	84730-NI Mini-Pendant	6	52.25		1	(M)	100		
E	84701-NI Wall Sconce	5.25	13.5	7.25	1	(M)	100		Ⓢ 🔥
F	84731-NI Inverted Pendant	22	22.5		3	(M)	100		
G	84703-NI 3 Light Bath Bar	24.75	8.75	7	3	(M)	100		Ⓢ 🔥
H	84704-NI 4 Light Bath Bar	34.5	9.5	7	4	(M)	100		Ⓢ 🔥



# Montreaux Collection

*Burnished Walnut Finish and Gold Accents with Goldenrod Glass*

Attractively over scaled with substantial scrolled arms, the French Old World is unmistakable. Very elegant offering!



A 815812-BWG



**Finish:**  
**Burnished Walnut**  
**with Gold Accents (BWG)**



**Glass:**  
**Goldenrod**



Decorative ceiling medallion  
is included on indicated models.

# Montreaux

Burnished Walnut Finish and Gold Accents with Goldenrod Glass

**B** 81589-BWG



**C** 81588-BWG



Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	<b>815812-BWG</b> 12 Light Chandelier	38	42.5		12	(M)	100	Incl. Decorative Medallion	
B	<b>81589-BWG</b> 9 Light Chandelier	33.25	33.5		9	(M)	100	Incl. Decorative Medallion	
C	<b>81588-BWG</b> 8 Light Oval Chandelier	37	32.75	28	8	(M)	100	Incl. Decorative Medallion	

# Montreaux

*Burnished Walnut Finish and Gold Accents with Goldenrod Glass*

**D** 81586-BWG



**E** 81583-BWG



Canopy Detail

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
D	81586-BWG 6 Light Chandelier	28.75	26.75		6	(M)	100		
E	81583-BWG 3L Down Chandelier	21.25	23.5		3	(M)	100		


# Alhambra Collection

*Natural Iron Finish*

The artistry is reflected in the abundance of intricate details and the complexity of the forged wrought iron.



A 9189-NI



Finish:  
Natural Iron (NI)



Canopy Detail

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	9189-NI 14 Light Chandelier	40.5	43		14	(C)	60		Ⓜ




# Alhambra

Natural Iron Finish

**B** 9186-NI



**C** 9192-NI



**D** 9181-NI



Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
B	9186-NI 6 Light Island	31.5	31.25		6	(C)	60		☎
C	9192-NI Semi-Flush	20.75	15		3	(M)	60		
D	9181-NI 2 Light Wall Sconce	12.5	14.75	7	2	(C)	60		💧

# Alhambra

Natural Iron Finish



E 9185-NI



F 9188-NI

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
E	9185-NI 8 Light Island	40.75	36.25		8	(C)	60		
F	9188-NI 8 Light Island	42.25	30.5	26	8	(C)	60		


# Timberline Collection

*Old Bronze Finish with Sculpted Ochere Lustre Glass*

Rustic charm with soft contemporary lines allow you to feel a sense of the outdoors.

A 95689-OB

B 95621-OB



Finish:  
Old Bronze (OB)



Glass:  
Sculpted Ochere Lustre



Canopy Detail

# Timberline

Old Bronze Finish with Sculpted Ochre Lustre Glass



C 95630-OB

D 95685-OB



E 95683-OB



Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	95689-OB 9 Light Chandelier	30.75	29.75		9	(M)	100		Ⓢ
B	95621-OB Flushmount	13	7.25		2	(M)	60		
C	95630-OB Mini Pendant	7.5	55.5		1	(M)	100		
D	95685-OB 5 Light Chandelier	26.75	24.75		5	(M)	100		
E	95683-OB 3 Light Chandelier	17.75	18		3	(M)	100		



# Timberline

*Old Bronze Finish with Sculpted Ochere Lustre Glass*

**F** 95632-OB



**G** 95631-OB



**H** 95686-OB



**I** 95611-OB



# Timberline

Old Bronze Finish with Sculpted Ochere Lustre Glass



J 95601-OB



K 95603-OB



L 95604-OB

	Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
F	95632-OB	Down Pendant	16	17.25		1	(M)	150		
G	95631-OB	Inverted Pendant	20	23.25		3	(M)	100		
H	95686-OB	5L Down Chandelier	22.75	18.5		5	(M)	100		
I	95611-OB	Semi-Flush	16	12.5		3	(M)	60		
J	95601-OB	Wall Sconce	5	12.75	7.25	1	(M)	100		
K	95603-OB	3 Light Bath Bar	24	7.25	6.5	3	(M)	100		
L	95604-OB	4 Light Bath Bar	34	7.25	6.5	4	(M)	100		

# Bollo Collection

*Venetian Bronze Finish*

Graceful refined arms and intricate scroll details abundantly adorned with antiqued amber crystal drops.



**A** 98302-VBR



**B** 98389-VBR



**Finish:**  
**Venetian Bronze (VBR)**



**Accents:**  
**Amber Crystal Drop**



**Canopy Detail**

# Bollo



Venetian Bronze Finish

C 98386-VBR



D 98383-VBR



Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	98302-VBR 2 Light Wall Sconce	11	19	7	2	(C)	60		
B	98389-VBR 9 Light Chandelier	32	42.5		9	(C)	60		
C	98386-VBR 6 Light Chandelier	23	31.5		6	(C)	60		
D	98383-VBR 3 Light Chandelier	19	28.25		3	(C)	60		





**T**he Contemporary style embraces a range of styles developed in the latter half of the 20th century. Pieces feature softened and rounded lines and interiors contain neutral elements and bold color, focusing on the basics of line, shape and form. Natural fabrics such as silk, wool, linen and cotton are used for their textural aspect and inherent neutral hues. However, bold color or geometric pattern may be brought into the design with pillows, a rug or a throw.



# Contemporary Collections

## Symbol Guide



ENERGY ATAR® Qualified



Bulb Included



Title 24 Compliant



ADA Compliant



Air Tight



Can be Mounted **UP** or **DOWN**



Suitable for **DAMP** Locations



Suitable for **WET** Locations



10 Ft. chain and 12 Ft. wire

**(M)** Incandescent Medium Base

**(C)** Incandescent Candelabra Base

**(FL)** Fluorescent Lamp

**(H)** Halogen Lamp

• All chain mounted fixtures include 3 feet of chain & 12 feet of wire, unless otherwise noted.

• All stem mounted fixtures include one each 6 in., 12 in. & 18 in. stems, unless otherwise noted.

# Mirage Collection

*Chrome Finish with White Opal Glass or White Fabric Shades*

Streamline silhouettes mixed with voluptuous curves of metal and glass shades, create a dramatic profile redefining luxury in lighting.




A 84089-CH


B 84011-CH



Finish:  
**Chrome (CH)**



Glass:  
**White Opal**




Shade:  
**White Fabric**



Canopy Detail

# Mirage

Chrome Finish with White Opal Glass or White Fabric Shades



C 84031-CH

D 84083-CH



E 84085-CH

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	84089-CH 9 Light Chandelier	34.5	37.5		9	(M)	100	White Opal Glass	
B	84011-CH Semi-Flush	18	12		3	(M)	60	White Fabric Shade	
C	84031-CH Inverted Pendant	22	59.5		3	(M)	100	White Fabric Shade	
D	84083-CH 3 Light Chandelier	18.5	22.25		3	(M)	100	White Opal Glass	
E	84085-CH 5 Light Chandelier	25.5	30		5	(M)	100	White Opal Glass	Ⓢ



# Mirage

Chrome Finish with White Opal Glass or White Fabric Shades

**F** 84001-CH



**G** 84030-CH










**H** 84003-CH



**I** 84004-CH



Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
F	84001-CH Wall Sconce	10	11	5.5	1	(M)	100	White Opal Glass	 
G	84030-CH Mini Pendant	6.5	50.5		1	(M)	100	White Opal Glass	
H	84003-CH 3 Light Bath Bar	24	5.75	6.5	3	(M)	100	White Opal Glass	 
I	84004-CH 4 Light Bath Bar	32	5.75	6.5	4	(M)	100	White Opal Glass	 

# Bellemeade Collection

Artisan Finish with White Opal Style Glass


Unique and refined with captured elongated glass cylinders.

**B** 84430-ART

**A** 84489-ART



Finish:  
Artisan (ART)



Glass:  
White Opal Style



Canopy Detail

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	84489-ART 9 Light Chandelier	34	37.5		9	(C)	60		Ⓢ
B	84430-ART Mini Pendant	7.5	51.75		1	(C)	60		

# Bellemeade

Artisan Finish with White Opal Style Glass



C 84411-ART



D 84483-ART



E 84485-ART

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
C	84411-ART Semi-Flush	15.5	10		3	(M)	100		
D	84483-ART 3 Light Chandelier	21	25.25		3	(C)	60		
E	84485-ART 5 Light Chandelier	27	29		5	(C)	60		

# Bellemeade

Artisan Finish with White Opal Style Glass



F 84401-ART



G 84403-ART



H 84404-ART

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
F	84401-ART Wall Sconce	4.5	12.25	6.5	1	(C)	60		
G	84403-ART 3 Light Bath Bar	23	10.75	6	3	(C)	60		
H	84404-ART 4 Light Bath Bar	30	10.75	6	4	(C)	60		



# Cordova Collection


*Chrome Finish with White Opal Glass or White Fabric Shades*

Sleek, bold and elegant, features elongated column style candle holders that extend from a softly tapered arm.


**B** 84589-CH



**A** 84511-CH



**Finish:**  
**Chrome (CH)**



**Shades:**  
**White Fabric**



**Glass:**  
**White Opal**



Canopy Detail

# Cordova

Chrome Finish with White Opal Glass or White Fabric Shades



C 84530-CH

D 84531-CH

E 84585-CH

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	84511-CH	Semi-Flush	13	11	3	(M)	100	White Fabric Shade	
B	84589-CH	9 Light Chandelier	27	74.25	9	(C)	60	Incl. 2-6" and 3-12" Stems	
C	84530-CH	Mini Pendant	5	42.75	1	(C)	60		
D	84531-CH	Pendant	18	63	3	(M)	100	White Fabric Shade	
E	84585-CH	5 Light Chandelier	24	70.25	5	(C)	60		

# Cordova

Chrome Finish with White Opal Glass or White Fabric Shades



F 84501-CH



G 84503-CH



H 84504-CH

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
F	84501-CH Wall Sconce	4.25	9.5	3.25	1	(C)	60		
G	84503-CH 3 Light Bath Bar	23	8.5	7.25	3	(M)	100	White Opal Glass	
H	84504-CH 4 Light Bath Bar	33	8.5	7.25	4	(M)	100	White Opal Glass	

# Avantí Collection

*Satin Platinum Finish with Fusione Glass*

A harmonious blend of sleek angular lines with softly sculpted and fused glass shades, captures the best attributes of Modern simplicity.



**A** 83011-SP



**B** 83089-SP



**Finish:**  
Satin Platinum (SP)



**Glass:**  
Fusione



Canopy Detail

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	83011-SP Semi-Flush	16.25	12		2	(M)	100		
B	83089-SP 9 Light Chandelier	34	37		9	(M)	100		Ⓢ



# Avantí

Satin Platinum Finish with Fusione Glass



C 83031-SP



D 83083-SP



E 83086-SP

# Avantí

Satin Platinum Finish with Fusione Glass



	Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
C	83031-SP	Inverted Pendant	26	32.75		3	(M)	100		
D	83083-SP	3 Light Chandelier	20.75	24.5		3	(M)	100		
E	83086-SP	6 Light Chandelier	31	31		6	(M)	60		
F	83030-SP	Mini Pendant	6	103.75		1	(M)	100	<i>Stems not included, 96" cord only</i>	
G	83007-SP	Wall Sconce	5.5	19.75	6.5	1	(M)	100		
H	83003-SP	3 Light Bath Bar	24.75	7.5	6.5	3	(M)	100		
I	83004-SP	4 Light Bath Bar	32.75	7.5	6.5	4	(M)	100		

# Candence Collection

*Chrome Finish with White Opal Glass or Silver Organza Fabric Shades*

The glimmer of crystal beads, polished metal and shimmering organza fabric, lights up a room with its fresh spirit and unique design.

**A** 83986-CH




**B** 83931-CH




**C** 83911-CH



**Finish:**  
**Chrome (CH)**



**Glass:**  
**White Opal**



**Shade:**  
**Silver Organza Fabric**



Canopy Detail

# Candence

Chrome Finish with White Opal Glass or Silver Organza Fabric Shades

D 83984-CH



E 839812-CH



Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	<b>83986-CH</b> 6 Light Chandelier	28	28.5		6	(C)	60	Silver Organza Fabric Shade	
B	<b>83931-CH</b> Pendant	22	26.5		3	(M)	100	Silver Organza Fabric Shade	
C	<b>83911-CH</b> Semi-Flush	16	11		3	(M)	60	Silver Organza Fabric Shade	
D	<b>83984-CH</b> 4 Light Chandelier	24	28.5		4	(C)	60	Silver Organza Fabric Shade	
E	<b>839812-CH</b> 12 Light Chandelier	35	38		12	(C)	60	Silver Organza Fabric Shade	Ⓢ



# Candence

Chrome Finish with White Opal Glass or Silver Organza Fabric Shades

F 83901-CH



G 83930-CH



H 83903-CH



I 83904-CH



Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
F	83901-CH Wall Sconce	5	17	7.25	1	(C)	60	Silver Organza Fabric Shade	
G	83930-CH Mini Pendant	6	47.5		1	(M)	100		
H	83903-CH 3 Light Bath Bar	24.75	8	5.5	3	(M)	100	White Opal Glass	
I	83904-CH 4 Light Bath Bar	33.75	8	5.5	4	(M)	100	White Opal Glass	

# Majorca Collection

*Oil Rubbed Bronze Finish with Clear Champagne and Frosted White Glass*

Converging subtle curves with bold lines and luminous layers of glass, Majorca creates an intriguing interpretation of Modernism.



**A** 83111-ORB



**B** 83189-ORB



**Finish:**  
Oil Rubbed Bronze  
(ORB)



**Glass:**  
Clear Champagne and  
Frosted White Glass



Canopy Detail

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	<b>83111-ORB</b> Semi-Flush	14.5	11.5		2	(M)	100		
B	<b>83189-ORB</b> 9 Light Chandelier	35	36.5		9	(M)	100		

# Majorca

*Oil Rubbed Bronze Finish with Clear Champagne and Frosted White Glass*



C 83183-ORB

D 83131-ORB

E 83186-ORB

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
C	<b>83183-ORB</b> 3 Light Chandelier	22	25		3	(M)	100		
D	<b>83131-ORB</b> Inverted Pendant	22	29.75		3	(M)	100		
E	<b>83186-ORB</b> 6 Light Chandelier	31	30.75		6	(M)	100		

# Majorca

*Oil Rubbed Bronze Finish with Clear Champagne and Frosted White Glass*



Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
F	83130-ORB Mini-Pendant	6.5	62.5		1	(M)	100		
G	83101-ORB Wall Sconce	6.25	16.5	7.25	1	(M)	100		
H	83103-ORB 3 Light Bath Bar	26.5	9.75	8.25	3	(M)	100		
I	83104-ORB 4 Light Bath Bar	36	9.75	8.25	4	(M)	100		





**O**ur Designers Value line offers collections of lighting that are inspired by all decorating styles but are re-interpreted to address more budget sensitive needs or smaller, more intimate areas of your home. The designs are a combination of simple and clean elements reflecting your style needs and the desire for high-quality products.

# Designers Value Collections



## Symbol Guide



ENERGY STAR® Qualified



Bulb Included



Title 24 Compliant



ADA Compliant



Air Tight



Can be Mounted **UP** or **DOWN**



Suitable for **DAMP** Locations



Suitable for **WET** Locations



10 Ft. chain and 12 Ft. wire

**(M)** Incandescent Medium Base

**(C)** Incandescent Candelabra Base

**(FL)** Fluorescent Lamp

**(H)** Halogen Lamp

- All chain mounted fixtures include 3 feet of chain & 12 feet of wire, unless otherwise noted.
- All stem mounted fixtures include one each 6 in., 12 in. & 18 in. stems, unless otherwise noted.



# Montego Collection

*Oil Rubbed Bronze Finish with Satin Bisque Glass*

Eclectic inspiration with clean lines and simplicity of form emanates versatility and timeless appeal.




A 96911-ORB


B 96930-ORB



C 96989-ORB



Finish:  
**Oil Rubbed Bronze  
(ORB)**



Glass:  
**Satin Bisque**



Canopy Detail

# Montego

Oil Rubbed Bronze Finish with Satin Bisque Glass



D 96932-ORB



E 96983-ORB



F 96985-ORB

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	96911-ORB Semi-Flush	16	10.5		2	(M)	100		
B	96930-ORB Mini Pendant	6	54.75		1	(M)	100		
C	96989-ORB 9 Light Chandelier	29	35.75		9	(M)	100		Ⓢ
D	96932-ORB Down Pendant	18	18.25		1	(M)	150		
E	96983-ORB 3 Light Chandelier	18	21		3	(M)	100		
F	96985-ORB 5 Light Chandelier	23.25	25.75		5	(M)	100		



# Montego

*Oil Rubbed Bronze Finish with Satin Bisque Glass*



Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
G	96931-ORB 3L Inverted Pendant	18.5	23.75		3	(M)	100		
H	96902-ORB 2 Light Bath Bar	18	8.75	7.25	2	(M)	100		
I	96903-ORB 3 Light Bath Bar	24	8.75	7.25	3	(M)	100		
J	96905-ORB 5 Light Bath Bar	36.5	8.75	7.25	5	(M)	100		

# Tackwood Collection

*Burnished Bronze Finish with Tea Stained Alabaster Glass*  
*Satin Platinum Finish with Alabaster Glass*

The minimalistic feel of the Tackwood collection is not equal to plainness. Actually, it is the contrary, it is elegant in its simplicity. Offered in two finishes.




**A** 82932-BNB  
82932-SP




**B** 82985-BNB  
82985-SP



**C** 82911-BNB  
82911-SP




**Finish:**  
**Burnished Bronze (BNB)**



**Glass:**  
**Tea Stained Alabaster**



**Finish:**  
**Satin Platinum (SP)**



**Glass:**  
**Alabaster**



Canopy Detail

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	82932-BNB 82932-SP Down Pendant	15.75	14		1	(M)	150		
B	82985-BNB 82985-SP 5 Light Chandelier	26.5	24.25		5	(M)	100		
C	82911-BNB 82911-SP Semi-Flush	14.5	12		2	(M)	100		

# Tackwood

*Burnished Bronze Finish with Tea Stained Alabaster Glass*  
*Satin Platinum Finish with Alabaster Glass*



**D** 82983-SP  
82983-BNB



**E** 82931-SP  
82931-BNB



**F** 829812-SP  
829812-BNB

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
D	82983-BNB 82983-SP	3 Light Chandelier	20	20	3	(M)	100		
E	82931-BNB 82931-SP	Inverted Pendant	17.75	21	3	(M)	100		
F	829812-BNB 829812-SP	12 Light Chandelier	48.5	45	12	(M)	100		

# Tackwood

Burnished Bronze Finish with Tea Stained Alabaster Glass  
Satin Platinum Finish with Alabaster Glass



**G** 82938-BNB  
82938-SP



**H** 82989-BNB  
82989-SP

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
G	82938-BNB 82938-SP	37.5	21	13	2	(M)	100		
H	82989-BNB 82989-SP	35.25	35		9	(M)	100		Ⓢ



# Tackwood

Burnished Bronze Finish with Tea Stained Alabaster Glass  
Satin Platinum Finish with Alabaster Glass



I 82930-BNB  
82930-SP



J 82901-SP  
82901-BNB











K 82902-SP  
82902-BNB



L 82903-BNB  
82903-SP



M 82904-SP  
82904-BNB

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
I	82930-BNB 82930-SP Mini Pendant	5	49.75		1	(M)	100		
J	82901-BNB 82901-SP Wall Sconce	5	10.5	6.25	1	(M)	100		 
K	82902-BNB 82902-SP 2 Light Bath Bar	15.5	8	6.25	2	(M)	100		 
L	82903-BNB 82903-SP 3 Light Bath Bar	24	8	6.25	3	(M)	100		 
M	82904-BNB 82904-SP 4 Light Bath Bar	29.25	8	6.25	4	(M)	100		 

# Stratton Collection

Satin Platinum Finish with Faux Alabaster Glass  
 Warm Mahogany Finish with Amber Sandstone Glass

Classic style that blends sweeping arms with curvaceous scrolls. Offered in two finishes.




**A** 98011-WM  
98011-SP



**B** 98086-WM  
98086-SP




Finish:  
**Warm Mahogany (WM)**



Glass:  
**Amber Sandstone**



Finish:  
**Satin Platinum (SP)**



Glass:  
**Faux Alabaster**




Canopy Detail

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
<b>A</b>	98011-WM 98011-SP Semi-Flush	17	12.5		3	(M)	100		
<b>B</b>	98086-WM 98086-SP 6 Light Chandelier	25.25	23		6	(M)	100		

# Stratton

Satin Platinum Finish with Faux Alabaster Glass  
 Warm Mahogany Finish with Amber Sandstone Glass



**C** 98031-SP  
98031-WM




**D** 98089-SP  
98089-WM

	Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
C	98031-WM 98031-SP	Inverted Pendant	19.75	25.25		3	(M)	100		
D	98089-WM 98089-SP	9 Light Chandelier	30	30.25		9	(M)	100		Ⓢ

# Stratton

Satin Platinum Finish with Faux Alabaster Glass  
 Warm Mahogany Finish with Amber Sandstone Glass



**E** 98030-SP  
98030-WM









**F** 98002-WM  
98002-SP



**G** 98003-SP  
98003-WM



**H** 98004-WM  
98004-SP

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
E	98030-WM 98030-SP Mini Pendant	5.25	54.25		1	(M)	100		
F	98002-WM 98002-SP 2 Light Bath Bar	13.5	9	7.5	2	(M)	100		 
G	98003-WM 98003-SP 3 Light Bath Bar	21.5	10	7.5	3	(M)	100		 
H	98004-WM 98004-SP 4 Light Bath Bar	29.75	10	7.5	4	(M)	100		 



# Apollo Collection

*Oil Rubbed Bronze Finish with Amber Sandstone Glass*  
*Satin Platinum Finish with Faux Alabaster Glass*

A casual classic with simple lines transcend style with an elegant and charming appeal most styles. Select items offered in two finishes.

A 94089-ORB



B 94011-ORB




**Finish:**  
**Oil Rubbed Bronze**  
**(ORB)**



**Glass:**  
**Amber Sandstone**



**Finish:**  
**Satin Platinum**  
**(SP)**



**Glass:**  
**Faux Alabaster**



Canopy Detail

# Apollo

*Oil Rubbed Bronze Finish with Amber Sandstone Glass*  
*Satin Platinum Finish with Faux Alabaster Glass*



**C** 94031-ORB

**D** 94030-ORB



**E** 94085-ORB



Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	<b>94089-ORB</b> 9 Light Chandelier	29.75	25.75		9	(M)	100		Ⓢ
B	<b>94011-ORB</b> Semi-Flush	12.5	12		2	(M)	60		
C	<b>94031-ORB</b> Inverted Pendant	20.5	25		3	(M)	100		
D	<b>94030-ORB</b> Mini Pendant	5	48.25		1	(M)	100		
E	<b>94085-ORB</b> 5 Light Chandelier	23.75	18		5	(M)	100		

# Apollo

*Oil Rubbed Bronze Finish with Amber Sandstone Glass*  
*Satin Platinum Finish with Faux Alabaster Glass*




**F** 94001-ORB



**G** 94002-SP  
94002-ORB



**H** 94003-ORB  
94003-SP



**I** 94004-SP  
94004-ORB

	Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
F	94001-ORB	Wall Sconce	5	9	8.75	1	(M)	100		
G	94002-ORB 94002-SP	2 Light Bath Bar	15.75	8.5	6.5	2	(M)	100		
H	94003-ORB 94003-SP	3 Light Bath Bar	23.75	8.5	6.5	3	(M)	100		
I	94004-ORB 94004-SP	4 Light Bath Bar	33	8.5	6.5	4	(M)	100		

# Seville Collection

*Oil Rubbed Bronze Finish with Satin Bisque Glass*

A bold silhouette is created then softened and refined to showcase the warm luminescence of the glass.

Designers Value


**B** 83485-ORB



**A** 83411-ORB



**Finish:**  
Oil Rubbed Bronze  
(ORB)



**Glass:**  
Satin Bisque



Canopy Detail

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	83411-ORB Semi-Flush	14.5	12		2	(M)	100		
B	83485-ORB 5 Light Chandelier	25	24		5	(M)	100		



# Seville

*Oil Rubbed Bronze Finish with Satin Bisque Glass*



Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
C	<b>83431-ORB</b> Inverted Pendant	17.75	21		3	(M)	100		
D	<b>83432-ORB</b> Down Pendant	15.75	14		1	(M)	150		
E	<b>83483-ORB</b> 3 Light Chandelier	21.5	22		3	(M)	100		

# Seville

Oil Rubbed Bronze Finish with Satin Bisque Glass

G 83402-ORB



F 83401-ORB

H 83403-ORB



I 83404-ORB



	Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
F	83401-ORB	Wall Sconce	6	8	7.5	1	(M)	100		
G	83402-ORB	2 Light Bath Bar	14.75	7.5	7.5	2	(M)	100		
H	83403-ORB	3 Light Bath Bar	23.5	7.5	7.5	3	(M)	100		
I	83404-ORB	4 Light Bath Bar	32.25	7.5	7.5	4	(M)	100		

# Arcadia Collection

*Oil Rubbed Bronze Finish with Goldenrod Glass*  
*Satin Platinum Finish with Frosted White Glass*

Simple minimalism with a clean silhouette, a blend of relaxed style and an urban simplicity of chic-casual living. Offered in two finishes.



A 83511-SP  
83511-ORB



B 83583-SP  
83583-ORB




Finish:  
**Oil Rubbed Bronze  
(ORB)**



Glass:  
**Goldenrod**



Finish:  
**Satin Platinum  
(SP)**



Glass:  
**Frosted White**



Canopy Detail

# Arcadia

Oil Rubbed Bronze Finish with Goldenrod Glass  
Satin Platinum Finish with Frosted White Glass



**C** 83531-SP  
83531-ORB

**D** 83532-ORB  
83532-SP

**E** 83585-ORB  
83585-SP

	Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	83511-ORB 83511-SP	Semi-Flush	14	10.25		2	(M)	100		
B	83583-ORB 83583-SP	3 Light Chandelier	20	17		3	(M)	100		
C	83531-ORB 83531-SP	Inverted Pendant	15.75	19.75		3	(M)	100		
D	83532-ORB 83532-SP	Down Pendant	15.75	13		1	(M)	100		
E	83585-ORB 83585-SP	5 Light Chandelier	24.5	19.75		5	(M)	100		



# Piazza

*Oil Rubbed Bronze Finish with Goldenrod Glass*  
*Satin Platinum Finish with Frosted White Glass*

Captures the essence of the relaxed style and clear silhouette of the Arcadian collection.



**F** 6601-ORB  
6601-SP



**G** 6602-SP  
6602-ORB



**H** 6603-ORB  
6603-SP



**I** 6604-SP  
6604-ORB

	Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
F	6601-ORB 6601-SP	Wall Sconce	5.5	7.75	7	1	(M)	100		
G	6602-ORB 6602-SP	2 Light Bath Bar	16.75	6.75	7	2	(M)	100		
H	6603-ORB 6603-SP	3 Light Bath Bar	24	6.75	7	3	(M)	100		
I	6604-ORB 6604-SP	4 Light Bath Bar	30	6.75	7	4	(M)	100		

# Marbella Collection

*Oil Rubbed Bronze Finish with Satin Bisque Glass*

Classic simplicity with a casual blending of strong lines and column style glass is our vision of Traditional styling.


Designers Value




**A** 83211-ORB



**B** 83285-ORB



**Finish:**  
Oil Rubbed Bronze  
(ORB)



**Glass:**  
Satin Bisque



Canopy Detail

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	83211-ORB Semi-Flush	14	10		2	(M)	100		
B	83285-ORB 5 Light Chandelier	24.25	24		5	(M)	100		

# Marbella

*Oil Rubbed Bronze Finish with Satin Bisque Glass*



Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
C	<b>83231-ORB</b> Inverted Pendant	15	18.25		3	(M)	100		
D	<b>83232-ORB</b> Down Pendant	13.5	8		1	(M)	100		
E	<b>83283-ORB</b> 3 Light Chandelier	19.5	22.25		3	(M)	100		

# Marbella

*Oil Rubbed Bronze Finish with Satin Bisque Glass*



**F** 83201-ORB



**G** 83202-ORB



**H** 83203-ORB



**I** 83204-ORB

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
F	83201-ORB Wall Sconce	4.5	7.5	5.5	1	(M)	100		
G	83202-ORB 2 Light Bath Bar	13	7.25	5.5	2	(M)	100		
H	83203-ORB 3 Light Bath Bar	18.75	7.25	5.5	3	(M)	100		
I	83204-ORB 4 Light Bath Bar	24.75	7.25	5.5	4	(M)	100		



# Madison Collection


*Oil Rubbed Bronze Finish with Amber Glass*

Sweeping metal curves and warm rich finishes create a welcoming ambience and relaxed style.

A 83383-ORB



B 83331-ORB



Finish:  
**Oil Rubbed Bronze  
(ORB)**



Glass:  
**Amber**



Canopy Detail

# Madison

*Oil Rubbed Bronze Finish with Amber Glass*



Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	<b>83383-ORB</b> 3 Light Chandelier	20.25	18.75		3	(M)	100		
B	<b>83331-ORB</b> Inverted Pendant	18.75	22.75		3	(M)	100		
C	<b>83311-ORB</b> Semi-Flush	16	10.5		2	(M)	100		
D	<b>83332-ORB</b> Down Pendant	18	18.25		1	(M)	100		
E	<b>83385-ORB</b> 5 Light Chandelier	24.25	20		5	(M)	100		

# Madison

*Oil Rubbed Bronze Finish with Amber Glass*



**F** 83301-ORB



**G** 83302-ORB



**H** 83303-ORB



**I** 83304-ORB

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
F	83301-ORB Wall Sconce	6	8.25	9.25	1	(M)	100		
G	83302-ORB 2 Light Bath Bar	16.25	8.25	9	2	(M)	100		
H	83303-ORB 3 Light Bath Bar	23	8.25	9	3	(M)	100		
I	83304-ORB 4 Light Bath Bar	30.25	8.25	9	4	(M)	100		

# Bistro & Palladium

Pewter Finish with Faux Alabaster Glass



A 4208-AL-PW



B 5695-PW



Finish:  
**Pewter  
(PW)**



Glass:  
**Faux Alabaster**



Canopy Detail

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	4208-AL-PW 5 Light Chandelier	22.5	14		5	(M)	100		
B	5695-PW 5 Light Chandelier	26.5	23		5	(M)	100		



# Pendants & Ceiling



## Symbol Guide



ENERGY STAR® Qualified



Bulb Included



Title 24 Compliant



ADA Compliant



Air Tight



Suitable for **DAMP** Locations



Suitable for **WET** Locations



10 Ft. chain and 12 Ft. wire

**(M)** Incandescent Medium Base

**(C)** Incandescent Candelabra Base

**(FL)** Fluorescent Lamp

**(H)** Halogen Lamp

- All chain mounted fixtures include 3 feet of chain and 12 feet of wire, unless otherwise noted.
- All stem mounted fixtures include one each 6 in., 12 in. and 18 in. stems, unless otherwise noted.



# Pendants

Transitional

Finish: Artisan



A 6201-ART



B 6202-ART



C 83731-ART



D 83831-FBZ



E 84131-CHA



F 83631-TU

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Page
A	6201-ART	Continental	20	59	3	(M)	100	Ivory Fabric Shade Incl. 2-6" and 3-12" Stems	
B	6202-ART	Continental	26	59	3	(M)	100	Ivory Fabric Shade Incl. 2-6" and 3-12" Stems	
C	83731-ART	Modesto	22	25.25	3	(M)	100	White Fabric Shade	7
D	83831-FBZ	Del Ray	21.75	23	3	(M)	100	White Fabric Shade	12
E	84131-CHA	Bradley	16.5	21.5	3	(M)	100		15
F	83631-TU	Castello	19	22.75	3	(M)	100		18

# Pendants



**A** 97331-WSD



**B** 82131-WM



**C** 82831-BNB

## Traditional



**D** 97531-BU



**E** 97551-BU



**F** 84231-CH



**G** 81832-FSN

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	Page
A	97331-WSD	Austin	21.25	30.5	3	(M)	100			21
B	82131-WM	Mission Ridge	18.5	22	3	(M)	100			27
C	82831-BNB	Del Amo	21.25	24.25	3	(M)	100			32
D	97531-BU	Amherst	25.25	30	3	(M)	100			38
E	97551-BU	Amherst	15	28.25	3	(C)	60			38
F	84231-CH	Palatial	21	23.5	3	(M)	100	White Fabric Shade, Glass Diffuser		42
G	81832-FSN	Mendocino	16	16.5	1	(M)	150			45

# Pendants



**A** 81831-FSN



**B** 96131-NI



**C** 96151-NI



**D** 96132-NI



**E** 84731-NI



**F** 95631-OB

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Page
A	81831-FSN	Mendocino	26.25	28.75	3	(M)	100		46
B	96131-NI	Barcelona	21	25.25	3	(M)	100		48
C	96151-NI	Barcelona	14	29	1	(M)	100		50
D	96132-NI	Barcelona	18	14.5	1	(M)	150		51
E	84731-NI	Lauderhill	22	22.5	3	(M)	100		55
F	95631-OB	Timberline	20	23.25	3	(M)	100		64

# Pendants

## Contemporary



**A** 95632-OB



**B** 84031-CH



**C** 84531-CH



**D** 83031-SP



**E** 83931-CH



**F** 83131-ORB

	Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Page
A	95632-OB	Timberline	16	17.25		1	(M)	150		64
B	84031-CH	Mirage	22	59.5		3	(M)	100	White Fabric Shade	71
C	84531-CH	Cordova	18	63		3	(M)	100	White Fabric Shade	77
D	83031-SP	Avanti	26	32.75		3	(M)	100		80
E	83931-CH	Candence	22	26.5		3	(M)	100	Silver Organza Fabric Shade	82
F	83131-ORB	Majorca	22	29.75		3	(M)	100		86

# Pendants

## Designers Value



**A** 96932-ORB



**B** 96931-ORB



**C** 82932-SP  
82932-BNB



**D** 82931-BNB  
82931-SP



**E** 98031-WM  
98031-SP



**F** 94031-ORB



**G** 83432-ORB



**H** 83431-ORB

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Page
A	96932-ORB	Montego	18	18.25	1	(M)	150		91
B	96931-ORB	Montego	18.5	23.75	3	(M)	100		92
C	82932-BNB 82932-SP	Tackwood	15.75	14	1	(M)	150		93
D	82931-BNB 82931-SP	Tackwood	17.75	21	3	(M)	100		94
E	98031-WM 98031-SP	Stratton	19.75	25.25	3	(M)	100		98
F	94031-ORB	Apollo	20.5	25	3	(M)	100		101
G	83432-ORB	Seville	15.75	14	1	(M)	150		104
H	83431-ORB	Seville	17.75	21	3	(M)	100		104



# Pendants



**A** 83531-ORB  
83531-SP



**B** 83532-ORB  
83532-SP



**C** 83231-ORB



**D** 83232-ORB



**E** 83331-ORB



**F** 83332-ORB

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Page
A	83531-ORB 83531-SP	Arcadia	15.75	19.75	3	(M)	100		107
B	83532-ORB 83532-SP	Arcadia	15.75	13	1	(M)	100		107
C	83231-ORB	Marbella	15	18.25	3	(M)	100		110
D	83232-ORB	Marbella	13.5	8	1	(M)	100		110
E	83331-ORB	Madison	18.75	22.75	3	(M)	100		112
F	83332-ORB	Madison	18	18.25	1	(M)	100		113

# Mini-Pendants

## Transitional



A 83730-ART



B 84330-FBZ



C 83830-FBZ



D 84130-CHA



E 83630-TU



F 97330-WSD



G 84630-CH

	Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Page
A	83730-ART	Modesto	5.5	45.5		1	(M)	100	White Opal Glass	8
B	84330-FBZ	Fieldhouse	6.25	50.25		1	(C)	60		10
C	83830-FBZ	Del Ray	6	52		1	(M)	100	White Opal Glass	13
D	84130-CHA	Bradley	6	54		1	(M)	100		14
E	83630-TU	Castello	5.5	48.5		1	(M)	100		17
F	97330-WSD	Austin	5.75	49.75		1	(M)	100		22
G	84630-CH	Cortona	6	49.50		1	(M)	100		25

# Mini-Pendants

## Traditional



**A** 82130-WM



**B** 82830-BNB



**C** 97530-BU



**D** 84230-CH



**E** 81830-FSN



**F** 96130-NI



**G** 84730-NI



**H** 95630-OB

	Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Page
A	82130-WM	Mission Ridge	6	48.25		1	(M)	100		26
B	82830-BNB	Del Amo	6.5	45		1	(M)	100		30
C	97530-BU	Amherst	6.5	49.5		1	(M)	100		39
D	84230-CH	Palatial	6	49.25		1	(C)	60		43
E	81830-FSN	Mendocino	7	53		1	(M)	100		44
F	96130-NI	Barcelona	7.25	55.25		1	(M)	100		49
G	84730-NI	Lauderhill	6	52.25		1	(M)	100		55
H	95630-OB	Timberline	7.5	55.5		1	(M)	100		63


# Mini-Pendants

Contemporary

Gem Collection  
Finish: Chrome



Sapphire



Amber



Amethyst



Emerald



Garnet



Moonstone



Aquamarine



Agate

**A** 6313-SA-CH  
6313-GA-CH

**B** 6314-AM-CH  
6314-MS-CH

**C** 6315-AH-CH  
6315-AQ-CH

**D** 6316-EM-CH  
6316-AG-CH



**E** 84030-CH



**F** 84430-ART

	Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	Page
A	6313-SA-CH 6313-GA-CH	Gem	7	48		1	MR16	35	Sapphire Garnet		
B	6314-AM-CH 6314-MS-CH	Gem	5	49		1	MR16	35	Amber Moonstone		
C	6315-AH-CH 6315-AQ-CH	Gem	5	49		1	MR16	35	Amethyst Aquamarine		
D	6316-EM-CH 6316-AG-CH	Gem	7	47		1	MR16	35	Emerald Agate		
E	84030-CH	Mirage	6.5	50.5		1	(M)	100	White Opal Glass		72
F	84430-ART	Bellemeade	7.5	51.75		1	(C)	60			73

# Mini-Pendants



**A** 84530-CH



**B** 83030-SP



**C** 83930-CH



**D** 83130-ORB

## Designers Value



**E** 96930-ORB



**F** 82930-SP  
82930-BNB



**G** 98030-SP  
98030-WM



**H** 94030-ORB

	Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Page
A	84530-CH	Cordova	5	42.75		1	(C)	60		77
B	83030-SP	Avanti	6	103.75		1	(M)	100		81
C	83930-CH	Candence	6	47.5		1	(M)	100		84
D	83130-ORB	Majorca	6.5	62.5		1	(M)	100		87
E	96930-ORB	Montego	6	54.75		1	(M)	100		90
F	82930-SP 82930-BNB	Tackwood	5	49.75		1	(M)	100		96
G	98030-SP 98030-WM	Stratton	5.25	54.25		1	(M)	100		99
H	94030-ORB	Apollo	5	48.25		1	(M)	100		101



# Semi-Flush

Transitional



A 83711-ART



B 83811-FBZ



C 84111-CHA



D 83611-TU



E 97311-WSD



F 82111-WM



G 82811-BNB

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Page
A	83711-ART	Modesto	14.5	10.5	3	(M)	60	White Fabric Shade	6
B	83811-FBZ	Del Ray	17.5	11.5	3	(M)	60	White Fabric Shade	13
C	84111-CHA	Bradley	13.5	9	3	(M)	60		15
D	83611-TU	Castello	15.5	11	2	(M)	100		18
E	97311-WSD	Austin	16.25	11.5	3	(M)	60		21
F	82111-WM	Mission Ridge	13	10	2	(M)	100		27
G	82811-BNB	Del Amo	14.75	12.5	2	(M)	100		32

# Semi-Flush

## Traditional



A 97511-BU



B 84211-CH



C 81811-FSN



D 96111-NI



E 84711-NI



F 9192-NI



G 95611-OB

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Page
A	97511-BU	Amherst	17.5	13.25	3	(M)	100		36
B	84211-CH	Palatial	15.75	12.25	3	(M)	100	White Fabric Shade, Glass Diffuser	41
C	81811-FSN	Mendocino	15.75	13	2	(M)	100		45
D	96111-NI	Barcelona	18.5	14.75	2	(M)	100		48
E	84711-NI	Lauderhill	17.25	9.75	3	(M)	100		54
F	9192-NI	Alhambra	20.75	15	3	(M)	60		60
G	95611-OB	Timberline	16	12.5	3	(M)	60		64

# Semi-Flush

## Contemporary



**A** 84011-CH



**B** 84411-ART



**C** 84511-CH



**D** 83011-SP



**E** 83911-CH



**F** 83111-ORB

## Designers Value



**G** 96911-ORB



**H** 82911-BNB  
82911-SP

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Page
A	84011-CH	Mirage	18	12	3	(M)	60	White Fabric Shade	70
B	84411-ART	Bellemeade	15.5	10	3	(M)	100		74
C	84511-CH	Cordova	13	11	3	(M)	100	White Fabric Shade	76
D	83011-SP	Avanti	16.25	12	2	(M)	100		79
E	83911-CH	Candence	16	11	3	(M)	60	Silver Organza Fabric Shade	82
F	83111-ORB	Majorca	14.5	11.5	2	(M)	100		85
G	96911-ORB	Montego	16	10.5	2	(M)	100		90
H	82911-BNB 82911-SP	Tackwood	14.5	12	2	(M)	100		93

# Semi-Flush

## Designers Value



**A** 98011-SP  
98011-WM



**B** 94011-ORB



**C** 83411-ORB



**D** 83511-SP  
83511-ORB



**E** 83211-ORB



**F** 83311-ORB

	Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Page
A	98011-WM 98011-SP	Stratton	17	12.5		3	(M)	100		97
B	94011-ORB	Apollo	12.5	12		2	(M)	60		100
C	83411-ORB	Seville	14.5	12		2	(M)	100		103
D	83511-ORB 83511-SP	Arcadia	14	10.25		2	(M)	100		106
E	83211-ORB	Marbella	14	10		2	(M)	100		109
F	83311-ORB	Madison	16	10.5		2	(M)	100		113

# Flushmounts



**A** 82121-WM



**B** 81821-FSN



**C** 96121-NI



**D** 95621-OB



**E** 1245S-WH



**H** 1245XL-WH



**F** 1245M-WH



**G** 1245L-WH

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Page
A	82121-WM	Mission Ridge	13	5	2	(M)	60		26
B	81821-FSN	Mendocino	14.75	8	2	(M)	60		44
C	96121-NI	Barcelona	13	6.75	2	(M)	60		50
D	95621-OB	Timberline	13	7.25	2	(M)	60		62
E	1245S-WH	Lunar	11.5	3.75	1	(M)	75	Twist-Lock Glass	
F	1245M-WH	Lunar	14	4.75	2	(M)	60	Twist-Lock Glass	
G	1245L-WH	Lunar	16.75	5.25	3	(M)	60	Twist-Lock Glass	
H	1245XL-WH	Lunar	20	5.5	4	(M)	60	Twist-Lock Glass	



# Flushmounts



**A** 1245S-ORB



**B** 1245M-ORB



**C** 1245L-ORB



**D** 1245XL-ORB



**E** 1245S-PW



**F** 1245M-PW



**G** 1245L-PW



**H** 1245XL-PW



**I** 1245M-AM-AO



**J** 1245L-AM-AO

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	1245S-ORB	Lunar	11.5	3.75	1	(M)	75	Twist-Lock Glass	
B	1245M-ORB	Lunar	14	4.75	2	(M)	60	Twist-Lock Glass	
C	1245L-ORB	Lunar	16.75	5.25	3	(M)	60	Twist-Lock Glass	
D	1245XL-ORB	Lunar	20	5.5	4	(M)	60	Twist-Lock Glass	
E	1245S-PW	Lunar	11.5	3.75	1	(M)	75	Twist-Lock Glass	
F	1245M-PW	Lunar	14	4.75	2	(M)	60	Twist-Lock Glass	
G	1245L-PW	Lunar	16.75	5.25	3	(M)	60	Twist-Lock Glass	
H	1245XL-PW	Lunar	20	5.5	4	(M)	60	Twist-Lock Glass	
I	1245M-AM-AO	Lunar	14	4.75	2	(M)	60	Twist-Lock Glass	
J	1245L-AM-AO	Lunar	16.75	5.25	3	(M)	60	Twist-Lock Glass	

# Flushmounts



A 1258S-ORB



D 1257S-ORB-AL



G 1257S-PW-AL



J 1257S-SP-AL



B 1258M-ORB



E 1257M-ORB-AL



H 1257M-PW-AL



K 1257M-SP-AL



C 1258L-ORB



F 1257L-ORB-AL



I 1257L-PW-AL



L 1257L-SP-AL

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	1258S-ORB	Allegro	8	3.75	1	(M)	60	Interior/Exterior Use	
B	1258M-ORB	Allegro	11	5	2	(M)	60	Interior/Exterior Use	
C	1258L-ORB	Allegro	13	5.75	2	(M)	60	Interior/Exterior Use	
D	1257S-ORB-AL	Decorative Flushmount	11.25	4.5	2	(M)	60		
E	1257M-ORB-AL	Decorative Flushmount	13.25	5.25	2	(M)	60		
F	1257L-ORB-AL	Decorative Flushmount	15.25	5.5	3	(M)	60		
G	1257S-PW-AL	Decorative Flushmount	11.25	4.5	2	(M)	60		
H	1257M-PW-AL	Decorative Flushmount	13.25	5.25	2	(M)	60		
I	1257L-PW-AL	Decorative Flushmount	15.25	5.5	3	(M)	60		
J	1257S-SP-AL	Decorative Flushmount	11.25	4.5	2	(M)	60		
K	1257M-SP-AL	Decorative Flushmount	13.25	5.25	2	(M)	60		
L	1257L-SP-AL	Decorative Flushmount	15.25	5.5	3	(M)	60		

# Flushmounts



**A** 1257S-WM-AM



**D** 1257S-WH-AL



**G** 4731-WH



**B** 1257M-WM-AM



**E** 1257M-WH-AL



**H** 4731-PW



**C** 1257L-WM-AM



**F** 1257L-WH-AL



**I** 4732-WH



**J** 4732-PW

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	1257S-WM-AM	Decorative Flushmount	11.25	4.5	2	(M)	60		
B	1257M-WM-AM	Decorative Flushmount	13.25	5.25	2	(M)	60		
C	1257L-WM-AM	Decorative Flushmount	15.25	5.5	3	(M)	60		
D	1257S-WH-AL	Decorative Flushmount	11.25	4.5	2	(M)	60		
E	1257M-WH-AL	Decorative Flushmount	13.25	5.25	2	(M)	60		
F	1257L-WH-AL	Decorative Flushmount	15.25	5.5	3	(M)	60		
G	4731-WH	Basic Flushmount	7	4.75	1	(M)	60		
H	4731-PW	Basic Flushmount	7	4.75	1	(M)	60		
I	4732-WH	Basic Flushmount	9.25	4.75	2	(M)	60		
J	4732-PW	Basic Flushmount	9.25	4.75	2	(M)	60		

## BEAUTIFY THE ENVIRONMENT INSIDE AND OUT WITH ENERGY STAR® QUALIFIED LIGHTING FROM DESIGNERS FOUNTAIN



We all have the opportunity to make a change for the better, and the way we light our homes is a perfect place to start. ENERGY STAR® qualified fixtures use about 75% less energy.

*Designers Fountain* is leading the way in offering a wide range of ENERGY STAR® qualified fixtures in a comprehensive array of types, styles, and finishes to provide you with the most fashionable options that save you money and help protect our environment.

### LOOK FOR THE BLUE LABEL: THE BENEFITS OF ENERGY STAR® QUALIFIED LIGHTING

ENERGY STAR® is a joint program of the United States Environmental Protection Agency (EPA) and the U.S. Department of Energy, helping us all save money and protect the environment through energy-efficient products and practices.

#### ENERGY BILL SAVINGS

You can save hundreds on energy bills and bulb replacement costs just by installing ENERGY STAR® qualified CFL or LED light fixtures from the *Designers Fountain* catalog. That's because ENERGY STAR® qualified fixtures use about 75% less energy than standard models and last 10 times as long. Just look for the blue label next to the model number at the bottom of the page!

#### QUALITY PERFORMANCE

Quality is built into the ENERGY STAR® guidelines set by the U.S. EPA to ensure that qualified fixtures light within one second, have excellent color rendering, and use bulbs that last at least 10,000 hours (9 years of household use at 3 hours per day).

#### ENVIRONMENTAL PROTECTION

More than half of the country's electric supply is produced by burning coal, and lighting consumes almost half the energy used in the average American home. Lowering energy use at home helps limit greenhouse gas emissions and air pollutants at the source.

An ENERGY STAR® qualified fixture prevents more than 450 pounds of greenhouse gas emissions over its lifetime, the equivalent of keeping nearly 200 pounds of coals from being burned.



[www.energystar.gov](http://www.energystar.gov)



# Fluorescent



**A** **ES97522-BU**  
**Finish:** Burnt Umber  
**Acrylic Lens:** Warm Amber Glaze



**B** **ES97523-BU**  
**Finish:** Burnt Umber  
**Acrylic Lens:** Warm Amber Glaze








**C** **ES82223-SP**  
**Finish:** Satin Platinum  
**Acrylic Lens:** Milk White



**D** **ES82323-ORB**  
**Finish:** Oil Rubbed Bronze  
**Acrylic Lens:** Glacier



**E** **ES82423-WM**  
**Finish:** Warm Mahogany  
**Acrylic Lens:** Amber

Item	Family	W	H	L	Bulbs	Type	Watts/K	Features/Notes	Symbol	Page
A	ES97522-BU Amherst	15.75	15.75	3.5	2	(FL)	22 & 32 /2,700K	T9 Lamps		40
B	ES97523-BU Amherst	18.25	4.25	55.5	4	(FL)	32/2,700K	T8 BI-pin Lamp		40
C	ES82223-SP Aliotta	11.25	5.25	49.5	3	(FL)	32/2,700K	T8 BI-pin Lamp		
D	ES82323-ORB Ballenger	11.25	5.5	49.5	3	(FL)	32/2,700K	T8 BI-pin Lamp		
E	ES82423-WM Cabrillo	17.5	4.5	50.25	4	(FL)	32/2,700K	T8 BI-pin Lamp		



# Fluorescent

*Satin Nickel Finish and White Acrylic lens*

*Oil Rubbed Bronze Finish or Satin Platinum Finish with Alabaster Glass*



**A** S1170MCFL-SN



**B** S1170LCFL-SN



**C** S117MCFL-SN



**D** S117LCFL-SN















**E** ES1257S-ORB-AL  
ES1257S-SP-AL



**F** ES1257M-SP-AL  
ES1257M-ORB-AL



**G** ES1257L-ORB-AL  
ES1257L-SP-AL

Item	Family	W	H	L	Bulbs	Type	Watts	Features/Notes	Symbol
A	S1170MCFL-SN	Oval Fluorescent	14.25	4.5	28.5	2 (FL)	22	T9 Circline Lamp	 
B	S1170LCFL-SN	Oval Fluorescent	18	4.75	32.5	2 (FL)	32	T9 Circline Lamp	
C	S117MCFL-SN	Round Fluorescent	16	4.5		2 (CFL)	18	G24q1 Lamp	
D	S117LCFL-SN	Round Fluorescent	23.75	4.75		4 (CFL)	26	G24q2 Lamp	 
E	ES1257S-ORB-AL ES1257S-SP-AL	Fluorescent	11.25	4.5		2 (CFL)	13	GU24 Lamp	 
F	ES1257M-ORB-AL ES1257M-SP-AL	Fluorescent	13.25	5.25		2 (CFL)	13	GU24 Lamp	 
G	ES1257L-ORB-AL ES1257L-SP-AL	Fluorescent	15.25	5.5		3 (CFL)	13	GU24 Lamp	 

# Fluorescent

*Oil Rubbed Bronze Finish, Old Bronze Finish and Aged Oil Rubbed Bronze with Acrylic Lens/Glacier  
Brushed Nickel Finish with Acrylic Lens/Milk White*



**A ES1246-ORB**  
**Finish:** Oil Rubbed Bronze  
**Acrylic Lens:** Glacier











**B ES1247-OB**  
**Finish:** Old Bronze  
**Acrylic Lens:** Glacier



**C ES1248-AOR**  
**Finish:** Aged Oil Rubbed Bronze  
**Acrylic Lens:** Glacier



**D ES1249-BN**  
**Finish:** Brushed Nickel  
**Acrylic Lens:** Milk White

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	ES1246-ORB	Round Fluorescent	16	3.5	2	(FL)	22W+32W	T9 Circline Lamp	 
B	ES1247-OB	Round Fluorescent	18.5	3.5	2	(FL)	22W+32W	T9 Circline Lamp	 
C	ES1248-AOR	Round Fluorescent	19	5.25	2	(FL)	22W+32W	T9 Circline Lamp	 
D	ES1249-BN	Round Fluorescent	16	3.75	2	(FL)	22W+32W	T9 Circline Lamp	 

# Fluorescent

White Finish with Acrylic Lens




A S116M2S-WH



B S116M3S-WH



C S116M2FL32-WH



D S116M4FL32-WH










E WA217120MPF



F WA232120MPF



G SL-18

Item	Family	W	H	L	Bulbs	Type	Watts/K	Features/Notes	Symbol
A	S116M2S-WH Cloud Fluorescent	8	2.75	48.75	2	(FL)	28/4,100K	T5 Lamp	
B	S116M3S-WH Cloud Fluorescent	10.5	2.75	48.75	3	(FL)	28/4,100K	T5 Lamp	
C	S116M2FL32-WH Cloud Fluorescent	11.5	5	51.25	2	(FL)	32/2,700K	T8 Bi-pin Lamp	
D	S116M4FL32-WH Cloud Fluorescent	17.5	5	51.25	4	(FL)	32/2,700K	T8 Bi-pin Lamp	
E	WA217120MPF Wraparound Fluorescent	6.5	2.5	24	2	(FL)	17/2,700K	T8 Bi-pin Lamp	
F	WA232120MPF Wraparound Fluorescent	6.5	2.5	48	2	(FL)	32/2,700K	T8 Bi-pin Lamp	
G	SL-18 Wraparound Fluorescent	6.5	2.5	48	2	(FL)	32/2,700K	T8 Bi-pin Lamp	

# LED Recessed

White and Brushed Nickel Finish

## Recessed Trim

Simple installation  
- no additional  
wiring

Save on bulb  
replacement up  
to 50,000 hour life

Medium base socket  
adapter

IC and non-IC  
recessed housings

Air tight seal saves  
energy by preventing  
leakage



Bright white light  
(3000K)

**A** **RTL67301-WH**  
For use with 5" or 6" housings

**C** **RTL47301-WH**  
For use with 4" housings

# LED Recessed

White and Brushed Nickel Finish




Item	Description	W	H	Ext	Bulbs	Type	Watts/L	Features/Notes	Symbol
A	RTL67301-WH 6" LED Retrofit Trim	7.5	5		(LED)	14.5/650L	Dimmable		
B	RTL67301-BN 6" LED Retrofit Trim	7.5	5		(LED)	14.5/650L	Dimmable		
C	RTL47301-WH 4" LED Retrofit Trim	5	3.5		(LED)	8.3/400L	Dimmable		
D	RTL47301-BN 4" LED Retrofit Trim	5	3.5		(LED)	8.3/400L	Dimmable		



# LED Recessed

## New Construction Housing



### Air Tight




- Rated for Air Tight construction when used with Air Tight rated trim.

### Air Tight Housing

- Aluminum construction provides heat dissipation.
- Gasket prevents air flow from temperature controlled spaces.


### Frame

- IC Rated
- Regressed Locking screw for securing hanger bars.
- Cutouts make it easy to crimp hanger bars in place.

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	CAT2000LICAT	4"	LED New Con. Hous.	7.25	5.5	(LED)			T24 
B	CAT5LICAT	5"	LED New Con. Hous.	10.5	7.5	(LED)			T24 
C	CAT7LICAT	6"	LED New Con. Hous.	10.5	7.5	(LED)			T24 

# LED Recessed

## Remodel Housing



### Junction Box

- Positional to handle straight conduit runs.
- Includes wire traps to make connections outside the box.
- Simple installation.

### Fast Nail Hanger Bars

- Pre-installed nails work with regular lumber, engineered lumber and laminated beams.
- Leveling flange to automatically align and hold the housing using one hand.
- Integral T-bar clips - no other clips required.

### Connection

Non-screw based insures high efficacy rating and prevents use of incandescent replacements.

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	CAT2000LICRAT	4"	LED Remodel Hous.	11.5	5.5	(LED)			T24
B	CAT5LICRAT	5"	LED Remodel. Hous.	13.5	7.75	(LED)			T24
C	CAT7LICRAT	6"	LED Remodel Hous.	11.5	7.5	(LED)			T24

# Bath, Vanity & Wall Sconces



## Symbol Guide



ENERGY STAR® Qualified



Bulb Included



ADA Compliant



Air Tight



Can be Mounted **UP** or **DOWN**



Suitable for **DAMP** Locations

**(FL)** Fluorescent Lamp

**(H)** Halogen Lamp

**(M)** Incandescent Medium Base

**(C)** Incandescent Candelabra Base

# Bath, Vanity & Wall Sconces

*Transitional*

**Finish:** *Tuscana*  
**Glass:** *White Opal*

**B** 6633-TU



**A** 6631-TU

**C** 6634-TU















**Finish:** *Biscayne Bronze*  
**Glass:** *Satin Etched*

**E** 6663-BBR



**D** 6661-BBR

**F** 6664-BBR

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	
A	6631-TU	Facet	9	4.5	5.5	1	(H)	60	G9 Lamp	 
B	6633-TU	Facet	25.25	4.5	5.5	3	(H)	60	G9 Lamp	 
C	6634-TU	Facet	34.5	4.5	5.5	4	(H)	60	G9 Lamp	 
D	6661-BBR	Cantebury	5.5	13.25	7.25	1	(M)	100		 
E	6663-BBR	Cantebury	24	7.75	7.25	3	(M)	100		 
F	6664-BBR	Cantebury	33.75	7.75	7.25	4	(M)	100		 

# Bath, Vanity & Wall Sconces

**Finish:** Oil Rubbed Bronze/Chrome  
**Glass:** White Opal



**A** 6491-ORB  
6491-CH



**B** 6492-CH  
6492-ORB



**C** 6493-CH  
6493-ORB



**D** 6494-ORB  
6494-CH



**E** 6495-ORB  
6495-CH

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A 6491-ORB 6491-CH	Hudson	5.25	7.5	5.5	1	(M)	100		
B 6492-ORB 6492-CH	Hudson	13.75	7.5	5.5	2	(M)	100		
C 6493-ORB 6493-CH	Hudson	21.75	7.5	5.5	3	(M)	100		
D 6494-ORB 6494-CH	Hudson	29.75	7.5	5.5	4	(M)	100		
E 6495-ORB 6495-CH	Hudson	37.75	7.5	5.5	5	(M)	100		



# Bath, Vanity & Wall Sconces

**A** 83701-ART



**C** 83703-ART



**B** 83702-ART



**D** 83704-ART



**F** 83803-FBZ



**E** 83801-FBZ

**G** 83804-FBZ



Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	Page
A	83701-ART Modesto	10	7	4.5	1	(M)	100			8
B	83702-ART Modesto	14.5	6.25	5.25	2	(M)	100			8
C	83703-ART Modesto	22	6.25	5.25	3	(M)	100			8
D	83704-ART Modesto	29.5	6.25	5.25	4	(M)	100			8
E	83801-FBZ Del Ray	5	16.5	6	1	(M)	100			13
F	83803-FBZ Del Ray	24	6.5	6	3	(M)	100			13
G	83804-FBZ Del Ray	31.5	6.5	6	4	(M)	100			13

# Bath, Vanity & Wall Sconces



**A** 84101-CHA



**B** 84103-CHA



**C** 84104-CHA



**D** 83601-TU



**E** 83603-TU



**F** 83604-TU

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	Page
A	84101-CHA	Bradley	5	14.75	5.5	1	(M)	100		16
B	84103-CHA	Bradley	29	5	4.5	3	(M)	100		16
C	84104-CHA	Bradley	38.75	5	4.5	4	(M)	100		16
D	83601-TU	Castello	4.5	12.25	6	1	(M)	100		19
E	83603-TU	Castello	22.5	7.75	5.5	3	(M)	100		19
F	83604-TU	Castello	30	7.75	5.5	4	(M)	100		19

# Bath, Vanity & Wall Sconces



**A** 97301-WSD



**B** 97302-WSD



**C** 97303-WSD



**D** 82101-WM










**F** 82103-WM



**E** 82102-WM



**G** 82104-WM


Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	Page
A	97301-WSD Austin	5.5	10	8.25	1	(M)	100			22
B	97302-WSD Austin	17.5	10	7.5	2	(M)	100			22
C	97303-WSD Austin	27.5	10	7.5	3	(M)	100			22
D	82101-WM Mission Ridge	5	10.5	7	1	(M)	100			29
E	82102-WM Mission Ridge	14.5	9.25	7	2	(M)	100			29
F	82103-WM Mission Ridge	23.5	9.25	7	3	(M)	100			29
G	82104-WM Mission Ridge	29.5	9.25	7	4	(M)	100			29

# Bath, Vanity & Wall Sconces



## Traditional



Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	Page	
A	82807-BNB	Del Amo	6.5	13	10.25	1	(M)	100		33	
B	82802-BNB	Del Amo	19.25	8.5	9	2	(M)	100		33	
C	82803-BNB	Del Amo	25.25	8.5	9	3	(M)	100		33	
D	82804-BNB	Del Amo	33.5	8.5	6	4	(M)	100		33	
E	ES97540-BU	Amherst	16	6.5	4.5	1	(F)	26	PLC G24q-3 base 		40
F	97501-BU	Amherst	6	10.25	8	1	(M)	100		39	
G	97502-BU	Amherst	14	10	8	2	(M)	100		39	
H	97503-BU	Amherst	22	10	8	3	(M)	100		39	
I	97504-BU	Amherst	30	10	8	4	(M)	100		39	



# Bath, Vanity & Wall Sconces



**A** 84201-CH



**B** 84203-CH



**C** 84204-CH



**D** 81801-FSN



**E** 81802-FSN



**F** 81803-FSN



**G** 81804-FSN

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	Page
A	84201-CH	Palatial	4.75	10.75	5.75	1	(C)	60		43
B	84203-CH	Palatial	22.50	9.75	5.75	3	(C)	60		43
C	84204-CH	Palatial	29.50	9.75	5.75	4	(C)	60		43
D	81801-FSN	Mendocino	7	17.25	7.5	1	(M)	100		47
E	81802-FSN	Mendocino	19.5	10.25	7.75	2	(M)	100		47
F	81803-FSN	Mendocino	24.25	10.25	7.75	3	(M)	100		47
G	81804-FSN	Mendocino	31.75	10.25	7.75	4	(M)	100		47



# Bath, Vanity & Wall Sconces



Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	Page
A	9032-NI	Barcelona	11	12	7.5	2	(C)	60		51
B	96101-NI	Barcelona	7.25	8.5	9.25	1	(M)	100		53
C	96102-NI	Barcelona	17.25	8.5	9.75	2	(M)	100		53
D	96103-NI	Barcelona	26	8.5	9.75	3	(M)	100		53
E	96104-NI	Barcelona	34.25	8.5	9.75	4	(M)	100		53
F	84701-NI	Lauderhill	5	13.5	7.25	1	(M)	100		55
G	84703-NI	Lauderhill	24.75	9	7	3	(M)	100		55
H	84704-NI	Lauderhill	34.5	9.50	7	4	(M)	100		55

# Bath, Vanity & Wall Sconces



**A** 95601-OB



**B** 95603-OB



**C** 95604-OB

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	Page
A	95601-OB Timberline	5	12.75	7.25	1	(M)	100			65
B	95603-OB Timberline	24	7.25	6.5	3	(M)	100			65
C	95604-OB Timberline	34	7.25	6.5	4	(M)	100			65


# Bath, Vanity & Wall Sconces

Contemporary

**Finish:** Chrome  
**Glass:** Frosted White Inside



A 6701-CH



B 6703-CH



C 6704-CH

**Finish:** Satin Platinum  
**Glass:** Frosted White Inside















D 6681-SP



E 6683-SP



F 6684-SP

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	
A	6701-CH	Belize	4.75	8.75	7.25	1	(M)	100		 
B	6703-CH	Belize	23.25	8	6.75	3	(M)	100		 
C	6704-CH	Belize	31.25	8	6.75	4	(M)	100		 
D	6681-SP	Geneva	6	7	4.75	1	(H)	60	G9 Lamp	 
E	6683-SP	Geneva	24	5	4.75	3	(H)	60	G9 Lamp	 
F	6684-SP	Geneva	33	5	4.75	4	(H)	60	G9 Lamp	 

# Bath, Vanity & Wall Sconces

**Finish:** Chrome

**Glass:** Top Sand + Bottom Clear



**A** 6691-CH

**B** 6693-CH



**C** 6694-CH

**Finish:** Chrome

**Glass:** Frosted















**D** 6671-CH



**E** 6673-CH



**F** 6674-CH

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	
A	6691-CH	Essence	5.25	8.75	7.25	1	(M)	100		 
B	6693-CH	Essence	23	8	7.25	3	(M)	100		 
C	6694-CH	Essence	32.25	8	7.25	4	(M)	100		 
D	6671-CH	Metropolis	5.5	9	6	1	(H)	60	G9 Lamp	 
E	6673-CH	Metropolis	24	6	7	3	(H)	60	G9 Lamp	 
F	6674-CH	Metropolis	32.75	6	7	4	(H)	60	G9 Lamp	 

## Bath, Vanity & Wall Sconces

**Finish:** Chrome  
**Glass:** White Opal



**A** 6621-CH

**B** 6623-CH



**C** 6624-CH

**Finish:** Chrome  
**Glass:** Clear and Etched

**E** 6453-CH



**D** 6452-CH



**F** 6454-CH

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
<b>A</b>	6621-CH	Venetian	6.5	8.5	5.5	1	(M)	100	
<b>B</b>	6623-CH	Venetian	24.5	8.5	5.5	3	(M)	100	
<b>C</b>	6624-CH	Venetian	33.5	8.5	5.5	4	(M)	100	
<b>D</b>	6452-CH	Astoria	15.25	8.75	6.75	2	(M)	100	
<b>E</b>	6453-CH	Astoria	25	8.75	6.75	3	(M)	100	
<b>F</b>	6454-CH	Astoria	34	8.75	6.75	4	(M)	100	



# Bath, Vanity & Wall Sconces

**Finish: Silver Sand**  
**Glass: Frosted**



Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	Page
A	4562-SI	Newave	25.75	5.75	4.5	2	(M)	100		
B	4563-SI	Newave	36.5	5.75	4.5	3	(M)	100		
C	4564-SI	Newave	47.5	5.75	4.5	4	(M)	100		
D	84001-CH	Mirage	10	11	5.5	1	(M)	100		72
E	84003-CH	Mirage	24	5.75	6.5	3	(M)	100		72
F	84004-CH	Mirage	32	5.75	6.5	4	(M)	100		72

# Bath, Vanity & Wall Sconces



**A** 84401-ART

**B** 84403-ART



**C** 84404-ART



**D** 84501-CH

**E** 84503-CH



**F** 84504-CH

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	Page
A	84401-ART	Bellemeade	4.5	12.25	6.5	1	(C)	60		75
B	84403-ART	Bellemeade	23	10.75	6	3	(C)	60		75
C	84404-ART	Bellemeade	30	10.75	6	4	(C)	60		75
D	84501-CH	Cordova	4.25	9.5	3.25	1	(C)	60		78
E	84503-CH	Cordova	23	8.5	7.25	3	(M)	100		78
F	84504-CH	Cordova	33	8.5	7.25	4	(M)	100		78

# Bath, Vanity & Wall Sconces



Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	Page
A	83007-SP	Avanti	5.5	19.75	6.5	1	(M)	100		81
B	83003-SP	Avanti	24.75	7.5	6.5	3	(M)	100		81
C	83004-SP	Avanti	32.75	7.5	6.5	4	(M)	100		81
D	83901-CH	Candence	5	17	7.25	1	(C)	60		84
E	83903-CH	Candence	24.75	8	5.5	3	(M)	100		84
F	83904-CH	Candence	33.75	8	5.5	4	(M)	100		84

# Bath, Vanity & Wall Sconces



A 83101-ORB



B 83103-ORB



C 83104-ORB

## Designers Value

**Finish:** Aged Bronze Patina Finish with Amber Glaze Glass  
Pewter Finish with Satin Opal Glass



D 4772-AM-ABP  
4772-PW



E 4773-PW  
4773-AM-ABP



F 4774-AM-ABP  
4774-PW

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	Page
A	83101-ORB	Majorca	6.25	16.5	7.25	1	(M)	100		87
B	83103-ORB	Majorca	26.5	9.75	8.25	3	(M)	100		87
C	83104-ORB	Majorca	36	9.75	8.25	4	(M)	100		87
D	4772-AM-ABP 4772-PW	Savon	17.5	7.25	9	2	(M)	100		
E	4773-AM-ABP 4773-PW	Savon	25.75	7.5	8.5	3	(M)	100		
F	4774-AM-ABP 4774-PW	Savon	32.75	7.75	9	4	(M)	100		

# Bath, Vanity & Wall Sconces

**Finish:** Chrome  
**Glass:** Satin Opal



**A** 4967-CH



**B** 4963-CH



**C** 4964-CH















**D** 96902-ORB



**E** 96903-ORB



**F** 96905-ORB

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	Page
A	4967-CH	Opal Essence	17.5	8.25	10	2	(M)	100	 	
B	4963-CH	Opal Essence	26.5	8.25	10	3	(M)	100	 	
C	4964-CH	Opal Essence	35.75	8.25	10	4	(M)	100	 	
D	96902-ORB	Montego	18	8.75	7.25	2	(M)	100	 	92
E	96903-ORB	Montego	24	8.75	7.25	3	(M)	100	 	92
F	96905-ORB	Montego	36.5	8.75	7.25	5	(M)	100	 	92



## Bath, Vanity & Wall Sconces



**A** 82901-BNB  
82901-SP











**B** 82902-SP  
82902-BNB



**C** 82903-SP  
82903-BNB



**D** 82904-BNB  
82904-SP

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	Page
A 82901-BNB 82901-SP	Tackwood	5	10.5	6.25	1	(M)	100		 	96
B 82902-BNB 82902-SP	Tackwood	15.5	8	6.25	2	(M)	100		 	96
C 82903-BNB 82903-SP	Tackwood	24	8	6.25	3	(M)	100		 	96
D 82904-BNB 82904-SP	Tackwood	29.25	8	6.25	4	(M)	100		 	96

# Bath, Vanity & Wall Sconces



**A** 98002-WM  
98002-SP



**B** 98003-SP  
98003-WM



**C** 98004-WM  
98004-SP




**D** 94001-ORB



**F** 94003-ORB  
94003-SP



**E** 94002-SP  
94002-ORB



**G** 94004-SP  
94004-ORB

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	Page
A	98002-WM 98002-SP	Stratton	13.5	9	7.5	2	(M)	100		99
B	98003-WM 98003-SP	Stratton	21.5	10	7.5	3	(M)	100		99
C	98004-WM 98004-SP	Stratton	29.75	10	7.5	4	(M)	100		99
D	94001-ORB	Apollo	5	9	8.75	1	(M)	100		102
E	94002-ORB 94002-SP	Apollo	15.75	8.5	6.5	2	(M)	100		102
F	94003-ORB 94003-SP	Apollo	23.75	8.5	6.5	3	(M)	100		102
G	94004-ORB 94004-SP	Apollo	31.25	8.5	6.5	4	(M)	100		102

# Bath, Vanity & Wall Sconces



**A** 83401-ORB



**C** 83403-ORB

**B** 83402-ORB



**D** 83404-ORB



**E** 6601-ORB  
6601-SP



**G** 6603-ORB  
6603-SP



**F** 6602-SP  
6602-ORB



**H** 6604-SP  
6604-ORB

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	Page
<b>A</b> 83401-ORB	Seville	6	8	7.5	1	(M)	100			105
<b>B</b> 83402-ORB	Seville	14.75	7.5	7.5	2	(M)	100			105
<b>C</b> 83403-ORB	Seville	23.5	7.5	7.5	3	(M)	100			105
<b>D</b> 83404-ORB	Seville	32.25	7.5	7.5	4	(M)	100			105
<b>E</b> 6601-ORB 6601-SP	Piazza	5.5	7.75	7	1	(M)	100			108
<b>F</b> 6602-ORB 6602-SP	Piazza	16.75	6.75	7	2	(M)	100			108
<b>G</b> 6603-ORB 6603-SP	Piazza	24	6.75	7	3	(M)	100			108
<b>H</b> 6604-ORB 6604-SP	Piazza	30	6.75	7	4	(M)	100			108

# Bath, Vanity & Wall Sconces



A 83201-ORB



C 83203-ORB



B 83202-ORB



D 83204-ORB



E 83301-ORB



G 83303-ORB



F 83302-ORB



H 83304-ORB

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	Page
A	83201-ORB	Marbella	4.5	7.5	5.5	1	(M)	100		111
B	83202-ORB	Marbella	13	7.25	5.5	2	(M)	100		111
C	83203-ORB	Marbella	18.75	7.25	5.5	3	(M)	100		111
D	83204-ORB	Marbella	24.75	7.25	5.5	4	(M)	100		111
E	83301-ORB	Madison	6	8.25	9.25	1	(M)	100		114
F	83302-ORB	Madison	16.25	8.25	9	2	(M)	100		114
G	83303-ORB	Madison	23	8.25	9	3	(M)	100		114
H	83304-ORB	Madison	30.25	8.25	9	4	(M)	100		114

# Bath, Vanity & Wall Sconces

**Finish:** Chrome  
**Glass:** Frosted Ribbed



**A** 4412-CH

**B** 4413-CH



**C** 4414-CH

**Finish:** Brushed Nickel



**D** 6613-BN



**E** 6614-BN

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	4412-CH	Value Bath/Vanity	11.5	7.75	7.5	2	(M)	100	
B	4413-CH	Value Bath/Vanity	16.5	7.75	9	3	(M)	100	
C	4414-CH	Value Bath/Vanity	24	7.75	10	4	(M)	100	
D	6613-BN	Value Bath/Vanity	18	4.5	2.5	3	(M)	100	
E	6614-BN	Value Bath/Vanity	24	4.5	2.5	4	(M)	100	



# Wall Sconces

## Transitional



A 84301-FBZ



B 84601-CH

## Traditional



C 9181-NI



D 98302-VBR

## Contemporary



E 6040-CH



F 6041-CH

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	Page	
A	84301-FBZ	Fieldhouse	5	12.5	5	1	(C)	60		9	
B	84601-CH	Cortona	6	11.5	8	1	(M)	100		24	
C	9181-NI	Alhambra	12.5	14.75	7	2	(C)	60		60	
D	98302-VBR	Bollo	11	19	7	2	(C)	60		66	
E	6040-CH	Moderne	14.25	6.75	3	1	(H)	100	T3 Lamp	ADA	
F	6041-CH	Moderne	7.75	14.5	3	1	(H)	100	T3 Lamp	ADA	

# Wall Sconces



**A** 6020-AST  
Glass: Frosted



**B** 6021-AST  
Glass: Scavo

6020-AST Caps Included:



Pewter      Distressed Bronze      Polished Brass      White

6021-AST Caps Included:



Distressed Bronze      European Gold      Sandstone

**Finish: Satin Platinum**  
**Glass: Opal**













**C** 4481-SP



**D** 6030-WH



**E** 6031-WH

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	
A	6020-AST	Value Wall Sconce	13.25	6.5	6.5	1	(M)	100	4 Accent Caps	 
B	6021-AST	Value Wall Sconce	12	6.25	6	1	(M)	100	3 Accent Caps	 
C	4481-SP	Brussels	5.25	10.5	5	1	(M)	100		 
D	6030-WH	Value Wall Sconce	12.5	5.5	6	1	(M)	100	Paintable Ceramic	 
E	6031-WH	Value Wall Sconce	12	5.25	6	1	(M)	100	Paintable Ceramic	 



# Exterior Collections



## Symbol Guide



ENERGY STAR® Qualified



Bulb Included



Title 24 Compliant



Cast Aluminum



All Exterior Fixtures are Suitable for **WET** Locations (Unless otherwise noted)



10 Ft. chain and 12 Ft. wire



Dark Sky



**ON** at Dusk, **OFF** at Dawn



Suitable for **DAMP** Locations



**(M)** Incandescent Medium Base



**(C)** Incandescent Candelabra Base



**(FL)** Fluorescent Lamp



**(H)** Halogen Lamp

• All chain mounted fixtures include 3 feet of chain and 12 feet of wire, unless otherwise noted.



# Guide to Exterior Lighting

## *Designers Fountain* offers the very best in outdoor lighting

Every outdoor fixture is specially designed with unique styling that compliments the exterior décor of any home. Sturdy construction, weather resistant finishing, and waterproof seals protect these fixtures from harsh outdoor elements to deliver warm, welcoming, safe and reliable outdoor lighting.

### LED

LED lamps are built into the fixtures and last up to 50,000 hours. They produce the same quality of light as the others using a fraction of the energy and are ideal for harsh conditions including cold weather climates.



### Fluorescent

These bulbs offer the same quality of light as the incandescent bulb using a fraction of the energy. They are more expensive to replace but last 5 times longer.



### Incandescent

These bulbs have been around the longest. They are the least expensive to purchase and contain no mercury.



### Dark Sky

Light pollution allows artificial light to shine outward and upward, where it's not wanted. It obscures the night sky, and can bother neighbors by shining over fences and into windows. *Designers Fountain* is pleased to join the fight against light pollution by offering four decorative outdoor collections that are designed to preserve and protect the nighttime environment. With the lamp recessed up into the hood, light shines downward only where it is needed, and the products meet the 90 degree cutoff requirement to qualify them as Dark Sky fixtures.



### Energy Saving Dusk 'til Dawn & Motion Activated

Selected *Designers Fountain* outdoor fixtures include the options to set the light to turn on automatically at dusk and turn off at dawn or to only turn on when someone passes by. These features are adjustable and makes it easy to save hundreds in electricity costs over the life of the fixture.



## Which Lamp is Right for Your Home?

	Incandescent	CFL	LED
Frequent Switching On/Off	Shortens Life	Shortens Life	No Effect
Lights Instantly	Yes	Some Delay	Yes
Light Focused Directionally	No	No	Yes
Durability	Low	Low	High
Sensitivity to Temperature	Some	Yes	No
Sensitivity to Humidity	Some	Yes	No
Hazardous Material Content	None	5 mg Mercury	None
Lifetime in Hours	2,000	10,000	50,000
Wattage Comparison	60-100 Watts	13-22 Watts	6-13 Watts

# Winston Collection

*Aged Bronze Patina Finish with Clear Crackle Glass*

A distinctive accessory for the home, the Winston collection impacts a 19th century hand crafted quality with a multi-faceted crackle glass pattern showcasing the luminescence of the LED light source.

LED


**A** LED21331-ABP



**B** LED21321-ABP











**C** LED21346-ABP



**Finish:**  
Aged Bronze Patina  
(ABP)



**Glass:**  
Clear Crackle

Item	Description	W	H	Ext	Bulbs	Type	Watts/K	Features/Notes	Symbol
A	LED21331-ABP 9" Wall Lantern	9	17.5	11.25	(LED)	12/3,000K		  	
B	LED21321-ABP 7" Wall Lantern	7	13.75	9.25	(LED)	9/3,000K		  	
C	LED21346-ABP 9" Post Lantern	9	18.5		(LED)	12/3,000K		 	



# Abbington-LED Collection

*Driftwood Finish with Clear Crackle Glass*

Old World influences blend seamlessly with today's new LED technology elevating this distinctive lantern design with the functionality of the modern lifestyle.



**A** LED2751-DWD



**B** LED2761-DWD



**C** LED2771-DWD











**D** LED2776-DWD



**Finish:**  
**Driftwood (DWD)**



**Glass:**  
**Clear Crackle**

Item	Description	W	H	Ext	Bulbs	Type	Watts/K	Features/Notes	Symbol
A	LED2751-DWD 6 1/2" Wall Lantern	6.5	12.25	7.5	(LED)	9/3,000K			 
B	LED2761-DWD 8" Wall Lantern	8	14	8.25	(LED)	12/3,000K			 
C	LED2771-DWD 9 1/2" Wall Lantern	9.5	17.25	9.75	(LED)	12/3,000K			 
D	LED2776-DWD 9 1/2" Post Lantern	9.5	18		(LED)	12/3,000K			 

# LED Collection

LED

## Whitmore

**Finish:** Mystic Bronze  
**Glass:** Clear Crackle



A LED21721-MBZ



B LED21731-MBZ

## Hillcrest

**Finish:** Aged Bronze Patina  
**Glass:** Clear Crackle



C LED21631-ABP

## Drake

**Finish:** Aged Bronze Patina  
**Glass:** Clear Seedy



D LED30821-ABP

Item	Description	W	H	Ext	Bulbs	Type	Watts/K	Features/Notes	Symbol
A	LED21721-MBZ 7" Wall Lantern	7	12.25	8	(LED)	10/3,000K			
B	LED21731-MBZ 9" Wall Lantern	9	15.75	10.5	(LED)	10/3,000K			
C	LED21631-ABP 8 3/4" Wall Lantern	8.75	15	11.75	(LED)	6/4,500K			
D	LED30821-ABP 8 3/4" Wall Lantern	8.75	13.25	10	(LED)	10/3,000K			

# LED

## Monarch

**Finish:** Forged Sienna

**Glass:** Clear Crackle



A LED21521-FSN

## Prado

**Finish:** Oil Rubbed Bronze

**Glass:** Clear Crackle















B LED31111-ORB



C LED31121-ORB



D LED31136-ORB

Item	Description	W	H	Ext	Bulbs	Type	Watts/K	Features/Notes	Symbol
A	LED21521-FSN 7" Wall Lantern	7	15.75	9.25	(LED)	7/4,500K		Bright White Light	  
B	LED31111-ORB 7" Wall Lantern	7	13	9.75	(LED)	10.6/3,000K			  
C	LED31121-ORB 9" Wall Lantern	9	16.25	11.75	(LED)	12/3,000K			  
D	LED31136-ORB 9" Post Lantern	9	18.25		(LED)	12/3,000K			  

# LED

## Lexington

**Finish:** Black  
**Glass:** Clear Seedy



A 7103LED-05

## Cortland

**Finish:** Dark Bronze  
**Glass:** Clear Seedy












B 7104LED-149

## Bedford

**Finish:** Natural Iron  
**Glass:** Rain



C 7105LED-151

Item	Description	W	H	Ext	Bulbs	Type	Watts/K	Features/Notes	Symbol
A	7103LED-05 6 1/2" Wall Lantern	6.5	14	7.75	(LED)	6/4,500K		  	
B	7104LED-149 6 1/2" Wall Lantern	6.5	16	8.25	(LED)	6/4,500K		  	
C	7105LED-151 7" Wall Lantern	7	13.25	8.25	(LED)	6/4,500K		  	

# LED

## Brighton

**Finish:** Black  
**Glass:** Clear Crackle



A 7101LED-05

## Hawthorne

**Finish:** Black  
**Glass:** Clear Seedy



B 7102LED-05

## Weston

**Finish:** Chestnut  
**Glass:** Clear Seedy



C 7106LED-260

Item	Description	W	H	Ext	Bulbs	Type	Watts/K	Features/Notes	Symbol
A	7101LED-05 6 1/4" Wall Lantern	6.25	9.75	7.5	(LED)	6/4,500K			
B	7102LED-05 5 1/4" Wall Lantern	5.25	9.25	7.25	(LED)	6/4,500K			
C	7106LED-260 6 1/2" Wall Lantern	6.5	10.5	7.75	(LED)	6/4,500K			



# Stonyridge Collection

*Flemish Bronze Finish with Tea Stained Glass*

The Stonyridge Collection evokes in the familiar and comfortable silhouette of an oil lantern, which warms the entrance with it's undeniable charm.

Fluorescent




**A** ES32021-FBZ



**B** ES32031-FBZ











**C** FL32036-FBZ



**Finish:**  
Flemish Bronze  
(FBZ)



**Glass:**  
Tea Stained

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	ES32021-FBZ 7 3/4" Wall Lantern	7.75	13	8.5	1	(CFL)	13	GU24 Lamps	  
B	ES32031-FBZ 9" Wall Lantern	9	16.5	10	1	(CFL)	13	GU24 Lamps	  
C	FL32036-FBZ 9" Post Lantern	9	20		1	(CFL)	13	GU24 Lamps	 

# Parkview Collection

*Flemish Bronze Finish with Tea Stained French Swirl Glass*

The simplicity of twisted iron details are paired with the calming comfort of a glowing candle in the Parkview Collection.



**A** ES31921-FBZ



**B** ES31931-FBZ











**C** FL31936-FBZ



**Finish:**  
Flemish Bronze  
(FBZ)



**Glass:**  
Tea Stained French Swirl

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	ES31921-FBZ 7 1/4" Wall Lantern	7.25	11.25	7.25	1	(CFL)	13	GU24 Lamps	  
B	ES31931-FBZ 9 1/2" Wall Lantern	9.5	13.5	9.25	1	(CFL)	13	GU24 Lamps	  
C	FL31936-FBZ 9 1/4" Post Lantern	9.25	16		1	(CFL)	13	GU24 Lamps	 

# Stockholm-ES Collection

*Oil Rubbed Bronze Finish with Clear Champagne and Frosted White Glass*

Fluorescent

Converging subtle curves with bold lines and luminous layers of glass, Majorca creates an intriguing interpretation of Modernism.



**A** ES31711-ORB



**C** ES31731-ORB



**D** ES31734-ORB



**B** ES31721-ORB


















**E** ES31736-ORB



**Finish:**  
Oil Rubbed Bronze  
(ORB)



**Glass:**  
Clear Champagne and  
Frosted White Glass

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	ES31711-ORB 7" Wall Lantern	7	12.25	9.5	1	(CFL)	13	GU24 Lamps	  
B	ES31721-ORB 9" Wall Lantern	9	15.75	11.75	1	(CFL)	18	GU24 Lamps	  
C	ES31731-ORB 11" Wall Lantern	11	18.75	14.25	1	(CFL)	23	GU24 Lamps	  
D	ES31734-ORB 11" Hanging Lantern	11	19.5		1	(CFL)	23	GU24 Lamps	  
E	ES31736-ORB 11" Post Lantern	11	20.5		1	(CFL)	23	GU24 Lamps	  

# Sedona-ES Collection

*Oil Rubbed Bronze Finish with Amber Glass*

The harmony and balance found in this Mission style collection recalls simplicity and grace.



**A** ES2301-AM-ORB



**C** ES2391-AM-ORB



**B** ES2394-AM-ORB



**D** FL2396-AM-ORB



**Finish:**  
Oil Rubbed Bronze  
(ORB)



**Glass:**  
Amber

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	ES2301-AM-ORB 12 1/2" Wall Lantern	12.5	23.5	16.75	1	(CFL)	18	GU24 Lamps	    
B	ES2394-AM-ORB 11" Hanging Lantern	11	19		1	(CFL)	18	GU24 Lamps	    
C	ES2391-AM-ORB 11" Wall Lantern	11	20	14.25	1	(CFL)	18	GU24 Lamps	    
D	FL2396-AM-ORB 11" Post Lantern	11	23		1	(CFL)	18	GU24 Lamps	   

# Sedona-ES

*Oil Rubbed Bronze Finish with Amber Glass*

Fluorescent



**E** ES2370-AM-ORB























**F** ES2375-AM-ORB



**G** ES2371-AM-ORB



**H** ES2381-AM-ORB

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
E	ES2370-AM-ORB 5 1/2" Wall Lantern	5.5	11.25	7.75	1	(CFL)	13	GU24 Lamps	    
F	ES2375-AM-ORB 13" Flushmount Lantern	13	5.25		1	(CFL)	22	GU24 Lamps	    
G	ES2371-AM-ORB 7" Wall Lantern	7	13	9.75	1	(CFL)	13	GU24 Lamps	    
H	ES2381-AM-ORB 9" Wall Lantern	9	16.25	11.75	1	(CFL)	13	GU24 Lamps	    



# Westchester-ES Collection

Bronze Finish with Amber Glass

Classic design featuring curved warm amber glass provides an inviting welcome.



A ES30511-AM-BZ



B ES30521-AM-BZ




C ES30531-AM-BZ



D ES30534-AM-BZ






















E FL30536-AM-BZ



Finish:  
Bronze (BZ)



Glass:  
Amber

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	ES30511-AM-BZ 7" Wall Lantern	7	12.75	9	1	(CFL)	13	GU24 Lamps	   
B	ES30521-AM-BZ 9.25" Wall Lantern	9.25	15.75	11.5	1	(CFL)	13	GU24 Lamps	   
C	ES30531-AM-BZ 11" Wall Lantern	11	19.5	13.5	1	(CFL)	18	GU24 Lamps	   
D	ES30534-AM-BZ 11" Hanging Lantern	11	19.5		1	(CFL)	13	GU24 Lamps	   
E	FL30536-AM-BZ 11" Post Lantern	11	21		1	(CFL)	18	GU24 Lamps	  

# Builder Cast Aluminum-ES Collection

Black Finish with Glacier Glass and Autumn Gold Finish with Warm Amber Glaze Glass

Fluorescent



**A** ES2861-AM-AG  
ES2861-GL-BK



**B** ES2461-AM-AG  
ES2461-GL-BK



**C** ES2462-GL-BK  
ES2462-AM-AG




Finish:  
Autumn Gold (AG)



Glass:  
Warm Ambre Glaze Glass



Finish:  
Black (BK)



Glass:  
Glacier Glass

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	ES2861-AM-AG ES2861-GL-BK 5.25" Wall Lantern	5.25	9.5	7	1	(CFL)	13	GU24 Lamps	
B	ES2461-AM-AG ES2461-GL-BK 6.75" Wall Lantern	6.75	14	8.5	1	(CFL)	13	GU24 Lamps	
C	ES2462-AM-AG ES2462-GL-BK 6.75" Wall Lantern	6.75	14	8.5	1	(CFL)	13	GU24 Lamps	

# Fluorescent

## Kensington-ES

**Finish:** Oil Rubbed Bronze Finish  
**Glass:** Tuscan Beige Glass












A ES21421-ORB

## Builder-ES

**Finish:** Black and Pewter Finish with White Glass  
 Rust Patina Finish with Amber Glass



B ES1161-BK  
 ES1161-PW  
 ES1161-RP

	Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	ES21421-ORB	7" Wall Lantern	7	11	8.75	1	(CFL)	13	GU24 Lamps	    
B	ES1161-RP ES1161-PW ES1161-BK	4 3/4" Wall Lantern	4.75	7.5		1	(CFL)	13	GU24 Lamps	   

# Gladiator Collection

Polished Brass Finish with Clear Glass

Solid brass lanterns with a durable Physical Vapor Deposition finish that will last longer than traditional polished brass.

Incandescent



**A** 1532-PVD-PB



**B** 1542-PVD-PB



**C** 1552-PVD-PB



**D** 1554-PVD-PB



**E** 1556-PVD-PB



Finish:  
Polished Brass (PB)

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	1532-PVD-PB 6.75" Wall Lantern Solid Brass	6.75	14.75	7.75	1	(M)	100	PVD Finish	
B	1542-PVD-PB 8" Wall Lantern Solid Brass	8	17.25	9.25	3	(C)	60	PVD Finish	
C	1552-PVD-PB 10" Wall Lantern Solid Brass	10	20.5	11.5	3	(C)	60	PVD Finish	
D	1554-PVD-PB 10" Hanging Lantern Solid Brass	10	21		3	(C)	60	PVD Finish	
E	1556-PVD-PB 11" Post Lantern Solid Brass	10	19		3	(C)	60	PVD Finish	







# Berkshire Collection

*Burnished Antique Copper Finish with Clear and Frosted Seedy Glass*

Featuring a boldy scrolled cast arm, vaulted arch style glass panels and a distressed hammered finish.

Incandescent



**A** 20601-BAC



**B** 20611-BAC



**C** 20621-BAC



**D** 20631-BAC



**Finish:**  
Burnished Antique Copper  
(BAC)



**Glass:**  
Clear and Frosted Seedy

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	20601-BAC 5 1/2" Wall Lantern	5.5	8.5	6.5	1	(M)	60		
B	20611-BAC 7" Wall Lantern	7	18	9	1	(M)	100		
C	20621-BAC 9" Wall Lantern	9	23	11.5	3	(C)	60		
D	20631-BAC 11" Wall Lantern	11	27.5	13.75	4	(C)	60		

# Berkshire

*Burnished Antique Copper Finish with Clear and Frosted Seedy Glass*



**E** 20634-BAC



**F** 20635-BAC



**H** 20613-BAC



**G** 20626-BAC

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
E	20634-BAC 11" Hanging Lantern	11	25.25		4	(C)	60		
F	20635-BAC 11" Flushmount	11	11		2	(C)	60		
G	20626-BAC 9" Post Lantern	9	22.5		3	(C)	60		
H	20613-BAC 3 Head Post Lantern	22	88.75		3	(M)	100		

# Canyon Lake Collection

*Chestnut Finish with Aged Crackle Optic Glass*

Tudor inspired collection featuring exquisite detailing of hand forged iron, intricately scrolled arms and cast appointments.

Incandescent



A 20934-CHN



B 20935-CHN









C 20936-CHN



**Finish:**  
Chestnut (CHN)



**Glass:**  
Aged Crackle Optic

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	20934-CHN 11" Hanginh Lantern	11	19		4	(C)	60		 
B	20935-CHN 12" Flushmount	12	6.5		2	(M)	60		 
C	20936-CHN 11" Post Lantern	11	24		4	(C)	60		 

# Canyon Lake

*Chestnut Finish with Aged Crackle Optic Glass*



D 20901-CHN



E 20911-CHN



F 20921-CHN



G 20931-CHN

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
D	20901-CHN 5 1/2" Wall Lantern	5.5	10.5	8.25	1	(M)	60		
E	20911-CHN 7" Wall Lantern	7	12.5	9	1	(M)	100		
F	20921-CHN 9" Wall Lantern	9	16	11	3	(C)	60		
G	20931-CHN 11" Wall Lantern	11	19.5	13.75	4	(C)	60		



# Stockholm Collection

*Oil Rubbed Bronze Finish with Clear Champagne and Frosted White Glass*

**B**alancing form and function, Stockholm is defined by its strong and well crafted lines. A flattering light filters through the double shades of clear champagne and frosted white glass.

Incandescent



**A** 31711-ORB



**B** 31721-ORB



**C** 31731-ORB



**Finish:**  
Oil Rubbed Bronze  
(ORB)



**Glass:**  
Clear Champagne and  
Frosted White Glass

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	<b>31711-ORB</b> 7" Wall Lantern	7	12.25	9.5	1	(M)	100		
B	<b>31721-ORB</b> 9" Wall Lantern	9	15.75	11.75	1	(M)	100		
C	<b>31731-ORB</b> 11" Wall Lantern	11	18.75	14.25	1	(M)	100		



# Stockholm

*Oil Rubbed Bronze Finish with Clear Champagne and Frosted White Glass*



**D** 31722-ORB



**E** 31734-ORB



**F** 31736-ORB

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
D	31722-ORB 13" Flushmount	13	8.25		2	(M)	100		
E	31734-ORB 11" Hanging Lantern	11	19.5		1	(M)	100		
F	31736-ORB 11" Post Lantern	11	20.5		1	(M)	100		

# Sedona Collection

*Mediterranean Patina Finish or Oil Rubbed Bronze Finish with Amber Glass*

The harmony and balance found in this Mission style collection recalls the simplicity and grace of Sedona.

Incandescent



**A** 2370-AM-ORB  
2370-AM-MP



**B** 2371-AM-MP  
2371-AM-ORB



**C** 2375-AM-ORB  
2375-AM-MP




**D** 2394-AM-ORB  
2394-AM-MP



**E** 2381-AM-ORB  
2381-AM-MP



**Finish:**  
Mediterranean Patina  
(MP)



**Finish:**  
Oil Rubbed Bronze  
(ORB)



**Glass:**  
Amber

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	2370-AM-ORB 2370-AM-MP	5.5	10.75	8	1	(M)	60		
B	2371-AM-ORB 2371-AM-MP	7	13	9.75	1	(M)	100		
C	2375-AM-ORB 2375-AM-MP	13	5.25		2	(M)	60		
D	2394-AM-ORB 2394-AM-MP	11	19		3	(C)	60		
E	2381-AM-ORB 2381-AM-MP	9	16.25	11.75	3	(C)	60		

# Sedona

Mediterranean Patina Finish or Oil Rubbed Bronze Finish with Amber Glass



**F** 2391-AM-MP  
2391-AM-ORB

**G** 2301-AM-ORB  
2301-AM-MP

**H** 2396-AM-MP  
2396-AM-ORB

**L** 23813-AM-ORB

Matching foyer pieces for Indoor use



**I** 23853-AM-ORB



**J** 23854-AM-ORB

220°  
DETECTION ANGLE  
3in1



**K** 2371MD-MP  
2371MD-ORB

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
F	2391-AM-MP 2391-AM-ORB	11	20	14.25	3	(C)	60		
G	2301-AM-MP 2301-AM-ORB	12.5	23.5	16.75	4	(C)	60		
H	2396-AM-MP 2396-AM-ORB	11	23		3	(C)	60		
I	23853-AM-ORB	19	33		3	(M)	100	Indoor Use	
J	23854-AM-ORB	21.5	43.25		4	(M)	100	Indoor Use	
K	2371MD-MP 2371MD-ORB	7	12	9.75	1	(M)	100	220° Detection Angle	
L	23813-AM-ORB	25	86		9	(C)	60		

# Sedona Collection

Oil Rubbed Bronze Finish with Seedy Glass

Incandescent



**A** 2394-ORB



**B** 2370-ORB



**C** 2371-ORB



**D** 2381-ORB



**E** 2391-ORB



**F** 2396-ORB

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	2394-ORB 11" Hanging Lantern	11	19		3	(C)	60		
B	2370-ORB 5 1/2" Wall Lantern	5.5	10.75	8	1	(M)	60		
C	2371-ORB 7" Wall Lantern	7	13	9.75	1	(M)	100		
D	2381-ORB 9" Wall Lantern	9	16.25	11.75	3	(C)	60		
E	2391-ORB 11" Wall Lantern	11	20	14.25	3	(C)	60		
F	2396-ORB 11" Post Lantern	11	23		3	(C)	60		



# Oak Park Collection

*Mediterranean Patina Finish with Amber Patina Glass*

Elegant mission style lanterns with strong simple lines and pyramid shaped roof.



A 30701-MP



B 30711-MP



C 30721-MP



D 30724-MP




E 30725-MP



F 30726-MP



Finish:  
**Mediterranean Patina  
(MP)**



Glass:  
**Amber Patina**

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	30701-MP 7" Wall Lantern	7	9.5		1	(M)	100		
B	30711-MP 9 1/2" Wall Lantern	9.5	13		3	(C)	60		
C	30721-MP 12" Wall Lantern	12	16.5		4	(C)	60		
D	30724-MP 12" Hanging Lantern	12	17.5		4	(C)	60		
E	30725-MP 12" Flushmount	12	7.5		2	(M)	60		
F	30726-MP 12" Post Lantern	12	19.75		4	(C)	60		



# Dayton Collection

*Aged Bronze Patina Finish with Ochere Glass*

Reminiscent of the Arts and Craft era, yet with a fresh and modern approach for today's exteriors.

Incandescent




**A** 30811-ABP



**B** 30821-ABP



**D** 30834-ABP



**C** 30831-ABP



**E** 30836-ABP



Finish:  
**Aged Bronze Patina (ABP)**



Glass:  
**Ochere**

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	30811-ABP 6 1/2" Wall Lantern	6.5	10.75		1	(M)	100		
B	30821-ABP 8 3/4" Wall Lantern	8.75	13		1	(M)	100		
C	30831-ABP 10 3/4" Wall Lantern	10.75	16.5		3	(C)	60		
D	30834-ABP 10 3/4" Hanging Lantern	10.75	16.25		3	(C)	60		
E	30836-ABP 10 3/4" Post Lantern	10.75	18		3	(C)	60		

# Braxton Collection

Charcoal Finish with Frosted with Painted White Glass Inside

The craftsmanship of forged iron is skillfully performed creating intersections of textured metal with smooth glass blending Modern with new transitional elegance.



A 31811-CHA



B 31821-CHA



C 31822-CHA



D 31831-CHA



E 31836-CHA



Post also converts to Hanging fixture. Hardware included to convert.  
W: 9" H: 15.75"



Finish:  
Charcoal (CHA)



Glass:  
Frosted with Painted White Glass Inside

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	31811-CHA 5" Wall Lantern	5	9.25	5	1	(M)	100		
B	31821-CHA 7" Wall Lantern	7	13	7.25	1	(M)	100		
C	31822-CHA 7" Pocket Wall Lantern	7	11.25	4.5	1	(M)	100		
D	31831-CHA 9" Wall Lantern	9	16.5	9	1	(M)	100		
E	31836-CHA 9" Post/Hanging Lantern	9	18		1	(M)	100	Convertible	

# Chelsea Collection

Black Finish with Clear Glass

Incandescent



**A** 2701-BK



**B** 2712-BK



**C** 2722-BK



**D** 2726-BK



Finish:  
Black (BK)

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	2701-BK 7 1/2" Wall Lantern	7.5	14.5		1	(M)	100		
B	2712-BK 8 1/4" Wall Lantern	8.25	13		2	(C)	60		
C	2722-BK 9" Wall Lantern	9	18.5		3	(C)	60		
D	2726-BK 9" Post Lantern	9	21.25		3	(C)	60		

# Westchester Collection

Bronze Finish with Amber Glass

Classic design featuring curved warm amber glass provides an inviting welcome.



A 30511-AM-BZ



B 30521-AM-BZ



C 30531-AM-BZ



D 30536-AM-BZ



Finish:  
Bronze (BZ)



Glass:  
Amber

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	30511-AM-BZ 7" Wall Lantern	7	12.75	9	1	(M)	100		
B	30521-AM-BZ 9" Wall Lantern	9	16	11.75	2	(C)	60		
C	30531-AM-BZ 11" Wall Lantern	11	19.5	13.5	3	(C)	60		
D	30536-AM-BZ 11" Post Lantern	11	21		3	(C)	60		

# Westchester

Bronze Finish and Rustic Silver Finish with Seedy Glass

Incandescent



**A** 30511-RS  
30511-BZ



**B** 30521-BZ



**C** 30531-BZ



Finish:  
**Rustic Silver (RS)**



Finish:  
**Bronze (BZ)**



Glass:  
**Seedy**

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	30511-RS 30511-BZ 7" Wall Lantern	7	12.75	9	1	(M)	100		
B	30521-BZ 9" Wall Lantern	9	16	11.75	2	(C)	60		
C	30531-BZ 11" Wall Lantern	11	19.5	13.5	3	(C)	60		



# Capella Collection

Autumn Gold Finish or Black Finish with Satin Crackle Glass



A 2864-BK



B 2867-AG  
2867-BK


C 2868-BK  
2868-AG




D 2866-AG  
2866-BK




E 2867MD-BK  
2867MD-AG




F 2868MD-AG  
2868MD-BK



Finish:  
Autumn Gold (AG)



Finish:  
Black (BK)



Glass:  
Satin Crackle

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	2864-BK 11" Hanging Lantern	11	20		1	(M)	100		
B	2867-AG 2867-BK 6 1/2" Wall Lantern	6.5	13.5	7.75	1	(M)	100		
C	2868-AG 2868-BK 9" Wall Lantern	9	18		1	(M)	100		
D	2866-AG 2866-BK 9" Post Lantern	9	19.25		1	(M)	100		
E	2867MD-AG 2867MD-BK 6 1/2" Cast Wall Lantern MD	6.5	15.5	8.75	1	(M)	100	180° Detection Angle	
F	2868MD-AG 2868MD-BK 9" Cast Wall Lantern MD	9	20	10	1	(M)	100	180° Detection Angle	

# Nantucket Collection

*Rustique Finish with Clear Seedy Glass*

Incandescent



# Kensington

*Oil Rubbed Bronze with Tuscan Beige*



Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	1751-RT	7 1/2"	14.25	9.25	1	(M)	100		
B	1761-RT	10"	18.25	11.75	1	(M)	100		
C	1766-RT	10"	19		1	(M)	150		
D	21421-ORB	7"	11	8.75	1	(M)	100		

# Riviera Collection

Black Finish with Clear Glass

Eight sided lanterns with clear beveled glass offered in three sizes.



A 2414-BK



B 2416-BK

C 2402-BK



D 2412-BK



E 1923-BK  
1923-WH



Finish:  
Black (BK)

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	2414-BK 7 1/2" Hanging Lantern	7.5	25		3	(C)	60		
B	2416-BK 7 1/2" Post Lantern	7.5	21.75		3	(C)	60		
C	2402-BK 6 1/4" Wall Lantern	6.25	19.75	11.25	1	(M)	150		
D	2412-BK 7 1/2" Wall Lantern	7.5	25	12	3	(C)	60		
E	1923-BK 1923-WH 3" Head Post Lantern	23.5	84.5		3	(M)	100		

# Tiverton Collection

Autumn Gold Finish, Black Finish and White Finish with Clear Glass

Six sided lanterns with rounded clear beveled glass panels.

Incandescent



**A** 2420-BK



**B** 2420MD-BK  
2420MD-AG  
2420MD-WH

180°  
DETECTION ANGLE  
**3 in 1**



**C** 2421-BK



**E** 2431-BK



**D** 2422-BK



Finish:  
**Black (BK)**

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	2420-BK	6 1/2"	14.75	7.75	1	(M)	100		
B	2420MD-AG 2420MD-BK/WH	6 1/4"	16.25	8	1	(M)	100	180° Detection Angle	
C	2421-BK	8"	16	9.25	1	(M)	100		
D	2422-BK	8"	21.5	9.25	1	(M)	100		
E	2431-BK	9 1/2"	18.25	9.5	1	(M)	100		



# Tiverton

Autumn Gold Finish or Black Finish with Clear Glass



Finish:  
Black (BK)

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
F	2432-BK 9 1/2" Cast Wall Lantern	9.5	24.25	9.5	1	(M)	100		
G	2434-BK 9 1/2" Cast Hanging Lantern	9.5	14		1	(M)	100		
H	2442-BK 13" Cast Wall Lantern	13	29.25	13.75	3	(C)	60		
I	2436-BK 9 1/2" Cast Post Lantern	9.5	21.5		1	(M)	100		
J	2446-BK 13" Cast Post Lantern	13	27.5		3	(C)	60		



# Devonshire Collection

*Black Finish with Clear Glass*

Six sided lanterns with rounded clear beveled glass panels.

Incandescent



**A** 2961-BK









**B** 2971-BK



**C** 2976-BK



Finish:  
Black (BK)

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	2961-BK 6 1/4" Wall Lantern	6.25	14.25	7.5	1	(M)	60		 
B	2971-BK 8" Wall Lantern	8	16.5	9.25	1	(M)	60		 
C	2976-BK 8" Wall Lantern	8	20		1	(M)	60		 

# Devonshire

Black Finish with Clear Glass



D 2981-BK



E 2984-BK



F 2986-BK


Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
D	2981-BK 9 1/2" Wall Lantern	9.5	19	9.75	3	(C)	60		
E	2984-BK 9 1/2" Hanging Lantern	9.5	15		3	(C)	60		
F	2986-BK 9 1/2" Post Lantern	9.5	23.5		3	(C)	60		

# Beveled Lanterns Collection

Pewter Finish, Weathered Brass Finish, Distressed Bronze and Rust Patina Finish with Clear Glass

Beveled glass acts as prisms in the sunlight, creating an interesting color diffraction which both highlights the glass and provides a spectrum of colors that ordinarily would be absent.

Incandescent







**A** 1101-PW  
1101-CL-WB

**B** 1103-PW  
1103-DB

**C** 1273-RP

**D** 30223-PW

	<b>Finish: Rust Patina (RP)</b>
	<b>Pewter (PW)</b>
	<b>Distressed Bronze (DB)</b>
	<b>Weathered Brass (WB)</b>

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	1101-PW 1101-CL-WB 7" Wall Lantern	7	13	6.75	1	(M)	100		
B	1103-PW 1103-DB 7" Wall Lantern	7	24	6.75	1	(M)	100	Convertible	
C	1273-RP 7" Wall Lantern	7	25.25	6.75	1	(M)	100	Convertible	
D	30223-PW 5 1/4" Wall Lantern	5.25	15	6	1	(M)	100	Convertible	

# Builder Cast Aluminum Collection



A 2067-BK



Finial Included

B 2861-AG  
2861-BK



C 2952-BK



D 2956-BK

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	2067-BK 10 1/2" Flushmount	10.5	5		1	(M)	100		CAST Aluminum
B	2861-AG 2861-BK 5 1/4" Aluminum Wall Lantern	5.25	8	7	1	(M)	100	Finial Included	CAST Aluminum
C	2952-BK 13" Wall Lantern	13	30.5	13.5	3	(C)	60		CAST Aluminum
D	2956-BK 13" Post Lantern	13	28		3	(C)	60	Fits 3" Post	CAST Aluminum

# Incandescent Collection

*Builder Cast Aluminum*

*Black Finish, Autumn Gold Finish and White Finish with Clear Glass*



A

2461-WH  
2461-BK  
2461-AG



B

2462-AG  
2462-BK  
2462-WH

*Bullet*

*Finish: Black*

*Bulkhead*

*Finish: White*

*Glass: Ribbed Frosted*



C

2994-BK



D

2071-WH



E

2073-WH

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	2461-AG 2461-BK/WH	7"	14.25"	9"	1	(M)	100		
B	2462-AG 2462-BK/WH	7"	14.25"	9"	1	(M)	100		
C	2994-BK	6.25"	11"		2	(M)	150	Par38 Lamp Holder with reflectors and adjustable swivels	
D	2071-WH	5"	8.5"	4.25"	1	(M)	60		
E	2073-WH	7"	7.75"	4.25"	1	(M)	60		



# Incandescent

## Porch Lights

Finished in Pewter, Polished Brass, Rustic Patina, Black and White with Clear Glass



A

1161-PW  
1161-CL-PB  
1161-RP  
1161-BK



B

2061-BK  
2061-WH


## Address Light

## Pier Mounts



C

31310-BK



D

1916-BK  
1916-ORB

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	1161-CL-PB 1161-PW/RP/BK	4 3/4"	8	5.75	1	(M)	60		
B	2061-BK 2061-WH	4 1/2"	7	5.75	1	(M)	100		
C	31310-BK	10.25	5.25	2.25	2	(Wedge)	3W(14 Volt)	Incl. 3 sets of ea. number	
D	1916-BK 1916-ORB	5.75	3.5						

# Incandescent

## Allegro



**A** 1258S-ORB



**B** 1258M-ORB



**C** 1258L-ORB

## Riviera



**D** 1923-BK  
1923-WH

## Sedona



**E** 23813-AM-ORB

## Berkshire



**F** 20613-BAC

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	Page
A	1258S-ORB Allegro	8	3.75		1	(M)	60	Interior/Exterior Use		133
B	1258M-ORB Allegro	11	5		2	(M)	60	Interior/Exterior Use		133
C	1258L-ORB Allegro	13	5.75		2	(M)	60	Interior/Exterior Use		133
D	1923-BK 1923-WH Riviera	23.5	84.5		3	(M)	100			204
E	23813-AM-ORB Sedona	25	86		9	(C)	60			194
F	20613-BAC Berkshire	22	88.75		3	(M)	100			188

# Bayport-DS Collection

Bronze Finish

This collection makes a statement with its casual silhouette and charm of a seaside haven.



A 31311-BZ



B 31321-BZ



C 31331-BZ



D 31336-BZ



Finish:  
Bronze (BZ)

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	31311-BZ 7" Wall Lantern-DS	7	7.75	8	1	(M)	100		
B	31321-BZ 9" Wall Lantern-DS	9	8.5	10	1	(M)	100		
C	31331-BZ 11" Wall Lantern-DS	11	10.25	13.5	1	(M)	100		
D	31336-BZ 11" Post Lantern-DS	11	15.25		1	(M)	100		

# Amherst-DS Collection

Burnt Umber Finish

The distinctive style of our popular Amherst collection has been integrated into a new Dark Sky outdoor collection.

Dark Sky



A 97591-BU

B 97592-BU



C 97593-BU



D 97594-BU



E 97596-BU



Finish:  
Burnt Umber (BU)

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	97591-BU 6 1/2" Wall Lantern-DS	6.5	13.25	8.75	1	(M)	100		
B	97592-BU 8" Wall Lantern-DS	8	17.75	11	1	(M)	100		
C	97593-BU 10" Wall Lantern-DS	10	21.25	13.25	1	(M)	100		
D	97594-BU 10" Hanging Lantern-DS	10	17.75		1	(M)	100		
E	97596-BU 10" Post Lantern-DS	10	20.25		1	(M)	100		



# Ellington-DS Collection

*Mediterranean Patina Finish or Oil Rubbed Bronze*

This collection's delicate pattern of scroll grill work is offered in two finishes.



**A** 31111-MP  
31111-ORB



**B** 31121-ORB  
31121-MP



**D** 31134-MP  
31134-ORB



**C** 31131-ORB  
31131-MP



**E** 31136-MP  
31136-ORB



Finish:  
**Mediterranean Patina (MP)**



Finish:  
**Oil Rubbed Bronze (ORB)**

	Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	31111-ORB 31111-MP	7" Wall Lantern-DS	7	13	9.75	1	(M)	60		
B	31121-ORB 31121-MP	9" Wall Lantern-DS	9	16.25	11.75	1	(M)	100		
C	31131-ORB 31131-MP	11" Wall Lantern-DS	11	20	14.25	1	(M)	100		
D	31134-ORB 31134-MP	11" Hanging Lantern-DS	11	19		1	(M)	100		
E	31136-ORB 31136-MP	11" Post Lantern-DS	11	23		1	(M)	100		



# Barrington-DS Collection

Old Bronze Finish

**B**old grill design makes a statement when softly illuminated for a warm inviting welcome.

Dark Sky



**A** 31011-OB



**B** 31021-OB




**D** 31034-OB



**C** 31031-OB



**E** 31036-OB



Finish:  
Old Bronze (OB)

Item	Description	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A	31011-OB 7" Wall Lantern-DS	7	13.75	9.5	1	(M)	100		
B	31021-OB 9" Wall Lantern-DS	9	17	11.5	1	(M)	100		
C	31031-OB 11" Wall Lantern-DS	11	20.25	9.5	1	(M)	100		
D	31034-OB 11" Hanging Lantern-DS	11	21		1	(M)	100		
E	31036-OB 11 1/4" Post Lantern-DS	11.25	23.75		1	(M)	100		

# Motion Detectors-Security Collection

The beauty and elegance of Solid Cast Aluminum with **Three** functions in **One**:

1. Motion Detector
2. Dusk 'til Dawn operation
3. Conventional lantern



**A** 2371MD-MP  
2371MD-ORB



**B** 2867MD-BK  
2867MD-AG



**C** 2868MD-AG  
2868MD-BK



**D** 2420MD-BK  
2420MD-AG  
2420MD-WH



**E** 2900MD-AG

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol	Page	
A	2371MD-MP 2371MD-ORB	Sedona	7	12	9.75	1	(M)	100	220° Detection Angle		194
B	2867MD-AG 2867MD-BK	Capella	6.5	15.5	8.75	1	(M)	100	180° Detection Angle		202
C	2868MD-AG 2868MD-BK	Capella	9	20	10	1	(M)	100	180° Detection Angle		202
D	2420MD-AG 2420MD-BK/WH	Tiverton	6.25	16.25	8	1	(M)	100	180° Detection Angle		205
E	2900MD-AG	Quintessence	7.5	12.5	10.75	1	(M)	100	180° Detection Angle		

# Motion Detector-Security

## Motion Detector Flood Light Twin Light

Finish: White - 06  
Distressed Bronze - 87



A P218C-06  
P218C-87

## Motion Detector Quartz Halogen Twin Light



B PH218S-87  
PH218S-06

## Quartz Halogen Twin Security Light

Finish: White - 06  
Distressed Bronze - 87



C Q102H-06  
Q102H-87



D Q152-87  
Q152-06

Item	Family	W	H	Ext	Bulbs	Type	Watts	Features/Notes	Symbol
A P218C-06 P218C-87	Area & Security	16.5	7.25	7.25	2	(M)	150	Bulb shield incl for PAR38 Flood Lamp, 180° Detection Angle	
B PH218S-06 PH218S-87	Quartz Halogen	9.75	10.25	5.25	2	(H)	100	180° Detection Angle	
C Q102H-06 Q102H-87	Quartz Halogen	10.5	4.75	7	2	(H)	100		
D Q152-06 Q152-87	Quartz Halogen	11	6	6.25	2	(H)	150		

# Backplate Dimensions for Outdoor Lanterns

Collection	Model	Width (in)	Height (in)	Junction Box Center to Top of Fixture
Abbington	LED2751	5	7 1/4	3
Abbington	LED2761	5	7	3
Abbington	LED2771	5	7	3 3/4
Amherst-DS	97591	4 1/2	6	8 3/4
Amherst-DS	97592	4 1/2	7 7/8	10 1/2
Amherst-DS	97593	4 1/2	8	12 3/4
Area & Security	P218C	4 3/8	Round	
Area & Security	PH218S	4 1/4	Round	
Area & Security	Q102H	4 3/4	Round	
Area & Security	Q152	4 3/4	Round	
Barrington-DS	31011	4 3/8	6 1/4	7 1/4
Barrington-DS	31021	4 3/4	9	8 1/2
Barrington-DS	31031	4 7/8	10 1/8	10 1/4
Bayport-DS	31311	4 1/2	Round	4
Bayport-DS	31321	4 1/2	Round	4 1/2
Bayport-DS	31331	5 1/8	Round	6 1/4
Bedford	7105LED	4 5/8	6 7/8	4 1/2
Berkshire	20601	4 3/8	5 1/8	5
Berkshire	20611	4 5/8	7 1/2	9
Berkshire	20621	4 7/8	9 5/8	11 3/4
Berkshire	20631	4 7/8	9 5/8	15 3/4
Beveled Lanterns	1101	4 5/8	5 1/2	4 3/4
Beveled Lanterns	1103	4 5/8	5 5/8	14 7/8
Beveled Lanterns	1273	4 3/4	Round	15
Beveled Lanterns	30223	4 3/4	Round	9
Braxton	31811-CHA	5	5	2 1/2
Braxton	31821-CHA	5	5	3 1/2
Braxton	31822-CHA	7	9 3/4	6 1/4
Braxton	31831-CHA	6 1/2	9	4 1/2
Brighton	7101LED	4 3/4	Round	2
Buckingham	1671	4 3/4	7	8
Buckingham	1681	4 3/4	7 1/8	9 1/4
Buckingham	1691	5 1/2	9 7/8	12 1/2
Builder Cast	2861	4 1/2	2 1/2	3
Builder Cast	2461	4 1/2	5 3/4	3 1/4
Builder Cast	2462	4 1/2	5 3/4	11
Builder Cast	1161	4 5/8	Round	2 1/2
Builder Cast	2952	4 1/2	13 3/4	21 1/2
Builder Cast	2061	4 3/4	Round	2 3/8
Bullet	2994	4 3/8	Round	2 1/8
Canyon Lake	20901	4 5/8	7 7/8	2 3/4
Canyon Lake	20911	4 5/8	7 7/8	2 3/4
Canyon Lake	20921	4 5/8	7 7/8	3
Canyon Lake	20931	5 5/8	9 5/8	6 1/2
Capella	2867MD	4 3/8	6 1/2	10 3/4
Capella	2868MD	4 3/8	6 1/2	13 3/4
Capella	2867	4 3/8	5	10 3/4
Capella	2868	4 5/8	6 3/4	13 1/2
Chelsea	2701	5 1/8	7 1/8	3 5/8
Chelsea	2712	5 1/2	7 1/4	5

Collection	Model	Width (in)	Height (in)	Junction Box Center to Top of Fixture
Chelsea	2722	5 1/8	9	4 1/2
Cortland	7104LED	4 3/8	5 7/8	5
Dayton	30811	4 1/2	8	2 3/8
Dayton	30821	4 7/8	9	3 5/8
Dayton	30831	6	11 1/4	4 3/8
Devonshire	2961	4 1/2	7 1/4	4
Devonshire	2971	4 3/8	7 1/8	4 3/4
Devonshire	2981	4 1/2	7 1/4	5 3/4
Ellington-DS	31111	4 3/8	6 3/8	3 1/4
Ellington-DS	31121	4 1/2	10	4 1/4
Ellington-DS	31131	4 1/2	12	4 7/8
Gladiator	1532	4 3/4	9	9 1/4
Gladiator	1542	4 3/4	10 3/8	11 1/2
Gladiator	1552	5 3/4	12 1/2	12 3/4
Hawthorne	7102LED	4 5/8	4 5/8	4
Kensington	21421	6 3/8	6 3/8	3 1/4
Lexington	7103LED	4 3/8	5 3/4	3 1/2
Monarch	LED21521-FSN	5	7	6 1/2
Nantucket	1751	4 1/2	5 3/8	10
Nantucket	1761	4 1/2	5 7/8	11 3/4
Oak Park	30701	4 3/4	6 1/4	4 3/8
Oak Park	30711	4 3/4	8 5/8	4 3/4
Oak Park	30721	4 3/4	10 3/4	6
Prado	LED31111	4 1/2	6 1/2	3 1/4
Prado	LED31121	4 1/2	10	4 1/4
Quintessence	2900MD	4 5/8	6 7/8	2 3/4
Riviera	2402	4 1/2	7 3/4	11 3/8
Riviera	2412	4 1/2	13 5/8	16
Sedona	2301	5 1/4	14	4 3/4
Sedona	2370	4 3/8	6 3/8	3 1/2
Sedona	2371	4 1/4	6 1/4	3 3/4
Sedona	2371MD	6 3/4	5	2 1/4
Sedona	2381	4 1/2	10	4 1/2
Sedona	2391	4 1/2	1 1/4	7 7/8
Stockholm	31711	5 1/2	7	4 1/2
Stockholm	31721	5 1/2	7	5 1/2
Stockholm	31731	6 3/4	9	6 1/2
Tiverton	2420MD	4 1/2	6 1/2	12
Tiverton	2421	4 1/2	7 1/4	4 7/8
Tiverton	2422	4 1/2	7 1/4	16 3/8
Tiverton	2431	4 1/2	7 1/4	5 1/2
Tiverton	2432	4 1/2	7 1/8	18 3/4
Tiverton	2442	4 1/2	13 3/4	20 1/2
Tiverton	2420	4 3/8	5 3/4	8 1/4
Westchester	30511	4 3/4	7	6
Westchester	30521	4 3/4	7	7 1/4
Westchester	30531	4 3/4	9 1/4	9
Weston	7106LED	4 3/4	Round	2 1/2
Winston	LED21331	5 3/4	8	8
Winston	LED21321	5	7 1/4	7

## Stems & Chains

### Additional Stems

Used to increase overall length of stem mounted fixtures.  
Contact Customer Service to determine the correct stem for your fixture.

Item	Finish
<b>6" Stems</b>	
ST06-AO	Ancient Oak
ST06-BNB	Burnished Bronze
ST06-BU	Burnt Umber
ST06-BWG	Burnished Walnut w/Gold
ST06-FSN	Forged Sienna
ST06-OB	Old Bronze
ST06-PW	Pewter
ST06-SP	Satin Platinum
ST06-TU	Tuscana
ST06-WM	Warm Mahogany
ST06-WSD	Weathered Saddle
ST06S-ORB	Oil Rubbed Bronze
<b>18" Stems</b>	
ST18-DB	Distressed Bronze
ST18-PW	Pewter

### Additional Chain

Used to increase overall length of chain mounted fixtures.  
Contact Customer Service Rep to determine the correct gauge for your fixture.

Item	Finish
<b>4 Gauge Chain</b>	
CHNBNB4G	Burnished Bronze
CHNBUH4G	Burnt Umber
CHNBWG4G	Burnished Walnut w/Gold
CHNCHH4G	Chrome
CHNFNS4G	Forged Sienna
CHNNIH4G	Natural Iron
CHNSPH4G	Satin Platinum
CHNVBR4G	Venetian Bronze
CHNWSD4G	Weathered Saddle
<b>8 Gauge Chain</b>	
CHNBNB8G	Burnished Bronze
CHNBUL8G	Burnt Umber
CHNBWG8G	Burnished Walnut w/Gold
CHNCHL8G	Chrome
CHNFNS8G	Forged Sienna
CHNMPL8G	Mediterranean Patina
CHNNIL8G	Natural Iron
CHNOBL8G	Old Bronze
CHNORB8G	Oil Rubbed Bronze
CHNPBL8G	Polished Brass
CHNPWL8G	Pewter
CHNSPL8G	Satin Platinum
CHNTUL8G	Tuscana
CHNVBR8G	Venetian Bronze
CHNWHL8G	White
CHNWML8G	Warm Mahogany



# Index

1101-CL-WB	209	1273-RP	209	2371-AM-ORB	193
1101-PW	209	1532-PVD-PB	185	2371MD-MP	194,218
1103-DB	209	1542-PVD-PB	185	2371MD-ORB	194,218
1103-PW	209	1552-PVD-PB	185	2371-ORB	195
1161-BK	212	1554-PVD-PB	185	2375-AM-MP	193
1161-CL-PB	212	1556-PVD-PB	185	2375-AM-ORB	193
1161-PW	212	1751-RT	203	23813-AM-ORB	194,213
1161-RP	212	1761-RT	203	2381-AM-MP	193
1245L-AM-AO	132	1766-RT	203	2381-AM-ORB	193
1245L-ORB	132	1916-BK	212	2381-ORB	195
1245L-PW	132	1916-ORB	212	23853-AM-ORB	194
1245L-WH	131	1923-BK	204,213	23854-AM-ORB	194
1245M-AM-AO	132	1923-WH	204,213	2391-AM-MP	194
1245M-ORB	132	20601-BAC	187	2391-AM-ORB	194
1245M-PW	132	20611-BAC	187	2391-ORB	195
1245M-WH	131	20613-BAC	188,213	2394-AM-MP	193
1245S-ORB	132	2061-BK	212	2394-AM-ORB	193
1245S-PW	132	2061-WH	212	2394-ORB	195
1245S-WH	131	20621-BAC	187	2396-AM-MP	194
1245XL-ORB	132	20626-BAC	188	2396-AM-ORB	194
1245XL-PW	132	20631-BAC	187	2396-ORB	195
1245XL-WH	131	20634-BAC	188	2402-BK	204
1257L-ORB-AL	133	20635-BAC	188	2412-BK	204
1257L-PW-AL	133	2067-BK	210	2414-BK	204
1257L-SP-AL	133	2071-WH	211	2416-BK	204
1257L-WH-AL	134	2073-WH	211	2420-BK	205
1257L-WM-AM	134	20901-CHN	190	2420MD-AG	205,218
1257M-ORB-AL	133	20911-CHN	190	2420MD-BK	205,218
1257M-PW-AL	133	20921-CHN	190	2420MD-WH	205,218
1257M-SP-AL	133	20931-CHN	190	2421-BK	205
1257M-WH-AL	134	20934-CHN	189	2422-BK	205
1257M-WM-AM	134	20935-CHN	189	2431-BK	205
1257S-ORB-AL	133	20936-CHN	189	2432-BK	206
1257S-PW-AL	133	21421-ORB	203	2434-BK	206
1257S-SP-AL	133	2301-AM-MP	194	2436-BK	206
1257S-WH-AL	134	2301-AM-ORB	194	2442-BK	206
1257S-WM-AM	134	2370-AM-MP	193	2446-BK	206
1258L-ORB	133,213	2370-AM-ORB	193	2461-AG	211
1258M-ORB	133,213	2370-ORB	195	2461-BK	211
1258S-ORB	133,213	2371-AM-MP	193	2461-WH	211

# Index

2462-AG	211	30711-MP	196	31836-CHA	198
2462-BK	211	30721-MP	196	4208-AL-PW	115
2462-WH	211	30724-MP	196	4412-CH	166
2701-BK	199	30725-MP	196	4413-CH	166
2712-BK	199	30726-MP	196	4414-CH	166
2722-BK	199	30811-ABP	197	4481-SP	168
2726-BK	199	30821-ABP	197	4562-SI	157
2861-AG	210	30831-ABP	197	4563-SI	157
2861-BK	210	30834-ABP	197	4564-SI	157
2864-BK	202	30836-ABP	197	4731-PW	134
2866-AG	202	31011-OB	217	4731-WH	134
2866-BK	202	31021-OB	217	4732-PW	134
2867-AG	202	31031-OB	217	4732-WH	134
2867-BK	202	31034-OB	217	4772-AM-ABP	160
2867MD-AG	202,218	31036-OB	217	4772-PW	160
2867MD-BK	202,218	31111-MP	216	4773-AM-ABP	160
2868-AG	202	31111-ORB	216	4773-PW	160
2868-BK	202	31121-MP	216	4774-AM-ABP	160
2868MD-AG	202,218	31121-ORB	216	4774-PW	160
2868MD-BK	202,218	31131-MP	216	4963-CH	161
2900MD-AG	218	31131-ORB	216	4964-CH	161
2952-BK	210	31134-MP	216	4967-CH	161
2956-BK	210	31134-ORB	216	5695-PW	115
2961-BK	207	31136-MP	216	6020-AST	168
2971-BK	207	31136-ORB	216	6021-AST	168
2976-BK	207	31310-BK	212	6030-WH	168
2981-BK	208	31311-BZ	214	6031-WH	168
2984-BK	208	31321-BZ	214	6040-CH	167
2986-BK	208	31331-BZ	214	6041-CH	167
2994-BK	211	31336-BZ	214	6201-ART	117
30223-PW	209	31711-ORB	191	6202-ART	117
30511-AM-BZ	200	31721-ORB	191	6313-GA-CH	125
30511-BZ	201	31722-ORB	192	6313-SA-CH	125
30511-RS	201	31731-ORB	191	6314-AM-CH	125
30521-AM-BZ	200	31734-ORB	192	6314-MS-CH	125
30521-BZ	201	31736-ORB	192	6315-AH-CH	125
30531-AM-BZ	200	31811-CHA	198	6315-AQ-CH	125
30531-BZ	201	31821-CHA	198	6316-AG-CH	125
30536-AM-BZ	200	31822-CHA	198	6316-EM-CH	125
30701-MP	196	31831-CHA	198	6452-CH	156

# Index

6453-CH	156	6701-CH	154	82803-BNB	33,150
6454-CH	156	6703-CH	154	82804-BNB	33,150
6491-CH	146	6704-CH	154	82807-BNB	33,150
6491-ORB	146	7101LED-05-DF	176	82811-BNB	32,127
6492-CH	146	7102LED-05-DF	176	82830-BNB	30,124
6492-ORB	146	7103LED-05-DF	175	82831-BNB	32,118
6493-CH	146	7104LED-149-DF	175	828815-BNB	30
6493-ORB	146	7105LED-151-DF	175	82883-BNB	32
6494-CH	146	7106LED-260-DF	176	82885-BNB	31
6494-ORB	146	815812-BWG	56	82889-BNB	31
6495-CH	146	81583-BWG	58	82901-BNB	96,162
6495-ORB	146	81586-BWG	58	82901-SP	96,162
6601-ORB	108,164	81588-BWG	57	82902-BNB	96,162
6601-SP	108,164	81589-BWG	57	82902-SP	96,162
6602-ORB	108,164	81801-FSN	47,151	82903-BNB	96,162
6602-SP	108,164	81802-FSN	47,151	82903-SP	96,162
6603-ORB	108,164	81803-FSN	47,151	82904-BNB	96,162
6603-SP	108,164	81804-FSN	47,151	82904-SP	96,162
6604-ORB	108,164	81811-FSN	45,128	82911-BNB	93,129
6604-SP	108,164	81821-FSN	44,131	82911-SP	93,129
6613-BN	166	81830-FSN	44,124	82930-BNB	96,126
6614-BN	166	81831-FSN	46,119	82930-SP	96,126
6621-CH	156	81832-FSN	45,118	82931-BNB	94,121
6623-CH	156	81838-FSN	45	82931-SP	94,121
6624-CH	156	81883-FSN	46	82932-BNB	93,121
6631-TU	145	81885-FSN	46	82932-SP	93,121
6633-TU	145	81889-FSN	44	82938-BNB	95
6634-TU	145	82101-WM	29,149	82938-SP	95
6661-BBR	145	82102-WM	29,149	829812-BNB	94
6663-BBR	145	82103-WM	29,149	829812-SP	94
6664-BBR	145	82104-WM	29,149	82983-BNB	94
6671-CH	155	82111-WM	27,127	82983-SP	94
6673-CH	155	82121-WM	26,131	82985-BNB	93
6674-CH	155	82130-WM	26,124	82985-SP	93
6681-SP	154	82131-WM	27,118	82989-BNB	95
6683-SP	154	82138-WM	28	82989-SP	95
6684-SP	154	82183-WM	28	83003-SP	81,159
6691-CH	155	82186-WM	27	83004-SP	81,159
6693-CH	155	82189-WM	26	83007-SP	81,159
6694-CH	155	82802-BNB	33,150	83011-SP	79,129

# Index

83030-SP	81,126	83485-ORB	103	83904-CH	84,159
83031-SP	80,120	83511-ORB	106,130	83911-CH	82,129
83083-SP	80	83511-SP	106,130	83930-CH	84,126
83086-SP	80	83531-ORB	107,122	83931-CH	82,120
83089-SP	79	83531-SP	107,122	839812-CH	83
83101-ORB	87,160	83532-ORB	107,122	83984-CH	83
83103-ORB	87,160	83532-SP	107,122	83986-CH	82
83104-ORB	87,160	83583-ORB	106	84001-CH	72,157
83111-ORB	85,129	83583-SP	106	84003-CH	72,157
83130-ORB	87,126	83585-ORB	107	84004-CH	72,157
83131-ORB	86,120	83585-SP	107	84011-CH	70,129
83183-ORB	86	83601-TU	19,148	84030-CH	72,125
83186-ORB	86	83603-TU	19,148	84031-CH	71,120
83189-ORB	85	83604-TU	19,148	84083-CH	71
83201-ORB	111,165	83611-TU	18,127	84085-CH	71
83202-ORB	111,165	83630-TU	17,123	84089-CH	70
83203-ORB	111,165	83631-TU	18,117	84101-CHA	16,148
83204-ORB	111,165	83686-TU	18	84103-CHA	16,148
83211-ORB	109,130	83689-TU	17	84104-CHA	16,148
83231-ORB	110,122	83701-ART	8,147	84111-CHA	15,127
83232-ORB	110,122	83702-ART	8,147	84130-CHA	14,123
83283-ORB	110	83703-ART	8,147	84131-CHA	15,117
83285-ORB	109	83704-ART	8,147	84183-CHA	15
83301-ORB	114,165	83711-ART	6,127	84186-CHA	14
83302-ORB	114,165	83730-ART	8,123	84201-CH	43,151
83303-ORB	114,165	83731-ART	7,117	84203-CH	43,151
83304-ORB	114,165	83738-ART	7	84204-CH	43,151
83311-ORB	113,130	83786-ART	7	84211-CH	41,128
83331-ORB	112,122	83789-ART	6	84230-CH	43,124
83332-ORB	113,122	83801-FBZ	13,147	84231-CH	42,118
83383-ORB	112	83803-FBZ	13,147	84283-CH	42
83385-ORB	113	83804-FBZ	13,147	84286-CH	42
83401-ORB	105,164	83811-FBZ	13,127	84289-CH	41
83402-ORB	105,164	83830-FBZ	13,123	84301-FBZ	9,167
83403-ORB	105,164	83831-FBZ	12,117	84330-FBZ	10,123
83404-ORB	105,164	83884-FBZ	12	84384-FBZ	10
83411-ORB	103,130	83886-FBZ	12	84386-FBZ	10
83431-ORB	104,121	83889-FBZ	11	84389-FBZ	9
83432-ORB	104,121	83901-CH	84,159	84401-ART	75,158
83483-ORB	104	83903-CH	84,159	84403-ART	75,158

# Index

84404-ART	75,158	94003-ORB	102,163	96931-ORB	92,121
84411-ART	74,129	94003-SP	102,163	96932-ORB	91,121
84430-ART	73,125	94004-ORB	102,163	96983-ORB	91
84483-ART	74	94004-SP	102,163	96985-ORB	91
84485-ART	74	94011-ORB	100,130	96989-ORB	90
84489-ART	73	94030-ORB	101,126	97301-WSD	22,149
84501-CH	78,158	94031-ORB	101,121	97302-WSD	22,149
84503-CH	78,158	94085-ORB	101	97303-WSD	22,149
84504-CH	78,158	94089-ORB	100	97311-WSD	21,127
84511-CH	76,129	95601-OB	65,153	97330-WSD	22,123
84530-CH	77,126	95603-OB	65,153	97331-WSD	21,118
84531-CH	77,120	95604-OB	65,153	973812-WSD	20
84585-CH	77	95611-OB	64,128	97386-WSD	21
84589-CH	76	95621-OB	62,131	97501-BU	39,150
84601-CH	24,167	95630-OB	63,124	97502-BU	39,150
84630-CH	25,123	95631-OB	64,119	97503-BU	39,150
84683-CH	24	95632-OB	64,120	97504-BU	39,150
84685-CH	25	95683-OB	63	97511-BU	36,128
84689-CH	23	95685-OB	63	97530-BU	39,124
84701-NI	55,152	95686-OB	64	97531-BU	38,118
84703-NI	55,152	95689-OB	62	97538-BU	38
84704-NI	55,152	96101-NI	53,152	97551-BU	38,118
84711-NI	54,128	96102-NI	53,152	975815-BU	36
84730-NI	55,124	96103-NI	53,152	97583-BU	37
84731-NI	55,119	96104-NI	53,152	97585-BU	37
84785-NI	54	96111-NI	48,128	97586-BU	38
84789-NI	54	96121-NI	50,131	97589-BU	37
9031-NI	52	96130-NI	49,124	97591-BU	215
9032-NI	51,152	96131-NI	48,119	97592-BU	215
9036-NI	52	96132-NI	51,119	97593-BU	215
9039-NI	49	96151-NI	50,119	97594-BU	215
9181-NI	60,167	961815-NI	50	97596-BU	215
9185-NI	61	96185-NI	49	98002-SP	99,163
9186-NI	60	96186-NI	48	98002-WM	99,163
9188-NI	61	96189-NI	51	98003-SP	99,163
9189-NI	59	96902-ORB	92,161	98003-WM	99,163
9192-NI	60,128	96903-ORB	92,161	98004-SP	99,163
94001-ORB	102,163	96905-ORB	92,161	98004-WM	99,163
94002-ORB	102,163	96911-ORB	90,129	98011-SP	97,130
94002-SP	102,163	96930-ORB	90,126	98011-WM	97,130



# Index

98030-SP	99,126	ES2461-GL-BK	183	LED31111-ORB	174
98030-WM	99,126	ES2462-AM-AG	183	LED31121-ORB	174
98031-SP	98,121	ES2462-GL-BK	183	LED31136-ORB	174
98031-WM	98,121	ES2861-AM-AG	183	P218C-06	219
98086-SP	97	ES2861-GL-BK	183	P218C-87	219
98086-WM	97	ES30511-AM-BZ	182	PH218S-06	219
98089-SP	98	ES30521-AM-BZ	182	PH218S-87	219
98089-WM	98	ES30531-AM-BZ	182	Q102H-06	219
98302-VBR	66,167	ES30534-AM-BZ	182	Q102H-87	219
98383-VBR	67	ES31711-ORB	179	Q152-06	219
98386-VBR	67	ES31721-ORB	179	Q152-87	219
98389-VBR	66	ES31731-ORB	179	RTL47301-BN	141
CAT2000LICAT	142	ES31734-ORB	179	RTL47301-WH	140
CAT2000LICRAT	143	ES31736-ORB	179	RTL67301-BN	141
CAT5LICAT	142	ES31921-FBZ	178	RTL67301-WH	140
CAT5LICRAT	143	ES31931-FBZ	178	S116M2FL32-WH	139
CAT7LICAT	142	ES32021-FBZ	177	S116M2S-WH	139
CAT7LICRAT	143	ES32031-FBZ	177	S116M3S-WH	139
ES1161-BK	184	ES82223-SP	136	S116M4FL32-WH	139
ES1161-PW	184	ES82323-ORB	136	S117LCFL-SN	137
ES1161-RP	184	ES82423-WM	136	S117MCFL-SN	137
ES1246-ORB	138	ES97522-BU	40,136	S117OLCFL-SN	137
ES1247-OB	138	ES97523-BU	40,136	S117OMCFL-SN	137
ES1248-AOR	138	ES97540-BU	40,150	SL-18	139
ES1249-BN	138	FL2396-AM-ORB	180	WA217120MPF	139
ES1257L-ORB-AL	137	FL30536-AM-BZ	182	WA232120MPF	139
ES1257L-SP-AL	137	FL31936-FBZ	178		
ES1257M-ORB-AL	137	FL32036-FBZ	177		
ES1257M-SP-AL	137	LED21321-ABP	171		
ES1257S-ORB-AL	137	LED21331-ABP	171		
ES1257S-SP-AL	137	LED21346-ABP	171		
ES21421-ORB	184	LED21521-FSN	174		
ES2301-AM-ORB	180	LED21631-ABP	173		
ES2370-AM-ORB	181	LED21721-MBZ	173		
ES2371-AM-ORB	181	LED21731-MBZ	173		
ES2375-AM-ORB	181	LED2751-DWD	172		
ES2381-AM-ORB	181	LED2761-DWD	172		
ES2391-AM-ORB	180	LED2771-DWD	172		
ES2394-AM-ORB	180	LED2776-DWD	172		
ES2461-AM-AG	183	LED30821-ABP	173		

## Notes

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---

# Finishes & Symbol Guide

## Finishes

<b>ABP</b>	Aged Bronze Patina
<b>AG</b>	Autumn Gold
<b>AO</b>	Ancient Oak
<b>AOR</b>	Aged Oil Rubbed Bronze
<b>ART</b>	Artisan
<b>BAC</b>	Burnished Antique Copper
<b>BBR</b>	Biscayne Bronze
<b>BK</b>	Black
<b>BN</b>	Brushed Nickel
<b>BNB</b>	Burnished Bronze
<b>BU</b>	Burnt Umber
<b>BWG</b>	Burnished Walnut w/Gold
<b>BZ</b>	Bronze
<b>CH</b>	Chrome

<b>CHA</b>	Charcoal
<b>CHN</b>	Chestnut
<b>DB</b>	Distressed Bronze
<b>DBZ</b>	Dark Bronze
<b>DWD</b>	Driftwood
<b>FBZ</b>	Flemish Bronze
<b>FSN</b>	Forged Sienna
<b>MBZ</b>	Mystic Bronze
<b>MP</b>	Mediterranean Patina
<b>NI</b>	Natural Iron
<b>OB</b>	Old Bronze
<b>ORB</b>	Oil Rubbed Bronze
<b>PB</b>	Polished Brass
<b>PW</b>	Pewter

<b>RP</b>	Rust Patina
<b>RS</b>	Rustic Silver
<b>RT</b>	Rustique
<b>SI</b>	Silver Sand
<b>SN</b>	Satin Nickel
<b>SP</b>	Satin Platinum
<b>TU</b>	Tuscan
<b>VBR</b>	Venetian Bronze
<b>WB</b>	Weathered Brass
<b>WH</b>	White
<b>WM</b>	Warm Mahogany
<b>WSD</b>	Weathered Saddle

## Symbol Guide



ENERGY STAR® Qualified



Can be Mounted **UP** or **DOWN**



**ON** at Dusk, **OFF** at Dawn



Bulb Included



Suitable for **DAMP** Locations



Dark Sky



Title 24 Compliant



Suitable for **WET** Locations



**(M)** Incandescent Medium Base



ADA Compliant



10 ft. chain and 12 ft. wire



**(C)** Incandescent Candelabra Base



Air Tight



Cast Aluminum



**(FL)** Fluorescent Lamp



**(H)** Halogen Lamp

• All Chain mounted fixtures include 3 feet of chain and 12 feet of wire, unless otherwise noted.

• All stem mounted fixtures include one each 6 in., 12 in. & 18 in. stems, unless otherwise noted.

- Designers Fountain reserves the right to make product changes without prior notice.
- Product specifications in this catalog are approximate and based on the most current information available at the time of publication.
- Finishes may vary due to multiple chemical process.
- Bulbs not included unless otherwise noted.
- Wattages stated are the maximum recommended; however, lower wattages may be used.
- Larger, heavier fixtures may require additional support and reinforced outlet boxes.
- Most outdoor fixtures are UL/cUL listed and suitable for Wet conditions, unless otherwise noted.
- Some finishes, specially outdoor fixtures, are subject to change slightly due to prolonged exposure to the sun or extreme weather conditions.
- Designers Fountain products are subject to revision to comply with changes in UL, CSA or the National Electrical Code.

# *Designers Fountain®*

**Distinctive Lighting**

20101 S. Santa Fe Avenue  
Rancho Dominguez, CA 90221

**Toll Free** 800-228-6197

**Fax** 800-762-3401

**Email** [email@designersftn.com](mailto:email@designersftn.com)

**www.DesignersFtn.com**



Design Winner 2011

Copyright 2012 Designers Fountain  
All rights reserved

*Master Catalog 118*  
*January 2012*

