



Combination Devices

C

Traditional	C-2
Decora®	C-4
Combination Devices.....	C-5
USB Charger Combination Devices.....	C-6
SmartlockPro® GFCI Combination Devices.....	C-7
LED Sensor Guide Lights	C-8

Combination Devices

COMMERCIAL



TRADITIONAL

Traditional Combination Devices

Leviton's combination devices offer pleasing, practical designs that fit standard wallboxes. Switch/switch, switch/receptacle and switch/pilot light combinations are available. These devices come in a range of colors and are backed by a limited two-year warranty.

Sample Traditional Devices



Features and Benefits

- AC quiet switches have silver-cadmium oxide contacts and receptacles have double-wire contacts for maximum conductivity
- All devices have a grounding screw, except where noted
- Terminal screws accept up to #12 AWG copper or copper-clad wire
- Fit standard wallboxes
- Break-off tabs on devices with switches permit conversion to separate feeds
- Limited 2-year warranty

Tamper-Resistant Receptacles

- Shutter mechanism inside the receptacle blocks access to the contacts unless a two-prong plug is inserted, helping ensure hairpins, keys, etc., will be locked out
- TR symbol on residential receptacles assures they meet the NEC requirement
- Heavy-duty construction offers long, trouble-free service life

Color Choices Traditional combination devices are offered in a wide range of colors. To order colors, add suffix to Cat. No.



White
(-W)



Ivory
(-I)



Light Almond
(-T)



Black
(-E)



Brown



Related Products

Leviton carries a complete line of traditional switches. See page A-2 in the Switches & Motor Controls section for more information. Leviton carries a complete line of traditional receptacles. See page B-3 in the Straight Blade Devices section for more information.

15A, 20A Combination Devices

Rating	Switch: 15A-120V AC Receptacle: 15A-125V	Switch: 20A-120V AC Receptacle: 20A-125V
--------	---	---

NEMA	5-15R	5-20R
------	-------	-------

Description	Color	Cat. No.	Cat. No.
Single Pole Switch/ Tamper-Resistant Receptacle*	White	T5225-W	—
	Ivory	T5225-I	—
	Light Almond	T5225-T	—
	Brown	T5225	—
Single Pole Switch/Receptacle*	White	5225-W	5335-W
	Ivory	5225-I	5335-I
	Light Almond	5225-T	—
	Black	—	5335-E
	Brown	5225	5335

Rating	15A-120/277V AC	20A-120/277V AC
--------	-----------------	-----------------

Description	Color	Cat. No.	Cat. No.
Two Single Pole Switches, non-ground	White	5224-W	—
	Ivory	5224-I	—
	Brown	5224	—
Two Single Pole Switches*	White	5224-2W	5334-W
	Ivory	5224-2I	5334-I
	Light Almond	5224-2T	—
	Brown	5224-2	5334

Rating	Switch: 15A-120V AC Pilot Light: 1/25W-125V AC	Switch: 20A-120V AC Pilot Light: 1/25W-125V AC
--------	---	---

NEMA	5-15R	5-20R
------	-------	-------

Description	Color	Cat. No.	Cat. No.
Single Pole Switch/ Pilot Light*	White	5226-W	—
	Ivory	5226-I	5336-I
	Light Almond	5226-T	—
	Brown	5226	5336

Rating	15A-120/277V AC
--------	-----------------

Description	Color	Cat. No.
3-Way Switch/Single Pole Switch*	White	5241-W
	Ivory	5241-I
	Light Almond	5241-T
	Brown	5241
Two 3-Way Switches*	White	5243-W
	Ivory	5243-I
	Light Almond	5243-T
	Brown	5243

Rating	Switch: 15A-120/277V AC Receptacle: 15A-125V
--------	---

Description	Color	Cat. No.
3-Way Switch/ Receptacle*	White	5245-W
	Ivory	5245-I
	Brown	5245



T5225-W



5224-W



5226-W



5241-I

*With ground screw

Continued on next page

Combination Devices

COMMERCIAL



DECORA®

Decora® Combination Devices

Decora® combination devices offer switch/switch, switch/receptacle and switch/pilot light pairings in sleek packages suitable for the finest interiors. For the ultimate in convenience and safety, the Decora® Combination Switch/SmartlockPro® GFCI receptacles pair a single pole switch with a GFCI receptacle equipped with Leviton's pioneering true dead-face design. The USB Charger Devices offers powerful charging capabilities to get your electronic devices up and running fast.

Sample Decora® Combination Devices



Features and Benefits

- Elegant Decora® styling provides multiple controls in a single-gang wallbox
- Impact-resistant thermoplastic and double-wipe contacts
- Common shunted internally to all switches
- Limited 2-year warranty

Tamper-Resistant Receptacles

- Shutter mechanism inside the receptacle blocks access to the contacts unless a two-prong plug is inserted, helping ensure hairpins, keys, etc., will be locked out
- TR symbol on residential receptacles assures they meet the 2008 NEC requirement
- Heavy-duty construction offers long, trouble-free service life

USB Charger Devices

- Smart chip recognizes and optimizes the charging requirements of the connected device
- Compatible with most tablets and other electronic mobile devices
- Vertical ports for easy maneuvering and reduced stress on USB cables

Hospital Grade USB Charger (Added Features)

- Self-grounding clip
- Extra heavy-duty impact-resistant polyester cover

All SmartlockPro® GFCI Combination Devices

- TEST/RESET buttons match device color
- Dual function LED indicator light — provides indication of wiring error and power availability

SmartlockPro® GFCI/Sensor Guide Light

- Manual control of sensor light using the TEST/RESET buttons
- Long-lasting, energy efficient LEDs with 20-year life expectancy — no bulbs to replace
- Light sensor provides automatic ON/OFF features

SmartlockPro® GFCI/Switch

- Replaces standard switch/outlet combination devices in residential and light commercial installations
- Permits multiple wiring options that allow for GFCI protection of switched load and downstream receptacles

Color Choices Decora® combination devices are offered in a wide range of colors. To order colors, add suffix to Cat. No.



White
(-W)



Ivory
(-I)



Light Almond
(-T)



Gray
(-G/-GY)



Black
(-E)



Brown



Decora® Combination Devices

15A, 20A Combination Devices

Rating	Switch: 15A-120V AC Receptacle: 15A-125V	Switch: 20A-120V AC Receptacle: 20A-125V
NEMA	 5-15R	 5-20R

Description	Color	Cat. No.	Cat. No.
Single Pole Switch/ Tamper-Resistant Receptacle	White	T5625-W	—
	Ivory	T5625-I	—
	Light Almond	T5625-T	—
	Black	T5625-E	—
Single Pole Switch/Receptacle	White	5625-W	5636-W
	Ivory	5625-I	5636-I
	Light Almond	5625-T	—
	Black	5625-E	—
	Gray	5625-GY	—



T5625-W



5625-W

Rating	Switch: 15A-120V AC Pilot Light: 1/25W-125V AC	Switch: 20A-120V AC Pilot Light: 1/25W-125V AC	
Description	Color	Cat. No.	Cat. No.
Single Pole Switch/Pilot Light	White	5626-W	—
	Ivory	5626-I	—

Rating	15A-120/277V AC	20A-120/277V AC	
Description	Color	Cat. No.	Cat. No.
Two Single Pole Switches	White	5634-W	5627-W
	Ivory	5634-I	5627-I
	Light Almond	5634-T	5627-T
	Black	5634-E	—
	Gray	5634-GY	—
	Brown	5634	—
3-Way Switch/ Single Pole Switch	White	5641-W	—
	Ivory	5641-I	—
	Light Almond	5641-T	—
	Black	5641-E	—
Two 3-Way Switches	White	5643-W	5640-W
	Ivory	5643-I	5640-I
	Light Almond	5643-T	5640-T

Continued on next page



Related Products

Leviton carries a complete line of Decora® switches. **See page A-16 in the Switches & Motor Controls section for more information.** Leviton carries a complete line of Decora® receptacles. **See page B-20 in the Straight Blade Devices section for more information.** Leviton carries a complete line of Decora® GFCIs. **See page D-3 in the GFCIs and AFCIs section for more information.**

Combination Devices

RESIDENTIAL



DECORA® | 15A, 20A

Continued from previous page

15A, 20A Combination Switches*

Rating	Switch: 15A-120V AC Pilot Light: 1/25W-125V AC		
Description	Color	Cat. No.	
3-Way Switch/ Receptacle	White	5645-W	
	Ivory	5645-I	
	Black	5645-E	

Rating	Individual Switches: 15A-120V Device Total: 20A-120V		Individual Switches: 15A-120V Device Total: 20A-120V
Description	Color	Cat. No. non-grounded	Cat. No. with ground screw
Dual Rockers	White	1754-W	1754-2W
	Ivory	1754-I	—
	Light Almond	1754-T	—
Illuminated Dual Rockers (Light is ON when top rocker is OFF)	White	1754-ILW	—
	Ivory	1754-ILI	—
Three Rockers	White	1755-W	1755-2W
	Ivory	1755-I	1755-2I
	Light Almond	1755-T	—



1755-W

*Warning: Although each individual rocker switch is rated up to 15A-120V, the total combined load for both duplex or all three triplex switches must not exceed 20 Amps

Decora® USB Charger Combination Devices

15A, 20A USB Charger Combination Switches

Rating	USB Port: 3.6A Receptacle: 15A-125V		USB Port: 3.6A Receptacle: 20A-125V
Description	Color	Cat. No.	Cat. No.
USB Charger/Duplex Tamper-Resistant Receptacle	White	T5632-W	T5832-W
	Ivory	T5632-I	T5832-I
	Light Almond	T5632-T	T5832-T
	Black	T5632-E	T5832-E
	Gray	T5632-GY	T5832-GY
	Brown	T5632-B	—
Hospital Grade USB Charger/Duplex Tamper-Resistant Receptacle	White	T5632-HGW	T5832-HGW
	Ivory	T5632-HGI	T5832-HGI
	Light Almond	T5632-HGT	T5832-HGT
	Black	T5632-HGE	T5832-HGE
	Gray	T5632-HGG	T5832-HGG
	Brown	T5632-HG	T5832-HG
	Red	T5632-HGR	T5832-HGR

Rating	USB Port: 4.2A	
Description	Color	Cat. No.
4-Port USB Charger	White	USB4P-W
	Ivory	USB4P-I
	Light Almond	USB4P-T
	Black	USB4P-E
	Gray	USB4P-GY



T5632-HGW



T5832-W



USB4P-W

Decora® SmartlockPro® GFCI-Protected Combination Devices

SmartlockPro® 15A, 20A GFCI-Protected Combination Devices		
Rating	15A-125V @ Receptacle, 20A-125V Feed-through Switch Rating 15A, 1800W @ 120V AC	
Description	Color	Cat. No.
Single Pole Switch and Tamper-Resistant SmartlockPro® Slim GFCI-Protected Receptacle with Indicator Light	White	X7299-W
	Ivory	X7299-T



X7299-W

SmartlockPro® GFCI Receptacle with Professional Grade Lockout Fed Spec				
Rating	15A-125V @ Receptacle 20A-125V Feed-Through		20A-125V @ Receptacle 20A-125V Feed-Through	
Description	Color	Cat. No.	Cat. No.	
SmartlockPro® Single Outlet Tamper-Resistant GFCI Protected Receptacle with Red Pilot Light	Brown	X7591-PL	X7891-PL	
	Ivory	X7591-PLI	X7891-PLI	
	White	X7591-PLW	X7891-PLW	
	Black	X7591-PLE	X7891-PLE	
	Gray	X7591-PLG	X7891-PLG	
	Light Almond	X7591-PLT	X7891-PLT	
	Red	X7591-PLR	X7891-PLR	
Automatic ON/OFF Sensor LED Guide Light and Tamper-Resistant SmartlockPro® GFCI-Protected Receptacle with Indicator Light*	White	X7592-W	X7892-W	
	Ivory	X7592-I	X7892-I	
Hospital Grade Duplex GFCI with Guide Light and Tamper-Resistant SmartlockPro® GFCI-Protected Receptacle with Indicator Light with self-grounding clip	White	X7592-HGW	X7892-HGW	
	Black	X7592-HGE	X7892-HGE	
	Gray	X7592-HGG	X7892-HGG	
	Light Almond	X7592-HGT	X7892-HGT	
	Red	X7592-HGR	X7892-HGR	



X7891-PLW



X7892-HGW



Related Products

Leviton carries a complete line of Decora® switches. **See page A-16 in the Switches & Motor Controls section for more information.** Leviton carries a complete line of Decora® receptacles. **See page B-20 in the Straight Blade Devices section for more information.** Leviton carries a complete line of Decora® GFCIs. **See page D-3 in the GFCIs and AFCIs section for more information.**

Combination Devices

RESIDENTIAL/COMMERCIAL



DECORA® | 15A

Decora® LED Sensor Guide Lights

Our LED Sensor Guide Light Series unites Leviton's quality Decora® wiring devices with energy-saving LED guide lights for a smart combination. The Sensor LEDs turn ON and OFF automatically in switch/guide light or tamper-resistant receptacle/guide light combinations. A full LED guide light version is perfect for hallways and stairways.

Features and Benefits

All Devices

- Impact-resistant face and body
- Long-lasting energy-efficient LED with long life expectancy — no bulbs to replace
- Light sensor provides automatic ON/OFF features
- All devices have a self grounding clip
- Fit standard wall boxes
- Back or side wired

Tamper-Resistant Receptacle/Guide Light

- Uses two LEDs
- Shutter mechanism inside the receptacle blocks access to the contacts unless a two-prong plug is inserted, helping ensure foreign objects will be locked out
- Complies with section 406.12 of the NEC Code


Combination Switch/Guide Light

- Uses two LEDs
- Single pole
- Neutral required

Full LED Guide Light

- Uses three LEDs
- Color Change Kits available for select models

15A LED Sensor Guide Lights

Rating	15A-125V AC	
NEMA	 5-15R	
Description	Color	Cat. No.
Decora® Tamper-Resistant Receptacle/LED Guide Light	White	T6525-W
	Ivory	T6525-I
	Light Almond	T6525-T
Decora® Single Pole Switch/LED Guide Light	White	6526-W
	Ivory	6526-I
	Light Almond	6526-T
Rating	1W-120V AC	
Description	Color	Cat. No.
Decora® Full LED Guide Light	White	6527-W
	Ivory	6527-I
	Light Almond	6527-T



T6525-W



6527-W