* **22471**
Mini Bi-Pin Quartz MR16 Socket
GX5.3 Base
12" 18 Gauge Leads
SF-1 200° C Leads
100 Watts Max., 250 Volts
Height - 1"

* **22470 - GY6.35 Base**
* **22472 - GX5.3 Base**
Mini Bi-Pin Quartz MR16 Socket
12" 18 Gauge Leads
SF-1 200° C Leads
100 Watts Max., 250 Volts
Height - ⅜"

* **22481**
High Pressure Sodium Lamp Socket
9" Wire Leads
Medium Base
SF-2/SEW-2 200° Leads
4 K.V. Pulse Rated
660 Watts Max., 600 Volts
⅝₂ Bushing
Height - 1¾"

* **22480**
High Pressure Sodium Lamp Socket
9" Wire Leads
Medium Base
SF-2/SEW-2 200° Leads
4 K.V. Pulse Rated
660 Watts Max., 600 Volts
⅝₂ Screw-Down
Height - 1¾"

* **11110**
Quartz Lamp Holder
5" Wire Leads
SF-1 200° C 300V Leads
For 4⅝" Lamp
500 Watts Max.
250 Volts
Fits R7S, 4⅝" Lamp Bases
Height - 1⅜"



* **11112**
HQI Lamp Holder
15" SF-2 200° C Leads
1000 Watt Max.
250 Volts
For R7S Lamp Bases
Height - 1⅝"

* **11109**
Quartz Lamp Holder
5" Wire Leads
SF-1 200° C
500 Watts Max.
250 Volts
300 Volts Leads
Fits R7S, 3¹⁵⁄₁₆" Lamp Bases
Height - 1⅞"

* **11100**
Double Contact Bayonet Socket
11" Wire Leads
Threaded 1/8-IP
SF-1 200° C 300V Leads
150 Watts Max.
125 Volts
Height - 1¼"

* **11104**
Porcelain Halogen Socket
5" Wire Leads
SF-1 200° C 300V Leads
100 Watts Max., 250 Volts
Fits G4, GX5.3, GV5.3
and G6.35 Lamp Bases
Height - ⅜"

* **11107**
MR16 Porcelain Socket
5" Wire Leads
SF-1 200° C Leads
75 Watts Max., 125 Volts
Fits G5.3, GU5.3
and GX5.3 Lamp Bases

* **11108**
MR16 Porcelain Socket
5" Wire Leads
SF-1 200° C Leads
75 Watts Max., 300 Volts
Fits G5.3, GU5.3
and GZ5.3 Lamp Bases

* **11033**
Electronic Transformer
Halogen
Use with 12 Volt MR11 or
MR16 Halogen Lamps
Input 120 Volts AC
Output 12 Volts, 80 Watt Max.
3½" White and 6" Black
18 Gauge Leads

***Bulk Pack**

CARDED PRODUCT SOLD IN INNER PACK ONLY