M18™ Blower
0884-20

Specifications:

Max Air Flow	100 CFM 160 MPH
Speed	3-Speed Electronic Switch
Length	20-1/2"
Weight	2.6 lbs

5 YEAR WARRANTY

Battery and Charger Sold Separately

Includes: Flexible Nozzle, 9" Extension, Universal Inflator/Deflator

M18™ Radio Charger
2792-20

Specifications:

Modes	AM / FM / AUX / Bluetooth®
Battery Charger	Charges all M18™ Batteries
Bluetooth® Antenna	100 ft Range
USB Charging Port	2.1 Amps

iPod MP3

1 YEAR WARRANTY

Battery Sold Separately

Includes: (1) 16" Auxiliary Input Cord, (2) AAA Batteries (For Memory Backup)

M18™ Jobsite Radio
2790-20

Specifications:

Tuner	Digital Reception with Signal Processor
Modes	AM / FM / AUX
USB Port	Ideal for Charging a Cell Phone, MP3, Digital Camera, GPS and Other Portable Electronic Devices
Powered By	Milwaukee® 12V – 28V Batteries (Including M Series, V Series and NiCd), 120V AC

iPod MP3

1 YEAR WARRANTY

Battery and Charger Sold Separately

Includes: (1) Auxiliary Input Cord, (2) AA Batteries (For Memory Backup)

M18™ Wet/Dry Vacuum
0880-20

Specifications:

Material	Wet/Dry
Capacity	2 gal
Max Air Flow	45 cu-ft/min
Sealed Suction in Water	32"
Washable/Reusable Filter	Yes
Compatibility	All Milwaukee® 18-Volt Slide-On Batteries (LITHIUM-ION or NiCd)

CERTIFIED HEPA FILTER

5 YEAR WARRANTY

Battery and Charger Sold Separately

Includes: Filter Assembly, Crevice Tool, Wide Utility Nozzle, Wireless Vinyl Hose

M18™ Power Source
49-24-2371

Specifications:

Powered By	All M18™ Batteries
Run-Time	Up to 18 Hours
2.1 Amp USB Port	Universal Charging for Smartphones, Tablets and Other Portable Electronic Devices

Batteries Sold Separately

Powers all Milwaukee® M12™ Heated Gear

M18™ Stick Light
2352-20

Specifications:

Light Type	LED
Lumens (2 Settings)	300 / 150
LUX	140 / 70
Hands Free	2 Hooks for Hanging Vertically and Horizontally
Length	11-5/8"
Weight	1.1 lbs

LIMITED LIFETIME WARRANTY

Battery and Charger Sold Separately

M18™ Flood/Lantern
2363-20

Specifications:

Light Type	LED
Lumens (4 Settings)	700 / 350 / 70 / Strobe
Beam Distance	29m
Hands Free	2 Hook Design Works as Handle and Hook
Length	11-1/2"
Weight	1.2 lbs

LIMITED LIFETIME WARRANTY

Battery and Charger Sold Separately

M18™ LED Flood Light
2361-20

Specifications:

Light Type	LED
Lumen	1,100
LUX	Up to 1,300
Length	8-3/4"
Weight	3.4 lbs

LIMITED LIFETIME WARRANTY

Battery and Charger Sold Separately

M18™ LED Work Light
2735-20

Specifications:

Light Type	LED
Lumen	99
Hands Free	Integrated Hook
Head Rotation	90°

LIMITED LIFETIME WARRANTY

Battery and Charger Sold Separately

Related Accessory:
49-81-0090 – LED Upgrade Bulb

Compatible with Milwaukee® M12™, M18™, M28™, and most other power tool work lights

LIMITED LIFETIME WARRANTY

REDLITHIUM™ XC BATTERY ADVANTAGES

- Full M18™ System Compatibility
- Double the Run-Time of Compact Packs
- Increased Performance and Power

M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack
48-11-1850

3 YEAR WARRANTY

2-Pack Available
48-11-1852

M18™ REDLITHIUM™ XC4.0 Extended Capacity Battery Pack
48-11-1840

3 YEAR WARRANTY

M18™ REDLITHIUM™ XC Extended Capacity Battery Pack
48-11-1828

3 YEAR WARRANTY

2-Pack Available
48-11-1822

M18™ BATTERY STARTER KITS

M18™ REDLITHIUM™ XC5.0 System Starter Kit
48-59-1850

M18™ REDLITHIUM™ XC System Starter Kit
48-59-1813

REDLITHIUM™ COMPACT BATTERY ADVANTAGES

- Full M18™ System Compatibility
- Lighter Weight for Less Fatigue
- Compact Size for Increased Versatility

M18™ REDLITHIUM™ 2.0 Compact Battery Pack
48-11-1820

2 YEAR WARRANTY

M18™ REDLITHIUM™ Compact Battery Pack
48-11-1815

2 YEAR WARRANTY

2-Pack Available
48-11-1811

REDLITHIUM™ RUN-TIME ADVANTAGE



M12™ and M18™ Multi-Voltage Charger
48-59-1812

Specifications:

Compatibility	All M12™ and M18™ Batteries
Charge Sequence	Sequential (First In, First Charged)
Integrated Hang-Holes	Yes
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes

5 YEAR WARRANTY

Batteries Sold Separately

M12™ & M18™ Rapid Charge Station
48-59-1807

Specifications:

Compatibility	All M12™ and M18™ Batteries
Charge Sequence	Charges 3 Batteries Simultaneously
Charge Speed	Charges Individual Batteries up to 50% Faster
Capacity	Holds (3) M18™ & (3) M12™ Batteries
Integrated Hang-Holes	Yes
Cell Voltage Monitoring	Yes
Pass-Through Plug	Yes

5 YEAR WARRANTY

Pass-Through Plug

Batteries Sold Separately

M18™ AC/DC Wall & Vehicle Charger
2710-20

Compatibility	All M18™ Batteries
Integrated Hang-Holes	Yes
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes

5 YEAR WARRANTY

M18™ Six-Pack Sequential Charger
48-59-1806

Specifications:

Compatibility	All M18™ Batteries
Charge Sequence	Sequential (Counter-Clockwise Rotation)
Skip Button	Manually Designate which Battery Charges First
Integrated Hang-Holes	Yes
Cell Voltage Monitoring	Yes
Pass-Through Plug	Yes

5 YEAR WARRANTY

Pass-Through Plug

Batteries Sold Separately