SATCO

Lighting Components



New York, Florida, Texas, California,
Washington & Puerto Rico

Sockets & Lampholders







Switches & Accessories







Wire, Cords & Accessories







SATCO®

The SATCO trademark has been recognized as the preferred brand for quality lighting products for more than 45 years. SATCO offers a wide variety of products including; a full line of decorative and general service light bulbs, lighting hardware, electrical accessories and consumer products.

NUVO® LIGHTING

Our NUVO line of lighting fixtures and track lighting boasts more than 3000 items, 700 which are ENERGY STAR qualified. The NUVO brand delivers a “one stop shop” option to meet the majority of your decorative and functional lighting needs.

HYGRADE™

The HYGRADE family of products is a commercially oriented lamp line which includes linear T5 & T8 fluorescents, pin base compact fluorescent and HID product collections. All product groups meet or exceed today’s efficiency and environmental requirements and initiatives.

KolourOne LED TECHNOLOGY

KolourOne is the newest member of the SATCO family. KolourOne represents quality LED lighting products in all areas and applications – lamps, components and custom solutions are all part of the KolourOne experience.

Hardware & Lamp Parts







Canopies & Glass Holders







Glassware & Shades







See Our Full Line of Catalogs for All Your Lighting Needs

Energy Efficient Lamp Catalog



SA2030

Consumer Products Catalog



SA2040

Lamp Specification Catalog



SA2013

NUVO Energy Efficient Lighting Catalog



NU3090R

NUVO Lighting Catalog



NU3020

Table of Contents

Sockets, Lampholders & Ballasts 5

Medium Base Aluminum 6-15
Medium Base 3 & 4 Piece Stamped Solid Brass 16-23
Medium Base Interiors, Shells & Accessories 24-25
Assorted Socket Clusters 26-27
Medium Base Phenolic 28-32
Medium Base (Paper Liner) 33
Medium Base Porcelain 34-43
Medium Base Porcelain – 4KV 44-45
Mogul Base Porcelain – 4KV – 6KV 46-49
Specialty Porcelain & Lamps 50-51
Medium Base Receptacles & Bulb Cages 52-53
Medium Base Phenolic Sockets 54-55
Medium Base Phenolic Socket Clusters 56-59
Candelabra Base Phenolic 60-63
Specialty Porcelain/Halogen 64-67
Bayonet & Linear Sockets 68
Sign Receptacles 69
Fluorescent Lamps, Sockets & Ballasts 70-90

Switches & Accessories 91

Switches (Rotary, Push, Pull Chain, Toggle) 92-95
Dimmer Controls & Switches 96-97
Attachment Plugs 98
Cord Switches 99
Rocker Switches & Receptacles 100
Touch & Photoelectric Switches 101-102
Socket Extenders, Reducers & Adapters 103-105
Outlets (Plug-In & Add-On) 106

Wire, Cords & Accessories 107

Bulk Wire 108-113
Cord Sets 114-119
Extension Cords & Surge Suppressors 120-125
Wire Covers 126
Wire Nuts & Electrical Tape 127
Bushings 128

Hardware & Lamp Parts 129

Harps & Accessories 130-132
Finials 133-136
Reel & Bulk Chain 137-139
Steel & Brass Nipples 140-141
Cross Bars 142-143
Locknuts 144-145
Check Rings 146-147
Washers & Pads 148
Fixture & Screw Collar Loops 149-151
Hardware, Caps, Screws & Bushings 152-154
Brass Couplings & Balls 155
Brass Necks & Spindles 156
Brass Swivels 157
Armbacks & Elbows 158
Swag Hook Kits 159
Spacers & Candle Cups 160
Steel Necks 161
Candle Covers 162-165
Bead Chain & Accessories, Pulls & Tassels 166
Crystal & Accessories 167
Lighting Accessories 168

Canopies & Glass Holders 172

Canopy Parts & Kits 170-172
Canopies & Extensions 173
Canopy, Fan & Blank Up Kits 174-175
Wired Fixture, Bent Glass, Ceiling Pans 176-178
Fitters & Ball Glass Holders 179
Cast Brass Canopies 180-181
Heavy 2-Step Steel Canopies 182
Wall Sconces 183
U-Channel Glass Holders 184-185
Glass Holders & Fixture Bodies 186

Glassware & Shades 187

Globe, Schoolhouse, Drum & Mushroom Glass 188-191
Screw Fitter & Cased Glass 192
Lexan & Poly 193
Hall, Porch, I.E.S. Fixture & Specialty Glass 194-195
Bent Glass (Round Square & U-Channel) 196-197
Clip on Shades 198-200

INDEX 201

Sockets, Lampholders & Ballasts















Medium Base Aluminum 6-15
Medium Base 3 & 4 Piece Stamped Solid Brass 16-23
Medium Base Interiors, Shells & Accessories 24-25
Assorted Socket Clusters 26-27
Medium Base Phenolic 28-32
Medium Base (Paper Liner) 33
Medium Base Porcelain 34-43
Medium Base Porcelain – 4KV 44-45
Mogul Base Porcelain – 4KV – 6KV 46-49
Specialty Porcelain & Lamps 50-51
Medium Base Receptacles & Bulb Cages 52-53
Medium Base Phenolic Sockets 54-55
Medium Base Phenolic Socket Clusters 56-59
Candelabra Base Phenolic 60-63
Specialty Porcelain/Halogen 64-67
Bayonet & Linear Sockets 68
Sign Receptacles 69
Fluorescent Lamps, Sockets & Ballasts 70-90

Aluminum *Screw Terminals / Push-In Terminals*



80-1000
660W-250V



On-Off Push Thru Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1000	Brite Gilt	Screw	1/8 IPS	Less	No	500
90-410	Brite Gilt	Screw	1/8 IPS	Less	No	250
80-1001	Nickel	Screw	1/8 IPS	Less	No	500
80-1527	Nickel	Screw	1/8 IPS	With	No	250
80-1529	Brite Gilt	Screw	1/8 IPS	With	No	250
90-1408	Brite Gilt	Screw	1/8 IPS	With	Yes	200/10
80-1348	Brite Gilt	Push-In	1/8 IPS	Less	No	500



90-418
660W-250V



On-Off Push Thru Socket w/Side Outlet - For SPT–2

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
90-418	Brite Gilt	Screw w/Sideout Hole	1/8 IPS	Less	No	250
80-1754	Nickel	Screw w/Sideout Hole	1/8 IPS	With	No	250



80-1009
250W-250V



3 Terminal (2 Circuit) Turn Knob Socket



Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1008	Brite Gilt	Screw	1/8 IPS	Less	No	500
90-421	Brite Gilt	Screw	1/8 IPS	Less	No	250
80-1009	Nickel	Screw	1/8 IPS	Less	No	500
80-1501	Brite Gilt	Screw	1/4 IPS	Less	No	250

3 Way (2 Circuit) Turn Knob Socket w/Removable Knob

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1002	Brite Gilt	Screw	1/8 IPS	Less	No	500
90-412	Brite Gilt	Screw	1/8 IPS	Less	No	250
80-1003	Nickel	Screw	1/8 IPS	Less	No	500
80-1004	Brite Gilt	Screw	1/4 IPS	Less	No	500
80-1005	Nickel	Screw	1/4 IPS	Less	No	500
80-1098	Nickel	Screw	1/8 IPS	With	No	250
80-1192	Brite Gilt	Screw	1/8 IPS	With	No	250
90-1410	Brite Gilt	Screw	1/8 IPS	With	Yes	200/10
80-1158	Brite Gilt	Push-In	1/8 IPS	Less	No	500
80-1453	Nickel	Push-In	1/8 IPS	Less	No	500
80-1968	Dark Antique	Screw	1/8 IPS	Less	No	250
80-1969	Dark Antique	Screw	1/8 IPS	With	Yes	250





80-1002
250W-250V

3 Way (2 Circuit) Turn Knob Socket w/Removable Knob & Strain Relief



w/Strain Relief Hooks

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1118	Brite Gilt	Screw	1/8 IPS	Less	No	500
80-1119	Nickel	Screw	1/8 IPS	Less	No	500





80-1119
250W-250V

On-Off Turn Knob Socket w/Removable Knob

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1012	Brite Gilt	Screw	1/8 IPS	Less	No	500
90-413	Brite Gilt	Screw	1/8 IPS	Less	No	250
80-1013	Nickel	Screw	1/8 IPS	Less	No	500
80-1101	Nickel	Screw	1/8 IPS	With	No	250
80-1193	Brite Gilt	Screw	1/8 IPS	With	No	250
90-1411	Brite Gilt	Screw	1/8 IPS	With	Yes	200/10
80-1159	Brite Gilt	Push-In	1/8 IPS	Less	No	500





80-1012
250W-250V

SATCO®

Aluminum *Screw Terminals / Push-In Terminals*

c UL us LISTED



80-1010
660W-250V



Short Keyless Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1010	Brite Gilt	Screw	1/8 IPS	Less	No	500
90-420	Brite Gilt	Screw	1/8 IPS	Less	No	250
80-1011	Nickel	Screw	1/8 IPS	Less	No	500
80-1100	Nickel	Screw	1/8 IPS	With	No	250
80-1194	Brite Gilt	Screw	1/8 IPS	With	No	250
90-1412	Brite Gilt	Screw	1/8 IPS	With	Yes	200/10
80-1981	Nickel	Screw	1/4 IPS	With	No	250



80-1373
660W-250V



Short Keyless Socket w/Side Outlet

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1373	Nickel	Screw w/Sideout Hole	1/8 IPS	Less	No	250
80-1753	Brite Gilt	Screw w/Sideout Hole	1/8 IPS	With	No	250



80-1669
660W-250V



Standard Keyless Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1669	Brite Gilt	Screw	1/8 IPS	Less	No	250
80-1670	Nickel	Screw	1/8 IPS	Less	No	250
80-1218	Brite Gilt	Push-In	1/8 IPS	Less	No	250



80-1021
660W-250V



3 Way (2 Circuit) Keyless Socket



Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1020	Brite Gilt	Screw	1/8 IPS	With	No	500
90-1314	Brite Gilt	Screw	1/8 IPS	With	No	250/10
80-1021	Nickel	Screw	1/8 IPS	With	No	500

c UL us LISTED

On-Off Pull Chain Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1006	Brite Gilt	Screw	1/8 IPS	Less	No	500
90-411	Brite Gilt	Screw	1/8 IPS	Less	No	250
80-1007	Nickel	Screw	1/8 IPS	Less	No	500
80-1099	Nickel	Screw	1/8 IPS	With	No	250
80-1188	Brite Gilt	Screw	1/8 IPS	With	No	500
90-1409	Brite Gilt	Screw	1/8 IPS	With	Yes	200/10





80-1006
660W-250V

3 Position Pull Chain Socket w/Diode
Low - Medium - High - Off
For Standard A Type Household Bulb

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1672	Brite Gilt	Screw	1/8 IPS	With	No	250
90-4310	Brite Gilt	Screw	1/8 IPS	With	No	250
80-1673	Nickel	Screw	1/8 IPS	With	No	250





80-1673
150W-120V

2 Position Pull Chain Socket w/Diode
Hi - Low - Off
For Standard A Type Household Bulb

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1502	Brite Gilt	Screw	1/8 IPS	With	No	250
80-1503	Nickel	Screw	1/8 IPS	With	No	250





80-1502
150W-120V

Aluminum *Screw Terminals*





80-1504
150W-120V

5 Position Turn Knob Socket For Standard Type A Household Bulb

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1504	Brite Gilt	Screw	1/8 IPS	With	No	250
80-1505	Nickel	Screw	1/8 IPS	With	No	250





80-1017
250W-250V

Hi-Low Turn Knob Socket For Standard A Type Household Bulb

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1016	Brite Gilt	Screw	1/8 IPS	With	No	100
80-1017	Nickel	Screw	1/8 IPS	With	No	100





80-1671
250W-250V

On-Off Large Key Socket w/Non Removable Knob

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1671	Brite Gilt	Screw	1/8 IPS	With	No	250

150W Full Range Turn Knob Dimmer Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1014	Brite Gilt	Screw	1/8 IPS	With	No	100
80-1015	Nickel	Screw	1/8 IPS	With	No	100





80-1014
150W-120V



Optional Phenolic Knobs



80-1757 *Brass Plated*

80-1758 *Nickel Plated*



80-2602
Blue Insert for Knobs

200W Full Range Matching Turn Knob Dimmer Socket w/Matching Finish Removable Knob

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1547	Brite Gilt	Screw	1/8 IPS	With	No	100
80-1548	Nickel	Screw	1/8 IPS	With	No	100





80-1548
200W-120V

Special Finishes Available – Call For Information



Satin Brass



Dark Antique

SATCO®

Aluminum *Push-In Terminals / Strain Relief Hooks*

c UL us LISTED



w/Strain Relief Hooks



80-1558
250W-250V

On-Off Turn Knob Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1558	Brite Gilt	Push-In	1/8 IPS	Less	No	250
80-1559	Nickel	Push-In	1/8 IPS	Less	No	250



w/Strain Relief Hooks



80-1566
660W-250V

On-Off Push Thru Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1565	Brite Gilt	Push-In	1/8 IPS	Less	No	250
80-1566	Nickel	Push-In	1/8 IPS	Less	No	250



w/Strain Relief Hooks



80-1562
660W-250V

Short Keyless Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1562	Brite Gilt	Push-In	1/8 IPS	Less	No	250
80-1563	Nickel	Push-In	1/8 IPS	Less	No	250

3 Way Turn Knob Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1560	Brite Gilt	Push-In	1/8 IPS	Less	No	250
80-1561	Nickel	Push-In	1/8 IPS	Less	No	250

w/Strain Relief Hooks





80-1560
250W-250V

"Push-In" Strain Relief Lampholder Wiring Instructions:

1. *Strip SPT-2 #18AWG wire 0.75" & tin the ends 0.413" in length.*
2. *The socket terminals are marked with minus (-) & plus (+). Push the tinned end by hand into the correct terminal.*
   a) Neutral – (ribbed wire) into the minus (-).
   b) Positive – (smooth wire) into the plus (+).
3. *Loop wires under the strain relief hooks.*
4. *If you make a mistake – insert a wire removing pin into the terminal and push down to release the wire.*





Aluminum *Quick Slide Terminals*





80-1543
250W-250V

On-Off Turn Knob Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1543	Brite Gilt	Slide-In	1/8 IPS	Less	No	250
80-1544	Nickel	Slide-In	1/8 IPS	Less	No	250





80-1667
250W-250V

On-Off Push Thru Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1666	Brite Gilt	Slide-In	1/8 IPS	Less	No	250
80-1667	Nickel	Slide-In	1/8 IPS	Less	No	250





80-1545
250W-250V

Short Keyless Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1545	Brite Gilt	Slide-In	1/8 IPS	Less	No	250
80-1546	Nickel	Slide-In	1/8 IPS	Less	No	250

c UL us LISTED

3 Way Turn Knob Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1533	Brite Gilt	Slide-In	1/8 IPS	Less	No	250
80-1542	Nickel	Slide-In	1/8 IPS	Less	No	250





80-1533
250W-250V

"Quick Slide" Wiring Instructions:

1. *Use SPT-2 wire.*
2. *The wire must be "Cut Blunt" on the end.* **(A)**
3. *The socket terminals are marked with minus(-) & plus(+).*
   a) Neutral, (ribbed wire) into the minus(-) side.
   b) Positive, (smooth wire) into the plus(+) side.
4. *Push the blunt wire by hand straight into the socket interior all the way to the end.* **(B)**
   When you push the wire into the connector, the slide bar will slide out automatically, (you may have to push down gently on the slide bar to have the wire go in correctly). **(C)**
5. *Before closing push down on the wire to make good contact with the pins.*
6. *Slide the bar all the way back into place.* **(D)**
7. *No UL knot required.*





PLEASE NOTE: *Only use SPT-2 wire – the wire must be cut blunt.*





3 Piece Stamped Solid Brass *Screw / Push-In Terminals*





80-1022
660W-250V

On-Off Push Thru Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1022	Polished Brass	Screw	1/8 IPS	Less	No	100
80-1023	Polished Nickel	Screw	1/8 IPS	Less	No	100
80-1032	Polished Brass	Screw	1/8 IPS	With	Yes	100
80-1033	Polished Nickel	Screw	1/8 IPS	With	Yes	100
90-870	Polished Brass	Screw	1/8 IPS	With	No	250/10
90-1667	Polished Nickel	Screw	1/8 IPS	With	No	250/10





80-1031
250W-250V

On-Off Turn Knob Socket w/Removable Knob

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1030	Polished Brass	Screw	1/8 IPS	Less	No	100
80-1031	Polished Nickel	Screw	1/8 IPS	Less	No	100
80-1040	Polished Brass	Screw	1/8 IPS	With	Yes	100
80-1041	Polished Nickel	Screw	1/8 IPS	With	Yes	100
80-1179	Polished Brass	Screw	1/8 IPS	With	No	100
90-868	Polished Brass	Screw	1/8 IPS	With	No	250/10
80-1180	Polished Nickel	Screw	1/8 IPS	With	No	100
90-1670	Polished Nickel	Screw	1/8 IPS	With	No	250/10
80-1349	Polished Nickel	Push-In	1/8 IPS	Less	No	100
80-1772	Satin Brass	Screw	1/8 IPS	With	No	100





80-1428
250W-250V

3 Terminal (2 Circuit) Turn Knob Socket w/Removable Knob

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1428	Polished Brass	Screw	1/8 IPS	With	No	100
90-1672	Polished Brass	Screw	1/8 IPS	With	No	250/10
80-1429	Polished Nickel	Screw	1/8 IPS	With	No	100
90-1673	Polished Nickel	Screw	1/8 IPS	With	No	250/10

3 Way (2 Circuit) Turn Knob Socket w/Removable Knob

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1024	Polished Brass	Screw	1/8 IPS	Less	No	100
80-1025	Polished Nickel	Screw	1/8 IPS	Less	No	100
80-1034	Polished Brass	Screw	1/8 IPS	With	Yes	100
80-1035	Polished Nickel	Screw	1/8 IPS	With	Yes	100
80-1190	Polished Brass	Screw	1/8 IPS	With	No	100
90-867	Polished Brass	Screw	1/8 IPS	With	No	250/10
80-1191	Polished Nickel	Screw	1/8 IPS	With	No	100
90-1669	Polished Nickel	Screw	1/8 IPS	With	No	250/10
80-1737	Satin Brass	Screw	1/8 IPS	With	No	100
80-1738	Dark Antique	Screw	1/8 IPS	With	No	100





80-1024
250W-250V

On-Off Pull Chain Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1026	Polished Brass	Screw	1/8 IPS	Less	No	100
80-1027	Polished Nickel	Screw	1/8 IPS	Less	No	100
80-1036	Polished Brass	Screw	1/8 IPS	With	Yes	100
80-1037	Polished Nickel	Screw	1/8 IPS	With	Yes	100
90-869	Polished Brass	Screw	1/8 IPS	With	No	250/10
90-1668	Polished Nickel	Screw	1/8 IPS	With	No	250/10
80-1739	Satin Brass	Screw	1/8 IPS	With	No	100
80-1740	Dark Antique	Screw	1/8 IPS	With	No	100





80-1037
660W-250V

Special Finishes Available – Call For Information



Satin Brass



Dark Antique

SATCO®

3 Piece Stamped Solid Brass *Screw Terminals*

c UL us LISTED



80-1028
660W-250V



Short Keyless Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1028	Polished Brass	Screw	1/8 IPS	Less	No	100
80-1029	Polished Nickel	Screw	1/8 IPS	Less	No	100
80-1038	Polished Brass	Screw	1/8 IPS	With	Yes	100
80-1039	Polished Nickel	Screw	1/8 IPS	With	Yes	100
80-1177	Polished Brass	Screw	1/8 IPS	With	No	100
90-871	Polished Brass	Screw	1/8 IPS	With	No	250/10
80-1178	Polished Nickel	Screw	1/8 IPS	With	No	100
90-1671	Polished Nickel	Screw	1/8 IPS	With	No	250/10



80-1447
660W-250V



Standard Keyless Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1446	Polished Brass	Screw	1/8 IPS	With	Yes	250
80-1447	Polished Nickel	Screw	1/8 IPS	With	Yes	250



80-1175
660W-250V



3 Way (2 Circuit) Keyless Socket



Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1175	Polished Brass	Screw	1/8 IPS	With	No	100
80-1176	Polished Nickel	Screw	1/8 IPS	With	No	100

Hi-Low Turn Knob Socket For Standard A Type Household Bulb

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1462	Polished Brass	Screw	1/8 IPS	With	No	100
80-1463	Polished Nickel	Screw	1/8 IPS	With	No	100





80-1462
250W-250V

150W Full Range Turn Knob Dimmer Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1042	Polished Brass	Screw	1/8 IPS	With	No	100
80-1043	Polished Nickel	Screw	1/8 IPS	With	No	100
80-1044	Polished Brass	Screw	1/8 IPS	With	Yes	100
80-1045	Polished Nickel	Screw	1/8 IPS	With	Yes	100





80-1045
150W-125V

200W Full Range Turn Knob Dimmer Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1695	Polished Brass	Screw	1/8 IPS	With	No	100
80-1696	Polished Nickel	Screw	1/8 IPS	With	No	100





80-1695
250W-120V

4 Piece Stamped Solid Brass *Screw Terminals*





80-1432
660W-250V

On-Off Push Thru Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1432	Polished Brass	Screw	1/8 IPS	With	No	100
80-1433	Polished Nickel	Screw	1/8 IPS	With	No	100





80-1059
250W-250V

On-Off Turn Knob Socket w/Matching Finish Removable Knob

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1058	Polished Brass	Screw	1/8 IPS	With	No	100
80-1059	Polished Nickel	Screw	1/8 IPS	With	No	100
80-1060	Polished Brass	Screw	1/8 IPS	With	Yes	100
80-1061	Polished Nickel	Screw	1/8 IPS	With	Yes	100
80-1062	Polished Brass	Screw	1/4 IPS	With	No	100
80-1063	Polished Nickel	Screw	1/4 IPS	With	No	100
80-1321	Unfinished	Screw	1/8 IPS	With	No	100





80-1430
250W-250V

3 Terminal (2 Circuit) Turn Knob Socket w/Matching Finish Removable Knob

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1430	Polished Brass	Screw	1/8 IPS	With	No	100
80-1431	Polished Nickel	Screw	1/8 IPS	With	No	100

3 Way (2 Circuit) Turn Knob Socket w/Matching Finish Removable Knob

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1046	Polished Brass	Screw	1/8 IPS	With	No	100
80-1047	Polished Nickel	Screw	1/8 IPS	With	No	100
80-1048	Polished Brass	Screw	1/8 IPS	With	Yes	100
80-1049	Polished Nickel	Screw	1/8 IPS	With	Yes	100
80-1050	Polished Brass	Screw	1/4 IPS	With	No	100
80-1051	Polished Nickel	Screw	1/4 IPS	With	No	100
80-1319	Unfinished	Screw	1/8 IPS	With	No	100





80-1046
250W-250V

On-Off Pull Chain Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1052	Polished Brass	Screw	1/8 IPS	With	No	100
80-1053	Polished Nickel	Screw	1/8 IPS	With	No	100
80-1291	Polished Brass	Screw	1/8 IPS	With	Yes	100
80-1292	Polished Nickel	Screw	1/8 IPS	With	Yes	100





80-1053
660W-250V

Special Finishes Available – Call For Information



Satin Brass



Dark Antique

4 Piece Stamped Solid Brass *Screw Terminals*



80-1054
660W-250V



Short Keyless Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1054	Polished Brass	Screw	1/8 IPS	With	No	100
80-1055	Polished Nickel	Screw	1/8 IPS	With	No	100
80-1056	Polished Brass	Screw	1/8 IPS	With	Yes	100
80-1057	Polished Nickel	Screw	1/8 IPS	With	Yes	100
80-1434	Unfinished	Screw	1/8 IPS	With	No	100



80-1196
660W-250V





3 Way (2 Circuit) Keyless Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1195	Polished Brass	Screw	1/8 IPS	With	Yes	100
80-1196	Polished Nickel	Screw	1/8 IPS	With	Yes	100

Stamped Solid Brass Rings



80-1450
Polished Brass Uno Ring



80-1451
Polished Nickel Uno Ring

1/4 IP Stamped Solid Brass Caps



80-1749
1/4 IP Polished Brass with Set Screw



80-1750
1/4 IP Polished Nickel with Set Screw

150W Full Range Turn Knob Dimmer Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1064	Polished Brass	Screw	1/8 IPS	With	No	100
80-1065	Polished Nickel	Screw	1/8 IPS	With	No	100
80-1320	Unfinished	Screw	1/8 IPS	With	No	100
80-1795	Polished Brass	Screw	1/4IPS	With	No	100





80-1064
150W-125V



80-1984 *Polished Nickel*

Extra Knobs



80-1985 *Polished Brass*

150W Full Range Turn Knob Dimmer Socket w/Uno Thread

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1066	Polished Brass	Screw	1/8 IPS	With	Yes	100
80-1067	Polished Nickel	Screw	1/8 IPS	With	Yes	100





80-1067
150W-125V



80-1984 *Polished Nickel*

Extra Knobs



80-1985 *Polished Brass*

200W Full Range Turn Knob Dimmer Socket

Cat. No.	Finish	Terminal	Cap	Set Screw	Uno-Thread	Master
80-1703	Polished Brass	Screw	1/8 IPS	With	No	100
80-1704	Polished Nickel	Screw	1/8 IPS	With	No	100





80-1703
200W-125V

Interior Mechanisms • Accessories

Interior Mechanisms w/Screw Terminals



90-1138
Push Thru
660W-250V



90-1140
3-Way Turn Knob
250W-250V



90-1141
On-Off Turn Knob
250W-250V



90-1143
3 Terminal (2 Circuit) Turn Knob
250W-250V



90-1139 *Brass Chain*
80-1705 *Nickel Chain*
Pull Chain 660W-250V



90-1142
Short Keyless
660W-250V



80-1475
3-Way Keyless
660W-250V



80-1476
Hi-Low Turn Knob
250W-250V



80-1477
150W Full Range Dimmer w/Ivory Knob
& Paper Liner 150W-125V

Socket Key



90-020 *Brass Finish*
4/36

Mandrel Thread – 4/36
Base Socket Key Extenders



90-1657 *1/2"*
90-1658 *5/8"*
90-181 *3/4"*
90-182 *1"*
90-183 *1¼"*

Socket Knob



90-021 *Brown*
4/36

Metal Shells • Caps • Knobs *Aluminum / Solid Brass*

Aluminum Shells & Caps w/Paper Liners



90-1144 Bright Gilt
80-1439 Nickel
Push Thru



90-1145 Bright Gilt
80-1440 Nickel
Pull Chain / Turn Knob



90-1146 Bright Gilt
80-1441 Nickel
Short Keyless



80-1701 Bright Gilt
80-1702 Nickel
1/8 IP Sideout w/Set Screw



80-1419 Bright Gilt
80-1435 Nickel
1/8 IP Sideout Hole Less Set Screw



90-1147 Bright Gilt
80-1215 Nickel
1/8 IP Less Set Screw



80-1242 Bright Gilt
80-1217 Nickel
1/8 IP With Set Screw



80-1210 Bright Gilt
80-1437 Nickel
1/4 IP Less Set Screw



80-1436 Bright Gilt
80-1211 Nickel
1/4 IP With Set Screw

Solid Brass Shells & Caps w/Paper Liners



80-1467 Polished Brass
80-1468 Polished Nickel
Push Thru



80-1442 Polished Brass
80-1351 Polished Nickel
Pull Chain / Turn Knob



80-1471 Polished Brass
80-1472 Polished Nickel
Short Keyless



80-1438 Polished Brass
80-1350 Polished Nickel
1/8 IP Less Set Screw



80-1287 Polished Brass
80-1288 Polished Nickel
1/8 IP With Set Screw



80-1483 Polished Brass
80-1692 Polished Nickel
1/4 IP Less Set Screw



80-1289 Polished Brass
80-1290 Polished Nickel
1/4 IP With Set Screw

Paper Socket Liners

90-2619
Paper Liner for Short Keyless Sockets



90-1777
Paper Liner for Turn Knob & Pull Chain Sockets



Solid Brass Knobs



80-1353 Polished Brass



80-1352 Polished Nickel

Stamped Brass Cluster Bodies • Steel "S" Clusters

Solid Brass Cluster Body



80-1523 Polished Brass
80-1524 Polished Chrome
80-1532 Antique Brass

1/8 IP Nipple & Locknut Top
1/4IP Bottom 250W-250V

3 Light Candelabra Cluster Solid Brass – Unfinished



80-1797 3 Light Candelabra Cluster
1/8 x 1/8 w/ 8 Ft. SPT-2 Gold Wire

Steel "S" Cluster Pull Chain



80-1525 1/8 IP Top, 1/8 IP Bottom
80-1598 1/8 IP Top, 1/4 IP Bottom

Twin Antique Brass
Pull Chain & End Ball
14" 18/2 SPT-2 105° Clear Gold Wire
&18AWM 105° Internal Wire, 7" Centers, 660W-250V

Steel "S" Clusters – No Wiring



80-1161 Unfinished
80-1162 Bright Gilt
80-1636 Nickel

No Wire, 7" Centers
1/8 IP Top and 1/4 IP Bottom

Steel Candelabra "S" Cluster



80-1706 Nickel
80-1707 Bright Gilt
80-1709 Antique Brass

Inside Wiring Only, 6" Centers 1/8 IP Top and Bottom

2 Light Pull Chain Cluster w/Solid Brass Socket

80-1763 Polished Brass
84" SPT-1 Clear Gold Wire
Metal Housing & Pipe

80-1764 Antique Brass
84" SPT-1 Brown Wire
Metal Housing & Pipe

8¾" Height



Steel "S" Clusters



80-1189 Brite Gilt
Twin Keyless
with 14" 18/2 SPT–2 105°C
Clear Gold Wire
Internal Wire–18 AWM 105°C
7" Centers 1/8 IP Top and
1/8 IP Bottom 660W-250V



80-1268 Brite Gilt
Twin Pull Chain
Brite Gilt Chain and End Ball
with 14" 18/2 SPT–2 105°C Clear Gold Wire
Internal Wire–18 AWM 105°C
7" Centers 1/8 IP Top and
1/8 IP Bottom 660W-250V



80-1272 Nickel
Twin Keyless
with 14" 18/2 SPT–2 105°C
Clear Silver Wire
Internal Wire–18 AWM 105°C
7" Centers 1/8 IP Top and
1/8 IP Bottom 660W-250V



80-1270 Nickel
Twin Pull Chain
Nickel Chain and End Ball
with 14" 18/2 SPT–2 105°C Clear Silver Wire
Internal Wire–18 AWM 105°C
7" Centers 1/8 IP Top and
1/8 IP Bottom 660W-250V



80-1271 Satin Nickel
Twin Keyless
with 14" 18/2 SPT–2 105°C
Clear Silver Wire
Internal Wire–18 AWM 105°C
7" Centers 1/8 IP Top and
1/8 IP Bottom 660W-250V



80-1269 Satin Nickel
Twin Pull Chain
Satin Nickel Chain and
End Ball with 14" 18/2 SPT–2 105°C
Clear Silver Wire
7" Centers 1/8 IP Top and
1/8 IP Bottom 660W-250V

Phenolic • Smooth



80-1110
Push–Thru
1/8 IP Cap w/Metal Bushing Less Set Screw
660W-250V



80-1108 *Brass On–Off Pull Chain*
80-1637 *Nickel On–Off Pull Chain*
1/8 IP Cap w/Metal Bushing Less Set Screw
660W-250V



80-1109 *1/8 IP Cap*
80-1927 *1/4 IP Cap*
3–Way Turn Knob w/Metal Bushing Less Set Screw
250W-250V



80-1112
On–Off Turn Knob
1/8 IP Cap w/Metal Bushing Less Set Screw
250W-250V



80-1111 *Short Keyless–Less Set Screw*
90-458 *Short Keyless–With Set Screw*
1/8 IP Cap w/Plastic Bushing
660W-250V



80-1638 *Brass 3–Way Pull Chain*
80-1639 *Nickel 3–Way Pull Chain*
1/8 IP Cap w/Metal Bushing Less Set Screw
250W-250V



80-1266
3 Terminal 2 Circuit Turn Knob
1/8 IP Cap w/Metal Bushing Less Set Screw
250W-250V



80-1641
1/8 IP CAP ONLY
w/Metal Bushing Less Set Screw
for Turn Knob &
Pull Chain Sockets



80-1267
1/4 IP CAP ONLY
w/Metal Bushing Less Set Screw
for Turn Knob &
Pull Chain Sockets



80-1265
3-Way Turn Knob
1/8 IP Cap w/Metal Bushing Less Set Screw
250W-250V



80-1070
On-Off Turn Knob
1/8 IP Cap w/Metal Bushing Less Set Screw
250W-250V



80-1069
3 Terminal 2 Circuit Turn Knob
1/8 IP Cap with Metal Bushing
250W-250V



80-1072
Short Keyless-Less Set Screw
1/8 IP Cap w/Plastic Bushing Less Set Screw
660W-250V



80-1071
Push-Thru
1/8 IP Cap w/Metal Bushing Less Set Screw
660W-250V



80-1068 *Brass On-Off Metal Pull Chain*
80-1640 *Nickel On-Off Metal Pull Chain*
1/8 IP Cap w/Metal Bushing Less Set Screw
660W-250V



80-1759
3 Terminal 2 Circuit Keyless
1/8 IP Cap w/Set Screw & Plastic Bushing
660W-250V



80-1389
Uno Ring

MEDIUM BASE SOCKETS

Phenolic • 1/2 Uno Thread



80-1104
3–Way Turn Knob
1/8 IP Cap
w/Metal Bushing Less Set Screw
250W-250V



80-1105
Brass On–Off Pull Chain
1/8 IP Cap
w/Metal Bushing Less Set Screw
660W-250V



80-1106
Push–Thru
1/8 IP Cap
w/Metal Bushing Less Set Screw
660W-250V



80-1107
3 Terminal – 2 Circuit Turn Knob
1/8 IP Cap
w/Metal Bushing Less Set Screw
250W-250V



80-1389
Uno Ring

Smooth Phenolic (3 Piece)



80-2061
Keyless
1/8 IP Cap
w/Set Screw
660W-250V



80-2062
On-Off Turn Knob
1/8 IP Cap
w/Set Screw
660W-250V



80-2063
3–Way Turn Knob
1/8 IP Cap
w/Set Screw
660W-250V



80-2070
Push Thru
1/8 IP Cap
w/Set Screw
660W-250V

With Uno Thread & Ring (4 Piece)



80-2067
Keyless
1/8 IP Cap
w/Set Screw
660W-250V



80-2068
On-Off Turn Knob
1/8 IP Cap
w/Set Screw
660W-250V



80-2069
3–Way Turn Knob
1/8 IP Cap
w/Set Screw
660W-250V



80-2071
Push Thru
1/8 IP Cap
w/Set Screw
660W-250V



GU24 Connection



Push-in Quick Terminals

GU24 MEDIUM BASE SOCKETS

Phenolic *Pre-Wired 60" Leads*

Smooth Phenolic (3 Piece)



80-2064
Keyless
1/8 IP Cap
60" 18/2 SPT-1 105° Clear Silver Wire
Strip 3/4" Slit 1½"
660W-250V



80-2065
On-Off Turn Knob
1/8 IP Cap
60" 18/2 SPT-1 105° Clear Silver Wire
Strip 3/4" Slit 1½"
660W-250V



80-2066
3-Way Turn Knob
1/8 IP Cap
60" 18/2 SPT-1 105° Clear Silver Wire
Strip 3/4" Slit 1½"
660W-250V



80-2072
Push-Thru
1/8 IP Cap
60" 18/2 SPT-1 105° Clear Silver Wire
Strip 3/4" Slit 1½"
660W-250V



GU24 Connection



90-1153

2"
Three Way Turn Knob
Screw Terminals
1/8 IP Inside Extrusion
with Paper Liner
250W–250V



80-2034

2½"
2 Circuit 3 Terminal
Turn Knob
1/8 IP Inside Extrusion
with Paper Liner
250W–250V



90-1152

2"
On–Off Turn Knob
Screw Terminals
1/8 IP Inside Extrusion
with Paper Liner
250W–250V



90-424

4" to 5½" Adjustable
On–Off Turn Knob
Screw Terminals
with Paper Liner
1/8 IP Inside Extrusion
250W–250V



90-405

2" Keyless
Screw Terminals – 1/8IP
with Paper Liner
660W–250V



80-1337

3" Keyless
Screw Terminals – 1/8IP
with Paper Liner
660W–250V



90-404

4" to 5½" Keyless – 1/8IP
Screw Terminals
with Paper Liner
660W–250V

SATCO®

Porcelain *Screw Terminals*

c UL us LISTED



80-1214
Glazed 660W-250V



Keyless Porcelain Socket w/Metal 1/8 IP Cap

Cat. No.	Terminal	Cap	Screw Shell	Master
80-1214	Screw	Metal - 1/8 IPS	CSSNP	200 Bulk
90-409	Screw	Metal - 1/8 IPS	CSSNP	200/10



80-2047
Glazed 660W-250V



Keyless Porcelain Socket w/2 Wireways & Metal 1/8 IP Cap

Cat. No.	Terminal	Cap	Screw Shell	Master
80-2047	Screw	Metal - 1/8 IPS	CSSNP	200/10



80-1150
Unglazed 660W-250V



Keyless Porcelain Socket w/Phenolic 1/8 IP Cap

Cat. No.	Terminal	Cap	Screw Shell	Master
80-1150	Screw	Phenolic - 1/8 IPS	CSSNP	200
90-417	Screw	Phenolic - 1/8 IPS	CSSNP	200 Bulk



80-1078
Glazed 660W-250V



Keyless Porcelain Socket w/Metal 1/4 IP Cap

Cat. No.	Terminal	Cap	Screw Shell	Master
80-1078	Screw	Metal - 1/4 IPS	CSSNP	200 Bulk
90-1706	Screw	Metal - 1/4 IPS	CSSNP	200/10



90-1707
Glazed 660W-250V



Keyless 3 Terminal Grounded Porcelain Socket w/Metal Cap

Cat. No.	Terminal	Cap	Screw Shell	Master
90-1707	3 - Screw	Metal - 1/8 IPS	CSSNP	200/10
80-1318	3 - Screw	Metal - 1/4 IPS	CSSNP	200/10

Metal Caps with Set Screw



80-1677
1/8 IP



80-1678
1/4 IP

c UL us LISTED

Porcelain Socket w/Hickey

Cat. No.	Terminal	Hickey	Screw Shell	Master
90-419	Screw	1/8 IPS	Aluminum	200/10
80-2089	Screw	1/4 IPS	Aluminum	200/10
80-2120	Screw	1/8 IPS	CSSNP(Glazed)	200/10





90-419
Unglazed 660W-250V

Porcelain Socket w/Side Outlet & Bushing

Cat. No.	Terminal	Bushing	Screw Shell	Master
80-1083	Screw	1/8 IPS	CSSNP	200 Bulk
90-1108	Screw	1/8 IPS	CSSNP	200/10





80-1083
Glazed 660W-250V

Porcelain Socket w/L Bracket

Cat. No.	Terminal	Bracket	Screw Shell	Master
80-1925	Screw	L Bracket w/ 8/32 Hole	CSSNP	200/10





80-1925
Unglazed 660W-250V

Keyless Porcelain One Piece Sign Socket

Cat. No.	Terminal	Flange / Bushing	Screw Shell	Master
80-1097	Screw	Top (shown) / 2 #8-32	CSSNP	100 Bulk
80-1149	Screw	Center / 2 #8-32	CSSNP	200/10





80-1097
Glazed 660W-250V

Keyless Threaded Porcelain w/ Cap & Ring

Cat. No.	Terminal	Cap	Screw Shell	Master
80-1073	Screw	1/8 IPS	CSSNP	200 Bulk
80-1075	Screw	1/4 IPS	CSSNP	200/10
90-1074	Screw	1/8 IPS	CSSNP	200/10





80-1073
Glazed 660W-250V

Metal Rings



80-1076
Metal Ring for Threaded Socket



80-1074
White Die Cast Ring for Threaded Socket

SATCO®

Porcelain *Screw Terminals*

c UL us LISTED



80-1679
Glazed 660W-250V



Keyless Threaded Porcelain Socket w/Hickey & Ring

Cat. No.	Terminal	Hickey	Screw Shell	Master
80-1679	Screw	1/8 IPS	CSSNP	200/10



80-2032
Unglazed 660W-250V



Keyless Porcelain 1 Piece Shallow Back Socket

Cat. No.	Terminal	Clip	Screw Shell	Master
80-2032	Screw	Double	CSSNP	100/10



80-1680
Glazed 660W-250V



Keyless Porcelain 1 Piece Shallow Back Socket

Cat. No.	Terminal	Clip	Screw Shell	Master
80-1680	Screw	Double	CSSNP	100/10



80-1682
Glazed 660W-250V



Keyless Porcelain Beaded Body Socket w/Flange

Cat. No.	Terminal	Cap	Screw Shell	Master
80-1682	Screw	1/8 IPS	CSSNP	200/10

Porcelain *Screw Terminals*

c UL us LISTED



Twin Porcelain Socket w/Flange Bushing Cap

Cat. No.	Terminal	Cap	Screw Shell	Master
90-1109	Screw	1/8 IPS	CSSNP	100/10
80-1225	Screw	1/8 IPS	CSSNP	100 Bulk



90-1109
Glazed 660W-250V



Twin Porcelain Socket w/Single Bushing Strap

Cat. No.	Terminal	Bushing	Screw Shell	Master
90-1110	Screw	1/8 IPS	CSSNP	100/10
80-1226	Screw	1/8 IPS	CSSNP	100 Bulk



90-1110
Glazed 660W-250V



Twin Porcelain Socket w/Double Bushing Strap

Cat. No.	Terminal	Bushing	Screw Shell	Master
90-1708	Screw	1/8 IPS	CSSNP	100/10
80-1080	Screw	1/8 IPS	CSSNP	100 Bulk



90-1708
Glazed 660W-250V



Porcelain Bottom Turn Knob Socket

Cat. No.	Terminal	Switch	Screw Shell	Master
80-1157	Screw	Turn Knob	CSSNP	100/10



80-1157
Unglazed 250W-250V

SATCO®

Porcelain *Pre-Wired*

c UL us LISTED



90-1107
Unglazed 660W-250V



Keyless Porcelain Socket w/Double Snap-in Clip

Cat. No.	Leads	Clips	Screw Shell	Master
90-1107	8½" AWM B/W 105°	Double	CSSNP	100/10



80-1691
Unglazed 660W-250V



Keyless Porcelain Socket w/Double Snap-in Clip High Temperature Leads

Cat. No.	Leads	Clips	Screw Shell	Master
80-1691	9½" SF-1 B/W 200°	Double	CSSNP	200/10



80-1531
Unglazed 660W-250V



Keyless Porcelain Socket w/Front Rim & Double Snap-in Clip

Cat. No.	Leads	Clips	Screw Shell	Master
80-1531	8" AWM B/W 105°	Double	CSSNP	100/10



80-1212
Unglazed 660W-250V



Keyless Porcelain Socket w/Adapter & Double Snap-in Clip

Cat. No.	Leads	Clips	Screw Shell	Master
80-1212	10" AWM B/W 150°	Double	CSSNP	100 Bulk



80-1263
Unglazed 660W-250V



Keyless Porcelain Socket w/Rim & Double Snap-in Clip

Cat. No.	Leads	Clips	Screw Shell	Master
80-1263	28" AWM B/W 150°	Double	CSSNP	200 Bulk

c UL us LISTED

Keyless Porcelain Socket – Unglazed

Cat. No.	Leads	Mount	Screw Shell	Master
80-1155	8½" AWM B/W 105°	Bushing	Bronze	200 Bulk





80-1155
Unglazed 660W-250V

Keyless Porcelain Socket – Glazed

Cat. No.	Leads	Mount	Screw Shell	Master
90-2621	9" AWM B/W 105°	2-6/32 Screws	CSSNP	200 Bulk

Keyless Porcelain Socket 1/4 IP Cap w/Set Screw

Cat. No.	Leads	Cap	Screw Shell	Master
80-1113	20" AWM B/W 150° w/grd.	1/4 IPS	CSSNP	200 Bulk





80-1113
Glazed 660W-250V

Keyless Porcelain Socket 1/8 IP Cap w/Set Screw

Cat. No.	Leads	Cap	Screw Shell	Master
80-1202	61" AWM B/W 150° w/grd.	1/8 IPS	CSSNP	100 Bulk





80-1202
Unglazed 660W-250V

Keyless Porcelain Socket w/Black Rim & Hickey

Cat. No.	Leads	Hickey	Screw Shell	Master
80-1685	9" AWM B/W 105°	1/8 IPS	CSSNP	200/10





80-1685
Unglazed 660W-250V

Keyless Porcelain Socket w/Hickey & Nipple

Cat. No.	Leads	Hickey	Screw Shell	Master
80-1708	24" AWM B/W 125°	1/2" Hickey & 1/8 IPS Nipple 3/8" Long	Aluminum	200 Bulk





80-1708
Unglazed 660W-250V

SATCO®

Porcelain *Pre-Wired*

c UL us LISTED



80-1317
Glazed 660W-250V



Keyless Porcelain Socket w/Hickey

Cat. No.	Leads	Hickey	Screw Shell	Master
80-1317	72" SPT-1 105° Gold w/grd.	1/8 IPS-3/8"	CSSNP	100/10



80-1223
Unglazed 660W-250V



Keyless Porcelain Socket w/Hickey

Cat. No.	Leads	Hickey	Screw Shell	Master
80-1223	18" AWM B/W 150°	1/8 IPS-1/2"	CSSNP	200 Bulk



80-1224
Unglazed 660W-250V



Keyless Porcelain Socket w/Hickey

Cat. No.	Leads	Hickey	Screw Shell	Master
80-1224	18" AWM B/W 150°	1/8 IPS- 1½"	Aluminum	200 Bulk



80-1768
Glazed 660W-250V



Keyless Threaded Porcelain Socket w/Hickey & Ring

Cat. No.	Leads	Hickey	Screw Shell	Master
80-1768	26" AWM B/W 125°	1/8 IPS-1/2"	CSSNP	100/1

c UL us LISTED

Keyless Porcelain Socket w/Snap-in Clip

Cat. No.	Leads	Clip	Screw Shell	Master
80-1220	12" AWM B/W 150°	Extends 1" from Socket	Aluminum	200 Bulk
80-2128	12" AWM B/W 150° w/Grd. Wire	Extends 1" from Socket	CSSNP(Glazed)	200 Bulk



80-1220
Unglazed 660W-250V

Keyless Porcelain Socket w/Snap-in Double Spring Clip

Cat. No.	Leads	Clip	Screw Shell	Master
80-1956	12" AWM B/W 150°	Extends 1" from Socket	CSSNP	100/10



80-1956
Unglazed 660W-250V

Keyless Porcelain Socket w/Snap-in Clip

Cat. No.	Leads	Clip	Screw Shell	Master
80-1221	12" AWM B/W 150°	Extends 1/2" from Socket	Aluminum	200 Bulk



80-1221
Unglazed 660W-250V

Keyless Porcelain Socket w/Snap-in Clip

Cat. No.	Leads	Clip	Screw Shell	Master
80-1222	12" AWM B/W 150°	Extends 3/8" from Socket	Aluminum	200 Bulk
80-2652	12" AWM B/W 150°	Extends 3/8" from Socket	Aluminum	200 Bulk



80-1222
Unglazed 660W-250V

Keyless Porcelain Socket w/Snap-in Clip

Cat. No.	Leads	Clip	Screw Shell	Master
80-1328	9" AWM B/W 150°	Extends 3/4" from Socket	CSSNP	200 Bulk



80-1328
Unglazed 660W-250V

SATCO®

Porcelain *Pre-Wired*

c UL us LISTED



90-760
Unglazed 660W-250V



Keyless Porcelain Socket w/Hickey

Cat. No.	Leads	Hickey	Screw Shell	Master
90-760	10" AWM 105°	1/8 IPS - PTH	Aluminum	200/10
90-466	16" AWM 105°	1/8 IPS - PTH	Aluminum	200/10
90-759	24" AWM 105°	1/8 IPS - PTH	Aluminum	200/10
80-2182	20" AWM 125°	1/8 IPS - PTH	Aluminum	200 Bulk
80-2041	36" AWM 125°	1/8 IPS - PTH	CSSNP	100 Bulk
80-2042	48" AWM 125°	1/8 IPS - PTH	CSSNP	100 Bulk



90-1563
Unglazed 660W-250V



Keyless Porcelain Socket w/Hickey, Strain Relief & Fiber Sleeving

Cat. No.	Leads	Hickey	Screw Shell	Master
90-1563	8 Ft. 18/3 SVT-1 White 105°	1/8 IPS U Bracket	Aluminum	50 Bulk
90-1564	8 Ft. 18/3 SVT-1 Black 105°	1/8 IPS U Bracket	Aluminum	50 Bulk



80-1313
Glazed 660W-250V



Keyless Porcelain Socket w/Cap

Cat. No.	Leads	Cap	Screw Shell	Master
80-1313	9" AWM 150°	1/8 IPS	CSSNP	100/10
80-1315	24" AWM 150°	1/8 IPS	CSSNP	100/10
80-1278	30" AWM 105°	1/8 IPS	CSSNP	200 Bulk
80-1316	36" AWM 150°	1/8 IPS	CSSNP	100/10



90-1150
Glazed 660W-250V



Keyless Porcelain Socket w/Cap & Nipple

Cat. No.	Leads	Cap	Screw Shell	Master
90-1150	48" 18/2 SPT-1 Gold 105° w/Grd. Wire	1¼" Nipple – 1/8 IPS	CSSNP	100 Bulk

c UL us LISTED

Porcelain Socket w/Side Mount Bushing



Cat. No.	Leads	Cap	Screw Shell	Master
80-1330	9" AWM 150°	1/8 IPS	CSSNP	100/10
80-1445	12" AWM 105°	1/8 IPS	CSSNP	200/10



80-1330
Glazed 660W-250V

Twin Porcelain Socket w/Flange Bushing Cap



Cat. No.	Leads	Cap	Screw Shell	Master
80-1314	9" AWM 150°	1/8 IPS	CSSNP	100/10



80-1314
Glazed 660W-250V

Twin 2 Circuit Porcelain Socket w/Single Bushing Cap



Cat. No.	Leads	Cap	Screw Shell	Master
80-1081	24" (3 leads) AWM 150°	1/8 IPS	CSSNP	100 Bulk



80-1081
Glazed 660W-250V

Three Light Porcelain Socket w/ 1/8 IP Metal Strap



Cat. No.	Leads	Cap	Screw Shell	Master
80-1082	24" AWM 150°	1/8 IPS Strap	Aluminum	100 Bulk



80-1082
Glazed 660W-250V

SATCO®

Porcelain *4KV Pulse Rated w/Screw Terminals*

4KV

c UL us LISTED



80-1647
Unglazed 660W-600V



Keyless Threaded Porcelain Socket w/ Cap & Ring

Cat. No.	Terminal	Cap	Screw Shell	Master
80-1647	Screw	1/8 IPS	CSSNP	100/1



80-1870
Glazed 660W-600V



Keyless Smooth Porcelain Socket w/Terminal Screws

Cat. No.	Terminal	Cap	Screw Shell	Master
80-1870	Screw	1/8 IPS	CSSNP	100/10



80-1681
Glazed 660W-250V



Keyless Porcelain Socket w/Spring Center Contact & Reinforced Screw Shell w/Washers (w/2 6-32 Screws)

Cat. No.	Terminal	Cap	Screw Shell	Master
80-1681	Screw	No	CSSNP	100/10



80-1793
Glazed 660W-600V



Keyless Two-Piece Heavy Duty Porcelain Socket w/Mounting Screws Assembled 1 ½" on Center

Cat. No.	Terminal	Cord Hole	Screw Shell	Master
80-1793	Screw	3/4" (in cap)	CSSNP	100/10

Metal Rings for Threaded Socket



80-1076
Metal Ring



80-1074
White Die Cast Ring

Metal Caps with Set Screw



80-1677
1/8 IP



80-1678
1/4 IP

c UL us LISTED

4KV

Porcelain 4KV Pulse Rated Pre-Wired w/1/2"Strip

Keyless Porcelain Socket
1/8 IP Cap w/Side Notches, 2 Wireways

Cat. No.	Leads	Cap	Screw Shell	Master
80-1614	18" 18GA SF-2 B/W 200°	1/8 IPS	CSSNP	100/10
80-2092	36" 18GA SF-2 B/W 200°	1/8 IPS	CSSNP	100/1





80-1614
Glazed 660W-600V

Keyless Porcelain Socket w/Paper Liner
Mounting Screws Held Captive, 2 Wireways

Cat. No.	Leads	Cap	Screw Shell	Master
80-1689	18" 18GA SF-2 B/W 200°	Less	CSSNP	100/10
80-1700	36" 18GA SF-2 B/W 200°	Less	CSSNP	100/10





80-1689
Glazed 660W-600V

Keyless Porcelain Socket w/Paper Liner
2 Bushings, 2 Wireways

Cat. No.	Leads	Cap	Screw Shell	Master
80-1734	9" 18GA SF-2 B/W 200°	Less	CSSNP	100/10
80-1875	48" 18GA SF-2 B/W 200°	Less	CSSNP	100/10





80-1734
Glazed 660W-600V

Keyless Porcelain Snap-in Socket

Cat. No.	Leads	Clips	Screw Shell	Master
80-1674	9" 18GA SF-2 B/W 200°	Double	CSSNP	200/10





80-1674
Unglazed 660W-600V

4KV

Lampholders rated at high wattage that require a pulse rating of 4KV (kilovolts) to start.



Porcelain *4KV Pulse Rated E39 Base w/Screw Terminals*



90-429
Glazed 1500W-600V



Keyless Porcelain Mogul Socket w/Metal 1/4 IP Cap

Cat. No.	Terminal	Cap	Screw Shell	Master
90-429	Screw	1/4 IPS	CSSNP	50/1



80-1378
Glazed 1500W-600V



Keyless Porcelain Mogul Socket w/Metal 1/4 IP Cap, 2 Wireways

Cat. No.	Terminal	Cap	Screw Shell	Master
80-1378	Screw	1/4 IPS	CSSNP	50/1



80-1307
Glazed 1500W-600V



Keyless Porcelain Mogul Socket w/Metal 1/4 IP Cap, 3 Terminal

Cat. No.	Terminal	Cap	Screw Shell	Master
80-1307	3 - Screw	1/4 IPS	CSSNP	50/1

Metal Caps with Set Screw



80-1631
1/4 IP



80-1665
3/8 IP

Lampholders rated at high wattage that require a pulse rating of 4KV (kilovolts) to start.



c UL us LISTED

4KV

Porcelain 4KV Pulse Rated E39 Base Pre-Wired

Keyless Porcelain Mogul Socket, Mounting Screws Held Captive, 2 Wireways, 1/2" Strip Leads

Cat. No.	Leads	Cap	Screw Shell	Master
80-1376	10" 16GA SF-2 B/W 200°	Less	CSSNP	50/1
80-2093	24" 16GA SF-2 B/W 200°	Less	CSSNP	50/1





80-1376
Glazed 1500W-600V

Keyless Porcelain Mogul Socket w/Metal 1/4 IP Cap, 2 Wireways

Cat. No.	Leads	Cap	Screw Shell	Master
80-1613	11" 16GA SF-2 B/W 200°	1/4 IPS	CSSNP	50/1





80-1613
Glazed 1500W-600V

Keyless Porcelain Mogul Socket, Fiber Gasket Mounting Screws Held Captive, 2 Wireways, Lug Leads

Cat. No.	Leads	Cap	Screw Shell	Master
80-1103	40" 16GA SF-2 B/W 200°	Fiber, Less Cap	CSSNP	50/1





80-1103
Glazed 1500W-600V

Keyless Porcelain Mogul Socket 2 Bushings 8/32, 2 Wireways, 1/2" Strip Leads

Cat. No.	Leads	Cap	Screw Shell	Master
80-1751	10" 14GA SF-2 B/W 200°	Less	CSSNP	50/1





80-1751
Glazed 1500W-600V

SATCO®

Porcelain 4-5KV Pulse Rated E39 Base Pre-Wired

c UL us LISTED



80-1791
PINK Glazed 1500W-600V



4KV

Keyless Pink Porcelain Mogul Socket for Open HID Fixtures, Mounting Screws Held Captive, 1/2" Strip Leads, 2 Wireways

Cat. No.	Leads	Cap	Screw Shell	Master
80-1791	11" 16GA SF-2 B/W 200°	Less	CSSNP	50/1



80-2090
YELLOW Glazed 1500W-600V



4KV

Keyless Porcelain Mogul Socket, for Position Oriented HID Fixtures w/Body Notch for Correct Mounting, 2 Wireways

Cat. No.	Leads	Cap	Screw Shell	Master
80-2090	12" 14GA SF-2 B/W 200°	Less	CSSNP	50/1



80-1530
Glazed 1500W-600V



5KV

Keyless Porcelain Mogul Socket, Mounting Screws Held Captive, 2 Wireways, 1/2" Strip Leads

Cat. No.	Leads	Cap	Screw Shell	Master
80-1530	30" 16GA SF-2 B/W 200°	Less	CSSNP	50/1

Metal Caps with Set Screw



80-1631
1/4 IP



80-1665
3/8 IP

5KV

Keyless Porcelain Mogul Socket, Mounting Screws Held Captive, 2 Wireways, 1/2" Strip Leads

Cat. No.	Leads	Cap	Screw Shell	Master
80-1377	16" 18GA SF-2 B/W 200°	Less	CSSNP 2 #8/32 Screws	50/1
80-2030	16" 14GA SF-2 B/W 200°	Less	CSSNP 2 #8/32 Screws	50/1
80-2031	16" 14GA SF-2 B/W 200°	Less	CSSNP 2 #8/32 Bushings	50/1





80-1377
Glazed 1500W-600V

5KV

Keyless Porcelain Mogul Socket Mounting Screws Held Captive, 1/2" Strip Leads

Cat. No.	Leads	Cap	Screw Shell	Master
80-1646	21" 14GA SF-2 B/W 200°	Less	CSSNP	50/1





80-1646
Glazed 1500W-600V

6KV

Keyless Porcelain Mogul Socket w/Lamp Grip Mounting Screws Held Captive, 2 Wireways, 1/2" Strip Leads

Cat. No.	Leads	Cap	Screw Shell	Master
80-2091	12" 14GA SF-2 B/W 200°	Less	CSSNP	50/1





80-2091
Glazed 1500W-600V

4KV 5KV 6KV

Lampholders rated at high wattage that require a pulse rating of 4-6KV (kilovolts) to start.



SATCO®

Bayonet, Medium & Mogul Base

c UL us LISTED



80-2035
Unglazed 660W-1000V

Keyless Low Pressure Sodium Surface Mount Porcelain Socket w/Single-End Bayonet Base

Cat. No.	Leads	Cap	Screw Shell	Master
80-2035	9" 16GA SF-1 B/W 150°	Less (surface mount)	CSSNP	50/1





80-1120
Unglazed 660W-250V

Keyless Medium Base Surface Mount Porcelain Socket w/2 Bushings

Cat. No.	Terminal	Cap	Screw Shell	Master
80-1120	Screw	Less (surface mount)	CSSNP	150





90-428
Unglazed 750W-250V

Porcelain 3-Way Turn Knob Mogul Socket w/Hickey

Cat. No.	Terminal	Hickey	Screw Shell	Master
90-428	Screw	1/4 IPS	CSSNP	50/1

Available Lamps



S4870
18W
Low Pressure Sodium
Bayonet (BY22D) Base



S1822
100/200/300W
3-Way
Mogul Base



S5862
175W
Metal Halide
Medium Base



S5831
250W
Metal Halide
Mogul Base

Medium & Mogul Base

c UL us LISTED

Porcelain Par 46 & 38 Connector – Medium Base HID

Cat. No.	Leads	Type	Porcelain	Master
80-1690	18"	16GA SF-2 200°	Unglazed	200/10



80-1690
6600W-125V

Porcelain Par 46 & 38 5KV Harness Set w/Medium Base Adapter

Cat. No.	Leads	Type	Porcelain	Master
80-1769	10"	18GA SF-1 200°	Unglazed	100/1



80-1769
660W-125V

Porcelain Par 56 & 64 Connector – Mogul Base

Cat. No.	Leads	Type	Porcelain	Master
80-1865	18"	14GA SEW 200°	Unglazed	100



80-1865
1000W-125V

Available Lamps



S1934
175W
Mercury Vapor
Mogul Base



S3127
70W
HPS – High Pressure Sodium
Mogul Base



S1940
250W
HPS – High Pressure Sodium
Mogul Base

Porcelain

c UL us LISTED



90-445 2 Terminal
80-1648 4 Terminal
90-2638 7" AWM B/W Leads 105°C
Keyless Glazed Porcelain
Ceiling Receptacle
Screw Terminals
660W-250V



90-443 2 Terminal
90-2638 7" AWM B/W Leads 105°C
Glazed Porcelain
On-Off Pull Chain Ceiling Receptacle
Screw Terminals
250W-250V



90-444
Glazed Porcelain
Ceiling Receptacle
On-Off Pull Chain w/Grounded
Convenience Outlet
Screw Terminals
15A-250W-125V

See Page 77 for
GU24 Base Receptacles

90-1310
Brass Finish
Light Bulb Cage
Height: 5¼"
Packing: 60/Master 10/Inner



90-2612
Yellow Trouble Light
Plastic Cage Suitable
for Outdoor Locations
Height: 6½"
Packing: 12/Master



Phenolic

c UL us LISTED



90-480 *4 Terminal*
Keyless White Phenolic
Ceiling Receptacle
Screw Terminals
660W-250V



90-481 *4 Terminal*
White Phenolic
On-Off Pull-Chain Ceiling Receptacle
Screw Terminals
250W–250V

Phenolic Receptacles with Leads



90-1502
Keyless White Phenolic
Ceiling Receptacle
6" AWM B/W Leads 105°C
660W-250V



90-1503
White Phenolic
On-Off Pull-Chain Ceiling Receptacle
6" AWM B/W Leads 105°C
250W–250V

SATCO®

Phenolic Lampholders

c UL us LISTED

Keyless Lampholders



90-407
1/8 IP Hickey
Screw Terminals
660W-250V



90-1151 10"
80-2095 24"
80-2096 36"
AWM B/W Leads 105°C
1/8 IP Hickey
660W-250V



80-1077
Threaded Socket w/Ring
1/8 IP Hickey
Screw Terminals
660W-250V



80-1762
Medium Base Pin Socket
Pressure Fit w/ Metal Clip
CSSNP
660W-250V



80-2080
Medium Base
Pressure Fit w/Hook
Suited for 14GA Wire
CSSNP
660W-250V

Special Orders for Additional Hickey & Bushing Combination



"Z" Bracket Inside Extrusion



"C" Bracket Inside Extrusion



Bushing Bracket Outside



"Z" Bracket Outside Extrusion

Keyless Lampholder



80-2036
Medium Base w/Rim
1/8 IP Hickey
12" AWM B/W105°C
Leads & Ground Wire
660W-250V

Phenolic Bottom Turn Knob Sockets



90-1782
2¼" Bottom Turn Knob
13" AWM B/W
105°C Leads
250W-250V



80-1755
2½" Bottom Turn Knob
Phenolic & Porcelain Shell
Screw Terminals 1/8 IP
2½" Ht. w/ 3/8" Bushing
660W-250V



90-4300
Bottom Turn Knob
Screw Terminals 1/8 IP
2½" Ht. w/ 3/8" Bushing
250W-250V



80-1326
Bottom Turn Knob
w/Removable Husk
Screw Terminals 1/8 IP
2" Ht. w/ 3/8" Bushing
250W-250V

c UL us LISTED

Keyless Lampholders – Snap-In



90-540 *Snap-In Socket*
6" AWM
B/W Leads
105°C
660W-250V



90-595 *Snap-In Socket*
Bracket Extends 3/4" from End of Socket
7" AWM
B/W Leads 105°C
660W-250V



90-543 *Snap-In Socket*
for 6" Pans Bracket Extends 1" from End of Socket
8" AWM
B/W Leads 105°C
660W-250V



90-542 *Snap-In Socket*
for 8" & 10" Pans Bracket Extends 1¾" from End of Socket
8" AWM
B/W Leads 105°C
660W-250V

Special Orders for Additional Snap Brackets



Vertical



Horizontal



Angled

Keyless Lampholders – "U" Clip Snap-In



90-541 *8" AWM Leads*
80-1798 *12" AWM Leads*
Snap-In Socket
for 3¼"–4" Holders
B/W Leads 105°C
660W-250V



80-1645
Snap-In Socket
for 3¼"–4" Holders
12" AWM
B/W Leads 125°C
660W-250V



80-1642
Snap-In Double Spring Clip
w/ 12" B/W Leads 150°C
660W-250V



80-1766
Snap-In Double with Flange Rim
13" B/W Leads
660W-250V

Phenolic *Twin Cluster*

c UL us LISTED

PLEASE NOTE: *Socket Cluster measurements are from the center line to the top & bottom of brackets.*



90-432

- *Snap–On Top*
- *2⅜" Top Bracket + Snap*
- *1¾" 1/8 IP Threaded Bottom Bracket with 3/8" Nipple*
- *8" AWM B/W Leads 105°C*
- *660W–250V*



80-1379

- *Snap–On Top*
- *2⅜" Top Bracket + Snap*
- *1¾" 1/8 IP Threaded Bottom Bracket with 1/2" Nipple*
- *8" AWM B/W Leads 105°C w/Ground Wire*
- *660W–250V*



90-465

- *1½" 1/8 IP Threaded Top Bracket with 3/8" Nipple*
- *2⅛" 1/8 IP Threaded Bottom Bracket with 1/2" Nipple*
- *8" AWM B/W Leads 105°C*
- *660W–250V*



80-1380

- *1¾" 1/8 IP Threaded Top Bracket with 1/2" Nipple*
- *1¾" 1/8 IP Threaded Bottom Bracket with 1/2" Nipple*
- *7" AWM B/W Leads 105°C w/Ground Wire*
- *660W–250V*



90-415 *On-Off Brass Finish Pull Chain*

- *1½" 1/8 IP Threaded Top Bracket with 3/8" Nipple*
- *1¾" 1/8 IP Threaded Bottom Bracket*
- *7" AWM B/W Leads 105°C*
- *660W–250V*



90-416 *On-Off Brass Finish Turn Knob*

- *1" 1/8 IP Threaded Top Bracket with 1/4" Nipple*
- *1¾" 1/8 IP Threaded Bottom Bracket*
- *6" AWM B/W Leads 105°C*
- *660W–250V*



90-414 *Twin Offset*

- *1½" 1/8 IP Female Top & Bottom Bracket w/Set Screw*
- *8" AWM B/W Leads 105°C*
- *660W–250V*



80-1664 *Twin Offset*

- *1½" 1/8-27 Threaded Top Bracket with 3/8" Nipple*
- *1½" 1/8-27 Threaded Bottom Bracket with 3/8" Nipple*
- *8" AWM B/W Leads 105°C*
- *660W–250V*

Phenolic *Twin Cluster • Special Order Options*

PLEASE NOTE: *Socket Cluster measurements are from the center line to the top & bottom of brackets.*



Special Order Options

PLEASE SPECIFY WIRE: • Length • Gauge • Type • Temperature • Color • Strip Ends



1/8" IP Tapped Hole



1/8" IP Nipple (Specify Length)



1/4" IP Nipple (Specify Length)



1/8" IP Bushing with Set Screw



1/4" IP Bushing with Set Screw



Felt Bracket with Two 6/32" Tapped Holes



Snap Spring



1/8" IP Milled Flat Nipple (Specify Length)



Turn Knob Switch as Selected



Pull Chain Switch as Selected

MEDIUM BASE SOCKETS

Phenolic *3 Light Cluster*





90-463

- *3 Light Cluster Socket*
- *1¾" 1/8 IP Threaded Top Bracket with 5/8" Nipple*
- *1¾" 1/8 IP Threaded Bottom Bracket with 5/8" Nipple*
- *8" AWM B/W Leads 105°C*
- *660W–250V*



90-1587

- *3 Light Cluster Socket*
- *On-Off Nickel Pull Chain*
- *1¾" 1/8 IP Threaded Top Bracket with 5/8" Nipple*
- *1¾" 1/8 IP Threaded Bottom Bracket*
- *7" AWM B/W Leads 105°C*
- *660W–250V*

PLEASE NOTE: *Socket Cluster measurements are from the center line to the top & bottom of brackets.*





90-464

- *4 Light Cluster Socket*
- *1¾" 1/8 IP Threaded Top Bracket with 1/2" Nipple*
- *1¾" 1/8 IP Threaded Bottom Bracket with 1/2" Nipple*
- *7" AWM B/W Leads 105°C*
- *660W–250V*



90-1588

- *4 Light Cluster Socket*
- *On-Off Nickel Pull Chain*
- *1¾" 1/8 IP Threaded Top Bracket with 5/8" Nipple*
- *1¾" 1/8 IP Threaded Bottom Bracket*
- *7" AWM B/W Leads 105°C*
- *660W–250V*

PLEASE NOTE: *Socket Cluster measurements are from the center line to the top & bottom of brackets.*

SATCO®

Phenolic *Paper Liner*

c UL us LISTED

Phenolic Candelabra Sockets with Paper Liner



90-422 1½"
Screw Terminals-Double Leg
1/8 IP–Outside Extrusion
75W-125V



80-1996 1¾"
Screw Terminals-Double Leg
1/8 IP–Inside Extrusion
75W-125V



90-403 2" Double Leg
80-2054 2" Single Leg
Screw Terminals
1/8 IP–Outside Extrusion
75W-125V



80-1347 2½"
Screw Terminals-Double Leg
1/8 IP–Inside Extrusion
75W-125V



80-1088 3"
Screw Terminals-Double Leg
1/8 IP–Inside Extrusion
75W-125V



80-1087 3½"
Screw Terminals-Double Leg
1/8 IP–Inside Extrusion
75W-125V



80-1615 3⁹⁄₁₀"
Screw Terminals-Double Leg
1/8 IP–Inside Extrusion
75W-125V



80-1327 4" (shown)
80-1649 6"
Screw Terminals-Double Leg
1/8 IP–Inside Extrusion
75W-125V



90-402 3¼"–4¼"
Screw Terminals-Adjustable Leg
1/8 IP–Inside Extrusion
75W-125V



80-1089 5⅜"–6⅝"
Screw Terminals-Adjustable Leg
1/8 IP–Inside Extrusion
75W-125V

c UL us LISTED

Phenolic Candelabra Sockets with Leads



90-738 1⅝" Smooth
6" AWM B/W Leads 105°C
1/8 IP–Inside Extrusion
Single Leg, 75W-125V



80-1145 1⅝" Flange 12" Leads
80-2097 1⅝" Flange 18" Leads
AWM B/W Leads 105°C
1/8 IP–Inside Extrusion
Single Leg, 75W-125V



80-1146 1⅝" Flange
24" AWM B/W Leads 105°C
1/8 IP–Inside Extrusion
Single Leg, 75W-125V



80-2098 2 3/32"
42" AWM B/W Leads 125°C
1/8 IP–Inside Extrusion
Single Leg
75W-125V



80-1300 26" Leads
80-1398 36" Leads
80-1844 48" Leads
1¾" Flange
#18 UL 1430 B/W Leads 105°C
1/8 IP–Inside Extrusion Double Leg
75W-125V



90-739 1⅝" Smooth
6" AWM B/W Leads 105°C
1/8 IP Nipple
Single Leg, 75W-125V



80-1552 1 11/16" Flange
12½" AWM B/W Leads
2" Overall Height
1/8 IP Nipple
Single Leg, 75W-125V



80-1596 1¾" Smooth
24" #18 UL 1015
B/W Leads 105°C
1/8 IP–Inside Extrusion
Double Leg
75W-125V



80-1301 3" Flange
26" #18 UL 1430
B/W Leads 105°C
1/8 IP–Inside Extrusion
Double Leg
75W-125V



80-1148 3" Flange
24" 18/2 SPT-2 105°C
Clear Silver Leads
1/8 IP–Inside Extrusion
Single Leg
75W-125V



80-1302 4" Flange
26" #18 UL 1430
B/W Leads 105°C
1/8 IP–Inside Extrusion
Double Leg
75W-125V



90-1709
Paper Liner
for Candelabra Sockets

Phenolic

Candelabra Base Phenolic Sockets with Spring Clip



80-1794 Gold
14" AWM B/W Leads 105°C
75W-125V



80-1198 Ivory
6" AWM B/W Leads 105°C
75W-125V



80-1275 Brown
14" AWM B/W Leads 105°C
75W-125V



80-1093 Brown
24" AWM B/W Leads 105°C
75W-125V



90-1709
Paper Liner
for Candelabra Sockets



90-548
Pin Socket
Pressure Fit
75W-125V



80-1274 2¾"
Screw Terminals
1/8 IP Slip Round Hole Bracket
75W-125V

Push-in Terminals



80-1312 2"
80-1718 4"
80-1719 6"
Flange Type-Single Leg
1/8 IP–Inside Extrusion
75W-125V



80-1294 1⅝"
80-1303 2"
80-1304 3"
80-1305 4"
Full Threaded-Single Leg
1/8 IP–Inside Extrusion
75W-125V

#18 SPT-1 Candelabra Snap Sockets with Cord Switch & Plug (non-UL)



80-1651 6 Ft. #18 SPT-1 Brown
80-1782 6 Ft. #18 SPT-1 White
80-1784 8 Ft. #18 SPT-1 Brown
80-1785 8 Ft. #18 SPT-1 White
Cord, Switch & Plug (switch 17" from socket)

#18 SPT-2 Candelabra Snap Sockets with Cord Switch & Plug (non-UL)



80-1652 6 Ft. #18 SPT-2 Brown
80-1786 6 Ft. #18 SPT-2 White
80-1787 8 Ft. #18 SPT-2 Brown
80-1788 8 Ft. #18 SPT-2 White
Cord, Switch & Plug (switch 17" from socket)

Phenolic *with Leads / Rings / European Style*

c UL us LISTED

Phenolic Threaded Candelabra Sockets with Leads / Rings



90-1556 1¼"
w/Shoulder and Phenolic Ring
8" AWM B/W Leads 105°C
75W-125V



80-1473 1¼"
w/Shoulder and Phenolic Ring
24" 18/2 SPT-1 Brown Leads 105°C
75W-125V

80-1694 1¼"
w/Shoulder and Phenolic Ring
6 Ft.18/2 SPT-2 Brown Wire &
Plug105°C 75W-125V



90-1557 1¾"
w/Shoulder and Phenolic Ring
8" AWM B/W Leads 105°C
Pulled Thru 1/8 IP Inside Extrusion
75W-125V

(non-UL)



80-1693 1¾"
w/Shoulder and Phenolic Ring
6 Ft.18/2 SPT-1 Brown Wire
& Plug105°C w/Brown
Switch 21" from Socket
75W-125V

3 Light Phenolic Threaded Candelabra Harness Sets



80-1912 1¼"
with Shoulder and Phenolic Ring
9" Centers 18" Tail
AWM B/W Leads 150°C
75W-125V



80-1474 1¼"
with Shoulder and Phenolic Ring
6" Centers 18" Tail
18/2 SPT-1 105°C Brown
75W-125V

Rings for Threaded Candelabra Sockets



80-1485
Brass Finish



80-1486
Chrome Finish Ring



80-1977
Phenolic Ring

Candelabra European Style Sockets



80-1094 *Brown Phenolic*
80-1650 *White Phenolic*
4 Piece, Full Uno Thread and Ring
1/8 IP Screw Terminals
75W-125V



80-1095 *4 Piece*
1/2 Uno Thread and Ring
w/Shoulder 1/8 IP
Screw Terminals
75W-125V



80-1311 *3 Piece*
Smooth
1/8 IP
Screw Terminals
75W-125V

European Socket Release Tab Directions

WARNING: Disconnect from power source first!

Press & hold release tab with screwdriver to remove outer shell for wiring



Release tab (close-up) with outer shell removed

Candelabra – Porcelain Sockets w/Paper Liner



80-1893 1½"
80-1090 1¾"
Screw Terminals
1/8 IP Inside Extrusion
Double Leg
75W-125V



80-1948 1¾"
Waterproof Screw Terminals
w/Phenolic Cover
1/8 IP Inside Extrusion
75W-125V



80-1091 2"
80-2013 3"
80-2012 3¾"
Screw Terminals
1/8 IP Inside Extrusion
Double Leg
75W-125V



80-1092
Adjustable Leg 3½"–4⅝" Screw Terminals
1/8 IP Outside Extrusion Double Leg
75W-125V
80-2003
Adjustable Leg 4¾"–6" Screw Terminals
1/8 IP Inside Extrusion Double Leg
75W-125V



80-1653 1¾"
24" #18 UL 1015 B/W Leads 105°C
1/8 IP–Inside Extrusion Double Leg
75W-125V

Twin Socket Cluster



80-1654 4½"
24" #18 UL 1015 B/W Leads 105°C
1/8 IP–Inside Extrusion Double Leg
75W-125V

Intermediate Base Porcelain Sockets



90-1554 1¾"
Screw Terminals
1/8 IP Inside Extrusion
Single Leg
75W-250V



90-1555 1¾"
1/8 IP Inside Extrusion
8" AWM B/W 105°C Leads
Pulled Thru Single Leg
75W-250V

Threaded G-9 Sockets



80-1582
Porcelain Socket
Push-In Terminals
1/8 IP Hickey Inside Extrusion
Double Leg



80-1589 21" Leads
80-1590 72" Leads
Porcelain Socket w/Ring
UL 10362 Leads
1/8 IP Hickey Inside Extrusion
Double Leg

Halogen Double Loop G-9 Socket 120V



80-1500
Phenolic Socket
20" UL 1430 B/W Leads
1/8 IP Bushing

G-9 Socket Accessories



S4614
G-9 Bulb



80-1591
Tubular Clear Glass
with Threads



80-1583
Chrome Ring
to Stop Tubular Glass

Porcelain Halogen Sockets



90-1553
Round Halogen Socket
1/8 IP Hickey
G4-GX5.3-GY6.35 Base
8" SF–1 200°C Leads
1000W–250V



90-1590 6" Leads
80-2049 12" Leads
Round Halogen Socket
G4-GX5.3-GY6.35 Base
SF–1 200°C Leads
750W–250V



80-1668 8" Leads
80-2044 24" Leads
Round Analog Socket
GX5.3-GY6.35 Base
SF–1 200°C Leads
75W-250V



80-1813
Halogen Socket w/Metal
Plate & 2 Mounting Holes
GX5.3 Base
8" 180°C Leads
750W–250V



80-1816
GU7 Halogen Socket
6" 18 GA 200°C
Teflon Wire
1000W–250V



90-475
MR16 Socket
GX5.3 Base
6" SF–1 200°C Leads
75W–250V



90-1080
Mini Can Halogen Socket
Screw Mount Bracket
E11 Base 6" SF–1 200°C Leads
1000W–250V



80-1873
G8 Porcelain
Halogen Socket
6" 200°C Leads
1000W–250V



80-2019
Round Halogen Socket
1/8 IP Hickey w/Spring Clip
8" SF–1 200°C Leads
1000W–250V



80-1796
GU10 Socket
1/8 IP Hickey
8" SF–1 200°C Leads
1000W–250V



90-1552
Round Halogen Socket
GU10 w/Mounting Holes
8" SF–1 200°C Leads
1000W–250V



90-1081
Porcelain 4 Terminal
Wire Connector
1000W–250V

Porcelain Halogen Sockets



90-1078
78mm Double Ended
Halogen Socket
R7S Base, 6" SF–1 200°C Leads
1000W–250V



90-1077
118mm Double Ended
Halogen Socket
R7S Base, 6" SF–1 200°C Leads
1000W–250V



90-1561 6" SF–1 200°C Leads
80-2004 18" SF–1 200°C Leads
Halogen Socket – R7S Base
1000W–250V



90-474
Double Ended Halogen Socket Set
R7S Base, 12" SF–1 200°C Leads
500W–250V



80-1742
G4 Wedge Type
8" SF–1 200°C Leads
1000W–250V



80-1741
G9 Porcelain Smooth Body
U-Channel Hickey Push-in Wiring
500W–250V



80-1872
HID Socket
G12 - 5KV 8" SF–2 Leads
6A–1000V

See pg. 127 for Additional Wire Connectors

Porcelain Wire Connectors High Heat 300V



90-1311
Small
Rated Up to
2 #18



90-1312
Medium
Rated Up to
4 #18



90-1313
Large
Rated Up to
6 #18

Metal • Phenolic

Bayonet Base Single Contact Sockets



80-2099
1/8 IP Nipple
8" AWM B/W Leads 105°C
Pulled Thru
500W-125V

Bayonet Base Double Contact Sockets



90-1558 8" Leads
80-1997 36" Leads
1/8 IP Nipple
AWM B/W Leads 105°C
Pulled Thru
500W-125V



90-1559
1/8 IP Nipple
Angle Bracket
8" AWM B/W Leads 105°C
Pulled Thru
500W-125V



90-1560
Flat Mounting Bracket
Screw Holes 1¼" CC
8" AWM B/W Leads 105°C
500W-125V

Linear Sockets (non-UL)



90-250
Replacement for 2 Base lamp ONLY
(2 Base Lamp shown on the right)
NEED 2 PIECES PER LAMP!



90-248
1 Base
Replacement for old style 1 Base lamp ONLY
(Old Style1 Base Lamp shown on the right)

2 Base Linear Lamp – T10 S14S Base



S4894 LN60 19 11/16" M.O.L.
60W-125V

S4895 LN150 39⅛" M.O.L.
150W-125V



1 Base Lamp

Medium Base



80-1926
Medium Base Glazed Porcelain Pull Chain Socket
CSSNP
250W-250V



90-1112
Two Piece Medium Base Porcelain Sign Receptacle
Screw Terminals
1½" x 1⅝"
660W-250V



90-425
Two Piece Medium Base Porcelain Sign Receptacle
Screw Terminals
1½" x 1⅝"
660W-250V



90-1111
Two Piece Medium Base Porcelain Sign Receptacle
8" AWM B/W Leads 105°C
1½" x 1⅝"
660W-250V



90-449
Medium Base, Snap-In Phenolic Sign Receptacle
Lay-In Wiring-Twist Top
660W-250V



90-1113 *Brown*
90-2452 *White*
Medium Base Phenolic Receptacle
w/Mounting Holes
Screw Terminals
660W-250V



90-1097 *Standard Screw Shell*
80-2100 *Left Hand Screw Shell (non-UL)*
Rubber Coated
Pigtail with 6" Leads
660W-600V

Medium Base Porcelain Pony Cleat



80-1748
Screw Terminals – CSSNP
660W-250V

Miniature Base (non-UL)



90-1076
Miniature Base
Plastic Receptacle
75W-125V

Candelabra Base (non-UL)



90-532
Candelabra Base
Plastic Receptacle
75W-125V

Quad Tube *4-Pin for Electronic & Dimming Ballasts*



T4 Bulb 13W
G24q-1 Base

Cat. No.	Lamp Code	CCT (K)	CRI	Hours	Lumens	MOL	Packaging	Master
S8329	CFD13W/4P/827/ENV	2700	82	10,000	900	5.2"	Hang Box	50
S8330	CFD13W/4P/830/ENV	3000	82	10,000	900	5.2"	Hang Box	50
S8331	CFD13W/4P/835/ENV	3500	82	10,000	900	5.2"	Hang Box	50
S8332	CFD13W/4P/841/ENV	4100	82	10,000	900	5.2"	Hang Box	50



T4 Bulb 18W
G24q-2 Base

Cat. No.	Lamp Code	CCT (K)	CRI	Hours	Lumens	MOL	Packaging	Master
S8333	CFD18W/4P/827/ENV	2700	82	10,000	1250	5.8"	Hang Box	50
S8334	CFD18W/4P/830/ENV	3000	82	10,000	1250	5.8"	Hang Box	50
S8335	CFD18W/4P/835/ENV	3500	82	10,000	1250	5.8"	Hang Box	50
S8336	CFD18W/4P/841/ENV	4100	82	10,000	1250	5.8"	Hang Box	50



T4 Bulb 26W
G24q-3 Base

Cat. No.	Lamp Code	CCT (K)	CRI	Hours	Lumens	MOL	Packaging	Master
S8337	CFD26W/4P/827/ENV	2700	82	10,000	1825	6.5"	Hang Box	50
S8338	CFD26W/4P/830/ENV	3000	82	10,000	1825	6.5"	Hang Box	50
S8339	CFD26W/4P/835/ENV	3500	82	10,000	1825	6.5"	Hang Box	50
S8340	CFD26W/4P/841/ENV	4100	82	10,000	1825	6.5"	Hang Box	50



S8329 *13W Quad* | **S8333** *18W Quad* | **S8337** *26W Quad* | **S8396** *13W Triple* | **S8342** *18W Triple* | **S8346** *26W Triple* | **S8350** *32W Triple* | **S8354** *42W Triple*

NOTE: These 4-pin CF lamp have an internal end-of-life mechanism (EOL) that shuts down the lamp preventing abnormal end-of life failure modes. This lamp was designed for use with high frequency ballasts that do not have their own end-of-life (lamp) sensing circuits, but it is also compatible with high frequency ballasts that have their own end-of-life (lamp) sensing circuits.

Triple Tube *4-Pin for Electronic & Dimming Ballasts*

Cat. No.	Lamp Code	CCT (K)	CRI	Hours	Lumens	MOL	Packaging	Master
S8396	CFT13W/4P/830/ENV	3000	82	10,000	900	4.2"	Hang Box	50
S8397	CFT13W/4P/835/ENV	3500	82	10,000	900	4.2"	Hang Box	50
S8398	CFT13W/4P/841/ENV	4100	82	10,000	900	4.2"	Hang Box	50



T4 Bulb 13W
GX24q-1 Base

Cat. No.	Lamp Code	CCT (K)	CRI	Hours	Lumens	MOL	Packaging	Master
S8341	CFT18W/4P/827/ENV	2700	82	10,000	1200	4.4"	Hang Box	50
S8342	CFT18W/4P/830/ENV	3000	82	10,000	1200	4.4"	Hang Box	50
S8343	CFT18W/4P/835/ENV	3500	82	10,000	1200	4.4"	Hang Box	50
S8344	CFT18W/4P/841/ENV	4100	82	10,000	1200	4.4"	Hang Box	50



T4 Bulb 18W
GX24q-2 Base

Cat. No.	Lamp Code	CCT (K)	CRI	Hours	Lumens	MOL	Packaging	Master
S8345	CFT26W/4P/827/ENV	2700	82	10,000	1800	5"	Hang Box	50
S8346	CFT26W/4P/830/ENV	3000	82	10,000	1800	5"	Hang Box	50
S8347	CFT26W/4P/835/ENV	3500	82	10,000	1800	5"	Hang Box	50
S8348	CFT26W/4P/841/ENV	4100	82	10,000	1800	5"	Hang Box	50



T4 Bulb 26W
GX24q-3 Base

Cat. No.	Lamp Code	CCT (K)	CRI	Hours	Lumens	MOL	Packaging	Master
S8349	CFT32W/4P/827/ENV	2700	82	10,000	2400	5.6"	Hang Box	50
S8350	CFT32W/4P/830/ENV	3000	82	10,000	2400	5.6"	Hang Box	50
S8351	CFT32W/4P/835/ENV	3500	82	10,000	2400	5.6"	Hang Box	50
S8352	CFT32W/4P/841/ENV	4100	82	10,000	2400	5.6"	Hang Box	50



T4 Bulb 32W
GX24q-3 Base

Cat. No.	Lamp Code	CCT (K)	CRI	Hours	Lumens	MOL	Packaging	Master
S8353	CFT42W/4P/827/ENV	2700	82	10,000	3200	6.5"	Hang Box	50
S8354	CFT42W/4P/830/ENV	3000	82	10,000	3200	6.5"	Hang Box	50
S8355	CFT42W/4P/835/ENV	3500	82	10,000	3200	6.5"	Hang Box	50
S8356	CFT42W/4P/841/ENV	4100	82	10,000	3200	6.5"	Hang Box	50



T4 Bulb 42W
GX24q-4 Base

SATCO®

Push Tab Lock *GU24 – 4-Pin CFL*

Electronic Self-Ballasted CFL Lampholders – Less Caps – 2 Yr. Warranty (Replacement Only)

c UL us LISTED



Smooth Phenolic

80-1710 *120V, 60Hz, 0.17A*
80-2073 *277V, 60Hz, 0.17A*
13W G24q-1 & GX24q-1
Height: 2"



Smooth Phenolic

80-1712 *120V, 60Hz, 0.23A*
80-2075 *277V, 60Hz, 0.23A*
18W G24q-2 & GX24q-2
Height: 2"



Smooth Phenolic

80-1949 *120V, 60Hz, 0.34A*
80-2077 *277V, 60Hz, 0.34A*
26W G24q-3 & GX24q-3
Height: 2"



Phenolic w/Uno Ring

80-1711 *120V, 60Hz, 0.17A*
80-2074 *277V, 60Hz, 0.17A*
13W G24q-1 & GX24q-1
Height: 2"



Phenolic w/Uno Ring

80-1713 *120V, 60Hz, 0.23A*
80-2076 *277V, 60Hz, 0.23A*
18W G24q-2 & GX24q-2
Height: 2"



Phenolic w/Uno Ring

80-1950 *120V, 60Hz, 0.34A*
80-2078 *277V, 60Hz, 0.34A*
26W G24q-3 & GX24q-3
Height: 2"



Phenolic w/Uno Ring

80-1869 *120V, 60Hz, 0.34A*
26W G24q-3 & GX24q-3
Height: 2¾"



Phenolic w/Uno Ring

80-1891 *120V, 60Hz, 0.34A*
32W G24q-3 & GX24q-3
Height: 2¾"



Phenolic w/Uno Ring

80-2104 *120V, 60Hz, 0.34A*
42W G24q-4 & GX24q-4
Height: 2¾"

NOTE: Maximum 6 Ballasts to a Harness Set

TAB LOCKING GU24 SOCKET (pat. pending)

FEATURES:

- *These are Self-Ballasted Lampholders, with electronic ballasts built in for CFLs.*
- *For use in dry, damp and wet locations.*
- *Withstand dielectric voltage test (Hi-Pot) at 1250V for one minute.*
- *Instant start*
- *Power Factor (PF) >50%.*
- *Ambient Temperature: -20°C ~ 50°C.*
- *Automatically protected from:*
  - *Poor contact between lamp & lampholder*
  - *Air leakage into bulb*
  - *Damaged bulb*
- *A quick-blow fuse is integrated into the lampholder to protect against power surges and the lampholder would have to be replaced when the fuse is blown.*



c UL us LISTED

CFL Self Ballast *GU24 – also for 4-Pin Ballast & Socket Combinations*



80-1715
1/8IP Bushing, Height: 1/2",
24" 18AWM 105° Leads



80-1717
w/Ring U-Channel 1/8IP Hickey
Height: 2", Screw Terminals



80-1714 *24" 18AWM 105° Leads*
80-2594 *60" 18AWM 105° Leads*
U-Channel 1/8IP Hickey, Height: 1¼"



80-1716
w/Ring U-Channel 1/8IP Hickey
Height: 2", 24" 18AWM 105° Leads



80-1720
Side Mount 1/8IP Hickey, Height: 1/2",
24" 18AWM 105° Leads



80-1721
w/Ring U-Channel 1/8IP Hickey, Height: 2",
24" 18AWM 105° Leads w/24" Ground Wire Attached PTH

CFL Self-Ballast GU24 Lamps

T2 Mini Spiral
S8201 *9W-2700K*
S8202 *11W-2700K*
S8203 *13W-2700K*

T3 Mini Spiral
S8204 *15W-2700K*
S8205 *18W-2700K*
S8206 *23W-2700K*
S8207 *26W-2700K*

T2 Squat Spiral
S8227 *13W-2700K*
S8228 *18W-2700K*



T2 Mini Spiral T3 Mini Spiral T2 Squat Spiral

GU24 Socket Reducer

80-1888 *Locking Function*
90-2434 *Removable Grip Function*
Medium to GU24 Reducer
660W-250V





80-2105
Uno Ring

SATCO®

SOCKETS & LAMPHOLDERS

3 Step Safety Design *GU24 – 4-Pin CFL – 120V / 277V*

Electronic Self-Ballasted CFL Lampholders – Less Caps – 2 Yr. Warranty (Replacement Only)

c UL us LISTED



Smooth Phenolic

80-1846 120V, 60Hz, 0.15A
80-1852 277V, 60Hz, 0.15A
13W G24q-1 & GX24q-1
Height: 2"



Smooth Phenolic

80-1847 120V, 60Hz, 0.20A
80-1853 277V, 60Hz, 0.20A
18W G24q-2 & GX24q-2
Height: 2"



Smooth Phenolic

80-1848 120V, 60Hz, 0.30A
80-1854 277V, 60Hz, 0.30A
26W G24q-3 & GX24q-3
Height: 2"



Phenolic w/Uno Ring

80-1849 120V, 60Hz, 0.15A
80-1855 277V, 60Hz, 0.15A
13W G24q-1 & GX24q-1
Height: 2"



Phenolic w/Uno Ring

80-1850 120V, 60Hz, 0.20A
80-1856 277V, 60Hz, 0.20A
18W G24q-2 & GX24q-2
Height: 2"



Phenolic w/Uno Ring

80-1851 120V, 60Hz, 0.30A
80-1857 277V, 60Hz, 0.30A
26W G24q-3 & GX24q-3
Height: 2"

NOTE: Maximum 6 Ballasts to a Harness Set

3 STEP SAFETY DESIGN GU24 SOCKET INSTRUCTIONS

STEP 1 Turn the locking device on the ballast housing (B) to position "1" and insert the pins on the ballast housing (B) into the cap (A) of the GU24 lampholder & turn cap to the right to lock (Fig. 1 & 2).

STEP 2 Set the locking device on the ballast housing (B) to position "2" and install the bulb (Fig. 3 & 4).

STEP 3 Twist the bulb & locking device on the ballast housing (B) to position "3" to lock (Fig. 5).

RE-LAMPING Twist the bulb & locking device on the ballast housing to position "2" to remove & re-install the bulb. Twist the bulb & locking device on the ballast housing to position "3" to re-lock.

Figure 1



Figure 2



Figure 3



Figure 4



Figure 5



c UL us LISTED

3 Step Safety Design *GU24 – 4-Pin Ballast & Socket Combinations – also for GU24 Self Ballasted*



80-1858 24" 18AWM 105° Leads
80-1934 W/Quick Wire Terminals
U-Channel 1/8IP Hickey, Height: 1 1/8"



80-1859 24" 18AWM 105° Leads
80-1935 W/Quick Wire Terminals
1/8IP Bushing, Height: 3/4"



80-1860 24" 18AWM 105° Leads
80-2005 13" 18AWM 105° Leads & 13" Ground Wire
Snap Bracket, Height: 3/4"



80-1861
L- Bracket, Height: 3/4"
24" 18AWM 105° Leads



80-1862 24" 18AWM 105° Leads
80-1953 W/Quick Wire Terminals
Side Mount Bracket, Height: 3/4"



80-1863
Double Snap Bracket, Height: 3/4"
24" 18AWM 105° Leads

CFL Self-Ballast GU24 Lamps

T2 Mini Spiral
S8201 9W-2700K
S8202 11W-2700K
S8203 13W-2700K

T3 Mini Spiral
S8204 15W-2700K
S8205 18W-2700K
S8206 23W-2700K
S8207 26W-2700K

T2 Squat Spiral
S8227 13W-2700K
S8228 18W-2700K



T2 Mini Spiral T3 Mini Spiral T2 Squat Spiral

GU24 Socket Reducer

80-1888 Locking Function
90-2434 Removable Grip Function
Medium to GU24 Reducer
660W-250V





80-1955
Uno Ring

With L-Bracket Cap (unassembled) *GU24 – 4-Pin CFL*

2 Yr. Warranty (Replacement Only)



80-1773
13W L- Bracket Height: 2½"
14" 105°C Leads
G24q-1 and GX24q-1
120VAC, 60Hz, 200MA



80-1774
18W L- Bracket Height: 2½"
14" 105°C Leads
G24q-2 and GX24q-2
120VAC, 60Hz, 250MA



80-1775
26W L- Bracket Height: 2¾"
14" 105°C Leads
G24q-3 and GX24q-3
120VAC, 60Hz, 350MA

NOTE: Maximum 6 Ballasts to a Harness Set

Ceiling Receptacles *GU24 – Self Ballasted Lamp*

c UL us LISTED

GU24 Fluorescent Phenolic & Porcelain Receptacles with Screw Terminals

90-2467 *Phenolic*
Keyless White Phenolic
GU24 Ceiling Receptacle
Screw Terminals
75W-250V



See Page 79 for Accessory Item:
90-2513 *6.2" White Lexan Lens*

90-2579 *Porcelain*
Keyless White Porcelain
GU24 Ceiling Receptacle
Screw Terminals
75W-250V



90-2468 *Phenolic*
White Phenolic GU24
On-Off Pull-Chain
Ceiling Receptacle
Screw Terminals
75W–250V



90-2581 *Porcelain*
White Porcelain GU24
On-Off Pull-Chain
Ceiling Receptacle
Screw Terminals
75W–250V



90-2483 *Phenolic*
White Phenolic GU24 On-Off
Pull-ChainCeiling Receptacle
w/Grounded Outlet
Screw Terminals
75W–250V



Pre-wired Ceiling Receptacles *GU24 – Self Ballasted Lamp*

GU24 Fluorescent Phenolic & Porcelain Receptacles with Leads

90-2469 *Phenolic*
Keyless White Phenolic
GU24 Ceiling Receptacle
6" AWM B/W Leads 105°C
75W-250V



90-2580 *Porcelain*
Keyless White Porcelain
GU24 Ceiling Receptacle
6" AWM B/W Leads 105°C
75W-250V



90-2470 *Phenolic*
White Phenolic GU24
On-Off Pull-Chain Ceiling Receptacle
6" AWM B/W Leads 105°C
75W–250V



90-2582 *Porcelain*
White Porcelain GU24
On-Off Pull-Chain Ceiling Receptacle
6" AWM B/W Leads 105°C
75W–250V



90-2484 *Phenolic*
White Phenolic GU24 On-Off Pull-Chain Ceiling Receptacle w/Grounded Outlet
6" AWM B/W Leads 105°C
75W–250V



CFL Self-Ballast GU24 Lamps

T2 Mini Spiral
S8201 *9W-2700K*
S8202 *11W-2700K*
S8203 *13W-2700K*

T3 Mini Spiral
S8204 *15W-2700K*
S8205 *18W-2700K*
S8206 *23W-2700K*
S8207 *26W-2700K*

T2 Squat Spiral
S8227 *13W-2700K*
S8228 *18W-2700K*



T2 Mini Spiral *T3 Mini Spiral* *T2 Squat Spiral*

c UL us LISTED

Ceiling Receptacle *GU24 w/Lexan Lens – for Self Ballasted Lamps*

GU24 Fluorescent Pull Chain Receptacle & Lens (2-Piece Set)
for Self Ballasted Lamps – 15W Maximum.



(2 Piece Set)



90-2499 (Shown Unassembled)

90-2499
GU24 Pull Chain Ceiling Receptacle w/Lens
2 Knockouts 5.5" White Lens
2 Piece Set

GU24 Fluorescent Keyless Receptacle & Lens (Sold Separately)
for Self Ballasted Lamps – 15W Maximum.



(Base Only)

90-2467
GU24 Keyless Ceiling Receptacle
Screw Terminals
Base Only

(Lens Only)

90-2513
6.2" White Lexan Lens for
GU24 Keyless Ceiling Receptacle
Lens Only



90-2467/90-2513 (Shown Assembled)

Socket – 2-Pin Lamps *Rated 75W–600V*

Socket – 2-Pin Lamps



90-1540
Horizontal Snap–In
G23–G23-2 Base
For: CF5, 7, 9DS and CF9DD



90-1541
Horizontal Screw Down
G23–G23-2 Base
For: CF5, 7, 9DS and CF9DD



90-1542
Vertical Screw Down
G23–G23-2 Base
For: CF5, 7, 9DS and CF9D



90-1543
Horizontal Snap–In
GX23 and GX23-2 Base
For: CF13DS and CF13DD



90-1544
Horizontal Screw Down
GX23 and GX23-2 Base
For: CF13DS and CF13DD



90-1545
Vertical Screw Down
GX23 and GX23-2 Base
For: CF13DS and CF13DD



90-1547
18W Two–Pin Bottom Screw Down
G24D-2 and GX24D-2 Base
For: CF18DD and CF18DT



90-1548
26W Two–Pin Bottom Screw Down
G24D-3 and GX24D-3 Base
For: CF26DD and CF26DT

c UL us LISTED

Socket – 2 & 4-Pin Lamps *Rated 75W–600V*

Socket – 2-Pin Lamps



80-1506
13W 2-Pin Lampholder w/Uno Thread & Ring
Height: 1½", Push-In Terminals Solid Wire
w/U Channel 1/8IP Hickey, GX23 Twin, GX23-2 Quad
75W-600V



80-1227
13W Bright Gilt Socket
w/Fluorescent GX23 and GX23-2
2-Pin Lampholder, Height: 2"
75W-600V

Socket – 4-Pin Lamp



80-1228
13W Bright Gilt Socket
w/Fluorescent G24Q and GX24Q-1
4-Pin Lampholder, Height: 1¼"
75W-600V

VERTICAL MOUNT Socket – 4-Pin Lamps



90-1549
13W Four-Pin Bottom Screw Down
G24Q-1 and GX24Q-1 Base
For: CF13DD/E and CF13DT/E
Vertical Mount



90-1550
18W Four-Pin Bottom Screw Down
G24Q-2 and GX24Q-2 Base
For: CF18DD/E and CF18DT/E
Vertical Mount



90-1551
26-32W Four-Pin Bottom Screw Down
G24Q-3 and GX24Q-3 Base
For: CF26DD/E and CF26DT/E
Vertical Mount



90-2498
42W Four-Pin Bottom Screw Down
G42Q-4 and GX24Q-4 Base
For: CF42DD/E and CF42DT/E
Vertical Mount

HORIZONTAL MOUNT Socket – 4-Pin Lamps



80-2106
13W Four-Pin Screw Down
G24Q-1 and GX24Q-1 Base
For: CF13DD/E and CF13DT/E
Horizontal Mount



80-2107
18W Four-Pin Screw Down
G24Q-2 and GX24Q-2 Base
For: CF18DD/E and CF18DT/E
Horizontal Mount



80-2108
26-32W Four-Pin Screw Down
G24Q-3 and GX24Q-3 Base
For: CF26DD/E and CF26DT/E
Horizontal Mount



80-2109
42W Four-Pin Screw Down
G42Q-4 and GX24Q-4 Base
For: CF42DD/E and CF42DT/E
Horizontal Mount



2-Pin CFL



4-Pin CFL

Shallow Base

T8 & T12 Slimline Single Pin Fluorescent Sockets



80-1496 *Plunger*
1¾"H x 1¼"W x 1¼"D



80-1497 *Fixed*
1¾"H x 1¼"W x 1¼"D

Shallow Base
Slide–On Quick Wire for
Wet and Damp Locations
Rapid Start for 20 Gauge Panels
Strip 3/8"–1/2"
660W–1000V

T8 & T12 (HO) High Output Fluorescent Sockets – Recessed Double Contact



80-1498 *Plunger*
1⅞"H x 1⅜"W x 1¼"D



80-1499 *Fixed*
1⅞"H x 1⅜"W x 1¼"D

Quickwire Terminals
Accept Up to 18 Gauge
Solid Or Tinned Leads
Slide–On Shallow Base
Rapid Start
Strip 3/8"–1/2"
660W–1000V

c UL us LISTED

Medium Profile – T8 & T12

Rotary Locking T8–T12
Used in Troffers
and Wrap Fixtures
for Retro Fit Kits
and Replacement
Snap Wing Mounting
Made from Urea
660W-600V



80-1252 Shunted for Instant Start Ballast Applications

80-1253 Rapid Start Applications

1 1/2"H x 1 1/4"W x 3/4"D



Standard Twist–In
Used in Troffers
and Wrap Fixtures
Slide–On Mounting
Made from Urea
660W-600V

80-1254 Rapid Start Applications, Slide–On Mounting 20 Gauge Slots Upper and Lower

80-1255 Shunted for Instant Start Ballast Applications Slide–On Mounting, 20 Gauge Slots Upper and 18 Gauge Lower

1 5/8"H x 1 1/4"W x 3/4"D

Twist–In T12 Shunted
Dedicated T8 Lampholder
w/T12 Stop
Used in Troffers
and Wrap Fixtures
Slide–On Mounting
20 Gauge Slots Upper
and 18 Gauge Slots Lower
Made from Urea
660W-600V



80-1256 Shunted for Instant Start Ballast Applications

1 5/8"H x 1 1/4"W x 3/4"D



U–Bend Straight In
Used for 2x2 Troffers
Slide–On Mounting
20 Gauge Slots
Upper and Lower
Made from Urea
660W-600V

80-1257 Rapid Start Applications

80-1258 Shunted for Instant Start Ballast Applications

1 9/16"H x 1 1/4"W x 3/4"D

Tall Profile



80-1245 Shunted for Instant Start Ballast Applications

80-1246 Rapid Start Applications

Tall Rotary Locking T8/T12
Used in Troffers and Wrap Fixtures
for Retro Fit Kits/Replacements
Snap Wing Mounting
Made from Urea 660W-600V
1 3/4"H x 1 1/8"W x 7/8"D



80-1247 Tall Standard Twist–In

Used in Strip Fixtures
for Rapid Start Applications
Slide–On Mounting
20 Gauge Slots Upper and Lower
Made from Urea 660W-600V
2"H x 1 1/4"W x 3/4"D



80-1248 Tall Standard Twist–In Externally Shunted

Used in Strip Fixtures
for Instant Start Ballasts
Slide–On Mounting
20 Gauge Slots Upper
and 18 Gauge Lower
Made from Urea 660W-600V
2"H x 1 1/4"W x 3/4"D

Lampholders • Starter Holders • Circle Connectors



80-1249

Butt–On Mounting
T8 or T12 Lampholder
Rapid Start Applications
660W–600V
1 7/16"H x 1 3/8"W x 3/8"D



80-1250

Fluorescent Starter Holder
Snap–In Mounting Spring
660W–250V
1 1/4"L x 7/8"W x 3/8"D



80-1944

T5 Lampholder – Slide-On,
Rotary Locking
Rapid Start Applications
120W–600V
1 1/8"H x 7/8"W x 5/8"D



80-1251

T5 Lampholder
w/8" AWM B/W Solid Leads
for Retro Fit and Replacement
Tall Right Angle Bracket
660W–600V
1 1/4"H x 5/8"W x 3/8"D



80-1490

Circle Connector–Quickwire
Used with High Voltage
Instant Starting Transformers
Accepts 18AWG Leads
Solid or Stranded w/Brass
Alloy Contact
660W–600V
7/8"H x 5/8"W

c UL us LISTED

Low Profile Long Twin Tube Lampholders

2G11 LampHolders



80-1600

Horizontal Snap–In Mounting
Multiple Bottom Push–In Wiring Ports
Metal–Spring Lamp Retainer Clip
660W–600V
1 5/8"H x 1 7/8"W x 3/4"D



80-1601

Shunted Horizontal Snap–In Mounting
for Electronic Ballasts
Bottom Push–In Wiring
660W–600V
1 5/8"H x 1 7/8"W x 3/4"D



80-1602

Shunted Vertical Snap–In Mounting
for Electronic Ballasts
Side Push–In Wiring
Wireways Allow Routing on Top
or Bottom of Mounting Panel
660W–600V
2"H x 1 1/4"W x 3/4"D

2G11 Lamp Support Clips

80-1603

Clear Vertical Clip
UV Stable Polycarbonate
Panel Thickness .023 - .039 (0.58 -0.99)
Max. Including paint
1 1/8"H x 7/8"W



80-1604

Clear Horizontal Clip
UV Stable Polycarbonate
Panel Thickness .023 - .039 (0.58 -0.99)
Max. Including paint
1 1/4"H x 1 5/8"W

4-Pin Long Twin Tube Lampholder & Clips



80-1605

4-Pin Long Twin Tube Lampholder
Molded White Thermosetting Urea
Copper Alloy, Double-Edge Contacts
Push–In Wiring
Accepts 18AWG Leads – Solid, Solder
Dipped or Twisted Tinned & Fused
660W–600V
1 7/8"H x 2 1/8"W x 7/8"D



80-1606

Clear Plastic Horizontal Clip
Panel Thickness .023 - .039 (0.58 -0.99)
Max. Including paint
1 1/4"H x 1 5/8"W

Magnetic

T8 and T12 Preheat / Trigger Start Ballasts

Cat. No.	Primary Lamp	No. of Lamps	Input Voltage	Ballast Code	Start Method	Potted	Master
S5268	F15T12	1	120	MB1X15/120PH/TP	Trigger	Yes	16
S5269	F20T12	1	120	MB1X20/120PH/TP	Preheat	Yes	40
S5270	F20T12	1	120	MB1X20/120PH/TP	Preheat	No	40
S5271	F20T12	2	120	MB2X20/120PH/TP	Trigger	Yes	16
Listed for: F14T8, F14T12, F15T8, F15T12, F20T12 Lamps							
(Preheat ballasts require the use of a starter, Trigger start ballasts eliminate the need for a starter)							

T12 Rapid Start Ballasts

Cat. No.	Primary Lamp	No. of Lamps	Input Voltage	Ballast Code	Sound Rating	Power Factor	Master
S5170	F30T12	2	120	MB2X30/120RS/SRNK	Class A	HPF	10
S5171	F30T12	2	277	MB2X30/277RS/SRNK	Class A	HPF	10
Listed for: F25T12/SS, F30T12 Lamps							
S5274	F34T12	1	120	MB1X40/120RS/SRNK	Class A	HPF	10
S5275	F34T12	1	277	MB1X40/277RS/SRNK	Class A	HPF	10
Listed for: F25T12/SS, F30T12, F34T12, FB34T12, F40T10, F40T12, FB40T12 Lamps							
S6620	F34T12	2	120	MB2X40/120RS/SRNK	Class A	HPF	10
S6622	F34T12	2	277	MB2X40/277RS/SRNK	Class A	HPF	10
Listed for: F34T12, FB34T12, F40T10, F40T12, FB40T12 Lamps							
S5276	F40T12	1	120	MB1X40/120RES/SRNK	Class A	HPF	16
Listed for: F40T12 FULL WATTAGE ONLY – Residential Application							

T12 Instant Start Slimline Ballasts

Cat. No.	Primary Lamp	No. of Lamps	Input Voltage	Ballast Code	Sound Rating	Power Factor	Master
S5277	F48T12	2	120	MB2X48/120IS/SRNK	Class B	HPF	6
S5278	F48T12	2	277	MB2X48/277IS/SRNK	Class B	HPF	6
Listed for: F48T12/SS, F48T12 Lamps							
S5279	F96T12	1	120	MB1X96/120IS/SRNK	Class B	HPF	6
S5280	F96T12	1	277	MB1X96/277IS/SRNK	Class B	HPF	6
S6621	F96T12	2	120	MB2X96/120IS/SRNK	Class B	HPF	6
S5281	F96T12	2	277	MB2X96/277IS/SRNK	Class B	HPF	6
Listed for: F60T12, F64T12, F72T12, F84T12, F96T12/SS, F96T12 Lamps							

Preheat/Trigger Start



Rapid Start



Instant Start Slimline



T12 HO (800mA) Rapid Start Ballasts

Cat. No.	Primary Lamp	No. of Lamps	Input Voltage	Ballast Code	Sound Rating	Power Factor	Master
S5282	F96T12/HO	1	120	MB1X96HO/120RS/SRNK	Class C	HPF	4
S5283	F96T12/HO	1	277	MB1X96HO/277RS/SRNK	Class C	HPF	4
S5284	F96T12/HO	2	120	MB2X96HO/120RS/SRNK	Class C	HPF	4
S5285	F96T12/HO	2	277	MB2X96HO/277RS/SRNK	Class C	HPF	4
Listed for all T12 HO lamps 18" thru 96": F18T12, F24T12, F30T12, F42T12, F48T12/SS, F48T12, F60T12, F64T12, F72T12, F84T12, F96T12/SS, F96T12/CT, F96T12							

T12 HO (800mA) Rapid Start Sign Ballasts

Cat. No.	Primary Lamp	No. of Lamps	Input Voltage	Ballast Code	Total Lamp Length	Master
S5290	T12/RS/HO	1-2	120	MSB-12-0412-TP	4 ft. to 12 ft.	1
S5291	T12/RS/HO	2-4	120	MSB-24-0620-TP	6 ft. to 20 ft.	1
S5292	T12/RS/HO	2-4	120	MSB-24-1224-TP	12 ft. to 24 ft.	1
S5293	T12/RS/HO	2-4	120	MSB-24-2040-TP	20 ft. to 40 ft.	1
S5294	T12/RS/HO	4-6	120	MSB-46-1240-TP	12 ft. to 40ft.	1
S5295	T12/RS/HO	4-6	120	MSB-46-2448-TP	24 ft. to 48 ft.	1
Listed for all T12 HO lamps 18" thru 96": F18T12, F24T12, F30T12, F42T12, F48T12/SS, F48T12, F60T12, F64T12, F72T12, F84T12, F96T12/SS, F96T12/CT, F96T12						

T12 VHO (1500mA) Rapid Start Ballasts

Cat. No.	Primary Lamp	No. of Lamps	Input Voltage	Ballast Code	Sound Rating	Power Factor	Master
S5264	F96T12/VHO	1	120	MB1X96VHO/120RS/SRNK	Class D	HPF	4
S5265	F96T12/VHO	1	277	MB1X96VHO/277RS/SRNK	Class D	HPF	4
S5266	F96T12/VHO	2	120	MB2X96VHO/120RS/SRNK	Class D	HPF	4
S5267	F96T12/VHO	2	277	MB2X96VHO/277RS/SRNK	Class D	HPF	4
Listed for: F48T12/VHO, F60T12/VHO, F72T12/VHO, F96T12/VHO/SS, F96T12/VHO							

Rapid Start HO



Rapid Start Sign HO



Rapid Start VHO



T2 Rapid Start FM Dedicated Voltage Ballasts

Cat. No.	Primary Lamp	No. of Lamps	Input Voltage	Ballast Code	Wiring Method	Master
Y49735	FM6 or FM8	1	120	QT1X6-8FM/120	Wiretap Connectors	50
Y49736	FM11 or FM13	1	120	QT1X11-13FM/120	Wiretap Connectors	50

T5 Programmed Start, < 10% THD, Universal Voltage Ballasts

Cat. No.	Primary Lamp	No. of Lamps	Input Voltage	Ballast Code	Wiring Method	Master
S5221	FP28T5	1	120/277	QTP1X28T5/UNIV/PSN/NL	Wiretap Connectors	20
S5222	FP28T5	2	120/277	QTP2X28T5/UNIV/PSN/NL	Wiretap Connectors	20
Listed for: FP14, FP21, FP28, FP35 Lamp(s)						

T5HO Programmed Start, < 10% THD, Universal Voltage Ballasts

Cat. No.	Primary Lamp	No. of Lamps	Input Voltage	Ballast Code	Wiring Method	Master
S5214	FP24T5	1	120/277	QTP1X39/24T5HO/UNV/PSN/NL	Wiretap Connectors	20
S5215	FP24T5	2	120/277	QTP2X39/24T5HO/UNV/PSN/NL	Wiretap Connectors	20
Listed for: FPC22T5, FPC24T5HO, FT24DL, CF24DF, FT36DL, FP39T5HO, FPC40T5 Lamp(s)						
S5218	FP54T5	1	120/277	QTP1X54T5HO/UNV/PSN/NL	Wiretap Connectors	20
S5219	FP54T5	2	120/277	QTP2X54T5HO/UNV/PSN/NL	Wiretap Connectors	20
Listed for: FP54T5/HO, FT55DL, FPC55 Lamp(s)						
S5220	FP80T5	1	120/277	QTP1X80T5HO/UNV/PSN/NL	Wiretap Connectors	20
Listed for: FP54T5/HO, FT80DL Lamp(s)						

T8 Instant Start, Professional < 10% THD, Universal Voltage Ballasts

Cat. No.	Primary Lamp	No. of Lamps	Input Voltage	Ballast Code	Wiring Method	Master
S5207	F32T8	1	120/277	QTP1X32T8/UNIV/ISN/SC	Leads	10
S5208	F32T8	2	120/277	QTP2X32T8/UNIV/ISN/SC	Leads	10
S5209	F32T8	3	120/277	QTP3X32T8/UNIV/ISN/SC	Leads	10
S5210	F32T8	4	120/277	QTP4X32T8/UNIV/ISN/SC	Leads	10
Listed for: FBO16, FO17, FBO24, FO25, FBO31, FO32, FO40 & SS Equivalents						
Can operate 1 lamp on 2 lamp ballast, 2 lamps on 3 lamp ballast, 3 lamps on 4 lamp ballast						
For 40T8 operation use 1 lamp on 2 lamp ballast, 2 lamps on 3 lamp ballast, 3 lamps on 4 lamp ballast						

T2 Subminiature



T5 Programmed Start



T8 Instant Start Professional



T8 Programmed (Rapid) Start, Professional < 10% THD, Universal Voltage Ballasts

Cat. No.	Primary Lamp	No. of Lamps	Input Voltage	Ballast Code	Wiring Method	Master
S5286	F32T8	1	120/277	QTP1X32T8/UNIV/PSN/TC	Leads	10
S5287	F32T8	2	120/277	QTP2X32T8/UNIV/PSN/TC	Leads	10
S5288	F32T8	3	120/277	QTP3X32T8/UNIV/PSN/TC	Leads	10
S5289	F32T8	4	120/277	QTP4X32T8/UNIV/PSN/TC	Leads	10
Listed for: FBO16, FO17, FBO24, FO25, FBO31, FO32, FBO32 & SS Equivalents						
Can operate 1 lamp on 2 lamp ballast, 2 lamps on 3 lamp ballast, 3 lamps on 4 lamp ballast						
For 40T8 operation use 1 lamp on 2 lamp ballast, 2 lamps on 3 lamp ballast, 3 lamps on 4 lamp ballast						

T8 Instant Start, Professional < 10% THD, Universal Voltage Ballasts

Cat. No.	Primary Lamp	No. of Lamps	Input Voltage	Ballast Code	Wiring Method	Master
S5213	F96T8	2	120/277	QT2X59T8/UNIV/ISN/SC	Leads	10
Listed for: FO96T8 & SS Equivalents						
Can operate 1 lamp on 2 lamp ballast						

T12 Rapid Start, < 10% THD, Dedicated Voltage Ballasts

Cat. No.	Primary Lamp	No. of Lamps	Input Voltage	Ballast Code	Wiring Method	Master
S5258	F40T12	1	120	QT1X40T12/120/RSN B	Leads	20
S5259	F40T12	1	277	QT1X40T12/277/RSN B	Leads	20
S5260	F40T12	2	120	QT2X40T12/120/RSN B	Leads	20
S5261	F40T12	2	277	QT2X40T12/277/RSN B	Leads	20
S5262	F40T12	3	120	QT3X40T12/120/RSN B	Leads	20
S5263	F40T12	3	277	QT3X40T12/277/RSN B	Leads	20
Listed for: F34T12, FB34T12, F40T12, FB40T12, F40T10 Lamp(s)						

T8 Rapid Start Professional



T8 Instant Start Professional



T12 Rapid Start



Electronic

FT40DL Instant Start, < 10% THD, Universal Voltage Ballasts

Cat. No.	Primary Lamp	No. of Lamps	Input Voltage	Ballast Code	Wiring Method	Master
Y49428	FT40TT5	1	120/277	QHE1X40DL/UNIV ISN-SC	Leads	10
Y49429	FT40TT5	2	120/277	QHE2X40DL/UNIV ISN-SC	Leads	10
Y49430	FT40TT5	3	120/277	QHE3X40DL/UNIV ISN-SC	Leads	10
Listed for: FT40DL/28W/SS/IS						

Compact Fluorescent Programmed Start, < 10% THD, Universal Voltage Ballasts

Cat. No.	Primary Lamp	No. of Lamps	Input Voltage	Ballast Code	Wiring Method	Master
S5223	CF13	1/2	120/277	QTP1/2X13CF/UNV/BS	Wiretap Connectors	20
S5225	CF13	1/2	120/277	QTP1/2X13CF/UNV/TS	Wiretap Connectors	20
Listed for: 1 or 2 CF13DD/E or CF13DT/E Lamp(s)						
S5226	CF18	1/2	120/277	QTP1/2X18CF/UNV/BS	Wiretap Connectors	20
S5228	CF18	1/2	120/277	QTP1/2X18CF/UNV/TS	Wiretap Connectors	20
Listed for: 1 or 2 CF18DD/E or CF18DT/E Lamp(s)						
S5229	CF26	1/2	120/277	QTP1/2X26CF/UNV/Dual Entry	Wiretap Connectors	20
Listed for: 1 or 2 CF26DD/E or CF26DT/E Lamp(s)						
Also Listed for: 1 ea. CF32DT/E, CF42DT/E, F28/2D, F38/2D, FPC40T5, FT40DL Lamp						
Also Listed for: 2 ea. CF13DS/E, FT18DL/RS, CF18DF, F21/2D Lamps						
S5233	CF26	1/2	120/277	QTP1/2CF/UNV/PM	Wiretap Connectors	18
Listed for: 1 or 2 CF26DD/E or CF26DT/E Lamp(s)						
Also Listed for: 1 ea. CF32DT/E or CF42DT/E Lamp						
S5235	CF26	2	120/277	QTP1/2CF/UNV/Dual Entry	Wiretap Connectors	20
Listed for: 1 or 2 CF26DD/E or CF26DT/E Lamp(s)						
Also Listed for: 1 ea. CF32DT/E or CF42DT/E Lamp						

Circline Instant Start, < 10% THD, Dedicated Voltage Ballasts

Cat. No.	Primary Lamp	No. of Lamps	Input Voltage	Ballast Code	Wiring Method	Master
S5296	FC8	1	120	MB1X22/120/W SOCKET	Leads & Socket	60
S5297	FC12, FC16, FC30	1	120	LC12014TW/ SOCKET	Leads & Sockets	48
S5298	FC8 & FC12	2	120	MB1X22&32/W SOCKET	Leads & Sockets	32
S5299	FC12 & FC16	2	120	SL26TW/ SOCKET	Leads & Sockets	32

F40DL Instant Start



CFL Programmed Start



Circline Instant Start





Switches & Accessories













Switches (Rotary, Push, Pull Chain, Toggle) 92-95
Dimmer Controls & Switches 96-97
Attachment Plugs 98
Cord Switches 99
Rocker Switches & Receptacles 100
Touch & Photoelectric Switches 101-102
Socket Extenders, Reducers & Adapters 103-105
Outlets (Plug-In & Add-On) 106

On-Off • 3-Way

On-Off Metal Rotary Switch, Metal Bushing, Single Circuit. Rated: 6A-125V, 3A-250V

Item No.	Finish	Function	Bushing	Leads	Strip	Packed
80-1132	Brass	On-Off	3/8"	6"	3/4"	250
90-501	Brass	On-Off	3/8"	6"	3/4"	250
80-1133	Nickel	On-Off	3/8"	6"	3/4"	250
90-507	Nickel	On-Off	3/8"	6"	3/4"	250
80-1134	Brass	On-Off	5/8"	6"	3/4"	250
80-1135	Nickel	On-Off	5/8"	6"	3/4"	250
80-1363	Brass	On-Off	1 ⅛"	6"	3/4"	250
80-1364	Nickel	On-Off	1 ⅛"	6"	3/4"	250
80-1413	Brass	On-Off	1 ½"	6"	3/4"	250
80-1414	Nickel	On-Off	1 ½"	6"	3/4"	250



80-1132 *Brass Finish*

3-Way Metal Rotary Switch, Metal Bushing, 2 Circuit, 4 Position(L-1, L-2, L1-2, Off). Rated: 6A-125V, 3A-250V

Item No.	Finish	Function	Bushing	Leads	Strip	Packed
80-1136	Brass	3-Way	3/8"	6"	3/4"	250
90-504	Brass	3-Way	3/8"	6"	3/4"	250
80-1137	Nickel	3-Way	3/8"	6"	3/4"	250
90-590	Nickel	3-Way	3/8"	6"	3/4"	250
80-1138	Brass	3-Way	5/8"	6"	3/4"	250
80-1139	Nickel	3-Way	5/8"	6"	3/4"	250
80-1365	Brass	3-Way	1 ⅛"	6"	3/4"	250
80-1366	Nickel	3-Way	1 ⅛"	6"	3/4"	250
80-1415	Brass	3-Way	1 ½"	6"	3/4"	250
80-1416	Nickel	3-Way	1 ½"	6"	3/4"	250



80-1136 *Brass Finish*

On-Off Lighted Rotary Switch, Plastic Bushing, Single Circuit. Rated: 6A-125V, 3A-250V

Item No.	Finish	Function	Bushing	Leads	Strip	Packed
80-1359	Brass	On-Off	3/8"	6"	3/4"	250
80-1360	Nickel	On-Off	3/8"	6"	3/4"	250



80-1360 *Nickel Finish*

3-Way Lighted Rotary Switch, Plastic Bushing, 2 Circuit, 4 Position(L-1, L-2, L1-2, Off). Rated: 6A-125V, 3A-250V

Item No.	Finish	Function	Bushing	Leads	Strip	Packed
80-1361	Brass	3-Way	3/8"	6"	3/4"	250
80-1362	Nickel	3-Way	3/8"	6"	3/4"	250



80-1361 *Brass Finish*

On-Off Metal Push Switch, Metal Bushing, Single Circuit. Rated: 6A-125V, 3A-250V

Item No.	Finish	Function	Bushing	Leads	Strip	Packed
80-1124	Brass	On-Off	3/8"	6"	3/4"	250
90-508	Brass	On-Off	3/8"	6"	3/4"	250
80-1125	Nickel	On-Off	3/8"	6"	3/4"	250
90-1676	Nickel	On-Off	3/8"	6"	3/4"	250
80-1126	Brass	On-Off	5/8"	6"	3/4"	250
80-1127	Nickel	On-Off	5/8"	6"	3/4"	250
80-1367	Brass	On-Off	1 ⅛"	6"	3/4"	250
80-1368	Nickel	On-Off	1 ⅛"	6"	3/4"	250
80-1409	Brass	On-Off	1 ½"	6"	3/4"	250
80-1410	Nickel	On-Off	1 ½"	6"	3/4"	250



80-1124 *Brass Finish*

3-Way Metal Push Switch, Metal Bushing, 2 Circuit, 4 Position(L-1, L-2, L1-2, Off). Rated: 6A-125V, 3A-250V

Item No.	Finish	Function	Bushing	Leads	Strip	Packed
80-1128	Brass	3-Way	3/8"	6"	3/4"	250
90-1678	Brass	3-Way	3/8"	6"	3/4"	250
80-1129	Nickel	3-Way	3/8"	6"	3/4"	250
90-1679	Nickel	3-Way	3/8"	6"	3/4"	250
80-1130	Brass	3-Way	5/8"	6"	3/4"	250
80-1131	Nickel	3-Way	5/8"	6"	3/4"	250
80-1369	Brass	3-Way	1 ⅛"	6"	3/4"	250
80-1370	Nickel	3-Way	1 ⅛"	6"	3/4"	250
80-1411	Brass	3-Way	1 ½"	6"	3/4"	250
80-1412	Nickel	3-Way	1 ½"	6"	3/4"	250



80-1128 *Brass Finish*

On-Off Lighted Push Switch, Plastic Bushing, Single Circuit. Rated: 6A-125V, 3A-250V

Item No.	Finish	Function	Bushing	Leads	Strip	Packed
80-1355	Brass	On-Off	3/8"	6"	3/4"	250
80-1356	Nickel	On-Off	3/8"	6"	3/4"	250



80-1356 *Nickel Finish*

3-Way Lighted Push Switch, Plastic Bushing, 2 Circuit, 4 Position(L-1, L-2, L1-2, Off). Rated: 6A-125V, 3A-250V

Item No.	Finish	Function	Bushing	Leads	Strip	Packed
80-1357	Brass	3-Way	3/8"	6"	3/4"	250
80-1358	Nickel	3-Way	3/8"	6"	3/4"	250



80-1357 *Brass Finish*

Canopy & Ceiling Fan



90-704 Brass Finish

On-Off Canopy Switch, Single Circuit w/Metal Chain, White Cord & Bell – Rated: 6A-125V, 3A-250V

Item No.	Finish	Function	Bushing	Leads	Strip	Packed
90-704	Brass	On-Off	3/8"	6"	3/4"	250
90-505	Nickel	On-Off	3/8"	6"	3/4"	250



90-2260 Brass Finish

3 Way Canopy Switch, 2 Circuit, 4 Position w/Metal Chain, White Cord & Bell – Rated: 6A-125V, 3A-250V

Item No.	Finish	Function	Bushing	Leads	Strip	Packed
90-2260	Brass	4 Position	3/8"	6"	3/4"	250
90-2261	Nickel	4 Position	3/8"	6"	3/4"	250



90-689 Nickel Finish

3 Way Ceiling Fan Switch, 2 Circuit w/Metal Chain, White Cord & Bell – Rated: 6A-125V, 3A-250V

Item No.	Finish	Function	Bushing	Leads	Strip	Packed
90-689	Nickel	3 Way	3/8"	6"	3/4"	250



90-690 Nickel Finish

3 Speed Ceiling Fan Switch, 4 Wire Quick Connect, 2 Circuit w/Metal Chain, White Cord & Bell – Rated: 6A-125V, 3A-250V

Item No.	Finish	Function	Bushing	Leads	Strip	Packed
80-1983	Nickel	3 Speed	3/8"	None	N/A	250
80-1994	Brass	3 Speed	3/8"	None	N/A	250

2 Speed Ceiling Fan Switch, 4 Position w/Metal Chain, White Cord & Bell – Rated: 6A-125V, 3A-250V

Item No.	Finish	Function	Bushing	Leads	Strip	Packed
90-690	Nickel	2 Speed	3/8"	6"	3/4"	250

On-Off Phenolic Rotary Switch, Single Circuit
Rated: 1A-125V, 3A-125V, 1.5A-250V

Item No.	Finish	Function	Bushing	Leads	Strip	Packed
90-502	Black	On-Off	3/8"	6"	3/4"	250
90-703	White	On-Off	3/8"	6"	3/4"	250
80-1770	Black	On-Off	Snap	6"	3/4"	250
80-1771	White	On-Off	Snap	6"	3/4"	250



90-502 Black (bushing)



80-1770 Black (snap)

Hi-Low Metal Rotary Switch w/Diode, 2 Circuit
Rated: 6A-125V, 3A-250V

Item No.	Finish	Function	Bushing	Leads	Strip	Packed
80-1140	Brass	On-Off	3/8"	6"	3/4"	250



80-1140 Brass Finish

On-Off Metal Toggle Switch, Single Circuit
Rated: 6A-125V, 3A-250V

Item No.	Finish	Function	Bushing	Leads	Strip	Packed
90-1106	Nickel	On-Off	3/8"	6"	3/4"	250
80-1767	Brass	On-Off	3/8"	6"	3/4"	250



90-1106 Nickel Finish

Slide • Step On



90-1069 White 4¾" x 2½" x 1½"

Slide – Floor Lamp Dimmer
Rated: 500W-120V 4.3A

Item No.	Finish	Length	Wire	Receptacle	Packed
90-1069	White	7 ft.	SPT-2 White	Yes	50/1
90-1070	Black	7 ft.	SPT-2 Black	Yes	50/1



80-1244 Black 4¾" x 2½" x 1½"

Slide – 2-Wire Floor Lamp Dimmer
Rated: 500W-120V 4.3A

Item No.	Finish	Length	Wire	Receptacle	Packed
80-1244	Black	8 ft. x 8 ft.	SPT-2 Black	No	50/1



93-5012 Black 1½" x 1" x 3½"

Slide – Table Top Lamp Dimmer
Rated: 300W-120V

Item No.	Finish	Length	Wire	Receptacle	Packed
93-5011	White	8 ft.	SPT-2 White	Yes	24
93-5012	Black	8 ft.	SPT-2 Black	Yes	24



93-5016 Brown 3" x ¾" x 1⅜"

Slide – Lamp Cord Table Dimmer – No Wire
Rated: 300W-120V for SPT-2 Wire Only

Item No.	Finish	Connectors	Receptacle	Packed
93-5014	White	Quick Terminals	No	24/1
93-5016	Brown	Quick Terminals	No	24/1



80-1163 Black 1⅓" x 2"

Step-on-Button On/Off Push Switch
Rated: 2A-125V, 1A-125V, 1A-250V,

Item No.	Finish	Length	Wire	Receptacle	Packed
80-1163	Black	(Terminal)	No	No	250/1
80-1466	White	(Terminal)	No	No	250/1
80-1229	Black	8 ft. x 7 ft.	SPT-2 Black	No	50/1
80-1381	Black	8 ft. x 11 ft.	SPT-2 Black	No	50/1

Full Range Dimmer Switches



80-1166

Full Range Table Lamp Dimmer Switch
Phenolic Housing Black 300W Dimmer
2" x 1¼" x 1⅛"
12" AWM 105°C Black Leads Strip 1/2"
w/Two Knobs: Black & Gold
300W-120V



80-1293

Full Range Table Lamp Dimmer Switch
Paper Housing 300W Dimmer
2" x 1¼" x ⅝"
12" AWM 105°C Black Leads Strip 1/2"
w/Two Knobs: Black & Gold
60-300W-120V



80-1241

Full Range Table Lamp Dimmer Switch
Phenolic Housing Black 300W Dimmer
2" x 1¼" x 1½"
12" AWM 105°C Black Leads Strip 1/2"
w/One Knob: Black
300W-120V



90-1082

Full Range Pole Lamp Dimmer Switch
Paper Housing
4¾" x ¾"
500W Pole or Post Lamp Dimmer
w/One End 2 Foot Leads SPT-1 Black
Other End 7" SPT-1, Strip 1/2"
w/One Brass Knob
500W-120V



80-1481 *Brown*
80-1482 *Ivory*

Full Range Lamp Cord
Rotary Dimmer Switch
3" x 1¼"
Phenolic – 200W-120V



80-1167

Full Range Socket Dimmer
Medium Base
Candle Socket w/Paper Liner
150W Full Range w/Removable Black Knob
4" x 1¾"
1/8 IP Bushing w/Set Screw
5½" AWM B/W150°C Leads Strip1/2"
150W-120V

Plastic Dimmer Knobs



90-798

Gold Finish Knob



90-799

Chrome Finish Knob



90-2315

Black Knob

SPT–1



Attachment Plug
Polarized 18/2–SPT-1

90-393 Ivory
90-394 Brown

SPT–1



Quick Connect Plug
Non Polarized 18/2–SPT-1

90-631 White
90-632 Brown

SPT–1



Quick Connect Plug
Polarized 18/2–SPT-1

90-1520 White
90-1521 Brown
90-1522 Black

SPT–1



Slide Plug–Polarized
18/2–SPT-1 8A-125V

90-715 Brown
90-716 Ivory
90-719 Black
90-2041 Gold
90-2245 Silver
90-2605 White

SPT–1



Female Slide Plug
Polarized 18/2–SPT-1

90-793 Brown
90-794 Ivory

SPT–2



Slide Plug–Polarized
18/2–SPT-2 8A-125V

90-695 Brown
90-696 Ivory
90-697 Black
90-2040 Gold
90-2244 Silver
90-2606 White

SPT–2



Quick Connect Plug
Polarized 18/2–SPT-2

90-2607 White
90-2608 Brown
90-2609 Black
90-2617 Gold
90-2618 Silver

SPT–2



Quick Connect Flat Plug
Non Polarized
18/2–SPT-2

90-1083 White
90-1084 Brown

SVT



Attachment Plug
with Terminal Screws
18/2–SVT Round Wire

90-1114 Brown
90-1115 White
90-1116 Black

SVT



3 Prong Rubber Plug
with Metal Grip
18/3–SVT Round Wire
15A-125V

80-1688 Black

SPT–1



On-Off Cord Switch
for 18/2 SPT-1
6A–125V 3A–250V 3A–125V

90-500 White **90-814** Black
90-506 Brown **90-2587** Ivory



On-Off Cord Switch
for 18/2 SPT-1
3A–120V

90-2424 Gold
90-2425 Silver

SPT–2



On-Off Cord Switch
for 18/2 SPT-2
6A–125V 3A–250V 3A–125V

90-573 White **90-825** Black
90-574 Brown **90-2629** Ivory



On-Off Cord Switch
for 18/2 SPT-2
3A–120V

90-2426 Gold
90-2427 Silver

SPT–1



200 Watt Hi–Low Dimmer
for 18/2 SPT-1
200W-120V

90-436 White
90-435 Brown

SPT–2



200 Watt Hi–Low Dimmer
for 18/2 SPT-2
200W-120V

90-820 White
90-821 Brown

SPT–1 / SPT–2 / SVT



Heavy Duty Rocker Switch
for 18/2 SPT-1 & SPT-2, 16/2 SPT-2 &
18/2 SVT 3A-125V 1/2HP-125V

90-434 Ivory
90-433 Brown

SPT–2



Feed Thru Rocker Switch
for 18/2 SPT-2 3A-120V

90-2368 Black **90-2371** Silver
90-2369 White **90-2372** Gold
90-2370 Brown

Snap-In *On-Off • Hi-Low*



80-1819 Black Lighted



80-1820 White Lighted



80-1141 Black

On-Off Phenolic Rocker Switch w/Dot

Item No.	Finish	Function	Bushing	Leads	Strip	Rating	Packed
80-1141	Black	On-Off	Snap	6"	3/4"	15A-125V, 10A-250V	250
80-1617	White	On-Off	Snap	6"	3/4"	15A-125V, 10A-250V	250
80-1819	Black	Lighted On-Off	Snap	9"	3/4"	15A-125V, 10A-250V	250
80-1820	White	Lighted On-Off	Snap	9"	3/4"	15A-125V, 10A-250V	250
80-1947	Black	On-Off (small)	Snap	6"	3/4"	10A-125V, 6A-250V	250
80-1980	Black	On-Off (mini)	Snap	6"	3/4"	6A-125V, 3A-250V	250
80-2037	White	On-Off (mini)	Snap	6"	3/4"	6A-125V, 3A-250V	250



80-1371 Black



Hi-Low Metal Round Rocker Switch w/Diode
2 Circuit, Rated: 6A-250V, 10A-125V

Item No.	Finish	Function	Bushing	Leads	Strip	Packed
80-1371	Black	Hi-Off-Low	Snap-In	6"	3/4"	250
80-2101	Black	On-Off	Snap-In	6"	3/4"	250



80-1142 Black

3 Wire, 2 Pole Snap-In Convenience Outlet,
Opening Size: 1" x 1" x 1" Rated: 15A-125V

Item No.	Finish	Wire	Bushing	Leads	Strip	Packed
80-1142	Black	3 Wire	Snap-In	6"	3/4"	250
80-1408	White	3 Wire	Snap-In	6"	3/4"	250



90-545 Black

2 Wire Snap-In Convenience Outlet,
Opening Size: 1⅛" x 1/2" x 7/8" Rated: 15A-125V

Item No.	Finish	Wire	Bushing	Leads	Strip	Packed
90-545	Black	2 Wire	Snap-In	6"	3/4"	250

Mechanical Photoelectric Switches



90-2430 Photoelectric Switch
Plastic DOS Shell Rated: 25W-125V
Indoor Use Only
5/8" x 5/8" x 3/8"



90-2431 Photoelectric Switch
Plastic DOS Shell Rated: 100W-120V
Indoor Use Only
1 1/2" x 5/8" x 1 1/8"



90-2432 Photoelectric Switch
Plastic DOS Shell Rated: 250W-120V
Indoor Use Only
1 3/16" x 5/8" x 1 1/4"



80-1733 Photoelectric Switch
Plastic DOS Shell Rated: 500W-120V
For Outdoor Use
2" x 1 3/4" x 1 1/4"



90-2611 Photoelectric Switch
Plastic DOS Shell Rated: 100W-125V
For Outdoor Use
1 1/2" x 1 1/8" x 1"



90-2633 Photoelectric Switch
Plastic DOS Shell Rated: 500W-120V
7.1A-850VA Ballast
For Outdoor Use – HID
2" x 1 3/4" x 1 1/4"

Plastic Shell *On-Off • Hi-Med-Low*

Touch Controls



90-2428 Low-Med-Hi-Off Touch Switch
Plastic Outer Shell. Rated: 150W-120V
Indoor Incandescent Use Only
1⅞" x 1⅜" x ⅝"



90-2429 On-Off Touch Switch
Plastic Outer Shell. Rated: 150W-120V
Indoor Incandescent Use Only
1⅞" x 1⅜" x ⅝"

Touch Control Wiring Diagram





80-1888 White
Medium to GU24 Reducer
E26 - GU24
with Locking Device
Overall Ext. ¾"
660W-600V



90-2434 White
Medium to GU24 Reducer
E26 - GU24
(no locking feature)
Overall Ext. ¾"
660W-250V



80-1970 Brown
Medium Based Phenolic
E26
Flanged Adapter w/10" Leads
Overall Ext. ½"
660W-250V



90-2433 White
Medium to GU10 Reducer
E26 - GU10
(no locking feature)
Overall Ext. ¾"
660W-250V

Photocell Adapters



90-2610 White
Medium to GU24 Adapter
E26 - GU24
with Photocell
Overall Ext. 1⅛"
60W-120V



90-2604 Brown
Medium to Medium Adapter
E26 - E26
with Photocell
Overall Ext. 2"
150W-120V (incandescent)
60W-120V (fluorescent)
Suitable for Dry or Damp Location

SOCKET EXTENDERS & ADAPTERS



92-408
Candelabra to Candelabra
E12 - E12 Extender



92-405
Candelabra to Intermediate
E12 - E17 Extender



90-1519
Candelabra to Medium
E12 - E26 Extender



92-407
French to Intermediate
E14 - E17 Extender



90-1801
Mogul to Mogul
E39 - E39 Extender
4KV – Porcelain
Overall Ext. 2⅜"
1500W-600V



92-414
Medium to Mogul
E26 - E39 Extender
Overall Ext. 1¾"
660W-250V



92-323
Medium to Medium
E26 - E26 Extender
Phenolic
Overall Ext. 1"
660W-250V



92-324
Medium to Medium
E26 - E26 Extender
Porcelain
Overall Ext. 1"
660W-250V



90-2589
Medium to Medium E26 - E26
2 Piece Glazed Porcelain Extender
Overall Ext. 1¼"
660W-250V



90-446 *Brown*
90-2451 *Ivory*
Medium Base
Pull Chain Current Tap
660W-125V



90-2449 *Brown*
90-2450 *Ivory*
Medium Base
Keyless Current Tap
660W-125V



90-1121 *Brown*
90-2465 *Ivory*
Single to Twin Lampholder
660W Max. Total-250V



92-400
Medium to Candelabra E26 - E12 Reducer 75W-250V



92-321
Medium to French E26 - E14 Reducer 75W-250V



92-322
Medium to Intermediate E26 - E17 Reducer 75W-250V



92-401
French to Candelabra E14 - E12 Reducer



92-403
Intermediate to Candelabra E17 - E12 Reducer



92-406
Mogul to Medium E39 - E26 Reducer 660W-250V



90-546 *Ivory*
Medium Base – Polarized Socket Outlet Adapter 660W-125V



90-547 *Brown*
Medium Base – Polarized Socket Outlet Adapter 660W-125V



90-438 *Ivory*
Medium Base – Polarized Socket Outlet Adapter 660W-125V



90-437 *Brown*
Medium Base – Polarized Socket Outlet Adapter 660W-125V

Plug-In • Add-On



c UL us LISTED

90-1120 Ivory
Triple Cube Tap
Polarized
15A-125V



c UL us LISTED

90-1119 Brown
Triple Cube Tap
Polarized
15A-125V



c UL us LISTED

90-1118 Ivory
Single to Triple Adapter
Polarized
15A-125V



c UL us LISTED

90-1117 Brown
Single to Triple Adapter
Polarized
15A-125V



UL

91-227 White
Single to Triple Adapter
With Glow Light
15A-125V, 1875W





UL

90-2630 Ivory
6 Outlet Grounded Adapter
15A-125V



UL

90-806
Three to Two Adapter
Polarized
15A-125V



90-1404 White
90-1405 Brown
Add-On Outlet
18/2 SPT-1
10A-125V

Wire, Cords & Accessories















Bulk Wire 108-113
Cord Sets 114-119
Extension Cords & Surge Suppressors 120-125
Wire Covers 126
Wire Nuts & Electrical Tape 127
Bushings 128

Lamp & Lighting Wire *Spools*



18/2 SPT–1 105°C 250 Ft./Spool

93-130	White
93-132	Black
93-131	Brown
93-138	Clear Silver
93-139	Clear Gold
93-140	Metallic Gold
93-241	Ivory

Packing: 8 Spools/Master



18/2 SPT–1.5 105°C 250 Ft./Spool

93-336	Clear Gold
93-337	Clear Silver
93-338	Black
93-343	Brown

Packing: 4 Spools/Master



18/2 SPT–2 105°C 250 Ft./Spool

93-127	Black
93-168	Clear Silver
93-129	Clear Gold
93-126	White
93-128	Brown

Packing: 4 Spools/Master



16/2 SPT–2 105°C 250 Ft./Spool

93-141	White
93-142	Brown
93-165	Clear Gold
93-166	Black
93-167	Clear Silver

Packing: 4 Spools/Master

18/2 SJT 105°C Pulley Cord
250 Ft./Spool

93-311 Black
93-312 White

Packing: 2 Spools/Master



18/3 SJT 105°C Pulley Cord
250 Ft./Spool

93-313 Black
93-314 White

Packing: 2 Spools/Master



18/2 SVT 105°C Pulley Cord
250 Ft./Spool

93-183 Black
93-150 White

Packing: 4 Spools/Master



18/3 SVT 105°C Pulley Cord
250 Ft./Spool

93-182 Black
93-144 White

Packing: 4 Spools/Master



18/3 SVT 105°C Pulley Cord
250 Ft./Spool (non UL Listed)

93-332 Clear Silver
93-333 Clear Gold

Packing: 4 Spools/Master



18/3 FEP PVC 600V
High Temperature 105°C
Teflon Wire – Tinned Copper
250 Ft./Spool

93-340 Clear Silver

Packing: 2 Spools/Master



Lighting Wire *Spools*



18/1 Stranded AWM 105°C UL 1015 Wire 500 Ft./Spool

93-315 Black
93-316 White
93-317 Green

Packing: 4 Spools/Master



18/1 Solid 105°C AWM TFN-PVC Nylon Wire 500 Ft./Spool

93-203 White
93-204 Black
93-341 Green



18/1 Stranded UL 1316 105°C AWM TFN-PVC Nylon Wire 1000 Ft./Spool

93-329 White
93-330 Black



18/1 Stranded AWM UL 3173 125°C Wire 500 Ft./Spool

93-318 Black
93-319 White



18/1 Stranded AWM UL 3321 150°C Wire 500 Ft./Spool

93-320 Black
93-321 White



18/1 Stranded Braid 200°C SF-1 Wire 250 Ft./Spool

93-205 White
93-206 Black

18/1 Rayon Braid 90°C Wire
250 Ft./Spool

93-207 Gold
93-208 Gold with Red Marker



18/2 Rayon Braid 90°C Wire
250 Ft./Spool

93-209 White
93-210 Brown
93-211 Black
93-212 Gold



20/2 PLT 105°C Wire
250 Ft./Spool

93-134 Clear Gold
93-186 Black
93-187 Clear Silver
93-188 Brown



22/2 PLT 105°C Wire
250 Ft./Spool

93-133 Clear Gold
93-184 Black
93-185 Clear Silver
93-189 Brown



18/1 Grounding Wire 500 Ft./Spool

93-110 Bare Copper
93-115 Tinned Copper





Ground Wires *with Lugs*



93-322 1/8 IP Round Ground Lug with 10Ft. 18/1 Bare Copper Ground Wire

80-1964 1/8 IP Round Ground Lug with 12" 18/1 Bare Copper Ground Wire



93-334 1/8 IP Round Ground Lug with 10Ft. 18/1 Tinned Copper Ground Wire

80-1965 1/8 IP Round Ground Lug with 12" 18/1 Tinned Copper Ground Wire



93-335 1/4 IP Round Ground Lug with 10Ft. 18/1 Bare Copper Ground Wire

80-1966 1/4 IP Round Ground Lug with 12" 18/1 Bare Copper Ground Wire



93-325 1/4 IP Round Ground Lug with 10Ft. 18/1 Tinned Copper Ground Wire

80-1967 1/4 IP Round Ground Lug with 12" 18/1 Tinned Copper Ground Wire



93-326 8/32 Ground Lug with 10" 18/1 Bare Copper Ground Wire

18/2 SPT-1 105°C Wire 2500 Ft./Reel

93-300 Clear Gold
93-301 Clear Silver
93-302 Black

Packing: 1 Spool/Master



18/2 SPT-1.5 105°C Wire 2500 Ft./Reel

93-303 Clear Gold
93-304 Clear Silver
93-305 Black
93-339 Brown

Packing: 1 Spool/Master



18/2 SPT-2 105°C Wire 2500 Ft./Reel

93-306 Clear Gold
93-307 Clear Silver
93-308 Black
93-309 White
93-310 Brown

Packing: 1 Spool/Master





2,500 FT. REELS

SATCO®

18/2 SPT-1 *105°C*

18/2 SPT–1–105°C

Colors Available:



Ivory White Black Brown Clear Silver Clear Gold Metallic Gold



All Cord Sets – Molded Plug – Tinned Tips 3/4" Strip with 2" Slit

7 Ft.
36" Hank – 200 Ctn.

- 90-2416 Ivory
- 90-2417 White
- 90-2598 Brown

8 Ft.
36" Hank – 200 Ctn.

- 90-1523 White
- 90-1524 Brown
- 90-1525 Black
- 90-1526 Clear Gold
- 90-1527 Clear Silver
- 90-2418 Ivory
- 90-2392 Metallic Gold

10 Ft.
48" Hank – 150 Ctn.

- 90-2460 White
- 90-2461 Black
- 90-2462 Brown
- 90-2463 Clear Gold
- 90-2464 Clear Silver
- 90-2628 Ivory

12 Ft.
72" Hank – 150 Ctn.

- 90-2033 White
- 90-2034 Black
- 90-2035 Brown
- 90-2036 Clear Gold
- 90-2037 Clear Silver

15 Ft.
100 Ctn.

- 90-1528 White
- 90-1529 Brown
- 90-1530 Black
- 90-1531 Clear Gold
- 90-1532 Clear Silver

20 Ft.
100 Ctn.

- 90-1534 White
- 90-1535 Brown
- 90-1536 Black
- 90-1537 Clear Gold
- 90-1538 Clear Silver

18/2 SPT–2–105°C

All Cord Sets – Molded Plug – Tinned Tips 3/4" Strip with 2" Slit

8 Ft.
36" Hank – 200 Ctn.

90-100	White
90-101	Brown
90-102	Black
90-105	Clear Gold
90-967	Clear Silver

9 Ft.
36" Hank – 150 Ctn.

90-2038	Clear Gold
90-2039	Brown
90-2042	Black
90-2101	Clear Silver

10 Ft.
36" Hank – 150 Ctn.

90-2183	Clear Gold
90-2184	Clear Silver
90-2185	Black
90-2599	Brown

12 Ft.
72" Hank – 150 Ctn.

90-1413	White
90-1414	Brown
90-1415	Black
90-1416	Clear Gold
90-1417	Clear Silver

15 Ft.
100 Ctn.

90-103	Clear Gold
90-490	Brown
90-491	White
90-492	Black
90-493	Clear Silver

20 Ft.
50 Ctn.

90-496	Brown
90-497	White
90-498	Black
90-460	Clear Silver
90-462	Clear Gold



90-1566
Plug Cover

Colors Available:



White Black Brown Clear Silver Clear Gold



Flat Plug Cord Set 18/2 SPT–2–105°C

Molded Plug - Tinned Tips - 3/4" Strip with 2" Slit

Colors Available:



White *Black* *Brown* *Clear Silver* *Clear Gold*

8 Ft.	*90-2323*	*White*
36" Hank – 200 Ctn.	*90-2324*	*Brown*
	90-2321	*Black*
	90-2320	*Clear Gold*
	90-2322	*Clear Silver*

12 Ft.	*90-2390*	*Clear Gold*
72" Hank – 150 Ctn.		





90-1566

Plug Cover

Flat Plug Cord Set 18/3 SPT–2–105°C (Non UL)

Molded Plug - Tinned Tips - 3/4" Strip with 3" Slit

Colors Available:



Black *Clear Silver* *Clear Gold* *White*

10 Ft.	*90-2435*	*Black*
No Hank – 100 Ctn.	*90-2436*	*Clear Silver*
	90-2437	*Clear Gold*
	90-2459	*White*



Full Tinned Cord Sets18/2 SPT–2–105°C

Cord Sets - Molded Plug - Full Tinned Tips for Push-In Terminals - 3/4" Strip with 2" Slit

8 Ft.

36" Hank – 200 Ctn.

- **90-2043** Clear Gold
- **90-2044** Black
- **90-2046** Brown
- **90-2045** Clear Silver
- **90-2087** Clear Gold w/White Stripe
- **90-2186** Clear Gold w/White Stripe & Plug Guard

10 Ft.

36" Hank – 150 Ctn.

- **90-2596** Black

12 Ft.

72" Hank – 150 Ctn.

- **90-2047** Clear Gold
- **90-2048** Clear Silver

Colors Available:



Clear Gold/ White Stripe | Black | Brown | Clear Silver | Clear Gold



90-1566
Plug Cover



With Line Switches *8 Ft.*

Colors Available:



White *Black* *Brown* *Clear Silver* *Clear Gold*

8 Ft. Cord Sets with Line Switches

All Cord Sets – Molded Plug
Tinned tips 3/4" Strip with 2" Slit

SPT–1 18/2 SPT-1 105°C	**90-1581**	White	Switch 24" From Free End 36" Hank – 200 Ctn.
	90-1582	Brown	
	90-1583	Black	
	90-1584	Clear Gold	
	90-1585	Clear Silver	

SPT–2 18/2 SPT-2 105°C	**90-106**	White	Switch 24" From Free End 36" Hank – 200 Ctn
	90-107	Brown	
	90-723	Clear Gold	
	90-968	Clear Silver	
	90-1425	Black	





90-1566
Plug Cover

8Ft. Cord Sets w/Hi–Low Switch – 18/2 SPT-2 105°

SPT–2 18/2 SPT-2 105°C	**90-2309**	Clear Gold	Switch 29" From Free End 36" Hank – 100 Ctn
	90-2310	Clear Silver	



Heavy Duty Cord Set

18/3 SVT –105°C 3 Prong
Molded Plug, Stripped & Slit

90-2414	**8ft.**	White – 100 Ctn
90-2413	**10ft.**	White – 100 Ctn



90-2413 White

Heavy Duty Cord Set

18/3 SVT –105°C 3 Prong
Molded Plug, Stripped & Slit

Non UL Listed

90-2312	**10ft.**	Clear Silver – 100 Ctn
90-2313	**10ft.**	Clear Gold – 100 Ctn



90-2312 Clear Silver



90-2313 Clear Gold

Heavy Duty Cord Set

18/3 SVT –105°C
3 Prong Molded Plug
Stripped & Slit

90-2085	**8ft.**	Black – 100 Ctn
90-2086	**10ft.**	Black – 100 Ctn
90-2210	**12ft.**	Black – 50 Ctn
90-2243	**15ft.**	Black – 50 Ctn



Heavy Duty Cord Set

18/3 SJT –105°C
3 Prong Molded Plug
Stripped & Slit

90-2208	**6ft.**	Black – 100 Ctn
90-2209	**8ft.**	Black – 50 Ctn
90-2325	**10ft.**	Black – 50 Ctn



Coiled *12 Ft.(extended)*



12 FT. COILED (Extended) EXTENSION CORDS

All extension cords rated at 13A 125V 1625 watts maximum and supplied with safety cover to conceal unused outlets.

Indoor Use Only.

93-179	*Blue*
93-175	*Yellow*
93-170	*White*
93-174	*Red*
93-169	*Green*
93-173	*Black*

c UL us LISTED

Packing: *48/Master, 12/Inner, 1/Card*



EXTENSION CORDS 16/2 SPT-2

All extension cords rated at 13A 125V 1625 watts maximum and supplied with safety cover to conceal unused outlets.

Indoor Use Only.

White		*Brown*		*Green*	
93-192	6 ft.	**93-193**	6 ft.	**93-5020**	6 ft.
93-194	9 ft.	**93-195**	9 ft.	**93-5021**	9 ft.
93-196	12 ft.	**93-197**	12 ft.	**93-5022**	12 ft.
93-198	15 ft.	**93-199**	15 ft.	**93-5023**	15 ft.

Packing: 50/Master

SATCO®

Heavy Duty *16/3 • 14/3 • 12/3*



#14/3 Ga. SPT-3 Gray Air Conditioner/Appliance Cords

Item No.	Footage	Description	Amps	Wattage	Master/Inner
93-5000	3 ft.	14-3 SPT-3 Gray Cord w/Sleeve	15A/125V	1875W	24
93-5001	6 ft.	14-3 SPT-3 Gray Cord w/Sleeve	15A/125V	1875W	24
93-5002	9 ft.	14-3 SPT-3 Gray Cord w/Sleeve	15A/125V	1875W	12
93-5003	12 ft.	14-3 SPT-3 Gray Cord w/Sleeve	15A/125V	1875W	12
93-5004	15 ft.	14-3 SPT-3 Gray Cord w/Sleeve	15A/125V	1875W	12



#16/3 Ga. SJTW-3 Orange Outdoor Extension Cords

Item No.	Footage	Description	Amps	Wattage	Master/Inner
93-5034	8 ft.	16-3 SJTW-3 Orange Cord w/Sleeve	13A/125V	1625W	24
93-5035	15 ft.	16-3 SJTW-3 Orange Cord w/Sleeve	13A/125V	1625W	12
93-5005	25 ft.	16-3 SJTW-3 Orange Cord w/Sleeve	13A/125V	1625W	12
93-5006	50 ft.	16-3 SJTW-3 Orange Cord w/Sleeve	13A/125V	1625W	12
93-5007	100 ft.	16-3 SJTW-3 Orange Cord w/Sleeve	10A/125V	1250W	6



#14/3 Ga. SJTW-3 Orange Outdoor Extension Cords

Item No.	Footage	Description	Amps	Wattage	Master/Inner
93-5008	25 ft.	14-3 SJTW-3 Orange Cord w/Sleeve	15A/125V	1875W	12
93-5009	50 ft.	14-3 SJTW-3 Orange Cord w/Sleeve	15A/125V	1875W	6
93-5010	100 ft.	14-3 SJTW-3 Orange Cord w/Sleeve	13A/125V	1625W	6

#12/3 Ga. SJTW-3 Orange Outdoor Extension Cords

Item No.	Footage	Description	Amps	Wattage	Master/Inner
93-5017	25 ft.	12-3 SJTW-3 Orange Cord w/Sleeve	15A/125V	1875W	12
93-5018	50 ft.	12-3 SJTW-3 Orange Cord w/Sleeve	15A/125V	1875W	6
93-5019	100 ft.	12-3 SJTW-3 Orange Cord w/Sleeve	13A/125V	1625W	4

Heavy Duty *16/3 • 12/3*

#16/3 Ga. SJTW-3 Green Outdoor Extension Cords

Item No.	Footage	Description	Amps	Wattage	Master/Inner
93-5024	25 ft.	16-3 SJTW-3 Green Cord w/Sleeve	13A/125V	1625W	12
93-5025	50 ft.	16-3 SJTW-3 Green Cord w/Sleeve	13A/125V	1625W	12
93-5026	80 ft.	16-3 SJTW-3 Green Cord w/Sleeve	10A/125V	1250W	4





#16/3 Ga. SJTW-3 White Outdoor Extension Cords

Item No.	Footage	Description	Amps	Wattage	Master/Inner
93-5027	35 ft.	16-3 SJTW-3 White Cord w/Sleeve	13A/125V	1625W	6



#12/3 Ga. 3 Outlet Outdoor Extension Cord

Item No.	Footage	Description	Amps	Wattage	Master/Inner
93-5030	2 ft.	12-3 STW Orange 3 Outlet Cord	15A/125V	1875W	12



Heavy Duty *Dryer • Range • Trouble Light Cage*





Replacement Dryer Cords

Item No.	Footage	Description	Amps	Wattage	Master/Inner
93-5039	4 ft. – 3 Wire	10-3 SRDT Gray Flat	30A/125V-250V	7,500W	12
93-5028	6 ft. – 3 Wire	10-3 SRDT Gray Flat	30A/125V-250V	7,500W	12
93-5031	4 ft. – 4 Wire	10-4 SRDT Black Round	30A/125V-250V	7,500W	12
93-5029	6 ft. – 4 Wire	10-4 SRDT Black Round	30A/125V-250V	7,500W	12

Indoor Use Only





Replacement Range Cords

Item No.	Footage	Description	Amps	Wattage	Master/Inner
93-5032	3 ft. – 3 Wire	6-2 – 8-1 SRDT Gray Flat	50A/125V-250V	12,500W	12
93-5036	4 ft. – 3 Wire	6-2 – 8-1 SRDT Gray Flat	50A/125V-250V	12,500W	12
93-5037	6 ft. – 3 Wire	6-2 – 8-1 SRDT Gray Flat	50A/125V-250V	12,500W	12
93-5033	4 ft. – 4 Wire	6-2 – 8-2 SRDT Black Round	50A/125V-250V	12,500W	12
93-5038	6 ft. – 4 Wire	6-2 – 8-2 SRDT Black Round	50A/125V-250V	12,500W	12

Indoor Use Only

90-1310

Brass Finish Light Bulb Cage
Height: 5¼"
***Packing**: 60/Master 10/Inner*



90-2612

Yellow Trouble Light Plastic Cage
Suitable for Outdoor Locations
Height: 6½"
***Packing**: 12/Master*



80-1979

Wire Cage for Warehouse Shades
Fits Items: 76-283, 76-284, 76-660, 76-661, 76-662, 76-663
Width: 15½", Height: 4¾"
***Packing**: 6/Master*



6 Outlet Strips *Indoor Use Only*



Flat Plug



91-220 3' Cord
91-229 6' Cord

6 Outlet Standard Surge Strip w/flat plug, 245 Joules 15A-125V, 1875W

Packing: 12/Master



91-221 4' Cord

6 Outlet Superior Surge Strip, 540 Joules 15A-120V, 1800W

Packing: 12/Master



91-222 4' Cord

6 Outlet Professional Metal Surge Strip, 540 Joules 15A-125V, 1875W

Packing: 12/Master



91-223

6 Outlet Surge Wall Tap 540 Joules 15A-120V, 1800W

Packing: 12/Master







S70-830 White

Inside Elbow

Packing: 144/Master, 12/Inner



S70-832 White

Outside Elbow

Packing: 144/Master, 12/Inner



S70-829 White

Straight Coupling

Packing: 144/Master, 12/Inner



S70-831 White

Flat Elbow

Packing: 144/Master, 12/Inner



S70-826

40" White

Packing: 24/Master

S70-827

40" Brass

Packing: 24/Master

A COMPLETE DO-IT-YOURSELF SELF STICKING WIRE COVER SYSTEM

For:

- Wall lamps
- Telephones
- Track lighting
- Speaker wire
- Extension cords
- Home alarm systems
- CATV cable
- Television wire
- Ceiling swag lighting
- Stereo and VCR

Wire covers available in white and brass.
Couplings, available in white and can be painted.

Splice Connectors for Ballast Disconnect



90-2536 Orange 2 Piece Snap Together Connector for Solid or Tinned Tip Wire: 18 AWG (Female Housing), 12/14 AWG (Male Housing)
3A-125V, 1.3A-277V 105°C



80-2010 Yellow (small) 2 Piece Snap Together Connector for Solid or Tinned Tip Wire: 18/12 AWG (Female Housing), 18 AWG (Male Housing)
6A-600V 105°C

Splice Connector Instructions



Provides fast & easy disconnect/connect of hot & neutral wires, reducing shock hazard during ballast replacement.

Wing Nut Wire Connectors with Spring Inserts for 105°C Supply Wire 600V



90-2237 Yellow
4 #18 Max.

90-2238 Tan
9 #18 Max.

90-2239 Red
5 #16 Max.

90-2240 Grey
4 #12 Max.

90-2241 Blue
4 #10 Max.

Wire Connectors with Spring Inserts for 600V Supply Wire



90-1418
High Heat Black (150°C)
2 #18 Max.

90-1419
Medium Orange (105°C)
5 #18 Max.

90-1440
Large Yellow (105°C)
6 #18 Max.

90-1421
Extra Large Red (105°C)
8 #18 Max.

Porcelain Connectors (Non UL) for High Heat 150°C 300V



90-1311
Small
2 #18 Max.

90-1312
Medium
4 #18 Max.

90-1313
Large
6 #18 Max.

Plastic Connectors for 105°C Supply Wire 300V



90-396
Ext. Small
2 #18 Max.

90-469
Small
4 #18 Max.

90-470
Medium
5 #18 Max.



90-1420 Black
90-1814 White
Electrical Tape 3/4" x 60 ft.

BUSHINGS

Assorted *Nylon • Metal • Plastic*

Nylon Snap–In Bushings



90-157
for 5/16" Hole
Black



90-1824
for 5/16" Hole
Gold



90-158
for 3/8" Hole
Black



90-1825
for 3/8" Hole
Gold



90-161
for 7/16" Hole
Black



90-180
for 7/16" Hole
Gold

Metal Strain Reliefs



90-1158
Small



90-998
Small
with Tab



90-1159
Large
with Tab

Plastic Pipe Bushings



90-1422
1/8 IP



90-1423
1/4 IP

Plastic Bushings

90-327
1/8 IP
Male / White



90-328
1/8 IP
Male / Black



90-321
1/8 IP
Female / White



90-322
1/8 IP
Female / Black



90-325
1/4 IP
Male / White



90-326
1/4 IP
Male / Black



90-323
1/4 IP
Female / White



90-324
1/4 IP
Female / Black



Hardware & Lamp Parts













Harps & Accessories 130-132
Finials 133-136
Reel & Bulk Chain 137-139
Steel & Brass Nipples 140-141
Cross Bars 142-143
Locknuts 144-145
Check Rings 146-147
Washers & Steel Pipe 148
Fixture & Screw Collar Loops 149-151
Hardware, Caps, Screws & Bushings 152-154
Brass Couplings & Balls 155
Brass Necks & Spindles 156
Brass Swivels 157
Armbacks & Elbows 158
Swag Hook Kits & Drop Ceiling/Track Accessories 159
Spacers & Candle Cups 160
Steel Necks 161
Candle Covers 162-165
Bead Chain & Accessories, Pulls & Tassels 166
Crystal & Accessories 167
Lighting Accessories 168

Heavy Duty Harps *1/8 IP Saddle • 1/4-27 Thread*



Polished Brass Finish
125 CTN

90-2203	– 6"	90-555	– 10½"
90-2204	– 6½"	90-923	– 11"
90-919	– 7"	90-556	– 11½"
90-552	– 7½"	90-924	– 12"
90-2235	– 7¾"	90-557	– 12½"
90-920	– 8"	90-925	– 13"
90-553	– 8½"	90-2256	– 13½"
90-921	– 9"	90-2257	– 14"
90-554	– 9½"	90-2520	– 15"
90-922	– 10"		



Polished Nickel Finish
125 CTN

90-2205	– 6"	90-2010	– 10½"
90-2206	– 6½"	90-2004	– 11"
90-2000	– 7"	90-2011	– 11½"
90-2007	– 7½"	90-2005	– 12"
90-2236	– 7¾"	90-2012	– 12½"
90-2001	– 8"	90-2006	– 13"
90-2008	– 8½"	90-2258	– 13½"
90-2002	– 9"	90-2259	– 14"
90-2009	– 9½"	90-2521	– 15"
90-2003	– 10"		



Antique Brass Finish
125 CTN

90-2264	– 6"	90-2268	– 10"
90-2265	– 7"	90-2269	– 11"
90-2266	– 8"	90-2270	– 12"
90-2267	– 9"		



Dark Antique Brass Finish
125 CTN

90-2088	– 7"	90-2079	– 8½"
90-2078	– 7½"	90-2080	– 9½"
90-2089	– 8"		

1/8 IP – 2¾" Wide Saddles for CFL – Heavy Duty



90-2340 *1/8 IP Saddle – Brass Plated*
90-2341 *1/8 IP Saddle – Nickel Plated*

1/8 IP & 1/4 IP Saddles – Heavy Duty



90-2291 *1/8 IP Saddle – Brass Plated*
90-2292 *1/8 IP Saddle – Nickel Plated*
90-2031 *1/4 IP Saddle – Brass Plated*
90-2032 *1/4 IP Saddle – Nickel Plated*

1/2" Finial–Zinc Die Cast 1/4–27



80-1181 *Polished Brass Finish*
80-1182 *Nickel Finish*
80-1518 *Ant. Brass*
80-1519 *Dark Ant. Brass*

Shade Rings – Plated 3/4" Diameter



90-2456 *3 Hole Brass*
90-2533 *3 Hole Nickel*



90-2457 *4 Hole Brass*
90-2534 *4 Hole Nickel*

Light Duty Harps *1/8 IP Saddle • 1/4-27 Thread*

Polished Brass Finish
125 CTN

90-2029 – 4"	90-222 – 10"
90-2030 – 5"	90-561 – 10½"
90-2374 – 5½"	90-223 – 11"
90-2376 – 6"	90-562 – 11½"
90-570 – 6½"	90-224 – 12"
90-219 – 7"	90-563 – 12½"
90-558 – 7½"	90-225 – 13"
90-220 – 8"	90-571 – 13½"
90-559 – 8½"	90-2378 – 14"
90-221 – 9"	90-2522 – 15"
90-560 – 9½"	



Polished Nickel Finish
125 CTN

90-2242 – 4"	90-2016 – 10"
90-2028 – 5"	90-2024 – 10½"
90-2375 – 5½"	90-2017 – 11"
90-2377 – 6"	90-2025 – 11½"
90-2020 – 6½"	90-2018 – 12"
90-2013 – 7"	90-2026 – 12½"
90-2021 – 7½"	90-2019 – 13"
90-2014 – 8"	90-2027 – 13½"
90-2022 – 8½"	90-2379 – 14"
90-2015 – 9"	90-2523 – 15"
90-2023 – 9½"	



All Harps are measured from the top of the harp, (not including the 1/4-27 thread riser), to the bottom of the assembled saddle.

Dark Antique Brass Finish
125 CTN

90-2081 – 7"	90-2083 – 9"
90-2082 – 8"	



1/8 IP – 2¾" Wide Saddles for CFL – Light Duty



90-2338 *1/8 IP Saddle – Brass Plated*
90-2339 *1/8 IP Saddle – Nickel Plated*

1/8 IP & 1/4 IP Saddles – Light Duty



90-2293 *1/8 IP Saddle – Brass Plated*
90-2289 *1/8 IP Saddle – Nickel Plated*
90-2093 *1/4 IP Saddle – Brass Plated*
90-2094 *1/4 IP Saddle – Nickel Plated*

1/2" Finial–Zinc Die Cast 1/4–27



80-1181 *Polished Brass Finish*
80-1182 *Nickel Finish*
80-1518 *Ant. Brass*
80-1519 *Dark Ant. Brass*

Steel Finials – Plated 1/4–27



90-139 *1/2" Brass*
90-136 *1" Brass*
90-137 *1½" Brass*



90-2453 *1/2" Nickel*
90-2454 *1" Nickel*
90-2455 *1½" Nickel*

Heavy Duty Cup Harps *1/4-27 Thread*



All Cup Harps are measured exact size. (not including Harp Cup)

Polished Brass Plated

90-2246 – 6"
90-2248 – 7"
90-2250 – 8"
90-2252 – 9"
90-2254 – 10"



Polished Nickel Plated

90-2247 – 6"
90-2249 – 7"
90-2251 – 8"
90-2253 – 9"
90-2255 – 10"

Bulb Clips 1/4–27



90-2535 3" Diameter Ring with Bulb Clip

90-2529 2" Short Medium Base Bulb Clip & Finial

90-940 Medium Base Bulb Clip Brass Plated

90-1567 Cand. Base Bulb Clip Brass Plated

Steel Risers 1/4–27

Brass Plated



90-2458 1/2" Brass Plated
90-142 1" Brass Plated
90-2597 1½" Brass Plated
90-141 2" Brass Plated

Solid Brass Risers 1/4–27

Burnished and Lacquered



90-1562 1/2"
90-140 1"
90-1589 1½"
90-701 2"

2 ½ Heavy Duty Cup for Swing Arm Lamps



90-2353 Polished Brass Finish

90-2354 Nickel Finish

1/2" Finial–Zinc Die Cast 1/4–27



80-1181 Polished Brass Finish
80-1182 Nickel Finish
80-1518 Ant. Brass
80-1519 Dark Ant. Brass

Socket Saddle Protector



80-1197
Steel U–Bracket Unfinished

Shade Rings – Plated 3/4" Diameter



90-2456 3 Hole Brass
90-2533 3 Hole Nickel



90-2457 4 Hole Brass
90-2534 4 Hole Nickel

Die Cast *Assorted Finishes*



Bud Finial
1 3/8" Height – 1/8 IP
90-1723 *Pol. Brass*
90-1724 *Ant. Brass*
90-1725 *Pol. Chrome*



Acorn Finial
1 1/2" Height – 1/8 IP
90-133 *Pol. Brass*
90-1712 *Ant. Brass*
90-1713 *Pol. Chrome*



Spindle Finial
2 1/4" Height – 1/8 IP
90-135 *Pol. Brass*



Bullet Finial
2" Height – 1/4-27
90-1717 *Pol. Brass*
90-1718 *Ant. Brass*
90-1719 *Pol. Chrome*



Modern Finial
1 1/2" Height – 1/4-27
90-1714 *Pol. Brass*
90-1715 *Ant. Brass*
90-1716 *Pol. Chrome*



Pyramid Finial
1 1/2" Height – 1/4-27
90-1720 *Pol. Brass*
90-1721 *Ant. Brass*
90-1722 *Pol. Chrome*



Eagle Finial
2" Height – 1/8 IP
90-134 *Pol. Brass*



90-762
Use 90-762 to Reduce
1/8 IP to 1/4-27
(Thread on Lamp Harp)



Small Pyramid Knob
3/4" Height – 1/8 IP
90-959 *Pol. Brass*



Large Pyramid Knob
1 1/4" Height – 1/8 IP
90-1160 *Pol. Brass*
90-1161 *Ant. Brass*
90-1711 *Pol. Chrome*



1" Plain Knob
1/8 IP
90-1050 *Pol. Brass*
90-1051 *Pol. Chrome*



1 1/2" Plain Knob
1/8 IP
90-166 *Pol. Brass*
90-1056 *Pol. Chrome*

Solid Brass *Polished • Burnished & Lacquered*



90-886
Urn Finial
1¾" Height – 1/8 IP
Burnished and Lacquered



90-130
Small Spindle Finial
1⅞" Height – 1/4-27
Burnished and Lacquered



90-1731
Large Spindle Finial
2⅜" Height – 1/4-27
Polished Brass



90-838 *Brass*
80-2102 *Nickel*
Bullet Finial
2" Height – 1/8 IP
Burnished and Lacquered



90-1735
Urn Finial
1 7/16" Height – 1/4-27
Polished Brass



90-837
Acorn Finial
1½" Height – 1/8 IP
Burnished and Lacquered



90-1732
Finial
1½" Height – 1/4-27
Polished Brass



90-1733 *Brass*
80-2103 *Nickel*
Polished Tear Drop Finial
1½" Height – 1/8 IP



90-842 *Brass Ball Finial*
1¼" Height 3/4" Dia. –1/8 IP
Burnished and Lacquered
80-1880 *Satin Nickel Ball Finial*
1¼" Height 3/4" Dia. –1/4-27



90-132
Ball Finial
1⅜" Height 7/8" Dia. –1/8 IP
Burnished and Lacquered



90-1386
Ball Knob Finial
1⅛" Height – 1/4-27
Burnished and Lacquered



90-762
Use 90-762 to Reduce
1/8 IP to 1/4-27
(Thread on Lamp Harp)

Solid Brass *Polished*



90-1744
Flame Ribbed
Brass Finial
2¾" Height – 1/4-27
Polished Brass



90-1743
Leaf Brass
Finial
3½" Height – 1/4-27
Polished Brass



90-1745
U-Shaped
Leaf Brass Finial
2¾" Height – 1/4-27
Polished Brass



90-1734
Large Urn Finial
2¾" Height – 1/8 IP
Polished Brass



90-1746
Fan
Brass Finial
3" Height – 1/4-27
Polished Brass



90-1747
Oriental
Brass Finial
2¾" Height – 1/4-27
Polished Brass



90-1748
Ceramic
Urn Finial
2½" Height – 1/4-27



90-1740
Beige Marble
Ball Finial
2" Height – 1/4-27



90-1738
Diamond Cut
Crystal Finial
2¼" Height – 1/4-27



90-1737
Pendalog Cut
Crystal Finial
2¾" Height – 1/4-27



90-1739
U–Drop Cut
Crystal Finial
3¼" Height – 1/4-27



90-1736
Ball Cut
Crystal Finial
2¼" Height – 1/4-27



90-1741
Wood Ball
Finial
1⅝" Height – 1/4-27



90-1742
Wood Ribbed
Ball Finial
2" Height – 1/4-27

11 Gauge / 8 Gauge



11 Gauge Chain – *50 yds. (150 ft.) to Reel / 1 Reel to Master*



15 lbs MAX

79-200	79-204	79-201	79-233	79-203	79-205 (120' Reel)	79-206 (120' Reel)
Brass Finish	Ant. Brass Finish	Nickel Finish	White Finish	Black Finish	Spanish Type Brass Finish	Spanish Type Ant. Brass

8 Gauge Chain – *100 ft. to Reel / 1 Reel to Master*



35 lbs MAX

79-209	79-212	79-210	79-213	79-211
Brass Finish	Ant. Brass Finish	Nickel Finish	White Finish	Black Finish



Malleable Iron Chain Pliers

79-099 *Chain Pliers*

Packing: *1 Box/50 Master*

1 Yard Lengths

11 Gauge

- 1 ½" Link Length
- 7/8" Link Width
- 3/32" Thick
- 1 yd. Length
- 200 yds./ctn.



90-070	90-071	90-072	90-077	90-670
Brass Finish	Ant. Brass Finish	Black Finish	Nickel Finish	White Finish

8 Gauge

- 1 ½" Link Length
- 7/8" Link Width
- 1/8" Thick
- 1 yd. Length
- 100 yds./ctn.



79-455	79-464	79-460	79-458	79-457
Brass Finish	Ant. Brass Finish	Nickel Finish	White Finish	Black Finish

1 Yard Lengths

8 Gauge

- 1 ½" Link Length
- 7/8" Link Width
- 1/8" Thick
- 1 yd. Length
- 24 yds./ctn.



25-1067
8 Gauge
Old Bronze
Finish

25-1072
8 Gauge
Textured White
Finish

25-1069
8 Gauge
Brushed Nickel
Finish

8 Gauge

- 1 ½" Link Length
- 7/8" Link Width
- 1/8" Thick
- 1 yd. Length
- 24 yds./ctn.



25-1080
8 Gauge
Copper Bronze
Finish

25-1074
8 Gauge
Flemish Gold
Finish

25-1081
8 Gauge
Dorado Bronze
Finish

4 Gauge

- 1 ¾" Link Length
- 1 ⅛" Link Width
- 1/4" Thick
- 1 yd. Length
- 50 yds./ctn.



90-080
4 Gauge
Brass
Finish

90-081
4 Gauge
Ant. Brass Finish

90-000
4 Gauge
Nickel
Finish

90-085
4 Gauge
Black
Finish

Specialty Chain – 1 Yard Length 100 yds./ctn.



90-078
Spanish Type
Pol. Brass
Finish

90-086
Spanish Type
Ant. Brass
Finish

79-432
Fluorescent
Chrome
Finish

79-306
#12
Jack Chain
(100 ft. Lengths)

1/8IP Steel Nipple – Zinc Plated

1/8 IP



1/8 IP Thread size
3/8" Wide

Item No.	Length	Item No.	Length	Item No.	Length	Item No.	Length
90-1028	3/8"	90-1008	2⅛"	90-1030	5¼"	90-2105	16"
90-280	1/2"	90-289	2¼"	90-1031	5½"	90-2106	18"
90-281	5/8"	90-290	2½"	90-1198	5¾"	90-2107	20"
90-282	3/4"	90-1012	2⅝"	90-255	6"	90-271	24"
90-1021	7/8"	90-1022	2¾"	90-1004	6⅛"	90-270	30"
90-283	1"	90-291	3"	90-1281	6½"	90-274	36" Unfinished
90-284	1⅛"	90-292	3¼"	90-1005	7"	90-2233	36"
90-258	1¼"	90-293	3½"	90-256	8"	90-2108	45"
90-285	1⅜"	90-1014	3¾"	90-2102	9"	90-2109	48"
90-286	1½"	90-294	4"	90-1068	10"	90-2110	54"
90-2111	1⅝"	90-1023	4¼"	90-2103	11"	90-2627	60"
90-257	1¾"	90-1003	4½"	90-1009	11½"	90-2625	72"
90-287	1⅞"	90-1029	4¾"	90-272	12"		
90-288	2"	90-295	5"	90-2104	14"		

Zinc plated steel except 90-274 (36") which is unfinished steel

1/4IP Steel Nipple – Zinc Plated

1/4 IP



1/4IP Thread size
1/2" Wide

Item No.	Length	Item No.	Length	Item No.	Length	Item No.	Length
90-296	1/2"	90-299	2"	90-1002	4½"	90-2124	10"
90-1199	5/8"	90-2115	2¼"	90-2117	4¾"	90-2125	11"
90-302	3/4"	90-301	2½"	90-261	5"	90-2126	12"
90-2112	7/8"	90-1162	2¾"	90-2118	5¼"	90-2127	24"
90-297	1"	90-259	3"	90-2119	5½"	90-1063	36" Unfinished
90-2113	1⅛"	90-1026	3¼"	90-2120	5¾"	90-2545	48"
90-1000	1¼"	90-1027	3½"	90-262	6"	90-2546	48" Unfinished
90-2114	1⅜"	90-1163	3¾"	90-2121	7"	90-2594	50"
90-298	1½"	90-260	4"	90-2122	8"	80-1938	72"
90-1025	1¾"	90-2116	4¼"	90-2123	9"		

Zinc plated steel except 90-1063 (36") & 90-2546 (48") which are unfinished steel

3/8IP Steel Nipple – Zinc Plated

3/8 IP



3/8IP Thread size
5/8" Wide

Item No.	Length	Item No.	Length	Item No.	Length	Item No.	Length
90-2128	1/2"	90-2131	1⅛"	90-1062	2"	90-609	5"
90-2129	5/8"	90-1018	1¼"	90-607	2½"	90-610	6"
90-1016	3/4"	90-2132	1⅜"	90-1060	3"	90-611	36" Unfinished
90-2130	7/8"	90-606	1½"	90-1173	3¾"	90-2626	48"
90-1015	1"	90-1017	1¾"	90-608	4"		

Zinc plated steel except 90-611 (36") which is unfinished steel

1/8IP Yellow Zinc Plated

Item No.	Length	Item No.	Length	Item No.	Length	Item No.	Length
90-5003	3/8"	90-5032	4"	90-5092	11½"	90-5152	19"
90-5004	1/2"	90-5036	4½"	90-5096	12"	90-5156	19½"
90-5005	5/8"	90-5040	5"	90-5100	12½"	90-5160	20"
90-5006	3/4"	90-5044	5½"	90-5104	13"	90-5168	21"
90-5007	7/8"	90-5048	6"	90-5108	13½"	90-5176	22"
90-5008	1"	90-5052	6½"	90-5112	14"	90-5180	22½"
90-5010	1¼"	90-5056	7"	90-5116	14½"	90-5184	23"
90-5012	1½"	90-5060	7½"	90-5120	15"	90-5192	24"
90-5014	1¾"	90-5064	8"	90-5124	15½"	90-2622	30"
90-5016	2"	90-5068	8½"	90-5128	16"	90-5199	36"
90-5020	2½"	90-5072	9"	90-5132	16½"	90-5200	45"
90-5024	3"	90-5076	9½"	90-5136	17"	90-5201	48"
90-5026	3¼"	90-5080	10"	90-5140	17½"	90-5203	54"
90-5028	3½"	90-5084	10½"	90-5144	18"	90-2623	60"
90-5030	3¾"	90-5088	11"	90-5148	18½"		

1/8 IP



1/8 IP Thread size
3/8" Wide

1/8IP Solid Brass Nipples – Unfinished

Item No.	Length	Item No.	Length	Item No.	Length	Item No.	Length
90-2211	3/8"	90-1188	1½"	90-1192	3"	90-2137	5"
90-1182	1/2"	90-2133	1⅝"	90-1193	3¼"	90-2138	5½"
90-1183	5/8"	90-2134	1¾"	90-1194	3½"	90-2158	6"
90-1184	3/4"	90-1189	2"	90-2136	3¾"	90-2234	36"
90-1185	1"	90-1190	2¼"	90-1195	4"		
90-1186	1⅛"	90-1191	2½"	90-1196	4¼"		
90-1187	1¼"	90-2135	2¾"	90-1197	4½"		

1/8 IP



1/8 IP Thread size
3/8" Wide

1/4IP Solid Brass Nipples – Unfinished

Item No.	Length	Item No.	Length	Item No.	Length	Item No.	Length
90-2518	1/2"	90-2472	7/8"	90-2475	2"	90-2476	3½"
90-2519	5/8"	90-2473	1"	90-2407	2½"		
90-2471	3/4"	90-2474	1½"	90-2385	3"		

1/4 IP



1/4 IP Thread size
1/2" Wide

1/8" Dia. 5/32" Dia. 1/4" Dia. 3/8" Dia. 1/2" Dia. 5/8" Dia.

Thread Size Reference Guide



Assorted Cross Bars

Gem Bars 1/8 IP



90-113 3/4" x 3⅞"



90-1125 with Ground Screw – 3/4" x 3⅞"

Cross Bars 1/4 IP



90-110 1" x 4⅜"



90-1126 with Ground Screw – 1" x 4⅜"
90-2477 with Ground Screw – 1" x 4⅜" (heavy duty)

Cross Bar 3/8 IP



90-1065 1" x 4⅜"

Adjustable Cross Bar



90-179 Center Hole Slips 3/8 IP
Adjusts from 4½" to 6½"

Offset Cross Bars



90-109 1" x 4⅝"
Screw Holes – 4¼" Center to Center



90-112 1" x 4"
Screw Holes – 2¾", 3⅜" and 3½"
Center to Center
Center Hole Slips 3/8 IP
With Ground Screw

Double Cross Bars



90-575
Screw Holes – 2¾" and 3⅞"
Center to Center



90-1073
Screw Holes – 2¾"and 3⅞"
Center to Center
with Ground Screw

Universal Crossbars & Lamp Parts



Round Universal Crossbar – Flat Sides
Screw Holes 2¾" x 3½" Center to Center
90-1784



Universal Crossbar
Screw Holes 2¾" x 3½" Center to Center
90-111
90-2478 (with Ground Screw)



Round Universal Crossbar
Screw Holes 2¾" x 3½" Center to Center
90-1650
90-1785 (with Ground Screw)



1/2" Small Ceiling Hickey w/Screw Hole
90-5310 1/8 IP x 1/8 IP



1" Small Ceiling Hickey w/Screw Hole
80-2015 1/8 IP x 1/8 IP



1" Ceiling Hickey

90-114	1/8 IP x 1/4 IP
90-115	1/8 IP x 1/8 IP
90-178	1/8 IP x 3/8 IP
90-1705	1/4 IP x 1/4 IP
90-175	1/4 IP x 3/8 IP
90-589	3/8 IP x 3/8 IP
90-612	1/2 IP x 1/2 IP



1" Malleable Iron Hickey

90-1127	1/8 IP x 1/8 IP
90-1128	1/8 IP x 1/4 IP
90-1217	1/8 IP x 3/8 IP
90-1565	1/4 IP x 1/4 IP
90-1129	1/4 IP x 3/8 IP
90-598	3/8 IP x 3/8 IP
90-613	1/2 IP x 1/2 IP



Ceiling Extension
3/8 IP Male x
3/8 IP Female
90-165 1"
90-593 1⅜"



Crowfoot
90-1130 3/8 IP Male

LOCKNUTS & WASHERS

SATCO®

Steel *Unfinished • Brass Plated • Zinc Plated*

Locknuts, Pal Nuts and Toothwashers



Steel Locknut – 1/8 IP
9/16" hex., 1/8" thick
90-001 *Unfinished*
90-1036 *Brass Plated*
90-1037 *Zinc Plated*



Steel Locknut – 1/8 IP
9/16" hex., 3/16" thick
90-034 *Unfinished*
90-033 *Brass Plated*
90-1035 *Zinc Plated*



Steel Locknut – 1/8 IP
1/2" hex., 1/8" thick
90-187 *Unfinished*
90-1066 *Brass Plated*
90-1636 *Zinc Plated*



Steel Locknut – 1/8 IP
1/2" hex., 3/16" thick
90-1648 *Unfinished*
90-1646 *Brass Plated*
90-1649 *Zinc Plated*



Steel Locknut – 1/4 IP
11/16" hex., 1/8" thick
90-1038 *Unfinished*
90-591 *Brass Plated*
90-171 *Zinc Plated*



Steel Locknut – 1/4 IP
3/4" hex., 1/4" thick
90-1702 *Unfinished*
90-1703 *Brass Plated*
90-1704 *Zinc Plated*



Steel Locknut – 3/8 IP
7/8" dia., 1/8" thick
90-002 *Zinc Plated*



Steel Square Locknut – 3/8 IP
1" dia., 1/8" thick
90-1424 *Zinc Plated*

Steel Locknuts



90-015
6/32
Zinc Plated



90-017
8/32
Zinc Plated



90-018
1/4–20
Zinc Plated

Steel Pal Nuts 1/8 IP



90-019
Unfinished



90-594
Brass Plated

Toothwashers 1/8 IP Slip



90-390
Unfinished



90-392
Brass Plated



90-592
Zinc Plated

Toothwasher 8/32 Slip



90-1578
Zinc Plated

Toothwashers 1/4 IP Slip



90-1804
Zinc Plated



90-1579
Unfinished



90-1580
Brass Plated

Toothwasher 3/8 IP Slip



90-1698
Zinc Plated

Brass Round Knurled Locknuts 9/16" Diameter 1/8 IP



90-003
Burnished & Lacquered



90-1042
Nickel Plated



90-1699
Unfinished

Brass Round Knurled Locknuts 3/4" Diameter 1/8 IP



90-004
Burnished & Lacquered



90-1577
Nickel Plated



90-1623
Unfinished

Brass Hexagon Locknuts 1/8 IP



90-172
1/2" Hex. 1/8" Thick Unfinished



90-1385
1/2" Hex., 1/8" Thick Nickel Plated



90-1700
1/2" Hex., 3/16" Thick Unfinished

Brass Round Beaded Locknut 1/8 IP



90-1634
9/16" Dia., 5/32" Thick Unfinished

Brass Round Plain Locknut 1/8 IP



90-1621
3/4" Dia. 1/8" Thick Unfinished

Brass Battery Nut 8/32



90-016
Burnished & Lacquered

Brass Hexagon Locknut 1/4 IP



90-1701
11/16" Hex., 3/16" Thick Unfinished

Brass Round Knurled Locknut 1/4 IP



90-014
3/4" Dia., 1/8" Thick Burnished & Lacquered

Brass Round Knurled Locknut 1/8 IP



90-1601
1" Dia., 1/8" Thick Unfinished

CHECK RINGS

SATCO®

Steel *Unfinished • Brass Plated • Nickel Plated*

1/8 IP = 7/16"
1/4 IP = 9/16"

Curled Edge 1/8 IP Slip



Steel Check Ring
Curled Edge
1/8 IP Slip – Brass Plated

90-2049	½"	90-333	1¼"
90-379	⅝"	90-2061	1⅜"
90-359	¾"	90-364	1½"
90-360	⅞"	90-350	1¾"
90-362	1"	90-351	2"
90-363	1⅛"		



Steel Check Ring
Curled Edge
1/8 IP Slip – Nickel Plated

90-1661	½"	90-1710	1⅛"
90-2051	⅝"	90-1095	1¼"
90-381	¾"	90-1096	1½"
90-383	⅞"	90-1644	1¾"
90-361	1"	90-1790	2"



Steel Check Ring
Curled Edge
1/8 IP Slip – Unfinished

90-2050	½"	90-2059	1¼"
90-2052	⅝"	90-2062	1⅜"
90-2053	¾"	90-2063	1½"
90-2055	⅞"	90-2074	1¾"
90-2056	1"	90-2076	2"
90-2058	1⅛"		



Beaded Steel
Check Ring
1/8 IP Slip

90-388 1⅛" Brass Plated
90-389 1⅛" Nickel Plated



Steel Check Ring
Curled Edge
1/8 IP Slip – Vacuum Brass

90-176 1"
90-177 1¼"



Steel Check Ring
Curled Edge
1/8 IP Slip – Antique Brass

90-1838	1/2"	90-1766	1"
90-1788	5/8"	90-2182	1¼"
90-1765	3/4"	90-1763	1½"
90-1789	7/8"	90-1839	2"

Straight Edge 1/8 IP Slip



Steel Check Ring
Straight Edge
1/8 IP Slip – Brass Plated

90-353	1¼"
90-354	1½"
90-355	1⅝"
90-356	1¾"
90-357	2"
90-1772	3"
90-1641	3¼"



Steel Check Ring
Straight Edge
1/8 IP Slip – Unfinished

90-2064	1⅝"	90-1654	3"
90-2066	1⅞"	90-2072	3¼"
90-2067	2"	90-2073	3½"
90-2068	2⅛"	80-1204	3¾"
90-2069	2¼"	80-1282	4"
90-2070	2½"	80-1205	4¼"
90-1640	2¾"		

Curled Edge 1/4 IP Slip



Steel Check Ring
Curled Edge
1/4 IP Slip – Brass Plated

90-358	¾"
90-472	1"
90-473	1¼"
90-2091	1½"
90-2075	1¾"
90-1656	2"



Steel Check Ring
Curled Edge
1/4 IP Slip – Unfinished

90-2054	¾"
90-2057	1"
90-1655	1⅛"
90-2060	1¼"
90-2090	1½"
90-2077	2"



Steel Check Ring
Curled Edge
1/4 IP Slip – Nickel Plated

90-1832	1"
90-1833	1¼"
90-1834	1½"
90-1835	2"

Brass *Unfinished • Nickel Plated • Burnished & Lacquered*

Turned Brass Check Rings – Plated



Turned Brass Check Ring
1/8 IP Slip
Burnished and Lacquered

90-2139	½"	**90-1091**	1¼"
90-2140	⅝"	**90-1092**	1½"
90-2141	¾"	**90-2146**	1¾"
90-2142	⅞"	**90-1094**	2"
90-1090	1"		



Turned Brass Check Ring
1/8 IP Slip
Nickel Plated

90-1093	1"
90-1088	1¼"
90-1089	1½"



Turned Brass Check Ring
1/4 IP Slip
Burnished and Lacquered

90-2147	¾"
90-2148	⅞"
90-2149	1"
90-2150	1½"

Turned Brass Check Rings – Unfinished



Turned Brass Check Ring
1/8 IP Slip – Unfinished

90-1608	½"	**90-1602**	1⅛"	**90-1605**	1¾"
90-1594	⅝"	**90-1598**	1¼"	**90-1606**	1⅞"
90-1595	¾"	**90-1603**	1⅜"	**90-1607**	2"
90-1596	⅞"	**90-1599**	1½"		
90-1597	1"	**90-1604**	1⅝"		



Turned Brass Check Ring
1/4 IP Slip – Unfinished

90-1609	⅝"	**90-1613**	1⅛"	**90-1617**	1⅝"
90-1610	¾"	**90-1614**	1¼"	**90-1618**	1¾"
90-1611	⅞"	**90-1615**	1⅜"	**90-1619**	1⅞"
90-1612	1"	**90-1616**	1½"	**90-1620**	2"

Turned Brass Double Check Ring





(Cross Section)

1/8 IP Slip
Burnished and Lacquered

90-2151	¾"
90-2152	1"

Knurl Solid Brass Check Ring



(Side View)



1/8 IP Tapped

90-2438	¾"
90-2439	⅞"
90-2440	1"
90-2441	1¼"

Solid Brass Square Check Ring



1/8 IP Slip

90-2318	¾" Polished
90-2319	1" Polished

WASHERS & STEEL PIPE

Assorted *Steel • Felt • Rubber • Plastic*

Steel Washers



Steel Washer
1/8 IP Slip – 16 Gauge
Unfinished

90-1652	7/8"	90-991	1 3/4"
90-985	1"	90-992	2"
90-987	1 1/8"	90-1218	2 1/2"
90-988	1 1/4"	90-995	3"
90-989	1 1/2"	90-1830	3 1/2"



Steel Washer
1/4 IP Slip – 16 Gauge
Unfinished

90-986	1"	90-1660	2 1/4"
90-1298	1 1/4"	90-1149	2 1/2"
90-990	1 1/2"	90-996	3"
90-1653	1 3/4"	90-1831	4"
90-993	2"		



Light Steel Washer
1/8 IP Slip

Brass Plated		Nickel Plated	
90-1020	5/8"	90-2634	3/4"
90-384	3/4"	90-2635	1"
90-385	1"		



Reducing Washer
9/16" x 7/16"
Brass Plated

90-365

Felt, Rubber & Plastic Washers

Felt Washer
1/8 IP Slip – White

90-1175	5/8"	90-1179	1 1/4"
90-1176	3/4"	90-1180	1 1/2"
90-1177	7/8"	90-1181	2"
90-1178	1"		



Rubber Washer
1/8 IP Slip – White

90-386	1/2"	90-154	1 1/4"
90-152	3/4"	90-155	1 1/2"
90-153	7/8"	90-156	2"
90-387	1"		



Rubber Washer
1/8 IP Slip – Black

90-1166	1/2"	90-1174	1 1/4"
90-1167	3/4"	90-1169	1 1/2"
90-1168	1"	90-1170	2"



Plastic Crystal Washer
1 1/4" Dia. w/Lip – 1/8 IP Slip

90-1429

Steel Pipe

3/4" x 3/4" Threaded Ends 1/8 IP



Brass Plated



Nickel Plated



Raw Steel

Brass Plated		Nickel Plated		Raw Steel	
90-276	4"	90-2501	4"	90-2507	4"
90-277	6"	90-2502	6"	90-2508	6"
90-278	8"	90-2503	8"	90-2509	8"
90-267	10"	90-2504	10"	90-2510	10"
90-268	12"	90-2505	12"	90-2511	12"
90-269	14"	90-2506	14"	90-2512	14"

Adjustable Figurine

90-273

10" –15" 1/8 IP
Threaded Ends
Brass Plated



Die Cast *Assorted Finishes*

10 lbs MAX

1" Male Loops–1/8 IP w/Wireway



90-200 *Brass Finish*



90-202 *Ant. Brass Finish*



90-204 *Black Finish*



90-721 *White Finish*



90-212 *Chrome Finish*



90-206 *Ant. Copper Finish*

10 lbs MAX

1" Female Loops–1/8 IP w/Wireway



90-201 *Brass Finish*



90-203 *Ant. Brass Finish*



90-205 *Black Finish*



90-720 *White Finish*



90-714 *Chrome Finish*



90-2514 *Brushed Nickel Finish*

10 lbs MAX

1½" Female Loops–1/8 IP w/Wireway



90-2515 *Brushed Nickel Finish*



90-249 *Brass Finish*



90-254 *Ant. Brass Finish*



90-599 *Chrome Finish*

3/4" Loops–1/8 IP w/Wireway



90-957 *1/8 IP Male Brass Finish*



90-958 *1/8 IP Female Brass Finish*

20 lbs MAX

2" Die Cast Fixture Loops–1/8 IP w/Wireway



90-1776 *1 Notch Hang Straight Brass Finish*



90-253 *Brass Finish*
90-340 *Ant. Brass Finish*
90-341 *Chrome Finish*



90-263 *Brass Finish*
90-1726 *Ant. Brass Finish*
90-1727 *Pol. Chrome Finish*



Hang Straight Loop
90-1728 *Pol. Brass Finish*
90-1729 *Ant. Brass Finish*
90-1730 *Pol. Chrome Finish*



90-1775 *5 Notch Hang Straight Brass Finish*

DIE CAST LOOPS

Assorted Finishes

1/8 IP

1/8 IP Screw Collar Loops with Ring

25 lbs MAX



90-2342
Brass Finish



90-2344
Ant. Brass Finish



90-2343
Chrome Finish



90-2422
White Finish



90-2421
Black Finish

1/4 IP

1/4 IP Screw Collar Loops with Ring



90-2595
Unfinished



90-2494
Brushed Nickel Finish



90-2495
Old Bronze Finish



90-335
Brass Finish



90-1848
Brushed Pewter Finish

1/4 IP

1/4 IP Screw Collar Loops with Ring



90-336
Ant. Brass Finish



90-337
Chrome Finish



90-338
White Finish



90-339
Black Finish

3/8 IP

3/8 IP Screw Collar Loops with Ring



90-1164
Brass Finish



90-2352
Ant. Brass Finish



90-2351
Chrome Finish

50 lbs MAX

1/8 IP Cast Brass Screw Collar Loops with Ring



90-2295
Polished & Lacquered



90-2301
Polished Chrome



90-2294
Unfinished

1/8 IP
Fits 1" Canopy Hole
Ring Diameter 1⅛"
Height 1¾"

1/4 IP Cast Brass Screw Collar Loops with Ring



90-1572
Polished & Lacquered



90-2300
Polished Chrome



90-1571
Unfinished

1/4 IP
Fits 1" Canopy Hole
Ring Diameter 1⅛"
Height 1¾"

3/8 IP Cast Brass Screw Collar Loops with Ring



90-2297
Polished & Lacquered



90-2302
Polished Chrome



90-2296
Unfinished

3/8 IP
Fits 1" Canopy Hole
Ring Diameter 1⅛"
Height 1¾"

1/4 IP Heavy Duty Cast Brass Screw Collar Loops with Ring



90-2299
Polished & Lacquered



90-2303
Polished Chrome



90-2298
Unfinished

1/4 IP
Fits 1¼" Canopy Hole
Ring Diameter 1⅝"
Height 2¼"

Cap Nuts – 8/32



90-208
Brass Plated



90-209
Antique Brass



90-210
Black



90-710
Chrome



90-1836
White



90-1842
Bronze

Brass Balls – 8/32



90-666
3/8"
Burnished & Lacquered



90-711
Knurled 3/8"
Burnished & Lacquered

Brass Knobs – 8/32



90-955
Knurled 3/8"
Brass Burnished & Lacquered



90-1837
Knurled 3/8"
Nickel

Brass Pear Knobs – 8/32



90-652
Brass Burnished & Lacquered



90-651
Antique Brass



90-653
Nickel



90-1843
Bronze

Brass Lock-Up Caps – 1/8 IP



90-169
Brass Burnished & Lacquered



90-640
Nickel



90-168
Antique Brass



90-1809
Black



90-551
Brass Burnished & Lacquered

Plastic Lock-Up Caps – 1/8 IP



90-167
White 3/4"

90-822
White 1"



90-159
Brass Finish 1"

90-245
White w/Pull Chain Hole 1"

Brass / Steel *Assorted Finishes*

Steel Round Head Slotted Machine Screws – 8/32 – Plated Finishes



90-722	90-2544	90-797	90-027	90-026	90-1773	90-028	90-1774	90-030	90-029	90-1032
1/2" Brass Plated	1/2" Nickel Plated	3/8" Green Ground (combo head)	1" Brass Plated	1" Nickel Plated	1¼" Zinc Plated	1½" Brass Plated	1½" Nickel Plated	2" Brass Plated	2" Nickel Plated	3" Nickel Plated

Steel Knurled Head Thumb Screws – 8/32



90-1778	90-022	90-023	90-024	90-025	90-059	90-060	90-031	90-032
1/2" White	1/2" Brass Plated	1/2" Nickel Plated	1/2" Antique Brass	1/2" Black	3/4" Brass Plated	3/4" Antique Brass	1" Brass Plated	1" Nickel Plated

Steel Knurled Head Thumb Screws – 6/32



90-1154	90-1156	90-1155
1/2" Brass Plated	1/2" Nickel Plated	1/2" Antique Brass

Steel Switchplate Screws – 6/32



90-538	90-535	90-536
1/2" Brass Plated	1/2" Antique Brass	1/2" Black

Plastic Switchplate Screws – 6/32



90-537	90-539
1/2" White Plastic	1/2" Ivory Plastic

Solid Brass Thumb Screws Burnished and Lacquered – 8/32

Ball Head



90-035	90-036	90-037	90-038
3/8"	1/2"	5/8"	3/4"

Flat Head



90-744	90-635
3/8"	1/4"

Nozzles, Nipples, Knobs & Bushings

Hexagon Head Nipples – Brass Plated–1/8 IP



90-636
1/4"



90-637
3/8"



90-638
1/2"



90-639
5/8"

Acorn Knobs–1/8 IP
Brass Burnished & Lacquered



90-668
Knurled



90-667
Hex

Brass Knobs–1/8 IP
Brass Burnished & Lacquered



90-626
Brass



90-625
Brass

Brass Beaded Nozzles
Brass Burnished & Lacquered



90-642
1/8 F x 1/8
Male



90-643
1/4 F x 1/8
Male

Brass Bushing
Unfinished



90-207
1/8 F x 3/8
Female.

Brass Closed
Gas Cap



90-702
3/8 IP
Burnished & Lacquered



90-1308
3/8 IP x 1/8 IP
Burnished & Lacquered

Brass Reducing Bushings – Unfinished



90-761
1/8 M x 8/32 F
with shoulder



90-762
1/8 M x 1/4-27 F
with shoulder



90-963
1/4 M x 1/8 F
with shoulder



90-764
3/8 M x 1/8 F
with shoulder



90-765
3/8 M x 1/4 F
with shoulder



90-644
1/8 M x 8/32 F



90-645
1/8 M x 1/4-27 F



90-646
1/4 M x 1/8 F

Brass *Unfinished • Nickel Plated • Burnished & Lacquered*

Brass Couplings



90-162
1/2" Long – 1/8 IP
Burnished & Lacquered



90-332
1/2" Long – 1/8 IP
Burnished & Lacquered



90-1059
1/2" Long – 1/8 IP
Nickel Plated



90-241
1/2" Long – 1/4 IP
Burnished & Lacquered



90-623
1/2" Long – 1/4 F x 1/8 F
Burnished & Lacquered



90-634
1/2" Long – 1/4 F x 1/8 Slip
8/32 Hole
Burnished & Lacquered



90-614
7/8" Long – 3/8 IP
Burnished & Lacquered

Brass Couplings–Unfinished



90-1622 5/8"
90-1600 7/8"
1/8 IP



90-2153 1/2" Long
90-2154 3/4" Long
Hexagon Head
Coupling – 1/8 IP



90-2155
5/8" Long
5/8" Diameter
1/8 IP



90-2156
5/8" Long
5/8" Diameter
1/4 IP



90-2157
5/8" Long
5/8" Diameter
1/8 F x 1/4 F

Brass Balls–Unfinished



90-1624 3/8" – 8/32
90-1625 1/2" – 8/32
90-1626 1/2" – 1/8 IP
90-1627 5/8" – 1/8 IP
90-1628 3/4" – 1/8 IP
90-1629 1" – 1/8 IP
90-1631 1 ¼" – 1/8 IP
90-1630 1 ½" – 1/8 IP
90-1632 1 ¾" – 1/8 IP
90-1633 2" – 1/8 IP

Brass Half Balls–Unfinished



90-2095 1/2" – 8/32
90-2096 5/8" – 1/8 IP
90-2097 3/4" – 1/8 IP
90-2098 1" – 1/8 IP
90-2099 1 ¼" – 1/8 IP
90-2100 1 ½" – 1/8 IP

BRASS NECKS & SPINDLES

Brass *Unfinished • Burnished & Lacquered*

Solid Brass Necks & Spindles–Burnished and Lacquered



90-095
15/16" x 5/8"
1/8 Slip



90-096
11/16" x 1½"
1/8 Slip



90-097
7/8" x 2"
1/8 Slip



90-098
3/4" x 3"
1/8 Slip



90-163
13/16" x 7/8"
1/8 Slip



90-174
13/16" x 7/8"
1/8 IP Tapped

Solid Brass Necks & Spindles–Unfinished



90-2171
5/8" x 2 11/16"
1/8 IP – Tapped



90-2170
3/4" x 4⅛"
1/8 IP – Tapped



90-2168
7/8" x 1¼"
1/8 IP – Tapped



90-2169
7/8" x 1¼"
1/8 IP – Slip



90-2163
15/16" x 5/8"
1/8 IP – Tapped



90-2165
1¼" x 9/16"
1/8 IP – Tapped



90-2164
1¼" x 3/4"
1/8 IP – Tapped



90-2166
7/8" x 13/16"
1/8 IP – Tapped



90-2167
7/8" x 13/16"
1/8 IP – Slip

Solid Brass Swivels



90-2332
Knurled Swivel
1/8 M x 1/8 F
1 3/16" Height
Unfinished



90-2331
Hang Straight Swivel w/Stop
1/8 M x 1/8 F
1 1/2" Height
Unfinished



90-2330
Modern Swivel
1/8 M x 1/8 F
1 5/16" Height
Unfinished



90-2333
Modern Long Swivel
1/8 M x 1/8 F
1 1/2" Height
Unfinished



90-2329
Stop Swivel
1/8 M x 1/4 F
1 5/8" Height
Unfinished



90-2334
Side Swivel
1/8 M x 1/8 F
1 3/4" Height
Unfinished



90-2335
Heavy Duty Swivel
1/8 M x 1/8 F
1 3/4" Height
Unfinished



90-2593
Large Hang Straight Swivel
1/4 F x 1/8 M
Ring Nut to Seat 1 1/16"
1 1/2" Height
Unfinished



90-2336
Large Hang Straight Swivel
1/4 F x 1/4 F
Ring Nut to Seat 1 1/16"
1 1/2" Height
Unfinished



90-2337
Large Hang Straight Swivel
1/4 F x 1/4 F
Ring Nut to Seat 1 1/16"
1 1/2" Height
Barrel Nickel Finish

Brass *Unfinished*

Brass Ball Armbacks – Unfinished



90-2172
5/8" x 3/4"
1/8 IP x1/8 IP



90-2173
3/4" x 1 1/16"
1/8 IP x 1/8 IP



90-2174
7/8" x 1 1/16"
1/8 IP



90-2175
7/8" x 1 1/16"
1/8 IP x 1/8 IP



90-2176
7/8" x 1 1/16"
1/4 IP x 1/8 IP



90-2177
7/8" x 1 1/16"
1/4 IP x 1/4 IP

Brass Armbacks – Unfinished



90-2180
5/8" x 13/16"
1/8 IP x1/8 IP x1/8 IP



90-2373
5/8" x 13/16"
1/8 IP x 1/8 IP
x1/8 IP x 1/8 IP

Brass Large Elbows – Unfinished



90-2178
1 1/8" x 1 3/16"
1/4 IP x 1/4 IP



90-2179
1 1/8" x 1 3/16"
3/8 IP x 3/8 IP

10 lbs MAX

Die Cast Swag Hook Kits

90-450 *Brass Plated*
90-451 *Ant. Brass*
90-452 *Black*
90-453 *Ant. Copper*
90-456 *Chrome*
90-770 *White*

Shown: brass finish.
Kits contain 2 hooks and hardware shown
Packing: *Poly Bagged*





Die Cast Revolving Swivel Hooks

90-815 *Brass Plated*
90-816 *Ant. Brass*
90-817 *Black*

Shown: black finish.
Kits contain 1 hook and hardware shown
Packing: *Poly Bagged*





Die Cast Large Swag Hooks

90-440 *Brass Plated*
90-441 *Ant. Brass*
90-442 *Black*

Shown: Ant. brass finish.
Kits contain 1 hook and hardware shown
Packing: *Poly Bagged*





Drop Ceiling Hook Set

90-846
White
Contain 2 sets per bag.
No hardware needed
Packing: *Poly Bagged*



Drop Ceiling T-Bar Track Clips

TP185
To Attach Track Lighting to a Drop Ceilings.
4 Pieces per bag.
Packing: *Poly Bagged*



NOTE: *Compatable steel locknut is Item# 90-018*

SPACERS & CANDLE CUPS

Steel / Brass *Assorted Finishes*

Steel Spacers



7/16" Hole–1" Height
7/8" Dia.–1" Base Dia.
90-2277 Brass Plated
90-2278 Nickel Plated
90-2279 Ant. Brass
90-2280 Unfinished



7/16" Hole–1½" Height
7/8" Dia.–1" Base Dia.
90-2281 Brass Plated
90-2282 Nickel Plated
90-2283 Ant. Brass
90-2284 Unfinished



7/16" Hole–2" Height
7/8" Dia.–1" Base Dia.
90-2285 Brass Plated
90-2286 Nickel Plated
90-2287 Ant. Brass
90-2288 Unfinished

Steel Candle Cups



7/16" Hole–1⅞" Height
1" Diameter
80-1183 Brass Plated
80-1184 Nickel Plated
80-1185 Unfinished



7/16" Hole–3" Height
1" Diameter
80-1186 Brass Plated
80-1187 Unfinished

Solid Brass Candle Cup



7/16" Hole–1⅞" Height
1" Diameter
90-2227 Polished & Lacquered
90-2228 Polished Nickel
90-2226 Unfinished

Solid Brass Spacers



7/16" Hole– 1" Height
7/8 " Dia.–1" Base Dia.
90-2223 Polished & Lacquered
90-2222 Unfinished



7/16" Hole–1½" Height
7/8" Dia.–1" Base Dia.
90-2225 Polished & Lacquered
90-2224 Unfinished



7/16" Hole–2" Height
7/8" Dia.–1" Base Dia.
90-2221 Polished & Lacquered
90-2220 Unfinished

Flanged Steel Necks



1/2" Height–7/8" Bottom
90-2192 *Brass Plated*
90-2212 *Nickel Plated*
90-2271 *Ant. Brass*
90-2213 *Unfinished*



1" Height–7/8" Bottom
90-2193 *Brass Plated*
90-2214 *Nickel Plated*
90-2272 *Ant. Brass*
90-2215 *Unfinished*



1½" Height–7/8" Bottom
90-2194 *Brass Plated*
90-2216 *Nickel Plated*
90-2273 *Ant. Brass*
90-2217 *Unfinished*



2" Height–7/8" Bottom
90-2195 *Brass Plated*
90-2218 *Nickel Plated*
90-2274 *Ant. Brass*
90-2219 *Unfinished*



7/16" Hole–9/16" Height
11/16" Top–7/8" Bottom
90-2230 *Brass Plated*
90-2275 *Ant. Brass*
90-2229 *Unfinished*



9/16" Hole–9/16" Height
11/16" Top–7/8" Bottom
90-2232 *Brass Plated*
90-2276 *Ant. Brass*
90-2231 *Unfinished*



7/16" Hole–1" Height
13/16" Top–Bottom Seats 1⅜"
90-2190 *Brass Plated*
90-2201 *Nickel Plated*
90-2199 *Ant. Brass*
90-2202 *Unfinished*



9/16" Hole–1" Height
13/16" Top–Bottom Seats 1⅜"
90-2191 *Brass Plated*
80-2121 *Nickel Plated*



7/16" Hole–1 3/16" Height
3/4" Top–Bottom Seats 1¾"
90-2188 *Brass Plated*
90-2200 *Nickel Plated*
90-2197 *Ant. Brass*
90-2196 *Unfinished*



9/16" Hole–1 3/16" Height
3/4" Top–Bottom Seats 1¾"
90-2189 *Brass Plated*

CANDLE COVERS

Candelabra Drip / Plain *Plastic • Paper*

Plastic Drip Candle Covers – 13/16" Inside Dia. – 7/8" Outside Dia.



White Plastic with Gold Drip

90-1509	2"
90-352	3"
90-372	4"



Black Plastic with Gold Drip

90-1510	2"
90-366	3"
90-374	4"



Antique Plastic Drip

90-1511	2"
90-1262	2½"
90-1512	3"
90-1263	3½"
90-1264	4"



White Plastic Drip

90-1505	2"
90-1256	2½"
90-1506	3"
90-1258	3½"
90-1260	4"



Ivory Plastic Drip

90-1507	2"
90-1257	2½"
90-1508	3"
90-1259	3½"
90-1261	4"

Plastic *Candle Covers*
13/16" Inside Dia. – 7/8" Outside Dia.



White Plastic

90-1103	1½"	80-2011	4¾"
90-931	1¾"	90-905	5"
90-901	2"	90-906	6"
90-902	2¼"	90-907	8"
90-903	2¾"	90-908	12"
90-904	3"	90-909	24"
90-1148	3½"	90-910	36"
90-370	4"		



Black Plastic

90-2393	4"



Cream Plastic

90-2531	2"
90-2620	3"
90-2576	3½"
90-2443	4"
90-2444	6"
90-2445	12"

Ivory Drip Paper Candle Covers
13/16" Inside Dia. – 7/8" Outside Dia.



Ivory Drip Paper

80-1487	2"
80-1454	4"
80-1455	6"

Edison Drip / Plain *Plastic • Paper*

Plastic Drip Candle Covers 1 3/16" Inside Dia. – 1 1/4" Outside Dia.



White Plastic with Gold Drip

90-1514 2"
90-369 3"
90-373 4"



Black Plastic with Gold Drip

90-1513 2"
90-368 3"
90-375 4"



Antique Plastic Drip

90-1247 2"
90-1249 3"
90-1251 4"

White Plastic Drip

90-1246 2"
90-1248 3"
90-1250 4"



Ivory Plastic Drip

90-1515 2"
90-1516 3"
90-1517 4"

Plastic *Candle Covers*
1 3/16" Inside Dia. – 1 1/4" Outside Dia.



White Plastic

90-1104	2"	90-911	6"
90-913	2 1/8"	90-912	8"
90-914	3"	90-916	12"
90-371	4"	90-917	24"
90-915	5"	90-918	36"



Black Plastic

80-1555 4"



Cream Plastic

90-2446 4"
90-2447 6"
90-2448 12"

Ivory Drip Paper Candle Covers
1 3/16" Inside Dia. – 1 1/4" Outside Dia.



Ivory Drip Paper

80-1456 4"
80-1457 6"
80-1458 8"

Resin Drip *Edison Base • Candelabra Base*

Edison Base Oversize Resin Full Drip – 1.25" Inside Dia. – 2" Outside Dia.



80-1619 6" Amber



80-1621 6" Ivory



80-1620 4" Amber



80-1622 4" Ivory

Edison Base Resin Half Drip – 1.25" Inside Dia. – 1.55" Outside Dia.



80-1632 6" Amber



80-1627 6" Ivory



80-1633 4" Amber



80-1628 4" Ivory

Candelabra Base Resin Half Drip – .88" Inside Dia. – 1.15" Outside Dia.



80-1634 6" Amber



80-1629 6" Ivory



80-1635 4" Amber



80-1630 4" Ivory

Bee's Drip (Bee's Wax) *Edison Base • Candelabra Base*

Edison Base Bee's Drip – 1.25" Inside Dia. – 1.55" Outside Dia. 40W Max.



Ivory Bee's Drip

80-2081	1⅝"
80-2082	3"
80-2083	4"
80-2084	6"



Amber (Honey) Bee's Drip

80-2085	1⅝"
80-2086	3"
80-2087	4"
80-2088	6"

Candelabra Base Bee's Drip – .88" Inside Dia. – 1.15" Outside Dia. 40W Max.



Ivory Bee's Drip

80-1971	1⅝"
80-1972	3"
80-1973	4"
80-1987	6"



Amber (Honey) Bee's Drip

80-1974	1⅝"
80-1975	3"
80-1976	4"
80-1988	6"

#3 Beaded Chain
3/32" Dia. 250 Ft. Spool



90-122
Brass Finish



90-123
Nickel Finish

#6 Beaded Chain
1/8" Dia. 100 Ft. Spool



90-124
Brass Finish



90-125
Nickel Finish

Pull String



90-1034
3Ft. Pull String – Nickel Bell & Connector

90-2528
3Ft. Pull String – Brass Bell & Connector

Connector for #3 Beaded Chain



90-127
Brass Plated



90-173
Nickel

Connector for #6 Beaded Chain



90-129
Brass Plated



90-128
Nickel

Bells for #3 & #6 Beaded Chain



90-117
Brass Plated



90-116
Nickel

Tassels & Pulls



90-533
Wood 1¼"



90-522
Black 5"



90-521
Gold 5"



90-503
White 5"



90-534
Gold 7"

Glass Prisms & U-Drops



90-300
1½" Clear



90-305
1½"
Aurora Borealis



90-306
2" Clear



90-312
3" Clear
"U" Drop



90-317
3" Aurora Borealis
"U" Drop



90-318
4" Cut
Spear



90-319
6" Cut
Spear

30% Lead Crystal



90-777
3 Bead
14 mm



90-778
4 Bead
14 mm



90-784
1 1/2" Plug
14 mm Bead



90-783
1 3/4" Plug
14 mm Bead



90-780
1½" with
14 mm Bead



90-779
2" with
14 mm Bead



90-781
Ball
30 mm



90-782
Ball
40 mm

90-753
30% Lead Crystal
(54 Bead – 14mm)
Length: 1 meter (39 inch)



Crystal Clips



90-693 Gold
90-1779 Silver
Crystal Clip



90-691 Gold
90-1780 Silver
Small Bow-Tie Clip



90-692 Gold
90-1781 Silver
Large Bow-Tie Clip

Crystal Pins



90-747 1½" Brass Pins (250/bag)



90-748 1½" Silver Pins (250/bag)

90-934
Crystal Cleaner
Trigger Spray Bottle (32oz.)



Lamp Shade Wrapping



90-725
Cellophane Lamp Shade Wrap
4¾" x 500 ft. Roll

Electrical Tape



90-1420 Black
90-1814 White
Electrical Tape 3/4" x 60 ft.

Circline Clips



90-935
Circleline Fluorescent Clip

Corks



90-188	⅝" x ¾"
90-189	¾" x 1"
90-190	1 x 1¼"

Brass Plated S-Hooks



90-013	5/8"
90-008	1"
90-009	1¼"
90-010	1⅝"

Brass Plated Rings



90-011	3/4"
90-012	1"

Nylon Wire Ties



90-1822
11" Nylon Zipties
100 Pcs./Pack

Felt Pads and Dots

More Colors Available – Call for Information



90-489
Green Felt – 36" Wide
Sold by the Yard

90-488
Green Felt – 3/4" Dots
Sold by Roll Only
(1000 per Roll)

90-487
Green Felt – 1/2" Dots
Sold by Roll Only
(1000 per Roll)



Canopies & Glass Holders













Canopy Parts & Kits 170-172
Canopies & Extensions 173
Canopy, Fan & Blank Up Kits 174-175
Wired Fixture, Bent Glass, Ceiling Pans 176-178
Fitters & Ball Glass Holders 179
Cast Brass Canopies 180-181
Heavy 2-Step Steel Canopies 182
Wall Sconces 183
U-Channel Glass Holders 184-185
Glass Holders & Fixture Bodies 186

Canopy Only



Ribbed Canopy

90-1674 Brass Finish
90-1675 Ant. Brass Finish
90-1677 Black Finish
90-1680 White Finish
90-1681 Chrome Finish

Shown: antique brass finish

Dimensions:

Diameter	5"
Center Hole	7/16"
Bar Holes	2 –8/32

Packing: 200/Master

Canopy Only



Ribbed Canopy

90-1682 Brass Finish
90-1683 Ant. Brass Finish
90-1684 Chrome Finish
90-1685 White Finish
90-1686 Black Finish
90-1844 Brushed Nickel Finish
90-1845 Brushed Pewter Finish

Shown: brass finish

Dimensions:

Diameter	5"
Center Hole	1 1/16"

Packing: 200/Master

Canopy Parts Bags

10 lbs MAX



1" Loop Parts Bag

90-1687 Brass Finish
90-1688 Ant. Brass Finish
90-1689 Black
90-1690 White
90-1691 Chrome Finish

25 lbs MAX



Screw Collar Loop Parts Bag

90-1692 Brass Finish
90-1693 Ant. Brass Finish
90-1694 Chrome Finish
90-1695 White
90-1696 Black

Ribbed Canopy Kit

90-052 Brass Finish
90-053 Ant. Brass Finish
90-054 Ant. Copper Finish
90-055 Black Finish
90-056 White Finish
90-058 Chrome Finish

Shown: antique brass finish

Dimensions:

Diameter	5"
Center Hole	7/16"
Bar Holes	2 –8/32

Packing: 25/Master



Includes Hardware

10 lbs MAX



Ribbed Canopy Kit

90-192 Brass Finish
90-193 Ant. Brass Finish
90-196 Chrome
90-197 White Finish
90-198 Black Finish
90-1846 Brushed Nickel Finish
90-1847 Brushed Pewter Finish

Shown: brass finish

Dimensions:

Diameter	5"
Center Hole	1⅛"

Packing: 25/Master



Includes Hardware

25 lbs MAX



Standard Canopy Kit

90-062 Brass Finish
90-063 Ant. Brass Finish
90-065 Black Finish
90-066 White Finish
90-068 Chrome Finish

Shown: black finish

Dimensions:

Diameter	5"
Center Hole	7/16"
Bar Holes	2 –8/32

Packing: 25/Master



Includes Hardware

10 lbs MAX







Includes Hardware

10 lbs MAX

Contemporary Canopy Kit

90-890 Brass Finish
90-891 Chrome Finish
90-892 Ant. Brass Finish
90-893 Black Finish
90-894 White Finish

Shown: chrome finish

Dimensions:

Diameter	5"
Center Hole	7/16"
Bar Holes	2–8/32

Packing: 25/Master





Includes Hardware

25 lbs MAX

Ribbed Canopy Hanger Kit

90-1098 Brass Finish
90-1099 Ant. Brass Finish
90-1100 Black Finish
90-1101 White Finish
90-1102 Chrome Finish

Shown: brass finish

Dimensions:

Diameter	5"
Center Hole	1 ⅛"
with 1yd. 8 gauge chain	

Packing: 25/Master





Includes Hardware

10 lbs MAX

Bath Swag Canopy Kit

90-194 Brass Finish
90-191 Ant. Brass Finish
90-195 Black Finish
90-199 White Finish

Shown: White finish

Dimensions:

Diameter	5"
3– 7/16" Holes	

Packing: 25/Master

Plain Deep Fixture Canopy (Canopy Only)

90-047 *Brass Finish*
90-050 *Chrome Finish*

Shown:chrome finish

Dimensions:

Diameter	*5"*
Center Hole	*1 1/16"*
Depth	*1 3/4"*



Plain Deep Fixture Canopy (Canopy Only)

90-051 *Brass Finish*
90-061 *Chrome Finish*

Shown:brass finish

Dimensions:

Diameter	*5"*
Center Hole	*7/16"*
Depth	*1 3/4"*



Plain Shallow Fixture Canopy (Canopy Only)

90-048 *Brass Finish*

Dimensions:

Diameter	*5"*
Center Hole	*1 1/16"*



Canopy Extension

90-242 *Brass Finish*
90-108 *White Finish*
90-1518 *Chrome Finish*

Dimensions:

Diameter	*5 3/4"*
Fits 5" canopy	
Extension	*1 1/2"*







Includes Hardware

25 lbs MAX

Deep Canopy Kit

90-057 Brass Finish
90-1697 Chrome Finish

Shown: brass finish

Dimensions:

Diameter	5"
Center Hole	1⅛"
Depth	1¾"

Packing: 25/Master





Includes Hardware

10 lbs MAX

Canopy Kit with Convenience Outlet

90-040 Black Finish
90-041 Brass Finish
90-1072 White Finish

Shown: brass finish

Dimensions:

Diameter	5"
Center Hole	7/16"
Bar Holes	2–8/32

Packing: 25/Master



Intermediate Socket !

4" Wired Fan Light Holder w/On-Off Pull Chain & Intermediate Socket

77-461 White Finish
77-462 Brass Finish
77-466 Ant. Brass Finish

Shown: antique brass finish

Blank Up Kit for 4" Box

90-069 White Finish

Dimensions:

Diameter	5"
Bar Holes	2–8/32
Center to Center	3½"

Packing: 250/Master



Includes Hardware



Blank Up Kit for 3" Box

90-151 White Finish

Dimensions:

Diameter	5"
Bar Holes	2–8/32
Center to Center	3"

Packing: 250/Master



Includes Hardware



Blank Up Kit

90-045 White Finish

Dimensions:

Diameter	5"
Center Hole	7/16"

Packing: 25/Master



Includes Hardware



Blank Up Kit

90-044 Brass Finish

90-0580 White Finish

90-119 Black Finish

Shown: black finish

Dimensions:

Diameter	5"
Bar Holes	2–8/32

Packing: 25/Master



Includes Hardware







Includes Hardware

3¼" Wired Holder

90-230 Brass Finish
90-330 Ant. Brass Finish
90-430 White Finish
90-724 Black Finish
90-840 Chrome Finish
90-1435 Brushed Nickel

Shown: brass finish
Packing: 25/Master





Includes Hardware

4" Wired Holder

90-231 Pol. Brass Finish
90-331 Ant. Brass Finish
90-431 White Finish
90-841 Chrome Finish
90-749 Black Finish
90-1437 Brushed Nickel

Shown: polished brass finish
Packing: 25/Master





Includes Hardware

3¼" Wired Holder with Convenience Outlet

90-121 Chrome Finish
Packing: 25/Master

6" One Light Ceiling Pan

90-755 Chrome Finish
90-756 Brass Finish
90-686 White Finish
90-763 Ant. Brass Finish
90-1448 Brushed Nickel

Shown: brass finish
Packing: 25/Master



Includes Hardware



8" Two Light Ceiling Pan

90-757 Chrome Finish
90-876 Brass Finish
90-684 White Finish
90-877 Ant. Brass Finish
90-1439 Brushed Nickel

Shown: white finish
Packing: 25/Master



Includes Hardware



10" Two Light Ceiling Pan

90-758 Chrome Finish
90-766 Brass Finish
90-685 White Finish
90-767 Ant. Brass Finish
90-1433 Brushed Nickel

Shown: chrome finish
Packing: 25/Master



Includes Hardware







Includes Hardware

90-234

2 Light Bent Glass Fixture Holder

White Finish.

Dimensions:
Diameter 4¾"
Height 5"

Packing: 25/Master





Includes Hardware

90-235

2 Light Bent Glass Fixture Holder with Pull Chain Switch

White Finish.

Dimensions:
Diameter 4¾"
Height 5"

Packing: 25/Master



90-244

Bent Glass Ceiling Holder

White Finish.

Dimensions:
Diameter 4¾"
Height 1"

Neckless Ball Holders Kits



4" Neckless Ball Holder Kit
For 3⅞" Dia. Glass
8FT. 18/3 SVT
90-615 *White*
Packing: *25/Master*



Includes Hardware



5" Neckless Ball Holder Kit
For 5¼" Dia. Glass
8FT. 18/3 SVT
90-616 *White*
Packing: *25/Master*

Neckless Ball Holders with Inserts



4" Neckless Ball Holder
90-649 *White*
90-706 *Brass Finish*



5" Neckless Ball Holder
90-650 *White*
90-707 *Brass Finish*

Fitter



6" Fitter
90-1504 *White*
90-303 *Ant. Brass Finish*



90-2382 *Ant. Brass Finish*

Dimensions:

Diameter	*5½"*
Center Hole	*1 1⁄16"*
Height	*1½"*

Packing: *25/Master*



90-2383 *Polished Brass Finish*

Dimensions:

Diameter	*5½"*
Center Hole	*1 1⁄16"*
Height	*1½"*

Packing: *25/Master*



90-2384 *Polished Nickel Finish*

Dimensions:

Diameter	*5½"*
Center Hole	*1 1⁄16"*
Height	*1½"*

Packing: *25/Master*



90-2482 *Bronze Finish*

Dimensions:

Diameter	*5½"*
Center Hole	*1 1⁄16"*
Height	*1½"*

Packing: *25/Master*

90-039 *Ant. Brass Finish*

Dimensions:

Diameter	*4⅜"*
Center Hole	*1 1/16"*
Height	*1"*

Packing: *25/Master*



90-2480 *French Gold Finish*

Dimensions:

Diameter	*6½"*
Center Hole	*1 1/16"*
Height	*2½"*

Packing: *25/Master*



90-2481 *Bronze Finish*

Dimensions:

Diameter	*6½"*
Center Hole	*1 1/16"*
Height	*2½"*

Packing: *25/Master*



HEAVY 2-STEP STEEL CANOPIES

SATCO®

25 lbs MAX





90-2491 *Polished Brass Finish w/Matching Screw Collar Loop*

Dimensions:

Diameter	*5½"*
Center Hole	*1⅛"*
Height	*2¼"*

Packing: *25/Master*





90-2492 *Antique Brass Finish w/Matching Screw Collar Loop*

Dimensions:

Diameter	*5½"*
Center Hole	*1⅛"*
Height	*2¼"*

Packing: *25/Master*





90-2489 *Chrome Finish w/Matching Screw Collar Loop*

Dimensions:

Diameter	*5½"*
Center Hole	*1⅛"*
Height	*2¼"*

Packing: *25/Master*





90-2490 *Brushed Nickel Finish w/Matching Screw Collar Loop*

Dimensions:

Diameter	*5½"*
Center Hole	*1⅛"*
Height	*2¼"*

Packing: *25/Master*





90-2493 *Old Bronze Finish w/Matching Screw Collar Loop*

Dimensions:

Diameter	*5½"*
Center Hole	*1⅛"*
Height	*2¼"*

Packing: *25/Master*

25 lbs MAX

1/4 IP Matching Screw Collar Loops w/Ring



90-335	**90-336**	**90-337**	**90-2494**	**90-2495**
Polished Brass	*Antique Brass*	*Polished Chrome*	*Brushed Nickel*	*Old Bronze*

3¼" Wired Wall Bracket

90-708 Brass Finish
90-775 Black Finish
90-776 Ant. Brass Finish
90-1085 White Finish

Shown: antique brass finish

Packing: 25/Master



Includes Hardware



3" Wired Wall Bracket

with Bottom Turn Knob Switch

90-709 Brass Finish

Packing: 25/Master



Includes Hardware



1⅝" Wired Wall Bracket

with Bottom Turn Knob Switch

90-120 Brass Finish
90-1407 Ant. Brass Finish

Shown: brass finish

Packing: 25/Master



Includes Hardware







Includes Hardware

90-1306

2 Light U-Channel Glass Holder

2 Light for Use with 14" U-Bend Glass

Packing: 25/Master





Includes Hardware

90-1299

1 Light U-Channel Glass Holder

1 Light for Use with 7" U-Bend Glass

Packing: 25/Master





Includes Hardware

90-1307

4 Light U-Channel Glass Holder

4 Light for Use with 24" U-Bend Glass

Packing: 25/Master

90-768

2 Light U-Channel Glass Holder

2 Light–Convenience Outlet for Use with 14" U-Bend Glass

Packing: 25/Master



Includes Hardware



90-246

1 Light U-Channel Glass Holder

1 Light Holder with Bottom Turn Knob Switch for Use with 7" U-Bend Glass

Packing: 25/Master



Includes Hardware



90-769

4 Light U-Channel Glass Holder

4 Light–Convenience Outlet for Use with 24" U-Bend Glass

Packing: 25/Master



Includes Hardware





1⅝" Fitter
90-656 *Vacuum Brass Finish*



1⅝" Fitter
90-654 *Vacuum Brass Finish*
90-655 *Chrome Finish*



2⅝" Fitter
90-659 *Vacuum Brass Finish*
90-705 *Ant. Brass Finish*



3" Fitter
90-660 *Vacuum Brass Finish*



2¼" Fitter
90-577 *Brass Finish*
90-677 *Ant. Brass Finish*
90-878 *Chrome Finish*



3¼" Fitter
90-578 *Brass Finish*
90-678 *Ant. Brass Finish*
90-879 *Chrome Finish*



2¾" Fixture Body and Cover Vacuum Brass Finish
90-657 *3 Arm Holes*
90-658 *5 Arm Holes*



4" Fitter
90-439 *Brass Finish*
90-679 *Ant. Brass Finish*
90-880 *Chrome Finish*



4¼" Fitter
90-2404 *Brass Finish*
90-2405 *Chrome Finish*

Glassware & Shades















Globe, Schoolhouse, Drum & Mushroom Glass 188-191
Screw Fitter & Cased Glass 192
Lexan & Poly 193
Hall, Porch, I.E.S. Fixture & Specialty Glass 194-195
Bent Glass (Round Square & U-Channel) 186-187
Clip on Shades 198-200

Globes *White • Prismatic • Clear*



50-143 *Sprayed Glossy White Ball*

Dia.: 6" Fitter: 3 1/4"



50-927 *Clear Prismatic Ball*

Dia.: 6" Fitter: 3 1/4"



50-186 *White Ball*

Dia.: 5" Fitter: 3 1/4"



50-928 *Clear Prismatic Ball*

Dia.: 8" Fitter: 4"



50-144 *Sprayed Glossy White Ball*

Dia.: 8" Fitter: 4"

A Satco Best Seller!

50-351 *Blown Glossy Opal Ball*

Dia.: 6" Fitter: 3 1/4"



50-151 *Blown Glossy Opal Ball*

Dia.: 8" Fitter: 4"



Blown Glossy Opal Ball

50-153 *Dia.: 10" Fitter: 4"*
50-155 *Dia.: 12" Fitter: 4"*



Blown Glossy Opal Ball

50-218 *Dia.: 14" Fitter: 6"*





Blown Glossy Opal Neckless Ball

50-312 *Dia.: 6"*
Opening: 3"

50-152 *Dia.: 8"*
Opening: 3 7/8"

50-154 *Dia.: 10"*
Opening: 3 7/8"

50-156 *Dia.: 12"*
Opening: 5 1/4"

50-157 *Dia.: 14"*
Opening: 5 1/4"



Globes *Blown Opal*



50-275 *Blown Opal*
Dia.: 9" Fitter: 4"



50-276 *Blown Opal*
Dia.: 10" Fitter: 4"



Blown Opal
Schoolhouse Globes

50-468 *Dia.: 12" Fitter: 6"*
50-469 *Dia.: 14" Fitter: 6"*
50-470 *Dia.: 16" Fitter: 6"*
50-471 *Dia.: 18" Fitter: 6"*



A Satco Best Seller!

Sprayed Inside White Mushroom Glass

50-329	Dia.: 7 1/2"	Fitter: 5 7/8"	Ht.: 3 5/8"
50-330	Dia.: 9 1/2"	Fitter: 7 7/8"	Ht.: 4"
50-331	Dia.: 11 1/2"	Fitter: 9 7/8"	Ht.: 4 9/16"



Sprayed Inside White Drum Glass

50-334	Dia.: 6 5/8"	Fitter: 5 7/8"	Ht.: 3 1/2"
50-335	Dia.: 8 11/16"	Fitter: 7 7/8"	Ht.: 4 "
50-336	Dia.: 10 5/8"	Fitter: 9 7/8"	Ht.: 4 3/16"

50-109 *Etched with Grape Design*

Dia.: 5 9/16" Fitter: 6" Ht.: 3 3/4"

A Satco Best Seller!



Outside White Drum Glass with Clear Sides and Bottom

50-105	Dia.: 6 1/2"	Fitter: 5 7/8"	Ht.: 3 1/2"
50-106	Dia.: 8 3/8"	Fitter: 7 7/8"	Ht.: 4"
50-107	Dia.: 10 7/16"	Fitter: 9 7/8"	Ht.: 4 1/2"



Globes *White • Ribbed • Clear*

50-332 *Inside Sprayed White*
Dia.: 3 1/4"
Screw Fitter: 3 11/64"
Height: 6 1/4"



50-216 *Inside Sprayed White*
Dia.: 6"
Screw Fitter: 3 11/64"

A Satco Best Seller!



50-547 *Clear Ribbed Glass*
Dia.: 3 11/32"
Screw Fitter: 3 11/64"
Height: 6 15/16"



50-919 *Clear Glass*
Dia.: 3 11/32"
Screw Fitter: 3 11/64"
Height: 6 15/16"



Cased Class *Green • Opal • Butterscotch*

Cased Pharmacy Shade
Width:9" Slip Side Holes: 7/16"
50-667 *Green*
50-666 *Opal*
50-825 *Butterscotch*



A Satco Best Seller!

Cased Shade
Dia.:10" Fitter: 2 1/4" Height: 5"
50-664 *Opal*
50-665 *Green*



50-727 Lexan® White Ball

Dia.: 6"
Screw Fitter: 3 11/64"

50-231 Poly Ball

Dia.: 6"
Fitter: 3 1/4"



50-233 Poly Ball

Dia.: 6"
Screw Fitter: 3 11/64"



Poly Globe with 4" Lip Fitter

50-171 Dia.: 8"
50-172 Dia.: 10"
50-173 Dia.: 12"



Poly Globe with 3 3/8" or 4" Neckless Opening

50-429 Dia.: 6"
Opening: 3 3/8"
50-168 Dia.: 8"
Opening: 4"
50-169 Dia.: 10"
Opening: 4"

Poly Globe with 5 1/4" Neckless Opening

50-170 Dia.: 12"
50-230 Dia.: 14"
50-238 Dia.: 16"
50-239 Dia.: 18"



Lexan® Prismatic Cylinders

Dia.: 3 3/4"
Fitter: 3 1/4"

50-721 Ht.: 6 1/4"
50-723 Ht.: 7 1/4"
50-725 Ht.: 8 1/2"



Lexan® Prismatic Cylinders

Dia.: 3 3/4"
Screw Fitter: 3 11/64"

50-722 Ht.: 6 1/4"
50-724 Ht.: 7 1/4"
50-726 Ht.: 8 1/2"



Lexan® White Cylinders

Dia.: 3 3/4"
Screw Fitter: 3 11/64"

50-729 Ht.: 6 1/4"
50-730 Ht.: 7 1/4"

A Satco Best Seller!

50-728 Lexan® Smoke Ball

Dia.: 6"
Screw Fitter: 3 11/64"



Globes *Assorted Finished*



50-114 *Clear Porch Globe*

Dia.: 3 3/4" Fitter: 3 1/4"
Ht.: 4 1/2"



50-112 *Clear "Pineapple" Glass*

Dia.: 5 1/2" Fitter: 3 1/4"

50-382 *Frosted Porch Globe*

Dia.: 3 3/4" Fitter: 3 1/4"
Ht.: 4 1/2"



50-108 *Etched Hall Glass Clear Bottom*

Dia.: 5 9/16" Fitter: 3 1/4"
Ht.: 5"



50-111 *White with Clear Bottom Bath Shade*

Dia.: 5 1/4" Fitter: 3 1/4"
Ht.: 4 1/2" Depth: 5 13/16"

I.E.S. Shade



50-165
Dia.: 6" Fitter: 2 1/4" Ht.: 4 3/4"



Bobesches

50-777 Dia.: 4 " 1" Cent. hole: 5 pins
50-778 Dia.: 5 " 1" Cent. hole: 10 pins
50-779 Dia.: 6 " 1/2" Cent. hole: 8 pins

I.E.S. Shade



A Satco Best Seller!

50-166
Dia.: 8" Fitter: 2 1/4" Ht.: 5 3/4"



50-222 Acid Etched with Grape Design
Dia.: 4 1/2" Fitter: 1 5/8" Ht.: 5"



I.E.S. Shade

50-167
Dia.: 10" Fitter: 2 7/8" Ht.: 5 1/2"



A Satco Best Seller!

50-120 Acid Etched with Grape Design
Dia.: 4 3/8" Fitter: 1 5/8" Ht.: 5"

Bend Glass *Round*



White & Grape Pattern

50-194 13" Round
50-195 15" Round

Packing: 12/Master



White & Gold Sunburst Pattern

50-196 13" Round
50-197 15" Round

Packing: 12/Master

White

50-376 13" Round

Packing: 12/Master



Sunburst Pattern

Packing: 12/Master

Sunburst Pattern Semi Bend & Regular Bend Glass

Semi Bend/Shallow

50-505 Dia.: 11" Depth: 1/2"
50-202 Dia.: 11" Depth: 3/4"
50-506 Dia.: 12" Depth: 7/8"
50-203 Dia.: 13" Depth: 1 1/8"
50-204 Dia.: 14" Depth: 1 1/8"
50-205 Dia.: 15" Depth: 1"
50-508 Dia.: 16" Depth: 1 1/4"
50-307 Dia.: 17" Depth: 3/4"

Regular Bend/Deep

50-198 Dia.: 11" Depth: 1 3/4"
50-199 Dia.: 13" Depth: 1 7/8"
50-200 Dia.: 14" Depth: 2 1/2"
50-201 Dia.: 15" Depth: 2 1/2"
50-308 Dia.: 17" Depth: 2 1/2"

Bend Glass *Square • U-Channel*



White with Clear Floral Pattern

50-190 *12" Square*
50-191 *14" Square*



White & Gold Scroll Pattern

50-192 *13" Square*
50-193 *15" Square*



Ruffled Edge White with Wheat Design

50-503 *12" Square*

White

50-374 *12" Square*
50-375 *14" Square*



White "U" Channel

50-378 *7" (vertical) hole 1 3/4" from end 1/8 slip*
50-379 *14" (horizontal) hole centered 1/8 slip*
50-380 *24" (horizontal) holes 6 1/2" from ends 1/8 slip*



Diamond "U" Channel

50-234 *7" (vertical) hole 1 3/4" from end 1/8 slip*
50-235 *14" (horizontal) hole centered 1/8 slip*
50-236 *24" (horizontal) holes 6 1/2" from ends 1/8 slip*



90-2362
Ivory Floral
Top: 3" Bottom: 5" Side: 4¼"



90-2358
Beige Beaded Floral
Top: 3" Bottom: 5" Side: 4¼"



90-2359
Khaki Beaded Floral
Top: 3" Bottom: 5" Side: 4¼"



90-2360
White Shantung
Top: 3" Bottom: 5" Side: 4¼"



90-2361
Ivory Shantung
Top: 3" Bottom: 5" Side: 4¼"



90-2357
Beige Shantung
Top: 3" Bottom: 5" Side: 4¼"



90-2363
Beige Folded Pleat
Top: 3" Bottom: 5" Side: 4"



90-2364
White Folded Pleat
Top: 3" Bottom: 5" Side: 4"



90-2365
Black Folded Pleat
Top: 3" Bottom: 5" Side: 4"



90-2486
Cream Bamboo Linen
Top: 3" Bottom: 6" Side: 4½"



90-2487
French Beige Flower Silk
Top: 3" Bottom: 6" Side: 4½"



90-2488
Cream Leaf Linen
Top: 3" Bottom: 6" Side: 4½"



90-2485
Black Linen
Top: 3" Bottom: 6" Side: 4"



90-1270
White Pleated Round
Top: 3" Bottom: 4" Side: 4"



90-1271
Bone Pleated Round
Top: 3" Bottom: 4" Side: 4"



90-1273
Beige Pleated Round
Top: 3" Bottom: 4" Side: 4"



90-1272
Black Pleated Round
Top: 3" Bottom: 4" Side: 4"



90-2366
White Swirl Folded Pleat
Top: 3" Bottom: 5" Side: 4"



90-2367
Beige Swirl Folded Pleat
Top: 3" Bottom: 5" Side: 4"



Beige Leather Look
90-2524 Top: 3" Bottom: 5½" Side: 5¼"
90-2525 Top: 2⅛" Bottom: 4" Side: 5⅛"



Cream Leather Look
90-2526 Top: 3" Bottom: 5½" Side: 5¼"
90-2527 Top: 2⅛" Bottom: 4" Side: 5⅛"



90-1277
White Silk Bell
Top: 3" Bottom: 5" Side: 4"



90-1275
Beige Parchment Round
Top: 3" Bottom: 4" Side: 4"



90-1276
White Linen Round
Top: 3" Bottom: 4" Side: 4"



90-1274
Black Round with Gold Interior
Top: 3" Bottom: 4" Side: 4"

Beaded Shades



90-1252
Amber Beaded Cone
Top: 1" Bottom: 5" Side: 4"



90-1253
Silver Beaded Cone
Top: 1" Bottom: 5" Side: 4"



90-1254
Blue Beaded Cone
Top: 1" Bottom: 5" Side: 4"



90-1255
Green Beaded Cone
Top: 1" Bottom: 5" Side: 4"



90-1335
Amber Beaded Square
Top: 3" Bottom: 4" Side: 4"



90-1336
Silver Beaded Square
Top: 3" Bottom: 4" Side: 4"



90-1337
Blue Beaded Square
Top: 3" Bottom: 4" Side: 4"



90-1338
Green Beaded Square
Top: 3" Bottom: 4" Side: 4"

Item No.	Page
Item #	Page #
25-1067	139
25-1069	139
25-1072	139
25-1074	139
25-1080	139
25-1081	139
50-105	191
50-106	191
50-107	191
50-108	194
50-109	191
50-111	194
50-112	194
50-114	194
50-120	195
50-143	188
50-144	188
50-151	189
50-152	189
50-153	189
50-154	189
50-155	189
50-156	189
50-157	189
50-165	195
50-166	195
50-167	195
50-168	193
50-169	193
50-170	193
50-171	193
50-172	193
50-173	193
50-186	188
50-190	197
50-191	197
50-192	197
50-193	197
50-194	196
50-195	196
50-196	196
50-197	196
50-198	196
50-199	196
50-200	196
50-201	196
50-202	196
50-203	196
50-204	196
50-205	196
50-216	192
50-218	189
50-222	195
50-230	193
50-231	193
50-233	193
50-234	197
50-235	197
50-236	197
50-238	193
50-239	193
50-275	190
50-276	190
50-307	196
50-308	196
50-312	189
50-329	191
50-330	191
50-331	191
50-332	192
50-334	191
50-335	191
50-336	191
50-351	189
50-374	197
50-375	197
50-376	196
50-378	197
50-379	197
50-380	197
50-382	194
50-429	193
50-468	190
50-469	190
50-470	190
50-471	190
50-503	197
50-505	196
50-506	196
50-508	196
50-547	192
50-664	192
50-665	192
50-666	192
50-667	192
50-721	193
50-722	193
50-723	193
50-724	193
50-725	193
50-726	193
50-727	193
50-728	193
50-729	193
50-730	193
50-777	195
50-778	195
50-779	195
50-825	192
50-919	192
50-927	188
50-928	188
77-461	174
77-462	174
77-466	174
79-200	137
79-201	137
79-203	137
79-204	137
79-205	137
79-206	137
79-209	137
79-210	137
79-211	137
79-212	137
79-213	137
79-233	137
79-306	139
79-432	139
79-455	138
79-457	138
79-458	138
79-460	138
79-464	138
80-1000	6
80-1001	6
80-1002	7
80-1003	7
80-1004	7
80-1005	7
80-1006	9
80-1007	9
80-1008	6
80-1009	6
80-1010	8
80-1011	8
80-1012	7
80-1013	7
80-1014	11
80-1015	11
80-1016	10
80-1017	10
80-1020	8
80-1021	8
80-1022	16
80-1023	16
80-1024	17
80-1025	17
80-1026	17
80-1027	17
80-1028	18
80-1029	18
80-1030	16
80-1031	16
80-1032	16
80-1033	16
80-1034	17
80-1035	17
80-1036	17
80-1037	17
80-1038	18
80-1039	18
80-1040	16
80-1041	16
80-1042	19
80-1043	19
80-1044	19
80-1045	19
80-1046	21
80-1047	21
80-1048	21
80-1049	21
80-1050	21
80-1051	21
80-1052	21
80-1053	21
80-1054	22
80-1055	22
80-1056	22
80-1057	22
80-1058	20
80-1059	20
80-1060	20
80-1061	20
80-1062	20
80-1063	20
80-1064	23
80-1065	23
80-1066	23
80-1067	23
80-1068	29
80-1069	29
80-1070	29
80-1071	29
80-1072	29
80-1073	35
80-1074	35,44
80-1075	35
80-1076	35,44
80-1077	54
80-1078	34
80-1080	37
80-1081	43
80-1082	43
80-1083	35
80-1087	60
80-1088	60
80-1089	60
80-1090	64
80-1091	64
80-1092	64
80-1093	62
80-1094	63
80-1095	63
80-1097	35
80-1098	7
80-1099	9
80-1100	8
80-1101	7
80-1103	47
80-1104	30
80-1105	30
80-1106	30
80-1107	30
80-1108	28
80-1109	28
80-1110	28
80-1111	28
80-1112	28
80-1113	39
80-1118	7
80-1119	7
80-1120	50
80-1124	93
80-1125	93
80-1126	93
80-1127	93
80-1128	93
80-1129	93
80-1130	93
80-1131	93
80-1132	92
80-1133	92
80-1134	92
80-1135	92
80-1136	92
80-1137	92
80-1138	92
80-1139	92
80-1140	95
80-1141	100
80-1142	100
80-1145	61
80-1146	61
80-1148	61
80-1149	35
80-1150	34
80-1155	39
80-1157	37
80-1158	7
80-1159	7
80-1161	26
80-1162	26
80-1163	96
80-1166	97
80-1167	97
80-1175	18
80-1176	18
80-1177	18
80-1178	18
80-1179	16
80-1180	16
80-1181	130,131,132
80-1182	130,131,132
80-1183	160
80-1184	160
80-1185	160
80-1186	160
80-1187	160
80-1188	9
80-1189	27
80-1190	17
80-1191	17
80-1192	7
80-1193	7
80-1194	8
80-1195	22
80-1196	22
80-1197	132
80-1198	62
80-1202	39
80-1204	146
80-1205	146
80-1210	25
80-1211	25
80-1212	38
80-1214	34
80-1215	25
80-1217	25
80-1218	8
80-1220	41
80-1221	41
80-1222	41
80-1223	40
80-1224	40
80-1225	37
80-1226	37
80-1227	81
80-1228	81
80-1229	96
80-1241	97
80-1242	25
80-1244	96
80-1245	83
80-1246	83
80-1247	83
80-1248	83
80-1249	84
80-1250	84
80-1251	84
80-1252	83
80-1253	83
80-1254	83
80-1255	83
80-1256	83
80-1257	83
80-1258	83
80-1263	38
80-1265	29
80-1266	28
80-1267	28
80-1268	27
80-1269	27
80-1270	27
80-1271	27
80-1272	27
80-1274	62
80-1275	62
80-1278	42
80-1282	146
80-1287	25
80-1288	25
80-1289	25
80-1290	25
80-1291	21
80-1292	21
80-1293	97
80-1294	62
80-1300	61
80-1301	61
80-1302	61
80-1303	62
80-1304	62
80-1305	62
80-1307	46
80-1311	63
80-1312	62
80-1313	42
80-1314	43
80-1315	42
80-1316	42
80-1317	40
80-1318	34
80-1319	21
80-1320	23
80-1321	20
80-1326	54
80-1327	60
80-1328	41
80-1330	43
80-1337	33
80-1347	60
80-1348	6
80-1349	16
80-1350	25
80-1351	25
80-1352	25
80-1353	25
80-1355	93
80-1356	93
80-1357	93
80-1358	93
80-1359	92
80-1360	92
80-1361	92

Item No.	Page
80-1362	92
80-1363	92
80-1364	92
80-1365	92
80-1366	92
80-1367	93
80-1368	93
80-1369	93
80-1370	93
80-1371	100
80-1373	8
80-1376	47
80-1377	49
80-1378	46
80-1379	56
80-1380	56
80-1381	96
80-1389	29,30
80-1398	61
80-1408	100
80-1409	93
80-1410	93
80-1411	93
80-1412	93
80-1413	92
80-1414	92
80-1415	92
80-1416	92
80-1419	25
80-1428	16
80-1429	16
80-1430	20
80-1431	20
80-1432	20
80-1433	20
80-1434	22
80-1435	25
80-1436	25
80-1437	25
80-1438	25
80-1439	25
80-1440	25
80-1441	25
80-1442	25
80-1445	43
80-1446	18
80-1447	18
80-1450	22
80-1451	22
80-1453	7
80-1454	162
80-1455	162
80-1456	163
80-1457	163
80-1458	163
80-1462	19
80-1463	19
80-1466	96
80-1467	25
80-1468	25
80-1471	25
80-1472	25
80-1473	63
80-1474	63
80-1475	24
80-1476	24
80-1477	24
80-1481	97
80-1482	97
80-1483	25
80-1485	63
80-1486	63
80-1487	162
80-1490	84
80-1496	82
80-1497	82
80-1498	82
80-1499	82
80-1500	65
80-1501	6
80-1502	9
80-1503	9
80-1504	10
80-1505	10
80-1506	81
80-1518	130,131,132
80-1519	130,131,132
80-1523	26
80-1524	26
80-1525	26
80-1527	6
80-1529	6
80-1530	48
80-1531	38
80-1532	26
80-1533	15
80-1542	15
80-1543	14
80-1544	14
80-1545	14
80-1546	14
80-1547	11
80-1548	11
80-1552	61
80-1555	163
80-1558	12
80-1559	12
80-1560	13
80-1561	13
80-1562	12
80-1563	12
80-1565	12
80-1566	12
80-1582	65
80-1583	65
80-1589	65
80-1590	65
80-1591	65
80-1596	61
80-1598	26
80-1600	85
80-1601	85
80-1602	85
80-1603	85
80-1604	85
80-1605	85
80-1606	85
80-1613	47
80-1614	45
80-1615	60
80-1617	100
80-1619	164
80-1620	164
80-1621	164
80-1622	164
80-1627	164
80-1628	164
80-1629	164
80-1630	164
80-1631	46,48
80-1632	164
80-1633	164
80-1634	164
80-1635	164
80-1636	26
80-1637	28
80-1638	28
80-1639	28
80-1640	29
80-1641	28
80-1642	55
80-1645	55
80-1646	49
80-1647	44
80-1648	52
80-1649	60
80-1650	63
80-1651	62
80-1652	62
80-1653	64
80-1654	64
80-1664	56
80-1665	46,48
80-1666	14
80-1667	14
80-1668	66
80-1669	8
80-1670	8
80-1671	10
80-1672	9
80-1673	9
80-1674	45
80-1677	34,44
80-1678	34,44
80-1679	36
80-1680	36
80-1681	44
80-1682	36
80-1685	39
80-1688	98
80-1689	45
80-1690	51
80-1691	38
80-1692	25
80-1693	63
80-1694	63
80-1695	19
80-1696	19
80-1700	45
80-1701	25
80-1702	25
80-1703	23
80-1704	23
80-1705	24
80-1706	26
80-1707	26
80-1708	39
80-1709	26
80-1710	72
80-1711	72
80-1712	72
80-1713	72
80-1714	73
80-1715	73
80-1716	73
80-1717	73
80-1718	62
80-1719	62
80-1720	73
80-1721	73
80-1733	101
80-1734	45
80-1737	17
80-1738	17
80-1739	17
80-1740	17
80-1741	67
80-1742	67
80-1748	69
80-1749	22
80-1750	22
80-1751	47
80-1753	8
80-1754	6
80-1755	54
80-1757	11
80-1758	11
80-1759	29
80-1762	54
80-1763	26
80-1764	26
80-1766	55
80-1767	95
80-1768	40
80-1769	51
80-1770	95
80-1771	95
80-1772	16
80-1773	76
80-1774	76
80-1775	76
80-1782	62
80-1784	62
80-1785	62
80-1786	62
80-1787	62
80-1788	62
80-1791	48
80-1793	44
80-1794	62
80-1795	23
80-1796	66
80-1797	26
80-1798	55
80-1813	66
80-1816	66
80-1819	100
80-1820	100
80-1844	61
80-1846	74
80-1847	74
80-1848	74
80-1849	74
80-1850	74
80-1851	74
80-1852	74
80-1853	74
80-1854	74
80-1855	74
80-1856	74
80-1857	74
80-1858	75
80-1859	75
80-1860	75
80-1861	75
80-1862	75
80-1863	75
80-1865	51
80-1869	72
80-1870	44
80-1872	67
80-1873	66
80-1875	45
80-1880	134
80-1888	75,103
80-1891	72
80-1893	64
80-1912	63
80-1925	35
80-1926	69
80-1927	28
80-1934	75
80-1935	75
80-1938	140
80-1944	84
80-1947	100
80-1948	64
80-1949	72
80-1950	72
80-1953	75
80-1955	75
80-1956	41
80-1964	112
80-1965	112
80-1966	112
80-1967	112
80-1968	7
80-1969	7
80-1970	103
80-1971	165
80-1972	165
80-1973	165
80-1974	165
80-1975	165
80-1976	165
80-1977	63
80-1979	124
80-1980	100
80-1981	8
80-1983	94
80-1984	23
80-1985	23
80-1987	165
80-1988	165
80-1994	94
80-1996	60
80-1997	68
80-2003	64
80-2004	67
80-2005	75
80-2010	127
80-2011	162
80-2012	64
80-2013	64
80-2015	143
80-2019	66
80-2030	49
80-2031	49
80-2032	36
80-2034	33
80-2035	50
80-2036	54
80-2037	100
80-2041	42
80-2042	42
80-2044	66
80-2047	34
80-2049	66
80-2054	60
80-2061	31
80-2062	31
80-2063	31
80-2064	32
80-2065	32
80-2066	32
80-2067	31
80-2068	31
80-2069	31
80-2070	31
80-2071	31
80-2072	32
80-2073	72
80-2074	72
80-2075	72
80-2076	72
80-2077	72
80-2078	72
80-2080	54
80-2081	165
80-2082	165
80-2083	165
80-2084	165
80-2085	165
80-2086	165
80-2087	165
80-2088	165
80-2089	35
80-2090	48
80-2091	49
80-2092	45
80-2093	47
80-2095	54
80-2096	54
80-2097	61
80-2098	61
80-2099	68
80-2100	69
80-2101	100
80-2102	134
80-2103	134
80-2104	72
80-2105	73
80-2106	81
80-2107	81
80-2108	81
80-2109	81

Item No.	Page
80-2120	35
80-2121	161
80-2128	41
80-2182	42
80-2594	73
80-2602	11
80-2652	41
90-000	139
90-001	144
90-002	144
90-003	145
90-004	145
90-008	168
90-009	168
90-010	168
90-011	168
90-012	168
90-013	168
90-014	145
90-015	144
90-016	145
90-017	144
90-018	144
90-019	144
90-020	24
90-021	24
90-022	153
90-023	153
90-024	153
90-025	153
90-026	153
90-027	153
90-028	153
90-029	153
90-030	153
90-031	153
90-032	153
90-033	144
90-034	144
90-035	153
90-036	153
90-037	153
90-038	153
90-039	181
90-040	174
90-041	174
90-044	175
90-045	175
90-047	173
90-048	173
90-050	173
90-051	173
90-052	171
90-053	171
90-054	171
90-055	171
90-056	171
90-057	174
90-058	171
90-059	153
90-060	153
90-061	173
90-062	171
90-063	171
90-065	171
90-066	171
90-068	171
90-069	175
90-070	138
90-071	138
90-072	138
90-077	138
90-078	139
90-080	139
90-081	139
90-085	139
90-086	139
90-095	156
90-096	156
90-097	156
90-098	156
90-099	137
90-100	115
90-101	115
90-102	115
90-103	115
90-105	115
90-106	118
90-107	118
90-108	173
90-109	142
90-110	142
90-111	143
90-112	142
90-113	142
90-114	143
90-115	143
90-116	166
90-117	166
90-119	175
90-120	183
90-121	176
90-122	166
90-123	166
90-124	166
90-125	166
90-127	166
90-128	166
90-129	166
90-130	134
90-132	134
90-133	133
90-134	133
90-135	133
90-136	131
90-137	131
90-139	131
90-140	132
90-141	132
90-142	132
90-151	175
90-152	148
90-153	148
90-154	148
90-155	148
90-156	148
90-157	128
90-158	128
90-159	152
90-161	128
90-162	155
90-163	156
90-165	143
90-166	133
90-167	152
90-168	152
90-169	152
90-171	144
90-172	145
90-173	166
90-174	156
90-175	143
90-176	146
90-177	146
90-178	143
90-179	142
90-180	128
90-181	24
90-182	24
90-183	24
90-187	144
90-188	168
90-189	168
90-190	168
90-191	172
90-192	171
90-193	171
90-194	172
90-195	172
90-196	171
90-197	171
90-198	171
90-199	172
90-200	149
90-201	149
90-202	149
90-203	149
90-204	149
90-205	149
90-206	149
90-207	154
90-208	152
90-209	152
90-210	152
90-212	149
90-219	131
90-220	131
90-221	131
90-222	131
90-223	131
90-224	131
90-225	131
90-230	176
90-231	176
90-234	178
90-235	178
90-241	155
90-242	173
90-244	178
90-245	152
90-246	185
90-248	68
90-249	149
90-250	68
90-253	149
90-254	149
90-255	140
90-256	140
90-257	140
90-258	140
90-259	140
90-260	140
90-261	140
90-262	140
90-263	149
90-267	148
90-268	148
90-269	148
90-270	140
90-271	140
90-272	140
90-273	148
90-274	140
90-276	148
90-277	148
90-278	148
90-280	140
90-281	140
90-282	140
90-283	140
90-284	140
90-285	140
90-286	140
90-287	140
90-288	140
90-289	140
90-290	140
90-291	140
90-292	140
90-293	140
90-294	140
90-295	140
90-296	140
90-297	140
90-298	140
90-299	140
90-300	167
90-301	140
90-302	140
90-303	179
90-305	167
90-306	167
90-312	167
90-317	167
90-318	167
90-319	167
90-321	128
90-322	128
90-323	128
90-324	128
90-325	128
90-326	128
90-327	128
90-328	128
90-330	176
90-331	176
90-332	155
90-333	146
90-335	150,182
90-336	150,182
90-337	150,182
90-338	150
90-339	150
90-340	149
90-341	149
90-350	146
90-351	146
90-352	162
90-353	146
90-354	146
90-355	146
90-356	146
90-357	146
90-358	146
90-359	146
90-360	146
90-361	146
90-362	146
90-363	146
90-364	146
90-365	148
90-366	162
90-368	163
90-369	163
90-370	162
90-371	163
90-372	162
90-373	163
90-374	162
90-375	163
90-379	146
90-381	146
90-383	146
90-384	148
90-385	148
90-386	148
90-387	148
90-388	146
90-389	146
90-390	144
90-392	144
90-393	98
90-394	98
90-396	127
90-402	60
90-403	60
90-404	33
90-405	33
90-407	54
90-409	34
90-410	6
90-411	9
90-412	7
90-413	7
90-414	56
90-415	56
90-416	56
90-417	34
90-418	6
90-419	35
90-420	8
90-421	6
90-422	60
90-424	33
90-425	69
90-428	50
90-429	46
90-430	176
90-431	176
90-432	56
90-433	99
90-434	99
90-435	99
90-436	99
90-437	105
90-438	105
90-439	186
90-440	159
90-441	159
90-442	159
90-443	52
90-444	52
90-445	52
90-446	104
90-449	69
90-450	159
90-451	159
90-452	159
90-453	159
90-456	159
90-458	28
90-460	115
90-462	115
90-463	58
90-464	59
90-465	56
90-466	42
90-469	127
90-470	127
90-472	146
90-473	146
90-474	67
90-475	66
90-480	53
90-481	53
90-487	168
90-488	168
90-489	168
90-490	115
90-491	115
90-492	115
90-493	115
90-496	115
90-497	115
90-498	115
90-500	99
90-501	92
90-502	95
90-503	166
90-504	92
90-505	94
90-506	99
90-507	92
90-508	93
90-521	166
90-522	166
90-532	69
90-533	166
90-534	166
90-535	153
90-536	153
90-537	153
90-538	153
90-539	153
90-540	55
90-541	55

Item No.	Page
90-542	55
90-543	55
90-545	100
90-546	105
90-547	105
90-548	62
90-551	152
90-552	130
90-553	130
90-554	130
90-555	130
90-556	130
90-557	130
90-558	131
90-559	131
90-560	131
90-561	131
90-562	131
90-563	131
90-570	131
90-571	131
90-573	99
90-574	99
90-575	142
90-577	186
90-578	186
90-589	143
90-590	92
90-591	144
90-592	144
90-593	143
90-594	144
90-595	55
90-598	143
90-599	149
90-606	140
90-607	140
90-608	140
90-609	140
90-610	140
90-611	140
90-612	143
90-613	143
90-614	155
90-615	179
90-616	179
90-623	155
90-625	154
90-626	154
90-631	98
90-632	98
90-634	155
90-635	153
90-636	154
90-637	154
90-638	154
90-639	154
90-640	152
90-642	154
90-643	154
90-644	154
90-645	154
90-646	154
90-649	179
90-650	179
90-651	152
90-652	152
90-653	152
90-654	186
90-655	186
90-656	186
90-657	186
90-658	186
90-659	186
90-660	186
90-666	152
90-667	154
90-668	154
90-670	138
90-677	186
90-678	186
90-679	186
90-684	177
90-685	177
90-686	177
90-689	94
90-690	94
90-691	167
90-692	167
90-693	167
90-695	98
90-696	98
90-697	98
90-701	132
90-702	154
90-703	95
90-704	94
90-705	186
90-706	179
90-707	179
90-708	183
90-709	183
90-710	152
90-711	152
90-714	149
90-715	98
90-716	98
90-719	98
90-720	149
90-721	149
90-722	153
90-723	118
90-724	176
90-725	168
90-738	61
90-739	61
90-744	153
90-747	167
90-748	167
90-749	176
90-753	167
90-755	177
90-756	177
90-757	177
90-758	177
90-759	42
90-760	42
90-761	154
90-762	133,134,154
90-763	177
90-764	154
90-765	154
90-766	177
90-767	177
90-768	185
90-769	185
90-770	159
90-775	183
90-776	183
90-777	167
90-778	167
90-779	167
90-780	167
90-781	167
90-782	167
90-783	167
90-784	167
90-793	98
90-794	98
90-797	153
90-798	97
90-799	97
90-806	106
90-814	99
90-815	159
90-816	159
90-817	159
90-820	99
90-821	99
90-822	152
90-825	99
90-837	134
90-838	134
90-840	176
90-841	176
90-842	134
90-846	159
90-867	17
90-868	16
90-869	17
90-870	16
90-871	18
90-876	177
90-877	177
90-878	186
90-879	186
90-880	186
90-886	134
90-890	172
90-891	172
90-892	172
90-893	172
90-894	172
90-901	162
90-902	162
90-903	162
90-904	162
90-905	162
90-906	162
90-907	162
90-908	162
90-909	162
90-910	162
90-911	163
90-912	163
90-913	163
90-914	163
90-915	163
90-916	163
90-917	163
90-918	163
90-919	130
90-920	130
90-921	130
90-922	130
90-923	130
90-924	130
90-925	130
90-931	162
90-934	167
90-935	168
90-940	132
90-955	152
90-957	149
90-958	149
90-959	133
90-963	154
90-967	115
90-968	118
90-985	148
90-986	148
90-987	148
90-988	148
90-989	148
90-990	148
90-991	148
90-992	148
90-993	148
90-995	148
90-996	148
90-998	128
90-0580	175
90-1000	140
90-1002	140
90-1003	140
90-1004	140
90-1005	140
90-1008	140
90-1009	140
90-1012	140
90-1014	140
90-1015	140
90-1016	140
90-1017	140
90-1018	140
90-1020	148
90-1021	140
90-1022	140
90-1023	140
90-1025	140
90-1026	140
90-1027	140
90-1028	140
90-1029	140
90-1030	140
90-1031	140
90-1032	153
90-1034	166
90-1035	144
90-1036	144
90-1037	144
90-1038	144
90-1042	145
90-1050	133
90-1051	133
90-1056	133
90-1059	155
90-1060	140
90-1062	140
90-1063	140
90-1065	142
90-1066	144
90-1068	140
90-1069	96
90-1070	96
90-1072	174
90-1073	142
90-1074	35
90-1076	69
90-1077	67
90-1078	67
90-1080	66
90-1081	66
90-1082	97
90-1083	98
90-1084	98
90-1085	183
90-1088	147
90-1089	147
90-1090	147
90-1091	147
90-1092	147
90-1093	147
90-1094	147
90-1095	146
90-1096	146
90-1097	69
90-1098	172
90-1099	172
90-1100	172
90-1101	172
90-1102	172
90-1103	162
90-1104	163
90-1106	95
90-1107	38
90-1108	35
90-1109	37
90-1110	37
90-1111	69
90-1112	69
90-1113	69
90-1114	98
90-1115	98
90-1116	98
90-1117	106
90-1118	106
90-1119	106
90-1120	106
90-1121	104
90-1125	142
90-1126	142
90-1127	143
90-1128	143
90-1129	143
90-1130	143
90-1138	24
90-1139	24
90-1140	24
90-1141	24
90-1142	24
90-1143	24
90-1144	25
90-1145	25
90-1146	25
90-1147	25
90-1148	162
90-1149	148
90-1150	42
90-1151	54
90-1152	33
90-1153	33
90-1154	153
90-1155	153
90-1156	153
90-1158	128
90-1159	128
90-1160	133
90-1161	133
90-1162	140
90-1163	140
90-1164	150
90-1166	148
90-1167	148
90-1168	148
90-1169	148
90-1170	148
90-1173	140
90-1174	148
90-1175	148
90-1176	148
90-1177	148
90-1178	148
90-1179	148
90-1180	148
90-1181	148
90-1182	141
90-1183	141
90-1184	141
90-1185	141
90-1186	141
90-1187	141
90-1188	141
90-1189	141
90-1190	141
90-1191	141
90-1192	141
90-1193	141
90-1194	141
90-1195	141
90-1196	141
90-1197	141
90-1198	140
90-1199	140
90-1217	143
90-1218	148
90-1246	163
90-1247	163
90-1248	163
90-1249	163
90-1250	163
90-1251	163
90-1252	200
90-1253	200
90-1254	200
90-1255	200

Item No.	Page
90-1256	162
90-1257	162
90-1258	162
90-1259	162
90-1260	162
90-1261	162
90-1262	162
90-1263	162
90-1264	162
90-1270	199
90-1271	199
90-1272	199
90-1273	199
90-1274	200
90-1275	200
90-1276	200
90-1277	200
90-1281	140
90-1298	148
90-1299	184
90-1306	184
90-1307	184
90-1308	154
90-1310	52,124
90-1311	67,127
90-1312	67,127
90-1313	67,127
90-1314	8
90-1335	200
90-1336	200
90-1337	200
90-1338	200
90-1385	145
90-1386	134
90-1404	106
90-1405	106
90-1407	183
90-1408	6
90-1409	9
90-1410	7
90-1411	7
90-1412	8
90-1413	115
90-1414	115
90-1415	115
90-1416	115
90-1417	115
90-1418	127
90-1419	127
90-1420	127,168
90-1421	127
90-1422	128
90-1423	128
90-1424	144
90-1425	118
90-1429	148
90-1433	177
90-1435	176
90-1437	176
90-1439	177
90-1440	127
90-1448	177
90-1502	53
90-1503	53
90-1504	179
90-1505	162
90-1506	162
90-1507	162
90-1508	162
90-1509	162
90-1510	162
90-1511	162
90-1512	162
90-1513	163
90-1514	163
90-1515	163
90-1516	163
90-1517	163
90-1518	173
90-1519	104
90-1520	98
90-1521	98
90-1522	98
90-1523	114
90-1524	114
90-1525	114
90-1526	114
90-1527	114
90-1528	114
90-1529	114
90-1530	114
90-1531	114
90-1532	114
90-1534	114
90-1535	114
90-1536	114
90-1537	114
90-1538	114
90-1540	80
90-1541	80
90-1542	80
90-1543	80
90-1544	80
90-1545	80
90-1547	80
90-1548	80
90-1549	81
90-1550	81
90-1551	81
90-1552	66
90-1553	66
90-1554	64
90-1555	64
90-1556	63
90-1557	63
90-1558	68
90-1559	68
90-1560	68
90-1561	67
90-1562	132
90-1563	42
90-1564	42
90-1565	143
90-1566	115,116,117,118
90-1567	132
90-1571	151
90-1572	151
90-1577	145
90-1578	144
90-1579	144
90-1580	144
90-1581	118
90-1582	118
90-1583	118
90-1584	118
90-1585	118
90-1587	58
90-1588	59
90-1589	132
90-1590	66
90-1594	147
90-1595	147
90-1596	147
90-1597	147
90-1598	147
90-1599	147
90-1600	155
90-1601	145
90-1602	147
90-1603	147
90-1604	147
90-1605	147
90-1606	147
90-1607	147
90-1608	147
90-1609	147
90-1610	147
90-1611	147
90-1612	147
90-1613	147
90-1614	147
90-1615	147
90-1616	147
90-1617	147
90-1618	147
90-1619	147
90-1620	147
90-1621	145
90-1622	155
90-1623	145
90-1624	155
90-1625	155
90-1626	155
90-1627	155
90-1628	155
90-1629	155
90-1630	155
90-1631	155
90-1632	155
90-1633	155
90-1634	145
90-1636	144
90-1640	146
90-1641	146
90-1644	146
90-1646	144
90-1648	144
90-1649	144
90-1650	143
90-1652	148
90-1653	148
90-1654	146
90-1655	146
90-1656	146
90-1657	24
90-1658	24
90-1660	148
90-1661	146
90-1667	16
90-1668	17
90-1669	17
90-1670	16
90-1671	18
90-1672	16
90-1673	16
90-1674	170
90-1675	170
90-1676	93
90-1677	170
90-1678	93
90-1679	93
90-1680	170
90-1681	170
90-1682	170
90-1683	170
90-1684	170
90-1685	170
90-1686	170
90-1687	170
90-1688	170
90-1689	170
90-1690	170
90-1691	170
90-1692	170
90-1693	170
90-1694	170
90-1695	170
90-1696	170
90-1697	174
90-1698	144
90-1699	145
90-1700	145
90-1701	145
90-1702	144
90-1703	144
90-1704	144
90-1705	143
90-1706	34
90-1707	34
90-1708	37
90-1709	61,62
90-1710	146
90-1711	133
90-1712	133
90-1713	133
90-1714	133
90-1715	133
90-1716	133
90-1717	133
90-1718	133
90-1719	133
90-1720	133
90-1721	133
90-1722	133
90-1723	133
90-1724	133
90-1725	133
90-1726	149
90-1727	149
90-1728	149
90-1729	149
90-1730	149
90-1731	134
90-1732	134
90-1733	134
90-1734	135
90-1735	134
90-1736	136
90-1737	136
90-1738	136
90-1739	136
90-1740	136
90-1741	136
90-1742	136
90-1743	135
90-1744	135
90-1745	135
90-1746	135
90-1747	135
90-1748	136
90-1763	146
90-1765	146
90-1766	146
90-1772	146
90-1773	153
90-1774	153
90-1775	149
90-1776	149
90-1777	25
90-1778	153
90-1779	167
90-1780	167
90-1781	167
90-1782	54
90-1784	143
90-1785	143
90-1788	146
90-1789	146
90-1790	146
90-1801	104
90-1804	144
90-1809	152
90-1814	127,168
90-1822	168
90-1824	128
90-1825	128
90-1830	148
90-1831	148
90-1832	146
90-1833	146
90-1834	146
90-1835	146
90-1836	152
90-1837	152
90-1838	146
90-1839	146
90-1842	152
90-1843	152
90-1844	170
90-1845	170
90-1846	171
90-1847	171
90-1848	150
90-2000	130
90-2001	130
90-2002	130
90-2003	130
90-2004	130
90-2005	130
90-2006	130
90-2007	130
90-2008	130
90-2009	130
90-2010	130
90-2011	130
90-2012	130
90-2013	131
90-2014	131
90-2015	131
90-2016	131
90-2017	131
90-2018	131
90-2019	131
90-2020	131
90-2021	131
90-2022	131
90-2023	131
90-2024	131
90-2025	131
90-2026	131
90-2027	131
90-2028	131
90-2029	131
90-2030	131
90-2031	130
90-2032	130
90-2033	114
90-2034	114
90-2035	114
90-2036	114
90-2037	114
90-2038	115
90-2039	115
90-2040	98
90-2041	98
90-2042	115
90-2043	117
90-2044	117
90-2045	117
90-2046	117
90-2047	117
90-2048	117
90-2049	146
90-2050	146
90-2051	146
90-2052	146
90-2053	146
90-2054	146
90-2055	146
90-2056	146
90-2057	146
90-2058	146
90-2059	146
90-2060	146
90-2061	146
90-2062	146
90-2063	146
90-2064	146
90-2066	146
90-2067	146
90-2068	146
90-2069	146
90-2070	146
90-2072	146
90-2073	146
90-2074	146

Item No.	Page
90-2075	146
90-2076	146
90-2077	146
90-2078	130
90-2079	130
90-2080	130
90-2081	131
90-2082	131
90-2083	131
90-2085	119
90-2086	119
90-2087	117
90-2088	130
90-2089	130
90-2090	146
90-2091	146
90-2093	131
90-2094	131
90-2095	155
90-2096	155
90-2097	155
90-2098	155
90-2099	155
90-2100	155
90-2101	115
90-2102	140
90-2103	140
90-2104	140
90-2105	140
90-2106	140
90-2107	140
90-2108	140
90-2109	140
90-2110	140
90-2111	140
90-2112	140
90-2113	140
90-2114	140
90-2115	140
90-2116	140
90-2117	140
90-2118	140
90-2119	140
90-2120	140
90-2121	140
90-2122	140
90-2123	140
90-2124	140
90-2125	140
90-2126	140
90-2127	140
90-2128	140
90-2129	140
90-2130	140
90-2131	140
90-2132	140
90-2133	141
90-2134	141
90-2135	141
90-2136	141
90-2137	141
90-2138	141
90-2139	147
90-2140	147
90-2141	147
90-2142	147
90-2146	147
90-2147	147
90-2148	147
90-2149	147
90-2150	147
90-2151	147
90-2152	147
90-2153	155
90-2154	155
90-2155	155
90-2156	155
90-2157	155
90-2158	141
90-2163	156
90-2164	156
90-2165	156
90-2166	156
90-2167	156
90-2168	156
90-2169	156
90-2170	156
90-2171	156
90-2172	158
90-2173	158
90-2174	158
90-2175	158
90-2176	158
90-2177	158
90-2178	158
90-2179	158
90-2180	158
90-2182	146
90-2183	115
90-2184	115
90-2185	115
90-2186	117
90-2188	161
90-2189	161
90-2190	161
90-2191	161
90-2192	161
90-2193	161
90-2194	161
90-2195	161
90-2196	161
90-2197	161
90-2199	161
90-2200	161
90-2201	161
90-2202	161
90-2203	130
90-2204	130
90-2205	130
90-2206	130
90-2208	119
90-2209	119
90-2210	119
90-2211	141
90-2212	161
90-2213	161
90-2214	161
90-2215	161
90-2216	161
90-2217	161
90-2218	161
90-2219	161
90-2220	160
90-2221	160
90-2222	160
90-2223	160
90-2224	160
90-2225	160
90-2226	160
90-2227	160
90-2228	160
90-2229	161
90-2230	161
90-2231	161
90-2232	161
90-2233	140
90-2234	141
90-2235	130
90-2236	130
90-2237	127
90-2238	127
90-2239	127
90-2240	127
90-2241	127
90-2242	131
90-2243	119
90-2244	98
90-2245	98
90-2246	132
90-2247	132
90-2248	132
90-2249	132
90-2250	132
90-2251	132
90-2252	132
90-2253	132
90-2254	132
90-2255	132
90-2256	130
90-2257	130
90-2258	130
90-2259	130
90-2260	94
90-2261	94
90-2264	130
90-2265	130
90-2266	130
90-2267	130
90-2268	130
90-2269	130
90-2270	130
90-2271	161
90-2272	161
90-2273	161
90-2274	161
90-2275	161
90-2276	161
90-2277	160
90-2278	160
90-2279	160
90-2280	160
90-2281	160
90-2282	160
90-2283	160
90-2284	160
90-2285	160
90-2286	160
90-2287	160
90-2288	160
90-2289	131
90-2291	130
90-2292	130
90-2293	131
90-2294	151
90-2295	151
90-2296	151
90-2297	151
90-2298	151
90-2299	151
90-2300	151
90-2301	151
90-2302	151
90-2303	151
90-2309	118
90-2310	118
90-2312	119
90-2313	119
90-2315	97
90-2318	147
90-2319	147
90-2320	116
90-2321	116
90-2322	116
90-2323	116
90-2324	116
90-2325	119
90-2329	157
90-2330	157
90-2331	157
90-2332	157
90-2333	157
90-2334	157
90-2335	157
90-2336	157
90-2337	157
90-2338	131
90-2339	131
90-2340	130
90-2341	130
90-2342	150
90-2343	150
90-2344	150
90-2351	150
90-2352	150
90-2353	132
90-2354	132
90-2357	198
90-2358	198
90-2359	198
90-2360	198
90-2361	198
90-2362	198
90-2363	198
90-2364	198
90-2365	198
90-2366	199
90-2367	199
90-2368	99
90-2369	99
90-2370	99
90-2371	99
90-2372	99
90-2373	158
90-2374	131
90-2375	131
90-2376	131
90-2377	131
90-2378	131
90-2379	131
90-2382	180
90-2383	180
90-2384	180
90-2385	141
90-2390	116
90-2392	114
90-2393	162
90-2404	186
90-2405	186
90-2407	141
90-2413	119
90-2414	119
90-2416	114
90-2417	114
90-2418	114
90-2421	150
90-2422	150
90-2424	99
90-2425	99
90-2426	99
90-2427	99
90-2428	102
90-2429	102
90-2430	101
90-2431	101
90-2432	101
90-2433	103
90-2434	73,75,103
90-2435	116
90-2436	116
90-2437	116
90-2438	147
90-2439	147
90-2440	147
90-2441	147
90-2443	162
90-2444	162
90-2445	162
90-2446	163
90-2447	163
90-2448	163
90-2449	104
90-2450	104
90-2451	104
90-2452	69
90-2453	131
90-2454	131
90-2455	131
90-2456	130,132
90-2457	130,132
90-2458	132
90-2459	116
90-2460	114
90-2461	114
90-2462	114
90-2463	114
90-2464	114
90-2465	104
90-2467	77,79
90-2468	77
90-2469	78
90-2470	78
90-2471	141
90-2472	141
90-2473	141
90-2474	141
90-2475	141
90-2476	141
90-2477	142
90-2478	143
90-2480	181
90-2481	181
90-2482	180
90-2483	77
90-2484	78
90-2485	199
90-2486	199
90-2487	199
90-2488	199
90-2489	182
90-2490	182
90-2491	182
90-2492	182
90-2493	182
90-2494	150,182
90-2495	150,182
90-2498	81
90-2499	79
90-2501	148
90-2502	148
90-2503	148
90-2504	148
90-2505	148
90-2506	148
90-2507	148
90-2508	148
90-2509	148
90-2510	148
90-2511	148
90-2512	148
90-2513	79
90-2514	149
90-2515	149
90-2518	141
90-2519	141
90-2520	130
90-2521	130
90-2522	131
90-2523	131
90-2524	199
90-2525	199
90-2526	199
90-2527	199
90-2528	166
90-2529	132
90-2531	162
90-2533	130,132
90-2534	130,132
90-2535	132
90-2536	127
90-2544	153
90-2545	140
90-2546	140
90-2576	162
90-2579	77
90-2580	78
90-2581	77

Item No.	Page
90-2582	78
90-2587	99
90-2589	104
90-2593	157
90-2594	140
90-2595	150
90-2596	117
90-2597	132
90-2598	114
90-2599	115
90-2604	103
90-2605	98
90-2606	98
90-2607	98
90-2608	98
90-2609	98
90-2610	103
90-2611	101
90-2612	52,124
90-2617	98
90-2618	98
90-2619	25
90-2620	162
90-2621	39
90-2622	141
90-2623	141
90-2625	140
90-2626	140
90-2627	140
90-2628	114
90-2629	99
90-2630	106
90-2633	101
90-2634	148
90-2635	148
90-2638	52
90-2639	52
90-4300	54
90-4310	9
90-5003	141
90-5004	141
90-5005	141
90-5006	141
90-5007	141
90-5008	141
90-5010	141
90-5012	141
90-5014	141
90-5016	141
90-5020	141
90-5024	141
90-5026	141
90-5028	141
90-5030	141
90-5032	141
90-5036	141
90-5040	141
90-5044	141
90-5048	141
90-5052	141
90-5056	141
90-5060	141
90-5064	141
90-5068	141
90-5072	141
90-5076	141
90-5080	141
90-5084	141
90-5088	141
90-5092	141
90-5096	141
90-5100	141
90-5104	141
90-5108	141
90-5112	141
90-5116	141
90-5120	141
90-5124	141
90-5128	141
90-5132	141
90-5136	141
90-5140	141
90-5144	141
90-5148	141
90-5152	141
90-5156	141
90-5160	141
90-5168	141
90-5176	141
90-5180	141
90-5184	141
90-5192	141
90-5199	141
90-5200	141
90-5201	141
90-5203	141
90-5310	143
91-220	125
91-221	125
91-222	125
91-223	125
91-227	106
91-229	125
92-321	105
92-322	105
92-323	104
92-324	104
92-400	105
92-401	105
92-403	105
92-405	104
92-406	105
92-407	104
92-408	104
92-414	104
93-110	111
93-115	111
93-126	108
93-127	108
93-128	108
93-129	108
93-130	108
93-131	108
93-132	108
93-133	111
93-134	111
93-138	108
93-139	108
93-140	108
93-141	108
93-142	108
93-144	109
93-150	109
93-165	108
93-166	108
93-167	108
93-168	108
93-169	120
93-170	120
93-173	120
93-174	120
93-175	120
93-179	120
93-182	109
93-183	109
93-184	111
93-185	111
93-186	111
93-187	111
93-188	111
93-189	111
93-192	121
93-193	121
93-194	121
93-195	121
93-196	121
93-197	121
93-198	121
93-199	121
93-203	110
93-204	110
93-205	110
93-206	110
93-207	111
93-208	111
93-209	111
93-210	111
93-211	111
93-212	111
93-241	108
93-300	113
93-301	113
93-302	113
93-303	113
93-304	113
93-305	113
93-306	113
93-307	113
93-308	113
93-309	113
93-310	113
93-311	109
93-312	109
93-313	109
93-314	109
93-315	110
93-316	110
93-317	110
93-318	110
93-319	110
93-320	110
93-321	110
93-322	112
93-325	112
93-326	112
93-329	110
93-330	110
93-332	109
93-333	109
93-334	112
93-335	112
93-336	108
93-337	108
93-338	108
93-339	113
93-340	109
93-341	110
93-343	108
93-5000	122
93-5001	122
93-5002	122
93-5003	122
93-5004	122
93-5005	122
93-5006	122
93-5007	122
93-5008	122
93-5009	122
93-5010	122
93-5011	96
93-5012	96
93-5014	96
93-5016	96
93-5017	122
93-5018	122
93-5019	122
93-5020	121
93-5021	121
93-5022	121
93-5023	121
93-5024	123
93-5025	123
93-5026	123
93-5027	123
93-5028	124
93-5029	124
93-5030	123
93-5031	124
93-5032	124
93-5033	124
93-5034	122
93-5035	122
93-5036	124
93-5037	124
93-5038	124
93-5039	124
S1822	50
S1934	51
S1940	51
S3127	51
S4614	65
S4870	50
S4894	68
S4895	68
S5170	86
S5171	86
S5207	88
S5208	88
S5209	88
S5210	88
S5213	89
S5214	88
S5215	88
S5218	88
S5219	88
S5220	88
S5221	88
S5222	88
S5223	90
S5225	90
S5226	90
S5228	90
S5229	90
S5233	90
S5235	90
S5258	89
S5259	89
S5260	89
S5261	89
S5262	89
S5263	89
S5264	87
S5265	87
S5266	87
S5267	87
S5268	86
S5269	86
S5270	86
S5271	86
S5274	86
S5275	86
S5276	86
S5277	86
S5278	86
S5279	86
S5280	86
S5281	86
S5282	87
S5283	87
S5284	87
S5285	87
S5286	89
S5287	89
S5288	89
S5289	89
S5290	87
S5291	87
S5292	87
S5293	87
S5294	87
S5295	87
S5296	90
S5297	90
S5298	90
S5299	90
S5831	50
S5862	50
S6620	86
S6621	86
S6622	86
S70-826	126
S70-827	126
S70-829	126
S70-830	126
S70-831	126
S70-832	126
S8201	73,75,78
S8202	73,75,78
S8203	73,75,78
S8204	73,75,78
S8205	73,75,78
S8206	73,75,78
S8207	73,75,78
S8227	73,75,78
S8228	73,75,78
S8329	70
S8330	70
S8331	70
S8332	70
S8333	70
S8334	70
S8335	70
S8336	70
S8337	70
S8338	70
S8339	70
S8340	70
S8341	71
S8342	71
S8343	71
S8344	71
S8345	71
S8346	71
S8347	71
S8348	71
S8349	71
S8350	71
S8351	71
S8352	71
S8353	71
S8354	71
S8355	71
S8356	71
S8396	71
S8397	71
S8398	71
TP185	159
Y49428	90
Y49429	90
Y49430	90
Y49735	88
Y49736	88

SATCO®

National Toll-Free

800-43-SATCO (800-437-2826)

NEW YORK

Executive Offices & Warehouse
110 Heartland Blvd.,
Brentwood, N.Y. 11717
800-437-2826
(631) 243-2022
FAX (631) 243-2027

CALIFORNIA

31288 San Benito St.,
Hayward,CA 94544
800-437-2826
(510) 487-4822
FAX (510) 487-8955

PUERTO RICO

Compeche St. 23
Julio N. Matos Industrial Park
Carolina, PR 00984
(787) 757-3510
FAX (787) 757-3540

FLORIDA

900 N.W. 159th Drive,
Miami,FL 33169
800-437-2826
(305) 624-2044
FAX (305) 623-0286

WASHINGTON

4710 116th St. S.W.,
Mukilteo, WA 98275
800-437-2826
(425) 789-3300
FAX (425) 789-3310

TEXAS

2000 Valwood Parkway,
Farmers Branch, TX 75234
800-437-2826
(972) 247-2437
FAX (972) 247-5408

Visit Our Web Site at: www.satco.com
E-Mail us at: info@satco.com

Not responsible for typographical errors.
Data subject to change without notice.

© 2010 SATCO Products Inc.
All Rights Reserved

Printed in China

CAT. # SA3015

$10.00