NEBO®

ILLUMINATE YOUR WORLD®



PRODUCT CATALOG

1-2 NEBO PRODUCT DISPLAYS

3-59 NEBO LIGHTING

60-62 WEATHERRITE OUTDOOR

63-64 TRUE UTILITY POCKET TOOLS

65 iPROTEC FIREARM ACCESSORIES

66 QUARROW FISHING PRODUCTS

67 CUSTOM PRINTING & ENGRAVING

68 NEBO GEAR

table of contents

SLIM+ 5-6

REDLINE X 3-4

At NEBO, our lights are designed for everyone, everywhere. From the simplest task at home to the most daring adventure outdoors, we have a light for you. We create and see our products through every phase of development. From conceptual drawings on the sketch pad all the way to the end consumer, we deliver on the promise of innovative lighting solutions.

Illuminate your world with NEBO.

NEBO®

www.nebotools.com

Customer Care: 800.255.6061

Larry TRIO 7-8

CSI Flashlight 9-10

NEBO® technology

In a world of rapidly changing technology, keeping up with the latest trends is hard, but doing so only takes you as far as someone else has already gone. At NEBO, we like to explore uncharted territories. That's the trailblazer mind-set. What makes NEBO better? What makes NEBO different? The answers can be found in our technology, where instead of just asking why, we ask "why not?"

C·O·B features smaller, easier clustered LED chips that work together as one lighting module. With this design, C·O·B outperforms traditional lighting with more output, less energy consumption and longer LED life span.

ARCUS is a new proprietary C·O·B LED technology that allows the shaping of light into full 3D patterns, giving optimal, bright, uniform light exactly where it's needed.

Flex-Power gives the ability to use different quantities of the same battery, or two different battery types, such as rechargeable and standard alkaline.

OC Technology™ creates a perfectly dispersed beam of intense, pristine light that is as bright on the edge as it is in the center when used in flood mode.

Show More. Sell More. With NEBO Store Displays.

#6654

Large Aisle
Free-Standing Display

DESIGN
- All metal construction
- Double-sided display
- Locking casters
- 16 sku capacity
- 12 adjustable shelves
- 2 footer shelves
- 2 metal clip strips
- Peg hook capable (hooks not included)

ASSEMBLY
- Easy 10 minute assembly
- Instructions, tools and plan-o-gram provided

SPECS
- 100 lbs.
- (H) 76" x (W) 26" x (D) 24"



Adjustable height

Contact your NEBO Sales Manager to find out how to get your Free-Standing Display for FREE!!!

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397932253	6654	Large Aisle Free-Standing Display

#6880

POG Inline
Free-Standing Display

Ideal for peggable NEBO items in a plan-o-gram.

DESIGN
- All metal construction
- 20 sku capacity
- 1 footer shelf
- Peg hook capable (20 hooks included)
- Storage drawer

ASSEMBLY
- Easy 10 minute assembly
- Instructions, tools and plan-o-gram provided

SPECS
- 100 lbs.
- (H) 78.5" x (W) 28" x (D) 17.35"

#6879

Slim Line
Free-Standing Display

Ideal where space is limited as a one or two-sided display.

DESIGN
- All metal construction
- Adjustable size (55" or 36" height)
- One or two-sided display
- 12 sku capacity
- 3 adjustable shelves / 1 footer shelf
- Two metal clip strips
- Peg hook capable (12 hooks included)

ASSEMBLY
- Easy 10 minute assembly
- Instructions, tools and plan-o-gram provided

SPECS
- 50 lbs.
- (H) 55" or 36" x (W) 14.5" x (D) 20"

Use as a one-sided display with shelves.

Or use as a two-sided display with hooks on back side.

UPC CODE	ITEM	DESCRIPTION
645397935391	6880	POG Inline Free-Standing Display
645397935384	6879	Slim line Free-Standing Display

NEBO®

REDLINE® X™

The REDLINE X is a powerful ***waterproof*** (IPX7), ***rechargeable, 1800 lumen flashlight*** that features 4x zoom and **SwitchX Technology**, which uses a patented paddle switching mechanism to operate the power, mode selection and instant activation for TURBO and Variable Strobe Modes.

LIGHT OUTPUT
- *High (720 lumens): 2 hours / 155 meters*
- *Low (180 lumens): 4 hours / 85 meters*
- *Variable Strobe (1800 lumens): 1 hour / 253 meters*
- *TURBO (1800 lumens): 45 seconds / 253 meters*

FEATURES
- Fully rechargeable
- Momentary Power Memory Recall
- Anodized aircraft-grade aluminum; waterproof (IPX7) and impact-resistant
- Battery charging indicator
- SwitchX Technology

OPERATION
- Two rear-positioned buttons for power and mode selection

ACCESSORIES
- Micro USB to USB charging cable included

BATTERIES
- Powered by rechargeable battery (included) (Recharge time: 5 - 6 hours)

SPECS
- 0.37 lbs.
- Length: Compacted: 5.875" / Extended: 6.25"
- Diameter: 1.25"

WATERPROOF (IPX7)

Actual Size

X - THE CROSSROADS OF POWER AND SIMPLICITY

SWITCH-X™ TECHNOLOGY

SwitchX Technology uses a patented paddle switching mechanism to operate the power, mode selection and instant activation for TURBO and Variable Strobe Modes.

USB RECHARGEABLE

- *Display showcases 1 piece in front.*
- *Each X comes with a gift box.*

Display Dimensions
(H) 10.2" x (W) 6.1" x (D) 9.75"

Gift Box Dimensions
(H) 6.1" x (W) 1.5" x (D) 1.34"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397935063	6860	REDLINE X

NEBO®

SLIM+

The SLIM+ is a thin, ergonomic ***rechargeable 700 lumen pocket light*** with a ***red laser pointer*** and a ***Power Bank*** for your USB powered devices. Equipped with full dimming and Power Memory Recall, the SLIM+ also features a detachable magnetic pocket clip, collapsible hanging hook and powerful magnetic base for convenient hands-free lighting.

LIGHT OUTPUT
- *100% (700 lumens): 1.5 hours / 60 meters*
- *10% (70 lumens): 6 hours / 19 meters*
- *Red Laser (<5mW / 650nm): 20 hours*

FEATURES
- Fully rechargeable
- Power bank
- Full dimming
- Power Memory Recall
- Detachable magnetic clip w/ hanging hook
- Anodized aircraft-grade aluminum; water and impact-resistant
- Thin, ergonomic design
- Battery indicator
- Powerful magnetic base

OPERATION
- Side-positioned, ON/OFF button; hold for laser

ACCESSORIES
- Micro USB to USB charging cable included

BATTERIES
- Powered by rechargeable battery (included) (Recharge time: 5 - 6 hours)

SPECS
- 0.25 lbs.
- (H) 4.5" x (W) 1.75" x (D) 1.875"

USB RECHARGEABLE

POWER BANK

RED LASER POINTER

LIGHT. LASER. POWER.

+ SO MUCH MORE

DETACHABLE CLIP

- *Display showcases 1 piece in front.*
- *Each SLIM+ comes with a gift box.*

Display Dimensions
(H) 10.75" x (W) 6.375" x (D) 8"

Gift Box Dimensions
(H) 4.6" x (W) 1.9" x (D) 1.46"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397935056	6859	SLIM+

NEBO®

Larry™ TRIO™

The Larry TRIO is a powerful 3-in-1 ***rechargeable*** light featuring a ***200 lumen spot light***, ***300 lumen C·O·B work light*** and a ***red laser pointer***. The TRIO uses 2 buttons to independently control the light and laser, and is also equipped with a magnetic base for convenient hands-free operation.

LIGHT OUTPUT
- *Spot light (200 lumens): 2.5 hours / 80 meters*
- *Work light (300 lumens): 2 hours / 25 meters*
- *Red Laser (<5mW / 650nm): 8 hours*

FEATURES
- Fully rechargeable
- Full dimming
- Power Memory Recall
- Belt/pocket clip
- Anodized aircraft-grade aluminum; water and impact-resistant
- Battery charging indicator
- Powerful magnetic base

OPERATION
- Two side-positioned, ON/OFF buttons; for independent control of light and laser

ACCESSORIES
- Micro USB to USB charging cable included

BATTERIES
- Powered by rechargeable battery (included) (Recharge time: 5 - 6 hours)

SPECS
- 0.125 lbs.
- (H) 6.87" x (W) 0.7" x (D) 0.75"

Actual Size

AVAILABLE COLORS

Storm Blue Black

THE RECHARGEABLE 3-IN-1 LIGHT

READY FOR ANY TASK

- *Display holds 2 pieces - additional pieces included as replenishments.*
- *Each TRIO comes with a gift box.*

Display Dimensions
(H) 9.8" x (W) 7" x (D) 8"

Color Assortment:
8 black, 4 storm blue

Gift Box Dimensions
(H) 6.8" x (W) 0.9" x (D) 0.7"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397935148	6868	Larry TRIO

NEBO®

CSI FLASHLIGHT

The CSI Flashlight, the NEBO light that started it all, is back and better than ever. The newly redesigned CSI features ***250 lumens***, ***a red laser*** and a ***powerful magnetic base*** for convenient hands-free operation.

LIGHT OUTPUT
- *High (250 lumens): 3 hours / 135 meters*
- *Low (75 lumens): 10 hours / 78 meters*
- *Strobe (250 lumens): 4 hours / 135 meters*
- *Red Laser (<5mW / 650nm): 40 hours*

FEATURES
- Anodized aircraft-grade aluminum; water and impact-resistant
- Powerful magnetic base

OPERATION
- Rear-positioned, ON/OFF button

BATTERIES
- Powered by 3 AAA batteries (included)

SPECS
- 0.293 lbs.
- (H) 4.8" x (W) 1.2"

Actual Size

AVAILABLE COLORS

Gunmetal Gray | Black



MAGNETIC BASE

RED LASER POINTER

SLEEK. SIMPLE. REFINED.

NEBO NEW

THE CSI IS BACK AND BETTER THAN EVER

- *Display holds 2 pieces in front.*
- *Each CSI comes with a gift box.*

Display Dimensions
(H) 10.1" x (W) 6.1" x (D) 8"

Color Assortment:
16 black, 8 gunmetal gray

Gift Box Dimensions
(H) 4.8" x (W) 1.22" x (D) 1.22"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397935247	6873	CSI Flashlight

NEBO®

INSPECTOR™ RC

FLEX-POWER™
RECHARGEABLE
WATERPROOF

The NEBO INSPECTOR RC is a powerful 360 lumen ***rechargeable, waterproof*** (IP67) penlight. The INSPECTOR RC features ***FLEX-POWER*** and is equipped with a removable steel clip, 4x zoom and 3 light modes (high, low, strobe) and Soft-Touch Technology, which provides momentary operation when the light is off, with the slight touch of the button.

3 LIGHT MODES (Rechargeable Battery)
- *High (360 lumens) - 1 hour / 125 meters*
- *Low (120 lumens) - 3 hours / 70 meters*
- *Strobe (360 lumens) - 25 minutes / 125 meters*

3 LIGHT MODES (AAA Batteries)
- *High (100 lumens) - 1 hour / 90 meters*
- *Low (30 lumens) - 4 hours / 50 meters*
- *Strobe (100 lumens) - 25 minutes / 90 meters*

DESIGN
- Anodized aircraft-grade aluminum
- Impact-resistant and waterproof (IP67)
- 4x adjustable zoom
- Detachable steel belt/pocket clip

OPERATION
- Rear-positioned, ON/OFF button
- Soft Touch can be used only when light is OFF

ACCESSORIES
- Micro USB to USB charging cable included

BATTERIES
- Powered by either 2 AAA batteries or 1 10850 rechargeable battery(included)

SPECS
- 0.1375 lbs.
- Length: Compacted: 6.3" / Extended: 6.5"
- Diameter: 0.7"







Actual Size

Display Dimensions
(H) 9.41" x (W) 6.5" x (D) 5.875"
Gift Box Dimensions
(H) 6.37" x (W) 1.06" x (D) 0.78"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397933809	6810	INSPECTOR RC

NEBO®

INSPECTOR™

WATERPROOF

The INSPECTOR is an innovative, powerful pocket light that outputs ***180 lumens***, with 3 light modes and 3x adjustable zoom that provides the perfect amount of light for any situation. The INSPECTOR is also ***waterproof*** (IP67) and features a removable steel clip and Soft-Touch Technology, which provides momentary operation when the light is off, with the slight touch of the button.

3 LIGHT MODES
- *High (180 lumens) - 2 hours / 84 meters*
- *Low (54 lumens) - 6 hours / 46 meters*
- *Strobe (180 lumens) - 50 minutes / 84 meters*

DESIGN
- Anodized aircraft-grade aluminum
- Impact-resistant and waterproof (IP67)
- 3x adjustable zoom
- Detachable steel belt/pocket clip

OPERATION
- Rear-positioned, ON/OFF button
- Soft Touch can be used only when light is OFF

BATTERIES
- Powered by 2 AAA batteries (included)

SPECS
- 0.1375 lbs.
- Length: Compacted: 5.75" / Extended: 6"
- Diameter: 0.47"

Actual Size

AVAILABLE COLORS

Camo Black

Display Dimensions
(H) 7.5" x (W) 5.375" x (D) 5.875"
Gift Box Dimensions
(H) 6" x (W) 0.78" x (D) 0.57"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397932512	6713	INSPECTOR with Display
645397933618	6798	INSPECTOR - Bulk Camo

NEBO®

TiNO™

The NEBO TiNO is a thin, ergonomic pocket light that features a ***300 lumen spot light*** and a ***250 lumen C·O·B work light.*** Equipped with full dimming and Power Memory Recall, the TiNO also features a pocket clip, collapsible hanging hook and powerful magnetic base for convenient hands-free lighting.

2 LIGHT MODES
- *Spot Light (300 lumens) - 2 hours / 135 meters*
- *Work Light (250 lumens) - 3 hours / 25 meters*

DESIGN
- Rugged plastic housing
- Water and impact-resistant
- Full dimming
- Power Memory Recall
- Belt/pocket clip with hanging hook
- Powerful magnetic base

OPERATION
- Side-positioned, ON/OFF button

BATTERIES
- Powered by 3 AAA batteries (included)

SPECS
- 0.23 lbs.
- (H) 4.25" x (W) 1.75" x (D) 1.5"

ASSORTED COLORS

Blue Black Red

Display Dimensions
(H) 9.875" x (W) 5.5" x (D) 7.875"
Color Assortment:
8 of each color
Gift Box Dimensions
(H) 4.375" x (W) 1.75" x (D) 1.625"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397933793	6809	TiNO Two-in-One Light

NEBO®

SLIM

RECHARGEABLE

The NEBO SLIM is a thin, ergonomic rechargeable pocket light that outputs ***500 lumens of intense bright light***. Equipped with full dimming and Power Memory Recall, the SLIM also features a pocket clip, collapsible hanging hook and powerful magnetic base for convenient hands-free lighting.

1 LIGHT MODE - with Dimming
- *100% (500 lumens) - 2 hours / 58 meters*
- *10% (50 lumens) - 10 hours / 18 meters*

DESIGN
- Fully rechargeable
- Full dimming
- Anodized aircraft-grade aluminum; water and impact-resistant
- Collapsible hanging hook
- Belt/pocket clip
- Memory Power Setting
- Battery charging indicator
- Powerful magnetic base

OPERATION
- Side-positioned, ON/OFF button; hold to dim

ACCESSORIES
- Micro USB to USB charging cable included

BATTERIES
- Powered by rechargeable battery (included) (Recharge time: 5 - 6 hours)

SPECS
- 0.25 lbs.
- (H) 4.1" x (W) 1.77" x (D) 1.25"

ASSORTED COLORS

Pink Black Red Silver

Display Dimensions
(H) 10.5" x (W) 5.5" x (D) 7.75"
#6694 Color Assortment:
4 of each color
Gift Box Dimensions
(H) 4.2" x (W) 1.9" x (D) 1.5"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397932390	6694	SLIM Assorted Color Display
044435918530	6694BLK	SLIM - Bulk Black
044435918561	6694PNK	SLIM - Bulk Pink
044435918547	6694RED	SLIM - Bulk Red
044435918554	6694SIL	SLIM - Bulk Silver

NEBO® SLYDE®+

OPTIMIZED CLARITY TECHNOLOGY

The SLYDE+ is a ***powerful 400 lumen work light and flashlight*** equipped with programmable memory settings for each light mode, a C•O•B red light function, a 4x adjustable zoom and direct-to-red feature. The C•O•B LED automatically turns on when opened, and the magnetic base provides convenient hands-free lighting.

4 LIGHT MODES
- *Work Light (400 lumens) - 3.5 hours / 32 meters*
- *Red (40 lumens) - 2 hours / 9 meters*
- *Red Flash (40 lumens) - 9 hours / 9 meters*
- *Flashlight (400 lumens) - 2 hours / 89 meters*

DESIGN
- Convex lens
- Tactical edge
- OC™ Technology
- 4x adjustable zoom
- Fully dimmable
- Direct-to-Red Feature *(hold button and slide open)*
- Memory Power Setting
- Anodized aircraft-grade aluminum; weather-proof (IPX4) and impact-resistant
- Powerful magnetic base

OPERATION
- Side-positioned, ON/OFF button; hold to dim
- C•O•B Work Light automatically turns ON when opened and OFF when closed

BATTERIES
- Powered by 4 AAA batteries (included)

SPECS
- 0.7 lbs.
- Length: Compacted: 6.75" / Extended: 9.5"
- Diameter: (Head) 1.625" / (Barrel) 1.375"

U.S. PATENT
- D 786,466 S

Display Dimensions
(H) 11.75" x (W) 7.25" x (D) 7.75"
Gift Box Dimensions
(H) 6.825" x (W) 1.75" x (D) 1.75"

AVAILABLE COLORS

Camo Storm Gray

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397931249	6783	SLYDE+ with Display
645397931935	6797	SLYDE+ - Bulk Camo

NEBO® SLYDE® KING

RECHARGEABLE

OPTIMIZED CLARITY TECHNOLOGY

The 500 lumen SLYDE KING is equipped with dimming and programmable memory settings for each light mode, a C•O•B red light function, a 4x adjustable zoom and best of all...it's ***rechargeable!***

4 LIGHT MODES
- *C•O•B work light (500 lumens) - 3.5 hours / 37 meters*
- *Red light (40 lumens) - 5.5 hours / 9 meters*
- *Red flash - 24 hours / 9 meters*
- *Flashlight (500 lumens) - 2.5 hours / 160 meters*

DESIGN
- Fully rechargeable
- Tactical edge
- OC™ Technology
- Convex lens
- 4x adjustable zoom
- Fully dimmable
- Direct-to-Red Feature *(hold button and slide open)*
- Memory Power Setting
- Anodized aircraft-grade aluminum; water and impact-resistant
- Powerful magnetic base
- Battery charging indicator

OPERATION
- Side-positioned, ON/OFF button; hold to dim
- C•O•B Work Light automatically turns ON when opened and OFF when closed

BATTERIES
- Powered by 1 Li-ion rechargeable battery (included) (3-4 hour recharge time)

ACCESSORIES
- Micro USB to USB cable included

SPECS
- 0.8 lbs.
- Length: Compacted: 6.875" / Extended: 9.5"
- Diameter: (Head) 1.75" / (Barrel) 1.25"

U.S. PATENT
- D 786,466 S





Display Dimensions
(H) 11.5" x (W) 5.5" x (D) 7.875"
Gift Box Dimensions
(H) 6.79" x (W) 1.85" x (D) 1.82"

AVAILABLE COLORS

Camo Storm Gray

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
044435917922	6726	SLYDE KING with Display
044435917939	6754	SLYDE KING - Bulk Camo

NEBO®

TACSLYDE®

AS SEEN ON TV

The TAC SLYDE features 2 different light sources, ***8 unique light modes*** and a 12x adjustable zoom. A powerful magnetic base provides convenient hands-free lighting, and the lanyard helps keep this light handy when you need it most.

3 C·O·B MODES
- *High (200 lumens) - 3 hours / 19 meters*
- *Low (40 lumens) - 8 hours / 13 meters*
- *Red Flash (20 lumens) - 8 hours / 6 meters*

5 LED MODES
- *High (300 lumens) - 2.5 hours / 135 meters*
- *Medium (150 lumens) - 6 hours / 84 meters*
- *Low (30 lumens) - 22 hours / 40 meters*
- *Strobe (300 lumens) - 6 hours / 135 meters*
- *S.O.S. (300 lumens) - 48 hours / 135 meters*

DESIGN
- Convex lens
- Tactical edge
- 12x adjustable zoom
- Anodized aircraft-grade aluminum; impact and water-resistant (IPX4)
- Powerful magnetic base

OPERATION
- Rear-positioned, ON/OFF button

ACCESSORIES
- Lanyard included

BATTERIES
- Powered by 3 AAA batteries (included)

SPECS
- 0.36 lbs.
- Length: Compacted: 5.94" / Extended: 7.1"
- Diameter: (Head) 1.375" / (Barrel) 1.125"

U.S. PATENT
- D 786,466 S

Actual Size

Display Dimensions
(H) 11.75" x (W) 7.25" x (D) 7.875"
Gift Box Dimensions
(H) 6.02" x (W) 1.5" x (D) 1.5"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397932871	6746	TAC SLYDE

NEBO®

MYCRO™

RECHARGEABLE

The MYCRO is impossibly bright and unbelievably small. Featuring 6 unique light modes, including the ***400 lumen TURBO MODE*** and 3 LED color options to accommodate any situation. The MYCRO is small enough to conceal in your hand or fit on your key ring. This powerful pocket light even comes with a stainless steel chain necklace to keep this light with you wherever you go.

5 LIGHT MODES + TURBO MODE
- *High (150 lumens) - 1 hour / 51 meters*
- *Medium (50 lumens) - 2 hours / 31 meters*
- *Low (15 lumens) - 5 hours / 18 meters*
- *Green - 40 hours / 1 meter*
- *Red - 40 hours / 1 meter*
- *TURBO (400 lumens) - 30 seconds / 82 meters*

DESIGN
- Fully rechargeable
- Anodized aircraft-grade aluminum; water and impact-resistant
- Direct-to-Low
- Mode recall feature
- Battery charging indicator

OPERATION
- 2 top-positioned, ON/OFF buttons:
  Primary Button for 5 light modes
  Turbo Button uses momentary operation

ACCESSORIES
- Micro USB to USB charging cable included
- Stainless steel necklace
- Wrist lanyard

BATTERIES
- Powered by rechargeable battery (included) (Recharge time: 2 hours)

SPECS
- 0.13 lbs.
- (H) 1.73" x (W) 1.16" x (D) 0.67"

Actual Size

ASSORTED COLORS

Black Red Silver

Display Dimensions
(H) 9.75" x (W) 6" x (D) 4.5"
Color Assortment:
6 of each color
Gift Box Dimensions
(H) 4.3" x (W) 0.9" x (D) 0.9"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397932529	6714	MYCRO

NEBO® the BIG Larry® 2 POWER WORK LIGHT

The BIG Larry 2 outputs ***500 lumens*** with the C•O•B work light and ***200 lumens*** from the top light. The red C•O•B light is perfect for distress signaling or roadside emergencies. The steel clip and magnetic base provide convenient hands-free lighting options.

4 LIGHT MODES
- *Top light (200 lumens) - 8 hours / 75 meters*
- *Work light (500 lumens) - 2.5 hours / 31 meters*
- *Red light (40 lumens) - 20 hours / 7 meters*
- *Red hazard flasher - 40 hours / 7 meters*

DESIGN
- Fully dimmable
- Direct-to-Red Feature
- Memory Power Setting
- Anodized aircraft-grade aluminum; water and impact-resistant
- Steel belt/pocket clip
- Powerful magnetic base

OPERATION
- Top-positioned, ON/OFF button

BATTERIES
- Powered by 3 AA batteries (included)

SPECS
- 0.45 lbs.
- (H) 7.75" x (W) 0.98" x (D) 1.25"

ASSORTED COLORS

Camo | Red | Storm Gray

Display Dimensions
(H) 11.75" x (W) 7.25" x (D) 7.875"
#6737 Color Assortment:
4 Red / 10 Storm Gray
Gift Box Dimensions
(H) 7.76" x (W) 1.26" x (D) 0.98"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397932468	6737	BIG Larry 2 Assorted Color Display
645397933755	6737CAMO	BIG Larry 2 - Bulk Camo
645397933762	6737GRAY	BIG Larry 2 - Bulk Storm Gray
645397933748	6737RED	BIG Larry 2 - Bulk Red

NEBO® the BIG Larry® PRO POWER WORK LIGHT

RECHARGEABLE

The BIG Larry PRO features a high-power, ***500 lumen*** C•O•B work light and red hazard flasher. ***Fully rechargeable*** and equipped with 2 magnetic charging stations, the BIG Larry PRO is ready to handle any task at any time. The PRO also has a powerful magnetic base and adjustable steel clip for convenient hands-free lighting. When there is work to be done...bring a PRO!

3 LIGHT MODES
- *High (500 lumens) - 4.5 hours / 37 meters*
- *Red (45 lumens) - 8 hours / 13 meters*
- *Red hazard flasher - 24 hours / 13 meters*

DESIGN
- Fully dimmable
- Direct-to-Red
- Anodized aircraft-grade aluminum; water and impact-resistant
- Adjustable clip
- Powerful magnetic base
- Battery charging indicator

OPERATION
- Top-positioned, ON/OFF button

ACCESSORIES
- Two magnetic charging stations and cables

BATTERIES
- Powered by 1 Li-ion rechargeable battery (included) (Recharge time: 5 - 6 hours)

SPECS
- 0.8 lbs.
- (H) 7.75" x (W) 1.1875" x (D) 1.375"





Display Dimensions
(H) 12.75" x (W) 9.5" x (D) 8.75"
Gift Box Dimensions
(H) 7.75" x (W) 1.5625" x (D) 1.325"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397931959	6640	BIG Larry PRO Power Work Light

NEBO® the BIG Larry® POWER WORK LIGHT

The BIG Larry knows how to light up a room! Equipped with new C·O·B LED technology, the BIG Larry outputs ***400 lumens of intense light***. Secondary light modes include Low (160 lumens) and the Emergency Red Flash mode. This intense red light is perfect for distress signaling or roadside emergencies. The anodized aluminum body and recessed LED housing ensures that the BIG Larry can handle any situation.

3 LIGHT MODES
- *High (400 lumens) - 4.5 hours / 29 meters*
- *Low (160 lumens) - 15 hours / 17 meters*
- *Red Flash - 40 hours*

DESIGN
- Anodized aircraft-grade aluminum; water and impact-resistant
- Powerful magnetic base

OPERATION
- Top-positioned, ON/OFF button

BATTERIES
- Powered by 3 AA batteries (included)

SPECS
- 0.45 lbs.
- (H) 7.4375" x (W) 0.875" x (D) 1.125"

AVAILABLE COLORS

Black | Silver | Camo | Red | Patriotic

Display Dimensions
(H) 12" x (W) 5.5" x (D) 7.8125"
#6306 Color Assortment:
4 Silver / 10 Black
Gift Box Dimensions
(H) 7.5" x (W) 1.25" x (D) 1"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397930365	6306	BIG Larry Assorted Color Display
645397930648	6382	BIG Larry - Bulk Camo
645397930679	6384	BIG Larry - Bulk Black
645397930686	6385	BIG Larry - Bulk Silver
645397930792	6413	BIG Larry - Bulk Red
645397931157	6493	BIG Larry - Bulk Patriotic

NEBO® the LiL Larry® POWER POCKET LIGHT

FLEX-POWER™

Don't let the name fool you, LiL Larry packs enough power to take its rightful place in the Larry family. Equipped with a ***250 lumen C·O·B work light***, LiL Larry features 3 light modes: high, low and emergency red flash. The anodized aluminum body and recessed LED housing ensure that LiL Larry is ready for any task. Flex-Power allows the LiL Larry to condense in size and operate with 2 AAA batteries instead of 3 AAA.

3 LIGHT MODES
- *High (250 lumens) - 3 hours / 29 meters*
- *Low (95 lumens) - 10 hours / 17 meters*
- *Red Flash - 10 hours*

DESIGN
- Anodized aircraft-grade aluminum; water and impact-resistant
- Steel clip
- Powerful magnetic base

OPERATION
- Top-positioned, ON/OFF button

BATTERIES
- Powered by 3 AAA batteries (included)
- Flex-Power™ allows operation with just 2 AAA

SPECS
- 0.2 lbs.
- (H) 6.0625" x (W) 0.625" x (D) 1"





AVAILABLE COLORS

Silver | Red | Black | Camo | Patriotic

Display Dimensions
(H) 10" x (W) 5.5" x (D) 7.75"
#6373 Color Assortment:
4 Red, 4 Silver & 10 Black
Gift Box Dimensions
(H) 6.25" x (W) 1" x (D) 0.75"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397930570	6373	LiL Larry Assorted Color Display
645397931027	6463	LiL Larry - Bulk Red
645397931034	6464	LiL Larry - Bulk Black
645397931041	6465	LiL Larry - Bulk Silver
645397931058	6466	LiL Larry - Bulk Camo
645397931140	6492	LiL Larry - Bulk Patriotic

NEBO®

the Larry C®

The Larry C features C•O•B LED technology which outputs ***170 lumens of intense light***. The rotating magnetic clip gives you convenient hands-free lighting by attaching to virtually anything. The reinforced plastic body design is water and impact-resistant, making this light basically indestructible.

1 LIGHT MODE
- *170 lumens - 5.6 hours / 20 meters*

DESIGN
- Water and impact-resistant
- Ergonomic non-slip grip
- Magnetic clip
- Protective LED housing

OPERATION
- Top-positioned, ON/OFF button

BATTERIES
- Powered by 3 AAA batteries (included)

SPECS
- 0.1870 lbs.
- (H) 6.375" x (W) 0.55" x (D) 1.25"

AVAILABLE COLORS

Camo Red Yellow Blue Gray

Display Dimensions
(H) 8.75" x (W) 6" x (D) 6"
#6327 Color Assortment:
6 Red, 6 Gray, 6 Blue & 6 Yellow
Gift Box Dimensions
(H) 6.5" x (W) 1.5" x (D) 0.75"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397930402	6327	Larry C Assorted Color Display
645397930464	6350	Larry C - Bulk Red
645397930471	6351	Larry C - Bulk Blue
645397930488	6352	Larry C - Bulk Gray
645397930495	6353	Larry C - Bulk Yellow
645397930501	6354	Larry C - Bulk Camo

NEBO®

LEO™

The LEO is an amazingly versatile pocket light. Fully dimmable and equipped with Memory Power Setting, the work light and spot light pivot and rotate to direct the light wherever you need it. A pocket clip, magnetic base and a kick stand / hanging hook give the LEO ***endless options of hands-free lighting***.

2 LIGHT MODES
- *Work Light (220 lumens) - 5 hours / 22 meters*
- *Spot Light (80 lumens) - 7 hours / 52 meters*

DESIGN
- Rotating directional light
- Non-slip rubber coating
- Water and impact-resistant
- Fully dimmable
- Memory Power Setting
- Pocket clip
- Powerful magnetic base
- Kick stand / hanging hook

OPERATION
- Top-positioned, ON/OFF button; hold to dim

BATTERIES
- Powered by 3 AAA batteries (included)

SPECS
- 0.7 lbs.
- Length: 6.625" / Extended: 9.75"
- Width: 0.75" / Depth: 1.375"

ASSORTED COLORS

Gray Black Orange

Actual Size

Display Dimensions
(H) 13" x (W) 4.75" x (D) 5.5"
Color Assortment:
8 of each color
Gift Box Dimensions
(H) 6.7" x (W) 1.33" x (D) 0.9"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397932086	6657	LEO Work Light and Spot Light

NEBO®

REDLINE® BLAST RC

RECHARGEABLE

WATERPROOF

The REDLINE BLAST RC is a ***3200 lumen, waterproof, rechargeable flashlight*** that is also a power bank for your USB powered device. The BLAST RC includes a charging cable and lanyard for convenient carry. The button also serves as a battery charging indicator.

4 LIGHT MODES
- *High (3200 lumens) - 2 hours / 261 meters*
- *Medium (320 lumens) - 4.5 hours / 82 meters*
- *Low (32 lumens) - 50 hours / 26 meters*
- *Variable Strobe (3200 lumens) - 3 hours / 261 meters*

DESIGN
- Fully rechargeable
- Power bank for your USB powered devices
- Convex lens
- Signature Red Ring®
- Tactical edge
- 4x adjustable zoom
- Anodized aircraft-grade aluminum; waterproof (IPX7) and impact-resistant
- Battery charging indicator

OPERATION
- Side-positioned, ON/OFF button

ACCESSORIES
- Micro USB/Lightning to USB charging cable included
- Lanyard included

BATTERIES
- Powered by two 18650 rechargeable batteries (included)

SPECS
- 0.925 lbs.
- Length: Compacted: 9.5" / Extended: 10.375"
- Diameter: (Head) 1.875" / (Barrel) 1.125"

U.S. PATENT
- D 659,869 S, 4,664,971

Display Dimensions
(H) 12.96" x (W) 8.5" x (D) 9"
Gift Box Dimensions
(H) 9.66" x (W) 2" x (D) 2"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397932413	6697	REDLINE BLAST RC

NEBO®

REDLINE® FLEX

RECHARGEABLE

FLEX-POWER™

The REDLINE FLEX utilizes ***Flex-Power Technology***, which allows the light to be powered by a single AA battery or a 14500 rechargeable battery (included). The FLEX features 4 light modes, including the ***450 lumen Turbo Mode*** and 250 lumen High Mode. The FLEX also offers a 6x adjustable zoom, a dual-direction clip and a powerful magnetic base for convenient hands-free lighting.

4 LIGHT MODES - 14500 Rechargeable Battery
- *High (250 lumens) - 2.5 hours / 160 meters*
- *Low (80 lumens) - 5.5 hours / 89 meters*
- *Strobe (250 lumens) - 2 hours / 160 meters*
- *TURBO (450 lumens) - 40 seconds / 237 meters*

3 LIGHT MODES - AA Battery
- *High (90 lumens) - 2.5 hours / 102 meters*
- *Low (30 lumens) - 4.5 hours / 57 meters*
- *Strobe (90 lumens) - 4 hours / 102 meters*

DESIGN
- Fully rechargeable
- Convex lens
- 6x adjustable zoom
- Anodized aircraft-grade aluminum; water and impact-resistant
- Signature Red Ring®
- Dual-direction steel clip
- Flex-Power™ Technology
- Battery charging indicator
- Powerful magnetic base

OPERATION
- Side-positioned, ON/OFF button with battery indicator

ACCESSORIES
- Micro USB to USB charging cable included

BATTERIES
- Flex-Power™ uses either one AA battery or one 14500 rechargeable battery (14500 included)

SPECS
- 0.2 lbs.
- Length: Compacted: 4.23" / Extended: 4.7"
- Diameter: (Head) 1.14" / (Barrel) 0.78"

U.S. PATENT
- D 659,869 S, 4,664,971

Actual Size



Display Dimensions
(H) 9" x (W) 5.5" x (D) 8"
Gift Box Dimensions
(H) 4.3" x (W) 0.9" x (D) 0.9"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397932444	6700	REDLINE FLEX

NEBO® REDLINE® BIG DADDY™

WATERPROOF

The REDLINE BIG DADDY is a ***completely waterproof (IPX7)*** flashlight that features a ***powerful 2,000 lumen output***, 4x adjustable zoom, 5 unique light modes and a convenient carry lanyard. The BIG DADDY, everything you could need in a flashlight, and then some!

5 LIGHT MODES
- *High (2000 lumens) - 3 hours / 346 meters*
- *Medium (800 lumens) - 6 hours / 219 meters*
- *Low (500 lumens) - 15 hours / 173 meters*
- *Strobe (2000 lumens) - 6 hours / 346 meters*
- *Beacon (2000 lumens) - 8 hours / 346 meters*

DESIGN
- Waterproof (IPX7)
- Convex lens
- Tactical edge
- 4x adjustable zoom
- Signature Red Ring®
- Anodized aircraft-grade aluminum; impact-resistant

OPERATION
- Rear-positioned, glow-in-the-dark ON/OFF button with Soft Touch Technology

ACCESSORIES
- Lanyard included

BATTERIES
- Powered by 9 AA batteries (included)

SPECS
- 1.325 lbs.
- Length: Compacted: 9" / Extended: 9.75"
- Diameter: (Head) 2.25" / (Barrel) 1.5"

U.S. PATENT
- 659,869 S



Display Dimensions
(H) 13.75" x (W) 8.5" x (D) 9"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397932376	6692	REDLINE BIG DADDY

NEBO® REDLINE® V

WATERPROOF

The REDLINE V is a powerful, ***500 lumen flashlight***, featuring OC Technology. The REDLINE V is ***completely waterproof (IPX7)*** and is also equipped with a steel clip, powerful magnetic base, 4x zoom and 5 light modes (high, medium, low, defensive strobe & S.O.S.).

5 LIGHT MODES
- *High (500 lumens) - 2.5 hours / 170 meters*
- *Medium (200 lumens) - 6 hours / 110 meters*
- *Low (50 lumens) - 22 hours / 50 meters*
- *Strobe (500 lumens) - 6 hours / 170 meters*
- *S.O.S. (500 lumens) - 48 hours / 170 meters*

DESIGN
- Convex lens
- Tactical edge
- 4x adjustable zoom
- OC™ Technology
- Signature Red Ring®
- Anodized aircraft-grade aluminum; waterproof (IPX7) and impact-resistant
- Steel belt/pocket clip
- Powerful magnetic base

OPERATION
- Rear-positioned, glow-in-the-dark ON/OFF button with Soft Touch Technology

BATTERIES
- Powered by 3 AAA batteries (included)

SPECS
- 0.35 lbs.
- Length: Compacted: 5" / Extended: 5.5"
- Diameter: (Head) 1.375" / (Barrel) 1.25"

U.S. PATENT
- 659,869 S

Actual Size

AVAILABLE COLORS

Gunmetal Gray | Black



Display Dimensions
(H) 12" x (W) 6" x (D) 8.75"
Gift Box Dimensions
(H) 5.15" x (W) 1.5" x (D) 1.5"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397931942	6639	REDLINE V with Display
645397932475	6703	REDLINE V - Bulk Black

NEBO® REDLINE® BLAST

WATERPROOF

With ***1,400 lumens*** of high intensity light, this must-have flashlight can throw a spectacularly bright beam 260 meters. The REDLINE BLAST is ***completely waterproof (IPX7)*** and ready for any weather condition. Want more? How about a 4x zoom and 5 light modes (high, medium, low, defensive strobe & flashing beacon).

5 LIGHT MODES
- *High (1400 lumens) - 2.5 hours / 260 meters*
- *Medium (560 lumens) - 7 hours / 180 meters*
- *Low (140 lumens) - 30 hours / 90 meters*
- *Strobe (1400 lumens) - 6 hours*
- *Beacon (200 lumens) - 120 hours*

DESIGN
- Convex lens
- Tactical edge
- 4x adjustable zoom
- Signature Red Ring®
- Anodized aircraft-grade aluminum; waterproof (IPX7) and impact-resistant

OPERATION
- Rear-positioned, glow-in-the-dark ON/OFF button with Soft Touch Technology

ACCESSORIES
- Lanyard (included)

BATTERIES
- Powered by 6 AA batteries (included)

SPECS
- 0.95 lbs.
- Length: Compacted: 7.25" / Extended: 7.75"
- Diameter: (Head) 1.875" / (Barrel) 1.375"

U.S. PATENT
- 659,869 S







Actual Size

Display Dimensions
(H) 12" x (W) 6" x (D) 8.75"
Gift Box Dimensions
(H) 7" x (W) 2" x (D) 1.95"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397931331	6542	REDLINE BLAST

NEBO® REDLINE® RC™ with MAGDOCK

RECHARGEABLE

OPTIMIZED CLARITY TECHNOLOGY

The REDLINE RC with MagDock features a ***MagDock magnetic charging station*** that docks and charges your REDLINE. Small enough to fit in the palm of your hand, the RC is fully equipped with all of the features that make the REDLINE series so popular.

4 LIGHT MODES
- *High (320 lumens) - 1 hour / 110 meters*
- *Medium (125 lumens) - 2 hours / 70 meters*
- *Low (32 lumens) - 9 hours / 35 meters*
- *Strobe (320 lumens) - 2 hours / 110 meters*

DESIGN
- 4x adjustable zoom
- Anodized aircraft-grade aluminum; water and impact-resistant
- OC™ Technology
- Convex lens
- Signature Red Ring®
- Steel belt/pocket clip
- Magnetic base
- Protective LED housing
- Battery charging indicator

OPERATION
- Side-positioned, ON/OFF button

ACCESSORIES
- USB to Micro USB cable included
- Lanyard included

BATTERIES
- Internal, rechargeable lithium-ion battery (Recharge time - up to 2 hours)

SPECS
- 0.25 lbs.
- Length: Compacted: 3.5625" / Extended: 3.875"
- Diameter: 1.25"

U.S. PATENT
- 8,628,210

Actual Size



Display Dimensions
(H) 11.125" x (W) 5.5" x (D) 7.75"
Gift Box Dimensions
(H) 4.2" x (W) 2.95" x (D) 2.35"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397930754	6392	REDLINE RC with MagDock

NEBO® REDLINE® SELECT RC®

RECHARGEABLE

This ***fully rechargeable*** flashlight offers ***1,000 lumens***, a Smart Select Dial to control the 5 unique light modes, a 4x adjustable beam and a steel clip. The REDLINE Select RC also acts as a ***power bank for your USB powered device***.

5 LIGHT MODES
- *High (1000 lumens) - 2.5 hours / 222 meters*
- *Medium (500 lumens) - 6 hours / 130 meters*
- *Low (100 lumens) - 15 hours / 60 meters*
- *Strobe (1000 lumens) - 8 hours / 120 meters*
- *Stealth Light (Green Low Light) - 120 hours / 4 meters*

DESIGN
- Fully rechargeable
- Power bank for your USB powered devices
- Anodized aircraft-grade aluminum; water and impact-resistant
- Convex lens
- Signature Red Ring®
- Heat sink design
- Tactical edge
- 4x adjustable beam
- Steel belt/pocket clip
- Anti-roll tactical grip ring
- Magnetic base
- Battery charging indicator

OPERATION
- Rear-positioned, glow-in-the-dark ON/OFF button with Smart Select Dial

ACCESSORIES
- USB charging cable included
- Lanyard included

BATTERIES
- One 18650 Li-ion rechargeable battery (included)

SPECS
- 0.5 lbs.
- Length: Compacted: 6.25" / Extended: 6.75"
- Diameter: (Head) 1.625" / (Barrel) 1.3125"

U.S. PATENT
- 659,869 S

Actual Size

Display Dimensions
(H) 13.75" x (W) 8.5" x (D) 9"
Acrylic Box Dimensions
(H) 9.25" x (W) 3" x (D) 3"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397932420	6698	REDLINE Select RC

NEBO® MICRO REDLINE®

OPTIMIZED CLARITY TECHNOLOGY

Don't let the micro size fool you...the Micro REDLINE OC packs enough power to carry the REDLINE name. This light is ***small enough to fit in the palm of your hand***, but bright enough for any situation. Equipped with OC Technology the Micro has a perfectly dispersed beam of light while in flood mode. The Micro REDLINE OC...small never shined so big!

4 LIGHT MODES
- *High (360 LUX) - 6 hours / 76 meters*
- *Medium (183 LUX) - 12 hours / 54 meters*
- *Low (39 LUX) - 15 hours / 25 meters*
- *Strobe (360 LUX) - 12 hours / 76 meters*

DESIGN
- Anodized aircraft-grade aluminum; water and impact-resistant
- OC™ Technology
- Convex lens
- Signature Red Ring®
- 6x adjustable beam
- Steel belt/pocket clip
- Magnetic base

OPERATION
- Rear-positioned, glow-in-the-dark ON/OFF button with Soft Touch Technology

BATTERIES
- Powered by 1 CR123A battery (included)

SPECS
- 0.1 lbs.
- Length: Compacted: 2.625" / Extended: 3.15"
- Diameter: (Head) 0.875" / (Barrel) 0.8125"

U.S. PATENT
- 659,869 S

Actual Size



Display Dimensions
(H) 8" x (W) 6" x (D) 5.5"
Gift Box Dimensions
(H) 2.75" x (W) 1.25" x (D) 1.1875"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397930167	6272-A	Micro REDLINE OC

NEBO®

REDLINE® OC

OPTIMIZED CLARITY TECHNOLOGY

The REDLINE OC outputs 600 LUX of pristine white light. 600 LUX is bright, but what makes the OC so special is the OC (Optimized Clarity) Technology that creates ***a perfectly dispersed beam of light*** while in flood mode.

2 LIGHT MODES
- *Steady ON (600 LUX) - 2 hours / 92 meters*
- *Strobe (600 LUX) - 4.5 hours / 92 meters*

DESIGN
- Anodized aircraft-grade aluminum; water and impact-resistant
- OC™ Technology
- Convex lens
- Signature Red Ring®
- Tactical edge
- 6x adjustable beam
- Dual-direction belt/pocket clip
- Magnetic base

OPERATION
- Rear-positioned, glow-in-the-dark ON/OFF button with Soft Touch Technology

ACCESSORIES
- Lanyard included

BATTERIES
- Powered by 1 AA battery (included)

SPECS
- 0.25 lbs.
- Length: Compacted: 4.1825" / Extended: 4.75"
- Diameter: (Head) 1.375" / (Barrel) 1"

U.S. PATENT
- 659,869 S

Actual Size

Display Dimensions
(H) 8" x (W) 7.5" x (D) 8.25"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397929499	6092	REDLINE OC

NEBO®

TWYST® Z

ARCUS LED TECHNOLOGY

The TWYST Z is a high-power work light, lantern and flashlight, all in one! The TWYST Z uses ARCUS LED Technology to ***shape light like never before***! The TWYST Z also features a 4x adjustable zoom and a powerful magnetic base that provides convenient hands-free lighting.

3 LIGHT MODES
- *Flashlight (400 lumens) - 2 hours / 89 meters*
- *C·O·B Work Light (75 lumens) - 10 hours / 11 meters*
- *C·O·B Lantern (200 lumens) - 2 hours / 13 meters*

DESIGN
- 4x adjustable zoom
- ARCUS C·O·B LED Technology
- Tactical edge
- Fully dimmable beam
- Anodized aircraft-grade aluminum; water and impact-resistant
- Powerful magnetic base

OPERATION
- Side-positioned ON/OFF button

BATTERIES
- Powered by 4 AAA batteries (included)

SPECS
- 0.55 lbs.
- Length: Compacted: 6.3125" / Extended: 6.75"
- Diameter: (Head) 1.75" / (Barrel) 1"

U.S. PATENT
- D 774,230 S

Actual Size

Display Dimensions
(H) 8.5" x (W) 9.25" x (D) 7"
Gift Box Dimensions
(H) 6.5" x (W) 1.875" x (D) 1.875"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397933786	6775	TWYST Z

NEBO® BIG CRYKET™

The BIG CRYKET is a versatile 3-in-1 LED light, featuring a ***300 lumen C·O·B work light***, a bright ***300 lumen spot light*** and an intense red light. Its unique swivel design allows the light's head to rotate into a forward-facing light, perfect for various working conditions. The magnetic base and steel clip provide convenient hands-free lighting.

3 LIGHT MODES
- *Spot Light (300 lumens) - 5 hours / 140 meters*
- *C·O·B Work Light (300 lumens) - 5 hours / 20 meters*
- *Red (30 lumens) - 10 hours / 6 meters*

DESIGN
- Fully dimmable
- Power memory setting
- Direct-to-red feature
- Anodized aircraft-grade aluminum; water and impact-resistant
- 90º swivel head
- Dual-direction steel belt/pocket clip
- Powerful magnetic base
- Rubberized non-slip grip

OPERATION
- Side-positioned, ON/OFF button

BATTERIES
- Powered by 3 AA batteries (included)

SPECS
- 0.5625 lbs.
- (H) 5.4375" x (W) 1.8125"

PATENT PENDING

Actual Size

Display Dimensions
(H) 14" x (W) 5.5" x (D) 7.75"
Gift Box Dimensions
(H) 5.75" x (W) 3.1875" x (D) 2.625"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397932154	6666	BIG CRYKET

NEBO® CRYKET™

The NEBO CRYKET is a versatile 3-in-1 LED light, featuring a ***240 lumen C·O·B work light***, a bright ***250 lumen spot light*** and an intense red or green light. Its unique swivel design allows the light's head to rotate into a forward-facing light, perfect for various working conditions. The magnetic base and steel clip provide convenient hands-free lighting.

3 LIGHT MODES
- *Spot Light (250 lumens) - 3.5 hours / 113 meters*
- *C·O·B Work Light (240 lumens) - 2.75 hours / 21 meters*
- *Red (15 lumens) - 6.5 hours / 6 meters*
- *Green (30 lumens) - 3 hours / 8 meters [#6549 Camo]*

DESIGN
- Fully dimmable
- Anodized aircraft-grade aluminum; water and impact-resistant
- 90º swivel head
- Power memory setting
- Direct-to-red feature
- Steel belt/pocket clip
- Powerful magnetic base
- Rubberized non-slip grip

OPERATION
- Top-positioned, ON/OFF button

BATTERIES
- Powered by 4 AAA batteries (included)

SPECS
- 0.3 lbs.
- (H) 4.825" x (W) 1.625"

PATENT PENDING

Actual Size

AVAILABLE COLORS

Smoke Gray | Camo

Display Dimensions
(H) 13" x (W) 5.5" x (D) 7.75"
Gift Box Dimensions
(H) 4.825" x (W) 3" x (D) 2.325"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397930914	6437	CRYKET with Display
645397931393	6549	CRYKET - Bulk Camo

NEBO®

PaL+™

RECHARGEABLE

The PaL+ is a ***3-in-1 power bank, flashlight and folding knife*** that conveniently fits in your pocket, purse or briefcase. This portable, rechargeable 400 lumen flashlight also serves as a backup power source for mobile phones and other USB rechargeable electronic devices. The PaL+ also features 3" folding blade, that can be removed for safe travel.

3 LIGHT MODES
- *High (400 lumens) - 2.3 hours / 167 meters*
- *Low (40 lumens) - 13 hours / 57 meters*
- *Strobe (400 lumens) - 2.5 hours / 167 meters*

DESIGN
- Rechargeable
- Anodized aluminum; water and impact-resistant
- 420 grade stainless steel blade
- Removable folding blade
- Power bank for USB powered devices
- Charging indicator

OPERATION
- Side-positioned, ON/OFF button;

ACCESSORIES
- Micro USB to USB charging cable included

BATTERIES
- Powered by 1 rechargeable battery (included)

SPECS
- 0.44 lbs.
- Length: 5" / Extended: 8.375"
- Width: 1.25" / Depth: 1"

Actual Size

Display Dimensions
(H) 9" x (W) 16" x (D) 11"
Natralock Dimensions
(H) 4.375" x (W) 8.6" x (D) 1.75"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397932536	6715	PaL+ Power Bank Flashlight & Knife

NEBO®

BITBRITE™

The NEBO BITBRITE is an innovative, useful C•O•B task light that outputs 40 lumens of bright light. Stored inside the BITBRITE are 3 magnetic bits: Phillips, Flat & Torx (T15). A steel pocket clip and powerful magnetic base are also included for convenient hands-free lighting.

2 LIGHT MODES
- *High (40 lumens) - 1.5 hours / 10 meters*
- *Low (10 lumens) - 8 hours / 5 meters*

DESIGN
- Steel belt/pocket clip
- Three magnetized bits: Phillips, Slot & Torx (T15)
- Anodized aircraft-grade aluminum; water and impact-resistant
- Screw lid keeps bits safe
- Powerful magnetic base

OPERATION
- Rear-positioned, ON/OFF button

BATTERIES
- Powered by 1 AAA battery (included)

SPECS
- 0.13 lbs.
- (H) 4.2" x (W) 0.9" x (D) 0.75"

Actual Size



Display Dimensions
(H) 11.75" x (W) 7.25" x (D) 7.875"
Color Assortment:
4 Red / 10 Storm Gray
Gift Box Dimensions
(H) 7.76" x (W) 1.26" x (D) 0.98"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397932482	6706	BITBRITE

NEBO®

TANGO™

RECHARGEABLE

The TANGO features 2 high-power light sources, a 250 lumen spot light and 750 lumen C•O•B work light. The TANGO is fully rechargeable and also serves as a power bank for your USB powered devices. A seven position 180° rotating arm functions as a hanging hook, carry handle, or a kickstand. And best of all, use Turbo Mode to combine the spot light and work light for ***1,000 lumens of intense illumination***. After all, it takes two to TANGO.

3 LIGHT MODES
- *Work Light (750 lumens) - 2 hours / 52 meters*
- *Spot Light (250 lumens) - 5 hours / 22 meters*
- *TURBO MODE (1000 lumens) - 2 minutes*

DESIGN
- Fully rechargeable
- Power bank for your USB powered devices
- Full dimming
- Memory Power Setting
- Non-slip rubber coating
- Water and impact-resistant
- 180° pivoting base
- Battery charging indicator

OPERATION
- Rear-positioned, ON/OFF button; hold to dim

ACCESSORIES
- Micro USB to USB cable and AC adapter included

BATTERIES
- Powered by rechargeable battery (included) (Recharge time: 5 - 6 hours)

SPECS
- 0.7 lbs.
- (H) 5.875" x (W) 5.875" x (D) 1.75"

Display Dimensions
(H) 13" x (W) 4.75" x (D) 5.5"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397932147	6665	TANGO Work Light & Spot Light

NEBO®

ARMOR 3

WATERPROOF

ARMOR 3, the toughest light, period. Completely ***waterproof (IPX7) and impact-tested at 66 feet***, this incredibly strong light is also unbelievably bright. The ARMOR 3 features a 360 lumen work light and 160 lumen spot light that are both dimmable with programmable power memory. A powerful magnetic tilting base lets you direct light anywhere you need it, and the steel pocket clip allows you to keep this light handy while having your hands free.

Actual Size

3 LIGHT MODES
- *Spot Light (160 lumens) - 5 hours / 83 meters*
- *C•O•B Work Light (360 lumens) - 2.5 hours / 44 meters*
- *Red C•O•B Work Light (40 lumens) - 1.5 hours / 16 meters*

DESIGN
- Non-slip rubber coating
- Waterproof (IPX7) and impact-resistant (66 feet)
- Floats
- Fully dimmable
- Memory Power Setting
- Direct-to-Red feature
- Steel clip
- Powerful tilting magnetic base

OPERATION
- Front-positioned, ON/OFF button; hold to dim

BATTERIES
- Powered by 3 AAA batteries (included)

SPECS
- 0.43 lbs.
- (H) 5.78" x (W) 2.44" x (D) 1.26"

Display Dimensions
(H) 12" x (W) 4.875" x (D) 5.5"
Gift Box Dimensions
(H) 5.86" x (W) 2.44" x (D) 1.28"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397931256	6526	ARMOR 3 Work Light & Spot Light

NEBO®

WORKBRITE® 2

The WORKBRITE 2 adapts to your work environment, making it the handiest of work lights. Equipped with a ***200 lumen C•O•B LED work light***, the WORKBRITE 2 also features a ***100 lumen top light*** and a rear, emergency red flasher LED. The WORKBRITE 2 provides hands-free lighting in three different ways: a hanging hook, a 200° pivoting stand and a magnetic base. Whether you are under the hood, under the sink or just out in the dark, the WORKBRITE 2 works great for any application.

3 LIGHT MODES
- *Work Light (200 lumens) - 3 hours / 20 meters*
- *Top Light (100 lumens) - 8 hours / 47 meters*
- *Red Flash - 200 hours*

DESIGN
- Water and impact-resistant
- Ergonomic, non-slip grip
- 200° pivoting stand
- Collapsible, hanging hook
- Powerful magnetic base

OPERATION
- Front-positioned, ON/OFF button
- Emergency Red Flasher LED is independently controlled; press light to activate

BATTERIES
- Powered by 3 AAA batteries (included)

SPECS
- 0.35 lbs.
- (H) 8.5" x (W) 2" x (D) 1.5"

Display Dimensions
(H) 12.75" x (W) 5.5" x (D) 7.75"
Gift Box Dimensions
(H) 8.5" x (W) 2" x (D) 1.5"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397930341	6304	WORKBRITE 2

NEBO®

THE RECHARGEABLE

WORKBRITE® 2

RECHARGEABLE

Never worry about replacing batteries again, with The ***RECHARGEABLE*** WORKBRITE 2. This work light is equipped with a 220 lumen C•O•B LED work light, a 120 lumen top light and a rear, emergency red flasher LED. The WORKBRITE 2 provides hands-free lighting in three different ways: a hanging hook, a 200° pivoting stand and a magnetic base. Whether you are under the hood, under the sink or just out in the dark, the WORKBRITE 2 works great for any application.

3 LIGHT MODES
- *Work Light (220 lumens) - 6 hours / 22 meters*
- *Top Light (120 lumens) - 8 hours / 52 meters*
- *Red Flash - 200 hours*

DESIGN
- Fully rechargeable
- Water and impact-resistant
- Ergonomic, non-slip grip
- 200° pivoting stand
- Collapsible, hanging hook
- Powerful magnetic base
- Battery charging indicator

OPERATION
- Front-positioned, ON/OFF button
- Emergency Red Flasher LED is independently controlled; press light to activate

ACCESSORIES
- 16.5" USB to Micro USB cable included

BATTERIES
- Powered by 1 18650 Li-ion rechargeable battery Recharge time: 4-5 hours (AC) / 6-7 hours (USB)

SPECS
- 0.35 lbs.
- (H) 8.5" x (W) 2" x (D) 1.5"

Display Dimensions
(H) 13.25" x (W) 5.5" x (D) 7.75"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397930358	6305	The Rechargeable WORKBRITE 2

NEBO®

REBEL™

RECHARGEABLE

The REBEL is a fully rechargeable task light that includes an adjustable head strap for use as a head lamp. Small enough to fit in the palm of your hand, this powerful light rebels against its size with its impressive ***600 lumen Turbo Mode***. This bright light is also equipped with a rotating, removable steel clip and powerful magnetic base to provide even more hands-free lighting options.

4 LIGHT MODES
- *High (240 lumens) - 2 hours / 56 meters*
- *Low (60 lumens) - 4.5 hours / 28 meters*
- *Turbo (600 lumens) - 40 seconds / 90 meters*
- *Strobe (600 lumens) - 2 hours / 90 meters*

DESIGN
- Fully rechargeable
- Removable steel clip
- Anodized aircraft-grade aluminum; water and impact-resistant

OPERATION
- Top-positioned, ON/OFF button

ACCESSORIES
- Adjustable head strap; one size fits all
- Magnetic USB to Micro USB charging cable with charging indicator included

BATTERIES
- Powered by rechargeable battery (included) (Recharge time: 1.5 - 2 hours)

SPECS
- 0.1875 lbs.
- (H) 2.85" x (W) 1.2" x (D) 1"

Display Dimensions
(H) 11.5" x (W) 10.75" x (D) 13.75"
Gift Box Dimensions
(H) 5.25" x (W) 3.25" x (D) 2.45"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397932369	6691	REBEL Task Light & Head Lamp

NEBO®

DUO 250+ LUMEN HEAD LAMP

The NEBO DUO Head Lamp is an ***all-powerful, hands-free lighting solution***. The push button on/off button allows you to easily cycle through the FOUR light modes: one white LED (250 Lumens), 2 C•O•B strips (80 Lumens) or 2 RED C•O•B strips in steady or beacon mode. The red LED is a low-signature light, which ensures stealth in the dark, enhances night vision and makes reading in little to no light possible. Its signature 2 strip C•O•B design fully illuminates your immediate area with its wide flood beam. The DUO Head Lamp is tough, reliable, lightweight and completely shock-proof.

4 LIGHT MODES
- *Spot Light (250 lumens) - 3.5 hours / 122 meters*
- *C•O•B Flood Light (80 lumens) - 7 hours / 13 meters*
- *Red C•O•B (10 lumens) - 8 hours / 4 meters*
- *Red Beacon - 48 hours / visible over 1 mile*

DESIGN
- Fully dimmable
- Water and impact-resistant durable housing
- 90° tilt
- Power memory setting
- Direct-to-red feature

OPERATION
- Top-positioned, ON/OFF button

ACCESSORIES
- Dual adjustable head strap; one size fits all

BATTERIES
- Powered by 3 AAA batteries (included)

SPECS
- 0.2 lbs.



Display Dimensions
(H) 12.5" x (W) 6.625" x (D) 10"
Clamshell Dimensions
(H) 6.125" x (W) 5.25" x (D) 3"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397930983	6444	DUO 250+ Lumen Head Lamp

NEBO eye Smart Sensor light

The NEBO EYE Smart Sensor Light detects motion that automatically activates the ***260 lumen C·O·B area light***. The daylight sensor allows the light to remain off when enough light is already present. The 3 light modes (high, low & security flash), help you illuminate any space with the perfect amount of light. The EYE magnetically rests inside of the base, which allows for multi-directional rotation or easy removal for hand-held use.

3 LIGHT MODES
- *100% (260 lumens) - 2.5 hours / 24 meters*
- *30% (100 lumens) - 7 hours / 15 meters*
- *Security Flash (260 lumens) - 6.5 hours / 24 meters*

DESIGN
- Smart Sensor motion detection
- Sensor detects darkness to preserve battery life
- 360° rotating magnetic design
- Water and impact-resistant
- Powerful detachable magnetic base
- Drywall screw hole
- Hook & loop double-sided tape

OPERATION
- Top-positioned, ON/OFF button

BATTERIES
- Powered by 3 AAA batteries (included)

SPECS
- 0.33 lbs.
- (H) 3.125" x (W) 3" x (D) 3"

Actual Size

Display Dimensions
(H) 11" x (W) 6.725" x (D) 12"
Natralock Dimensions
(H) 10.9" x (W) 4.8" x (D) 3"
#6776 Dimensions
(H) 11" x (W) 9.75" x (D) 3"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397933823	6776	EYE Smart Sensor Light
645397930000	6776KIT	EYE Light Combo Pack

NEBO eye light

The NEBO EYE Light is a perfectly versatile ***220 lumen C·O·B work light*** that helps illuminate any space with just the right amount of light. The EYE magnetically rests inside of the base which allows for 360° rotation to direct the light wherever you need it most. The base is also magnetic and features a drywall screw hole for permanent mounting and hook & loop double-sided tape for additional mounting options. Each package contains two EYE Lights.

3 LIGHT MODES
- *100% (220 lumens) - 3 hours / 8.5 meters*
- *30% (70 lumens) - 9 hours / 4.5 meters*
- *S.O.S. (220 lumens) - 10 hours / 8.5 meters*

DESIGN
- 360° rotating magnetic design
- Water and impact-resistant
- Powerful detachable magnetic base
- Drywall screw hole
- Hook & loop double-sided tape

OPERATION
- Top-positioned, ON/OFF button

BATTERIES
- Powered by 3 AAA batteries (included)

SPECS
- 0.33 lbs.
- (H) 3.125" x (W) 3" x (D) 3"

Actual Size

Display Dimensions
(H) 11" x (W) 6.725" x (D) 12"
Natralock Dimensions
(H) 10.9" x (W) 4.8" x (D) 3"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397932352	6690	EYE Light

NEBO®

Flipit400

The Flipit400 is a ***400 lumen C·O·B LED light*** that operates like a standard household light switch. You can flip to High Mode for 400 lumens of intense bright light, or flip it halfway for 100 lumens of bright light to extend the battery life. Flipit400 includes hook & loop double-sided tape and 2 magnets for two easy mounting options, as well as a drywall screw hole for permanent mounting.

2 LIGHT MODES
- *High (400 lumens) - 5 hours / 28 meters*
- *Low (100 lumens) - 20 hours / 16 meters*

DESIGN
- Water and impact-resistant plastic design
- Powerful magnets, double-sided hook and loop tape, and screw hole for mounting

OPERATION
- Front-positioned, ON/OFF switch

BATTERIES
- Powered by 3 AA batteries (included)

SPECS
- 0.35 lbs.
- Size: (L) 4.5" x (W) 3.15" x (D) 1.25"

Actual Size



Display Dimensions
(H) 11.375" x (W) 7.375" x (D) 11"
Clamshell Dimensions
(H) 11.375" x (W) 4.75" x (D) 1.25"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397932437	6699	Flipit400

NEBO®

Contemporary

Flipit

The NEBO Contemporary Flipit is a ***240 lumen C·O·B LED light*** that operates like a standard household light rocker switch. Flipit includes hook & loop double-sided tape and 2 magnets for two easy mounting options, as well as a drywall screw hole for permanent mounting. The Flipit is powered by 3 AAA batteries (included). Each package contains 2 Contemporary Flipit portable LED lights.

1 LIGHT MODE
- *240 lumens - 4 hours / 21 meters*

DESIGN
- Water and impact-resistant plastic design
- Powerful magnets and double-sided hook and loop tape for mounting

BATTERIES
- Powered by 3 AAA batteries (included)

SPECS
- Size: (L) 3.875" x (W) 3.125" x (D) 0.75"

Actual Size

Display Dimensions
(H) 11.375" x (W) 7.375" x (D) 11"
Clamshell Dimensions
(H) 11.375" x (W) 4.75" x (D) 1.25"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397931539	6558	Contemporary Flipit

NEBO® POPPY™

Poppy is a combination ***300 lumen C·O·B LED lantern and bright 120 lumen LED spot light***. Poppy is the perfect light for indoor or outdoor use when versatility and powerful lighting are critical. With a rubberized impact-resistant body, Poppy is both rugged and soft to the touch. Poppy easily changes from spot light to lantern with just a slide of its top, revealing a full 360° C·O·B lantern. The handle is designed to easily adjust to conveniently serve both light modes.

2 LIGHT MODES
- *C·O·B Lantern (300 lumens) - 7.5 hours / 15 meters*
- *Spot Light (120 lumens) - 18 hours / 120 meters*

DESIGN
- Fully dimmable
- Rubberized body design; water and impact-resistant
- Adjustable handle
- Power memory setting

OPERATION
- Side-positioned, ON/OFF button

BATTERIES
- Powered by 3 AA batteries (included)

SPECS
- 0.3 lbs.
- Height: Closed - 5.46" / Open - 7.79"
- Diameter: 3.58"

AVAILABLE COLORS

Red | Dark Gray | Yellow | Green

Display Dimensions
(H) 15.5" x (W) 11.5" x (D) 11.5"
#6555 Color Assortment:
6 of each color
Gift Box Dimensions
(H) 5.625" x (W) 3.5" x (D) 3.5"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397931454	6555	Poppy Assorted Color Display
645397931713	6594	Poppy - Bulk Red
645397931720	6595	Poppy - Bulk Dark Gray
645397931737	6596	Poppy - Bulk Yellow
645397931744	6597	Poppy - Bulk Green
645397932031	6651	Poppy Countertop Display

NEBO® Z-BUG™ LANTERN + LIGHT

The next line of bug defense is Z-Bug Lantern + Light. Equipped with ***bug-attracting NUV LEDs*** and a ***360° bug-zapping electric grid***, this lantern & spot light combo will keep your outdoor excursions enjoyable and bug free! The handle easily adjusts to conveniently serve both light modes. Z-Bug Lantern + Light includes Z-Bug Bulb Sweeper to remove insect remains from the grid housing.

1 SPOT LIGHT MODE
- *120 lumens - 18 hours / 120 meters*

3 LANTERN MODES
- *White (250 lumens) - 6 hours / 10 meters*
- *White & NUV LEDs - 24 hours*
- *NUV LEDs (395nm) - 40 hours*

DESIGN
- Fully dimmable
- 360° insect-zapping rails (1,000 - 1,200V)
- 360° protective cover for electric rails
- Adjustable handle

OPERATION
- Side-positioned, ON/OFF button

ACCESSORIES
- Z-Bug Bulb™ Sweeper for easy cleaning

BATTERIES
- Powered by 3 AA batteries (included)

SPECS
- 0.3 lbs.
- Height: Closed - 5.46" / Open - 7.79"
- Diameter: 3.58"

Display Dimensions
(H) 14" x (W) 12.75" x (D) 10.25"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397931706	6587	Z-Bug Lantern + Light

NEBO®

BRITEBUCKET™

WATERPROOF

The BRITE BUCKET is a 5 liter (1.3 gallon) capacity bucket that features a ***200 lumen removable C·O·B puck light*** in the base, perfect to illuminate your bucket's contents or to use as an area light. The BRITE BUCKET's durable material is designed to quickly collapse for easy storage and transport.

3 LIGHT MODES
- *High (200 lumens) - 3 hours / 19 meters*
- *Low (60 lumens) - 6 hours / 10 meters*
- *S.O.S. (200 lumens) - 8 hours / 19 meters*

DESIGN
- Fully collapsible
- 5 liter (1.3 gallon) capacity
- Folding carry handle
- Removable magnetic work light
- Impact-resistant and waterproof (IPX7)

OPERATION
- Front-positioned, ON/OFF button; hold to dim

ACCESSORIES
- 200 lumen magnetic puck light

BATTERIES
- Powered by 3 AAA batteries (included)

SPECS
- 0.7 lbs.
- Open: (H) 7.6875" x (W) 10.25"
- Collapsed: (H) 2.25" x (W) 10.25"

Display Dimensions
(H) 10" x (W) 10.25" x (D) 11.625"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397932161	6667	BRITE BUCKET

NEBO®

GLOW™

ARCUS LED TECHNOLOGY

The NEBO GLOW Light + Handle fits most of the popular 30 oz. and 20 oz. tumblers. GLOW not only makes it easier to hold and carry, but gives you the ***power of light at your fingertips***. No more slipping, dripping or tripping in the dark while trying to balance your tumbler when your hands are full. The GLOW fits most standard vehicle cup holders, and perfectly holds your tumbler secure with the rubberized grip ring.

The GLOW fits a variety of 30 & 20 oz. tumblers, including, but not limited to:

YETI, RTIC, Glacier Point, Ozark Trail, NEBO, Member's Mark, Mossy Oak & zak!

3 LIGHT MODES
- *Task Light (220 lumens) - 3 hours / 24 meters*
- *Lantern (130 lumens) - 3 hours / 15 meters*
- *Task + Lantern - 2 hours / 24 meters*

DESIGN
- Ergonomic handle for 30 oz. tumbler
- Fully dimmable
- Memory Power Setting
- Direct-to-Lantern feature
- Rubberized non-slip grip
- Water and impact-resistant

OPERATION
- Top-positioned, ON/OFF button; hold to dim

ACCESSORIES
- Insert to fit 20 oz. tumbler included

BATTERIES
- Powered by 3 AAA batteries (included)

SPECS
- 0.47 lbs.
- (H) 4.625" x (W) 4.625" x (D) 6.75"

PATENT PENDING

Display Dimensions
(H) 13" x (W) 4.75" x (D) 5.5"
Gift Box Dimensions
(H) 4.825" x (W) 6.7" x (D) 4.75"
Natralock Dimensions
(H) 4.825" x (W) 6.7" x (D) 4.75"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397932178	6668	GLOW with Display
645397932642	6727	GLOW Light + Handle

NEBO®

POPLITE

The new NEBO POPLITE is a ***versatile, compact light and lantern***. Its expandable design allows the POPLITE to easily change from flood light, to spot light, to lantern, by sliding the body of the light. Small enough to fit on a key ring, the POPLITE also features a magnetic base and a detachable carabiner clip. To activate the light, just pop the carabiner clip from the light body and the POPLITE is ready to light the way!

3 LIGHT MODES
- *Spot Light (100 LUX) - 2.5 hours / 40 meters*
- *Flood Light (20 lumens) - 2.5 hours / 11 meters*
- *Lantern (20 lumens) - 2.5 hours / 6 meters*

DESIGN
- 8x adjustable zoom
- Anodized aircraft-grade aluminum; water and impact-resistant
- Lantern diffuser
- Carabiner clip
- Powerful magnetic base

OPERATION
- Pop-on power; just remove carabiner cap

BATTERIES
- Powered by 3 LR44 batteries (included)

SPECS
- 0.1 lbs.
- Length: Compacted: 2.52" / Extended: 3.66"
- Diameter: 0.75"

Actual Size

AVAILABLE COLORS

Black Silver Red

Display includes area for testing magnetic base. 'TRY ME' purposes only, not intended for display.

Display Dimensions
(H) 12" x (W) 7" x (D) 6"
Color Assortment:
16 of each color
Gift Box Dimensions
(H) 2.625" x (W) 1" x (D) 0.75"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397931522	6557	POPLITE Lantern and Spot Light

NEBO®

LUMO®

Compact, handy and bright…the LUMO Clip Light is ***the perfect "whatever you need it to be" light***. Key chain light, purse light, backpack light, book light…the possibilities are endless. This compact 25 lumen light comes with a carabiner attachment to clip anywhere you need. The white top of the LUMO is a diffuser dome that helps spread the light evenly to create a more omnidirectional light source. LUMO Clip Light…the brilliant clip light!

1 LIGHT MODE
- *25 lumens - 5 hours / 3 meters*

DESIGN
- Anodized aircraft-grade aluminum, water and impact-resistant
- Carabiner clip
- Diffuser dome softens the light

OPERATION
- Rear-positioned glow-in-the-dark ON/OFF button

BATTERIES
- Powered by 3 LR44 batteries (included)

SPECS
- 0.2 lbs.
- (L) 3.625" x (W) 0.75"



AVAILABLE COLORS

Silver Red Blue Black

Display Dimensions
(H) 9" x (W) 6.5" x (D) 6.5"
#6095 Color Assortment:
12 of each color

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397929529	6095	LUMO Assorted Color Display
645397929864	6157	LUMO - Bulk Red
645397929871	6158	LUMO - Bulk Silver
645397929888	6159	LUMO - Bulk Blue
645397929895	6160	LUMO - Bulk Black

NEBO®

TRANSPORT®

RECHARGEABLE

The TRANSPORT is a compact, ***rechargeable*** flashlight that provides powerful bright light at your fingertips! The TRANSPORT is compatible with any DC 12V socket. Just plug directly into your car, truck, boat or any other 12V outlet. Ideal for travel, the TRANSPORT conveniently fits in your pocket, purse or briefcase.

1 LIGHT MODE
- *125 lumens - 1 hour / 90 meters*

LIGHT
- High-power 125 lumen LED

DESIGN
- Fully rechargeable
- Fits any 12V outlet (car cigarette lighter)
- Anodized aircraft-grade aluminum; water and impact-resistant
- Battery charging indicator

OPERATION
- Top-positioned ON/OFF dial; twist to activate

BATTERIES
- Powered by 1 16340 Lithium Ion rechargeable battery (included)

SPECS
- 0.15 lbs.
- (L) 3.6875" x (W) 0.875"

Actual Size

AVAILABLE COLORS

Silver Black

Display Dimensions
(H) 7.25" x (W) 7.625" x (D) 6.25"
#6311 Color Assortment:
6 Silver / 12 Black

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397930396	6311	TRANSPORT Assorted Color Display
645397931065	6467	TRANSPORT - Bulk Black
645397931072	6468	TRANSPORT - Bulk Silver

NEBO®

Folding LOCK-BLADE
Utility Knife

The Folding Lock-Blade Utility Knife uses a ***quick change feature*** making it easier to change the blade without any tools. The utility knife accepts all standard utility blades and incorporates a blade lock system which makes this a safe, strong and secure knife that can be unlocked with one hand.

DESIGN
- Anodized aluminum handle with rubber grip
- Quick change blade feature; no tools required
- Thumb studs for one-handed opening
- Carabiner
- Lock release button to unfold

SPECS
- 0.5 lbs.
- Length: (Open) 8" / (Closed) 4.25"
- (W) 1.5" x (D) 0.75"

ASSORTED COLORS

Black Silver Yellow

Display Dimensions
(H) 8.75" x (W) 14" x (D) 10.5"
Color Assortment:
6 of each color
Clamshell Dimensions
(H) 8.25" x (W) 4.25" x (D) 1.25"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397900504	5517	Folding Lock-Blade Utility Knife

NEBO®

14-in-1 Ultra™ Socket

The NEBO 14-in-1 Ultra Socket comes with ***7 screwdriver bits and 5 sockets conveniently stored inside the handle***. The head of the Ultra Socket tilts a full 180° and locks at 0°, 45°, and 90°, working perfectly as a nut driver for those hard to reach places. The handle is ergonomically designed to add comfort and grip to improve performance. The Ultra Socket features a reversible ratchet mechanism making it easier to loosen or tighten any bolt. The 14-in-1 Ultra Socket meets and exceeds ANSI standards and is created to withstand more than the normal wear and tear.

DESIGN
- Head tilts and locks at 0°, 45° & 90°
- Reversible ratchet mechanism
- Water and impact-resistant
- Ergonomic reinforced plastic handle
- Socket adapter
- Sockets and bits stored inside handle

SOCKETS
- SAE: 1/4", 9/32", 5/16", 11/32", 3/8" & Socket adapter

BITS
- Phillips: P1-P3
- Slotted: 3/16" & 1/4"
- Torx: T15 & T20

SPECS
- 0.75 lbs.
- (L) 8.25" x (W) 1.5"

Display Dimensions
(H) 14.75" x (W) 9.125" x (D) 6"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397610113	5606	Ultra 14-in-1 Socket and Screwdriver

NEBO®

Ultra™ Socket
Combination Kit

The NEBO Ultra Socket Combination Kit comes with ***19 sockets conveniently stored in SAE and Metric trays***. The head of the Ultra Socket tilts and locks at 0°, 45°, and 90°, working perfectly as a nut driver for those hard to reach places. The Ultra Socket features a reversible ratchet mechanism making it easier to loosen or tighten any bolt and an ergonomic rubber handle to add comfort and grip.

DESIGN
- Head tilts and locks at 0°, 45° & 90°
- Reversible ratchet mechanism
- Water and impact-resistant
- Ergonomic rubber handle
- Magnetic 1/4" bit holder
- Screwdriver bits stored inside handle

SOCKETS
- Metric: 5mm, 6mm, 7mm, 8mm, 9mm, 10mm, 11mm, 12mm, 13mm
- SAE: 3/16", 1/4", 9/32", 5/16", 11/32", 3/8", 7/16", 15/32", 1/2", 9/16"

BITS
- Phillips: P1-P3
- Slotted: 1/8", 3/16", 1/4"
- Hex: 1/8", 5/32", 7/32"
- Torx: T15, T20 & T25

ACCESSORIES
- 600D Polyester carrying pouch

SPECS
- 1.6 lbs.
- (L) 8" x (W) 1.375"

U.S. PATENT
- 6,634,262 & 6,450,067

Box Dimensions
(H) 8.5" x (W) 3.5" x (D) 1.75"

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397130406	4327	Ultra Socket Combination Kit

NEBO®

Flashlight Holsters

Each NEBO flashlight holster has a pouch made to securely fit an assortment of NEBO flashlights and most other brands as well. The holsters are designed for ***protection, durability and structural strength***.

DESIGN
- Steel belt/pocket clip
- Designed specifically for the SLYDE
- Compatible with flashlights up to 1.5" diameter

WORKS WITH
- #6542 REDLINE Blast
- #6715 PaL+
- #6726 / #6754 SLYDE KING
- #6746 TAC SLYDE
- #6783 / #6797 SLYDE+
- #6775 TWYST Z

DESIGN
- Snap cover
- Hook and loop closure adds backup protection for snap cover
- Snap belt loop
- Pouch is designed to fit most NEBO flashlights, as well as most other brands
- High quality nylon design ensures protection, durability and structural strength

WORKS WITH
- #6542 REDLINE Blast
- #6726 / #6754 SLYDE KING
- #6746 TAC SLYDE
- #6783 / #6797 SLYDE+
- #6775 TWYST Z

DESIGN
- Steel belt/pocket clip
- Designed specifically for the REDLINE BLAST RC
- Compatible with flashlights up to 1.5" diameter

WORKS WITH
- #6542 REDLINE Blast
- #6692 REDLINE BIG DADDY
- #6698 REDLINE BLAST RC

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
645397930181	6274	Flashlight Holster
645397931560	6561	Flashlight Holster
044435918660	6784	Flashlight Holster

WEATHERRITE® SINCE 1941

OLD RED

The Old Red is a 15 LED, 100 lumen lantern that brings classic charm and warm, inviting light to any space. Blending rustic design with modern technology, the Old Red features a ***realistic flickering flame*** and a control to adjust the amount of light that is generated. No smoke and no fire...the Old Red operates for hours on end with 4 AA batteries, which are included.

ADJUSTABLE LIGHT OUTPUT
- *High (100 lumens) - 9 hours / 15 meters*
- *Low - 80 hours*

DESIGN
- Metal construction with wire-guarded glass globe
- Hanging hook
- No fire, realistic flickering flame

BATTERIES
- Powered by 4 AA batteries (included)

SPECS
- 0.9 lbs.
- (H) 9" x (D) 4.5" x (W) 4.5"

Moves just like a real flame!

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
044435917779	6642	Old Red Lantern

WEATHERRITE SINCE 1941

OIL LANTERN

The Oil Lantern captures a classic design and technology that has been around since 1850. This 12" high metal lantern has a wire-guard to protect the glass globe. The fuel tank is 12 oz., which provides ***35 hours of burn time*** on a full tank. The Oil Lantern has a control to adjust the wick height and light output (2 wicks included.) This lantern can be used indoors to provide light during power outages, or to just add a warm glow to any room. Also perfect for outdoor use as well for camping, hunting or any outdoor recreational activity.

DESIGN
- Metal construction with wire-guarded glass globe
- Hanging hook
- 12 oz.. fuel capacity
- 35 hours of burn time
- Adjustable light output
- Uses kerosene, lamp or citronella oil ONLY
- Child-proof fuel tank cap

SPECS
- 1.233 lbs.
- (H) 12" x (D) 5.5" x (W) 7"

ASSORTED COLORS
2 of each color

Black Red

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
044435915393	6048	Oil Lantern

WEATHERRITE SINCE 1941

15 LED LANTERN

This 15 LED Lantern is the perfect blend between classic design and modern technology. This 9" high metal lantern has a wire-guard to protect the glass globe. No kerosene, no lamp oil and no citronella…this 15 LED is completely battery operated (batteries not included.) To maintain the functionality of a traditional kerosene lantern, this 15 LED Lantern has a ***control to adjust the amount of light that is generated***. A reflector is positioned above the LEDs to cast the light evenly in every direction. Perfect for indoor or outdoor use, this lantern generates over 96 hours of continuous bright light. The 15 LED Lantern, the traditional lantern look with efficient LED lighting!

ADJUSTABLE LIGHT OUTPUT
- *High (25 lumens) - 96 hours / 5 meters*

DESIGN
- Metal construction with wire-guarded glass globe
- Hanging hook
- 25 lumens
- 96 hours of continuous light
- Adjustable light output
- Powered by 2 D batteries (not included)

SPECS
- 0.9 lbs.
- (H) 9" x (D) 4.5" x (W) 4.5"



CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

UPC CODE	ITEM	DESCRIPTION
044435627104	5572	15 LED Lantern

TRUE UTILITY®
...IN YOUR POCKET

TRUE UTILITY IS A BRITISH DESIGN AND MANUFACTURING COMPANY THAT CREATES CLEVER AND ORIGINAL PRODUCTS THAT BELONG IN PEOPLE'S POCKETS, GIVING THEM MINIMALISTIC, PRACTICAL SOLUTIONS TO EVERYDAY PROBLEMS.

TU264
FIRESTASH+
- Waterproof housing
- Hidden fire stash
- Refillable with lighter fluid

TU573DSP
SMARTKNIFE
- Folding lock blade
- 5 wrenches, razor cutter, ruler, bottle opener and flat head screwdriver
- Quick release belt clip

TU576
JACKNIFE
- 1.96" folding lock blade
- Hardwood mahogany handle
- Belt/pocket clip

TU579
CLIPSTER
- Stainless steel folding knife
- Handle doubles as money or belt clip

TU6780
KNIFE+
- Fold-out utility knife
- Extra blade storage compartment
- Two 1/4" bits included - #2 Philips and flat head
- Magnetic bit holder

TU181
HANDYMAN
- Pliers, wire cutter, bottle opener, file, knife/serrated blade, saw blade, Philips screwdriver
- 3 Philips, 3 flat, 3 hex bits and bit adapter
- *Durable carry pouch with belt loop*

SEE THE FULL LINE OF POCKET TOOLS, KNIVES, FLASHLIGHTS, LIGHTERS AND ACCESSORIES IN OUR LATEST TRUE UTILITY CATALOG. FOR ADDITIONAL INFORMATION, CATALOG REQUESTS, OR TO PLACE AN ORDER, PLEASE CONTACT YOUR TU SALES MANAGER.

CALL TOLL FREE: 800-255-6061 or VISIT OUR WEBSITE: WWW.TRUEUTILITY.COM

iPROTEC®

iPROTEC branded gun lights, lasers, scopes and accessories are built to the most rigid specifications and featuring the latest in firearm technology. Designed for home security, hunting and the gun enthusiasts alike, we provide the peace of mind that comes with reliability, performance and value.

All iPROTEC products are compact, easy to handle and lightweight, so they won't interfere with the balance and design of the firearm. Expertly designed and meticulously crafted, iPROTEC lights are powered by long-lasting lithium batteries and advanced circuitry to maximize life. With every iPROTEC product, you have our assurance of quality and craftsmanship that match the same standard you expect from your firearms and gear.

Ever-changing and never compromising, we carefully take our products through the entire process - from concept, to manufacturing, to the end consumer. Our greatest reward is the satisfaction of millions of consumers who continue to buy and love iPROTEC products.

LONG GUN LIGHTS

RAIL-MOUNT LIGHTS

SCOPES

FLASHLIGHTS

ACCESSORIES

See the full line of Long Gun Lights, Rail-Mount Lights, Scopes, Flashlights & Accessories in our latest iPROTEC catalog.

For additional information, catalog requests, or to place an order, please contact your NEBO sales manager.

CALL TOLL FREE: 800-255-6061 or VISIT OUR WEBSITE: WWW.iPROTEC.COM

Quarrow®

Quarrow offers a wide variety of products, essential to any angler. We offer fishing rods and reels, digital fishing scales, fishing tools, submersible fishing lights, fishing accessories, and must-haves for the tackle box. Quarrow has the perfect gear for all of your fishing needs.

There's more than one right choice for fishing accessories and gear.
Quarrow just happens to be the BEST choice.

See the full line up of fishing lights, tools and accessories in our latest Quarrow catalog.

For additional information, catalog requests, or to place an order, please contact your NEBO sales manager.

Underwater Fishing Lights

Fishing Tools

Rods & Reels

Digital Fishing Scales

Fishing Accessories

CALL TOLL FREE: 800-255-6061 or VISIT OUR WEBSITE: WWW.QUARROW.COM

Custom Printing and Engraving

NEBO offers custom screen printing and laser engraving services on most all products. Utilize NEBO products to advertise your company or event!

QUANTITY REQUIREMENTS
Custom printing orders must be a minimum of 100 pieces.

LEAD TIME
Allow 15-20 business days for production time.

SHIPPING
All orders ship FOB Fort Worth, TX. Prepaid DOES NOT apply for custom print orders.

PAYMENT
Orders will not be released for printing until payment has been received in full, via credit card or CIA.

LOGO
Orders over 1,000 pieces may have the NEBO and product logos removed.

Top Customer Picks

Laser Engraving

- #6697 REDLINE BLAST RC (pg. 25)
- #6700 REDLINE FLEX (pg. 26)
- #6713/#6798 INSPECTOR (pg. 12)
- #6306 BIG Larry (pg. 21)
- #6373 LiL Larry (pg. 22)

Screen Printing

- #6657 LEO (pg. 24)
- #6327 Larry C (pg. 23)
- #6668 GLOW (pg. 52)
- #6665 TANGO (pg. 39)
- #6555 PoPPY (pg. 49)

Screen Printing Prices

- 100 - 499 pieces = Dealer price + $2.00 per unit
- 500 - 999 pieces = Dealer price + $1.50 per unit
- 1000+ pieces = Dealer price + $1.00 per unit

Laser Engraving Prices

- 100 - 499 pieces = Dealer price + $2.50 per unit
- 500 - 999 pieces = Dealer price + $2.00 per unit
- 1000+ pieces = Dealer price + $1.50 per unit

*There is a one-time $35 fee (per custom print/engrave order), which includes the setup for either screen printing or laser engraving. This setup fee covers the logo/text printed in a single location on the product, using a single color. There is an additional charge for printing or laser engraving on multiple locations or printing in more than one color.

CONTACT YOUR SALES MANAGER FOR ADDITIONAL INFORMATION: 800-255-6061

NEBO® GEAR

NEBO T-Shirt - Screen printed. 50/50 cotton blend. Check for available colors.

NEBO Socks - Cotton socks with embroidered NEBO logo. Set equals 1 pair of each.

NEBO Sports Pack - Drawstring closure and front zipper pocket.

NEBO Tumblers - Double wall 20 & 30 oz. 18/8 stainless steel. Keeps drinks super cold or hot.

NEBO Caps - Cotton Chino cap or mesh back trucker cap. Embroidered logo. Adjustable for all sizes.

UPC CODE	ITEM	DESCRIPTION
645397721666	5115	NEBO T-Shirt (M)
645397721673	5116	NEBO T-Shirt (L)
645397721680	5117	NEBO T-Shirt (XL)
645397721697	5118	NEBO T-Shirt (XXL)
645397930204	6289	NEBO Socks
645397931010	6462-A	NEBO Cap - Red
645397931416	6551-A	NEBO 30 oz. Tumbler
645397931423	6552	NEBO Cap - Brown
645397931430	6553	NEBO Cap - Blue
645397931447	6554	NEBO Cap - Camo
N/A	6711	NEBO Sports Pack
044435918431	6769	NEBO 20 oz. Tumbler

*Styles and colors may vary for caps and t-shirts.

CALIFORNIA REQUIRED ⚠ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov

At NEBO, we like for our customers to **get the most** from their experience with us. These NEBO special giveaway products are our way of saying, **'Thank you!'** Place your order now to get these great giveaway products!

NEBO® GIVEAWAY

$250 Order: (Choose one)
- 1 set* of NEBO Socks
- 1 NEBO Cap (your choice)

$750 Order: (Choose two)
- 1 set* of NEBO Socks
- 1 NEBO Cap
- 1 NEBO Tumbler

$1000 Order: (Choose three)
- 1 set* of NEBO Socks
- 1 NEBO Cap
- 1 NEBO Tumbler
- 1 NEBO Sports Pack

$1500 Order: (YOU GET ALL FOUR!)

GIVEAWAYS

1. #6289 NEBO Socks (White No Show & Black Crew Cut)
   *Set equals 1 pair of each (White and Black)

2. #6462 NEBO Cap - Red (One Size Fits All)
   #6552 NEBO Cap - Brown (One Size Fits All)
   #6553 NEBO Cap - Blue(One Size Fits All)
   #6554 NEBO Cap - Camo (One Size Fits All)

3. #6711 NEBO Sports Pack

4. #6769 NEBO 20 oz. Tumbler

The giveaway offer is valid for qualified orders. The above promotions are valid while supplies last. Actual product style may vary from picture shown. Customer must choose only one applicable giveaway offer per order.

CALL TOLL FREE: 800-255-6061 or VISIT OUR WEBSITE: WWW.NEBOTOOLS.COM

For more information or to place an order, contact your NEBO sales manager.

NEBO®

2019 NEBO Catalog Pricing

UPC CODE	ITEM	NEBO® Tools	DISPLAY	COST	MSRP	CASE PACK	PAGE #
Flashlights and Lighting							
645397929499	6092	REDLINE OC Flashlight	Display	$11.75	$19.99	16 PIECES	33
645397929529	6095	LUMO Clip Light	Display	$2.98	$5.99	48 PIECES	54
645397929864	6157	LUMO Clip Light - Bulk Red	Bulk	$2.70	$5.99	12 PIECES	54
645397929871	6158	LUMO Clip Light - Bulk Silver	Bulk	$2.70	$5.99	12 PIECES	54
645397929888	6159	LUMO Clip Light - Bulk Blue	Bulk	$2.70	$5.99	12 PIECES	54
645397929895	6160	LUMO Clip Light - Bulk Black	Bulk	$2.70	$5.99	12 PIECES	54
645397930167	6272-A	Micro REDLINE OC Flashlight	Display	$7.95	$14.99	16 PIECES	32
645397930341	6304	WORKBRITE 2 C•O•B LED Work Light	Display	$11.95	$19.99	12 PIECES	41
645397930358	6305	The Rechargeable WORKBRITE 2	Display	$17.95	$29.99	12 PIECES	42
645397930365	6306	BIG Larry Power C•O•B LED Work Light	Display	$10.90	$19.99	14 PIECES	21
645397930396	6311	TRANSPORT 12V DC Rechargeable Flashlight	Display	$11.70	$19.99	18 PIECES	55
645397930402	6327	LarryC C•O•B LED Work Light	Display	$4.95	$8.99	24 PIECES	23
645397930464	6350	LarryC C•O•B LED Work Light - Bulk Red	Bulk	$4.75	$8.99	12 PIECES	23
645397930471	6351	LarryC C•O•B LED Work Light - Bulk Blue	Bulk	$4.75	$8.99	12 PIECES	23
645397930488	6352	LarryC C•O•B LED Work Light - Bulk Gray	Bulk	$4.75	$8.99	12 PIECES	23
645397930495	6353	LarryC C•O•B LED Work Light - Bulk Yellow	Bulk	$4.75	$8.99	12 PIECES	23
645397930501	6354	LarryC C•O•B LED Work Light - Bulk Camo	Bulk	$4.95	$8.99	12 PIECES	23
645397930570	6373	LiL Larry C•O•B LED Work Light	Display	$9.50	$16.99	18 PIECES	22
645397930648	6382	BIG Larry C•O•B LED Work Light - Bulk Camo	Bulk	$10.90	$19.99	7 PIECES	21
645397930679	6384	BIG Larry C•O•B LED Work Light - Bulk Black	Bulk	$10.70	$19.99	7 PIECES	21
645397930686	6385	BIG Larry C•O•B LED Work Light - Bulk Silver	Bulk	$10.70	$19.99	7 PIECES	21
645397930754	6392	REDLINE RC with MagDock	Display	$22.50	$39.99	10 PIECES	30
645397930792	6413	BIG LarryC•O•B LED Work Light - Bulk Red	Bulk	$10.70	$19.99	7 PIECES	21
645397930914	6437	CRYKET C•O•B Work Light & Spot Light	Display	$15.50	$24.99	16 PIECES	36
645397930983	6444	DUO 250+ Lumen Head Lamp	Display	$14.25	$24.99	12 PIECES	44
645397931027	6463	LiL Larry - Bulk Red	Bulk	$9.25	$16.99	9 PIECES	22
645397931034	6464	LiL Larry - Bulk Black	Bulk	$9.25	$16.99	9 PIECES	22
645397931041	6465	LiL Larry - Bulk Silver	Bulk	$9.25	$16.99	9 PIECES	22
645397931058	6466	LiL Larry - Bulk Camo	Bulk	$9.50	$16.99	9 PIECES	22
645397931065	6467	TRANSPORT 12V DC Rechargeable Flashlight - Bulk Black	Bulk	$11.50	$19.99	6 PIECES	55
645397931072	6468	TRANSPORT 12V DC Rechargeable Flashlight - Bulk Silver	Bulk	$11.50	$19.99	6 PIECES	55
645397931140	6492	LiL Larry - Bulk Patriotic	Bulk	$9.50	$16.99	9 PIECES	22
645397931157	6493	BIG Larry C•O•B LED Work Light - Bulk Patriotic	Bulk	$10.90	$19.99	7 PIECES	21
645397931256	6526	ARMOR 3 Work Light and Spot Light	Display	$14.25	$24.99	16 PIECES	40
645397931331	6542	REDLINE BLAST 1400 Lumen Flashlight	Display	$22.95	$39.99	12 PIECES	29
645397931393	6549	CRYKET Camo	Bulk	$15.25	$24.99	12 PIECES	36
645397931454	6555	Poppy Lantern & Spot Light	Display	$9.65	$16.99	24 PIECES	49
645397931522	6557	POPLITE Lantern and Flashlight	Display	$3.25	$5.99	48 PIECES	53
645397931539	6558	Contemporary Flipit	Display / Clam	$7.95	$14.99	24 PIECES	48
645397931706	6587	Z-Bug Lantern + Light	Display	$15.00	$24.99	12 PIECES	50
645397931713	6594	Poppy Lantern & Spot Light - Bulk Red	Bulk	$9.65	$16.99	6 PIECES	49
645397931720	6595	Poppy Lantern & Spot Light - Bulk Dark Gray	Bulk	$9.65	$16.99	6 PIECES	49
645397931737	6596	Poppy Lantern & Spot Light - Bulk Yellow	Bulk	$9.65	$16.99	6 PIECES	49
645397931744	6597	Poppy Lantern & Spot Light - Bulk Green	Bulk	$9.65	$16.99	6 PIECES	49
645397931942	6639	REDLINE V 500 Lumen Flashlight	Display	$14.20	$24.99	16 PIECES	28
645397931959	6640	BIG Larry PRO Power Work Light	Display	$20.85	$34.99	12 PIECES	20
645397932031	6651	Poppy Countertop Display	Display	FREE with 12 piece order		1 PIECE	49
645397932086	6657	LEO Work Light and Spot Light	Display	$7.65	$14.99	24 PIECES	24
645397932147	6665	TANGO Rechargeable Work Light & Spot Light	Display	$24.50	$39.99	10 PIECES	39
645397932154	6666	BIG CRYKET C•O•B Work Light & Spot Light	Display	$17.40	$29.99	16 PIECES	35
645397932161	6667	BRITE BUCKET	Display	$10.60	$19.99	12 PIECES	51
645397932178	6668	GLOW Light + Handle	Display	$11.50	$19.99	8 PIECES	52
645397932352	6690	EYE Light	Display / Clam	$9.85	$16.99	16 PIECES	46
645397932369	6691	REBEL 600 Lumen Task Light & Head Lamp	Display	$20.95	$34.99	12 PIECES	43
645397932376	6692	REDLINE BIG DADDY	Display	$28.00	$49.99	8 PIECES	27
645397932390	6694	SLIM Rechargeable Pocket Light	Display	$16.95	$29.99	12 PIECES	14

*Prices are subject to change without notice.

044435918530	6694BLK	SLIM Rechargeable Pocket Light - Bulk Black	Bulk	$16.80	$29.99	12 PIECES	14
044435918561	6694PNK	SLIM Rechargeable Pocket Light - Bulk Pink	Bulk	$16.80	$29.99	12 PIECES	14
044435918547	6694RED	SLIM Rechargeable Pocket Light - Bulk Red	Bulk	$16.80	$29.99	12 PIECES	14
044435918554	6694SIL	SLIM Rechargeable Pocket Light - Bulk Silver	Bulk	$16.80	$29.99	12 PIECES	14
645397932413	6697	REDLINE BLAST RC	Display	$45.75	$79.99	6 PIECES	25
645397932420	6698	REDLINE Select RC	Display	$35.00	$70.00	6 PIECES	31
645397932437	6699	Flipit 400	Display	$7.95	$14.99	24 PIECES	47
645397932444	6700	REDLINE FLEX	Display	$12.45	$21.99	16 PIECES	26
645397932475	6703	REDLINE V 500 Lumen Flashlight - Bulk Black	Bulk	$14.20	$24.99	8 PIECES	28
645397932482	6706	BITBRITE	Display	$5.50	$9.99	24 PIECES	38
645397932512	6713	INSPECTOR	Display	$10.80	$19.99	16 PIECES	12
645397932529	6714	MYCRO	Display	$16.95	$29.99	18 PIECES	18
645397932536	6715	PaL+ Power Bank Flashlight & Knife	Display	$18.40	$32.99	12 PIECES	37
044435917922	6726	SLYDE KING	Display	$23.95	$39.99	12 PIECES	16
645397932642	6727	GLOW Light + Handle	Natralock	$11.50	$19.99	8 PIECES	52
645397932468	6737	BIG Larry 2	Display	$12.75	$24.99	14 PIECES	19
645397933755	6737CAMO	BIG Larry 2 - Bulk Camo	Bulk	$12.75	$24.99	7 PIECES	19
645397933762	6737GRAY	BIG Larry 2 - Bulk Storm Gray	Bulk	$12.50	$24.99	7 PIECES	19
645397933748	6737RED	BIG Larry 2 - Bulk Red	Bulk	$12.50	$24.99	7 PIECES	19
645397932871	6746	TAC SLYDE	Display	$10.60	$19.99	18 PIECES	17
044435917939	6754	SLYDE KING - Bulk Camo	Bulk	$23.95	$39.99	8 PIECES	16
645397933786	6775	TWYST Z Work Light, Flashlight & Lantern	Display	$16.50	$29.99	16 PIECES	34
645397933823	6776	EYE Smart Sensor Light	Display	$15.00	$24.99	16 PIECES	45
645397934141	6776KIT	EYE Light & EYE Smart Sensor Light Combo	Natralock	$18.00	$29.99	12 PIECES	45
645397931249	6783	SLYDE+ Work Light & Flashlight	Display	$17.75	$29.99	16 PIECES	15
645397931935	6797	SLYDE+ Work Light & Flashlight - Bulk Camo	Bulk	$17.95	$29.99	8 PIECES	15
645397933618	6798	INSPECTOR - Bulk Camo	Bulk	$10.95	$19.99	8 PIECES	12
645397933793	6809	TiNO	Display	$8.25	$14.99	24 PIECES	13
645397933809	6810	INSPECTOR RC	Display	$16.75	$29.99	12 PIECES	11
645397935056	6859	SLIM+	Display	$20.20	$34.99	12 PIECES	5 - 6
645397935063	6860	REDLINE X	Display	$22.40	$39.99	12 PIECES	3 - 4
645397935148	6868	Larry TRIO	Display	$17.35	$29.99	12 PIECES	7 - 8
645397935247	6873	CSI Flashlight	Display	$8.70	$14.99	24 PIECES	9 - 10
Tools							
645397130406	4327	Ultra Socket Combination Kit	Box	$14.75	$24.99	12 PIECES	58
645397900504	5517	Folding Lock-Blade Utility Knife with Carabiner	Display/Clam	$5.90	$9.99	18 PIECES	56
645397610113	5606	14-in-1 Ultra Socket	Display	$9.95	$16.99	12 PIECES	57
645397930181	6274	Flashlight Holster	Hang Tag	$4.80	$8.50	16 PIECES	59
645397931560	6561	Flashlight Holster	Hang Tag	$4.80	$8.50	16 PIECES	59
044435918660	6784	Flashlight Holster	Hang Tag	$4.80	$8.50	6 PIECES	59
NEBO Gear							
645397721666	5115	NEBO 'Illuminate Your World' T-Shirt (Medium)	Bulk	$7.50	$14.95	6 PIECES	68
645397721673	5116	NEBO 'Illuminate Your World' T-Shirt (Large)	Bulk	$7.50	$14.95	6 PIECES	68
645397721680	5117	NEBO 'Illuminate Your World' T-Shirt (X-Large)	Bulk	$7.50	$14.95	6 PIECES	68
645397721697	5118	NEBO 'Illuminate Your World' T-Shirt (XX-Large)	Bulk	$7.50	$14.95	6 PIECES	68
645397930204	6289	NEBO Socks	Bulk	$3.10	$5.95	6 PIECES	68
645397931010	6462-A	NEBO Cap - Red	Bulk	$7.00	$14.95	6 PIECES	68
645397931416	6551-A	NEBO 30 oz. Tumbler	Bulk	$9.90	$19.95	6 PIECES	68
645397931423	6552	NEBO Cap - Brown	Bulk	$7.00	$14.95	6 PIECES	68
645397931430	6553	NEBO Cap - Blue	Bulk	$7.00	$14.95	6 PIECES	68
645397931447	6554	NEBO Cap - Camo	Bulk	$7.50	$14.95	6 PIECES	68
N/A	6711	NEBO Sports Pack	Bulk	$5.50	$10.95	6 PIECES	68
044435918431	6769	NEBO 20 oz. Tumbler	Bulk	$7.48	$14.95	6 PIECES	68

UPC CODE	ITEM	WEATHERRITE® Outdoor	DISPLAY	COST	MSRP	CASE PACK	PAGE #
044435627104	5572	15 LED Lantern	Hang Tag	$6.50	$12.99	4 PIECES	62
044435915393	6048	Oil Lanterns (Red & Black)	Hang Tag	$4.50	$8.99	4 PIECES	61
044435917779	6642	Old Red Lantern	Hang Tag	$11.00	$19.99	4 PIECES	60

CALL TOLL FREE: 800-255-6061 or VISIT OUR WEBSITE: WWW.NEBOTOOLS.COM

For more information or to place an order, contact your NEBO® sales manager.