Accent LED 8.5W 35 degree Lndscp 12 AZT

15742AZT (Textured Architectural Bronze)

Project Name: _____
Location: _____
Type: _____
Qty: _____
Comments: _____

Ordering Information

Product ID	15742AZT
Finish	Textured Architectural Bronze
Available Finishes	AZT, BBR, BKT

Specifications

Material	Aluminum
Glass Description	Clear Glass

Electrical

Voltage	12V
Lead Wire Length	24.00"

Qualifications

Safety Rated	Wet
Warranty	www.kichler.com/warranty

Primary Lamping

Light Source	LED
Lamp Included	Integrated
Number of Lights/LEDs	6
Max or Nominal Watt	8.5W

Dimensions

Height	3.50"
Length	2.50"
Width	3.00"

Kichler
7711 East Pleasant Valley Road
Cleveland, Ohio 44131-8010
Toll free: 866.558.5706 or kichler.com

Notes:
1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.

KICHLER