Product Data Sheet

FH36030

Molded Case Circuit Breaker , 600VAC, 30A

List Price	$964.00 USD
Availability	**Stock Item:** This item is normally stocked in our distribution facility.

Technical Characteristics

Frame Type	F-Frame
Circuit Breaker Type	Standard
For Use With	I-Line Panelboards and Switchboards
Marketing Trade Name	Square D
AC Magnetic Trip Setting	600A Fixed Trip (275A Hold)
Ampere Rating	30A
Approvals	UL Listed - CSA Certified
HACR Rated	Yes
Voltage Rating	600VAC
Mounting Type	Plug-On
Weight	5 Pounds
Number of Poles	3-Pole
Short Circuit Current Rating	18000AIR@600VAC
Phase Connection	ABC
Type	FH
Wire Size	(1)#12 to #4 AWG(Al) or (1)#14 to #4 AWG(Cu)
Width	4.50 Inches

Shipping and Ordering

Category	01010 - Circuit Breakers, Thermal Magnetic, 600 Vac, Type FA & FH, UL, I-Line
Discount Schedule	DE2
Article Number	785901241348
Package Quantity	1
Weight	6.36 lbs.
Availability Code	S
Returnability	Y

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.

Generated: 03/16/2009 14:18:26

© 2008 Schneider Electric. All rights reserved.