# High Speed HDMI 2.0 Digital Audio & Video

## VERTICAL CABLE
### Simply Connect.

## DESCRIPTION

HDMI 2.0, Type-A Gold Plated, with Ethernet. 2K/4K - 60Hz Refresh Rate.

## FEATURES

- High speed HDMI Cable
- Gold Plated Contacts, Type-A 19pin
- 18Gbps - UHD 2160P
- 2K/4K - 60Hz Refresh Rate
- UL Listed RoHS Compliant
- HDCP Compliant

## SKU: 242-034/10FT

**Technical Data**

| Connector | 19 Pin Male, Gold Plated (Solder Type) |
|-----------|----------------------------------------|
| Pins | Gold Plated |

**Jacket Construction**

| Material | PVC |
|----------|-----|
| AWG | 30 |
| Diameter | 6.0±0.2mm |
| Color | Black |
| Length | 10ft |
| RoHS Compliant | Yes |

**Electrical Test**

1. 100% Test (open short, miss wire)
2. Contact Resistance: 3 Ohm/M
3. Insulation Resistance: DC200V 10M Ohm
4. Dielectric Strength: 150V AC/Sec, 1mA

**Marking on Jacket**

High Speed HDMI® Cable with Ethernet E258105 AWM STYLE 20276 30AWG 80C 30V VW-1



PIN OUT

## VERTICAL CABLE
### 951.696.7772 California
### 800.749.2447 Florida
### 845.391.8318 New York

### www.verticalcable.com

Rev. 10/2017
Specs subject to change without notice.
It is the sole responsibility of the user to have the most current specs.