**Search Results**

Evaluate
- Advertisements
  - PDF Highest Perf..
- FAQ's
- Product Bulletins
  - PDF Direct Burial..
- Videos
  - WMV Panduit Comp..

Design a Solution
- Catalog Cut Sheet
  - PDF GCE1/0 1/0 P
- Part Drawings
  - DWG 2-D cad for ..
  - PDF E Style Grou..
  - DWG 3-D cad for ..

How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Install & Maintain
- Installation Instructions
  - PDF Direct Burial..

Home > Products Overview > Search Results >

Current refinements (click ☒ to remove) Search Tips

☒ **Text Search: 'GCE250-250'**

**Your search criteria matched only one product, shown below**

## GCE250-250

- Wide range-taking ability and multi-conductor design provide flexibility with a minimum number of parts, allowing for conductor to conductor, conductor to rebar, and conductor to ground rod applications
- Designed for the enhanced crimp process using patent pending technology meets IEEE Std 837™ – 2002
- Slotted design allows quick and easy assembly of conductor to connector using Panduit cable ties, included
- Pre-applied conductive antioxidant compound ensures a high quality mechanical and electrical bond, speeding installation
- Color-coded and marked with Panduit die index numbers for proper crimp die selection
- UL 467 Listed and CSA 22.2 Certified for grounding and bonding suitable for direct burial in earth or concrete when crimped with Panduit or industry standard crimping tools and Panduit dies
- Complies with vibration tests per MIL-STD-202G (METHOD 201A)

| | |
|---|---|
| Part Number | GCE250-250 |
| RoHS Compliancy Status | Compliant |
| Part Description | "E" style grounding connector for 1/0 STR – 250 kcmil (70 – 120mm²) main and tap. |
| CSA Certified | Yes |
| UL Listed | Yes |
| Height (In.) | 2.66 |
| Height (mm) | 67.6 |
| Length (In.) | 1.00 |
| Length (mm) | 25.4 |
| Width (In.) | 1.08 |
| Width (mm) | 27.4 |
| Copper Conductor Size Run | 1/0 STR – 250 kcmil |
| Copper Conductor Size Tap | 1/0 STR – 250 kcmil |
| CE Compliant | No |
| Copper Conductor Size Run (mm²) | (70 – 120) |
| Copper Conductor Size Tap (mm²) | (70 – 120) |
| Copper Lightning Conductor Size Range Run | 65.5 – 131.5 kcmil |
| Ground Rod Size Tap (In.) | 1/2 – 5/8 |
| Panduit Color Code | Black |
| Panduit Die Index No. | PG25 |
| Pricing Description | Ground "E" Style Connector, 1/0 STR-250 kcmil (70-120mm²) main and tap |
| Rebar Size Run (In.) | 3/8 – 1/2, #3 – #4 |
| Rebar Size Tap (In.) | 3/8 – 1/2, #3 – #4 |
| Min. Order UOM | PC |
| Min. Order Qty. | 1 |
| BOM Qty. (# of Pkgs.) | 0 |
| Add to Favorite Product List | |

**Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.**


Copyright © 1995-2011, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy