


6674-P0W



Color:



White

UPC Code: 07847756194

Country Of Origin: China

6674-P0W

Brand Features

Leviton Decora SureSlide® dimmers provide smooth, slide-action, full-range dimming for incandescent and dimmable LED and CFL lamps. Featuring a pre-set ON/OFF switch, this device allows the user to set the desired brightness level to operate automatically with the ON/OFF function. The dimmer is designed specifically for dimmable light-emitting diodes (LED) and dimmable compact fluorescent (CFL) lamps; it is also compatible for use with incandescent lamps.

Item Description

Universal Decora Dimmable LED, CFL and Incandescent SureSlide Slide Dimmer, 600W-120VAC Incandescent, and 150W-120VAC Dimmable LED and CFL, 60Hz, single pole and 3-way. - White

Technical Information

Product Features

Action: Standard ON/OFF

Warranty: 5-Year Limited

Preset: Preset

Color: White

Switch Type: Single-Pole & 3-Way

Load Type: Incandescent, Dimmable LED, Dimmable CFL

Available Colors: Ivory-I Wht- W Blk-E Brwn-B Light Almond-T

Wallplate: Order Separately

Type: Electro-Mechanical

Load Rating: 600W Incandescent, 150W LED and CFL

Light: None

Voltage: 120 VAC

Style Name: SureSlide

Ordering Notes: White

Standards and Certifications: UL/CSA

Protection: Radio/TV Filter

Features and Benefits

- New updated look.
- Integrated linear full-range slide control for easy, precise operation.
- Features a separate ON/OFF switch that preserves the selected brightness setting.
- Single pole or 3-way lighting control when used with a 3-way switch.
- Slim, compact housing fits easily into a standard wallbox and is suitable for multi-gang installations.
- Future-proof to control a variety of dimmable CFL and LED lamps.
- Backwards compatible with incandescent lamps.
- Built-in radio/TV interference filter.
- Available colors: White, Ivory, Light Almond, Black and Brown.

SPECIFICATION SUBMITTAL

JOB NAME: <input type="text"/>	CATALOG NUMBERS: <input type="text"/>	
JOB NUMBER: <input type="text"/>	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2012 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts/

