WAC LIGHTING

Fixture Type:

Catalog Number:

Project:

Location:

Charge 8010

11W H/J/L Track Luminaire

System Type & Voltage	*Model*	*Color Temp & CRI*	*Lumens*	*CBCP*	*Finish*
❍ H-120 VAC ❍ J-120 VAC ❍ L-120 VAC	❍ 8010	❍ 30 3000K - 90	850	1196	❍ BK Black ❍ WT White

Example: **H-8010-30-BK**

DESCRIPTION

The Charge 8010 track luminaire offers superior light output in a small, unobtrusive design. Developed for residential spaces and lower-mounted commercial applications.

FEATURES

- 350° horizontal and 90° vertical aiming
- Driver concealed within the fixture
- 5 year warranty

SPECIFICATIONS

Construction:	Die-cast aluminum with frosted TIR lens
Power:	11W
Input:	120 VAC, 50/60Hz
Dimming:	TRIAC: 100-5%, ELV: 100-5%
Light Source:	Integrated LED 3 Step Mac Adam Ellipse
Lens:	Frosted TIR Lens
Rated Life:	50000 Hours
Finish:	Electrostatically Powder Coated Black, White
Operating Temp:	-4°F to 104°F (-20°C to 40°C)
Standards:	ETL, cETL, Dry Location Listed, Energy Star 2.0, Title 24 JA8-2016 Compliant

FINISHES

Black White

LINE DRAWING