

# 5225



UPC Code: 07847722650

Country Of Origin: Mexico

*\*Eligible for ARRA funded projects > \$7,443,000*



# 5225

## Brand Features

With Leviton's extensive assortment of combination devices, you can fill a one-gang space with two switches, a switch and receptacle, even a switch and GFCI. From sensor guide lights to multi-purpose styles and Tamper-Resistant receptacles, we accommodate your every need. These devices come in a range of colors and are backed by a limited two-year warranty. Built to last and designed to save space, these attractively styled devices are at home in any setting.

## Item Description

15 Amp, 120 Volt, Duplex Style Single-Pole / 5-15R AC Combination Switch, Commercial Grade, Grounding, Side Wired, - Brown

## Technical Information

### AC Horsepower Ratings

**Max. Amperage:** 12 Amp

**HP Rating:** 1/2HP-120V

### Electrical Specifications

**Dielectric Voltage:** Withstands 1500V for 1 minute

**Grounding:** Grounding

**Switch Voltage:** 120V AC

**Overload UL20 Test:** 100 cycles of OL at 4.8 times rated current

**Temperature Rise:** Maximum 30 degrees C rise

**Receptacle Amperage:** 15 Amp

**Receptacle Voltage:** 125V AC

**Switch Amperage:** 15 Amp

### Environmental Specifications

**Operating Temperature:** -40°C to 65°C

**Flammability:** Rated V-2 per UL94

### Material Specifications

**Strap Material:** Steel

**Body Material:** Thermoplastic

**Color:** Brown

**Actuator Material:** Thermoplastic

### Mechanical Specifications

**Product ID:** Stamped on Strap

**Terminal ID:** Brass-Hot Black-Hot White-Neutral Green-Gnd

**Termination:** Side

**Terminal Accom.:** 14-12 AWG

**Torque Range:** 12-14 inch pounds

### Product Features

**Warranty:** 2 Year Limited

**Voltage:** 120 Volt

**Color:** Brown

### Standards and Certifications

**CSA C22.2 No. 111:** File #152105

**Warranty:** 2 Year Limited


**UL Standard:** UL 20

**ANSI:** C-73

**NOM:** 057

**NEMA:** WD-1 & WD-6

## Dimensional Diagram



### SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

#### Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

#### Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

#### Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

#### Visit our Website at: [www.leviton.com](http://www.leviton.com)

© 2012 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

#### Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

[www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)



*\*Leviton is the smart choice, providing the most comprehensive range of solutions to meet the needs of today's residential, commercial and industrial buildings. Leveraging more than a century of experience, Leviton helps customers create sustainable, intelligent environments through its electrical wiring devices, network and data center connectivity solutions, and lighting energy management systems. From switches and receptacles, to daylight harvesting controls, networking systems, and equipment for charging electric vehicles, Leviton solutions help customers achieve savings in energy, time and cost, all while enhancing safety.*