

## Largest line of colors available



### Gloss colors:

- S  White (WH)
- S  Ivory (IV)
- S  Almond (AL)
- S  Light Almond (LA)
- S  Gray (GR)
- S  Brown (BR)
- S  Black (BL)






### Satin Colors®:

- Hot (HT)
- Merlot (MR)
- Plum (PL)
- Turquoise (TQ)
- Sea Glass (SG)
- Midnight (MN)
- Sienna (SI)
- Terracotta (TC)
- Greenbriar (GB)
- Bluestone (BG)
- Taupe (TP)
- Eggshell (ES)
- Biscuit (BI)
- Snow (SW)
- Palladium (PD)
- Mocha Stone (MS)
- Goldstone (GS)
- Desert Stone (DS)
- Stone (ST)
- Limestone (LS)

### Availability

- S  = Stock items, ship in 2 days
- = Satin Colors, ship in 2–10 days

## Ordering information — C·L® dimmers

	Model number	Specifications	Voltage
 Ariadni®	AYCL-153P-XX*	3-way/single pole 150W dimmable CFL/LED, 600W incandescent/halogen	120V~
 Skylark®	SCL-153P-XX*	3-way/single pole 150W dimmable CFL/LED, 600W incandescent/halogen	120V~
 Skylark Contour®	CTCL-153P-XX*	3-way/single pole 150W dimmable CFL/LED, 600W incandescent/halogen	120V~
 Diva®	DVCL-153P-XX* DVSCCL-153P-YY*	3-way/single pole 150W dimmable CFL/LED, 600W incandescent/halogen	120V~
 Maestro®	MACL-153M-ZZ*	muti-location/3-way/single pole 150W dimmable CFL/LED, 600W incandescent/halogen	120V~

3-way dimmers work with mechanical 3-way switches

Multi-location dimmers work with up to nine companion dimmers

\* XX denotes gloss color suffix (above)

\* YY denotes Satin Color Suffix (above)

\* ZZ denotes gloss or Satin Color Suffix (above)

[www.lutron.com/dimcflled](http://www.lutron.com/dimcflled)

World Headquarters 1.610.282.3800

Technical Support Center 1.800.523.9466 (Available 24/7)

Customer Service 1.888.588.7661



NEW

# Lutron C·L<sup>®</sup> dimmers

Solve the challenges of light bulb compatibility



NEW Maestro C·L dimmer



Ariadni<sup>®</sup> C·L dimmer

- **C·L technology provides superior dimming**
  - Works with dimmable LED, compact fluorescent (CFL), and standard incandescent/halogen bulbs — **even mixed on the same circuit**
  - Highest-performance dimming minimizes problems like flicker, shimmer, and pop-on seen with other dimmers
- **Works with largest selection of light bulbs**
  - Tested and UL Listed to control over 250 LED and CFL bulbs
  - View the full list at [www.lutron.com/bulblast](http://www.lutron.com/bulblast)
- **Available in 5 styles and 27 colors!**



Ariadni<sup>®</sup>



Skylark<sup>®</sup>



Skylark Contour<sup>®</sup>



Diva<sup>®</sup>



Maestro<sup>®</sup>

## Check out our videos:

- Why C·L?
- Easy installation



## For more information:

[www.lutron.com/dimcflled](http://www.lutron.com/dimcflled)

## Order now:

Contact your local electrical distributor

































# Save time and money: Lutron offers one reliable dimmer for all dimmable light bulbs

## Lutron C·L® technology means no callbacks

Only Lutron C·L dimmers alleviate the challenges of controlling today's new light bulbs

### LED and CFL Dimmer Performance Comparison

	Company A	Company B	Company C	Company D	Lutron
Large list of compatible bulbs					
Large dimming range					
Minimizes flicker, shimmer, pop-on					
Ease of adjustment					
Tolerates power line noise					
Quiet – low dimmer noise					

For testing methods see  
[www.lutron.com/CLtest713](http://www.lutron.com/CLtest713)

 Poor

 OK

 Excellent

## Lutron performance and support

- **The Lutron LED Control Center of Excellence** is the industry resource for LED light bulb compatibility information call **1.877.DIM.LED8**, email **LEDS@lutron.com**, or visit **www.lutron.com/LED**
- Patent-pending technology ensures superior performance for hundreds of LED and CFL bulb models
- **24/7 live technical support 1.800.523.9466**
- Delivers reliable, consistent performance with dimmable LED and CFL light bulbs, as well as standard incandescent and halogen bulbs



LED



CFL



Incandescent/halogen

# Product information



---

## Lutron performance

- HED™ (High Efficacy Dimming) microprocessor technology means compatibility with the broadest range of light bulbs.
- UL Listed to dim over 250 different LED and CFL light bulbs. The bulb list is available at [www.lutron.com/bulblast](http://www.lutron.com/bulblast).

## Light bulb compatibility

■ = unique LED or CFL bulb model type



## Lutron reliability

- Offers superior light stability and easy low-end adjustment
- Works with 60° C rated wire found in older homes
- Reliable long-life performance — designed to last 10 years

## C-L dimmers available in a range of styles and colors

- All dimmers are 3-way/single pole



Ariadni®  
in White



Skylark®  
in Ivory



Skylark Contour®  
in Black



Diva®  
in Sea Glass



Maestro®  
in Terracotta