

BRASSGUARD® LANTERNS

Unique, clear lacquer applied for long-lasting finish. All-brass construction includes protective gasket to reduce staining on siding. Black fixtures utilize aluminum construction with clear lacquer coating.

FINISHES

- Brushed Nickel - 09
- Polished Brass - 10
- Black - 31

LARGE LANTERNS

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5432-10 P5432-31	Polished Solid Brass Black	Post lantern Fits 3" post (order separately).	9-1/2" dia., 21" ht.	3 candelabra base, each 60w max.
P5730-10	Polished Solid Brass	Wall lantern	9-1/2" W., 26" ht. Extends 9-1/2". H/CTR 20-1/4".	3 candelabra base, each 60w max.
P5731-31	Black	Wall lantern	9-1/2" W., 35" ht. Extends 9-1/2". H/CTR 20-1/2".	3 candelabra base, each 60w max.



MEDIUM LANTERNS

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5430-10	Polished Solid Brass	One-light post Fits 3" post (order separately).	7" dia., 17" ht.	1 medium base, 100w max.
P5831-31	Black	One-light wall lantern	7" W., 29" ht. Extends 6-3/4". H/CTR 15-3/8".	1 medium base, 100w max.
P5832-10	Polished Solid Brass	One-light wall lantern	7" W., 14-1/4" ht. Extends 7". H/CTR 5-3/8".	1 medium base, 100w max.
P5834-10	Polished Solid Brass	One-light hanging lantern. Chain and ceiling mounts both included.	7" dia., 10" ht. Overall ht. w/chain 39-1/2"; wire 10'.	1 medium base, 100w max.



SMALL LANTERNS

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5756-09 P5756-10 P5756-31	Brushed Nickel Polished Solid Brass Black	One-light wall lantern. Open bottom.	5-1/2" W., 10-1/4" ht. Extends 5-3/4". H/CTR 3-3/4".	1 medium base, 100w max.
P5758-31	Black	One-light wall lantern	5-1/2" W., 18-3/4" ht. Extends 5-5/8". H/CTR 7-1/4".	1 medium base, 100w max.
P5846-31	Black	One-light wall lantern	5-1/4" W., 14-3/4" ht. Extends 6". H/CTR 8-3/8".	1 medium base, 60w max.

