

# Panelboards

## A-Series™ II Panelboards

### Pro-Stock, Unassembled Lighting Panels

## Section 11

### 2 Select Box

Select a box of the correct height (see Step 1). Boxes come with blank endwalls. If endwalls with knockouts are required, also order knockout endwall kit AKEW2.

| Box Height | NEMA 1                               |                                      | NEMA 3R/12                           |
|------------|--------------------------------------|--------------------------------------|--------------------------------------|
|            | 20" Wide Product Number <sup>1</sup> | 30" Wide Product Number <sup>1</sup> | 20" Wide Product Number <sup>1</sup> |
| 31.5"      | AB31B                                | AB31BW                               | AB313                                |
| 37.5"      | AB37B                                | AB37BW                               | AB373                                |
| 43.5"      | AB43B                                | AB43BW                               | AB433                                |
| 49.5"      | AB49B                                | AB49BW                               | AB493                                |
| 64.5"      | AB64B                                | AB64BW                               | AB643                                |
| 76.5"      | AB76B                                | AB76BW                               | AB763                                |

<sup>1</sup>For CSA label, add "A" suffix to product number.



NEMA 1



NEMA 3R/12

### 3 Select Front

Select a front of the correct height (see Step 1).

| Front Height | Standard (20" wide) |                      | Door Within Door (20" wide) |                      | Front Hinged To Box (20" wide) |                      | Standard (30" Wide) |                      |
|--------------|---------------------|----------------------|-----------------------------|----------------------|--------------------------------|----------------------|---------------------|----------------------|
|              | Flush <sup>1</sup>  | Surface <sup>1</sup> | Flush <sup>1</sup>          | Surface <sup>1</sup> | Flush <sup>1</sup>             | Surface <sup>1</sup> | Flush <sup>1</sup>  | Surface <sup>1</sup> |
| 31.5"        | AF31F               | AF31S                | AF31FP                      | AF31SP               | AF31FD                         | AF31SD               | AF31FW              | AF31SW               |
| 37.5"        | AF37F               | AF37S                | AF37FP                      | AF37SP               | AF37FD                         | AF37SD               | AF37FW              | AF37SW               |
| 43.5"        | AF43F               | AF43S                | AF43FP                      | AF43SP               | AF43FD                         | AF43SD               | AF43FW              | AF43SW               |
| 49.5"        | AF49F               | AF49S                | AF49FP                      | AF49SP               | AF49FD                         | AF49SD               | AF49FW              | AF49SW               |
| 64.5"        | AF64F               | AF64S                | AF64FP                      | AF64SP               | AF64FD                         | AF64SD               | AF64FW              | AF64SW               |
| 76.5"        | AF76F               | AF76S                | AF76FP                      | AF76SP               | AF76FD                         | AF76SD               | AF76FW              | AF76SW               |

<sup>1</sup>For CSA label, add "A" suffix to product number.



Door Within Door



Standard



Front Hinged to Box

