

Load Centers and Circuit Breakers

Special Purpose Circuit Breakers

Section 1

60°C / 75°F Conductor Rating

Box Type Terminals

Quick-Make, Quick-Break

Multi-pole Breakers Incorporate Internal Common Trip

PowerMark Gold Main Circuit Breakers for use with 150A-225A PowerMark Gold Load Centers (Includes mounting base)

UL Listed.

Description	Ampere Rating	Product Number
Main Circuit Breaker Kits 22,000 AIC	100	THQMV100D
	125	THQMV125D
	150	THQMV150D
	175	THQMV175D
	200	THQMV200D
	225	THQMV225D



THQMVXXXD

PowerMark Gold Main Circuit Breaker Kit

For use with 125A PowerMark Gold load Centers; 22kAIC RMS symmetrical.

Description	Product Number
Main Circuit Breaker Kit - Order appropriate THQL 10kAIC or THHQL 22kAIC breakers separately	TQMH000 ¹

¹Do not use with TLM1212CCU

Arc Fault⁴

UL Listed

Arc-Fault Circuit Interrupters No. 1699


Ampere Rating	1-Pole, 120/240 Volts ac ²	1 Pole, 120/240 Volts ac ³
	Product Number	Product Number
10,000 AIC	15	THQL1115AF
	20	THQL1120AF
		THQL1115AF2
22,000 AIC	15	THHQL1115AF
	20	THHQL1120AF
		THHQL1115AF2
Std. Pkg.	20 Cartons of 1	10 Cartons of 1

As of Jan. 1, 2008, 2005 NEC[™] requires combination AFCI.

²Branch/feed AFCI compliant with 2002 NEC[™] or earlier

³Combination AFCI compliant with 2005 and 2008 NEC[™] and UL1699 (Feb. 2008)

⁴For 2-Pole shared neutral applications use two 1-pole circuit breakers with a handle tie. See DET-719 for more details on our Arc Fault products.



TQMH000



Arc Fault

Ground Fault

UL Listed

Ground Fault Circuit Interrupters No. 943.

Class A (5 milliamperes ground fault trip level).

No. 943 Ampere Rating	1-Pole, 120 Volts ac	2-Pole, 120/240 Volts ac
	Product Number	Product Number
10,000 AIC	15	THQL1115GF
	20	THQL1120GF
	30	THQL1130GF
	40	-
	50	-
22,000 AIC	15	THHQL1115GF
	20	THHQL1120GF
	30	THHQL1130GF
Std. Pkg.	10 cartons of 1	10 cartons of 1



THQL1120GF

Ground Fault Self Testing⁵

UL943 Ed5 (5 milliamperes residential) and 10mA

Ampere Rating	1-Pole, 120 Volts ac	2-Pole, 120/240 Volts ac
	Product Number	Product Number
10,000 AIC	15	THQL1115GF3
	20	THQL1120GF3
	30	THQL1130GF3
22,000 AIC	15	THHQL1115GF3
	20	THHQL1120GF3
	30	THHQL1130GF3
Std. Pkg.	10	10

⁵Check for availability

