


Lytecaster CFL 6 3/4", Horizontal Open, Performance Series, Reflector Trim

Page 1 of 2


Project:	Catalog No:	Mfg:
Location:	Fixture Type:	Qty:
Notes:		Lamps:



1101HCL/1101F Series
Uniframe CFL



1101HCL/1101HIDED Series
Uniframe HID



Complete Fixture consists of Frame-In Kit and Reflector Trim. Select each separately.

Uniframe Performance Series Reflector Trims		Compatible Compact Fluorescent Frame-In Kits (See Individual Frame-In Kit Specification Sheets)		
Catalog No.	Description	Catalog No.	Installation Type	Lamping
1101HCL 1101HCD 1101HWH*	6-3/4" Horizontal Open Downlight – Specular Clear 6-3/4" Horizontal Open Downlight – Clear Diffuse 6-3/4" Horizontal Open Downlight – Matte White	1101F18U 1101FR18U	Uniframe Non-IC 120/277v Uniframe Non-IC Remodeler 120/277v	18w Quad/Triple
		1101FD32L1 1101FD32L2	Uniframe Non-IC Lutron Dimming 120v Uniframe Non-IC Lutron Dimming 277v	32w Triple
		1101F2642U 1101FR2642U 1101F2642UEM 1101FD2642MX1 1101FD2642MX2 1101FD2642M7U 1101FR264MX1 1101FR264MX2	Uniframe Non-IC 120/277v Uniframe Non-IC Remodeler 120/277v Uniframe Non-IC Emergency 120/277v Uniframe Non-IC Advance Mark10 Dimming 120v Uniframe Non-IC Advance Mark10 Dimming 277v Uniframe Non-IC Advance Mark7 Dimming 120/277v Uniframe Non-IC Advance Mark10 Dimming 120v Rem. Uniframe Non-IC Advance Mark10 Dimming 277v Rem.	26w Quad/Triple 32w Triple 42w Triple
		1101F18ICU/N	Performance IC 120/277v	18w Quad/Triple
		1101F2642ICU 1101F2642IUN	Performance IC 120/277v	26w Quad/Triple 32w Triple 42w Triple
		1101FDICMX1/N	Performance IC Advance Mark10 Dimming 120v	26w Quad/Triple 32w Triple
		1101FDICMX2/N	Performance IC Advance Mark10 Dimming 277v	26w Quad/Triple 32w Triple

* Not listed for HID.


Features

- Reflector:** Formed aluminum. Matte White flange.
- Finishes:** CL = Specular Clear (Iridescent Free coating)
CD = Clear Diffuse
WH = Matte White Paint
- Performance Data:** 60° Cutoff angle.
See attached photometric reports for distribution and efficiency data.
Go to www.lightolier.com for .IES files.

Labels

cULus Listed. Suitable for Damp Locations. I.B.E.W.

Lytecaster CFL 6 3/4", Horizontal Open, Performance Series, Reflector Trim

32W TRIPLE TUBE LAMP, LUMEN RATING = 2200 LMS, ELECTRONIC BALLAST, CL FINISH TRIM**100W ED-17 COATED METAL HALIDE**, LUMEN RATING = 7900 LMS, CL FINISH TRIM