

EasyHeat, your industry leader in pipe freeze prevention and roof and gutter deicing applications, introduces PSRTM pre-terminated self-regulating heating cable. Imagine the convenience: each PSR cable is a pre-terminated, off the shelf product with the efficiency and functionality of self-regulating technology. With this built-in application flexibility, PSR becomes a first-choice solution for your heat tracing needs.

The PSR system can be installed with the confidence that it will operate satisfactorily for years. When it comes to freeze protection, stay with the leader—EasyHeat.



Each PSR cable is pre-assembled for quick selection and easy installation. Select from lengths of 6′, 12′, 18′, 24′, 50′, 75′ and 100′ right off the shelf. All cables have a 30" cold lead. PSR accommodates water pipe diameters from ½" to 2½". For roof and gutter areas, usually one PSR cable will be sufficient. PSR 120 Vac heating cables have a power indicator light in the plug, visual assurance that the system is energized.

Using self-regulating technology, a thermostat is not usually required; the cable can be overlapped if necessary. Self regulating heating cable varies its heat output in relation to the ambient temperature. As the surrounding temperature increases, the heat output of the PSR cable decreases. But when the temperature decreases, the cable heat output increases and provides the heat needed along the length of the cable.



- Prevent water pipes from freezing
- Prevent the formation of ice dams on roof tops
- Suitable for use on metal and plastic pipes, such as pvc or polybutylene, up to $2\frac{1}{2}$ " in diameter
- Self-regulating heating cable means energy efficiency
- 120 & 240 Vac
- Pilot light in the plug on 120 Vac

PSR 120 VOLT CABLE

	ITEM #	DESCRIPTION	CTN QTY	CTN WT	UPC
CUL LISTED	PSR 1006	6' Length, 30 Watts*	5	4.08	0-13627-06907-7
	PSR 1012	12' Length, 60 Watts*	5	6.78	0-13627-06908-4
	PSR 1018	18' Length, 90 Watts*	5	8.62	0-13627-06913-8
	PSR 1024	24' Length, 120 Watts*	5	10.44	0-13627-06909-1
	PSR 1050	50' Length, 250 Watts*	5	18.36	0-13627-06910-7
	PSR 1075	75' Length, 375 Watts*	5	11.20	0-13627-06911-4
	PSR 1100	100' Length, 500 Watts*	5	14.08	0-13627-06912-1

PSR 240 VOLT CABLE

	ITEM #	DESCRIPTION	CTN QTY	CTN WT	UPC
C UL LISTED	PSR 2006	6' Length, 30 Watts*	5	3.88	0-13627-06867-4
	PSR 2012	12' Length, 60 Watts*	5	6.88	0-13627-06868-1
	PSR 2018	18' Length, 90 Watts*	5	8.48	0-13627-06873-5
	PSR 2024	24' Length, 120 Watts*	5	10.60	0-13627-06869-8
	PSR 2050	50' Length, 250 Watts*	5	17.80	0-13627-06870-4
	PSR 2075	75' Length, 375 Watts*	5	10.92	0-13627-06871-1
	PSR 2100	100' Length, 500 Watts*	5	13.98	0-13627-06872-8

^{*} Wattage rated at 50°F