

Group metering tenant main circuit breaker cross-reference tables

A complete list of standard tenant main circuit breakers showing previous and new part numbers is shown in the following tables.

Commercial Meter Stacks												
Description	Number of Poles	Tenant Main Circuit Breaker Ampere Rating	10 kAIC		25 kAIC		42 kAIC		65 kAIC		100 kAIC	
			Previous Catalog Number	New Catalog Number ⑥⑥	Previous Catalog Number	New Catalog Number ①②	Previous Catalog Number	New Catalog Number ①②	Previous Catalog Number	New Catalog Number ①②	Previous Catalog Number	New Catalog Number ①②
Bolt-on type circuit breakers used with 35MM and 35SS (single-phase modular metering stacks) ⑤	2	60	EHD2060	EHD2060	CHH2060H2X	CVS2060XMM	CHH2060H4X	CVS2060XMM	—	CV2060XMM	CHH2060X	CVH2060XMM
	2	70	EHD2070	EHD2070	CHH2070H2X	CVS2070XMM	CHH2070H4X	CVS2070XMM	—	CV2070XMM	CHH2070X	CVH2070XMM
	2	80	EHD2080	EHD2080	CHH2080H2X	CVS2080XMM	CHH2080H4X	CVS2080XMM	—	CV2080XMM	CHH2080X	CVH2080XMM
	2	90	EHD2090	EHD2090	CHH2090H2X	CVS2090XMM	CHH2090H4X	CVS2090XMM	—	CV2090XMM	CHH2090X	CVH2090XMM
	2	100	CCV2100X	CCV2100X	CHH2100H2X	CCVH2100X	CHH2100H4X	CVS2100XMM	—	CV2100XMM	CHH2100X	CVH2100XMM
	2	125	CCV2125X	CCV2125X	CHH2125H2X	CCVH2125X	CHH2125H4X	CVS2125XMM	—	CV2125XMM	CHH2125X	CVH2125XMM
	2	150	CCV2150X	CCV2150X	CHH2150H2X	CCVH2150X	CHH2150H4X	CVS2150XMM	—	CV2150XMM	CHH2150X	CVH2150XMM
	2	175	CCV2175X	CCV2175X	CHH2175H2X	CCVH2175X	CHH2175H4X	CVS2175XMM	—	CV2175XMM	CHH2175X	CVH2175XMM
	2	200	CCV2200X	CCV2200X	CHH2200H2X	CCVH2200X	CHH2200H4X	CVS2200XMM	—	CV2200XMM	CHH2200X	CVH2200XMM
2	225	CCV2225X	CCV2225X	CHH2225H2X	CCVH2225X	CHH2225H4X	CVS2225XMM	—	CV2225XMM	CHH2225X	CVH2225XMM	
Bolt-on type circuit breakers used with 37MM and 37SS (three-phase modular metering stacks) ⑤	3	60	EHD3060	EHD3060	CHH3060H2X	CVS3060X	CHH3060H4X	CVS3060X	—	CV3060X	CHH3060	CVH3060X
	3	70	EHD3070	EHD3070	CHH3070H2X	CVS3070X	CHH3070H4X	CVS3070X	—	CV3070X	CHH3070	CVH3070X
	3	80	EHD3080	EHD3080	CHH3080H2X	CVS3080X	CHH3080H4X	CVS3080X	—	CV3080X	CHH3080	CVH3080X
	3	90	EHD3090	EHD3090	CHH3090H2X	CVS3090X	CHH3090H4X	CVS3090X	—	CV3090X	CHH3090	CVH3090X
	3	100	CC3100X	CC3100X	CHH3100H2X	CVS3100X	CHH3100H4X	CVS3100X	—	CV3100X	CHH3100	CVH3100X
	3	125	CC3125X	CC3125X	CHH3125H2X	CVS3125X	CHH3125H4X	CVS3125X	—	CV3125X	CHH3125	CVH3125X
	3	150	CC3150X	CC3150X	CHH3150H2X	CVS3150X	CHH3150H4X	CVS3150X	—	CV3150X	CHH3150	CVH3150X
	3	175	CC3175X	CC3175X	CHH3175H2X	CVS3175X	CHH3175H4X	CVS3175X	—	CV3175X	CHH3175	CVH3175X
	3	200	CC3200X	CC3200X	CHH3200H2X	CVS3200X	CHH3200H4X	CVS3200X	—	CV3200X	CHH3200	CVH3200X
3	225	CC3225X	CC3225X	CHH3225H2X	CVS3225X	CHH3225H4X	CVS3225X	—	CV3225X	CHH3225	CVH3225X	

Residential Meter Packs and Meter Stacks

Description	Number of Poles	Tenant Main Circuit Breaker Ampere Rating	10 kAIC		22 kAIC		25 kAIC		42 kAIC		65 kAIC		100 kAIC	
			Previous Catalog Number	New Catalog Number ⑥	Previous Catalog Number	New Catalog Number	Previous Catalog Number	New Catalog Number ①②③④	Previous Catalog Number	New Catalog Number ①②③	Previous Catalog Number	New Catalog Number ①②③	Previous Catalog Number	New Catalog Number ①②③
Plug-on type circuit breakers used with 1MP, 1MM and 3MM 125 ampere modular metering stacks	2	60	BR260	BR260	BRH260	BRH260	—	—	BRHH260	BRHH260	—	BRX260	—	—
	2	70	BR270	BR270	BRH270	BRH270	—	—	BRHH270	BRHH270	—	BRX270	—	—
	2	80	BR280	BR280	BRH280	BRH280	—	—	BRHH280	BRHH280	—	BRX280	—	—
	2	90	BR290	BR290	BRH290	BRH290	—	—	BRHH290	BRHH290	—	BRX290	—	—
	2	100	BR2100	BR2100	BRH2100	BRH2100	—	—	BRHH2100	BRHH2100	—	BRX2100	—	—
	2	110	BR2110	BR2110	BRH2110	BRH2110	—	—	BRHH2110	BRHH2110	—	BRX2110	—	—
	2	125	BR2125	BR2125	BRH2125	BRH2125	—	—	BRHH2125	BRHH2125	—	BRX2125	—	—
Bolt-on type circuit breakers used with 1MP, 1MM and 3MM 200 ampere modular metering stacks	2	60	—	—	—	—	CHH2060H2X	CVS2060XMM	CHH2060H4X	CVS2060XMM	—	CV2060XMM	CHH2060X	CVH2060XMM
	2	70	—	—	—	—	CHH2070H2X	CVS2070XMM	CHH2070H4X	CVS2070XMM	—	CV2070XMM	CHH2070X	CVH2070XMM
	2	80	—	—	—	—	CHH2080H2X	CVS2080XMM	CHH2080H4X	CVS2080XMM	—	CV2080XMM	CHH2080X	CVH2080XMM
	2	90	—	—	—	—	CHH2090H2X	CVS2090XMM	CHH2090H4X	CVS2090XMM	—	CV2090XMM	CHH2090X	CVH2090XMM
	2	100	CCV2100X	CCV2100X	—	—	CHH2100H2X	CCVH2100X	CHH2100H4X	CVS2100XMM	—	CV2100XMM	CHH2100X	CVH2100XMM
	2	125	CCV2125X	CCV2125X	—	—	CHH2125H2X	CCVH2125X	CHH2125H4X	CVS2125XMM	—	CV2125XMM	CHH2125X	CVH2125XMM
	2	150	CCV2150X	CCV2150X	—	—	CHH2150H2X	CCVH2150X	CHH2150H4X	CVS2150XMM	—	CV2150XMM	CHH2150X	CVH2150XMM
2	175	CCV2175X	CCV2175X	—	—	CHH2175H2X	CCVH2175X	CHH2175H4X	CVS2175XMM	—	CV2175XMM	CHH2175X	CVH2175XMM	
2	200	CCV2200X	CCV2200X	—	—	CHH2200H2X	CCVH2200X	CHH2200H4X	CVS2200XMM	—	CV2200XMM	CHH2200X	CVH2200XMM	

Blue indicates previous catalog numbers.

Green indicates new catalog numbers.

- ① "MM" suffix indicates mounting hardware kit is included as standard with the breaker. Needed for 200 ampere 1MP, 1MM and 3MM modular metering stacks only. Mounting hardware not needed for 35MM and 37MM modular metering stacks.
- ② #6–4/0 kcmil wire size range for CVS, CV and CVH standard for breakers. If #2–300 kcmil is needed, order 2TA225CVK (two-pole) or 3TA225CVK (three-pole). One kit needed per breaker.
- ③ #2–300 kcmil wire size range for Type CCV and Type CCVH tenant main circuit breakers.
- ④ 1MMCBK replacement mounting hardware kit. One kit needed per breaker. Mounting hardware kit ships standard with breaker "MM" suffix offering.
- ⑤ 37MMRCBK—Retrofit mounting hardware for installation of Type EHD and Type CV breakers in commercial meter stacks manufactured prior to February 2013. Order one kit per breaker.
- ⑥ Type EHD breakers also available from 15 to 50 amperes.