

Electrical Markets

3M™ ScotchCode™ Wire Marking and Identification System



Quality Marking

For Most Projects



Dispensers

3M™ ScotchCode™ Dispenser STD-TAG

The proprietary 3M™ ScotchCode™ Dispenser STD-TAG simplifies the process of permanently or temporarily marking wires with ScotchCode wire marker tags. The dispenser allows easy printing of the tag with a permanent marking pen. A built-in blade quickly and neatly cuts the marker. The STD-TAG dispenser is refillable. The tags are available in two sizes.



Specifications and Ordering Information for 3M™ ScotchCode™ Write-On Dispensers

Product Number	UPC (054007-)	Labels Per Roll	Write-On Area		Marker Size		Recommended Wire Size	Case Qty.
			A	B	A	B		
STD-TAG	50345	—	—	—	—	—	—	10*
STD-101	50347	50	1.53" (38,9 mm)	0.375" (61,0 mm)	2.40" (60,96 mm)	0.375" (9,53 mm)	18–10 AWG (0,75–4,0 mm²)	10
STD-102	50346	70	0.86" (21,84 mm)	0.250" (6,35 mm)	1.60" (40,6 mm)	0.250" (6,35 mm)	22–14 AWG (0,5–1,5 mm²)	10
SMP Marker Pen	09963	—	—	—	—	—	—	50

* This case quantity is 10 sets of: 1 STD-TAG, 1 STD-101, 1 STD-102, and 1 SMP pen.

3M™ ScotchCode™ Write-On Dispensers

These three self-laminating writeon marker dispensers are handy for identifying wire and cable as well as household, automotive, plumbing and sporting equipment.




Specifications and Ordering Information for 3M™ ScotchCode™ Write-On Dispensers

Product Number	UPC (054007-)	Description	Labels Per Roll	Write-On Area		Marker Size		Recommended Wire O.D.	Inner Unit Pack	Case Qty.
				A	B	A	B			
SLS	49653	Dispenser with tape and SMP pen	170	1" (25 mm)	0.5" (13 mm)	1" (25 mm)	2.125" (54 mm)	0.15 x 0.49 (3,8 x 12,4 mm)	1/card	10
SLS-R	49652	Refill roll for SLS	—	—	—	—	—	—	1/card	10
SLW	12177	Dispenser with tape and SMP pen	70	1" (25 mm)	0.75" (19 mm)	1" (25 mm)	5" (127 mm)	0.23 x 1.32 (5,8 x 35,5 mm)	1/card	10
SLW-R	49651	Refill roll SLW	—	—	—	—	—	—	1/card	10
SWD	11954	Dispenser with tape and SMP pen	50	0.75" (19 mm)	0.312" (8 mm)	0.75" (19 mm)	1.375" (35 mm)	0.09 x 0.31 (2,3 x 7,8 mm)	1/card	10
SWD-R	12201	Refill roll for SWD	—	—	—	—	—	—	1/card	10

3M™ ScotchCode™ Tape Dispenser STD

The 3M™ ScotchCode™ Tape Dispenser STD is a compact, carry-along dispenser with ten refillable compartments which hold eight-foot rolls of non-smear polyester tape. The tape's high tack, acrylic adhesive resists solvents, oil and water and adheres firmly to insulation surfaces. An end loop hooks the dispenser easily to a tool pouch or belt. Dispensers can be ordered empty or filled with 10 rolls of either pre-printed numbers 0-9 or NEMA colors.



Features	Benefits
Compact Design	Easy to handle
Hangs from a tool belt	Convenient
Provides contamination protection around the wire markers	Helps markers stay clean & dry
Can be custom filled to meet specific project requirements	Virtually no waste
Dispenses only the desired length	Helps prevent waste

Specifications and Ordering Information for 3M™ ScotchCode™ Wire Marker Tape Dispensers

Product Number	UPC (054007-)	Description	Case Qty.
STD	12172	Dispenser only—holds 10 rolls	25
STD-X	49519	Dispenser only—holds 10 rolls	10
STD-0-9	12174	Dispenser filled with 10 rolls of numbered tape (one each of 0–9)	25
STD-0-9X	49518	Dispenser filled with 10 rolls of numbered tape (one each of 0–9)	10
STD-C	12175	Dispenser filled with 10 rolls of colored tape (one each of black, blue, brown, green, gray, orange, red, violet, white and yellow)	25
STD-CX	49517	Dispenser filled with 10 rolls of colored tape (one each of black, blue, brown, green, gray, orange, red, violet, white and yellow)	10

3M™ ScotchCode™ Dispenser Refill Rolls SDR



3M ScotchCode Wire Marking Tape SDR is available in ten NEMA colors, individual numbers and consecutive numbers, letters and symbols.

The SDR tape can be used for the applications with operating temperatures between -40°F (-40°C) to 250°F (121°C):

- Marking all types of wire and cable including power, control, fiber optic, electronic, telecommunications, and instrumentation
- Phase identification on large or small gauge wire or cable
- Identification of terminal blocks, terminal strips, and wire in panel boards or a piece of switchgear
- Automotive applications on tubing, hoses and replacement parts

Specifications and Ordering Information for 3M™ ScotchCode™ Wire Marker Tape SDR (refills)

Product Number	UPC (054007-)	Description	Inner Unit Pack	Case Qty.
SDR-0	09369	0	10/box	50
SDR-1	09370	1	10/box	50
SDR-2	09371	2	10/box	50
SDR-3	09372	3	10/box	50
SDR-4	09373	4	10/box	50
SDR-5	09374	5	10/box	50
SDR-6	09375	6	10/box	50
SDR-7	09376	7	10/box	50
SDR-8	09377	8	10/box	50
SDR-9	09378	9	10/box	50
SDR-0-9	09368	Consecutive 0–9	10 rls/pk	50 rolls or 5 packs
SDR 10-19	09379	Consecutive 10–19	10 rls/pk	50 rolls or 5 packs
SDR 20-29	09380	Consecutive 20–29	10 rls/pk	50 rolls or 5 packs
SDR 30-39	09381	Consecutive 30–39	10 rls/pk	50 rolls or 5 packs
SDR 40-49	09382	Consecutive 40–49	10 rls/pk	50 rolls or 5 packs
SDR 50-59	09383	Consecutive 50–59	10 rls/pk	50 rolls or 5 packs
SDR 60-69	09384	Consecutive 60–69	10 rls/pk	50 rolls or 5 packs
SDR 70-79	09385	Consecutive 70–79	10 rls/pk	50 rolls or 5 packs
SDR 90-99	09387	Consecutive 90–99	10 rls/pk	50 rolls or 5 packs
SDR-A	09388	A	10/box	50
SDR-B	09389	B	10/box	50
SDR-C	09390	C	10/box	50
SDR-D	09391	D	10/box	50
SDR-E	09392	E	10/box	50
SDR-F	09393	F	10/box	50
SDR-G	09394	G	10/box	50

Specifications and Ordering Information for 3M™ ScotchCode™ Wire Marker Tape SDR (refills)

Product Number	UPC (054007-)	Description	Inner Unit Pack	Case Qty.
SDR-H	09395	H	10/box	50
SDR-I	09396	I	10/box	50
SDR-J	09397	J	10/box	50
SDR-K	09398	K	10/box	50
SDR-L	09399	L	10/box	50
SDR-M	09403	M	10/box	50
SDR-N	09405	N	10/box	50
SDR-O	09406	O	10/box	50
SDR-P	09407	P	10/box	50
SDR-R	09409	R	10/box	50
SDR-S	09410	S	10/box	50
SDR-T	09411	T	10/box	50
SDR-U	09415	U	10/box	50
SDR-V	09416	V	10/box	50
SDR-W	09417	W	10/box	50
SDR-X	09418	X	10/box	50
SDR-Y	09419	Y	10/box	50
SDR-Z	09420	Z	10/box	50
SDR-L1	09400	L1	10/box	50
SDR-L2	09401	L2	10/box	50
SDR-L3	09402	L3	10/box	50
SDR-T1	09412	T1	10/box	50
SDR-T2	09413	T2	10/box	50
SDR-T3	09414	T3	10/box	50
SDR- + (Plus)	09421	+	10/box	50
SDR- - (Minus)	09422	-	10/box	50
SDR-BK	09423	Black	10/box	50
SDR-BL	09424	Blue	10/box	50
SDR-BN	09425	Brown	10/box	50
SDR-GN	09426	Green	10/box	50
SDR-GY	09427	Gray	10/box	50
SDR-RD	09429	Red	10/box	50
SDR-VL	09458	Violet	10/box	50
SDR-WH	09430	White	10/box	50
SDR-YL	09431	Yellow	10/box	50
SDR-MC	09404	Multiple Colors	10/rls/pk	50 rolls or 5 packs

Books

3M™ ScotchCode™ Pre-Printed Wire Marker Books SPB

When you need to mark wires quickly, try 3M™ ScotchCode™ Pre-printed Wire Marker Books SPB. These handy books, 15 in all, contain printed vinyl coated cloth wire and terminal markers with clearly printed letters, numbers and industry-standard legends.



Specifications and Ordering Information for 3M™ ScotchCode™ Pre-Printed Wire Marker Book SPB

Product Number	UPC (054007-)	Quantity (each)	Contents	Inner Unit Pack	Case Qty.
SPB-01	49951	45 15	0-9 L1-L3, T1-T3	1/bag	5
SPB-02	49952	10	A-Z, 0-15, +, -, /	1/bag	5
SPB-03	49953	10	1-45	1/bag	5
SPB-04	49954	150	1, 2, 3	1/bag	5
SPB-05	49955	150	A, B, C	1/bag	5
SPB-06	49956	150	T1, T2, T3	1/bag	5
SPB-07	49957	150	L1, L2, L3	1/bag	5
SPB-08	49958	6 4 2	1-15 16-90 A-Z, +, -, /, 0	1/bag	5
SPB-09	49959	45 30	1,2,3,A,B,C L1-L3, T1-T3	1/bag	5
SPB-11	49960	15	1-30	1/bag	5
SPB-12	49961	15 8 6 21	A-Z + — Write-On Markers	1/bag	5
SPB-13	49962	45 33 27 21	+ , - , AC, DC POS, NEG, GND NEUT, SPARE Write-On Markers	1/bag	5
SPB-14	49963	10	46-90	1/bag	5
SPB-15AS	49964	9 5 2 21	30 Alarm System Legends* 1-15 16-45 Write-On Markers	1/bag	5
SPB-16LC	49965	5 110	68 Load Center Legends** Write-On Markers	1/bag	5


* 30 Alarm System Legends: + Circuit +, - Circuit -, + DC, -DC, AC AC, ZONE 1, ZONE 2, ZONE 3, ZONE 4, ZONE 5, ZONE 6, ZONE 7, ZONE 8, ZONE 9, SHUNT, GROUND, FIRE, BA BA, FEED, RETURN, PHONE FEED, PHONE RETURN, BELL, ANNUNCIATOR, TAMPER, 12 VOLT, 16 VOLT, 24 VOLT, SMOKE DETECTOR, THERMOSTAT.

**68 Load Center Legends: MAIN, REFRIGERATOR, FREEZER, RANGE, DISPOSAL, COMPACTOR, DISHWASHER, KITCHEN LIGHTS, KITCHEN OUTLETS, GFI KITCHEN, LIVING LIGHTS 1, LIVING LIGHTS 2, LIVING OUTLETS 1, LIVING OUTLETS 2, DINING LIGHTS, DINING OUTLETS, DEN LIGHTS, DEN OUTLETS, BATH 1 GFI, BATH 1 OUTLETS, BATH 1 LIGHTS, BATH 2 GFI, BATH 2 OUTLETS, BATH 2 LIGHTS, BATH 3 GFI, BATH 3 OUTLETS, BATH 3 LIGHTS, BEDR'M 1 LIGHTS, BEDR'M 1 OUTLETS, BEDR'M 2 LIGHTS, BEDR'M 2 OUTLETS, BEDR'M 3 LIGHTS, BEDR'M 3 OUTLETS, BEDR'M 4 LIGHTS, BEDR'M 4 OUTLETS, BEDR'M 5 LIGHTS, BEDR'M 5 OUTLETS, REC LIGHTS, REC OUTLETS, PATIO LIGHTS, PATIO OUTLETS, HEATING 1, HEATING 2, AIR COND 1, AIR COND 2, WATER HEATER 1, WATER HEATER 2, WASHER, DRYER, OUTSIDE OUTLETS, ATTIC LIGHTS, ATTIC OUTLETS, BASEM'T LIGHTS, BASEM'T OUTLETS, UTILITY LIGHTS, UTILITY OUTLETS, DRIVEWAY LIGHTS, POOL GFI, POOL LIGHTS, POOL HEATING, SHED LIGHTS, SHED OUTLETS, ENTRY LIGHTS, ENTRY OUTLETS, GARAGE LIGHTS, GARAGE OUTLETS, SUNR'M LIGHTS, SUNR'M OUTLETS.

Features	Benefits
Clearly printed (SPB-specific)	Legible, neat
Wide variety of printed characters	Contains marks for several standard applications
Contains markers for several standard applications	Variety
Single character marker included with each marker for terminal block identification	Convenient

3M™ ScotchCode™ Write-On Wire Marker Book SWB

The 3M™ ScotchCode™ Write-On Wire Marker Book SWB contains self-laminating, write-on markers designed for small volume applications involving special or complex legends that are hand written at the job site.



Specifications and Ordering Information for 3M™ ScotchCode™ Write-On Wire Marker Books SWB

Product Number	UPC (054007-)	Labels per Book	Write-On Area		Marker Size		Recommended Wire O.D.	Inner Unit Pack	Case Qty.
			A	B	A	C			
SWB-01	49904	180	0.5" (13 mm)	0.5" (13 mm)	0.5" (13 mm)	1.5" (38 mm)	0.16 x 0.31 (4 x 8 mm)	1/bag	5
SWB-02	49905	120	0.75" (19 mm)	0.75" (19 mm)	0.75" (19 mm)	1.75" (44 mm)	0.24 x 0.31 (6 x 8 mm)	1/bag	5
SWB-03	49906	60	1.0" (25 mm)	1.0" (25 mm)	1.0" (25 mm)	2.85" (72 mm)	0.32 x 0.58 (8 x 15 mm)	1/bag	5
SWB-04	49907	30	1.0" (25 mm)	1.0" (25 mm)	1.0" (25 mm)	5.0" (127 mm)	0.32 x 1.55 (8 x 39 mm)	1/bag	5

3M™ ScotchCode™ Marker Pens SMP

3M ScotchCode Marking Pens SMP are suggested for use with ScotchCode write-on products. The pen performs well on nonporous surfaces, has an extra-fine point with permanent, quick-drying ink and is available in black.



Specifications and Ordering Information for 3M™ ScotchCode™ Marker Pens SMP

Product Number	UPC (051128-)	Ink Color	Inner Unit Pack	Case Qty.
SMP	57743	Black	10/box	50



3M™ Portable Labeler Family

3M offers a family of portable labelers to tackle any number of jobs from DIY to industrial jobsite applications. All units are equipped with exclusive one-touch hot keys that provide shortcuts for the most common formatting tasks. The 3M™ Portable Labelers will print on a range of label materials. The label cartridges are interchangeable, and are easy to install and remove.



3M and ScotchCode are trademarks of 3M Company.

Important Notice

Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use.

Warranty; Limited Remedy; Limited Liability.

3M's product warranty is stated in its Product Literature available upon request. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Electrical Markets Division

6801 River Place Blvd.
Austin, TX 78726-9000
800/245 3573
www.3M.com/electrical

Please recycle. Printed in USA.
© 3M 2013. All rights reserved.
80-6109-4242-9B