

FIRE ALARM BOXES

The National Electrical Code® defines a fire alarm circuit as “the portion of the wiring system between the load side of the overcurrent device or the power-limited supply and the connected equipment of all circuits powered and controlled by the fire alarm system.” Additionally, the NEC requires that all fire alarm circuits be identified at terminal and junction locations in a manner that will prevent unintentional interference with the signaling circuit during testing and servicing.

Cooper Crouse-Hinds® steel Fire Alarm Boxes help meet those installation requirements and are available in the most popular 4" and 4 11/16" square boxes along with covers and box extensions. A 4" octagon box is also available. The red paint allows inspectors to quickly identify fire alarm circuit outlet boxes. The boxes are UL Listed with a two-hour fire rating and are available in a variety of configurations to meet varied applications.

FEATURES AND BENEFITS

- Red epoxy paint allows for quick identification of fire alarm systems meeting NEC® requirements
- Eliminates the need to paint boxes on the job site, saving time and expense
- UL Listed for use in two-hour, fire-rated walls
- Available in 4" and 4 11/16" square and 4" octagon, 1 1/2" and 2 1/8" deep welded or drawn construction to meet various applications and/or preferences

MATERIALS

- Outlet Boxes: Pre-Galvanized Steel

FINISH

- Red epoxy paint

CERTIFICATIONS AND COMPLIANCES

- UL Listed



National Electric Code® and NEC® are registered trademarks of the National Fire Protection Assoc. Inc.



FIRE ALARM BOXES



TP404RED



TP423RED



TP414RED



TP434RED



TP403RED



TP451RED



TP428RED



TP472RED



TP556RED



TP564RED



TP568RED



TP292RED

ORDERING INFORMATION

Catalog Number	Description	Depth Size	Cubic In. Capacity	Bracket	Knockouts		Std. Unit Pkg.	Wt. Lbs. Per 100
					Sides	Bottom		
TP404RED	4" SQ BOX SHALLOW WELDED	1 1/2"	22	—	8 1/2", 4 1/2" & 3/4" E	2 1/2", 2 1/2" & 3/4" E	50	72
TP423RED	4" SQ BOX SHALLOW WELDED	1 1/2"	22	VMS	6 1/2", 3 1/2" & 3/4" E	2 1/2", 2 1/2" & 3/4" E	25	81
TP414RED	4" SQ BOX SHALLOW DRAWN	1 1/2"	21	—	8 1/2", 4 3/4"	3 1/2", 2 3/4"	50	67
TP434RED	4" SQ DEEP DRAWN	1 1/2"	30.3	—	8 1/2", 4 3/4"	3 1/2", 2 3/4"	25	84
TP403RED	4" SQ BOX DEEP WELDED	2 1/8"	30.3	—	8 1/2", 4 1/2" & 3/4" E	2 1/2", 2 1/2" & 3/4" E	25	84
TP451RED	4" SQ BOX DEEP WELDED	2 1/8"	30.3	VMS	6 1/2", 3 1/2" & 3/4" E	2 1/2", 2 1/2" & 3/4" E	25	96
TP428RED	4" SQ EXTENSION RING	1 1/2"	21	—	8 1/2", 4 3/4"	—	50	46
TP472RED	4" SQ FLAT BLANK COVER	—	—	—	—	—	50	31
TP556RED	4 11/16" SQ BOX DEEP	2 1/8"	42	—	8 1/2", 4 3/4"	3 1/2", 2 3/4"	25	104
TP564RED	4 11/16" SQ EXTENSION RING	2 1/8"	42	—	8 1/2", 4 3/4"	—	25	84
TP568RED	4 11/16" SQ FLAT BLANK COVER	—	—	—	—	—	25	40
TP292RED	4" OCTAGON DEEP OUTLET BOX	2 1/8"	21.5	—	2 1/2", 2 3/4"	3 1/2", 2 3/4"	25	64

For more information:

Contact an authorized Cooper Crouse-Hinds Distributor,
Sales Office or Customer Service Department:

Distributed by:

In the U.S.:

Cooper Crouse-Hinds
P.O. Box 4999
Syracuse, NY 13221
Toll Free: 866-764-5454
(315) 477-5531
FAX: (315) 477-5179
crouse.customerctr@crouse-hinds.com

In Canada:

Cooper Crouse-Hinds Canada
Toll Free: 800-265-0502

**For office locations outside of North America
or for additional product information, visit our
website at: www.crouse-hinds.com**

Mexico • Latin America/Caribbean • Germany • Australia • Asia • Dubai • India

COOPER Crouse-Hinds

4889-0107

Solutions. Worldwide.™

Crouse-Hinds is a registered trademark of Cooper Industries, Inc.
© 2007 Cooper Industries, Inc.



Printed in U.S.A