

FENDER WASHERS

PC 4110

Fender Washers are for general purpose applications. Provides a large load bearing surface.

CAT. NO.	UPC	SIZE	STD	SLV	MSTR	WT/STD
FENW316114	15505	3/16 x 1-1/4"	100	500	3000	1.65#
FENW141	15510	1/4 x 1"	100	500	3000	1.00#
FENW14114	15515	1/4 x 1-1/4"	100	500	3000	1.62#
FENW14112	15520	1/4 x 1-1/2"	100	500	3000	2.37#
FENW142	15521	1/4 x 2"	100		3000	5.65#
FENW516114	15525	5/16 x 1-1/4"	100	500	3000	2.05#
FENW38114	15527	3/8 x 1-1/4"	100	500	3000	2.20#
FENW38112	15530	3/8 x 1-1/2"	100		1000	3.08#
FENW382	15531	3/8 x 2"	100		1000	5.50#
FENW12112	15535	1/2 x 1-1/2"	100		1000	2.75#
FENW122	15540	1/2 x 2"	100		1000	5.25#
FENWT14114	15536	1/4 x 1-1/4"	250		1500	5.23#
FENWT38114	15537	3/8 x 1-1/4"	250		1500	4.58#
FENWT12112	15538	1/2 x 1-1/2"	150		900	4.01#



FEATURES:

- Fender Washers
- Zinc Plated Steel

FENDER WASHERS - STAINLESS

PC 4010

Fender Washers are for general purpose applications. Provides a large load bearing surface. Stainless steel resists corrosion.

CAT. NO.	UPC	SIZE	STD	SLV	MSTR	WT/STD
FENWS3161	69906	3/16 x 1"	100	500	3000	1.19#
FENWS141	69908	1/4 x 1"	100	500	3000	1.25#
FENWS14114	69910	1/4 x 1-1/4"	100	500	3000	2.09#
FENWS14112	69912	1/4 x 1-1/2"	100		1000	2.85#
FENWS516112	69914	5/16 x 1-1/2"	100		1000	2.30#
FENWS38112	69916	3/8 x 1-1/2"	100		1000	3.26#
FENWS122	69918	1/2 x 2"	100		1000	5.12#



FEATURES:


- Fender Washers
- Stainless Steel

"S" HOOKS

PC 4870

"S" Hooks are manufactured from low carbon cold drawn steel wire supplied with blunt ends and zinc plated. Hooks are used to hang fixtures suspended from chain.

CAT. NO.	UPC	OVERALL DIAMETER LENGTH (L)	EYE (C)	OPENING (E)	WIRE GAUGE (D)	STD	MSTR	WT/STD
S1	30805	1"	1/4"	3/16"	11 Ga.	100	3000	0.74#
S2	30810	1-1/2"	7/16"	1/4"	7 Ga.	100	1000	2.47#
S3	30815	2"	9/16"	3/8"	1/4"	50	500	3.01#
S4	30820	2-1/2"	3/4"	7/16"	5/16"	50	200	6.04#
S5	30825	3"	7/8"	1/2"	5/16"	50	200	7.11#



FEATURES:

- "S" Hook
- Zinc Plated Steel