

# Single Pole Devices and Temporary Power

## Features and Benefits

### Temporary Power Accessories

Hubbell's SR50 is comprised of a pre-wired 50A receptacle, mounted in a fully non-metallic watertight FD wall box.

This weather resistant, UL listed, assembly provides significant labor savings for the contractor, because it's pre-wired with a 50A Twist-Lock® receptacle, installation time is significantly reduced. The 4 hole mounting pattern of the new FD box also provides added security for the device.



### Cable Sets and Receptacles

Description	Catalog Number
50A pre-wired wall mounted receptacle, with 2 ft. wire leads.	<b>SR50</b>
50A cord set - 50 ft. cable (input/output).	<b>SCB50</b>
50A cord set - 100 ft. cable (input/output).	<b>SCB100</b>
60A cord set - 6 ft. cable (input/output).	<b>SCC06</b>
60A cord set - 50 ft. cable (input/output).	<b>SCC50</b>
60A, 3Ø 120/208V Pin and Sleeve wall mounted receptacle.	<b>HBL560R9W</b>
1¼" hub 15 deg. non-metallic angle back box for 60A receptacle.	<b>BB601W</b>
1½" hub 15 deg. metallic 4-way angle back box for 60A receptacle.	<b>FW60100</b>

Note: Consult factory for alternate cable lengths.



SR50

### Replacement Parts

Description	Catalog Number
20A, 125V straight blade receptacle.	<b>HBL53R61</b>
20A, 125V Safety-Shroud Twist-Lock® receptacle.	<b>HBL2310SW</b>
30A, 250V Safety-Shroud Twist-Lock® receptacle.	<b>HBL2620SW</b>
30A, 125/250V Reverse Service Safety-Shroud connector.	<b>HBL2713SR</b>
30A, 125/250V Reverse Service inlet.	<b>HBL2715SWR</b>
50A, 125/250V Twist-Lock® receptacle.	<b>CS6369</b>
50A, 125/250V Twist-Lock® inlet.	<b>HBL6375S</b>
60A, 3Ø 120/208V Pin and Sleeve reversed service receptacle (inlet).	<b>HBL560B9R</b>
60A, 3Ø 120/208V Pin and Sleeve receptacle (outlet).	<b>HBL560R9W</b>
60A, 3Ø 120/208V Pin and Sleeve reversed service plug (female).	<b>HBL560P9WR</b>
60A, 3Ø 120/208V Pin and Sleeve plug (male).	<b>HBL560P9W</b>
GFCI module.	<b>GFM20</b>
50A Spider supervisory kit.	<b>SSK</b>
60A Spider supervisory kit.	<b>SSK60</b>
Spider circuit breaker cover.	<b>SCBC</b>
Spider leg kit.	<b>SLK</b>
Spider leg kit, green.	<b>SLKG</b>
50A receptacle cover plate.	<b>HBL77CM74WO</b>



SCB50



HBL560R9W



HBL2310SW



SCBC



GFM20



SSK



HBL77CM74WO



CS6369



HBL2713SR