


Specification grade GFCIs

Specification grade ground fault circuit interrupter receptacles


Product description

2-pole, 3-wire grounding
15A, 125V/AC; 20A, 125V/AC
NEMA 5-15, 5-20




5-15R


5-20R



VGFI5-AG



VGFS15



VGFD20

Tamper resistant specification grade automatic ground GFCIs



Rating	A	V/AC	NEMA	Description	Color suffix	Catalog no.
15	125	5-15R	Duplex GFCI, back & side wire	A, B, BK, GY, LA, V, W	<input type="checkbox"/> TRVGF15__-AG	
20	125	5-20R	Duplex GFCI, back & side wire	A, B, BK, GY, LA, V, W	<input type="checkbox"/> TRVGF20__-AG	

Specification grade automatic ground GFCIs



Rating	A	V/AC	NEMA	Description	Color suffix	Catalog no.
15	125	5-15R	Auto ground duplex GFCI, back & side wire	V, W	<input type="checkbox"/> VGFI5__-AG	
20	125	5-20R	Duplex receptacle, back & side wire	V, W	<input type="checkbox"/> VGFI20__-AG	

Specification grade combination GFCI receptacle & switch



Rating	A	V/AC	NEMA	Description	Color suffix	Catalog no.
15	125	5-15R	GFCI receptacle with feed-through single-pole switch (rated 1800W @ 120V/AC, 60Hz)	A, LA, V, W	<input type="checkbox"/> VGFS15__-MSP	

Specification grade blank face GFCI



Rating	A	V/AC	Description	Color suffix	Catalog no.
20	125		Blank face (dead front) GFCI, rated as 1.5HP motor control switch, back & side wire	A, BK, LA, V, W	<input type="checkbox"/> VGFD20__

Accessories for GFCIs

Description	Color suffix	Catalog no.	
GFCI 7/8" extension ring, cULus Listed	BLK, LA, V, W	<input type="checkbox"/> GFER__	
Metal self-closing horizontal 1-gang weather protective cover, decorator opening		<input type="checkbox"/> S1966	•
While-in-use metal weather protective standard depth 1-gang cover, vertical mount		<input type="checkbox"/> WIUMV-1	•



GFER



S1966




WIUMV-1



WIUMH-1

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White)



Specification information: Specification grade GFCI: H-16, Specification grade combo GFCI receptacle & switch: H-17, Specification grade blank face GFCI : H-17

Compliances, specifications and availability are subject to change without notice.

Indicates NAFTA compliant - Page Q-30

Tamper resistant