

**SAWZALL®**  
**M18™ Cordless Recip Saw Kit**

2620-22/2620-21 (Bare tool 2620-20)

**Specifications:**

SPM	0 – 3,200
Stroke Length	1"
Weight	7.9 lbs
Blade Clamp	Lever Action QUIK-LOK®
Anti-Vibration	YES



**Includes**

2620-22: (2) M18™ XC High Capacity LITHIUM-ION Batteries, 1-Hour Charger, SAWZALL® Blade, Carrying Case  
2620-21: (1) M18™ XC High Capacity LITHIUM-ION Battery, 1-Hour Charger, SAWZALL® Blade, Carrying Case

**M18™ Cordless Band Saw Kit**

2629-22 (Bare tool 2629-20)

**Specifications:**

SFPM	480
Capacity	3-1/4" x 3-1/4"
Weight	10.25 lbs
Material Guide	Tool-Free
Blade Ejection System	YES



**Includes** (2) M18™ XC High Capacity LITHIUM-ION Batteries, 1-Hour Charger, Blade, Carrying Case

**HACKZALL® M18™**  
**Cordless One-Handed Recip Saw Kit**

2625-21 (Bare tool 2625-20)

**Specifications:**

SPM	0 – 3,000
Stroke Length	3/4"
Weight	5.6 lbs
Blade Clamp	QUIK-LOK®
Anti-Vibration	YES



**Includes** (1) M18™ XC High Capacity LITHIUM-ION Battery\*, 1-Hour Charger, SAWZALL® Blade, Contractor Bag



**HACKZALL® M18™**  
**Cordless One-Handed Recip Saw Kit**

2625-21CT (Bare tool 2625-20)

**Specifications:**

SPM	0 – 3,000
Stroke Length	3/4"
Weight	5.0 lbs
Blade Clamp	QUIK-LOK®
Anti-Vibration	YES



**Includes** (1) M18™ Compact LITHIUM-ION Battery\*, 30-Minute Charger, SAWZALL® Blade, Contractor Bag

**M18™ Cordless 6-1/2" Circular Saw Kit**

2630-22 (Bare tool 2630-20)

**Specifications:**

RPM	3,500
Bevel Capacity	50°
Arbor	5/8"
Blade Guards	Magnesium
Shoe	Aircraft Aluminium



**Includes** (2) M18™ XC High Capacity LITHIUM-ION Batteries, 1-Hour Charger, Circular Saw Blade, Rip Fence, Wrench, Contractor Bag

**M18™ Cordless 4-1/2" Cut-Off/Grinder Kit**

2680-22 (Bare tool 2680-20)

**Specifications:**

RPM	9,000
Switch	Paddle
Guard Adjustment	Tool-Free
Overload Protection	YES
Handle Positions	3



**Includes** (2) M18™ XC High Capacity LITHIUM-ION Batteries, 1-Hour Charger, Type 1 Guard, Type 27 Guard, Type 1 Cut-Off Wheel, Spanner Wrench, Side-Handle, Contractor Bag

**M18™ Cordless Jig Saw Kit**

2645-22 (Bare tool 2645-20)

**Specifications:**

SPM	2,200
Stroke Length	1"
Orbital Settings	5
Blade Clamp	Tool-Free
Bevel Adjustment	45° Tool-Free



**Includes** (2) M18™ XC High Capacity LITHIUM-ION Batteries, 1-Hour Charger, Jig Saw Blade, Non-Marring Shoe, Carrying Case

**ProPEX® M18™ Cordless Expansion Tool Kit**

2632-22 (Bare tool 2632-20)

**Specifications:**

Speed	45 SPM
Head Rotation	Built-in Auto Rotator
Capacity	3/8" – 1-1/2"
Compatibility	3/8" – 1" M12, 1" – 1-1/2" M18/Uponor
LED light	YES



**AVAILABLE FALL 2010**



ProPEX® is a registered trademark of Uponor, Inc.

**M18™ ProPEX® Accessory Heads**

**Specifications:**

49-16-2608	M18™ 1" Expansion Head
49-16-2610	M18™ 1-1/4" Expansion Head
49-16-2612	M18™ 1-1/2" Expansion Head

Compatible with M18™ ProPEX® Expansion Tools Only



M18™ TOOLS

**M18™ Cordless 4-Tool Combo Kit**

2690-24

**Tools included:**

1/2" High Performance Hammer Drill Driver	2611-20
SAWZALL® Recip Saw	2620-20
Circular Saw	2630-20
Work Light	49-24-0171

**Includes** (2) M18™ XC High Capacity LITHIUM-ION Batteries, 1-Hour Charger, (1) SAWZALL® Blade, (1) Circular Saw Blade, Rip Fence, Wrench, Side Handle, Contractor Bag



**M18™ Cordless 2-Tool Combo Kit**

2690-22

**Tools included:**

1/2" High Performance Hammer Drill Driver	2611-20
SAWZALL® Recip Saw	2620-20

**Includes** (2) M18™ XC High Capacity LITHIUM-ION Batteries, 1-Hour Charger, (1) SAWZALL® Blade, Side Handle, Contractor Bag



**M18™ Cordless 4-Tool Combo Kit**

2692-24

**Tools included:**

1/2" High Performance Hammer Drill Driver	2611-20
1/4" Hex Impact Driver	2650-20
SAWZALL® Recip Saw	2620-20
Work Light	49-24-0171

**Includes** (2) M18™ XC High Capacity LITHIUM-ION Batteries, 1-Hour Charger, Side Handle, (1) SAWZALL® Blade, Belt Hook, Contractor Bag



**M18™ Cordless 2-Tool Combo Kit**

2694-22

**Tools included:**

1/2" Hammer Drill Driver	2602-20
SAWZALL® Recip Saw	2620-20

**Includes** (2) M18™ XC High Capacity LITHIUM-ION Batteries, 1-Hour Charger, (1) SAWZALL® Blade, Contractor Bag



**M18™ Cordless 4-Tool Combo Kit**

2694-24

**Tools included:**

1/2" Hammer Drill Driver	2602-20
SAWZALL® Recip Saw	2620-20
Circular Saw	2630-20
Work Light	49-24-0171

**Includes** (2) M18™ XC High Capacity LITHIUM-ION Batteries, 1-Hour Charger, Side Handle, (1) SAWZALL® Blade, (1) Circular Saw Blade, Rip Fence, Wrench, Contractor Bag



**M18™ Cordless 2-Tool Combo Kit**

2697-22

**Tools included:**

1/2" Hammer Drill Driver	2602-20
1/4" Hex Impact Driver	2650-20

**Includes** (2) M18™ XC High Capacity LITHIUM-ION Batteries, 1-Hour Charger, Belt Hook, Contractor Bag



**M18™ Cordless 3-Tool Combo Kit**

2696-23

**Tools included:**

1/2" High Torque Impact Wrench	2663-20
3/8" Compact Impact Wrench	2651-20
Work Light	49-24-0171

**Includes** (2) M18™ XC High Capacity LITHIUM-ION Batteries, 1-Hour Charger, Belt Hook, Contractor Bag



**M18™ Cordless 2-Tool Combo Kit**

2691-22

**Tools included:**

1/2" Compact Drill Driver	2601-20
1/4" Hex Impact Driver	2650-20

**Includes** (2) M18™ Compact LITHIUM-ION Batteries, 30-Minute Charger, Belt Hook, Carrying Case



**M18™ Cordless 3-Tool Combo Kit**

2691-23

**Tools included:**

3/8" Compact Impact Wrench	2651-20
1/2" Compact Drill Driver	2601-20
Work Light	49-24-0171

**Includes** (2) M18™ Compact LITHIUM-ION Batteries, 30-Minute Charger, Belt Hook, Contractor Bag



**M18™ Cordless 2-Tool Combo Kit**

2693-22

**Tools included:**

3/8" Compact Impact Wrench	2651-20
Work Light	49-24-0171

**Includes** (2) M18™ Compact LITHIUM-ION Batteries, 30-Minute Charger, Belt Hook, Contractor Bag

