


Milbank Temporary Power Solutions

The Milbank Millennium series of power outlets and pedestals offers a modular design concept that allows for a variety of receptacle and circuit breaker configurations. The products shown here can be field configured to accommodate up to three receptacles based on the application. Adding the receptacle kits is fast and easy. Our inventory of all components, offers a stock solution for immediate needs on the job site.



Ordering Information

Catalog Number	Service	Lugs	Description
U5000-XL	OH/UG	(2) #12-1/0	Unmetered post mount power outlet
U5101-XL	OH	(1) #6-250	Metered post mount power outlet, ringless
U5200-XL	UG	(2) #6-350	Unmetered single direct burial pedestal
U5210-XL*	UG	(2) #6-350	Unmetered single pad-mount pedestal
U5220-XL	UG	(2) #6-350	Unmetered double direct burial pedestal
*K5410			Pad mount kit required for U5210-XL

All power outlets and pedestals are 125 amp rated with: lockable and sealable covers, hub opening with plate, 6 pole circuit breaker interior, 3 position self-grounding receptacle bridge, convenient concentric knock-out provisions, mounting embosses and have a 3R rating for durable outdoor use. Contact factory for more detailed specifications or drawings.

Milbank also offers a variety of metered service pedestals (not shown) for permanent power requirements. Contact your local agent for more information.

816.483.5314 phone

816.483.6357 fax

www.milbankmfg.com


GFI 10/05




MILBANK[®]

Milbank Temporary Power Solutions


Receptacle Kits for Power Outlets



K5400-520GR



K5400-TT30



K5400-1450

Catalog Number

Description

K5400-520GR

20a, 120v GFI duplex receptacle kit

K5400-TT30

30a, 120v NEMA TT30 receptacle kit

K5400-1450

50a, 120/240v NEMA 1450 receptacle kit

All receptacle kits come with pre-wired copper conductors, mounting screws, cover plates and instruction sheet. Contact factory for other receptacle kits available.

SINGLE RECEPTACLE ONLY POWER OUTLET



P-13

Application:


- Overhead/Underground Power Outlet Receptacle, suitable for RV, temporary service, campground, marina & boatyard equipment

Features:


- Type 3R, 120/240 volt single phase
- Lockable cover

Ordering:


- Order catalog number from chart below.



P-10GR
20a 120v GFI



P-13
30a 120v



P-54
50a 120/250v

Catalog Number

Service

Wire Size

Description

P-10GR

OH/UG

(1) #12

20a, 120v GFI receptacle in 3R box

P-13

OH/UG

(1) #10

30a, 120v receptacle only in 3R box

P-54

OH/UG

(1) #6

50a, 120/240v receptacle only in 3R box

816.483.5314 phone

816.483.6357 fax

www.milbankmfg.com

