



INTRODUCING GFCI PROTECTION YOU CAN SEE AND HEAR.

According to the *National Electrical Code*® (NEC®), GFCI protection is now a requirement for receptacles in commercial and institutional kitchens, as well as those serving residential sump pumps. At Legrand, we've created a solution that's tailor-made to these environments: the Pass & Seymour Audible Alarm GFCI Receptacle.

Ideal for receptacles serving basement pump systems, commercial freezers, refrigerated display cases and other areas where a GFCI indicator light might not be readily apparent, this revolutionary device provides an audible warning of a tripped condition and that power to a receptacle is interrupted. It's an intelligent way to help customers minimize the likelihood of basement flooding, food spoilage and other damage caused by a power disruption — all while meeting the latest NEC requirements.



2095TRAW

The industry's first audible
alarm GFCI receptacle.


The most durable GFCI available — exceeds UL943 voltage surge requirements; survives 100X the required UL 3kA/6kV voltage surge test cycles.

Side or internal screw-pressure plate back-wire termination speeds installation; takes #14-#10 AWG stranded or solid, copper or copperclad conductors.

Two back-wire holes per termination add wiring flexibility, eliminate pigtailing, and save box space.

Ground terminal back-wire clamp for fast installation.

Patented SafeLock™ Protection for More Safety — shuts off power to the receptacle if there's a ground fault, if the GFCI is miswired, and even if the GFCI fails. This prevents the unsafe condition of power without protection.



Tamper-Resistant: Automatic shutter system prevents young children from inserting common objects such as hairpins or keys.

Audible Alarm alert of tripped condition. Alarm can be turned on/off.

Trip indicator light makes it easy to identify a tripped condition.

High-impact-resistant, thermoplastic construction for superior strength and durability.

2095TRAW

PART NO.	DESCRIPTION	RATINGS		COLORS	NEMA Config.	*COLOR DESIGNATION
		A.	V.			
1595TRA*	TradeMaster® Audible Alarm Tamper-Resistant Duplex GFCI	15	125	W, I, BK, LA, -	5-15R	W White I Ivory - Brown GRY Gray BK Black LA Light Almond RED Red
2095TRA*	Specification Grade Audible Alarm Tamper-Resistant Duplex GFCI	20	125	W, I, BK, LA, GRY, RED, -	5-20R	
1595HGTRA*	Hospital Grade Audible Alarm Tamper-Resistant Duplex GFCI	15	125	W, I, LA, GRY, RED, -	5-15R	
2095HGTRA*	Hospital Grade Audible Alarm Tamper-Resistant Duplex GFCI	20	125	W, I, LA, GRY, RED, -	5-20R	

All GFCIs are Fed Spec, FSUL Listed. US LISTED

©2013 Legrand SS1783 All Rights Reserved 04113 EMA/CGXTP

designed to be better.™



Electrical Wiring Systems

P.O. Box 4822
 Syracuse, NY 13221-4822
 800.776.4035
www.legrand.us/PassandSeymour

570 Applewood Crescent
 Vaughan, Ontario L4K 4B4
 905.738.9195
www.legrand.ca

FOLLOW US

