



Concrete Anchoring System Hi-Low Thread - PC 4560

Faster to install than most steel anchors, yet has significant load capacities. One tool drills the hole and sets the anchor without the need to remove from the drill chuck. Has the added advantage of close to edge fastening without potential breakout. Works in poured concrete, prestressed concrete, cinder block, brick, and mortar, and can be loosened for adjustment or removed. ICC Approval (Pending).

- Concrete Anchor System
- Hex Head Slotted or Flat Head Phillips
- Hi-Low Thread
- Ceramic Coated Blue Finish
- Includes Drill
- Caution! Always Wear Eye Protection

CAT NO	UPC		ANCHOR HEX/PHILLIPS SIZE	BIT SIZE	DRILL SIZE	STD	MSTR	WT/STD	UNIT
36H114	11208		3/16 x 1-1/4"	1/4"	5/32 x 3-1/2"	100	500	0.89#	C
36H134	11288	Hex Head	3/16 x 1-3/4"	1/4"	5/32 x 3-1/2"	100	500	1.07#	C
36H214	11368	Slotted	3/16 x 2-1/4"	1/4"	5/32 x 4-1/2"	100	500	1.30#	C
36H234	11448	3/16"	3/16 x 2-3/4"	1/4"	5/32 x 4-1/2"	100	500	1.51#	C
36H314	11528		3/16 x 3-1/4"	1/4"	5/32 x 5-1/2"	100	500	1.87#	C
14H114	25208		1/4 x 1-1/4"	5/16"	3/16 x 3-1/2"	100	500	1.44#	C
14H134	25288		1/4 x 1-3/4"	5/16"	3/16 x 3-1/2"	100	500	1.83#	C
14H214	25368	Hex Head	1/4 x 2-1/4"	5/16"	3/16 x 4-1/2"	100	500	2.26#	C
14H234	25448	Slotted	1/4 x 2-3/4"	5/16"	3/16 x 4-1/2"	100	500	2.96#	C
14H314	25528	1/4"	1/4 x 3-1/4"	5/16"	3/16 x 5-1/2"	100	500	3.02#	C
14H334	25608		1/4 x 3-3/4"	5/16"	3/16 x 5-1/2"	100	500	3.41#	C
14H400	25648		1/4 x 4"	5/16"	3/16 x 5-1/2"	100	500	3.62#	C
36P114	11201		3/16 x 1-1/4"	#2	5/32 x 3-1/2"	100	500	0.84#	C
36P134	11281		3/16 x 1-3/4"	#2	5/32 x 3-1/2"	100	500	1.04#	C
36P214	11361	Flat Head	3/16 x 2-1/4"	#2	5/32 x 4-1/2"	100	500	1.28#	C
36P234	11441	Phillips	3/16 x 2-3/4"	#2	5/32 x 4-1/2"	100	500	1.45#	C
36P314	11521	3/16"	3/16 x 3-1/4"	#2	5/32 x 5-1/2"	100	500	1.77#	C
14P114	25201		1/4 x 1-1/4"	#2	3/16 x 3-1/2"	100	500	1.39#	C
14P134	25281		1/4 x 1-3/4"	#2	3/16 x 3-1/2"	100	500	1.85#	C
14P214	25361	Flat Head	1/4 x 2-1/4"	#2	3/16 x 4-1/2"	100	500	2.05#	C
14P234	25441	Phillips	1/4 x 2-3/4"	#2	3/16 x 4-1/2"	100	500	2.53#	C
14P314	25521	1/4"	1/4 x 3-1/4"	#2	3/16 x 5-1/2"	100	500	2.96#	C
14P334	25601		1/4 x 3-3/4"	#2	3/16 x 5-1/2"	100	500	3.38#	C
14P400	25641		1/4 x 4"	#2	3/16 x 5-1/2"	100	500	3.61#	C



Installation Tool - Phillips & Hex Head PC 4590

Installation tool installs all lengths of both phillips & hex head concrete screws. Consists of one each: Masonry drill bit holder; Phillips socket driver with one #2 & one #3 Phillips bit; 1/4" Hex socket driver; 5/16" Hex socket driver & Allen wrench.

- Phillips or Hex Head
- Accommodates All Lengths
- Storage Box

CAT NO	UPC	DESCRIPTION	STD	MSTR	WT/STD	UNIT
IT1000	14495	Installation Tool	1	1	1.50#	Ea



Hammer Drill Carbide Tipped Masonry Drill Bits PC 4570

Hammer Drills (CD Series) made specifically for Concrete Screw Anchoring System and are manufactured with closer tolerances.

- Carbide Tipped
- Close Tolerances
- Caution! Always Wear Eye Protection

CAT NO	UPC		ANCHOR SIZE	DRILL SIZE	STD	MSTR	WT/STD	UNIT
CD5323	14500		3/16"	5/32 x 3-1/2"	10	10	0.22#	Ea
CD5324	14502	5/32"	3/16"	5/32 x 4-1/2"	10	10	0.22#	Ea
CD5325	14504		3/16"	5/32 x 5-1/2"	10	10	0.24#	Ea
CD3163	14506		1/4"	3/16 x 3-1/2"	10	10	0.25#	Ea
CD3164	14508	3/16"	1/4"	3/16 x 4-1/2"	10	10	0.27#	Ea
CD3165	14510		1/4"	3/16 x 5-1/2"	10	10	0.29#	Ea

SDS Rotohammer Bits See Page E4



Dottie

To Order: Phone (323)725-1000 / Fax (323)721-0000