



## Furniture and Work Surface Connectivity Boxes

### Square Flush Mount Boxes

Description	Finish	Dimensions	Catalog Number
2-Gang Square Flush Mount Box with Cover.	Black	6.5"L x 6.5"W x 3.75"H	<b>HBLSHA2</b>
	Stainless Steel		<b>HBLSHA2BSS</b>



HBLSHA2

### Rectangular Flush Mount Boxes

2-Gang Rectangular Flush Mount with Cover.	Black	10.75"L x 4.06"W x 3.5"H	<b>HBLPHA2</b>
	Stainless Steel		<b>HBLPHA2BSS</b>
4-Gang Rectangular Flush Mount with Cover.	Black	10.75"L x 6.5"W x 3.5"H	<b>HBLPHA4</b>
	Stainless Steel		<b>HBLPHA4BSS</b>



HBLPHA2

### Surface Mount Boxes

2-Gang Surface Mount Box.	Black	4.19"L x 4.81"W x 2.44"H	<b>HBLCON2</b>
3-Gang Surface Mount Box.	Black	6.19"L x 4.81"W x 2.44"H	<b>HBLCON3</b>



HBLCON2

### Recessed Mount Boxes

2-Gang Recessed Mount.	Black	10.25"L x 7.0"W x 5.88"H	<b>HBLMIR2</b>
4-Gang Recessed Mount.	Black	31.0"L x 10.25"W x 5.88"H	<b>HBLMIR4</b>

### Under Desk Mount Boxes

2-Gang Under Desk Mount.	Black	9.19"L x 3.0"W x 2.88"H	<b>HBLMAR2</b>
3-Gang Under Desk Mount.	Black	13.69"L x 3.0"W x 2.88"H	<b>HBLMAR3</b>



HBLMAR2


### Hubbell – Screw Type Face Plates

Description	Catalog Number
Duplex	<b>HBLST302SBK</b>
Style Line®	<b>HBLDE301SBK</b>
Toggle	<b>HBLTO310SBK</b>
Single Receptacle (1.56" Boss Dia.)	<b>HBLTL318SBK</b>
Single Receptacle (1.39" Boss Dia.)	<b>HBLTL319SBK</b>
Blank	<b>HBLBL300SBK</b>
3-Unit Hubbell iSTATION (See Network Wiring section Y for module options)	<b>HBLIMFSBK</b>
Hubbell 6-Port	<b>HBL317SBK</b>




### Open Systems – Screw Type Face Plates

Description	Catalog Number
AMP-ACO	<b>HBLAM303SBK</b>
AMP 6-Port	<b>HBLAMP313SBK</b>
Krone®/Leviton®	<b>HBLKR314SBK</b>
SYSTIMAX®	<b>HBLLT309SBK</b>
Panduit Mini-Com®	<b>HBLPA308SBK</b>
NORDX® 6-Port (Cat. 5e jacks only)	<b>HBLNO309SBK</b>
Siemon CT® Series	<b>HBLSI305SBK</b>
Siemon MAX® Series	<b>HBLSI315SBK</b>
Ortronics Series II®	<b>HBLOR306SBK</b>
Ortronics TracJack®	<b>HBLORT322SBK</b>



Note: \*Catalog number indicated is Black, replace "BK" with the following to designate color: "GY" for Gray, "I" for Ivory and "WA" for White.

AMP is a registered trademark of Tyco Electronics Corp. Krone® is a registered trademark of Krone, Inc. Leviton® is a registered trademark of Leviton. SYSTIMAX® is a registered trademark of CommScope, Inc. Mini-Com® and Panduit® are registered trademarks of Panduit Corp. NORDX® is a registered trademark of Belden/CDT, Inc. MAX® and CT® Series are registered trademarks of The Siemon Company. TracJack®, Series II® and Ortronics® are registered trademarks of Ortronics/Legrand.



### Table Top Boxes

#### Low Voltage Only

Description	Finish	Dimensions	Catalog Number
Table Top box; 2 inch diameter hole; (1) keystone opening; Keystone modules sold separately.	Black Anod. Alum.	2.19" Diameter	<b>TTBKSBK</b>
	Clear Anod. Alum.		<b>TTBKSAL</b>
	Solid Brass		<b>TTBKSBR</b>
Table Top box; 2 inch diameter hole; (1) XLR microphone jack installed.	Black Anod. Alum.	2.19" Diameter	<b>TTBXLRBK</b>
	Clear Anod. Alum.		<b>TTBXLRAL</b>
	Solid Brass		<b>TTBXLRBR</b>



TTBKSBK



TTBXLRBK

#### Pre-Wired Dual-Service

Description	Finish	Dimensions	Catalog Number
Table Top box; 3.5 inch diameter hole; (1) pre-wired 15A outlet with 9 foot power supply cord; (1) 3.5mm screw terminal audio jack; (1) 15-pin gender changer F/F; (2) keystone openings; Keystone modules sold separately.	Black Anod. Alum.	3.88" Diameter	<b>TTBDS1BK</b>
	Clear Anod. Alum.		<b>TTBDS1AL</b>
	Solid Brass		<b>TTBDS1BR</b>
Table Top box; 3.5 inch diameter hole; (2) pre-wired 15A outlets with 9 foot power supply cord; (2) keystone openings; Keystone modules sold separately.	Black Anod. Alum.	3.88" Diameter	<b>TTBDS2BK</b>
	Clear Anod. Alum.		<b>TTBDS2AL</b>
	Solid Brass		<b>TTBDS2BR</b>



TTBDS1BK



TTBDS2BK

Note: See section A for power devices and section Y for datacom accessories.