

Panelboards

A-Series™ II Panelboards

Pro-Stock, Unassembled Lighting Panels

Section 11

④ Select Main and/or Sub-feed Breaker Kit

Select main breaker kit appropriate for your interior type (see Step 1), amp rating and kAIC rating. If a sub-feed breaker is required, repeat the selection process.

Note: 400A and 600A breaker kits cannot be used for sub-feed applications in Pro-Stock panelboards.

For additional details, see Section 6 of the BuyLog.

Interior Type	Product Number ¹	Rating Amps	No. of Poles	Breaker Rating (kAIC)							
				10	14	22	25	65	100	200	
AQU1: 240 VAC 1 Phase	MB612	100	2	THQB		THHQB					
	MB614	100	4	(2) THQB		(2) THHQB					
	MB512	225	2	TQD		THQD					
	MB332	400	2					SGHA	SGLA	SGPA	
	MB331WB	400	3					SGDA+Kit			
	MB335WB	400	2					SGDA+Kit			
	MB334WB	400	3					SGDA+Kit			
	MB336WB	400	2					SGDA+Kit			
	MB332	600	2					SGHA	SGLA	SGPA	
	MB332WB	600	2					SGHA+Kit			
AQU3: 208/120 VAC, 3 Phase	MB613	100	3	THQB		THHQB					
	MB616	100	6	(2) THQB		(2) THHQB					
	MB513	225	3	TQD		THQD					
	MB516	400	6	(2) TQD		(2) THQD					
	MB233	225	3					SFHA	SFLA	SFPA	
	MB233WB	225	3					SFHA+Kit			
	MB2332 ⁵	400	6 ⁵					2nd SFHA			
	MB2332WB ⁵	400	6 ⁵					2nd SFHA+Kit			
	MB333	400	3					SGHA	SGLA	SGPA	
	MB331WB	400	3					SGDA+Kit			
	MB335WB	400	2					SGDA+Kit			
	MB334WB	400	3					SGDA+Kit			
	MB336WB	400	2					SGDA+Kit			
	MB333	600	3					SGHA	SGLA	SGPA	
		MB333WB	600	3					SGHA+Kit		
AEU3: 480/277 Vac, 3 Phase	MB423	100	3		TEY						
	MB426	100	6		(2) TEY						
	MB133	150	3		TED ²	THED					
	MB133	150	3			SEHA	SELA	SEPA			
	MB133WB	150	3			SEHA+Kit					
	MB233	225	3			SFHA ⁴	SFLA	SFPA			
	MB233WB	225	3			SFHA+Kit ⁴					
	MB2332 ⁵	400	6 ⁵			2nd SFHA ⁴					
	MB2332WB ⁵	400	6 ⁵			2nd SFHA+Kit ⁴					
	MB333	400	3			SGHA ⁴	SGLA	SGPA			
	MB334WB	400	3			SGDA+Kit					
	MB336WB	400	2			SGDA+Kit					
	MB333	600	3			SGHA ⁴	SGLA	SGPA			
		MB333WB	600	3			SGHA+Kit ⁴				


¹Breaker not included except for "WB" kits (where product number ends in "WB"). "WB" kits include a breaker, mounting kit and load-side lugs. Rating plugs must be ordered separately.

²Actual breaker rating is 18kAIC.


³Actual breaker rating is 30kAIC.

⁴Actual breaker rating is 35kAIC.


⁵To achieve 6 poles of subfeed, the MB233WB or MB233 kit is also required. 6 poles of subfeed only work with 400A and 600A interiors.



MB513 Breaker Kit



MB516 6-Pole Breaker Kit



MB233WB "WB" Breaker Kit

