

## Multi-Purpose Cable Ties

- General purpose cable tie for every day bundling and cable management
- UL recognized



Size	Thickness X Width (in.)	Color	Tensile Strength (lbs.)	Pkg. Qty.	Cat. No.
<b>Miniature Ties</b>					
4"	.039 x .095	Natural	18	100	B-4-18-9-C
4"	.039 x .095	UV Black	18	100	B-4-18-0-C
<b>Intermediate Ties</b>					
6"	.047 x .142	Natural	40	100	B-6-40-9-C
6"	.047 x .142	Natural	40	1000	B-6-40-9-M
6"	.047 x .142	UV Black	40	100	B-6-40-0-C
<b>Intermediate Ties</b>					
8"	.053 x .178	Burgundy	50	100	B-8-50-35-C
11"	.053 x .178	Burgundy	50	100	B-11-50-35-C
<b>Standard Ties</b>					
8"	.057 x .181	Natural	50	100	B-8-50-9-C
8"	.057 x .181	Natural	50	1000	B-8-50-9-M
8"	.057 x .181	UV Black	50	100	B-8-50-0-C
8"	.057 x .181	UV Black	50	1000	B-8-50-0-M
11"	.057 x .181	Natural	50	100	B-11-50-9-C
11"	.057 x .181	Natural	50	500	B-11-50-9-D
11"	.057 x .181	UV Black	50	100	B-11-50-0-C
11"	.057 x .181	UV Black	50	500	B-11-50-0-D
14"	.057 x .181	Natural	50	100	B-14-50-9-C
14"	.057 x .181	Natural	50	500	B-14-50-9-D
14"	.057 x .181	UV Black	50	100	B-14-50-0-C
14"	.057 x .181	UV Black	50	500	B-14-50-0-D
<b>Heavy-Duty Ties</b>					
14"	.066 x .299	Natural	120	50	B-14-120-9-C
14"	.066 x .299	UV Black	120	50	B-14-120-0-L
24"	.066 x .299	Natural	175	50	B-24-175-9-L
24"	.066 x .299	UV Black	175	50	B-24-175-0-L
36"	.066 x .299	Natural	175	50	B-36-175-9-L
48"	.066 x .299	Natural	175	50	B-48-175-9-L

Size	Thickness X Width (in.)	Color	Tensile Strength (lbs.)	Pkg. Qty.	Cat. No.
<b>Mounting Ties</b>					
8"	.057 x .189	Natural	50	100	B-8-50MT-9-C
8"	.057 x .189	UV Black	50	100	B-8-50MT-0-C
14"	.053 x .178	Natural	50	100	B-14-50MT-9-C
<b>Mounting Pads</b>					
3/4" x 3/4"	.142 Max. Tie Width	Natural	N/A	100	BMP-750-9-C
1" x 1"	.189 Max. Tie Width	Natural	N/A	100	BMP-1000-9-C

## Wire Marker Booklets

- Self-sticking on wire and cable
- Perforated 1/4" x 1-1/2" markers
- For applications above or below ground
- Resists abrasion, moisture, dirt and oil
- Non-smear black legend ensures high visibility



Legend	Qty.	Cat. No.
0-9	45 Markers each	<b>775101</b>
A-Z, 0-15, +, -, /	10 Markers each	<b>775102</b>
1-45	10 Markers each	<b>775103</b>
46-90	10 Markers each	<b>775104</b>

Ten pages per booklet with each page bearing the legend assortment indicated. All booklets contain 450 wire and terminal markers.