



Mogul Bodies, Covers and Gaskets

Condulet® Conduit Bodies – Cast Iron or Aluminum

Applications:

Mogul bodies are installed in conduit systems to:

- Act as pull outlets for conductors that are stiff, due to large size or type of insulation
- Provide the longer openings needed when pulling large conductors
- Prevent sharp bends and kinks in large conductors (protects insulation during installation)
- Provide ample openings for splices and taps
- Provide access to wiring for maintenance and future system changes

Features and Benefits:

Mogul bodies have:

- Long openings
- Provision for easy bends
- Taper tapped hubs with integral bushings
- Stainless steel cover screws
- Covers are provided with integral gasket
- **NEW!** Pre-installed rollers on select shapes and sizes (LB and C shapes 1-½" to 4") to aid in wire pulling (available in iron only)
- **NEW!** SnapPack™ option - completely assembled with cover, gasket and captive stainless steel screws

Certifications and Compliances:

- UL Standard: 514B
- Fed. Spec.: W-C-586d
- CSA Standard: C22.2 No. 18

Standard Material:

- Feraloy® iron alloy

Standard Finish:

- Feraloy® - electrogalvanized and aluminum acrylic paint

Options:

Suffix

- Material – copper-free aluminum **SA**
- Hot dipped galvanized..... **HDG**
- Rollers installed (available in iron only)... **WR**
- SnapPack™ assembly **CG**

Ordering Information – Blank Replacement Covers:



Feraloy® Iron Alloy

Size	With Round Neoprene Gasket Cat. #
1" or 1-¼"	BG48
1-½" or 2"	BG68
2-½" or 3"	BG88
3-½" or 4"	BG98

B Series Moguls from Eaton's Crouse-Hinds Business are now available with rollers and an optional SnapPack™ assembly.



Ordering Information — Moguls:

BC



Mogul Series

Size	Cat. #
1"	BC3
1-¼"	BC4
1-½"	BC5
2"	BC6
2-½"	BC7
3"	BC8
3-½"	BC9
4"	BC10

BLB†



Mogul Series

Size	Cat. #
1"	BLB3
1-¼"	BLB4
1-½"	BLB5
2"	BLB6
2-½"	BLB7
3"	BLB8
3-½"	BLB9
4"	BLB10

†For 5" size, use LBD012. For 6" size, use LBD014.

BUB



Mogul Series

Size	Cat. #
1"	BUB3
1-¼"	BUB4
1-½"	BUB5
2"	BUB6
2-½"	BUB7
3"	BUB8
3-½"	BUB9
4"	BUB10

BT



Mogul Series

Size	Cat. #
1"	BT3
1-¼"	BT4
1-½"	BT5
2"	BT6
2-½"	BT7
3"	BT8
3-½"	BT9
4"	BT10