



CAT#	A	B	SCREW SIZE
571	3.875	1.310	8/32 X 3/8
572	4.625	1.520	8/32 X 3/8
573	5.315	1.710	8/32 X 3/8
574	7.240	2.510	12/24 X 3/8
576	9.484	3.110	12/24 X 3/8
577	12.187	4.440	5/16 X 3/8
579	14.937	5.500	5/16 X 3/8

CAT#	A	B	SCREW SIZE
571P	3.875	1.310	8/32 X 3/8
572P	4.625	1.520	8/32 X 3/8
573P	5.315	1.710	8/32 X 3/8
574P	7.240	2.510	12/24 X 3/8
576P	9.484	3.110	12/24 X 3/8
577P	12.187	4.440	5/16 X 3/8
579P	14.937	5.500	5/16 X 3/8

CAT#	A	B	SCREW SIZE
571S	3.875	1.310	8/32 X 3/8
572S	4.625	1.520	8/32 X 3/8
573S	5.315	1.710	8/32 X 3/8
574S	7.240	2.510	12/24 X 3/8
576S	9.484	3.110	12/24 X 3/8
577S	12.187	4.440	5/16 X 3/8
579S	14.937	5.500	5/16 X 3/8



CAT#	A	B
581	3.935	1.360
582	4.600	1.550
583	5.370	1.760
584	7.250	2.500
586	9.500	3.070
587	12.125	4.355
589	14.812	5.400



CAT#	A	B	C
LB1M	4.56	2.06	1.31
LB2M	5.31	2.37	1.48
LB3M	6.25	2.63	1.75
LB4M	8.22	3.50	2.40
LB5M	8.22	3.75	2.40
LB6M	10.48	4.31	3.05
LB7M	13.75	4.45	4.38
LB8M	13.75	4.45	4.38
LB9M	16.75	5.80	5.63
LB10M	16.75	5.80	5.63

CONDUIT BODY COVERS

WITH SCREWS

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	ALUMINUM WT/ CASE
571	15450	1/2"	25	250	15
572	15460	3/4"	25	250	20
573	15470	1"	10	100	9
574	15480	1 1/4"-1 1/2"	—	25	4
576	15490	2"	—	25	7
577	15500	2 1/2"-3"	—	10	8
579	15510	3 1/2"-4"	—	5	7



E195124

PAINTED

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	PAINTED WT/ CASE
571P	51160	1/2"	25	250	17.5
572P	51177	3/4"	25	250	22.5
573P	51184	1"	10	100	10
574P	51191	1 1/4"-1 1/2"	25	25	4.25
576P	51207	2"	25	25	6.25
577P	51214	2 1/2"-3"	10	10	7.20
579P	51221	3 1/2"-4"	5	5	9.5



E195124

STEEL ZINC PLATED

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	STEEL ZINC PLATED WT/ CASE
571S	15520	1/2"	25	250	15
572S	15530	3/4"	25	250	20
573S	15540	1"	10	100	8
574S	15550	1 1/4"-1 1/2"	—	25	4
576S	15560	2"	—	25	7
577S	15570	2 1/2"-3"	—	10	7
579S	15580	3 1/2"-4"	—	5	9



E195124

CONDUIT BODY GASKETS

NEOPRENE

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	NEOPRENE WT/ CASE
581	15710	1/2"	50	500	1
582	15720	3/4"	50	500	1
583	15730	1"	25	500	2
584	15740	1 1/4"-1 1/2"	25	500	2
586	15750	2"	25	250	2
587	15760	2 1/2"-3"	10	100	2
589	15770	3 1/2"-4"	5	50	2



E195124

All Covers and Gaskets fit LB, LL, LR, C and T's, Aluminum and Malleable, Set Screw and Rigid Bodies

CONDUIT BODIES

RIGID THREADED TYPE

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	MALLEABLE IRON WT/ CASE
LB1M	20940	1/2"	—	10	7
LB2M	20950	3/4"	—	10	9
LB3M	20960	1"	—	5	6
LB4M	20970	1 1/4"	—	5	23
LB5M	20980	1 1/2"	—	10	26
LB6M	20990	2"	—	5	26
LB7M	21000	2 1/2"	—	1	10
LB8M	21010	3"	—	1	13
LB9M	21020	3 1/2"	—	1	22
LB10M	21030	4"	—	1	24



E195124