



## DUCT SPACERS

### FEATURES

- Integral holes offering base spacer fastening & stabilization
- Molded rebar slots allowing quick & efficient installation of full length rebar


PRODUCT INFORMATION BULLETIN

Kraloy offers a wide range of duct spacers to suit all your underground needs. Our duct spacers offer consistent operation, stability and relieve direct stress for duct materials that have to be encased in concrete.



Interlocking Spacer Assembly Dimensions

Dimension (in)	A	A1	B	B1
2 x 1-1/2	1-1/2	3	3-15/16	4-7/32
2 x 2	2	3	4-7/16	4-7/32
2 x 3	3	3	5-7/16	4-7/32
3 x 2	2	3	5-5/8	4-25/32
4 x 2	2	3-1/16	6-5/8	5-3/8
4 x 3	3	3-1/16	7-5/8	5-3/8
5 x 2	2-3/16	3-3/16	7-13/16	6
5 x 3	3-3/16	3-3/16	8-7/8	6



**KRALOY®**  
The Fitting Choice

Toll Free: (800) 265-1815



Direct: (519) 681-2140

[www.kraloyfittings.com](http://www.kraloyfittings.com)

Products are manufactured by IPEX Electrical Inc. and distributed by Kraloy, a division of Multi Fittings Corp.

Kraloy® is a trademark of Multi Fittings Corp.


Recommended  
Distance:  
6' - 7'



Utility Duct Spacers\*

Dimension (in)	A	B	E	F
3 x 1-1/2	5.130	4.615	3,000	1.50
3 x 3	6.630	4.615	3,000	3.00
4 x 1	5.630	4.060	1,750	1.00
4 x 1-1/2	6.130	5.315	3,000	1.50
5 x 1-1/2	7.325	6.900	3,000	1.50
6 x 1-1/2	8.230	6.375	3,000	1.50


\* Do not have rebar slots or base holes



Intermediate Vertical-Lok Spacers

Dimension (in)	Part Number	Product Code	Std Package
2 x 1-1/2	IV2015	029550	200
2 x 2	IV2020	029551	200
2 x 3	IV2030	029552	150
* 3 x 1-1/2	IV3015	029553	250
3 x 2	IV3020	029554	100
3 x 3	IV3030	029555	160
* 4 x 1	IV4010	029556	250
4 x 1-1/2	IV4015	029557	180
4 x 2	IV4020	029558	100
4 x 3	IV4030	029559	60
* 5 x 1-1/2	IV5015	029560	140
5 x 2	IV5020	029561	60
5 x 3	IV5030	029562	60
6 x 1-1/2	IV6015	029563	100
6 x 2	IV6020	029564	100
6 x 3	IV6030	029565	40
* 8 x 2	IV8020	029294	60

\* Do not have rebar slots or base holes



Base Vertical-Lok Spacers

Dimension (in)	Part Number	Product Code	Std Package
2 x 1-1/2	BV2015	029566	150
2 x 2	BV2020	029567	150
2 x 3	BV2030	029568	100
* 3 x 1-1/2	BV3015	029569	250
3 x 2	BV3020	029570	100
3 x 3	BV3030	029571	190
* 4 x 1	BV4010	029572	250
4 x 1-1/2	BV4015	029573	180
4 x 2	BV4020	029574	80
4 x 3	BV4030	029575	60
* 5 x 1-1/2	BV5015	029576	140
5 x 2	BV5020	029577	60
5 x 3	BV5030	029578	50
6 x 1-1/2	BV6015	029579	100
6 x 2	BV6020	029580	100
6 x 3	BV6030	029581	40
* 8 x 2	BV8020	029293	50

\* Do not have rebar slots or base holes