




S70-830 White
Inside Elbow
 Packing: 144/Master, 12/Inner




S70-832 White
Outside Elbow
 Packing: 144/Master, 12/Inner



S70-829 White
Straight Coupling
 Packing: 144/Master, 12/Inner



S70-831 White
Flat Elbow
 Packing: 144/Master, 12/Inner



S70-827
 40" Brass
 Packing: 24/Master

S70-826
 40" White
 Packing: 24/Master

A COMPLETE DO-IT-YOURSELF SELF STICKING WIRE COVER SYSTEM

For:

- Wall lamps
- Telephones
- Track lighting
- Speaker wire
- Extension cords
- Home alarm systems
- CATV cable
- Television wire
- Ceiling swag lighting
- Stereo and VCR

Wire covers available in white and brass.
 Couplings, available in white and can be painted.


Splice Connector for Ballast Disconnect



90-2536

2 Piece Snap Together Connector for Solid or Tinned Tip Wire - 18 AWG (Female Housing) 12/14 AWG (Male Housing)

Splice Connector Instructions



Provides fast & easy disconnect/connect of hot & neutral wires, reducing shock hazard during ballast replacement.

Wing Nut Wire Connectors with Spring Inserts for 105°C Supply Wire 600V



90-2237
Yellow
4 #18 Max.



90-2238
Tan
9 #18 Max.



90-2239
Red
5 #16 Max.



90-2240
Grey
4 #12 Max.



90-2241
Blue
4 #10 Max.

Wire Connectors with Spring Inserts for 105°C Supply Wire 300V



90-1418
High Heat
Black
2 #18 Max.



90-1419
Medium
Orange
5 #18 Max.



90-1440
Large
Yellow
6 #18 Max.



90-1421
Extra Large
Red
8 #18 Max.

Porcelain Wirenuts High Heat 300V



90-1311
Small
2 #18 Max.



90-1312
Medium
4 #18 Max.



90-1313
Large
6 #18 Max.

Plastic Wirenuts for 105°C Supply Wire 300V



90-396
Ext. Small
2 #18 Max.



90-469
Small
4 #18 Max.



90-470
Medium
5 #18 Max.



90-1420
Electrical Tape
3/4" x 60 ft.

Assorted *Nylon • Metal • Plastic*

WIRE, CORDS & ACCESSORIES

Nylon Snap-In Bushings



90-157
for 5/16" Hole
Black



90-158
for 3/8" Hole
Black



90-161
for 7/16" Hole
Black



90-180
for 7/16" Hole
Gold

Metal Strain Reliefs



90-1158
Small



90-998
Small
with Tab



90-1159
Large
with Tab

Plastic Pipe Bushings



90-1422
1/8 IP



90-1423
1/4 IP

Plastic Bushings



90-327
1/8 IP
Male / White



90-328
1/8 IP
Male / Black



90-321
1/8 IP
Female / White



90-322
1/8 IP
Female / Black



90-325
1/4 IP
Male / White



90-326
1/4 IP
Male / Black



90-323
1/4 IP
Female / White



90-324
1/4 IP
Female / Black