



CXL




Consumers Digest's
"BEST BUY"

CXL52AB with B5/52S-WB6 and LKE116
Antique Brass CXL and light kit with Walnut blades.

MODEL CXL52

DIMENSIONS



A (2" DR) – 11³/₈ C – 11¹/₂
A (6" DR) – 15³/₈ D – 5¹/₈
B (2" DR) – 9¹/₂ E – 4¹/₂
B (6" DR) – 13¹/₂

All Craftmade fans are shipped with two down rods, a 2" for mounting close to the ceiling, a 6" rod for mounting farther away.


WARRANTY

Limited Lifetime Warranty

SPECIFICATIONS

Blade Sweep – 52" or 56"
of Blades – 5
Blade Pitch – 14°
Motor Size – 188 x 15
AMPS (HI Speed) – .70
Watts (HI Speed) – 80
RPM (HI/MED/LO) – 210/120/78
CFM (HI Speed) – 7680

STANDARD OPERATION



FINISHES

Almond, Antique Brass, Antique White, Bronze, Bronze,
Brownstone, Brushed Nickel, English Toffee, European Bronze,
Flat Black, Galvanized, Graystone, Mocha, Moroccan Gold,
Old Iron, Pearl Essence, Pewter, Polished Brass, Rust, Rustic Iron,
Sandstone White, Textured White, Verde Green, White,
White Brass, Oiled Bronze, Aged Bronze, Burnt Sienna,
Saddle Leather



The CXL® Collection

Our most popular 14° pitch fan, the CXL Series incorporates our heavy duty motor in a seamless steel housing, giving you outstanding performance and quality. It features a traditional fan style in a variety of finishes.

- DECORATIVE FLANGE COVER
- HEAVY DUTY 188 X 15MM MOTOR
- 3-SPEED, REVERSIBLE
- 52" BLADE SPAN WITH 14° PITCH; WILL ACCEPT 56"
- BLADES MATCHED TO EXACT WEIGHT
- TWO DOWNRODS SUPPLIED, 2" AND 6"
- LIGHT KIT ADAPTABLE
- LIFETIME LIMITED WARRANTY
- BOTH TCS CONTROLS AVAILABLE
- ENERGY STAR CERTIFIED
- SEAMLESS HOUSING



TCS and TCS+ Controls Available



CXL52RT B5/52S-DO4
Rust finish with custom wood Dark Oak blades.

• HI RES •
• LO RES •



CXL52OB B5/52S-WWB
Oiled Bronze finish with Washed Walnut Birch blades.

• HI RES •
• LO RES •



CXL52PB B5/52S-LOK
Polished Brass with light kit (LK8-PB) and Light Oak blades.

• HI RES •
• LO RES •



CXL52AW B5/52S-BW10
Antique White finish with Custom Barnwood Blades.

• HI RES •
• LO RES •



CXL52BR B5/52S-DO4
Brown finish with custom wood Dark Oak blades.

• HI RES •
• LO RES •



CXL52BN B5/52L-BN
Brushed Nickel finish with light kit (LKE53 BN) and Brushed Nickel Limited blades.

• HI RES •
• LO RES •

Note: Fans and Blades are Sold Separately. [Page 1](#), [2](#), [3](#), [4](#), [5](#)

Craftmade International, Inc.

[Contact Us](#)

[Product Support](#)