

Accessories - Overload¹


Class 10 - Overload

Current Range	Maximum Fuse	Maximum Circuit Breaker Rating Amps	Product Number
0.16-0.26	1	15	RT1B
0.25-0.41	1	15	RT1C
0.4-0.65	3	15	RT1D
0.65-1.1	6	15	RT1F
1-1.5	6	15	RT1G
1.3-1.9	6	15	RT1H
1.8-2.7	10	15	RT1J
2.5-4.1	15	15	RT1K
4-6.3	20	15	RT1L
5.5-8.5	25	15	RT1M
8.0-12.0	40	30	RT1N
10.0-16.0	50	35	RT1P
14.5-18	60	40	RT1S
17.5-22	70	50	RT1T
21-26	80	60	RT1U
25-32	100	80	RT1V
30-40	100	80	RT1W

¹Factory assembled DP starters (CR554 series) are available. Please refer to the Control catalog, GEP-1260 for more information.

Class 20 - Overload

Current Range	Maximum Fuse	Maximum Circuit Breaker Rating Amps	Product Number
2.5-4.1	15	15	RT12K
4-6.3	20	15	RT12L
5.5-8.5	25	15	RT12M
8.0-12.0	40	30	RT12N
10.0-16.0	50	35	RT12P
14.5-18	60	40	RT12S
17.5-22	70	50	RT12T
21-26	80	60	RT12U
25-32	100	80	RT12V
30-40	100	80	RT12W



Overload Relay

Accessories – Auxiliary Contact Kits

Type	Mounting	Circuit	Product Number	Rating
250 VAC Auxiliary Contact	Side	1 SPDT	CR553XC211	11 A, 1/3 HP at 250 VAC; 1/2 A at 125 VDC; 1/4 A at 250 VDC
	Side	2 SPDT	CR553XC222	
600 VAC Auxiliary Contact	Front	1 NO	BCLF10	A600, Q600 Pilot Duty
	Front	1 NC	BCLF01	
	Side	1 NO, 1 NC	BCLL11	
	Side	2 NO	BCLL20	
Mechanical Interlock ²	-	2 NC	BEL02 includes 2 built-in NC contacts	A600, Q600 Pilot Duty

²Factory assembled DP 2-speed contactors (CR555 series) are available. Please refer to the Control catalog, GEP-1260 for more information.

Spare Coils

Coil Voltage	Product Number	
	2/3 Pole 25-30FLA	2/3 Pole 40FLA 4 Pole 25-40FLA
110-120V 50/60Hz	CRDB1AA	CRDB3AA
208-240V 50/60Hz	CRDB1AB	CRDB3AB
440-480V 60Hz	CRDB1AC	CRDB3AC
380-415V 50Hz		
550-600V 50/60Hz	CRDB1AD	CRDB3AD
12V 50/60Hz	CRDB1AE	CRDB3AE
277V 60Hz	CRDB1AF	CRDB3AF
24V 50/60Hz	CRDB1AH	CRDB3AH

Enclosure Kits NEMA Type 1

Contactor Prefix	Device	Rating	Product Number
CR553A	DP Contactors	25A-40A, 2-4 Pole	CR553XE1A
CR554A	DP Starters	25A-30A	CR553XE1A
CR554A	DP Starters	40A	CR553XE1B




250V Auxiliary Contact Kits



Side-Mount 600V Auxiliary Contact Block



Front-Mount 600V Auxiliary Contact Block



Mechanical Interlock



Enclosure Kit