



Ceiling Cutout: 8" (203 mm) Dia.

Shown with 8022 trim kit

Frame-In Kit		Compatible Reflector Trims	
S7142BU	Electronic 120V-277V 26, 32, or 42W Triple Tube 4-Pin (Amalgam)	Downlights	Wall Washers
		8022 Open, Vertical Lamping	8022WW Open, Single, Vertical Lamping
		8037 Open, Horizontal Lamping	8022DW Open, Double, Vertical Lamping
		8097 Lensed, Horizontal Lamping	8022CW Open, Corner, Vertical Lamping
		8097CB Cross Blade, Horizontal Lamping	8087 Open, Horizontal Lamping
		8097TB Parabolic Louver, Horizontal Lamping	8047 Lensed

Features

- Socket Cup:** Snaps onto reflector neck to assure consistently correct optical alignment without tools.
- Mounting Frame:** Galvanized stamped steel for dry or plaster ceilings.
- Retaining Springs:** Precision-tooled steel friction springs secure reflector to mounting frame for quick, tool-less installation.
- Mounting Brackets:** Galvanized steel. Adjust from inside of fixture. Use 3/4" or 1 1/2" lathing channel, 1/2" EMT, or optional mounting bars.
- Ballast/J-Box:** Electronic 120V - 277V. UL listed for through branch circuit wiring with max of (8) No. 12 AWG, 90°C supply conductors. Outboard mounted to reduce heat transfer and maintain lamp efficacy and life. Service from below without tools.

Note: For ballast electrical data and latest lamp/ballast compatibility refer to "Ballast" specification sheet for complete electrical data.

Options & Accessories

S7142BU 7" aperture, 1 lamp 26/32/42W Triple Tube CFL (120/277V)
4-Pin (Amalgam)

Dimming Options:

- S7142B**
- CU3** Lightolier PowerSpec 3% Dimming (120/277V)
J1LD3 Lutron 3% Dimming (120V) **J2LD3** Lutron 3% Dimming (277V)
JUM7 Mark 7 Dimming (120/277V) **J1MX** Mark 10 Dimming (120V)
J2MX Mark 10 Dimming (277V)

Other dimming product available, please consult factory

Options & Accessories (continued)

- Mounting Bars:** **1950** - 18" Set of (2)
 1951 - 27" Set of (2)
- T-Bar Anchor Clips:** **1956** - Set of (4), for use with above
- Slope Ceiling Adapter:** **7926** Series, (See specification sheet SCA)

Labels

UL, CUL listed for damp locations

Job Information	Type:
Job Name:	
Cat. No.:	
Lamp(s):	
Notes:	

631 Airport Road, Fall River, MA 02720 • (508) 679-8131 • Fax (508) 674-4710
 We reserve the right to change details of design, materials and finish.
 www.lightolier.com © 2008 Philips Group • A0708