Applications

- Boxes are installed in ceilings or walls for lighting fixtures, switches or receptacles
- Square boxes are used where multiple conductor runs are split into two or more directions to bring power to a number of electrical devices
- Drawn boxes are ideal for exposed work applications

Product Features

- · Combination screw heads provide for faster installation
- Thru-the-wall box is designed for shallow wall applications and allows for attachment of wall plate to both faces of box
- TKO® knockouts offer greater flexibility with RACO® patented combination 1/2" and 3/4" knockout
- TKO® knockouts allow for design and installation flexibility


Compliances

(**U**) - File E195978

All RACO® single gang, two gang, 4" square, and single gang gangable U.L. listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult U.L. "Fire Resistance Directory" or the U.L. website at www.ul.com

Per U.L. 514-A, suitable for use without a bonding jumper in circuits above or below 250 volts

4" SQUARE BOXES











190, 8190





204

192, 8192

189, 8189

181

ORDERING INFORMATION - DIMENSIONS

4" SQUARE - 1-1/4" DEEP - DRAWN With Conduit Ko's - 18.0 cubic inches						
CATALOG NUMBER	DESCRIPTION BRACKET & SETBACK	SIDES COND.	NOCKOUTS BOTTOM COND.	STD. PKG.	UPC BAR CODE	
185	_	10-1/2"	5-1/2"	50		

4" SQUARE - 1-1/2" DEEP - DRAWN WITH CONDUIT KO'S - 21.0 CUBIC INCHES						
CATALOG NUMBER	DESCRIPTION BRACKET & SETBACK	SIDES COND.	NOCKOUTS BOTTOM COND.	STD. PKG.	UPC BAR CODE	
190	_	12-1/2"	5-1/2"	50	_	
8190	_	12-1/2"	5-1/2"	50	IIIIIII	
191	_	8-3/4"	1-1/2", 4-3/4"	50	_	
8191	_	_	_	25		
192	_	8-1/2" 4-3/4"	3-1/2", 2-3/4"	50	_	
8192	_	_	_	50	WINNI	

	4" SQUARE - 1-1/2" DEEP - WELDED With Conduit Ko's - 21.0 cubic inches							
	0.0 1.4 4.0	DESCRIPTION	KNOCKOUTS		CTD	UPC		
	CATALOG NUMBER	BRACKET & SETBACK	SIDES COND.	BOTTOM COND.	STD. PKG.	BAR CODE		
٧	189	_	8-1/2" 4-TKO®	3-1/2", 2-TK0®	50	_		
٧	8189	_	_	_	50			
Ī	181	_	8-3/4"	1-1/2", 4-3/4"	50	_		

4" SQUARE - THRU-THE-WALL BOX - 1-1/2" DEEP - DRAWN With Conduit Ko's - 22.5 cubic inches						
CATALOG NUMBER	DESCRIPTION BRACKET & SETBACK	KNOCKOUTS SIDES BOTTOM COND. COND.		CU. STD. UPC BAR CODE		BAR
204	_	8-1/2", 4-3/4"	_	21	50	_

DIMENSIONS							
CATALOG NUMBER	А	В	С				
185	1-1/2"	_	_				
190, 8190	1-1/2"	_	_				
191, 8191	1-1/2"	_	_				
192, 8192	1-1/2"	_	_				
189, 8189	1-1/2"	_	_				
181	1-1/2"	_	_				
204	1-1/2"	_	_				