

Accessories

Single Circuit Track

Elco Single Circuit Track is UL/CUL listed, 120V, 20 amp circuit and is solid, safe and easy to use, with quality recognized throughout the lighting industry. For use in residential, commercial and retail applications.

Size

Track is only 5/8" deep and 1 3/8" wide.

Finishes

Track is available in four finishes: White, Black, Bronze and Brushed Nickel.

Connectors



Connectors simply push into the ends of the Track, eliminating splicing. L's, T's, X's and Flexible Connector allow track to be assembled in almost any pattern.

Grounding

To ensure safe operation the entire track system is fully polarized and grounded. Grounding is accomplished automatically by a separate solid copper ground conductor in the track. The ground conductor maintains continuity to the building's grounding system through the ground contact fingers in each of the connectors.

Specifications


The structural channel is extruded aluminum with 0.060" nominal wall thickness. Conductors are solid copper buss bars encased in rigid extruded PVC insulators.



Single Circuit Accessories

Single Circuit Accessories

B = Black Finish BZ = Bronze Finish N = Nickel Finish W = White Finish



One Circuit Track

EP002B, BZ, N, W

2' Track

EP004B, BZ, N, W

4' Track

EP006B, BZ, N, W

6' Track

EP008B, BZ, N, W

8' Track

EP012B, W

12' Track



Live End Connector

EP801W, B, BZ, N



Flexible Connector

EP802W, B, BZ, N




Straight Connector

EP803W, B, BZ, N



"L" Connector

EP804W, B, BZ, N



"T" Connector

EP805W, B, BZ, N



"X" Connector

EP806W, B, BZ, N



Wire Cover

EP807W, B, BZ, N



Mini Connector

EP808W, B, BZ, N



Floating Canopy and
Feed Point

EP809W, B, BZ, N



End Feed Kit for
Outlet Box Mount

EP810W, B, BZ, N



Dead End

EP812W, B, BZ, N



Sign Hanger

EP813W, B, BZ, N



Outlet Adapter

EP814W, B, BZ, N



Pendant Adapter

EP815W, B, BZ, N

With loop for cord-hung
or chain-hung fixtures.

Accessories

Single Circuit Accessories

Single Circuit Accessories

B = Black Finish

BZ = Bronze Finish

N = Nickel Finish

W = White Finish



T-Bar Ceiling Feed

EP817W, B, N



NEW

Dead Mini Connector

EP825B, W, N



Current Limiter

EP840W-1A

1 amp

EP840B-1A

1 amp

EP840W-2A

2.5 amp

EP840B-2A

2.5 amp

EP840W-5A

5 amp

EP840B-5A

5 amp

EP840W-7A

7.5 amp

EP840B-7A

7.5 amp

EP840W-10A

10 amp

EP840B-10A


10 amp

EP840W-12A

12 amp

EP840B-12A

12 amp




NEW

Straight Channel

EP844B, W

Provides support for straight connection points in suspended track system. 16 1/4" long, track sits inside the channel.



NEW

"L" Channel

EP845B, W

Provides support for corner connection points in suspended track system. 10" long in each side, track sits inside the channel.



Cord and Plug Connector

EP850W, B, BZ, N



Pendant Quick Jack Connector

EP865N



12V 50W Quick Jack Transformer

EP868W, B 50W max.



12V 75W Quick Jack Transformer

EP869W, B 75W max.
with switch, J Style



Conduit Connector

EP880W, B, BZ, N



Power Pack

EP900B, W

50W transformer for use with Track-22 12V fixtures (p. 72-73). Install on single circuit line voltage track only.



Dimmer Switch

EP901W, B, N 150W max.
For line voltage fixtures.



Conduit Continuation Kit

EP979W, B, N

Includes (1) Left and (1) Right feed; to continue around obstructions with 1/2" surface conduit.