

4" Dia. Round Outlet:

Residential Units

Series 9350



Cu. In. Volume	Catalog Number	Component Description	D	W	Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Pkg. Wt. (lb.)
22.5	9350	Bottom mount, Speed Klamps™ – bulk packed	2-3/8	4	50 lb.	10420	50	20
22.5	9350-K*	Bottom mount, Speed Klamps™ – factory installed	2-3/8	4	50 lb.	10418	50	21

Series 9350-24



Cu. In. Volume	Catalog Number	Component Description	D	W	Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Pkg. Wt. (lb.)
22.5	9350-24	24" adj. bar hanger, Speed Klamps™ – bulk packed	2-3/8	4	50 lb.	10428	50	45
22.5	9350-24C2	24" adj. bar hanger, two wire clamps – factory installed	2-3/8	4	50 lb.	10429	50	47
22.5	9350-24K*	24" adj. bar hanger, Speed Klamps™ – factory installed	2-3/8	4	50 lb.	62244	50	46

Series 9350-24G



Cu. In. Volume	Catalog Number	Component Description	D	W	Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Pkg. Wt. (lb.)
22.5	9350-24G	24" adj. bar hanger, ground strap, Speed Klamps™ – bulk packed	2-3/8	4	50 lb.	10454	50	46
22.5	9350-24GC2	24" adj. bar hanger, ground strap, 2 wire clamps – factory installed	2-3/8	4	50 lb.	10457	50	48
22.5	9350-24GK*	24" adj. bar hanger, ground strap, Speed Klamps™ – factory installed	2-3/8	4	50 lb.	10455	50	47

9350-HFK



Cu. In. Volume	Catalog Number	Component Description	D	W	Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Pkg. Wt. (lb.)
22.5	9350-HFK	"HF" hanger, Speed Klamps™ – factory installed	2-3/8	4	50 lb.	10419	50	27

Series 9350-HL



Cu. In. Volume	Catalog Number	Component Description	D	W	Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Pkg. Wt. (lb.)
22.5	9350-HL	"HL" hanger, Speed Klamps™ – bulk packed	2-3/8	4	50 lb.	10424	50	25
22.5	9350-HLC2	"HL" hanger, 2 wire clamps – factory installed	2-3/8	4	50 lb.	10425	50	27
22.5	9350-HLK*	"HL" hanger, Speed Klamps™ – factory installed	2-3/8	4	50 lb.	62094	50	26
22.5	9350-HLGK	"HL" hanger, ground strap Speed Klamps™ – factory installed	2-3/8	4	50 lb.	10443	50	26

* Indicates model shown • See page 7 for Attachment Coding descriptions

