Reduce Downtime With Quick Access to the Right Replacement Fuse

Section Contents

	3
Fuse service kits - supplemental 41	0-411
Fuse service kits - branch circuit41	0-411
Fuse service kits - premium branch circuit 4	10-411
Large electronic fuse kit - 270	. 412
Small electronic fuse kit - 140	. 412
Electrical and electronic fuse kit 5 x 20mm fuse kit 220	412
Clip clamps & rail adapters (DIN & American)	413
Spare fuse holders, pullers, testers & cabinets Telpower® spare fuse holders 5TPH Fuse pullers FT-2 & FT-3 fuse testers SFC spare fuse cabinet	414 414 414
Fuse reducers & dummy "neutrals" Class J dimension fuses - LPJ, JKS	415
Class H & K dimension fuses NON, REN, NOS & RES	415



Bussmann

Branch Circuit Fuse Service Kit Service CCI (Class CC) Page



Fuse Service Kits

Save Time and Money with These Fuse Service Kits

Selection

These service kits are filled with the most common fuse types and sizes for the most common applications - no need to search for the right fuse, it's in the kit.

Organization

The compact and sturdy carrying case allows organizing and modifying the fuses needed to assure a proper supply is kept on hand.

Accessories

All kits come with a fuse puller for the fuses it contains. As a bonus, all kits on this page include a free wire stripper or lineman's pliers.

Supplemental



Glass Fuse Kit Catalog Number: GSK-260

Kit Contents		
(5) GMA-500mA	(5) MDL-6	(5) AGC-10
(5) GMA-1A	(5) MDL-7	(5) AGC-15
(5) GMA-2A	(5) MDL-8	(5) AGC-20
(5) GMA-3A	(5) MDL-10	(5) GMC-2A
(5) GMA-4A	(5) MDL-15	(5) GMC-5A
(5) GMA-5A	(5) MDL-20	(5) GMC-10A
(5) GMA-6A	(5) AGC-1/4	(5) MDA-5
(5) GMA-10A	(5) AGC-½	(5) MDA-10
(5) GMA-15A	(5) AGC-1	(5) MDA-12
(5) MDL-1/4	(5) AGC-1½	(5) MDA-15
(5) MDL-1/2	(5) AGC-2	(5) MDA-20
(5) MDL-1	(5) AGC-2½	(5) ABC-5
(5) MDL-1½	(5) AGC-3	(5) ABC-10
(5) MDL-2	(5) AGC-4	(5) ABC-12
(5) MDL-2½	(5) AGC-5	(5) ABC-15
(5) MDL-3	(5) AGC-6	(5) ABC-20
(5) MDL-4	(5) AGC-7	

(5) AGC-8

(1) FT-3 Fuse tester/puller (1) 6-inch Crescent® wire stripper

(5) MDL-5

Midget Fuse Kit Catalog Number: MSK-45

Kit Contents	
(3) FNM-1	(3) KTK-20
(3) FNM-2	(3) KTK-30
(3) FNM-5	(3) FNQ-5
(3) FNM-10	(3) FNQ-10
(3) FNM-15	(3) FNQ-15
(3) KTK-5	(3) FNQ-20
(3) KTK-10	(3) FNQ-30
(3) KTK-15	(1) FT-3 Fuse tester/pull

(1) 6-inch Crescent® wire stripper

Branch Circuit



Class CC Fuse Kit

Catalog Number: CCSK-45

Kit Contents

Kit Odificitis	
(3) LP-CC-5	(3) KTK-R-15
(3) LP-CC-10	(3) KTK-R-20
(3) LP-CC-15	(3) KTK-R-30
(3) LP-CC-20	(3) FNQ-R-1/2
(3) LP-CC-30	(3) FNQ-R-3
(3) KTK-R-5	(3) FNQ-R-5
(3) KTK-R-10	(3) FNQ-R-10

(1) FT-3 Fuse tester/puller

(1) 6-inch Crescent® wire stripper

Fusetron® Class RK5 250/600V Fuse Kit

Catalog Number: RK5SK-39

Kit Contents	
(3) FRN-R-10	(3) FRS-R-10
(3) FRN-R-15	(3) FRS-R-15
(3) FRN-R-20	(3) FRS-R-20
(3) FRN-R-25	(3) FRS-R-30
(3) FRN-R-30	(3) FRS-R-60
(3) FRN-R-60	(3) FRS-R-100
(3) FRN-R-100	(1) FP-2 Fuse puller
(4) NO 000 D (00 to 0	0 A files rediles"

(1) NO.263-R (60 to 30A fuse reducer) (1) NO.663-R (60 to 30A fuse reducer)

(1) 6-inch Crescent® wire stripper

Premium Branch Circuit



Low-Peak® Class RK1 250/600V Fuse Kit

Catalog Number: RK1SK-39

Kit Contents

Kit Odificitis	
(3) LPN-RK-10SP	(3) LPS-RK-10SP
(3) LPN-RK-15SP	(3) LPS-RK-15SP
(3) LPN-RK-20SP	(3) LPS-RK-20SP
(3) LPN-RK-25SP	(3) LPS-RK-30SP
(3) LPN-RK-30SP	(3) LPS-RK-60SP
(3) LPN-RK-60SP	(3) LPS-RK-100SP
(3) I PNL-RK-100SP	

(1) NO.263-R (60 to 30A fuse reducer) (1) NO.663-R (60 to 30A fuse reducer)

(1) FP-2 Fuse puller

(1) 8%-inch Crescent® lineman's pliers



Low-Peak® Class J Fuse Kit

Catalog Number: JSK-36

Kit Contents

Tere ouritorito	
(3) LPJ-3SP	(3) LPJ-25SP
(3) LPJ-5SP	(3) LPJ-30SP
(3) LPJ-6SP	(3) LPJ-40SP
(3) LPJ-10SP	(3) LPJ-50SP
(3) LPJ-15SP	(3) LPJ-60SP
(3) LPJ-20SP	(3) LPJ-100SF

(1) FP-2 Fuse puller

(1) 8%-inch Crescent® lineman's pliers

Fuse Service Kits

Supplemental/Branch Circuit



Class CC / Midget Fuse Kit

Emergency fuse kit for replacement of 1\%2" x 1\%2" (Class CC and midget) fuses in a sturdy nylon box. Cross reference makes it easy to install the correct fuse in any Class CC or midget application.

Kit Size: 10%" W x 6%" D x 1%" H

Catalog Number: NO.36

Emergency Kit Contents

-		
(2) FNQ-R-½		(2) KTK-R-1
(2) FNQ-R-1		(2) KTK-R-2
(2) FNQ-R-2		(2) KTK-R-3
(2) FNQ-R-3		(2) KTK-R-5
(2) FNQ-R-4		(2) KTK-R-6
(2) FNQ-R-5		(2) KTK-R-10
(2) FNQ-10		(2) KTK-R-15
(2) FNQ-15		(2) KTK-R-20
(2) FNQ-20		(2) KTK-R-30
(1) FP-2 Fuse	ouller	

Branch Circuit



Fusetron® Class RK5 250V Fuse Kit

Compact kit in a sturdy nylon box rugged enough to withstand field use. Extra spaces and changeable compartments make it easy to customize for your particular need.

Catalog Number: ERK-28

Service Kit Contents

(2) FRN-R-3-3/40	(2) FRN-R-40
(2) FRN-R-6-1/4	(2) FRN-R-50
(2) FRN-R-10	(3) FRN-R-60
(2) FRN-R-15	(2) FRN-R-100
(3) FRN-R-20	(2) NO.263-R Reducers
(2) FRN-R-25	(2) NO.1 Clip Clamps
(4) FRN-R-30	(2) NO.2 Clip Clamps
(2) FRN-R-35	

Premium Branch Circuit



Low-Peak® Class RK1 250V Fuse Kit

Compact kit in a sturdy nylon box rugged enough to withstand field use. Extra spaces and changeable compartments make it easy to customize for your particular need.

Catalog Number: LPRK-28

Service Kit Contents

oci vioc itit oonit	21163
(2) LPN-RK-3-%SP	(2) LPN-RK-40SP
(2) LPN-RK-6-1/SP	(2) LPN-RK-50SP
(2) LPN-RK-10SP	(3) LPN-RK-60SP
(2) LPN-RK-15SP	(2) LPN-RK-100SP
(3) LPN-RK-20SP	(2) NO.263-R Reducers
(2) LPN-RK-25SP	(2) NO.1 Clip Clamps
(4) LPN-RK-30SP	(2) NO.2 Clip Clamps
(2) LPN-RK-35SP	(1) FP-2 Fuse puller



Fuse Service Kits

Large Electronic Fuse Kit



Fuse Kit 270

Small dimension fuse assortment with 270 fuses, fuse holders, fuse blocks and fuse clips to fit most electronic equipment.

Ratings:

Volts: - 125V/250V

Catalog Number: NO.270

Assortment Contents

(5) MDL-1/8	(5) AGC-½	(5) GMA-1A
(5) MDL-1/4	(5) AGC-3/4	(5) GMA-2A
(5) MDL-½	(5) AGC-1	(5) GMA-3A
(5) MDL-¾	(5) AGC-1-½	(5) GMA-4A
(5) MDL-1	(5) AGC-2	(5) GMA-6A
(5) MDL-1-½	(5) AGC-2-½	(5) GMC-1A
(5) MDL-2	(5) AGC-3	(5) GMC-2A
(5) MDL-3	(5) AGC-4	(5) GMC-3A
(5) MDL-4	(5) AGC-5	(5) GMC-4A
(5) MDL-5	(5) AGC-6	(5) GMC-6A
(5) MDL-6	(5) AGC-7	(4) AGC-V-1/2
(5) MDA-8	(5) AGC-8	(4) AGC-V-1
(5) MDA-10	(5) ABC-10	(4) AGC-V-2
(5) MDA-15	(5) ABC-15	(4) AGC-V-3
(5) MDA-20	(5) ABC-20	(4) MDL-V-½
(5) MDA-30	(5) ABC-30	(4) MDL-V-1
(5) AGC-1/8	(5) GMA-250mA	(4) MDL-V-2
(5) AGC-1/4	(5) GMA-500mA	(4) MDL-V-3
(2) Dr. 4121 Euro	olino	

- (2) Pr. 4121 Fuse clips
- (2) HHB Inline fuse holder(1) HTB-26I panel mount fuse holder
- (1) HTB-28M panel mount fuse holder
- (1) S-8202-2 Two-pole fuse block

Small Electronic Fuse Kit



Fuse Kit 140

Small dimension fuse kit with 140 fuses, fuse holders, fuse blocks and fuse clips to fit most electronic equipment.

Ratings:

Volts: - 125V/250V

Catalog Number: NO.140

Assortment Contents

A3301 tilletti	Contents
(5) MDL-½	(5) AGC-1-½
(5) MDL-1	(5) AGC-2
(5) MDL-1-½	(5) AGC-3
(5) MDQ-2	(5) MTH-4
(5) MDQ-3	(5) MTH-5
(5) MDQ-4	(5) MTH-6
(5) MDQ-5	(5) MTH-7
(5) MDQ-6	(5) MTH-8
(5) MDA-8	(5) ABC-10
(5) MDA-10	(5) ABC-15
(5) MDA-15	(5) ABC-20
(5) MDA-20	(5) ABC-30
(5) MDA-30	(2) Pr. #4121 Fuse clips
(5) AGC-1/4	(2) HHB Inline fuse hold
(5) AGC-½	(1) FP-A3 Fuse puller
(5) AGC-1	

Electrical and Electronic Fuse Kit



5 x 20mm Fuse Kit 220

A complete assortment of 125V and 250V 5 x 20mm fuses for the repair of both electrical and electronic devices.

Ratings:

Volts: - 125V/250V

Catalog Number: NO.220

Assortment Contents

(5) GDA-6.3	(5) GMD-200mA
(5) GDB-630mA	(5) GMD-500mA
(5) GDB-2	(5) GMD-1
(5) GDB-3.15	(5) GMD-1.6
(5) GDB-4	(5) GMD-2
(5) GMC-500mA	(5) GMD-3
(5) GMC-750mA	(5) GDC-250mA
(5) GMC-1	(5) GDC-500mA
(5) GMC-2	(5) GDC-1
(5) GMC-2.5	(5) GDC-1.6
(5) GMC-3	(5) GDC-2
(5) GMC-3.15	(5) GDC-3.15
(5) GMC-4	(5) GDC-4
(5) GMC-5	(5) GDC-5
(5) GMC-6.3	
	(5) GDB-630mA (5) GDB-2 (5) GDB-3.15 (5) GDB-4 (5) GMC-500mA (5) GMC-750mA (5) GMC-1 (5) GMC-2 (5) GMC-2.5 (5) GMC-3.15 (5) GMC-3.15 (5) GMC-4 (5) GMC-5

- (1) HTB-28M panel mount fuse holder
- (1) FP-A3 Fuse puller

Clip Clamps and Rail Adapters (DIN & American)

TRON™ Clip-Clamps

Specifications
Description: Clamps
for ferrule and bladetype cartridge fuse
clips. Provide tight
contacts between fuse
holder clips and fuse
ferrules/blades.





Construction:


Phenolic knob and plated-steel jaws.

Catalog Numbers

Catalog	Clamp Size		
Numbers	Volts	Amps	
NO.1	250	0-30	
NO.2	250	35-60	
NO.2	600	0-30	
NO.4	600	35-60	
NO.5	250/600	70-100	
NO.6	250/600	110-200	
NO.7	250/600	225-400	
NO.8	250/600	450-600	

Adapters for DIN and American Rails

Specifications
Description: Cooper
Bussmann® DIN rail
adapters permit secure,
positive snap-on mounting
of Cooper Bussmann 0-30A
fuse blocks (one-, two-, or
three-pole) onto various
size rails to eliminate
costly and time consuming
drilling, tapping, and screw
mounting. Adapters
mechanically lock into



With the exception of the 32mm DIN rail, all blocks with adapters can be removed from a rail simply by pulling up its release tab.

Use of rail end-stops on both sides of adapters is recommended.

Construction: Molded from "Lexan™ 241" for high strength and flexibility.

Catalog Numbers (For 0-30A Fuse Blocks)

Catalog	Fuse Block	•	•	Adapter
Numbers	Class	Rail Type	Size	Color
DRA-1	CC	DIN	15mm (Sym.)	Black
	G		32mm (Asym.)	
	*H (250V)		35mm (Sym.)	
DRA-2	*R (250)	American	17/4" (Sym.)	Gray
	M Type		(also 35mm DIN)	

Package Quantities: standard—10; bulk—100 (Cat. No. BK/DRA-1 or BK/DRA-2.)

*Mounting on 15mm rails is not recommended

NOTE—Newer Cooper Bussmann fuse blocks have elongated block-to-adapter mounting



Spare Fuse Holders, Pullers, Testers and Cabinets

Spare Fuse Holders



Specifications

Description: Spare fuse holders durably constructed using black thermoplastic with common mounting using #6 screws or bolts on 5-inch centers. Dovetailed interlocking between fuse holders simplifies installation and reduces needed hardware. Common footprint allows for any combination of fuse holders to be mounted together. Built-in retaining clips secure fuses.

Flammability Rating: UL 94V0.

Catalog Numbers

C	atalog	

Numbers	Capacity	For Use With:
TPSFH-CW	4-position	TPC and/or TPW fuses
TPSFH-M	4-position	TPM fuses
TPSFH-70	12-position	Series 70 fuses
TPSFH-LC	1-position	TPL-C series fuses
TPSFH-LB	1-position	TPL-B series fuses
TPSFH-N60	1-position	TPN (35-60A) fuses
TPSFH-N30	4-position	TPN (1-30A) fuses
TPSFH-AS	6-position	TPA & TPS fuses
TPSFH-T	10-position	GMT fuses

5TPH



Specifications

Description: 5-position spare fuse holder for midget size and Class CC fuses (13½2" diameter) fuses. Constructed of thermoplastic with adhesive tape on back for easy mounting on cabinet doors.

Size: 2.98" W x 1.03" H x 0.63" D

Catalog Number: 5TPH

Data Sheet: 5014

Fuse Pullers



Specifications

Description: Fuse pullers in various sizes to safely and easily extract fuses from blocks and holders.

Catalog Numbers

Catalog Numbers	Application
FP-2	13/2" to 13/6" dia. fuses
FP-3	1" to 1 ¾" dia. fuses
FP-4	1 ¾" to 2 ½" dia. fuses
FP-6	0-60A T-Tron fuses
FP-A3	Glass Tube & ATC fuses
Fuse pullers are only to be use has been de-energized.	d when the associated circuit

FT-2 Fuse Tester



Specifications

Description: Fuse tester for automotive, glass tube and ferrule fuses up to 1½" length. Probe slides to appropriate fuse length. Batteries are included and replaceable.

WARNING: **DO NOT** test electrical fuses in the fuse panel.

Catalog Number: FT-2

Replacement Battery:

Rayovac 364

SFC Spare Fuse Cabinet



Specifications

Description: Spare fuse cabinet with five cubic feet of storage space. Constructed of heavy gauge steel with durable baked ASA 61 grey enamel finish. Cabinet door is equipped with locking handle for security. Mounting holes are 16 inches on center with with key slots.

Size: 24" W x 30" H x 12" D Material: 0.062 sheet steel

Catalog Numbers:

SFC-FUSE-CAB

SFC-SHELF*
Extra shelf for fuse cabinet.

Data Sheet: 1119

FT-3 Fuse Tester



Specifications

Description: Fuse tester for automotive, glass tube and ferrule fuses up to 1½" length. Probe slides to appropriate fuse length. Batteries are included and replaceable.

WARNING: **DO NOT** test electrical fuses in the fuse panel.

Catalog Number: FT-3



Fuse Reducers and Dummy "Neutrals"





Fuse Reducers for Class J Dimension Fuses: LPJ, DFJ, JKS

Catalog Numbers

Numbers (Pair) Reducer No.	Fuse Amp Size Range	Equipment/Fuseblock Amp Size
J-63	1-30	60
J-13	1-30	100
J-16	35-60	100
J-26	35-60	200†
J-21	70-100	200†
J-41	70-100	400†
J-42	110-200	400†
J-62	110-200	600†
J-64	225-400	600†

†Not for Bolt-on Applications.

Fuse Reducers for Class R Dimension Fuses: FRN-R, LPN-RK, FRS-R, LPS-RK KTN-R, KTS-R

UL Listed File E12853

Catalog Numbers Catalog Numbers (Pairs)

Voltages		Fuse	Equipment/Fuseblock
250V	600V	Amp Size Range	Amp Size
NO.263-R	NO.663-R	1-30	60
NO.213-R	NO.216-R	1-30	100
NO.216-R	NO.616-R	35-60	100
NO.226-R	NO.626-R	35-60	200
NO.2621-R*	NO.2621-R	70-100	200
NO.2641-R	NO.2641-R	70-100	400
NO.242-R	NO.642-R	110-200	400
NO.2661-R	NO.2661-R	70-100	600
NO.2662-R	NO.2662-R	110-200	600
NO.2664-R**	NO.2664-R**	225-400	600
*Reducer NO 2621	-R does not apply to	LPN-RK-70SP to LPN	J-RK-100SP Fuses

^{*}Reducer NO.2621-R does not apply to LPN-RK-70SP to LPN-RK-100SP Fuses.
**Single reducer only (pair not required).

Fuse Reducers for Class H & K Dimension Fuses: NON, REN, NOS, RES

UL Listed File E12853

Catalog Numbers

Catalog Numbers. (Pairs)			Equipment/
250V	600V	Fuse	Fuseblock
Reducer	Reducer	Amp Size Range	Amp Size
NO.263	NO.663	1-30	60
NO.213	NO.216	1-30	100
NO.216	NO.616	35-60	100
NO.226	NO.626	35-60	200
NO.2621	NO.2621	70-100	200
NO.2641	NO.2641	70-100	400
NO.2642	NO.2642	110-200	400

Data Sheet: 1118



Dummy Fuse "Neutrals" (These are not fuses)

Catalog Numbers

	Fuse Equivalent		
Catalog			Fuse
Numbers	Voltage	Dimension	Amp Size Range
NNB	_	13/32" x 11/2"	_
NNB-R	_	Class CC	_
NNC	_	¼" x 1¼"	_
NTN-R-30	250	R/H	1-30
NTN-R-60	250	R/H	35-60
NTN-R-100	250	R/H	70-100
NTN-R-200	250	R/H	110-200
NTN-R-400	250	R/H	225-400
NTS-R-30	600	R/H	1-30
NTS-R-60	600	R/H	35-60
NTS-R-100	600	R/H	70-100
NTS-R-200	600	R/H	110-200
NTS-R-400	600	R/H	225-400
NTS-R-600	600	R/H	450-600





Cooper Bussmann Services

Electrical System Arc Flash Analysis and Training to Help Make Electrical Safety No Accident

COOPER Bussmann